



BIF-V型 小型(精密滚珠丝杠) 预压型

DN值

100000



公称型号	丝杠轴 外 径 d	导程 Ph	钢球 中心直径 dp	沟槽谷径 dc	负荷 圈数 列×圈	基本额定载荷		刚性 K N/μm
						Ca kN	C _{0a} kN	
BIF 1604V-5	16	4	16.5	13.8	1×2.5	4.3	8.7	298
BIF 1605V-5	16	5	16.75	13.2	1×2.5	7.4	13.9	330
BIF 2004V-5	20	4	20.5	17.8	1×2.5	4.8	10.9	360
BIF 2004V-10	20	4	20.5	17.8	2×2.5	8.6	21.8	692
BIF 2005V-5	20	5	20.75	17.2	1×2.5	8.3	17.5	390
BIF 2005V-10	20	5	20.75	17.2	2×2.5	15.1	35	762
BIF 2010V-5	20	10	20.75	17.2	1×2.5	8.3	17.6	394
BIF 2504V-5	25	4	25.5	22.8	1×2.5	5.2	13.7	426
BIF 2504V-10	25	4	25.5	22.8	2×2.5	9.5	27.4	824
BIF 2505V-5	25	5	25.75	22.2	1×2.5	9.2	21.9	470
BIF 2505V-10	25	5	25.75	22.2	2×2.5	16.7	43.9	910
BIF 2506V-5	25	6	26	21.4	1×2.5	12.4	27.4	482
BIF 2506V-10	25	6	26	21.4	2×2.5	22.6	54.8	934
BIF 2805V-5	28	5	28.75	25.2	1×2.5	9.7	24.6	520
BIF 2805V-10	28	5	28.75	25.2	2×2.5	17.5	49.2	1000
BIF 2806V-5	28	6	28.75	25.2	1×2.5	9.6	24.6	520
BIF 2806V-10	28	6	28.75	25.2	2×2.5	17.5	49.2	1000
BIF 3205V-5	32	5	32.75	29.2	1×2.5	10.2	28.1	570
BIF 3205V-10	32	5	32.75	29.2	2×2.5	18.5	56.3	1110
BIF 3206V-5	32	6	33	28.4	1×2.5	13.9	35.2	600
BIF 3206V-10	32	6	33	28.4	2×2.5	25.2	70.3	1150



单位: mm

	螺母尺寸							丝杠轴的 惯性力矩/mm	螺母 质量	轴 质量	最大容许 转速
	外径 D	法兰直径 D ₁	全长 L ₁	H	B ₁	PCD	d ₁ ×d ₂ ×h A	kg·m ² /mm	kg	kg/m	min ⁻¹
	36	59	53	11	42	47	5.5×9.5×5.5 M6	5.05×10 ⁻⁸	0.42	1.42	5000
	40	60	56	10	46	50	4.5×8×4.5 M6	5.05×10 ⁻⁸	0.56	1.37	5000
	40	63	49	11	38	51	5.5×9.5×5.5 M6	1.23×10 ⁻⁷	0.43	2.22	4870
	40	63	73	11	62	51	5.5×9.5×5.5 M6	1.23×10 ⁻⁷	0.55	2.22	4870
	44	67	56	11	45	55	5.5×9.5×5.5 M6	1.23×10 ⁻⁷	0.57	2.19	4810
	44	67	86	11	75	55	5.5×9.5×5.5 M6	1.23×10 ⁻⁷	0.79	2.19	4810
	46	74	90	15	75	59	5.5×9.5×5.5 M6	1.23×10 ⁻⁷	1.06	2.46	4810
	46	69	48	11	37	57	5.5×9.5×5.5 M6	3.01×10 ⁻⁷	0.55	3.6	3920
	46	69	72	11	61	57	5.5×9.5×5.5 M6	3.01×10 ⁻⁷	0.66	3.6	3920
	50	73	55	11	44	61	5.5×9.5×5.5 M6	3.01×10 ⁻⁷	0.75	3.52	3880
	50	73	85	11	74	61	5.5×9.5×5.5 M6	3.01×10 ⁻⁷	0.96	3.52	3880
	53	76	62	11	51	64	5.5×9.5×5.5 M6	3.01×10 ⁻⁷	0.9	3.43	3840
	53	76	98	11	87	64	5.5×9.5×5.5 M6	3.01×10 ⁻⁷	1.22	3.43	3840
	55	85	59	12	47	69	6.6×11×6.5 M6	4.74×10 ⁻⁷	0.98	4.35	3470
	55	85	89	12	77	69	6.6×11×6.5 M6	4.74×10 ⁻⁷	1.34	4.35	3470
	55	85	68	12	56	69	6.6×11×6.5 M6	4.74×10 ⁻⁷	1.09	4.52	3470
	55	85	104	12	92	69	6.6×11×6.5 M6	4.74×10 ⁻⁷	1.52	4.52	3470
	58	85	56	12	44	71	6.6×11×6.5 M6	8.08×10 ⁻⁷	0.94	5.89	3050
	58	85	86	12	74	71	6.6×11×6.5 M6	8.08×10 ⁻⁷	1.31	5.89	3050
	62	89	63	12	51	75	6.6×11×6.5 M6	8.08×10 ⁻⁷	1.21	5.88	3030
	62	89	99	12	87	75	6.6×11×6.5 M6	8.08×10 ⁻⁷	1.75	5.88	3030

注) 安装QZ自润滑器时, 螺母全长尺寸会增加。详细内容请参照■15-380。

关于公称型号的构成, 请参照■15-258。