

Model No.

LM Guide Actuator

Model No.	Ball screw lead	Inner block type	QZ specification	Stroke	Accuracy grade
SKR33	10	A	QZ	0270	P
①	②	③	④	⑤	⑥
SKR20	01: 1 mm	A	No symbol : No QZ	0020: 20 mm	No symbol: Normal grade
SKR26	02: 2 mm	B	QZ	0025: 25 mm	H: High accuracy grade
SKR33	06: 6 mm	C	QZA	}	P: Precision grade
SKR46	10: 10 mm	D	QZB	1490: 1490 mm	
SKR55	20: 20 mm		QZAD		
SKR65	25: 25 mm				

KR15
KR20
KR26
KR30H
KR33
KR45H
KR46
KR55
KR65

QZ specification ④ can be selected on the following models.

SKR33 (→ **A2-38**)

SKR46 (→ **A2-46**)

KR33 (→ **A2-158**)

KR46 (→ **A2-174**)

KR55 (→ **A2-182**)

KR65 (→ **A2-188**)

*It cannot be selected for SKR20, SKR26, SKR55, SKR65, KR15, KR20, KR26, KR30H and KR45H.

If QZ, QZA, QZB, or QZAD is selected for QZ specification ④, specify a stroke incorporating QZ.

(→ **A2-65**, **A2-193**)

If "2: with a bellows" has been selected for Cover ⑧, specify a stroke incorporating the bellows.

(→ **A2-76**, **A2-204**)

The available ball screw leads differ depending on the model.

SKR20: "01," "06"

SKR26: "02," "06"

SKR33: "06," "10," "20" (20 mm available for inner block A and B only)

SKR46: "10," "20"

SKR55: "20," "30," "40"

SKR65: "20," "25," "30," "50"

KR15: "01," "02"

KR20: "01," "06"

KR26: "02," "06"

KR30H: "06," "10"

KR33: "06," "10"

KR45H: "10," "20"

KR46: "10," "20"

KR55: "20"

KR65: "25"

	With/without a motor		Cover	Sensor	Housing A/ Intermediate flange
	0	-	1	B	AQ
	⑦		⑧	⑨	⑩

With direct coupling
0: Direct coupling (without motor)
1: Direct coupling (THK will purchase and mount the motor you specify)
With motor wrap
R1: Non-standard side wrap (without motor)
R2: Standard side wrap (without motor)
R3: Bottom side wrap (without motor)
R4: Non-standard side wrap (THK will purchase and mount the motor you specify)
R5: Standard side wrap (THK will purchase and mount the motor you specify)
R6: Bottom side wrap (THK will purchase and mount the motor you specify)

0: Without cover
1: With cover
2: With bellows

0: None
1
2
6
7
B
E
H
L
J
M

With direct coupling	With motor wrap
A0	WN-05D
AN	WP-08D
AP	WP-08K
AQ	WP-08M
AR	WQ-08D
AS	WQ-08K
AT	WQ-08M
AU	WV-14M
AV	WY-11M
AY	WY-14M
AZ	WZ-16M
A5	WZ-19M
A6	W5-19M
10	
20	
30	
40	
60	

If QZ specification ④ "QZ," "QZA," "QZB," or "QZAD" is selected, "2: With bellows" cannot be selected.

10, 30, and 40 are only available for the KR.

If "0" is selected:

No coupling will be attached. Please specify if a coupling is required when ordering.

If "R1," "R2," or "R3" is selected:

A timing pulley and timing belt will be included.

If "1," "R4," "R5," or "R6" is selected:

The designated motor will be mounted. Please specify the motor cable direction separately.

Please select an option for ⑩ Housing A/Intermediate flange that matches the specified motor.

This product is compatible with motors from various manufacturers. Contact THK for details.

⑦ Motor wrap direction

