


# Model D20



Unit: mm

Rail length L (±0.8)	Stroke S (±3)	Mounting hole dimensions			Permissible load N/pair	Mass [g/pair]
		A±0.3	B±0.3	n (pcs)		
80	80	50.0	—	2	20	94
100	100	70.0	—	2	30	118
150	160	60.0	120.0	3	80	179
200	223	85.0	170.0	3	140	241
300	345	135.0	270.0	3	145	364

Note) The Permissible Load and Mass each indicate when used as a pair of 2 units.

## Model number coding

### D20 +300L

Model number    Overall rail length (mm)