


## SK型



单位: mm

| 公称型号  | 主要尺寸 |     |    |    |     |                |            |            |     |    |    |         |                | 质量<br>g |
|-------|------|-----|----|----|-----|----------------|------------|------------|-----|----|----|---------|----------------|---------|
|       | H    | W   | L  | B  | S   | 安装<br>螺栓<br>型号 | h<br>±0.02 | A<br>±0.05 | b   | g  | l  | 轴径<br>d | 锁紧<br>螺栓<br>型号 |         |
| SK 10 | 32.8 | 42  | 14 | 32 | 5.5 | M5             | 20         | 21         | 5   | 6  | 18 | 10      | M4             | 24      |
| SK 12 | 37.5 | 42  | 14 | 32 | 5.5 | M5             | 23         | 21         | 5   | 6  | 20 | 12      | M4             | 30      |
| SK 13 | 37.5 | 42  | 14 | 32 | 5.5 | M5             | 23         | 21         | 5   | 6  | 20 | 13      | M4             | 30      |
| SK 16 | 44   | 48  | 16 | 38 | 5.5 | M5             | 27         | 24         | 5   | 8  | 25 | 16      | M4             | 40      |
| SK 20 | 51   | 60  | 20 | 45 | 6.6 | M6             | 31         | 30         | 7.5 | 10 | 30 | 20      | M5             | 70      |
| SK 25 | 60   | 70  | 24 | 56 | 6.6 | M6             | 35         | 35         | 7   | 12 | 38 | 25      | M6             | 130     |
| SK 30 | 70   | 84  | 28 | 64 | 9   | M8             | 42         | 42         | 10  | 12 | 44 | 30      | M6             | 180     |
| SK 35 | 83   | 98  | 32 | 74 | 11  | M10            | 50         | 49         | 12  | 15 | 50 | 35      | M8             | 270     |
| SK 40 | 96   | 114 | 36 | 90 | 11  | M10            | 60         | 57         | 12  | 15 | 60 | 40      | M8             | 420     |

注)SK型安装螺栓的支承面有进行沉孔加工。