


MBF型(轴端未加工品)

DN值

70000



公称型号	滚珠丝杠驱动型							螺母			
	丝杠轴 外径	导程	钢球 中心直径	沟槽直径	负荷 圈数	基本额定载荷		外径	法兰直径	全长	螺母
						Ca	C _{0a}				
d	Ph	dp	dc	列×圈	kN	kN	D	D _f	L _t	H	
MBF 0401-3.7	4	1	4.15	3.3	1×3.7	0.59	0.93	11	24	18	4
MBF 0601-3.7	6	1	6.15	5.3	1×3.7	0.74	1.5	13	30	21	5
MBF 0802-3.7	8	2	8.3	6.6	1×3.7	2.5	4.2	20	40	28	6
MBF 1002-3.7	10	2	10.3	8.6	1×3.7	2.8	5.3	23	43	28	6
MBF 1202-3.7	12	2	12.3	10.6	1×3.7	3	6.5	25	47	30	8
MBF 1402-3.7	14	2	14.3	12.6	1×3.7	3.3	7.5	26	48	30	8
MBF 1404-3.7	14	4	14.3	11.8	1×3.7	5.7	11.1	30	54	38	8

公称型号的构成例

MBF0802-3.7 RR GT +218L C5 A

公称型号

轴向间隙标记(※2)


精度标记(※3)

轴端未加工品标记

密封圈标记(※1)

丝杠轴总长度(单位mm)

(※1)参照A15-380。(※2)参照A15-19。(※3)参照A15-12。



单位: mm

尺寸							丝杠轴尺寸										螺母质量 kg	轴质量 kg/m	容许转速 min ⁻¹
B ₁	PCD	d ₁	d ₂	h	T _w	轴端未加工标记	全长 L	l ₀	l ₁	l ₂	l ₃	d ₃	d ₄	K	kg	kg/m			
14	17	3.4	6.5	2.5	13	A	90	48	10	30	50	4.3	3.2	2	0.02	0.07	3500		
							110	68			70								
							130	88			90								
16	21.5	3.4	6.5	3	17	A	131	58	20	50	61	6.3	5.2	3	0.04	0.14	3500		
							161	88			91								
							201	128			131								
22	30	4.5	8	4	24	A	168	85	25	55	88	8.3	6.2	3	0.1	0.19	3500		
							193	110			113								
							218	135			138								
22	33	4.5	8	4	27	A	183	95	25	60	98	10.3	8.2	3	0.11	0.36	3500		
							223	135			138								
							273	185			188								
22	36	5.5	9.5	5.5	29	A	210	117	30	60	120	12.3	10.2	3	0.15	0.58	3500		
							235	142			145								
							285	192			195								
22	37	5.5	9.5	5.5	32	A	205	102	40	60	105	14.3	12.2	3	0.16	0.85	3500		
							245	142			145								
							295	192			195								
							345	242			245								
30	42	5.5	9.5	5.5	34	A	233	129	40	60	133	14.3	11.2	4	0.25	1.2	3500		
							293	189			193								
							353	249			253								
							413	309			313								

注)MBF型标准规格无密封垫片。需要带密封垫片时,请咨询THK。