


## BIF型(轴端未加工品)

DN值

70000



公称型号	滚珠丝杠驱动型							螺母			
	丝杠轴 外径	导程	钢球 中心直径	沟槽谷径	负荷 圈数	基本额定载荷		外径	法兰直径	全长	螺母
						Ca	Coa				
d	Ph	dp	dc	列×圈	kN	kN	D	D <sub>1</sub>	L <sub>1</sub>	H	
BIF 2510A-5	25	10	26.3	21.4	1×2.5	15.8	33	58	85	100	18
BIF 2806-5 BIF 2806-10	28	6	28.75	25.2	1×2.5 2×2.5	9.6 17.5	24.6 49.4	55	85	68 104	12
BIF 3205-5 BIF 3205-10	32	5	32.75	29.2	1×2.5 2×2.5	10.2 18.5	28.1 56.4	58	85	56 86	12

## 公称型号的构成例

**BIF2806-10 RR G0 +1020L C5 A**

公称型号

轴间间隙标记(※2)

精度标记(※3)


轴端未加工品标记(A或者B)

密封圈标记(※1)

丝杠轴总长度(单位mm)

(※1)参照▲15-380。(※2)参照▲15-19。(※3)参照▲15-12。

## 轴端未加工品精密滚珠丝杠



单位：mm

尺寸							丝杠轴尺寸							螺母 质量 kg	轴 质量 kg/m	容许 转速 min <sup>-1</sup>
B <sub>1</sub>	PCD	d <sub>1</sub>	d <sub>2</sub>	h	润滑孔 A	轴端 未加工 标记	全长 L	l <sub>0</sub>	l <sub>1</sub>	l <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>				
82	71	6.6	11	6.5	M6	A	620	400	60	160	25	20.3	1.87	2.68	2660	
							820	600								
							1020	800								
							1220	1000								
							1420	1200								
56 92	69	6.6	11	6.5	M6	A	520	300	60	160	28	20.3	1 1.57	3.89	2430	
							620	400								
							720	500								
							920	700								
							1020	800								
							1220	1000								
						1420	1200									
						B	720	400	70	250	28	24.8				
							920	500		350						
							1100	700		330						
44 74	71	6.6	11	6.5	M6	A	730	500	70	160	32	25.3	0.87 1.32	5.03	2130	
							930	700								
							1230	1000								
							1430	1200								
							1630	1400								
							1830	1600								
											27.8					

滚珠丝杠