


轴端完成品精密滚珠丝杠



滚珠丝杠规格			
导程 (mm)	10		
BCD (mm)	15.75		
沟槽谷径 (mm)	12.5		
螺旋线向、条数	右, 2		
圈数	2.8圈×2列		
间隙标记	G0	GT	G2
轴向间隙 (mm)	0	0.005以下	0.02以下
基本动额定载荷Ca (kN)	9	14.3	14.3
基本静额定载荷C0a (kN)	13.9	27.9	27.9
预压扭矩 (N·m)	2×10 ⁻² ~9.8×10 ⁻²	—	—
间隔钢球	1 : 1	无	无
刚性值 (N/μm)	190	350	
循环方式	端盖		

单位：mm

	丝杠轴	螺母	法兰安装面	螺纹沟槽面	导程精度		螺母 质量 kg	轴 质量 kg/m	容许 转速 min ⁻¹
	轴心的振摆	外圆面的振摆	的振摆	的振摆	代表运行距离 误差	变动			
	0.035	0.015	0.011	0.012	±0.023	0.018	0.22	0.76	4440
	0.055	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440
	0.035	0.015	0.011	0.012	±0.023	0.018	0.22	0.76	4440
	0.055	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440
	0.04	0.015	0.011	0.012	±0.025	0.02	0.22	0.76	4440
	0.06	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440
	0.04	0.015	0.011	0.012	±0.025	0.02	0.22	0.76	4440
	0.06	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440
	0.05	0.015	0.011	0.012	±0.027	0.02	0.22	0.76	4440
	0.075	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440
	0.05	0.015	0.011	0.012	±0.027	0.02	0.22	0.76	4440
	0.075	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440
	0.05	0.015	0.011	0.012	±0.03	0.023	0.22	0.76	4440
	0.075	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440
	0.065	0.015	0.011	0.012	±0.03	0.023	0.22	0.76	4440
	0.09	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440
	0.065	0.015	0.011	0.012	±0.035	0.025	0.22	0.76	4440
	0.09	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440
	0.065	0.015	0.011	0.012	±0.035	0.025	0.22	0.76	4440
	0.09	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440
	0.085	0.015	0.011	0.012	±0.035	0.025	0.22	0.76	4440
	0.12	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440
	0.085	0.015	0.011	0.012	±0.04	0.027	0.22	0.76	4440
	0.12	0.03	0.018	0.014	运行距离误差: ±0.05/300		0.22	0.76	4440

滚珠丝杠