


DK型(精密滚珠丝杠) 无预压型


DN值

70000



DK2504~2510

公称型号	丝杠轴 外 径 d	导程 Ph	钢球 中心直径 dp	沟槽谷径 dc	负荷 圈数 列×圈	基本额定载荷		刚性 K N/μm
						Ca kN	C0a kN	
DK 2504-3	25	4	25.5	22.8	3×1	5.7	15	230
DK 2504-4	25	4	25.5	22.8	4×1	7.4	19.9	310
DK 2505-3	25	5	25.75	22.1	3×1	9.7	22.6	250
DK 2505-4	25	5	25.75	22.1	4×1	12.4	30.3	320
DK 2506-3	25	6	26	21.4	3×1	12.8	27	250
DK 2506-4	25	6	26	21.4	4×1	16.8	37.4	330
DK 2508-3	25	8	26	21.4	3×1	13.1	28.1	500
DK 2508-4	25	8	26	21.4	4×1	16.8	37.5	330
DK 2510-3	25	10	26	21.6	3×1	12.7	27	250
DK 2510-4	25	10	26	21.6	4×1	16.7	37.6	330
DK 2805-3	28	5	28.75	25.2	3×1	10.5	26.4	270
DK 2805-4	28	5	28.75	25.2	4×1	13.4	35.2	360
DK 2806-3	28	6	29	24.4	3×1	14	32	280
DK 2806-4	28	6	29	24.4	4×1	18	42.5	370
DK 2810-4	28	10	29.25	23.6	4×1	22.4	50	370



DK2805~2810

单位: mm

	螺母尺寸										丝杠轴的 惯性力矩/mm kg·m ² /mm	螺母 质量 kg	轴 质量 kg/m	容许 转速 min ⁻¹
	外径	法兰直径	全长							润滑孔				
	D	D ₁	L ₁	H	B ₁	B ₂	PCD	d ₁ ×d ₂ ×h	Tw	A				
	38	63	43	11	32	10	51	5.5×9.5×5.5	39	M6	3.01×10 ⁻⁷	0.33	3.5	2740
	38	63	47	11	36	10	51	5.5×9.5×5.5	39	M6	3.01×10 ⁻⁷	0.35	3.5	2740
	40	63	46	11	35	10	51	5.5×9.5×5.5	41	M6	3.01×10 ⁻⁷	0.38	3.35	2710
	40	63	51	11	40	10	51	5.5×9.5×5.5	41	M6	3.01×10 ⁻⁷	0.41	3.35	2710
	40	63	52	11	41	10	51	5.5×9.5×5.5	41	M6	3.01×10 ⁻⁷	0.41	3.19	2690
	40	63	60	11	49	10	51	5.5×9.5×5.5	41	M6	3.01×10 ⁻⁷	0.46	3.19	2690
	40	63	62	12	50	10	51	5.5×9.5×5.5	41	M6	3.01×10 ⁻⁷	0.48	3.35	2690
	40	63	71	12	59	15	51	5.5×9.5×5.5	41	M6	3.01×10 ⁻⁷	0.54	3.35	2690
	40	63	80	15	65	15	51	5.5×9.5×5.5	41	M6	3.01×10 ⁻⁷	0.62	3.45	2690
	40	63	85	15	70	20	51	5.5×9.5×5.5	41	M6	3.01×10 ⁻⁷	0.65	3.45	2690
	43	71	49	12	37	10	57	6.6×11×6.5	55	M6	4.74×10 ⁻⁷	0.48	4.27	2430
	43	71	54	12	42	10	57	6.6×11×6.5	55	M6	4.74×10 ⁻⁷	0.51	4.27	2430
	43	71	53	12	41	10	57	6.6×11×6.5	55	M6	4.74×10 ⁻⁷	0.5	4.36	2410
	43	71	61	12	49	10	57	6.6×11×6.5	55	M6	4.74×10 ⁻⁷	0.56	4.36	2410
	45	71	84	15	69	20	57	6.6×11×6.5	55	M6	4.74×10 ⁻⁷	0.82	4.18	2390

注) 安装QZ自润滑器时, 螺母全长尺寸会增加。详细内容请参照■15-390。

关于公称型号的构成, 请参照■15-262。