



WHF型(精密滚珠丝杠) 无预压型

DN值

120000




WHF1530/1540/2020/2025/
2030/2040/2550



WHF2525

公称型号	丝杠轴 外径 d	导程 Ph	钢球 中心直径 dp	沟槽谷径 dc	负荷 圈数 列×圈	基本额定载荷		刚性 K N/μm			
						Ca kN	Coa kN		外径 D	法兰直径 D ₁	全长 L ₁
WHF 1530-3.4	15	30	15.75	12.5	2×1.7	8	14.4	195	32	53	64.5
WHF 1540-3.4	15	40	15.75	12.5	2×1.7	7.7	16.3	209	34	57	81.6
WHF 2020-3.4	20	20	20.75	17.5	2×1.7	9.6	21	225	42	64	47.1
WHF 2025-3.4	20	25	20.75	17.6	2×1.7	9.8	22.3	236	39	62	56.2
WHF 2030-3.4	20	30	20.75	17.6	2×1.7	9.9	23.5	243	39	62	65.3
WHF 2040-3.4	20	40	20.75	17.5	2×1.7	9.6	20.3	256	37	57	82.7
WHF 2525-3.4	25	25	26	21.9	2×1.7	14.5	33.1	285	50	77	58.8
WHF 2550-3.4	25	50	26	21.9	2×1.7	14.4	31.9	323	45	69	103.3



单位: mm

螺母尺寸								丝杠轴的 惯性力矩/mm kg·m ² /mm	螺母 质量 kg	轴 质量 kg/m	容许 转速 min ⁻¹
	H	B ₁	PCD	d ₁	T _w	N ₁	润滑孔 A				
	10	47.5	43	5.5	33	5	M6	3.9×10^{-8}	0.38	1.26	5000
	10	64.6	45	5.5	40	5	M6	3.9×10^{-8}	0.48	1.28	5000
	10	24.1	53	5.5	46	5	M6	1.23×10^{-7}	0.49	2.25	5000
	10	33.2	50	5.5	46	5	M6	1.23×10^{-7}	0.51	2.26	5000
	10	43.3	50	5.5	46	5	M6	1.23×10^{-7}	0.55	2.28	5000
	10	65.7	47	5.5	38	5	M6	1.23×10^{-7}	0.58	2.34	5000
	12	31.3	63	6.6	56	6	M6	3.01×10^{-7}	0.65	3.52	4610
	12	79.3	57	6.6	46	6	M6	3.01×10^{-7}	0.72	3.66	4610

注)WHF型有可配备刷式密封圈的型号,使用时请咨询THK。

安装QZ自润滑器时,螺母全长尺寸会增加。详细内容请参照**■15-390**。

关于公称型号的构成,请参照**■15-262**。