



BIF-V型 小型(精密滾珠螺桿) 預壓型

DN值	10000
-----	-------



型號	螺桿軸 外徑 d	導程 Ph	滾珠 中心直徑 dp	溝槽谷徑 dc	負荷 回路數 列×圈	基本額定負荷		剛性 K N/μm
						Ca kN	Ca kN	
BIF 1604V-5	16	4	16.5	13.8	1×2.5	4.3	8.7	298
BIF 1605V-5	16	5	16.75	13.2	1×2.5	7.4	13.9	330
BIF 2004V-5	20	4	20.5	17.8	1×2.5	4.8	10.9	360
BIF 2004V-10	20	4	20.5	17.8	2×2.5	8.6	21.8	692
BIF 2005V-5	20	5	20.75	17.2	1×2.5	8.3	17.5	390
BIF 2005V-10	20	5	20.75	17.2	2×2.5	15.1	35	762
BIF 2010V-5	20	10	20.75	17.2	1×2.5	8.3	17.6	394
BIF 2504V-5	25	4	25.5	22.8	1×2.5	5.2	13.7	426
BIF 2504V-10	25	4	25.5	22.8	2×2.5	9.5	27.4	824
BIF 2505V-5	25	5	25.75	22.2	1×2.5	9.2	21.9	470
BIF 2505V-10	25	5	25.75	22.2	2×2.5	16.7	43.9	910
BIF 2506V-5	25	6	26	21.4	1×2.5	12.4	27.4	482
BIF 2506V-10	25	6	26	21.4	2×2.5	22.6	54.8	934
BIF 2805V-5	28	5	28.75	25.2	1×2.5	9.7	24.6	520
BIF 2805V-10	28	5	28.75	25.2	2×2.5	17.5	49.2	1000
BIF 2806V-5	28	6	28.75	25.2	1×2.5	9.6	24.6	520
BIF 2806V-10	28	6	28.75	25.2	2×2.5	17.5	49.2	1000
BIF 3205V-5	32	5	32.75	29.2	1×2.5	10.2	28.1	570
BIF 3205V-10	32	5	32.75	29.2	2×2.5	18.5	56.3	1110
BIF 3206V-5	32	6	33	28.4	1×2.5	13.9	35.2	600
BIF 3206V-10	32	6	33	28.4	2×2.5	25.2	70.3	1150



單位:mm

外徑 D	螺帽尺寸							螺桿軸的慣性 力矩/mm kg·m ² /mm	螺帽 質量 kg	軸 質量 kg/m	容許 轉速 min ⁻¹
	法蘭直徑 D ₁	全長 L ₁	H	B ₁	PCD	d ₁ ×d ₂ ×h	潤滑孔 A				
36	59	53	11	42	47	5.5×9.5×5.5	M6	5.05×10 ⁻⁸	0.42	1.42	5000
40	60	56	10	46	50	4.5×8×4.5	M6	5.05×10 ⁻⁸	0.56	1.37	5000
40	63	49	11	38	51	5.5×9.5×5.5	M6	1.23×10 ⁻⁷	0.43	2.22	4870
40	63	73	11	62	51	5.5×9.5×5.5	M6	1.23×10 ⁻⁷	0.55	2.22	4870
44	67	56	11	45	55	5.5×9.5×5.5	M6	1.23×10 ⁻⁷	0.57	2.19	4810
44	67	86	11	75	55	5.5×9.5×5.5	M6	1.23×10 ⁻⁷	0.79	2.19	4810
46	74	90	15	75	59	5.5×9.5×5.5	M6	1.23×10 ⁻⁷	1.06	2.46	4810
46	69	48	11	37	57	5.5×9.5×5.5	M6	3.01×10 ⁻⁷	0.55	3.6	3920
46	69	72	11	61	57	5.5×9.5×5.5	M6	3.01×10 ⁻⁷	0.66	3.6	3920
50	73	55	11	44	61	5.5×9.5×5.5	M6	3.01×10 ⁻⁷	0.75	3.52	3880
50	73	85	11	74	61	5.5×9.5×5.5	M6	3.01×10 ⁻⁷	0.96	3.52	3880
53	76	62	11	51	64	5.5×9.5×5.5	M6	3.01×10 ⁻⁷	0.9	3.43	3840
53	76	98	11	87	64	5.5×9.5×5.5	M6	3.01×10 ⁻⁷	1.22	3.43	3840
55	85	59	12	47	69	6.6×11×6.5	M6	4.74×10 ⁻⁷	0.98	4.35	3470
55	85	89	12	77	69	6.6×11×6.5	M6	4.74×10 ⁻⁷	1.34	4.35	3470
55	85	68	12	56	69	6.6×11×6.5	M6	4.74×10 ⁻⁷	1.09	4.52	3470
55	85	104	12	92	69	6.6×11×6.5	M6	4.74×10 ⁻⁷	1.52	4.52	3470
58	85	56	12	44	71	6.6×11×6.5	M6	8.08×10 ⁻⁷	0.94	5.89	3050
58	85	86	12	74	71	6.6×11×6.5	M6	8.08×10 ⁻⁷	1.31	5.89	3050
62	89	63	12	51	75	6.6×11×6.5	M6	8.08×10 ⁻⁷	1.21	5.88	3030
62	89	99	12	87	75	6.6×11×6.5	M6	8.08×10 ⁻⁷	1.75	5.88	3030

注)安裝潤滑裝置QZ時,螺帽全長尺寸會增加。詳細情況,請參閱▣15-378。
關於型號編號,參閱▣15-250。