



Ball Screw

THK General Catalog

Ball Screw

THK General Catalog

A Product Descriptions

Overview of THK Ball Screws.....	A 15-6
Selection Criteria	A 15-8
Flowchart for Selecting a Ball Screw.....	A 15-8
Accuracy of the Ball Screw.....	A 15-11
• Lead Angle Accuracy.....	A 15-11
• Accuracy of the Mounting Surface.....	A 15-14
• Axial Clearance.....	A 15-19
• Preload.....	A 15-20
Selecting a Screw Shaft.....	A 15-24
• Maximum Manufacturing Lengths of Screw Shafts.....	A 15-24
• Combinations of Shaft Diameter and Lead for Precision Ball Screws.....	A 15-26
• Combinations of Shaft Diameter and Lead for Rolled Ball Screws.....	A 15-27
Mounting Procedure for the Ball Screw Shaft.....	A 15-28
Permissible Axial Load.....	A 15-30
Permissible Rotational Speed.....	A 15-32
Advantages of Caged Ball Technology.....	A 15-35
• Types and Features.....	A 15-38
Selecting a Nut.....	A 15-41
• Types of Nuts.....	A 15-41
Selecting a Model Number.....	A 15-46
• Calculating the Axial Load.....	A 15-46
• Static Safety Factor.....	A 15-47
• Considering the Service Life.....	A 15-48
Considering the Rigidity.....	A 15-51
• Axial Rigidity of the Feed Screw System.....	A 15-51
Considering the Positioning Accuracy.....	A 15-55
• Causes of Error in the Positioning Accuracy.....	A 15-55
• Considering the Lead Angle Accuracy.....	A 15-55
• Considering the Axial Clearance.....	A 15-55
• Considering the Axial Rigidity in the Feed Screw System.....	A 15-57
• Considering the Thermal Displacement through Heat Generation.....	A 15-59
• Considering the Orientation Change during Travel.....	A 15-60
Considering the Rotational Torque.....	A 15-61
• Frictional Torque Due to an External Load.....	A 15-61
• Torque Due to a Preload on the Ball Screw.....	A 15-62
• Torque Required for Acceleration.....	A 15-63
• Considering the Strength of Ball Screw Shaft Ends.....	A 15-64
Considering the Driving Motor.....	A 15-66
• When Using a Servomotor.....	A 15-66
• When Using a Stepping Motor (Pulse Motor).....	A 15-68
Features of Each Model	A 15-69
Overview of THK Ball Screws	A 15-70
Positioning, ISO 3408 compliant	A 15-72
• Standard Combinations of Outer Diameters and Leads of the Screw Shafts.....	A 15-74

Dimensional Drawing, Dimensional Table

Models SDAN-V.....	A 15-76
Models SDA-V/SDA-VZ.....	A 15-82
Model EPB-V.....	A 15-94
Model EBB-V.....	A 15-98

Positioning Ball Screw..... A 15-102

- Standard Combinations of Outer
Diameters and Leads of the Screw Shafts .. A 15-108

Dimensional Drawing, Dimensional Table

Model SBN-V.....	A 15-112
Model SBK.....	A 15-116
Model SBKN.....	A 15-120
Model BIF-V.....	A 15-122
Model BIF.....	A 15-128
Model BNFN-V.....	A 15-136
Model BNFN.....	A 15-138
Model DIK.....	A 15-142
Model DKN.....	A 15-148
Model BLW.....	A 15-150
BNK0401-3 Shaft Diameter: 4; Lead: 1 ..	A 15-152
BNK0501-3 Shaft Diameter: 5; Lead: 1 ..	A 15-154
BNK0601-3 Shaft Diameter: 6; Lead: 1 ..	A 15-156
BNK0801-3 Shaft Diameter: 8; Lead: 1 ..	A 15-158
BNK0802-3 Shaft Diameter: 8; Lead: 2 ..	A 15-160
BNK0810-3 Shaft Diameter: 8; Lead: 10 ..	A 15-162
BNK1002-3 Shaft Diameter: 10; Lead: 2 ..	A 15-164
BNK1004-2.5 Shaft Diameter: 10; Lead: 4 ..	A 15-166
BNK1010-1.5 Shaft Diameter: 10; Lead: 10 ..	A 15-168
BNK1202-3 Shaft Diameter: 12; Lead: 2 ..	A 15-170
BNK1205-2.5 Shaft Diameter: 12; Lead: 5 ..	A 15-172
BNK1208-2.6 Shaft Diameter: 12; Lead: 8 ..	A 15-174
BNK1402-3 Shaft Diameter: 14; Lead: 2 ..	A 15-176
BNK1404-3 Shaft Diameter: 14; Lead: 4 ..	A 15-178
BNK1408-2.5 Shaft Diameter: 14; Lead: 8 ..	A 15-180
BNK1510-5.6 Shaft Diameter: 15; Lead: 10 ..	A 15-182
BNK1520-3 Shaft Diameter: 15; Lead: 20 ..	A 15-184
BNK1616-3.6 Shaft Diameter: 16; Lead: 16 ..	A 15-186
BNK2010-2.5 Shaft Diameter: 20; Lead: 10 ..	A 15-188
BNK2020-3.6 Shaft Diameter: 20; Lead: 20 ..	A 15-190
BNK2520-3.6 Shaft Diameter: 25; Lead: 20 ..	A 15-192
Model MDK.....	A 15-194
Model MBF.....	A 15-200
Model BNF-V.....	A 15-204
Model BNF.....	A 15-210
Model DK.....	A 15-222
Model WHF.....	A 15-230
Model BLK.....	A 15-232

Model WGF	A15-234	Maximum Manufacturing Lengths of Screw Shafts ..	A15-314
Model BNT	A15-236		
High-Thrust Ball Screw	A15-238	Ball Screw Peripherals	A15-317
• Standard Combinations of Outer			
Diameters and Leads of the Screw Shafts ..	A15-240		
• Examples of Assembling Models HBN-V, HBN-K, HBN-KA, HBN, and SBKH	A15-242		
Dimensional Drawing, Dimensional Table			
Model HBN-V	A15-244		
Models HBN-K and HBN-KA	A15-246		
Model HBN	A15-252		
Model SBKH	A15-254		
Transport Ball Screw	A15-256		
• Standard Combinations of Outer			
Diameters and Leads of the Screw Shafts ..	A15-258		
Dimensional Drawing, Dimensional Table			
Model JPF	A15-260		
Model BTK-V	A15-262		
Model BNT	A15-264		
Model BLK	A15-266		
Model WTF	A15-268		
Model CNF	A15-270		
Model MTF	A15-272		
Rotary Nut Ball Screw	A15-276		
• Standard Combinations of Outer			
Diameters and Leads of the Screw Shafts ..	A15-278		
• Accuracy Standards	A15-280		
• Assembly Examples	A15-285		
• Action Patterns	A15-287		
• Assembly Examples	A15-290		
• Example Application	A15-291		
• Lubrication	A15-292		
• Permissible Rotational Speeds for Rotary Ball Screws ..	A15-293		
Dimensional Drawing, Dimensional Table			
Model DIR	A15-294		
Model BLR	A15-296		
Model BNS-V	A15-300		
Model BNS-A	A15-302		
Model BNS	A15-304		
Model NS-V	A15-306		
Model NS-A	A15-308		
Model NS	A15-310		
• Ball Screw/Spline Permissible Rotational Speeds ..	A15-312		
		Support Unit	
		Models EK, BK, FK, EF, BF, and FF	A15-318
		• Structure and Features	A15-318
		• Types	A15-320
		• Types of Support Units and Applicable Screw Shaft Outer Diameters ..	A15-321
		• Model Numbers of Bearings and Characteristic Values ..	A15-322
		• Installation Example	A15-323
		• Mounting Procedure	A15-324
		• Types of Recommended Shapes for the Shaft Ends ..	A15-326
		Dimensional Drawing, Dimensional Table	
		Square Fixed-Side Support Unit Model EK ..	A15-328
		Square Fixed-Side Support Unit Model BK ..	A15-330
		Round Fixed-Side Support Unit Model FK ..	A15-332
		Square Supported-Side Support Unit Model EF ..	A15-336
		Square Supported-Side Support Unit Model BF ..	A15-338
		Round Supported-Side Support Unit Model FF ..	A15-340
		Recommended Shapes for Shaft Ends - Shape H (H1, H2, and H3) (For Support Unit Models FK and EK) ..	A15-342
		Recommended Shapes for Shaft Ends - Shape J (J1, J2, and J3) (For Support Unit Model BK)	A15-344
		Recommended Shapes for Shaft Ends - Shape K (For Support Unit Models FF, EF, and BF)	A15-346
		Nut Bracket (Model MC)	A15-348
		• Structure and Features	A15-348
		• Type	A15-348
		Dimensional Drawing, Dimensional Table	
		Nut Bracket	A15-349
		Lock Nut (Model RN)	A15-350
		• Structure and Features	A15-350
		• Types	A15-350
		Dimensional Drawing, Dimensional Table	
		Lock Nut	A15-351
		Options	A15-353
		Contaminaton Protection	A15-354
		Lubrication	A15-355
		Corrosion Resistance (Surface Treatment, etc.) ..	A15-355
		Contamination Protection Seal for Ball Screws ..	A15-356
		Wiper Ring W	A15-357
		Canvas Seal CC	A15-359

Dust Cover for Ball Screws.....	A 15-361
QZ Lubricator.....	A 15-362
Dimensions of Each Model with Options Attached ..	A 15-364
• Dimensions of the Ball Screw Nut with Wiper Ring W and QZ Lubricator Attached ..	A 15-364
• Ball Screw Nut Dimensions with Canvas Seal....	A 15-374
• Specifications of the Bellows	A 15-378
Model No.	A 15-379
• Model Number Coding.....	A 15-379
• Notes on Ordering.....	A 15-383
Handling Precautions	A 15-384
Handling Precautions for Optional Accessories for the Ball Screw..	A 15-386
• QZ Lubricator for the Ball Screw	A 15-386

B Support Book (Separate)

Features and Types	B 15-6
Features of the Ball Screw	B 15-6
• Driving Torque One Third that of a Sliding Screw ..	B 15-6
• Examples of Calculating Driving Torque	B 15-8
• Ensuring High Accuracy	B 15-9
• Capable of Micro Feeding	B 15-10
• High Rigidity without Backlash	B 15-11
• Capable of Fast Feed	B 15-12
Overview of THK Ball Screws	B 15-14
Selection Criteria	B 15-16
Flowchart for Selecting a Ball Screw	B 15-16
Accuracy of the Ball Screw	B 15-19
• Lead Angle Accuracy	B 15-19
• Accuracy of the Mounting Surface	B 15-22
• Axial Clearance	B 15-27
• Preload	B 15-28
• Example of Calculating the Preload Torque ..	B 15-31
Selecting a Screw Shaft	B 15-32
• Maximum Manufacturing Lengths of Screw Shafts ..	B 15-32
• Combinations of Shaft Diameter and Lead for Precision Ball Screws ..	B 15-34
• Combinations of Shaft Diameter and Lead for Rolled Ball Screws ..	B 15-35
Mounting Procedure for the Ball Screw Shaft ..	B 15-36
Permissible Axial Load	B 15-38
Permissible Rotational Speed	B 15-40
Selecting a Nut	B 15-43
• Types of Nuts	B 15-43
Selecting a Model Number	B 15-46
• Calculating the Axial Load	B 15-46
• Static Safety Factor	B 15-47
• Considering the Service Life	B 15-48
Considering the Rigidity	B 15-51
• Axial Rigidity of the Feed Screw System ..	B 15-51
Considering the Positioning Accuracy ..	B 15-55
• Causes of Error in the Positioning Accuracy ..	B 15-55
• Considering the Lead Angle Accuracy	B 15-55
• Considering the Axial Clearance	B 15-55
• Considering the Axial Rigidity in the Feed Screw System ..	B 15-57
• Example of considering the rigidity of a feed screw system ..	B 15-57
• Considering the Thermal Displacement through Heat Generation ..	B 15-59
• Considering the Orientation Change during Travel ..	B 15-60
Considering the Rotational Torque	B 15-61
• Frictional Torque Due to an External Load ..	B 15-61
• Torque Due to a Preload on the Ball Screw ..	B 15-62
• Torque Required for Acceleration	B 15-63
• Considering the Strength of Ball Screw Shaft Ends ..	B 15-64
Considering the Driving Motor	B 15-66
• When Using a Servomotor	B 15-66
• When Using a Stepping Motor (Pulse Motor) ..	B 15-68
Example Ball Screw Selections	B 15-69
• High-Speed Transfer Equipment (Horizontal Use) ..	B 15-69
• Vertical Conveyance System	B 15-83
Options	B 15-95
Contaminant Protection	B 15-96
Lubrication	B 15-97
Corrosion Resistance (Surface Treatment, etc.) ..	B 15-97
Contamination Protection Seal for Ball Screws ..	B 15-98
Wiper Ring W	B 15-99
Canvas Seal CC	B 15-101
Dust Cover for Ball Screws	B 15-103
QZ Lubricator	B 15-104
Mounting Procedure and Maintenance ..	B 15-106
Mounting Procedure	B 15-106
• Installing the Support Unit	B 15-106
• Installation onto the Table and the Base ..	B 15-106
• Checking the Accuracy and Fully Fastening the Support Unit ..	B 15-107
• Connection with the Motor	B 15-107
Maintenance Method	B 15-108
• Amount of Lubricant	B 15-108
Model No.	B 15-109
• Model Number Coding	B 15-109
• Notes on Ordering	B 15-113
Handling Precautions	B 15-114
Handling Precautions for Optional Accessories for the Ball Screw ..	B 15-116
• QZ Lubricator for the Ball Screw	B 15-116