Considering the Driving Motor

When selecting a driving motor required to rotate the ball screw, normally take into account the rotational speed, rotational torque, and minimum feed amount.

When Using a Servomotor

Rotational Speed

The rotation speed required for the motor is obtained using equation (52) based on the feed speed, ball screw lead, and reduction ratio.

$$N_{M} = \frac{V \times 1,000 \times 60}{Ph} \times \frac{1}{A} \quad \dots \dots \quad (52)$$

- N_M : Required rotation speed of the motor (min⁻¹)
- V : Feeding speed (m/s)
- Ph : Ball screw lead (mm)
- A : Reduction ratio

The rated rotational speed of the motor must be equal to or above the calculated value (N_{\mbox{\tiny M}}) above. N_{\mbox{\tiny M}} \leq N_{\mbox{\tiny R}}

 N_R : The rated rotation speed of the motor (min⁻¹)

Required Resolution

Resolutions required for the encoder and the driver are obtained using equation (53) based on the minimum feed amount, ball screw lead, and reduction ratio.

(mm)

- B : Resolution required for the encoder and the driver (p/rev)
- Ph : Ball screw lead
- A : Reduction ratio
- S : Minimum feed amount (mm)



Considering the Driving Motor

Motor Torque

The torque required for the motor differs between uniform motion, acceleration, and deceleration. To calculate the rotational torque, see "Considering the Rotational Torque" on **Δ15-61**.

a. Maximum torque

The maximum torque required for the motor must be equal to or below the maximum peak torque of the motor.

T_{max} ≦ Tp_{max}

- T_{max} : Maximum torque acting on the motor
- Tp_{max} : Maximum peak torque of the motor
- b. Effective torque value

The effective value of the torque required for the motor must be calculated. The effective value of the torque is obtained using equation (54).

- T_{ms} : Effective torque value (N⋅mm)
- T_n : Fluctuating torque (N·mm)
- t_n : Time during which the torque T_n is applied (s)

t : Cycle time

 $(t = t_1 + t_2 + t_3)$

The calculated effective value of the torque must be equal to or below the rated torque of the motor.

(s)

 $T_{\text{rms}} \leqq T_{\text{R}}$

 T_{R} : Rated torque of the motor (N·mm)

Inertial Moment

The inertial moment required for the motor is obtained using equation (55).

 $J_{\mbox{\scriptsize M}}$ $\,$: Inertial moment required for the motor (kg \cdot m^2)

C : Factor determined by the motor and the driver

(It is normally between 3 and 10. However, it varies depending on the motor and the driver. Check the specific value in the motor manufacturer's catalog.)

The inertial moment of the motor must be equal to or above the calculated $J_{\mbox{\tiny M}}$ value.



When Using a Stepping Motor (Pulse Motor)

Minimal Feed Amount (per Step)

The step angle required for the motor and the driver is obtained using equation (56) based on the minimum feed amount, ball screw lead, and reduction ratio.

- E : Step angle required for the motor and the driver (°)
- S : Minimum feed amount (mm) (per step)
- Ph : Ball screw lead (mm)
- A : Reduction ratio

Pulse Speed and Motor Torque

a. Pulse speed

The pulse speed is obtained using equation (57) based on the feed speed and the minimum feed amount.

Hz)

- V : Feeding speed (m/s)
- S : Minimum feed amount (mm)

b. Torque required for the motor

The torque required for the motor differs between the uniform motion, the acceleration and the deceleration. To calculate the rotational torque, see "Considering the Rotational Torque" on **Δ15-61**.

Thus, the pulse speed required for the motor and the required torque can be calculated in the manner described above.

Although the torque varies depending on the motors, normally the calculated torque should be doubled to ensure safety. Check if the torque can be used in the motor's speed-torque curve.

▲15-68 元光长