


SKR65 Without Cover, Motor Wrap

Model SKR65□□A (with a Single Long Block)

Model SKR65□□B (with Two Long Blocks)

For model number coding, see **A2-28**.



With bottom side motor wrap

Block details

B'-B' cross section

[†] Distance between the mechanical stopper and the stroke starting position.

Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L ₁ (mm)	C (mm)	G (mm)	F (mm)	H (mm)	n	n ₁	Overall main unit mass (kg)	
Type A	Type B [†]									Type A	Type B
790 (810)	640 (665)	980	1,078	900	40	800	90	7	5	31.9	34.9
990 (1,010)	840 (865)	1,180	1,278	1,050	65	1,000	90	8	6	37.1	40.1
1,190 (1,210)	1,040 (1,065)	1,380	1,478	1,200	90	1,200	90	9	7	42.3	45.3
1,490 (1,510)	1,340 (1,365)	1,680	1,778	1,500	90	1,600	40	11	9	50	53


[†] Indicates a value when two inner blocks are in close contact with each other.

SKR65 With Cover, Motor Wrap

Model SKR65□□A (with a Single Long Block)

Model SKR65□□B (with Two Long Blocks)

For model number coding, see **A2-28**.



With bottom side motor wrap

Sub-table details

B-B cross section

¹ Distance between the mechanical stopper and the stroke starting position.

Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L _r (mm)	C (mm)	G (mm)	F (mm)	H (mm)	n	n _r	Overall main unit mass (kg)	
Type A	Type B'									Type A	Type B
790 (810)	640 (665)	980	1,078	900	40	800	90	7	5	35.1	41.8
990 (1,010)	840 (865)	1,180	1,278	1,050	65	1,000	90	8	6	40.5	47.2
1,190 (1,210)	1,040 (1,065)	1,380	1,478	1,200	90	1,200	90	9	7	45.9	52.6
1,490 (1,510)	1,340 (1,365)	1,680	1,778	1,500	90	1,600	40	11	9	54	60.7

¹ Indicates a value when two inner blocks are in close contact with each other.