


KR33 Without Cover, Motor Wrap

Model KR33□□C (with a Single Short Block)

Model KR33□□D (with Two Short Blocks)

For model number coding, see **A2-136**.



¹ Distance between the mechanical stopper and the stroke starting position.

² This indicates the short block length when calculating the possible stroke range.

It is 97.2 mm (total) for a KR33 with two short blocks in close contact with each other (Type D, without QZ).

Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L_1 (mm)	C (mm)	G (mm)	P (mm)	F (mm)	H (mm)	n	n_1	Overall main unit mass (kg)	
Type C	Type D ¹										Type C	Type D
75 (87)	25 (36.5)	150	210	100	25	100	100	25	2	2	2	2.2
125 (137)	75 (86.5)	200	260	100	50	100	100	50	2	2	2.4	2.6
225 (237)	175 (186.5)	300	360	200	50	200	200	50	3	2	3.1	3.3
325 (337)	275 (286.5)	400	460	300	50	200	200	100	4	2	3.8	4
425 (437)	375 (386.5)	500	560	400	50	200	400	50	5	3	4.5	4.7
525 (537)	475 (486.5)	600	660	500	50	200	400	100	6	3	5.3	5.5
625 (637)	575 (586.5)	700	760	600	50	200	600	50	7	4	6	6.2


¹ Indicates a value when two inner blocks are in close contact with each other.

KR33 With Cover, Motor Wrap

Model KR33□□C (with a Single Short Block)

Model KR33□□D (with Two Short Blocks)

For model number coding, see **A2-136**.



¹ Distance between the mechanical stopper and the stroke starting position.

Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L_1 (mm)	C (mm)	G (mm)	P (mm)	F (mm)	H (mm)	n	n_1	Overall main unit mass (kg)	
Type C	Type D ¹										Type C	Type D
75 (87)	25 (36.5)	150	210	100	25	100	100	25	2	2	2.2	2.5
125 (137)	75 (86.5)	200	260	100	50	100	100	50	2	2	2.6	2.9
225 (237)	175 (186.5)	300	360	200	50	200	200	50	3	2	3.3	3.6
325 (337)	275 (286.5)	400	460	300	50	200	200	100	4	2	4.1	4.4
425 (437)	375 (386.5)	500	560	400	50	200	400	50	5	3	4.9	5.2
525 (537)	475 (486.5)	600	660	500	50	200	400	100	6	3	5.6	5.9
625 (637)	575 (586.5)	700	760	600	50	200	600	50	7	4	6.4	6.7

¹ Indicates a value when two inner blocks are in close contact with each other.

Note: It must be noted that the cover-mounting bolt is 0.2 mm higher than the top face of the sub-table.