


Model SKR46 Standard Type




Model SKR46□□C (with a Single Short Nut Block)

Model SKR46□□D (with Two Short Nut Blocks)

For model number coding, see **A2-28**.



* Distance between the mechanical stopper and the stroke starting position.



Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L ₁ (mm)	H (mm)	G (mm)	n	n ₁	Overall main unit mass (kg)	
Type C	Type D							Type C	Type D
220(241.5)	145(164.5)	340	440.5	70	70	3	2	6.3	6.9
320(341.5)	245(264.5)	440	540.5	20	70	4	3	7.7	8.3
420(441.5)	345(364.5)	540	640.5	70	70	5	3	9.1	9.7
520(541.5)	445(464.5)	640	740.5	20	70	6	4	10.5	11.1
620(641.5)	545(564.5)	740	840.5	70	70	7	4	11.9	12.5
720(741.5)	645(664.5)	840	940.5	20	70	8	5	13.4	14
820(841.5)	745(764.5)	940	1040.5	70	70	9	5	14.8	15.4




*Indicates a value when two inner blocks are in close contact with each other.

Model SKR46 (with a Cover)

Model SKR46□□C (with a Single Short Nut Block)

Model SKR46□□D (with Two Short Nut Blocks)

For model number coding, see **A2-28**.



A arrow view

B-B cross section

Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L_1 (mm)	H (mm)	G (mm)	n	n_1	Overall main unit mass (kg)	
Type C	Type D*							Type C	Type D
220(241.5)	145(164.5)	340	440.5	70	70	3	2	7.1	7.9
320(341.5)	245(264.5)	440	540.5	20	70	4	3	8.6	9.4
420(441.5)	345(364.5)	540	640.5	70	70	5	3	10.1	10.9
520(541.5)	445(464.5)	640	740.5	20	70	6	4	11.6	12.4
620(641.5)	545(564.5)	740	840.5	70	70	7	4	13.1	13.9
720(741.5)	645(664.5)	840	940.5	20	70	8	5	14.6	15.4
820(841.5)	745(764.5)	940	1040.5	70	70	9	5	16.1	16.9

*Indicates a value when two inner blocks are in close contact with each other.