


SKR46 Without Cover, Motor Wrap

Model SKR46□□C (with a Single Short Block)

Model SKR46□□D (with Two Short Blocks)

For model number coding, see **A2-28**.



Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L_1 (mm)	C (mm)	F (mm)	H (mm)	n	n_1	Overall main unit mass (kg)	
Type C	Type D ¹								Type C	Type D
220 (241.5)	145 (164.5)	340	419	200	200	70	3	2	7.3	7.9
320 (341.5)	245 (264.5)	440	519	300	400	20	4	3	8.7	9.3
420 (441.5)	345 (364.5)	540	619	400	400	70	5	3	10.1	10.7
520 (541.5)	445 (464.5)	640	719	500	600	20	6	4	11.5	12.1
620 (641.5)	545 (564.5)	740	819	600	600	70	7	4	12.9	13.5
720 (741.5)	645 (664.5)	840	919	700	800	20	8	5	14.3	14.9
820 (841.5)	745 (764.5)	940	1,019	800	800	70	9	5	15.7	16.3


¹ Indicates a value when two inner blocks are in close contact with each other.

SKR46 With Cover, Motor Wrap

Model SKR46□□C (with a Single Short Block)

Model SKR46□□D (with Two Short Blocks)

For model number coding, see **A2-28**.



¹ Distance between the mechanical stopper and the stroke starting position.

Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L_1 (mm)	C (mm)	F (mm)	H (mm)	n	n_1	Overall main unit mass (kg)	
Type C	Type D ¹								Type C	Type D
220 (241.5)	145 (164.5)	340	419	200	200	70	3	2	8	8.8
320 (341.5)	245 (264.5)	440	519	300	400	20	4	3	9.5	10.3
420 (441.5)	345 (364.5)	540	619	400	400	70	5	3	11	11.8
520 (541.5)	445 (464.5)	640	719	500	600	20	6	4	12.5	13.3
620 (641.5)	545 (564.5)	740	819	600	600	70	7	4	14	14.8
720 (741.5)	645 (664.5)	840	919	700	800	20	8	5	15.5	16.3
820 (841.5)	745 (764.5)	940	1,019	800	800	70	9	5	17	17.8

¹ Indicates a value when two inner blocks are in close contact with each other.