


Model LBGT



Model No.	Spline nut dimensions										
	Spline nut outer diameter		Length		Outer diameter		Width		Thrust raceway width	H	E
	D	Tolerance	L	Tolerance	D ₄	Tolerance	L ₁	Tolerance			
● LBGT 20	30	0 -0.009	60	0 -0.2	47	0 -0.011	20	0 -0.16	4	12	24
● LBGT 25	40	0 -0.011	70		60	0 -0.013	23	0 -0.19	5	14	28
● LBGT 30	45	0 -0.013	80		65	0 -0.015	27	0 -0.25	5	16	32
● LBGT 40	60	0 -0.015	100	0 -0.3	85	0 -0.025	31	0 -0.25	8	18	41
● LBGT 50	75	0 -0.015	112		100	0 -0.025	32		10	20	46
LBGT 60	90	0 -0.015	127		120	0 -0.025	38		12	22	52.5
● LBGT 85	120	0 -0.015	155		150	0 -0.025	40		16	26	64.5


Note) ●: indicates model numbers for which felt seal types are available (see **A3-126**).

Model number coding

2 LBGT40 UU CL +700L P K

Model No. Symbol for clearance in the rotational direction ⁽²⁾ Accuracy symbol ⁽³⁾ Symbol for spline shaft ⁽⁴⁾
 Number of spline nuts on one shaft (no symbol for one nut) ⁽¹⁾ Contamination protection accessory symbol ⁽¹⁾ Overall spline shaft length ⁽⁵⁾ (in mm)

(*1) See **A3-126**. (*2) See **A3-30**. (*3) See **A3-35**. (*4) See **A3-106**. (*5) See **A3-121**.



Unit: mm

	Gear specifications*				Basic torque rating		Basic load rating		Static permissible moment	Mass	
	Tip circle diameter D_s	Standard pitch diameter PCD	Module m	Number of teeth z	C_T N·m	C_{OT} N·m	C kN	C_0 kN	M_A^{**} N·m	Spline nut unit kg	Spline shaft kg/m
	56	52	2	26	90.2	213	9.4	20.1	103	0.67	1.8
	70	65	2.5	26	176	381	14.9	28.7	171	1.5	2.7
	75	70	2.5	28	312	657	22.5	41.4	295	2.2	3.8
	96	90	3	30	696	1420	37.1	66.9	586	3.3	6.8
	111	105	3	35	1290	2500	55.1	94.1	941	4.8	10.6
	133	126	3.5	36	1870	3830	66.2	121	1300	7.2	15.6
	168	160	4	40	4740	9550	119	213	3180	13.4	32

Note) *The gear specifications in the table represent the dimensions with maximum module.

Special gear types such as helical gear and worm gear can also be manufactured at your request.

** M_A indicates the permissible moment value in the axial direction when a single spline nut is used, as shown in the figure above.

For details on the maximum lengths of ball spline shafts by accuracy, please see **A3-121**.