


SKR65 With Cover, Direct Motor Coupling

Model SKR65□□A (with a Single Long Block)

Model SKR65□□B (with Two Long Blocks)

For model number coding, see **A2-28**.



¹ Distance between the mechanical stopper and the stroke starting position.

Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L ₁ (mm)	C (mm)	G (mm)	F (mm)	H (mm)	n	n ₁	Overall main unit mass (kg)	
Type A	Type B ¹									Type A	Type B
790 (810)	640 (665)	980	1,098	900	40	800	90	7	5	33.5	40.2
990 (1,010)	840 (865)	1,180	1,298	1,050	65	1,000	90	8	6	38.9	45.6
1,190 (1,210)	1,040 (1,065)	1,380	1,498	1,200	90	1,200	90	9	7	44.3	51
1,490 (1,510)	1,340 (1,365)	1,680	1,798	1,500	90	1,600	40	11	9	52.4	59.1

¹ Indicates a value when two inner blocks are in close contact with each other.