





KR26 With Cover, Motor Wrap


Model KR26□□A (with a Single Long Block)

Model KR26□□B (with Two Long Blocks)


For model number coding, see **A2-136**.




With bottom side motor wrap



Sub-table details



B-B cross section



¹ Distance between the mechanical stopper and the stroke starting position.

² Dimensions will vary if "WN" is selected for model number coding. ³ Housing A/intermediate flange. For details, see **A2-230**.

Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L ₁ (mm)	C (mm)	G (mm)	n	Overall main unit mass (kg)	
Type A	Type B ¹						Type A	Type B
60 (69)	—	150	201.8	80	35	2	1.43	—
110 (119)	45 (55)	200	251.8	160	20	3	1.65	1.93
160 (169)	95 (105)	250	301.8	160	45	3	1.87	2.15
210 (219)	145 (155)	300	351.8	240	30	4	2.1	2.38

¹ Indicates a value when two inner blocks are in close contact with each other.