


KR33 With Cover, Motor Wrap

Model KR33□□A (with a Single Long Block)

Model KR33□□B (with Two Long Blocks)

For model number coding, see **A2-136**.



¹ Distance between the mechanical stopper and the stroke starting position.

Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L_1 (mm)	C (mm)	G (mm)	P (mm)	F (mm)	H (mm)	n	n_1	Overall main unit mass (kg)	
Type A	Type B ¹										Type A	Type B
50 (61.5)	—	150	210	100	25	100	100	25	2	2	2.5	—
100 (111.5)	—	200	260	100	50	100	100	50	2	2	2.9	—
200 (211.5)	125 (135.5)	300	360	200	50	200	200	50	3	2	3.6	4.2
300 (311.5)	225 (235.5)	400	460	300	50	200	200	100	4	2	4.4	5
400 (411.5)	325 (335.5)	500	560	400	50	200	400	50	5	3	5.2	5.8
500 (511.5)	425 (435.5)	600	660	500	50	200	400	100	6	3	5.9	6.5
600 (611.5)	525 (535.5)	700	760	600	50	200	600	50	7	4	6.7	7.3

¹ Indicates a value when two inner blocks are in close contact with each other.

Note: It must be noted that the cover-mounting bolt is 0.2 mm higher than the top face of the sub-table.