




Model ST...UUB
(For medium load)

Unit: mm

Length								Basic dynamic load rating	Basic static load rating	Mass
	L	Tolerance	L ₁	L ₂	t	d ₀	r	C kN	C ₀ kN	g
	24	0 -0.2	15.3	1.5	0.5	1.5	0.5	0.98	0.27	17
	30		18.5	1.5	0.5	1.5	0.5	2.35	0.62	31
	32		20.1	1.5	0.5	1.5	0.5	4.02	1.08	49
	37		24.1	1.5	0.5	1.5	0.5	4.02	1.27	80
	45	0 -0.3	30.8	2	0.5	2	0.5	4.12 8.33	1.57 3.24	112 125
	45		30.8	2	0.5	2	1	4.12 8.14	1.76 3.63	132 145
	65		50.1	2.5	0.5	2.5	1	9.31 18.7	4.12 8.14	245 280
	70		55.1	2.5	0.7	2.5	1.5	9.41 18.7	4.51 9.02	375 420
	80		64.9	2.5	0.7	2.5	1.5	12.5 25	6.18 12.4	580 640
	80		64.9	2.5	0.7	2.5	1.5	12.6 25.2	6.76 13.5	635 705