


KR46 Without Cover, Motor Wrap

Model KR46□□C (with a Single Short Block)

Model KR46□□D (with Two Short Blocks)

For model number coding, see **A2-136**.



¹ Distance between the mechanical stopper and the stroke starting position.

² This indicates the short block length when calculating the possible stroke range.

It is 141 mm (total) for a KR46 with two short blocks in close contact with each other (Type D, without Q2).

Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L_1 (mm)	C (mm)	F (mm)	H (mm)	n	n_1	Overall main unit mass (kg)	
Type C	Type D ¹								Type C	Type D
220 (245.5)	150 (173)	340	417	200	200	70	3	2	7.2	7.8
320 (345.5)	250 (273)	440	517	300	400	20	4	3	8.6	9.2
420 (445.5)	350 (373)	540	617	400	400	70	5	3	10	10.6
520 (545.5)	450 (473)	640	717	500	600	20	6	4	11.4	12
620 (645.5)	550 (573)	740	817	600	600	70	7	4	12.8	13.4
720 (745.5)	650 (673)	840	917	700	800	20	8	5	14.2	14.8
820 (845.5)	750 (773)	940	1,017	800	800	70	9	5	15.6	16.2


¹ Indicates a value when two inner blocks are in close contact with each other.

KR46 With Cover, Motor Wrap

Model KR46□□C (with a Single Short Block)

Model KR46□□D (with Two Short Blocks)

For model number coding, see **A2-136**.



¹ Distance between the mechanical stopper and the stroke starting position.

Stroke (mm) (stroke between mechanical stoppers)		Outer rail length (mm)	Overall length L_1 (mm)	C (mm)	F (mm)	H (mm)	n	n_1	Overall main unit mass (kg)	
Type C	Type D ¹								Type C	Type D
220 (245.5)	150 (173)	340	417	200	200	70	3	2	8	8.8
320 (345.5)	250 (273)	440	517	300	400	20	4	3	9.4	10.2
420 (445.5)	350 (373)	540	617	400	400	70	5	3	10.9	11.7
520 (545.5)	450 (473)	640	717	500	600	20	6	4	12.4	13.2
620 (645.5)	550 (573)	740	817	600	600	70	7	4	13.9	14.7
720 (745.5)	650 (673)	840	917	700	800	20	8	5	15.4	16.2
820 (845.5)	750 (773)	940	1,017	800	800	70	9	5	16.8	17.6

¹ Indicates a value when two inner blocks are in close contact with each other.