



## Models LR and LR-Z





| Model No. | Main dimensions              |        |           |                |    |    |     |                              |                     |    |     |     |               |      | Mass<br>g | Basic dynamic<br>load rating<br>C<br>kN | Basic static<br>load rating<br>C <sub>0</sub><br>kN |
|-----------|------------------------------|--------|-----------|----------------|----|----|-----|------------------------------|---------------------|----|-----|-----|---------------|------|-----------|-----------------------------------------|-----------------------------------------------------|
|           | W <sub>1</sub>               | Length | Thickness | Width          | A  | t  | G   | ℓ                            | Mounting hole pitch |    |     |     | Mounting bolt |      |           |                                         |                                                     |
|           | <sup>0</sup> <sub>-0.1</sub> | L      | T         | W <sub>0</sub> |    |    |     | <sup>0</sup> <sub>-0.2</sub> | ℓ <sub>1</sub>      | B  | H   | S   |               |      |           |                                         |                                                     |
| LR 1547Z  | 15                           | 47     | 16        | 30             | 11 | 7  | 5   | 20                           | 12                  | 23 | 3.4 | 0.2 | M3*           | 60   | 21.6      | 39.9                                    |                                                     |
| LR 2055Z  | 20                           | 55     | 17.3      | 36             | 12 | 8  | 5.3 | 30                           | 18                  | 29 | 4.5 | 0.2 | M4*           | 110  | 38.9      | 84.9                                    |                                                     |
| LR 2565Z  | 25                           | 65     | 20.6      | 45             | 14 | 9  | 6.6 | 35                           | 20                  | 36 | 5.5 | 0.1 | M5*           | 190  | 55        | 113                                     |                                                     |
| LR 3275Z  | 32                           | 75     | 21.6      | 55             | 15 | 10 | 6.6 | 45                           | 27                  | 44 | 5.5 | 0.1 | M5*           | 320  | 88        | 208                                     |                                                     |
| LR 4095   | 40                           | 95     | 30        | 68             | 21 | 14 | 9   | 55                           | 35                  | 54 | 6.6 | 0.3 | M6            | 800  | 150       | 326                                     |                                                     |
| LR 50130  | 50                           | 130    | 42        | 82             | 30 | 20 | 12  | 78                           | 50                  | 66 | 9   | 0.3 | M8            | 1810 | 285       | 577                                     |                                                     |

Note) Using a hexagonal-socket-head type bolt as the mounting bolt marked with \* may cause interference.





## Models LRA and LRA-Z




Model LRA

Note: A type with UU seal is not available for model LRA without symbol Z.





Model LRA-Z




LRA-Z...model UU

Unit: mm

| Model No. | Main dimensions             |             |                |                         |    |    |     |                     |     |      | Mass<br>g | Basic dynamic<br>load rating<br>C<br>kN | Basic static<br>load rating<br>C <sub>0</sub><br>kN |
|-----------|-----------------------------|-------------|----------------|-------------------------|----|----|-----|---------------------|-----|------|-----------|-----------------------------------------|-----------------------------------------------------|
|           | W <sub>1</sub><br>0<br>-0.1 | Length<br>L | Thickness<br>T | Width<br>W <sub>0</sub> | A  | t  | G   | $\ell$<br>0<br>-0.2 | S   |      |           |                                         |                                                     |
| LRA 1547Z | 15                          | 47          | 16             | 22.2                    | 11 | 7  | 5   | 20                  | 0.2 | 54   | 21.6      | 39.9                                    |                                                     |
| LRA 2055Z | 20                          | 55          | 17.3           | 30                      | 12 | 8  | 5.3 | 30                  | 0.2 | 104  | 38.9      | 84.9                                    |                                                     |
| LRA 2565Z | 25                          | 65          | 20.6           | 38.1                    | 14 | 9  | 6.6 | 35                  | 0.1 | 180  | 55        | 113                                     |                                                     |
| LRA 3275Z | 32                          | 75          | 21.6           | 45                      | 15 | 10 | 6.6 | 45                  | 0.1 | 310  | 88        | 208                                     |                                                     |
| LRA 4095  | 40                          | 95          | 30             | 55                      | 21 | 14 | 9   | 55                  | 0.3 | 740  | 150       | 326                                     |                                                     |
| LRA 50130 | 50                          | 130         | 42             | 76.2                    | 30 | 20 | 12  | 78                  | 0.3 | 1770 | 285       | 577                                     |                                                     |



Model LRA or LRA-Z



Roller protrusion