


Model FBL 35S



Unit: mm

Rail length L (±0.8)	Stroke S (±3)	Mounting hole dimensions							Mounting hole		Permissible load N/pair	Mass kg/pair
		A	B	C	D	E	F	G	Inner rail	Outer rail		
305	229	—	152.4	254	—	149.2	260.3	273	4	7	490	0.6
356	279	—	203.2	304.8	—	200	311.1	323.8	4	7	400	0.7
406	305	—	254	355.6	—	250.8	361.9	374.6	4	7	390	0.8
457	330	203.2	304.8	406.4	212.7	301.6	412.7	425.4	5	8	380	0.9
508	381	228.6	355.6	457.2	238.1	352.4	463.5	476.2	5	8	330	1
559	406	254	406.4	508	263.5	403.2	514.3	527	5	8	320	1.1
610	432	279.4	457.2	558.8	288.9	454	565.1	577.8	5	8	310	1.2
660	483	304.8	508	609.6	314.3	504.8	615.9	628.6	5	8	280	1.3
711	508	330.2	558.8	660.4	339.7	555.6	666.7	679.4	5	8	270	1.4


Note) The Permissible Load and Mass each indicate when used as a pair of 2 units.

Model number coding

FBL35S +457L

Model number Overall rail length (mm)

Model FBL 35S-P13



Releasing the disconnection spring attached to the inner rail allows the inner rail to be pulled out. A locked state caused by the disconnection spring can be manually released when retracted.

Unit: mm

Rail length L (±0.8)	Stroke S (±3)	Mounting hole dimensions						Mounting hole		Permissible load N/pair	Mass kg/pair
		A	B	C	D	E	F	Inner rail	Outer rail		
305	224	152.4	—	136.5	—	247.6	260.3	3	6	490	0.6
356	275	203.2	—	187.3	—	298.4	311.1	3	6	400	0.72
406	315	254	—	238.1	—	349.2	361.9	3	6	390	0.84
457	330	203.2	406.4	200	288.9	400	412.7	4	7	380	0.96
508	381	228.6	457.2	225.4	339.7	450.8	463.5	4	7	330	1.04
559	406	254	508	250.8	390.5	501.6	514.3	4	7	320	1.16
610	432	279.4	558.8	276.2	441.3	552.4	565.1	4	7	310	1.24
660	483	304.8	609.6	301.6	492.1	603.2	615.9	4	7	280	1.36
711	493	330.2	660.4	327	542.9	654	666.7	4	7	270	1.48

Note) The Permissible Load and Mass each indicate when used as a pair of 2 units.

Model number coding

FBL35S-P13 +559L

Model number

Overall rail length (mm)