



Model FBL 35F



Mass Unit: kg/pair

Rail length L (± 0.8) mm	Mounting plate Model No.					
	#3	#4	#5	#6	#7	#8
305	0.60	0.67	0.74	0.81	—	—
356	0.66	0.73	0.80	0.87	0.94	1.01
406	0.73	0.80	0.87	0.94	1.01	1.08
457	0.80	0.87	0.94	1.01	1.08	1.15
508	0.86	0.93	1.0	1.07	1.14	1.21
559	0.93	1.0	1.07	1.14	1.21	1.28
610	1.0	1.07	1.14	1.21	1.28	1.35
660	1.06	1.13	1.20	1.27	1.34	1.41
711	1.13	1.20	1.27	1.34	1.41	1.48
762	1.20	1.27	1.34	1.41	1.48	1.55



Cross section

Note) The mass indicates the value for a pair of 2 product units.

Unit: mm

Mounting plate	Model No.	#3	#4	#5	#6	#7	#8	Dimension of the outer rail mounting hole (± 0.3)		
	Length (A ± 0.8)	76.2	101.6	127	152.4	177.8	203.2	C	D	E
Rail length L (± 0.8)		Stroke length S (± 3) *Varies with the combination with the mounting plate above.						C	D	E
305		225.4	200.0	174.6	149.2	—	—	—	152.4	254.0
356		276.2	250.8	225.4	200.0	174.6	149.2	—	203.2	304.8
406		327.0	301.6	276.2	250.8	225.4	200.0	—	254.0	355.6
457		377.8	352.4	327.0	301.6	276.2	250.8	203.2	304.8	406.4
508		428.6	403.2	377.8	352.4	327.0	301.6	228.6	355.6	457.2
559		479.4	454.0	428.6	403.2	377.8	352.4	254.0	406.4	508.0
610		530.2	504.8	479.4	454.0	428.6	403.2	279.4	457.2	558.8
660		581.0	555.6	530.2	504.8	479.4	454.0	304.8	508.0	609.6
711		631.8	606.4	581.0	555.6	530.2	504.8	330.2	558.8	660.4
762		682.6	657.2	631.8	606.4	581.0	555.6	355.6	609.6	711.2
Pitch of the mounting plate mounting hole (B ± 0.3)		60.2	85.6	111.0	136.4	161.8	187.2	—	—	—
Permissible load (N/pair)		294	392	490	588	686	784	—	—	—

Note) The Permissible Load and Mass each indicate when used as a pair of 2 units.

Model number coding


FBL35F +356L #5

Model number

Model number of mounting plate

Overall rail length (mm)

Model FBL 56F



Mass Unit: kg/pair

Rail length L (± 0.8) mm	Mounting plate Model No.					
	#3	#4	#5	#6	#7	#8
305	1.16	1.31	1.43	1.55	—	—
356	1.32	1.44	1.57	1.69	1.81	1.94
406	1.46	1.58	1.70	1.83	1.95	2.07
457	1.59	1.71	1.84	1.96	2.09	2.21
508	1.73	1.85	1.98	2.10	2.22	2.35
559	1.87	1.99	2.11	2.24	2.36	2.48
610	2.0	2.13	2.25	2.37	2.50	2.62
660	2.14	2.26	2.39	2.51	2.63	2.76
711	2.28	2.40	2.52	2.65	2.77	2.89
762	2.41	2.54	2.66	2.78	2.91	3.03

Note) The mass indicates the value for a pair of 2 product units.

Unit: mm

Mounting plate	Model No.	#3	#4	#5	#6	#7	#8	Dimension of the outer rail mounting hole (± 0.3)		
	Length ($A \pm 0.8$)	76.2	101.6	127	152.4	177.8	203.2	C	D	E
Rail length L (± 0.8)	Stroke length S (± 3) *Varies with the combination with the mounting plate above.									
305		224.6	199.2	173.8	148.4	—	—	—	152.4	254.0
356		275.4	250.0	224.6	199.2	173.8	148.4	—	203.2	304.8
406		326.2	300.8	275.4	250.0	224.6	199.2	—	254.0	355.6
457		377.0	351.6	326.2	300.8	275.4	250.0	203.2	304.8	406.4
508		427.8	402.4	377.0	351.6	326.2	300.8	228.6	355.6	457.2
559		478.6	453.2	427.8	402.4	377.0	351.6	254.0	406.4	508.0
610		529.4	504.0	478.6	453.2	427.8	402.4	279.4	457.2	558.8
660		580.2	554.8	529.4	504.0	478.6	453.2	304.8	508.0	609.6
711		631.0	605.6	580.2	554.8	529.4	504.0	330.2	558.8	660.4
762		681.8	656.4	631.0	605.6	580.2	554.8	355.6	609.6	711.2
Pitch of the mounting plate mounting hole ($B \pm 0.3$)		60.2	85.6	111.0	136.4	161.8	187.2	—	—	—
Permissible load (N/pair)		588	784	980	1176	1372	1568	—	—	—

Note) The Permissible Load and Mass each indicate when used as a pair of 2 units.

Model number coding

FBL56F +305L #6

Model number

Model number of mounting plate

Overall rail length (mm)