


SBN-V Medium With Preload

| | |
|----------|--------|
| DN value | 160000 |
|----------|--------|



| Model No. | Screw shaft outer diameter d | Lead Ph | Ball center-to-center diameter dp | Thread minor diameter dc | No. of loaded circuits Rows X turns | Basic load rating | | Rigidity K N/μm |
|-------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|----------|-----------------------|
| | | | | | | Ca kN | Ca kN | |
| SBN 2508V-7 | 25 | 8 | 26.25 | 20.5 | 1×3.5 | 26.2 | 43 | 650 |
| SBN 2510V-5 | 25 | 10 | 26.25 | 21.5 | 1×2.5 | 19.6 | 30.9 | 474 |
| SBN 2810V-3 | 28 | 10 | 29.75 | 22.4 | 1×1.5 | 19.5 | 27.8 | 332 |
| SBN 3210V-7 | 32 | 10 | 33.75 | 26.4 | 1×3.5 | 43 | 73.1 | 836.7 |
| SBN 3212V-5 | 32 | 12 | 34 | 26.1 | 1×2.5 | 37.4 | 58.7 | 612.2 |
| SBN 3216V-5 | 32 | 16 | 33.75 | 26.4 | 1×2.5 | 31.9 | 52.2 | 592 |
| SBN 3610V-7 | 36 | 10 | 37.75 | 30.4 | 1×3.5 | 45.6 | 82.3 | 900 |
| SBN 3612V-7 | 36 | 12 | 38 | 30.1 | 1×3.5 | 53.2 | 92.6 | 920 |
| SBN 3616V-5 | 36 | 16 | 38 | 30.1 | 1×2.5 | 39.7 | 66.4 | 662 |
| SBN 3620V-3 | 36 | 20 | 37.75 | 30.5 | 1×1.5 | 21.6 | 32.9 | 398 |
| SBN 4010V-5 | 40 | 10 | 41.75 | 34.4 | 1×2.5 | 35.8 | 65.2 | 708 |
| SBN 4012V-5 | 40 | 12 | 42 | 34.1 | 1×2.5 | 42 | 73.6 | 735.4 |
| SBN 4016V-5 | 40 | 16 | 42 | 34.1 | 1×2.5 | 41.9 | 73.8 | 736.6 |
| SBN 4020V-5 | 40 | 20 | 41.75 | 34.4 | 1×2.5 | 35.4 | 65.2 | 706 |
| SBN 4510V-5 | 45 | 10 | 46.75 | 39.5 | 1×2.5 | 37.9 | 73.8 | 780 |
| SBN 4512V-5 | 45 | 12 | 47 | 39.2 | 1×2.5 | 44.4 | 82.9 | 809.1 |
| SBN 4516V-5 | 45 | 16 | 47 | 39.2 | 1×2.5 | 44.3 | 83.1 | 810.1 |
| SBN 4520V-5 | 45 | 20 | 47 | 39.2 | 1×2.5 | 43.9 | 82.5 | 788 |
| SBN 5010V-5 | 50 | 10 | 51.75 | 44.4 | 1×2.5 | 39.4 | 81 | 838 |
| SBN 5012V-5 | 50 | 12 | 52.25 | 43.3 | 1×2.5 | 53.6 | 101.9 | 936 |
| SBN 5016V-5 | 50 | 16 | 52.7 | 42.9 | 1×2.5 | 89 | 167.7 | 1228 |
| SBN 5020V-5 | 50 | 20 | 52.7 | 42.9 | 1×2.5 | 88.7 | 167.7 | 1228 |

Model number coding

SBN4012V-5 QZ RR G0 +1200L C5

Model No.

Contamination protection accessory symbol ^(*)

Accuracy symbol ^(*)


Overall screw shaft length (in mm)

With QZ lubricator
(No code without QZ lubricator)

Symbol for Clearance in the axial direction
(G0 for all SBN-V variations)

^(*)1 See **A15-346**. ^(*)2 See **A15-12**.

Precision, Caged Ball Screw



Unit: mm

| | Nut dimensions | | | | | | | Greasing hole A | Screw shaft inertial moment/mm kg·m ² /mm | Nut mass kg | Shaft mass kg/m |
|--|--------------------------|--------------------------------------|-------------------------------------|----|----------------|-----|-------------------------------------|--------------------|---|-------------------|-----------------------|
| | Outer diameter Dg6 | Flange diameter D ₁ | Overall length L ₁ | H | B ₁ | PCD | d ₁ × d ₂ × h | | | | |
| | 58 | 85 | 98 | 15 | 83 | 71 | 6.6 × 11 × 6.5 | M6 | 3.01 × 10 ⁻⁷ | 1.5 | 3.51 |
| | 58 | 85 | 100 | 18 | 82 | 71 | 6.6 × 11 × 6.5 | | 3.01 × 10 ⁻⁷ | 1.31 | 3.5 |
| | 65 | 106 | 88 | 18 | 70 | 85 | 11 × 17.5 × 11 | | 4.74 × 10 ⁻⁷ | 2.41 | 4.15 |
| | 74 | 108 | 120 | 15 | 105 | 90 | 9 × 14 × 8.5 | | 8.08 × 10 ⁻⁷ | 3.1 | 5.53 |
| | 76 | 121 | 117 | 18 | 99 | 98 | 11 × 17.5 × 11 | | 8.08 × 10 ⁻⁷ | 3.7 | 5.7 |
| | 74 | 108 | 139 | 18 | 121 | 90 | 9 × 14 × 8.5 | | 8.08 × 10 ⁻⁷ | 3.81 | 5.82 |
| | 75 | 120 | 123 | 18 | 105 | 98 | 11 × 17.5 × 11 | | 1.29 × 10 ⁻⁶ | 3.82 | 7.1 |
| | 78 | 123 | 140 | 18 | 122 | 100 | 11 × 17.5 × 11 | | 1.29 × 10 ⁻⁶ | 4.34 | 7.99 |
| | 78 | 123 | 140 | 18 | 122 | 100 | 11 × 17.5 × 11 | | 1.29 × 10 ⁻⁶ | 4.31 | 7.99 |
| | 75 | 114 | 122 | 18 | 104 | 93 | 11 × 17.5 × 11 | | 1.29 × 10 ⁻⁶ | 3.4 | 7.54 |
| | 82 | 124 | 103 | 18 | 85 | 102 | 11 × 17.5 × 11 | | 1.97 × 10 ⁻⁶ | 3.61 | 8.87 |
| | 84 | 126 | 119 | 18 | 101 | 104 | 11 × 17.5 × 11 | | 1.97 × 10 ⁻⁶ | 4.2 | 8.83 |
| | 84 | 126 | 144 | 18 | 126 | 104 | 11 × 17.5 × 11 | | 1.97 × 10 ⁻⁶ | 4.9 | 9.09 |
| | 82 | 126 | 162 | 18 | 144 | 104 | 11 × 17.5 × 11 | | 1.97 × 10 ⁻⁶ | 5.17 | 9.37 |
| | 88 | 132 | 111 | 18 | 93 | 110 | 11 × 17.5 × 11 | R1/8 (PT1/8) | 3.16 × 10 ⁻⁶ | 4.29 | 11.36 |
| | 90 | 130 | 119 | 18 | 101 | 110 | 11 × 17.5 × 11 | | 3.16 × 10 ⁻⁶ | 4.6 | 11.32 |
| | 90 | 130 | 140 | 18 | 122 | 110 | 11 × 17.5 × 11 | | 3.16 × 10 ⁻⁶ | 5.3 | 11.61 |
| | 90 | 130 | 162 | 18 | 144 | 110 | 11 × 17.5 × 11 | | 3.16 × 10 ⁻⁶ | 5.96 | 11.1 |
| | 93 | 135 | 103 | 18 | 85 | 113 | 11 × 17.5 × 11 | | 4.82 × 10 ⁻⁶ | 4.28 | 14.16 |
| | 100 | 146 | 123 | 22 | 101 | 122 | 14 × 20 × 13 | | 4.82 × 10 ⁻⁶ | 6.12 | 13.82 |
| | 105 | 152 | 164 | 25 | 139 | 128 | 14 × 20 × 13 | | 4.82 × 10 ⁻⁶ | 8.82 | 13.71 |
| | 105 | 152 | 201 | 28 | 173 | 128 | 14 × 20 × 13 | | 4.82 × 10 ⁻⁶ | 10.63 | 14.05 |

Axial Clearance

Unit: mm

| Clearance symbol | G0 |
|------------------|-----------|
| Axial Clearance | 0 or less |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-356** for further details.
It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.

The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation when providing a preload equal to 10% of the basic axial dynamic load rating (Ca) and applying an axial load three times greater than the pre-load.

These values do not include the rigidity of the components related to mounting the ball screw nut.

Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.

If the applied preload (Fa₀) is not 0.1 Ca, the rigidity value (K_v) is obtained from the following equation.

$$K_v = K \left(\frac{F_{a0}}{0.1Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table.