








Transport Ball Screw

Series	Type		Features	
Transport	JPF		Fixed-point Preloading	
	BTK-V		High DN value	
	BNT		Flat nut	
	BLK		Large lead	
	WTF		Super large lead	
	CNF		Super large lead	
	MTF		Unfinished Shaft End Miniature	

Transport Ball Screw

	Caged ball	Compact nut	Miniature	High load capacity	Preload	DN Value	Shaft diameter (mm)	Lead (mm)	Page No.
					✓	50000	14 to 40	4 to 10	A15-224
						100000	10 to 50	6 to 16	A15-226
						50000	14 to 45	4 to 12	A15-228
						70000	15 to 50	10 to 50	A15-230
						70000	15 to 50	20 to 100	A15-232
						70000	15 to 30	30 to 60	A15-234
			✓			50000	6 to 12	1 to 2	A15-235

Standard combinations of outer diameters and leads of the screw shafts

Shaft diameter	Lead										
	1	2	4	5	6	8	10	12	16	20	
6	MTF										
8		MTF									
10		MTF			BTK-V						
12		MTF				BTK-V					
14			JPF BTK-V BNT	JPF BTK-V BNT							
15							BLK			WTF	
16				JPF BTK-V BNT					BLK		
18						BTK-V BNT					
20				JPF BTK-V BNT			BTK-V BNT			BLK	
25				JPF BTK-V BNT			JPF BTK-V BNT				
28				JPF	JPF BTK-V BNT						
30											
32							JPF BTK-V BNT				
36							JPF BTK-V BNT			BLK	
40							JPF BTK-V				
45								BTK-V BNT			
50									BTK-V		

Transport Ball Screw


Unit: mm

Lead										
	24	25	30	32	36	40	50	60	80	100
			WTF CNF							
						WTF CNF				
		BLK					WTF CNF			
								WTF CNF		
				BLK						
	BLK				BLK					
						BLK			WTF	
							BLK			WTF

Ball Screw

JPF With Preload

DN value	50000
----------	-------



Model No.	Screw shaft outer diameter d	Lead Ph	Ball center-to-center diameter dp	Thread minor diameter dc	No. of loaded circuits Rows X turns	Basic load rating		Outer diameter D	Flange diameter D ₁	Outer diameter D ₂
						C _a kN	C _{0a} kN			
JPF 1404-4	14	4	14.4	11.5	2×1	2.8	5.1	26	46	25.5
JPF 1405-4		5	14.5	11.2	2×1	3.9	8.6	26	46	25.5
JPF 1605-4	16	5	16.75	13.5	2×1	3.7	8.2	30	49	29.5
JPF 2005-6	20	5	20.5	17.2	3×1	6	16	34	57	33.5
JPF 2505-6	25	5	25.5	22.2	3×1	6.9	20.8	40	66	39.5
JPF 2510-4		10	26.8	20.2	2×1	11.4	24.5	47	72	46.5
JPF 2805-6	28	5	28.75	25.2	3×1	7.3	23.9	43	69	42.5
JPF 2806-6		6	28.5	25.2	3×1	7.3	23.9	43	69	42.5
JPF 3210-6	32	10	33.75	27.2	3×1	19.3	49.9	54	88	53.5
JPF 3610-6	36	10	37	30.5	3×1	20.6	56.2	58	98	57.5
JPF 4010-6	40	10	41.75	35.2	3×1	22.2	65.3	62	104	61.5

Model number coding

JPF1404-4 RR G0 +500L C7 T

Model No.

Seal symbol ^{(*)1}


Overall screw shaft length (in mm)

Symbol for rolled shaft

Symbol for clearance in the axial direction

Accuracy symbol ^{(*)2}

(*)1 See [A15-308](#). (*)2 See [A15-12](#).



Unit: mm

Nut dimensions								Screw shaft inertial moment kg·m ² /mm	Nut mass kg	Shaft mass kg/m
Overall length	L ₁	H	B ₁	B ₂	PCD	d ₁ ×d ₂ ×h	Greasing hole A			
52	10	42	16.5	36	4.5×8×4.5	M6	2.96×10 ⁻⁸	0.22	1	
60	10	50	20	36	4.5×8×4.5	M6	2.96×10 ⁻⁸	0.24	0.99	
60	10	50	19.5	39	4.5×8×4.5	M6	5.05×10 ⁻⁸	0.3	1.34	
80	11	69	26.5	45	5.5×9.5×5.5	M6	1.23×10 ⁻⁷	0.46	2.15	
80	11	69	26	51	5.5×9.5×5.5	M6	3.01×10 ⁻⁷	0.6	3.45	
112	12	100	42	58	6.6×11×6.5	M6	3.01×10 ⁻⁷	1.2	3.26	
80	12	68	25	55	6.6×11×6.5	M6	4.74×10 ⁻⁷	0.66	4.27	
90	12	78	35	55	6.6×11×6.5	M6	4.74×10 ⁻⁷	0.72	4.44	
135	15	120	53.5	70	9×14×8.5	M6	8.08×10 ⁻⁷	1.84	5.49	
138	18	120	53.5	77	11×17.5×11	M6	1.29×10 ⁻⁶	2.22	6.91	
138	18	120	53.5	82	11×17.5×11	Rc1/8 (PT1/8)	1.97×10 ⁻⁶	2.42	8.81	

Note) The ball screw nut and the screw shaft of model JPF are not sold separately.

The basic load rating corresponds to the recommended loading direction.

If a load is applied in the opposite direction, the value must be 0.1×Ca or less during use.

Maximum Manufacturing Length of Model JPF by Model Number


Unit: mm

Model No.	Overall screw shaft length
JPF1404-4	1000
JPF1405-4	
JPF1605-4	
JPF2005-6	2000
JPF2505-6	
JPF2510-4	


Model No.	Overall screw shaft length
JPF2805-6	2000
JPF2806-6	3000
JPF3210-6	
JPF3610-6	
JPF4010-6	

BTK-V No Preload

DN value	100000
----------	--------



Models 1006V and 1208V



Models 1404V to 5016V


Model No.	Screw shaft outer diameter d	Lead Ph	Ball center-to-center diameter dp	Thread minor diameter dc	No. of loaded circuits Rows X turns	Basic load rating		Rigidity K	Outer diameter D	Flange diameter D ₁	Overall length	
						C _a kN	C _{0a} kN				L ₁	H
BTK 1006V-2.6	10	6	10.5	7.8	1×2.65	2.8	4.9	88	26	42	36	8
BTK 1208V-2.6	12	8	12.65	9.7	1×2.65	3.8	6.8	108	29	45	44	8
BTK 1404V-3.6	14	4	14.4	11.5	1×3.65	5.5	11.5	150	31	50	40	10
BTK 1405V-2.6	14	5	14.5	11.2	1×2.65	5	11.4	116	32	50	40	10
BTK 1605V-2.6	16	5	16.75	13.5	1×2.65	5.4	13.3	130	34	54	40	10
BTK 1808V-3.6	18	8	19.3	14.4	1×3.65	13.1	31	210	50	80	61	12
BTK 2005V-2.6	20	5	20.5	17.2	1×2.65	6	16.5	150	40	60	40	10
BTK 2010V-2.6	20	10	21.25	16.4	1×2.65	10.6	25.1	160	52	82	61	12
BTK 2505V-2.6	25	5	25.5	22.2	1×2.65	6.7	20.8	180	43	67	40	10
BTK 2510V-5.3	25	10	26.8	20.2	2×2.65	31.2	83.7	400	60	96	98	15
BTK 2806V-2.6	28	6	28.5	25.2	1×2.65	7	23.4	200	50	80	47	12
BTK 2806V-5.3	28	6	28.5	25.2	2×2.65	12.8	46.8	390	50	80	65	12
BTK 3210V-2.6	32	10	33.75	27.2	1×2.65	19.8	53.8	250	67	103	68	15
BTK 3210V-5.3	32	10	33.75	27.2	2×2.65	36	107.5	490	67	103	98	15
BTK 3610V-2.6	36	10	37	30.5	1×2.65	20.8	59.8	270	70	110	70	17
BTK 3610V-5.3	36	10	37	30.5	2×2.65	37.8	118.7	530	70	110	100	17
BTK 4010V-5.3	40	10	41.75	35.2	2×2.65	40.3	134.9	590	76	116	100	17
BTK 4512V-5.3	45	12	46.5	39.2	2×2.65	49.5	169	650	82	128	118	20
BTK 5016V-5.3	50	16	52.7	42.9	2×2.65	93.8	315.2	930	102	162	145	25

Model number coding


BTK1405V-2.6 ZZ +500L C7 T H1K

Model No.	Contamination protection accessory symbol (*1)	Overall screw shaft length (in mm)	Symbol for rolled shaft	Accuracy symbol (*2)	Recommended shaft ends shape code
-----------	--	------------------------------------	-------------------------	----------------------	-----------------------------------

(*1) See [A15-308](#). (*2) See [A15-12](#).



Models 1006V and 1208V



Models 1404V to 5016V


Unit: mm

Nut dimensions						Axial clearance	Standard shaft length	Screw shaft inertial moment kg·m ² /mm	Nut mass kg	Shaft mass kg/m	Maximum permissible rotation speed min ⁻¹
B ₁	PCD	d ₁	T _w	Greasing hole							
				N ₁	A						
28	34	4.5	29	—	3	0.05	200, 300, 500, 1000	7.71×10^{-9}	0.12	0.48	5000
36	37	4.5	32	—	3	0.05	200, 300, 500, 1000	1.60×10^{-8}	0.18	0.72	5000
30	40	4.5	37	5	M6	0.1	500, 1000	2.96×10^{-8}	0.23	1	5000
30	40	4.5	38	5	M6	0.1	500, 1000	2.96×10^{-8}	0.22	0.99	5000
30	44	4.5	40	5	M6	0.1	500, 1000, 1500	5.05×10^{-8}	0.24	1.34	5000
49	65	6.6	60	5	M6	0.1	500, 1000, 1500	8.09×10^{-8}	0.84	1.71	5000
30	50	4.5	46	5	M6	0.1	500, 1000, 1500, 2000	1.23×10^{-7}	0.32	2.15	4870
49	67	6.6	64	5	M6	0.1	500, 1000, 1500, 2000	1.23×10^{-7}	0.93	2.16	4700
30	55	5.5	50	5	M6	0.1	500, 1000, 1500, 2000	3.01×10^{-7}	0.34	3.45	3920
83	78	9	72	5	M6	0.1	500, 1000, 1500, 2000	3.01×10^{-7}	1.83	3.26	3730
35	65	6.6	60	6	M6	0.1	500, 1000, 2000, 2500	4.74×10^{-7}	0.59	4.44	3500
53	65	6.6	60	6	M6	0.1	500, 1000, 2000, 2500	4.74×10^{-7}	0.75	4.44	3500
53	85	9	78	5	M6	0.14	500, 1000, 1500, 2000, 2500, 3000	8.08×10^{-7}	1.56	5.49	2960
83	85	9	78	5	M6	0.14	500, 1000, 1500, 2000, 2500, 3000	8.08×10^{-7}	2.1	5.49	2960
53	90	11	82	7	M6	0.17	500, 1000, 2000, 2500, 3000	1.29×10^{-6}	1.78	6.91	2700
83	90	11	82	7	M6	0.17	500, 1000, 2000, 2500, 3000	1.29×10^{-6}	2.35	6.91	2700
83	96	11	88	7	M6	0.17	1000, 1500, 2000, 2500, 3000, 3500	1.97×10^{-6}	2.6	8.81	2390
98	104	14	94	8	M6	0.17	1000, 1500, 2000, 3000, 3500, 4000	3.16×10^{-6}	3.48	11.08	2150
120	132	18	104	12.5	Rc1/8 (PT1/8)	0.2	1000, 1500, 2000, 3000, 3500, 4000	4.82×10^{-6}	6.52	13.66	1890

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-318** for further details.

BNT (Rolled Ball Screw) No Preload

DN value	50000
----------	-------



Model No.	Screw shaft outer diameter d	Lead Ph	Ball center-to-center diameter dp	Thread minor diameter dc	No. of loaded circuits Rows X turns	Basic load rating			Rigidity		
						Ca kN	C _{0a} kN	K N/μm	Width W	Center height F	Overall length L ₁
BNT 1404-3.6	14	4	14.4	11.5	1×3.65	5.5	11.5	150	34	13	35
BNT 1405-2.6		5	14.5	11.2	1×2.65	5	11.4	110	34	13	35
BNT 1605-2.6	16	5	16.75	13.5	1×2.65	5.4	13.3	130	42	16	36
BNT 1808-3.6	18	8	19.3	14.4	1×3.65	13.1	31	210	48	17	56
BNT 2005-2.6	20	5	20.5	17.2	1×2.65	6	16.5	150	48	17	35
BNT 2010-2.6		10	21.25	16.4	1×2.65	10.6	25.1	160	48	18	58
BNT 2505-2.6	25	5	25.5	22.2	1×2.65	6.7	20.8	180	60	20	35
BNT 2510-5.3		10	26.8	20.2	2×2.65	31.2	83.7	400	60	23	94
BNT 2806-2.6	28	6	28.5	25.2	1×2.65	7	23.4	200	60	22	42
BNT 2806-5.3			28.5	25.2	2×2.65	12.8	46.8	390	60	22	67
BNT 3210-2.6	32	10	33.75	27.2	1×2.65	19.8	53.8	250	70	26	64
BNT 3210-5.3			33.75	27.2	2×2.65	36	107.5	490	70	26	94
BNT 3610-2.6	36	10	37	30.5	1×2.65	20.8	59.3	270	86	29	64
BNT 3610-5.3			37	30.5	2×2.65	37.8	118.7	530	86	29	96
BNT 4512-5.3	45	12	46.5	39.2	2×2.65	49.5	169	650	100	36	115


Model number coding

BNT2010-2.6 ZZ +1000L C7 T H1K

Model No.	Contamination protection accessory symbol (*1)	Overall screw shaft length (in mm)	Accuracy symbol (*2)	Symbol for rolled shaft	Recommended shaft ends shape code
-----------	--	------------------------------------	----------------------	-------------------------	-----------------------------------

(*1) See **A15-308**. (*2) See **A15-12**.

Transport Ball Screw




Unit: mm

Nut dimensions										Axial clearance	Screw shaft inertial moment kg·m ² /mm	Nut mass kg	Shaft mass kg/m
Mounting hole			W _i	T	M	N ₁	N ₂	A					
B	C	S×ℓ											
26	22	M4×7	17	6	30	6	2	M6	0.1	2.96×10 ⁻⁸	0.15	1	
26	22	M4×7	17	6	31	6	2	M6	0.1	2.96×10 ⁻⁸	0.15	0.99	
32	22	M5×8	21	21.5	32.5	6	2	M6	0.1	5.05×10 ⁻⁸	0.3	1.34	
35	35	M6×10	24	10	44	8	3	M6	0.1	8.09×10 ⁻⁸	0.47	1.71	
35	22	M6×10	24	9	39	5	3	M6	0.1	1.23×10 ⁻⁷	0.28	2.15	
35	35	M6×10	24	9	46	10	2	M6	0.1	1.23×10 ⁻⁷	0.5	2.16	
40	22	M8×12	30	9.5	45	7	5	M6	0.1	3.01×10 ⁻⁷	0.41	3.45	
40	60	M8×12	30	10	55	10	—	M6	0.1	3.01×10 ⁻⁷	1.18	3.26	
40	18	M8×12	30	10	50	8	—	M6	0.1	4.74×10 ⁻⁷	0.81	4.44	
40	40	M8×12	30	10	50	8	—	M6	0.1	4.74×10 ⁻⁷	0.78	4.44	
50	45	M8×12	35	12	62	10	—	M6	0.14	8.08×10 ⁻⁷	1.3	5.49	
50	60	M8×12	35	12	62	10	—	M6	0.14	8.08×10 ⁻⁷	2	5.49	
60	45	M10×16	43	17	67	11	—	M6	0.17	1.29×10 ⁻⁶	1.8	6.91	
60	60	M10×16	43	17	67	11	—	M6	0.17	1.29×10 ⁻⁶	2.4	6.91	
75	75	M12×20	50	20.5	80	13	—	M6	0.2	3.16×10 ⁻⁶	4.1	11.08	

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-318** for further details.

BLK (Rolled Ball Screw) No Preload

DN value	70000
----------	-------



Model No.	Screw shaft outer diameter d	Lead Ph	Ball center-to-center diameter dp	Thread minor diameter dc	No. of loaded circuits Rows X turns	Basic load rating		Rigidity K	Outer diameter D	Flange diameter D ₁	Overall length L ₁	H
						Ca kN	C _{0a} kN					
BLK 1510-5.6	15	10	15.75	12.5	2×2.8	9.8	25.2	260	34	57	44	10
BLK 1616-3.6	16	16	16.65	13.7	2×1.8	5.8	12.9	170	32	53	38	10
BLK 1616-7.2	16	16	16.65	13.7	4×1.8	10.5	25.9	340	32	53	38	10
BLK 2020-3.6	20	20	20.75	17.5	2×1.8	7.7	22.3	210	39	62	45	10
BLK 2020-7.2	20	20	20.75	17.5	4×1.8	13.9	44.6	410	39	62	45	10
BLK 2525-3.6	25	25	26	21.9	2×1.8	12.1	35	270	47	74	55	12
BLK 2525-7.2	25	25	26	21.9	4×1.8	21.9	69.9	520	47	74	55	12
BLK 3232-3.6	32	32	33.25	28.3	2×1.8	17.3	53.9	330	58	92	70	15
BLK 3232-7.2	32	32	33.25	28.3	4×1.8	31.3	107.8	650	58	92	70	15
BLK 3620-5.6	36	20	37.75	31.2	2×2.8	39.8	121.7	570	70	110	78	17
BLK 3624-5.6	36	24	38	30.7	2×2.8	46.2	137.4	590	75	115	94	18
BLK 3636-3.6	36	36	37.4	31.7	2×1.8	22.4	70.5	370	66	106	77	17
BLK 3636-7.2	36	36	37.4	31.7	4×1.8	40.6	141.1	730	66	106	77	17
BLK 4040-3.6	40	40	41.75	35.2	2×1.8	28.1	89.8	420	73	114	85	17
BLK 4040-7.2	40	40	41.75	35.2	4×1.8	51.1	179.6	810	73	114	85	17
BLK 5050-3.6	50	50	52.2	44.1	2×1.8	42.1	140.4	510	90	135	106	20
BLK 5050-7.2	50	50	52.2	44.1	4×1.8	76.3	280.7	1000	90	135	106	20

Model number coding

BLK3232-3.6 ZZ +1500L C7 T H1K

Model No.

Contamination protection accessory symbol (*1)


Overall screw shaft length (in mm)

Symbol for rolled shaft

Accuracy symbol (*2)

Recommended shaft ends shape code

(*1) See **A15-308**. (*2) See **A15-12**.




Unit: mm

Nut dimensions								Axial clearance	Standard shaft length	Screw shaft inertial moment kg·m ² /mm	Nut mass kg	Shaft mass kg/m
B ₁	PCD	d ₁	T _w	Greasing hole		Seal M ₁						
				N ₁	A							
24	45	5.5	40	5	M6	3.5	0.1	500, 1000	3.90×10^{-8}	0.26	1.16	
21.5	42	4.5	38	5	M6	3.5	0.1	500, 1000, 1500	5.05×10^{-8}	0.21	1.35	
21.5	42	4.5	38	5	M6	3.5	0.1	500, 1000, 1500	5.05×10^{-8}	0.25	1.35	
27.5	50	5.5	46	5	M6	3.5	0.1	500, 1000, 1500	1.23×10^{-7}	0.35	2.18	
27.5	50	5.5	46	5	M6	3.5	0.1	500, 1000, 1500	1.23×10^{-7}	0.35	2.18	
35	60	6.6	56	6	M6	3.5	0.1	500, 1000, 1500, 2000, 2500	3.01×10^{-7}	0.64	3.41	
35	60	6.6	56	6	M6	3.5	0.1	500, 1000, 1500, 2000, 2500	3.01×10^{-7}	0.64	3.41	
45	74	9	68	7.5	M6	3.8	0.14	1000, 1500, 2000, 2500, 3000	8.08×10^{-7}	1.14	5.69	
45	74	9	68	7.5	M6	3.8	0.14	1000, 1500, 2000, 2500, 3000	8.08×10^{-7}	1.14	5.69	
45	90	11	80	8.5	M6	5	0.17	1000, 1500, 2000, 2500, 3000	1.29×10^{-6}	1.74	7.09	
59	94	11	86	9	M6	5	0.17	1000, 1500, 2000, 2500, 3000	1.29×10^{-6}	2.42	7.02	
50	85	11	76	8.5	M6	5	0.17	1000, 1500, 2000, 2500, 3000	1.29×10^{-6}	1.74	7.12	
50	85	11	76	8.5	M6	5	0.17	1000, 1500, 2000, 2500, 3000	1.29×10^{-6}	1.74	7.12	
56.5	93	11	84	8.5	M6	5.4	0.17	1000, 1500, 2000, 2500, 3000, 4000	1.97×10^{-6}	2.16	8.76	
56.5	93	11	84	8.5	M6	5.4	0.17	1000, 1500, 2000, 2500, 3000, 4000	1.97×10^{-6}	2.16	8.76	
72	112	14	104	10	M6	5.4	0.2	1000, 1500, 2000, 3000, 4000	4.82×10^{-6}	3.89	13.79	
72	112	14	104	10	M6	5.4	0.2	1000, 1500, 2000, 3000, 4000	4.82×10^{-6}	3.86	13.79	

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-318** for further details.

WTF No Preload

DN value	70000
----------	-------




Model No.	Screw shaft outer diameter d	Lead Ph	Ball center-to-center diameter dp	Thread minor diameter dc	No. of loaded circuits Rows X turns	Basic load rating		Rigidity K	Outer diameter D	Flange diameter D ₁	Overall length	
						Ca	C _{0a}				L ₁	H
						kN	kN	N/μm	D	D ₁	L ₁	H
WTF 1520-3	15	20	15.75	12.5	2X1.5	5.5	14.2	140	32	53	45	10
WTF 1520-6	15	20	15.75	12.5	4X1.5	10.1	28.5	280	32	53	45	10
WTF 1530-2	15	30	15.75	12.5	4X0.6	4.3	9.3	120	32	53	33	10
WTF 1530-3	15	30	15.75	12.5	2X1.6	5.6	12.4	160	32	53	63	10
WTF 2040-2	20	40	20.75	17.5	4X0.65	5.4	13.6	160	37	57	41.5	10
WTF 2040-3	20	40	20.75	17.5	2X1.65	6.6	17.2	200	37	57	81.5	10
WTF 2550-2	25	50	26	21.9	4X0.65	8.5	21.2	200	45	69	52	12
WTF 2550-3	25	50	26	21.9	2X1.65	10.4	26.9	260	45	69	102	12
WTF 3060-2	30	60	31.25	26.4	4X0.65	11.8	30.6	240	55	89	62.5	15
WTF 3060-3	30	60	31.25	26.4	2X1.65	14.5	38.9	310	55	89	122.5	15
WTF 4080-2	40	80	41.75	35.2	4X0.65	19.8	54.5	320	73	114	79	17
WTF 4080-3	40	80	41.75	35.2	2X1.65	24.3	69.2	400	73	114	159	17
WTF 50100-2	50	100	52.2	44.1	4X0.65	29.6	85.2	390	90	135	98	20
WTF 50100-3	50	100	52.2	44.1	2X1.65	36.3	108.1	500	90	135	198	20

Model number coding

WTF3060-3 ZZ +1500L C7 T H1K

Model No.	Contamination protection accessory symbol (*1)	Overall screw shaft length (in mm)	Symbol for rolled shaft	Accuracy symbol (*2)	Recommended shaft ends shape code
-----------	--	------------------------------------	-------------------------	----------------------	-----------------------------------

(*1) See **A15-308**. (*2) See **A15-12**.




Unit: mm

Nut dimensions							Seal	Axial clearance	Standard shaft length	Screw shaft inertial moment kg·m ² /mm	Nut mass kg	Shaft mass kg/m
B ₁	PCD	d ₁	Tw	Greasing hole		M ₁						
				N ₁	A							
28	43	5.5	33	5	M6	3.5	0.1	500, 1000	3.90×10^{-8}	0.2	1.17	
28	43	5.5	33	5	M6	3.5	0.1	500, 1000	3.90×10^{-8}	0.2	1.17	
17	43	5.5	33	5	M6	3.5	0.1	500, 1000, 1500	3.90×10^{-8}	0.22	1.19	
47	43	5.5	33	5	M6	3.5	0.1	500, 1000, 1500	3.90×10^{-8}	0.4	1.19	
25.5	47	5.5	38	5.5	M6	3.5	0.1	500, 1000, 1500, 2000	1.23×10^{-7}	0.25	2.12	
65.5	47	5.5	38	5.5	M6	3.5	0.1	500, 1000, 1500, 2000	1.23×10^{-7}	0.5	2.12	
31.5	57	6.6	46	7	M6	3.5	0.1	1000, 1500, 2000, 3000	3.01×10^{-7}	0.45	3.34	
81.5	57	6.6	46	7	M6	3.5	0.1	1000, 1500, 2000, 3000	3.01×10^{-7}	0.85	3.34	
37.5	71	9	56	9	M6	3.8	0.14	1000, 2000, 3000, 4000	6.24×10^{-7}	0.8	4.84	
97.5	71	9	56	9	M6	3.8	0.14	1000, 2000, 3000, 4000	6.24×10^{-7}	1.7	4.84	
50.5	93	11	74	9	M6	5.4	0.17	1000, 1500, 2000, 3000	1.97×10^{-6}	2.1	8.66	
130.5	93	11	74	9	M6	5.4	0.17	1000, 1500, 2000, 3000	1.97×10^{-6}	3.67	8.66	
64	112	14	92	10	M6	5.4	0.2	1500, 3000	4.82×10^{-6}	3.5	13.86	
164	112	14	92	10	M6	5.4	0.2	1500, 3000	4.82×10^{-6}	6.4	13.86	

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-318** for further details.

CNF No Preload

DN value	70000
----------	-------



Unit: mm

Model No.	Screw shaft outer diameter		Lead	Ball center-to-center diameter	Thread minor diameter	No. of loaded circuits	Basic load rating			Rigidity	Nut dimensions				
	d	Ph					Ca	C _{0a}	K		Outer diameter	Flange diameter	Overall length	H	B ₁
	d	Ph	dp	dc	Rows X turns	kN	kN	N/ μ m	D	D ₁	L ₁	H	B ₁		
CNF 1530-6	15	30	15.75	12.5	4×1.6	10.1	24.7	310	32	53	63	10	47		
CNF 2040-6	20	40	20.75	17.5	4×1.65	12	34.4	400	37	57	81	10	65		
CNF 2550-6	25	50	26	21.9	4×1.65	18.9	53.9	460	45	69	102	12	81.5		
CNF 3060-6	30	60	31.25	26.4	4×1.65	26.2	77.7	600	55	89	122	15	97		

Model No.	Nut dimensions					Axial clearance	Standard shaft length	Screw shaft inertial moment	Nut mass	Shaft mass
	PCD	d ₁	Greasing hole		Seal					
			N ₁	A	M ₁			kg·m ² /mm	kg	kg/m
CNF 1530-6	43	5.5	5	M6	3.5	0.1	500, 1000, 1500	3.90×10^{-8}	0.42	1.19
CNF 2040-6	47	5.5	5.5	M6	3.5	0.1	500, 1000, 1500, 2000	1.23×10^{-8}	0.5	2.12
CNF 2550-6	57	6.6	7	M6	3.5	0.1	1000, 1500, 2000, 3000	3.01×10^{-7}	0.85	3.34
CNF 3060-6	71	9	9	M6	3.8	0.14	1000, 2000, 3000, 4000	6.24×10^{-7}	1.7	4.84

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-318** for further details.

Model number coding


CNF2040-6 ZZ +1500L C7 T H1K

Model No.	Contamination protection accessory symbol (*1)	Overall screw shaft length (in mm)	Accuracy symbol (*2)	Symbol for rolled shaft	Recommended shaft ends shape code
-----------	--	------------------------------------	----------------------	-------------------------	-----------------------------------

(*1) See **A15-308**. (*2) See **A15-12**.

MTF No Preload

DN value	50000
----------	-------



Unit: mm

Model No.	Screw shaft outer diameter d	Lead Ph	Ball center-to-center diameter dp	Thread minor diameter dc	No. of loaded circuits Rows X turns	Basic load rating		Rigidity K	Nut dimensions		
						Ca kN	C _{0a} kN		Outer diameter D	Flange diameter D ₁	Overall length L ₁
MTF 0601-3.7	6	1	6.15	5.3	1×3.7	0.7	1.2	70	13	30	21
MTF 0802-3.7	8	2	8.3	6.6	1×3.7	2.1	3.8	90	20	40	28
MTF 1002-3.7	10	2	10.3	8.6	1×3.7	2.3	4.8	110	23	43	28
MTF 1202-3.7	12	2	12.3	10.6	1×3.7	2.5	5.8	130	25	47	30

Model No.	Nut dimensions					Axial clearance	Standard shaft length	Screw shaft inertial moment kg·m ² /mm	Nut mass kg	Shaft mass kg/m
	H	B ₁	PCD	d ₁	Tw					
MTF 0601-3.7	5	16	21.5	3.4	17	0.05	150, 250	9.99×10 ⁻¹⁰	0.03	0.19
MTF 0802-3.7	6	22	30	4.5	24	0.05	150, 250	3.16×10 ⁻⁹	0.08	0.31
MTF 1002-3.7	6	22	33	4.5	27	0.05	200, 300	7.71×10 ⁻⁹	0.1	0.52
MTF 1202-3.7	8	22	36	5.5	29	0.05	200, 300	1.60×10 ⁻⁸	0.13	0.77

Note) Model MTF cannot be attached with seal.

For the Model MTF, nuts are processed with AP-C Treatment as standard. For details, see [B0-20](#).

Model MTF is only sold as sets (ball screw nut and screw shaft).

Model MTF is applied only with anti-rust oil.

Model number coding

MTF 0802-3.7 +250L C7 T

Model No.

Overall screw shaft length (in mm)

Symbol for rolled shaft

Accuracy code: (No code for Normal Grade)