



# Ball Screw

THK General Catalog

# Ball Screw

THK General Catalog

## A Product Descriptions

Overview of THK Ball Screws..... A15-6

**Point of Selection** ..... A15-8

Flowchart for Selecting a Ball Screw ..... A15-8

Accuracy of the Ball Screw ..... A15-11

- Lead Angle Accuracy ..... A15-11
- Accuracy of the Mounting Surface ..... A15-14
- Axial Clearance ..... A15-19
- Preload ..... A15-20

Selecting a Screw Shaft ..... A15-24

- Maximum Manufacturing Length of the Screw Shaft .. A15-24
- Combinations of Shaft Diameter and Lead for the Precision Ball Screw .. A15-26
- Combinations of Shaft Diameter and Lead for the Rolled Ball Screw .. A15-27

Method for Mounting the Ball Screw Shaft .. A15-28

Permissible Axial Load ..... A15-30

Permissible Rotational Speed ..... A15-32

Studying the Caged Technology..... A15-35

- Types and Features ..... A15-38

Selecting a Nut ..... A15-41

- Types of Nuts ..... A15-41

Selecting a Model Number ..... A15-46

- Calculating the Axial Load ..... A15-46
- Static Safety Factor ..... A15-47
- Studying the Service Life ..... A15-48

Studying the Rigidity..... A15-51

- Axial Rigidity of the Feed Screw System .. A15-51

Studying the Positioning Accuracy ..... A15-55

- Causes of Error in the Positioning Accuracy .. A15-55
- Studying the Lead Angle Accuracy ..... A15-55
- Studying the Axial Clearance ..... A15-55
- Studying the Axial Clearance of the Feed Screw System .. A15-57
- Studying the Thermal Displacement through Heat Generation ... A15-59
- Studying the Orientation Change during Traveling .. A15-60

Studying the Rotational Torque ..... A15-61

- Frictional Torque Due to an External Load .. A15-61
- Torque Due to a Preload on the Ball Screw .. A15-62
- Torque Required for Acceleration ..... A15-63
- Investigating the Terminal Strength of Ball Screw Shafts .. A15-64

Studying the Driving Motor ..... A15-66

- When Using a Servomotor ..... A15-66
- When Using a Stepping Motor (Pulse Motor) .. A15-68

**Features of Each Model** ..... A15-69

**Overview of THK Ball Screws**..... A15-70

**Positioning, ISO 3408 compliant**..... A15-72

- Standard combinations of outer diameters and leads of the screw shafts .. A15-74

**Dimensional Drawing, Dimensional Table**

Models SDAN-V ..... A15-76

Models SDA-V/SDA-VZ..... A15-82

Model EPB-V ..... A15-94

Model EBB-V ..... A15-96

**Positioning Ball Screw**..... A15-102

- Standard combinations of outer diameters and leads of the screw shafts .. A15-106

**Dimensional Drawing, Dimensional Table**

Model SBN-V..... A15-110

Model SBK..... A15-114

Model BIF-V..... A15-118

Model BNFN-V ..... A15-124

Model BNFN ..... A15-126

Model DIK ..... A15-130

Model DKN ..... A15-136

Model BLW ..... A15-138

BNK0401-3 Shaft diameter: 4; lead: 1... A15-140

BNK0501-3 Shaft diameter: 5; lead: 1... A15-142

BNK0601-3 Shaft diameter: 6; lead: 1... A15-144

BNK0801-3 Shaft diameter: 8; lead: 1... A15-146

BNK0802-3 Shaft diameter: 8; lead: 2... A15-148

BNK0810-3 Shaft diameter: 8; lead: 10... A15-150

BNK1002-3 Shaft diameter: 10; lead: 2... A15-152

BNK1004-2.5 Shaft diameter: 10; lead: 4... A15-154

BNK1010-1.5 Shaft diameter: 10; lead: 10... A15-156

BNK1202-3 Shaft diameter: 12; lead: 2... A15-158

BNK1205-2.5 Shaft diameter: 12; lead: 5... A15-160

BNK1208-2.6 Shaft diameter: 12; lead: 8... A15-162

BNK1402-3 Shaft diameter: 14; lead: 2... A15-164

BNK1404-3 Shaft diameter: 14; lead: 4... A15-166

BNK1408-2.5 Shaft diameter: 14; lead: 8... A15-168

BNK1510-5.6 Shaft diameter: 15; lead: 10... A15-170

BNK1520-3 Shaft diameter: 15; lead: 20... A15-172

BNK1616-3.6 Shaft diameter: 16; lead: 16... A15-174

BNK2010-2.5 Shaft diameter: 20; lead: 10... A15-176

BNK2020-3.6 Shaft diameter: 20; lead: 20... A15-178

BNK2520-3.6 Shaft diameter: 25; lead: 20... A15-180

Model MDK..... A15-182

Model MBF ..... A15-188

Model BNF-V..... A15-192

Model BNF..... A15-198

Model DK ..... A15-202

Model WHF ..... A15-210

Model BLK..... A15-212

Model WGF ..... A15-214

Model BNT..... A15-216

|   |                |
|---|----------------|
| <b>High-Thrust Ball Screw</b> .....   | <b>A15-218</b> |
| • Standard combinations of outer diameters and leads of the screw shafts .. | <b>A15-220</b> |
| • Examples of Assembling Models HBN-V, HBN-K, HBN-KA, HBN, and SBKH .....   | <b>A15-222</b> |

### Dimensional Drawing, Dimensional Table

|                               |                |
|-------------------------------|----------------|
| Model HBN-V .....             | <b>A15-224</b> |
| Models HBN-K and HBN-KA ..... | <b>A15-226</b> |
| Model HBN .....               | <b>A15-232</b> |
| Model SBKH .....              | <b>A15-234</b> |

### Transport Ball Screw

- Standard combinations of outer diameters and leads of the screw shafts .. **A15-238**

### Dimensional Drawing, Dimensional Table

|                   |                |
|-------------------|----------------|
| Model JPF .....   | <b>A15-240</b> |
| Model BTK-V ..... | <b>A15-242</b> |
| Model BNT .....   | <b>A15-244</b> |
| Model BLK .....   | <b>A15-246</b> |
| Model WTF .....   | <b>A15-248</b> |
| Model CNF .....   | <b>A15-250</b> |
| Model MTF .....   | <b>A15-252</b> |

### Rotary Nut Ball Screw

- Standard combinations of outer diameters and leads of the screw shafts .. **A15-258**
- Accuracy Standards .. **A15-260**
- Example of Assembly .. **A15-265**
- Action Patterns .. **A15-267**
- Example of Assembly .. **A15-270**
- Example of Use .. **A15-271**
- Precautions on Use .. **A15-272**
- Permissible Rotational Speeds for Rotary Ball Screws .. **A15-273**

### Dimensional Drawing, Dimensional Table

|  |                |
|--|----------------|
| Model DIR .....                                      | <b>A15-274</b> |
| Model BLR .....                                      | <b>A15-276</b> |
| Model BNS-V .....                                    | <b>A15-280</b> |
| Model BNS-A .....                                    | <b>A15-282</b> |
| Model BNS .....                                      | <b>A15-284</b> |
| Model NS-V .....                                     | <b>A15-286</b> |
| Model NS-A .....                                     | <b>A15-288</b> |
| Model NS .....                                       | <b>A15-290</b> |
| • Ball Screw/Spline Permissible Rotational Speeds .. | <b>A15-292</b> |
| • Maximum Manufacturing Length of the Screw Shaft .. | <b>A15-294</b> |

### Ball Screw Peripherals

**A15-297**

### Support Unit

#### Models EK, BK, FK, EF, BF and FF

- Structure and Features .. **A15-298**
- Type .. **A15-300**
- Types of Support Units and Applicable Screw Shaft Outer Diameters .. **A15-301**
- Model Numbers of Bearings and Characteristic Values .. **A15-302**
- Example of Installation .. **A15-303**
- Mounting Procedure .. **A15-304**
- Types of Recommended Shapes of the Shaft Ends .. **A15-306**

### Dimensional Drawing, Dimensional Table

|   |                |
|---|----------------|
| Model EK Square Type Support Unit on the Fixed Side ..  | <b>A15-308</b> |
| Model BK Square Type Support Unit on the Fixed Side ..  | <b>A15-310</b> |
| Model FK Round Type Support Unit on the Fixed Side ..   | <b>A15-312</b> |
| Model EF Square Type Support Unit on the Supported Side ..  | <b>A15-316</b> |
| Model BF Square Type Support Unit on the Supported Side ..  | <b>A15-318</b> |
| Model FF Round Type Support Unit on the Supported Side ..   | <b>A15-320</b> |
| Recommended Shapes of Shaft Ends - Shape H (H1, H2 and H3) (For Support Unit Models FK and EK) .. | <b>A15-322</b> |
| Recommended Shapes of Shaft Ends - Shape J (J1, J2 and J3) (For Support Unit Model BK) ..         | <b>A15-324</b> |
| Recommended Shapes of Shaft Ends - Shape K (For Support Unit Models FF, EF and BF) ..             | <b>A15-326</b> |

### Nut Bracket (Model MC)

- Structure and Features .. **A15-328**
- Type .. **A15-328**

### Dimensional Drawing, Dimensional Table

|                   |                |
|-------------------|----------------|
| Nut Bracket ..... | <b>A15-329</b> |
|-------------------|----------------|

### Lock Nut (Model RN)

- Structure and Features .. **A15-330**
- Type .. **A15-330**

### Dimensional Drawing, Dimensional Table

|                |                |
|----------------|----------------|
| Lock Nut ..... | <b>A15-331</b> |
|----------------|----------------|

### Options

|  |                |
|--|----------------|
| Contaminaton Protection .....  | <b>A15-334</b> |
| Lubrication .....  | <b>A15-335</b> |
| Corrosion Resistance (Surface Treatment, etc.) ..                                  | <b>A15-335</b> |
| Contamination Protection Seal for Ball Screws ..                                   | <b>A15-336</b> |
| Wiper Ring W .....   | <b>A15-337</b> |
| Canvas seal CC .....   | <b>A15-339</b> |
| Dust Cover for Ball Screws .....   | <b>A15-341</b> |
| QZ Lubricator .....  | <b>A15-342</b> |
| Dimensions of Each Model with an Option Attached ..                                | <b>A15-344</b> |
| • Dimensions of the Ball Screw Nut Attached with Wiper Ring W and QZ Lubricator .. | <b>A15-344</b> |

- Ball Screw Nut Dimensions with Canvas Seal... **A** 15-353
- Specifications of the Bellows ..... **A** 15-356

**Model No.** ..... **A** 15-357

- Model Number Coding..... **A** 15-357
- Notes on Ordering..... **A** 15-361

**Precautions on Use** ..... **A** 15-362

Precautions on Using Options for the Ball Screw . **A** 15-364

- QZ Lubricator for the Ball Screw ..... **A** 15-364

## **B** Support Book (Separate)

|   |                 |
|---|-----------------|
| <b>Features and Types</b> .....   | <b>B</b> 15-6   |
| Features of the Ball Screw .....  | <b>B</b> 15-6   |
| • Driving Torque One Third of the Sliding Screw ..                        | <b>B</b> 15-6   |
| • Examples of Calculating Driving Torque .....                            | <b>B</b> 15-8   |
| • Ensuring High Accuracy .....  | <b>B</b> 15-9   |
| • Capable of Micro Feeding .....  | <b>B</b> 15-10  |
| • High Rigidity without Backlash .....                                    | <b>B</b> 15-11  |
| • Capable of Fast Feed .....  | <b>B</b> 15-12  |
| Overview of THK Ball Screws .....   | <b>B</b> 15-14  |
| <b>Point of Selection</b> .....   | <b>B</b> 15-16  |
| Flowchart for Selecting a Ball Screw .....                                | <b>B</b> 15-16  |
| Accuracy of the Ball Screw .....  | <b>B</b> 15-19  |
| • Lead Angle Accuracy .....   | <b>B</b> 15-19  |
| • Accuracy of the Mounting Surface .....                                  | <b>B</b> 15-22  |
| • Axial Clearance .....   | <b>B</b> 15-27  |
| • Preload .....   | <b>B</b> 15-28  |
| • Example of calculating the preload torque .....                         | <b>B</b> 15-31  |
| Selecting a Screw Shaft .....   | <b>B</b> 15-32  |
| • Maximum Manufacturing Length of the Screw Shaft ..                      | <b>B</b> 15-32  |
| • Combinations of Shaft Diameter and Lead for the Precision Ball Screw .. | <b>B</b> 15-34  |
| • Combinations of Shaft Diameter and Lead for the Rolled Ball Screw ..    | <b>B</b> 15-35  |
| Method for Mounting the Ball Screw Shaft ..                               | <b>B</b> 15-36  |
| Permissible Axial Load .....  | <b>B</b> 15-38  |
| Permissible Rotational Speed .....  | <b>B</b> 15-40  |
| Selecting a Nut .....   | <b>B</b> 15-43  |
| • Types of Nuts .....   | <b>B</b> 15-43  |
| Selecting a Model Number .....  | <b>B</b> 15-46  |
| • Calculating the Axial Load .....  | <b>B</b> 15-46  |
| • Static Safety Factor .....  | <b>B</b> 15-47  |
| • Studying the Service Life .....   | <b>B</b> 15-48  |
| Studying the Rigidity .....   | <b>B</b> 15-51  |
| • Axial Rigidity of the Feed Screw System ..                              | <b>B</b> 15-51  |
| Studying the Positioning Accuracy .....                                   | <b>B</b> 15-55  |
| • Causes of Error in the Positioning Accuracy ..                          | <b>B</b> 15-55  |
| • Studying the Lead Angle Accuracy .....                                  | <b>B</b> 15-55  |
| • Studying the Axial Clearance .....                                      | <b>B</b> 15-55  |
| • Studying the Axial Clearance of the Feed Screw System ..                | <b>B</b> 15-57  |
| • Example of considering the rigidity of a feed screw system ..           | <b>B</b> 15-57  |
| • Studying the Thermal Displacement through Heat Generation ...           | <b>B</b> 15-59  |
| • Studying the Orientation Change during Traveling ..                     | <b>B</b> 15-60  |
| Studying the Rotational Torque .....                                      | <b>B</b> 15-61  |
| • Frictional Torque Due to an External Load ..                            | <b>B</b> 15-61  |
| • Torque Due to a Preload on the Ball Screw ..                            | <b>B</b> 15-62  |
| • Torque Required for Acceleration .....                                  | <b>B</b> 15-63  |
| • Investigating the Terminal Strength of Ball Screw Shafts ..             | <b>B</b> 15-64  |
| Studying the Driving Motor .....  | <b>B</b> 15-66  |
| • When Using a Servomotor .....   | <b>B</b> 15-66  |
| • When Using a Stepping Motor (Pulse Motor) ..                            | <b>B</b> 15-68  |
| Examples of Selecting a Ball Screw .....                                  | <b>B</b> 15-69  |
| • High-speed Transfer Equipment (Horizontal Use) ..                       | <b>B</b> 15-69  |
| • Vertical Conveyance System .....  | <b>B</b> 15-83  |
| <b>Options</b> .....  | <b>B</b> 15-95  |
| Contaminaton Protection .....   | <b>B</b> 15-96  |
| Lubrication .....   | <b>B</b> 15-97  |
| Corrosion Resistance (Surface Treatment, etc.) ..                         | <b>B</b> 15-97  |
| Contamination Protection Seal for Ball Screws ..                          | <b>B</b> 15-98  |
| Wiper Ring W .....  | <b>B</b> 15-99  |
| Canvas seal CC .....  | <b>B</b> 15-101 |
| Dust Cover for Ball Screws .....  | <b>B</b> 15-103 |
| QZ Lubricator .....   | <b>B</b> 15-104 |
| <b>Mounting Procedure and Maintenance</b> ..                              | <b>B</b> 15-106 |
| Mounting Procedure .....  | <b>B</b> 15-106 |
| • Installing the Support Unit .....                                       | <b>B</b> 15-106 |
| • Installation onto the Table and the Base ..                             | <b>B</b> 15-106 |
| • Checking the Accuracy and Fully Fastening the Support Unit ...          | <b>B</b> 15-107 |
| • Connection with the Motor .....   | <b>B</b> 15-107 |
| Maintenance Method .....  | <b>B</b> 15-108 |
| • Amount of Lubricant .....   | <b>B</b> 15-108 |
| <b>Model No.</b> .....  | <b>B</b> 15-109 |
| • Model Number Coding .....   | <b>B</b> 15-109 |
| • Notes on Ordering .....   | <b>B</b> 15-113 |
| <b>Precautions on Use</b> .....   | <b>B</b> 15-114 |
| Precautions on Using Options for the Ball Screw ..                        | <b>B</b> 15-116 |
| • QZ Lubricator for the Ball Screw .....                                  | <b>B</b> 15-116 |

# Overview of THK Ball Screws

## Positioning Ball Screw

▲15-72

ISO 3408 compliant

## Positioning Ball Screw

▲15-102

Preload

Preload/  
No preload

Preload

Preload/  
No preload

No preload

### SDAN-V

Caged Ball

Double nut

High speed

Compact

### SDAN-VX

Double nut

High speed

Compact

### EPB-V

High speed

Compact

### SDA-V

Caged Ball

High speed

Various leads

Compact

### SDA-VZ

High speed

Various leads

Compact

### EBB-V

High speed

Compact

### SBN-V

Caged Ball

High speed

### SBK

Caged Ball

High speed

Large lead

### BIF-V

High speed

### BNFN-V

Double nut

High speed

### DIK

Compact

### DKN

Compact

Double nut

### BLW

Double nut

Large lead

### BNK

Standard to large lead

### MDK

### MBF

Miniature

### BNF-V

High speed

### DK

Compact

### WHF

High speed

Large lead

### BLK

### WGF


Large lead

### BNT

Flat nut

## Features and Types


### Overview of THK Ball Screws



## Flowchart for Selecting a Ball Screw


### [Ball Screw Selection Procedure]

When selecting a Ball Screw, it is necessary to make a selection while considering various parameters. The following is a flowchart for selecting a Ball Screw.





**Point of Selection**  
Flowchart for Selecting a Ball Screw



## [Conditions of the Ball Screw]

The following conditions are required when selecting a Ball Screw.

Transfer orientation (horizontal, vertical, etc.)  
 Transferred mass  $m$  (kg)  
 Table guide method (sliding, rolling)  
 Frictional coefficient of the guide surface  $\mu$  (—)  
 Guide surface resistance  $f$  (N)  
 External load in the axial direction  $F$  (N)  
 Desired service life time  $L_h$  (h)

Stroke length  $l_s$  (mm)  
 Operating speed  $V_{max}$  (m/s)  
 Acceleration time  $t_1$  (s)  
 Even speed time  $t_2$  (s)  
 Deceleration time  $t_3$  (s)

Acceleration  $\alpha = \frac{V_{max}}{t_1}$  (m/s<sup>2</sup>)

Acceleration distance  $l_1 = V_{max} \times t_1 \times 1000/2$  (mm)

Even speed distance  $l_2 = V_{max} \times t_2 \times 1000$  (mm)

Deceleration distance  $l_3 = V_{max} \times t_3 \times 1000/2$  (mm)

Number of reciprocations per minute  $n$  (min<sup>-1</sup>)

Positioning accuracy (mm)

Positioning accuracy repeatability (mm)

Backlash (mm)

Minimum feed amount  $s$  (mm/pulse)


Driving motor (AC servomotor, stepping motor, etc.)

The rated rotation speed of the motor  $N_{MO}$  (min<sup>-1</sup>)

Inertial moment of the motor  $J_M$  (kg·m<sup>2</sup>)

Motor resolution (pulse/rev)

Reduction ratio  $A$  (—)



Velocity diagram

# Accuracy of the Ball Screw

## Lead Angle Accuracy

The lead angle accuracy of the ball screw is controlled in accordance with the JIS standard JIS B 1192 (ISO 3408).

Accuracy grades C0 to C5 are defined in the linearity and the directional property, and C7 to C10 in the travel distance error in relation to 300 mm.




Fig.1 Terms on Lead Angle Accuracy

### [Actual Travel Distance]

An error in the travel distance measured with an actual Ball Screw.

### [Reference Travel Distance]

Generally, it is the same as nominal travel distance, but can be an intentionally corrected value of the nominal travel distance according to the intended use.

### [Target Value for Reference Travel Distance]

You may provide some tension in order to prevent the screw shaft from runout, or set the reference travel distance in “negative” or “positive” value in advance given the possible expansion/contraction from external load or temperature. In such cases, indicate a target value for the reference travel distance.

### [Representative Travel Distance]

It is a straight line representing the tendency in the actual travel distance, and obtained with the least squares method from the curve that indicates the actual travel distance.

### [Representative Travel Distance Error (in $\pm$ )]

Difference between the representative travel distance and the reference travel distance.

### [Fluctuation]

The maximum width of the actual travel distance between two straight lines drawn in parallel with the representative travel distance.

### [Fluctuation/300]

Indicates a fluctuation against a given thread length of 300 mm.

### [Fluctuation/2 $\pi$ ]

A fluctuation in one revolution of the screw shaft.

Table1 Lead Angle Accuracy (Permissible Value)

Unit:  $\mu\text{m}$ 

| Accuracy grades         |         | Precision Ball Screw                 |             |                                      |             |                                      |             |                                      |             |                                      |             | Rolled Ball Screw     |                       |                       |
|-------------------------|---------|--------------------------------------|-------------|--------------------------------------|-------------|--------------------------------------|-------------|--------------------------------------|-------------|--------------------------------------|-------------|-----------------------|-----------------------|-----------------------|
|                         |         | C0                                   |             | C1                                   |             | C2                                   |             | C3                                   |             | C5                                   |             | C7                    | C8                    | C10                   |
| Effective thread length |         | Representative travel distance error | Fluctuation | Representative travel distance error | Fluctuation | Representative travel distance error | Fluctuation | Representative travel distance error | Fluctuation | Representative travel distance error | Fluctuation | Travel distance error | Travel distance error | Travel distance error |
| Above                   | Or less |                                      |             |                                      |             |                                      |             |                                      |             |                                      |             |                       |                       |                       |
| —                       | 100     | 3                                    | 3           | 3.5                                  | 5           | 5                                    | 7           | 8                                    | 8           | 18                                   | 18          | $\pm 50/$<br>300 mm   | $\pm 100/$<br>300 mm  | $\pm 210/$<br>300 mm  |
| 100                     | 200     | 3.5                                  | 3           | 4.5                                  | 5           | 7                                    | 7           | 10                                   | 8           | 20                                   | 18          |                       |                       |                       |
| 200                     | 315     | 4                                    | 3.5         | 6                                    | 5           | 8                                    | 7           | 12                                   | 8           | 23                                   | 18          |                       |                       |                       |
| 315                     | 400     | 5                                    | 3.5         | 7                                    | 5           | 9                                    | 7           | 13                                   | 10          | 25                                   | 20          |                       |                       |                       |
| 400                     | 500     | 6                                    | 4           | 8                                    | 5           | 10                                   | 7           | 15                                   | 10          | 27                                   | 20          |                       |                       |                       |
| 500                     | 630     | 6                                    | 4           | 9                                    | 6           | 11                                   | 8           | 16                                   | 12          | 30                                   | 23          |                       |                       |                       |
| 630                     | 800     | 7                                    | 5           | 10                                   | 7           | 13                                   | 9           | 18                                   | 13          | 35                                   | 25          |                       |                       |                       |
| 800                     | 1000    | 8                                    | 6           | 11                                   | 8           | 15                                   | 10          | 21                                   | 15          | 40                                   | 27          |                       |                       |                       |
| 1000                    | 1250    | 9                                    | 6           | 13                                   | 9           | 18                                   | 11          | 24                                   | 16          | 46                                   | 30          |                       |                       |                       |
| 1250                    | 1600    | 11                                   | 7           | 15                                   | 10          | 21                                   | 13          | 29                                   | 18          | 54                                   | 35          |                       |                       |                       |
| 1600                    | 2000    | —                                    | —           | 18                                   | 11          | 25                                   | 15          | 35                                   | 21          | 65                                   | 40          |                       |                       |                       |
| 2000                    | 2500    | —                                    | —           | 22                                   | 13          | 30                                   | 18          | 41                                   | 24          | 77                                   | 46          |                       |                       |                       |
| 2500                    | 3150    | —                                    | —           | 26                                   | 15          | 36                                   | 21          | 50                                   | 29          | 93                                   | 54          |                       |                       |                       |
| 3150                    | 4000    | —                                    | —           | 30                                   | 18          | 44                                   | 25          | 60                                   | 35          | 115                                  | 65          |                       |                       |                       |
| 4000                    | 5000    | —                                    | —           | —                                    | —           | 52                                   | 30          | 72                                   | 41          | 140                                  | 77          |                       |                       |                       |
| 5000                    | 6300    | —                                    | —           | —                                    | —           | 65                                   | 36          | 90                                   | 50          | 170                                  | 93          |                       |                       |                       |
| 6300                    | 8000    | —                                    | —           | —                                    | —           | —                                    | —           | 110                                  | 60          | 210                                  | 115         |                       |                       |                       |
| 8000                    | 10000   | —                                    | —           | —                                    | —           | —                                    | —           | —                                    | —           | 260                                  | 140         |                       |                       |                       |

Note) Unit of effective thread length: mm

Table2 Fluctuation in Thread Length of 300 mm and in One Revolution (permissible value)

Unit:  $\mu\text{m}$ 

| Accuracy grades     | C0  | C1 | C2 | C3 | C5 | C7 | C8 | C10 |
|---------------------|-----|----|----|----|----|----|----|-----|
| Fluctuation/300     | 3.5 | 5  | 7  | 8  | 18 | —  | —  | —   |
| Fluctuation/ $2\pi$ | 3   | 4  | 5  | 6  | 8  | —  | —  | —   |

Table3 Types and Grades

| Type            | Grade             | Remarks       |
|-----------------|-------------------|---------------|
| For positioning | 0, 1, 3, 5        | ISO compliant |
| For transport   | 0, 1, 3, 5, 7, 10 |               |

## Point of Selection

## Accuracy of the Ball Screw

Example: When the lead of a Ball Screw manufactured is measured with a target value for the reference travel distance of  $-9 \mu\text{m}/500 \text{ mm}$ , the following data are obtained.

Table4 Measurement Data on Travel Distance Error

Unit: mm

|                             |         |         |         |         |
|-----------------------------|---------|---------|---------|---------|
| Command position (A)        | 0       | 50      | 100     | 150     |
| Travel distance (B)         | 0       | 49.998  | 100.001 | 149.996 |
| Travel distance error (A-B) | 0       | -0.002  | +0.001  | -0.004  |
| Command position (A)        | 200     | 250     | 300     | 350     |
| Travel distance (B)         | 199.995 | 249.993 | 299.989 | 349.985 |
| Travel distance error (A-B) | -0.005  | -0.007  | -0.011  | -0.015  |
| Command position (A)        | 400     | 450     | 500     |         |
| Travel distance (B)         | 399.983 | 449.981 | 499.984 |         |
| Travel distance error (A-B) | -0.017  | -0.019  | -0.016  |         |

The measurement data are expressed in a graph as shown in Fig.2.

The positioning error (A-B) is indicated as the actual travel distance while the straight line representing the tendency of the (A-B) graph refers to the representative travel distance.

The difference between the reference travel distance and the representative travel distance appears as the representative travel distance error.




Fig.2 Measurement Data on Travel Distance Error


[Measurements]

Representative travel distance error:  $-7 \mu\text{m}$

Fluctuation:  $8.8 \mu\text{m}$

## Accuracy of the Mounting Surface

The accuracy of the Ball Screw mounting surface complies with the JIS standard JIS B 1192 (ISO 3408).



Note) For the permissible overall radial runout of the outer diameter of the screw in relation to the screw shaft support axis, refer to JIS B 1192 (ISO 3408).

Fig.3 Accuracy of the Mounting Surface of the Ball Screw

### [Accuracy Standards for the Mounting Surface]


Table5 to Table9 show accuracy standards for the mounting surfaces of the precision Ball Screw.

Table5 Permissible Radial Runout of the Grooved Surface of the Screw in Relation to the Screw Shaft Support Axis and the Permissible Radial Runout of the Part-Mounting Surface  
Unit:  $\mu\text{m}$

| Screw shaft outer diameter (mm) |         | Runout (maximum) |    |    |    |    |    |
|---------------------------------|---------|------------------|----|----|----|----|----|
| Above                           | Or less | C0               | C1 | C2 | C3 | C5 | C7 |
| —                               | 8       | 3                | 5  | 7  | 8  | 10 | 14 |
| 8                               | 12      | 4                | 5  | 7  | 8  | 11 | 14 |
| 12                              | 20      | 4                | 6  | 8  | 9  | 12 | 14 |
| 20                              | 32      | 5                | 7  | 9  | 10 | 13 | 20 |
| 32                              | 50      | 6                | 8  | 10 | 12 | 15 | 20 |
| 50                              | 80      | 7                | 9  | 11 | 13 | 17 | 20 |
| 80                              | 100     | —                | 10 | 12 | 15 | 20 | 30 |

Note) The measurements on these items include the effect of the runout of the screw shaft diameter. Therefore, it is necessary to obtain the correction value from the overall runout of the screw shaft axis, using the ratio of the distance between the fulcrum and measurement point to the overall screw shaft length, and add the obtained value to the table above.

Example: model No. DIK2005-6RRGO+500LC5



$$E_1 = e + \Delta e$$

$e$  : Standard value in Table5(0.012)

$\Delta e$  : Correction value

$$\Delta e = \frac{L_1}{L} \times E_2$$

$$= \frac{80}{500} \times 0.06$$

$$= 0.01$$

$L$  : Overall screw shaft length

$L_1$  : Distance between the fulcrum and the measurement point

$E_2$  : Overall radial runout of the screw shaft axis (0.06)

$$E_1 = 0.012 + 0.01$$

$$= 0.022$$

Note) For the permissible overall radial runout of the outer diameter of the screw in relation to the screw shaft support axis, refer to JIS B 1192 (ISO 3408).

Table6 Permissible Axial Runout of the Support End Face in Relation to the Screw Shaft Support Axis

Unit:  $\mu\text{m}$ 

| Screw shaft outer diameter (mm) |         | Permissible Axial runout (maximum) |    |    |    |    |    |
|---------------------------------|---------|------------------------------------|----|----|----|----|----|
| Above                           | Or less | C0                                 | C1 | C2 | C3 | C5 | C7 |
| —                               | 8       | 2                                  | 3  | 3  | 4  | 5  | 7  |
| 8                               | 12      | 2                                  | 3  | 3  | 4  | 5  | 7  |
| 12                              | 20      | 2                                  | 3  | 3  | 4  | 5  | 7  |
| 20                              | 32      | 2                                  | 3  | 3  | 4  | 5  | 7  |
| 32                              | 50      | 2                                  | 3  | 3  | 4  | 5  | 8  |
| 50                              | 80      | 3                                  | 4  | 4  | 5  | 7  | 10 |
| 80                              | 100     | —                                  | 4  | 5  | 6  | 8  | 11 |

Table7 Permissible Axial Runout of the Flange Mounting Surface in Relation to the Screw Shaft Axis

Unit:  $\mu\text{m}$ 

| Nut diameter (mm) |         | Permissible Axial runout (maximum) |    |    |    |    |    |
|-------------------|---------|------------------------------------|----|----|----|----|----|
| Above             | Or less | C0                                 | C1 | C2 | C3 | C5 | C7 |
| —                 | 20      | 5                                  | 6  | 7  | 8  | 10 | 14 |
| 20                | 32      | 5                                  | 6  | 7  | 8  | 10 | 14 |
| 32                | 50      | 6                                  | 7  | 8  | 8  | 11 | 18 |
| 50                | 80      | 7                                  | 8  | 9  | 10 | 13 | 18 |
| 80                | 125     | 7                                  | 9  | 10 | 12 | 15 | 20 |
| 125               | 160     | 8                                  | 10 | 11 | 13 | 17 | 20 |
| 160               | 200     | —                                  | 11 | 12 | 14 | 18 | 25 |

Table8 Permissible Radial Runout of the Nut Circumference in Relation to the Screw Shaft Axis

Unit:  $\mu\text{m}$ 

| Nut diameter (mm) |         | Permissible radial runout |    |    |    |    |    |
|-------------------|---------|---------------------------|----|----|----|----|----|
| Above             | Or less | C0                        | C1 | C2 | C3 | C5 | C7 |
| —                 | 20      | 5                         | 6  | 7  | 9  | 12 | 20 |
| 20                | 32      | 6                         | 7  | 8  | 10 | 12 | 20 |
| 32                | 50      | 7                         | 8  | 10 | 12 | 15 | 30 |
| 50                | 80      | 8                         | 10 | 12 | 15 | 19 | 30 |
| 80                | 125     | 9                         | 12 | 16 | 20 | 27 | 40 |
| 125               | 160     | 10                        | 13 | 17 | 22 | 30 | 40 |
| 160               | 200     | —                         | 16 | 20 | 25 | 34 | 50 |

Table9 Permissible Parallelism of the Nut Circumference (Flat Mounting Surface) to the Screw Shaft Axis


Unit:  $\mu\text{m}$ 

| Mounting reference length (mm) |         | Permissible parallelism |    |    |    |    |    |
|--------------------------------|---------|-------------------------|----|----|----|----|----|
| Above                          | Or less | C0                      | C1 | C2 | C3 | C5 | C7 |
| —                              | 50      | 5                       | 6  | 7  | 8  | 10 | 17 |
| 50                             | 100     | 7                       | 8  | 9  | 10 | 13 | 17 |
| 100                            | 200     | —                       | 10 | 11 | 13 | 17 | 30 |

### [Method for Measuring Accuracy of the Mounting Surface]

#### ● Radial Runout of the Circumference of the Motor-mounting Shaft-end in Relation to the Bearing Journals of the Screw Shaft (see Table5 on **A15-15**)


Support the end journal of the screw shaft on V blocks. Place a probe on the circumference of the motor-mounting shaft-end, and record the largest difference on the dial gauge as a measurement while rotating the screw shaft through one revolution.






● **Radial Runout of the Circumference of the Raceway Threads in Relation to the Bearing Journals of the Screw Shaft (see Table5 on A15-15)**

Support the end journal of the screw shaft on V blocks. Place a probe on the circumference of the nut, and record the largest difference on the dial gauge as a measurement while rotating the screw shaft by one revolution without rotating the nut.




● **Axial Runout of the Support End Face in Relation to the Screw Shaft Axis Support (see Table6 on A15-16)**

Support the bearing journal portions of the screw shaft on V blocks. Place a probe on the screw shaft's supporting portion end, and record the largest difference on the dial gauge as a measurement while rotating the screw shaft through one revolution.




● **Axial Runout of the Flange Mounting Surface in Relation to the Screw Shaft Axis (see Table7 on A15-16)**

Support the thread of the screw shaft on V blocks near the nut. Place a probe on the flange end, and record the largest difference on the dial gauge as a measurement while simultaneously rotating the screw shaft and the nut through one revolution.




● **Radial Runout of the Nut Circumference in Relation to the Screw Shaft Axis (see Table 8 on A15-16)**

Support the thread of the screw shaft on V blocks near the nut. Place a probe on the circumference of the nut, and record the largest difference on the dial gauge as a measurement while rotating the nut through one revolution without rotating the screw shaft.




● **Parallelism of the Nut Circumference (Flat Mounting Surface) to the Screw Shaft Axis (see Table 9 on A15-16)**

Support the thread of the screw shaft on V blocks near the nut. Place a probe on the circumference of the nut (flat mounting surface), and record the largest difference on the dial gauge as a measurement while moving the dial gauge in parallel with the screw shaft.



● **Overall Radial Runout of the Screw Diameter Relative to the Shaft Support Axis**

Support the supporting portion of the screw shaft on V blocks. Place a probe on the circumference of the screw shaft, and record the largest difference on the dial gauge at several points in the axial directions as a measurement while rotating the screw shaft through one revolution.



Note) For the permissible overall radial runout of the outer diameter of the screw in relation to the screw shaft support axis, refer to JIS B 1192 (ISO 3408).

## Axial Clearance

### [Axial Clearance of the Precision Ball Screw]

Table10 shows the axial clearance of the precision Ball Screw. If the manufacturing length exceeds the value in Table11, the resultant clearance may partially be negative (preload applied).

The manufacturing limit lengths of the Ball Screws compliant with the DIN standard are provided in Table12. For the axial clearance of the Precision Caged Ball Screw, see **A15-76** to **A15-93**, **A15-110** to **A15-117**, **A15-224** to **A15-235**.

Table10 Axial Clearance of the Precision Ball Screw

Unit: mm

| Clearance symbol | G0        | GT         | G1        | G2        | G3        |
|------------------|-----------|------------|-----------|-----------|-----------|
| Axial Clearance  | 0 or less | 0 to 0.005 | 0 to 0.01 | 0 to 0.02 | 0 to 0.05 |

Table11 Maximum Manufacturing Length of Precision Ball Screws by Axial Clearance and Accuracy Grade

Unit: mm

| Screw shaft<br>outer diameter | Clearance GT |      |       |      | Clearance G1 |      |       |      | Clearance G2 |      |      |      |      |      |  |
|-------------------------------|--------------|------|-------|------|--------------|------|-------|------|--------------|------|------|------|------|------|--|
|                               | C0           | C1   | C2·C3 | C5   | C0           | C1   | C2·C3 | C5   | C0           | C1   | C2   | C3   | C5   | C7   |  |
| 4·6                           | 80           | 80   | 80    | 100  | 80           | 80   | 80    | 100  | 80           | 80   | 80   | 80   | 100  | 120  |  |
| 8                             | 230          | 250  | 250   | 200  | 230          | 250  | 250   | 250  | 230          | 250  | 250  | 250  | 300  | 300  |  |
| 10                            | 250          | 250  | 250   | 200  | 250          | 250  | 250   | 250  | 250          | 250  | 250  | 250  | 300  | 300  |  |
| 12·13                         | 440          | 500  | 500   | 400  | 440          | 500  | 500   | 500  | 440          | 500  | 630  | 680  | 600  | 500  |  |
| 14                            | 500          | 500  | 500   | 400  | 500          | 500  | 500   | 500  | 530          | 620  | 700  | 700  | 600  | 500  |  |
| 15                            | 500          | 500  | 500   | 400  | 500          | 500  | 500   | 500  | 570          | 670  | 700  | 700  | 600  | 500  |  |
| 16                            | 500          | 500  | 500   | 400  | 500          | 500  | 500   | 500  | 620          | 700  | 700  | 700  | 600  | 500  |  |
| 18                            | 720          | 800  | 800   | 700  | 720          | 800  | 800   | 700  | 720          | 840  | 1000 | 1000 | 1000 | 1000 |  |
| 20                            | 800          | 800  | 800   | 700  | 800          | 800  | 800   | 700  | 820          | 950  | 1000 | 1000 | 1000 | 1000 |  |
| 25                            | 800          | 800  | 800   | 700  | 800          | 800  | 800   | 700  | 1000         | 1000 | 1000 | 1000 | 1000 | 1000 |  |
| 28                            | 900          | 900  | 900   | 800  | 1100         | 1100 | 1100  | 900  | 1300         | 1400 | 1400 | 1400 | 1200 | 1200 |  |
| 30·32                         | 900          | 900  | 900   | 800  | 1100         | 1100 | 1100  | 900  | 1400         | 1400 | 1400 | 1400 | 1200 | 1200 |  |
| 36·40·45                      | 1000         | 1000 | 1000  | 800  | 1300         | 1300 | 1300  | 1000 | 2000         | 2000 | 2000 | 2000 | 1500 | 1500 |  |
| 50·55·63·70                   | 1200         | 1200 | 1200  | 1000 | 1600         | 1600 | 1600  | 1300 | 2000         | 2500 | 2500 | 2500 | 2000 | 2000 |  |
| 80·100                        | —            | —    | —     | —    | 1800         | 1800 | 1800  | 1500 | 2000         | 4000 | 4000 | 4000 | 3000 | 3000 |  |

\*When manufacturing the Ball Screw of precision-grade accuracy C7 with clearance GT or G1, the resultant clearance is partially negative.

G0 clearance is not available for models HBN-V, HBN-K (KA), HBN, and SBKH.

Accuracy grade C7 is not available when manufacturing a miniature ball screw (screw shaft outer diameter  $\phi$  14 mm or less) with a G0 clearance.

Table12 Manufacturing limit lengths of precision Ball Screws with axial clearances (DIN standard compliant Ball Screws)

Unit: mm

| Shaft<br>diameter | Clearance GT |              | Clearance G1 |              | Clearance G2 |              |         |
|-------------------|--------------|--------------|--------------|--------------|--------------|--------------|---------|
|                   | C3, Cp3      | C5, Cp5, Ct5 | C3, Cp3      | C5, Cp5, Ct5 | C3, Cp3      | C5, Cp5, Ct5 | C7, Cp7 |
| 16                | 500          | 400          | 500          | 500          | 700          | 600          | 500     |
| 20, 25            | 800          | 700          | 800          | 700          | 1000         | 1000         | 1000    |
| 32                | 900          | 800          | 1100         | 900          | 1400         | 1200         | 1200    |
| 40                | 1000         | 800          | 1300         | 1000         | 2000         | 1500         | 1500    |
| 50, 63            | 1200         | 1000         | 1600         | 1300         | 2500         | 2000         | 2000    |

\*When manufacturing the Ball Screw of precision-grade accuracy C7 (Ct7) with clearance GT or G1, the resultant clearance is partially negative.

### [Axial Clearance of the Rolled Ball Screw]

Table13 shows axial clearance of the rolled Ball Screw.

Table13 Axial Clearance of the Rolled Ball Screw

Unit: mm

| Screw shaft outer diameter | Axial clearance (maximum) |
|----------------------------|---------------------------|
| 6 to 12                    | 0.05                      |
| 14 to 28                   | 0.1                       |
| 30 to 32                   | 0.14                      |
| 36 to 45                   | 0.17                      |
| 50                         | 0.2                       |

## Preload

A preload is provided in order to eliminate the axial clearance and minimize the displacement under an axial load.

When performing a highly accurate positioning, a preload is generally provided.

### [Rigidity of the Ball Screw under a Preload]

When a preload is provided to the Ball Screw, the rigidity of the nut is increased.

Fig.4 shows elastic displacement curves of the Ball Screw under a preload and without a preload.






Fig.4 Elastic Displacement Curve of the Ball Screw

Fig.5 shows a single-nut type of the Ball Screw.



The A and B sides are provided with preload  $F_{a0}$  by changing the groove pitch in the center of the nut to create a phase. Because of the preload, the A and B sides are elastically displaced by  $\delta_{a0}$  each. If an axial load ( $F_a$ ) is applied from outside in this state, the displacement of the A and B sides is calculated as follows.

$$\delta_A = \delta_{a0} + \delta a \quad \delta_B = \delta_{a0} - \delta a$$

In other words, the loads on the A and B sides are expressed as follows:

$$F_A = F_{a0} + (F_a - F_{a'}) \quad F_B = F_{a0} - F_{a'}$$

Therefore, under a preload, the load that the A side receives equals to  $F_a - F_{a'}$ . This means that since load  $F_{a'}$ , which is applied when the A side receives no preload, is deducted from  $F_a$ , the displacement of the A side is smaller.

This effect extends to the point where the displacement ( $\delta_{a0}$ ) caused by the preload applied on the B side reaches zero.

To what extent is the elastic displacement reduced? The relationship between the axial load on the Ball Screw under no preload and the elastic displacement can be expressed by  $\delta_a \propto F_a^{2/3}$ . From Fig.6, the following equations are established.

$$\delta_{a0} = K F_{a0}^{2/3} \quad (K : \text{constant})$$

$$2\delta_{a0} = K F_t^{2/3}$$

$$\left(\frac{F_t}{F_{a0}}\right)^{2/3} = 2 \quad F_t = 2^{3/2} \times F_{a0} = 2.8F_{a0} \doteq 3F_{a0}$$

Thus, the Ball Screw under a preload is displaced by  $\delta_{a0}$  when an axial load ( $F_t$ ) approximately three times greater than the preload is provided from outside. As a result, the displacement of the Ball Screw under a preload is half the displacement ( $2\delta_{a0}$ ) of the Ball Screw without a preload.

As stated above, since the preloading is effective up to approximately three times the applied preload, the optimum preload is one third of the maximum axial load.

Note that an excessive preload adversely affects the service life and heat generation. The maximum preload should be set at 10% of the basic dynamic load rating ( $C_a$ ) in the axial direction.

### [Preload Torque]

The preload torque of the Ball Screw is controlled in accordance with the JIS standard JIS B 1192 (ISO 3408).




Fig.7 Terms on Preload Torque

#### ● Dynamic Preload Torque

A torque required to continuously rotate the screw shaft of a Ball Screw under a given preload without an external load applied.

#### ● Actual Torque

A dynamic preload torque measured with an actual Ball Screw.

#### ● Torque Fluctuation

Variation in a dynamic preload torque set at a target value. It can be positive or negative in relation to the reference torque.

#### ● Coefficient of Torque Fluctuation

Ratio of torque fluctuation to the reference torque.

#### ● Reference Torque

A dynamic preload torque set as a target.

#### ● Calculating the Reference Torque

The reference torque of a Ball Screw provided with a preload is obtained in the following equation (4).

$$T_p = 0.05 (\tan\beta)^{-0.5} \frac{F_{a0} \cdot Ph}{2\pi} \dots\dots\dots (4)$$

|          |                    |        |
|----------|--------------------|--------|
| $T_p$    | : Reference torque | (N·mm) |
| $\beta$  | : Lead angle       |        |
| $F_{a0}$ | : Applied preload  | (N)    |
| $Ph$     | : Lead             | (mm)   |

## Point of Selection

### Accuracy of the Ball Screw

Example: When a preload of 3,000 N is provided to the Ball Screw model BIF4010-10G0 + 1500LC3 with a thread length of 1,300 mm (shaft diameter: 40 mm; ball center-to-center diameter: 41.75 mm; lead: 10 mm), the preload torque of the Ball Screw is calculated in the steps below.

#### ■Calculating the Reference Torque

$\beta$  : Lead angle

$$\tan\beta = \frac{\text{lead}}{\pi \times \text{ball center-to-center diameter}} = \frac{10}{\pi \times 41.75} = 0.0762$$

$F_{a0}$  : Applied preload=3000N

$Ph$  : Lead = 10mm

$$T_p = 0.05 (\tan\beta)^{-0.5} \frac{F_{a0} \cdot Ph}{2\pi} = 0.05 (0.0762)^{-0.5} \frac{3000 \times 10}{2\pi} = 865 \text{ N}\cdot\text{mm}$$

#### ■Calculating the Torque Fluctuation

$$\frac{\text{thread length}}{\text{screw shaft outer diameter}} = \frac{1300}{40} = 32.5 \leq 40$$

Thus, with the reference torque in Table14 being between 600 and 1,000 N·mm, effective thread length 4,000 mm or less and accuracy grade C3, the coefficient of torque fluctuation is obtained as  $\pm 30\%$ .

As a result, the torque fluctuation is calculated as follows.

$$865 \times (1 \pm 0.3) = 606 \text{ N}\cdot\text{mm} \text{ to } 1125 \text{ N}\cdot\text{mm}$$

#### ■Result

Reference torque : 865 N·mm

Torque fluctuation : 606 N·mm to 1125 N·mm

Table14 Tolerance Range in Torque Fluctuation

| Reference torque<br>N·mm |         | Effective thread length  |      |      |      |      |      |  |      |      |      |      |   |      |
|--------------------------|---------|--|------|------|------|------|------|--|------|------|------|------|---|------|
|                          |         | 4000mm or less   |      |      |      |      |      |  |      |      |      |      | Above 4,000 mm and<br>10,000 mm or less |      |
|                          |         | $\frac{\text{thread length}}{\text{screw shaft outer diameter}} \leq 40$ |      |      |      |      |      | $40 < \frac{\text{thread length}}{\text{screw shaft outer diameter}} < 60$ |      |      |      |      | —                                       |      |
|                          |         | Accuracy grades  |      |      |      |      |      | Accuracy grades  |      |      |      |      | Accuracy grades                         |      |
| Above                    | Or less | C0   | C1   | C3   | C5   | C7   | C0   | C1   | C3   | C5   | C7   | C3   | C5                                      | C7   |
| 200                      | 400     | ±30%   | ±35% | ±40% | ±50% | —    | ±40% | ±40%   | ±50% | ±60% | —    | —    | —                                       | —    |
| 400                      | 600     | ±25%   | ±30% | ±35% | ±40% | —    | ±35% | ±35%   | ±40% | ±45% | —    | —    | —                                       | —    |
| 600                      | 1000    | ±20%   | ±25% | ±30% | ±35% | ±40% | ±30% | ±30%   | ±35% | ±40% | ±45% | ±40% | ±45%                                    | ±50% |
| 1000                     | 2500    | ±15%   | ±20% | ±25% | ±30% | ±35% | ±25% | ±25%   | ±30% | ±35% | ±40% | ±35% | ±40%                                    | ±45% |
| 2500                     | 6300    | ±10%   | ±15% | ±20% | ±25% | ±30% | ±20% | ±20%   | ±25% | ±30% | ±35% | ±30% | ±35%                                    | ±40% |
| 6300                     | 10000   | —  | —    | ±15% | ±20% | ±30% | —    | —  | ±20% | ±25% | ±35% | ±25% | ±30%                                    | ±35% |

# Selecting a Screw Shaft

## Maximum Manufacturing Length of the Screw Shaft

Table15 shows the maximum manufacturing lengths of precision ball screws by accuracy grade, Table16 shows the maximum manufacturing lengths of precision ball screws compliant with DIN standards by accuracy grade, and Table17 shows the maximum manufacturing lengths of rolled ball screws by accuracy grade.

If the shaft dimensions exceed the maximum manufacturing lengths in Table15, Table16, or Table17, contact THK.

Table15 Maximum Manufacturing Length of Precision Ball Screws by Accuracy Grade

Unit: mm

| Screw shaft<br>outer diameter | Overall screw shaft length |      |      |       |       |       |
|-------------------------------|----------------------------|------|------|-------|-------|-------|
|                               | C0                         | C1   | C2   | C3    | C5    | C7    |
| 4                             | 90                         | 110  | 120  | 120   | 120   | 120   |
| 6                             | 150                        | 170  | 210  | 210   | 210   | 210   |
| 8                             | 230                        | 270  | 340  | 340   | 340   | 340   |
| 10                            | 350                        | 400  | 500  | 500   | 500   | 500   |
| 12                            | 440                        | 500  | 630  | 680   | 680   | 680   |
| 13                            | 440                        | 500  | 630  | 680   | 680   | 680   |
| 14                            | 530                        | 620  | 770  | 870   | 890   | 890   |
| 15                            | 570                        | 670  | 830  | 950   | 980   | 1100  |
| 16                            | 620                        | 730  | 900  | 1050  | 1100  | 1400  |
| 18                            | 720                        | 840  | 1050 | 1220  | 1350  | 1600  |
| 20                            | 820                        | 950  | 1200 | 1400  | 1600  | 1800  |
| 25                            | 1100                       | 1400 | 1600 | 1800  | 2000  | 2400  |
| 28                            | 1300                       | 1600 | 1900 | 2100  | 2350  | 2700  |
| 30                            | 1450                       | 1700 | 2050 | 2300  | 2570  | 2950  |
| 32                            | 1600                       | 1800 | 2200 | 2500  | 2800  | 3200  |
| 36                            | 2000                       | 2100 | 2550 | 2950  | 3250  | 3650  |
| 40                            | 2000                       | 2400 | 2900 | 3400  | 3700  | 4300  |
| 45                            | 2000                       | 2750 | 3350 | 3950  | 4350  | 5050  |
| 50                            | 2000                       | 3100 | 3800 | 4500  | 5000  | 5800  |
| 55                            | 2000                       | 3450 | 4150 | 5300  | 6050  | 6500  |
| 63                            | 2000                       | 4000 | 5200 | 5800  | 6700  | 7700  |
| 70                            | 2000                       | 4000 | 6300 | 6450  | 7650  | 9000  |
| 80                            | 2000                       | 4000 | 6300 | 7900  | 9000  | 11000 |
| 100                           | 2000                       | 4000 | 6300 | 11000 | 11000 | 11000 |

\*For ball screw models HBN-V, HBN-K (KA), HBN, and SBKH, the standard maximum length of the screw shaft is 3000 mm.  
For lengths greater than this, please contact THK.  
For details, refer to **A15-294**.



## Point of Selection

### Selecting a Screw Shaft

Table16 Maximum Manufacturing Length of Precision Ball Screws (DIN Standard-Compliant Ball Screws)

Unit: mm

| Shaft diameter | Ground shaft |      |      | CES shaft |      |      |      |
|----------------|--------------|------|------|-----------|------|------|------|
|                | C3           | C5   | C7   | Cp3       | Cp5  | Ct5  | Ct7  |
| 16             | 1050         | 1100 | 1400 | 1050      | 1100 | 1100 | 1400 |
| 20             | 1400         | 1600 | 1800 | 1400      | 1600 | 1600 | 1800 |
| 25             | 1800         | 2000 | 2400 | 1800      | 2000 | 2000 | 2400 |
| 32             | 2500         | 2800 | 3200 | 2500      | 2800 | 2800 | 3200 |
| 40             | 3400         | 3700 | 4300 | 3400      | 3700 | 3700 | 4300 |
| 50             | 4500         | 5000 | 5800 | —         | —    | —    | —    |
| 63             | 5800         | 6700 | 7700 | —         | —    | —    | —    |

Table17 Maximum Manufacturing Length of Rolled Ball Screws  
by Accuracy Grade

Unit: mm

| Screw shaft<br>outer diameter | Overall screw shaft length |      |      |
|-------------------------------|----------------------------|------|------|
|                               | C7                         | C8   | C10  |
| 6 to 8                        | 320                        | 320  | —    |
| 10 to 12                      | 500                        | 1000 | —    |
| 14 to 15                      | 1500                       | 1500 | 1500 |
| 16 to 18                      | 1500                       | 1800 | 1800 |
| 20                            | 2000                       | 2200 | 2200 |
| 25                            | 2000                       | 3000 | 3000 |
| 28                            | 3000                       | 3000 | 3000 |
| 30                            | 3000                       | 3000 | 4000 |
| 32 to 36                      | 3000                       | 4000 | 4000 |
| 40                            | 3000                       | 5000 | 5000 |
| 45                            | 3000                       | 5500 | 5500 |
| 50                            | 3000                       | 6000 | 6000 |

For details, refer to **A15-294**.

## Combinations of Shaft Diameter and Lead for the Precision Ball Screw

Table18 shows combinations of shaft diameters and leads of precision ball screws, and Table19 shows combinations of shaft diameters and leads of precision ball screws compliant with DIN standards.

If a ball screw not covered by the table is required, contact THK.

Table18 Combinations of Screw Shaft Diameter and Lead (Precision Ball Screw)

Unit: mm

| Screw shaft outer diameter | Lead |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |
|----------------------------|------|-----|---|-----|---|---|---|---|---|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|-----|---|---|
|                            | 1    | 1.5 | 2 | 2.5 | 3 | 4 | 5 | 6 | 8 | 10 | 12 | 15 | 16 | 20 | 24 | 25 | 30 | 32 | 35 | 36 | 40 | 42 | 50 | 60 | 80 | 90 | 100 |   |   |
| 4                          | ●    |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |
| 5                          | ●    |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |
| 6                          | ●    |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |
| 8                          | ●    | ●   | ● | ●   | ● | ● |   | ● | ● | ●  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |
| 10                         | ●    | ●   | ● | ●   | ● | ● | ● | ● | ● | ●  | ●  | ●  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |
| 12                         |      |     | ● | ●   | ● | ● | ● | ● | ● | ●  | ●  | ●  |    | ●  |    |    |    | ●  |    |    |    |    |    |    |    |    |     |   |   |
| 13                         |      |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    | ●  |    |    |    |    |    |    |    |    |     |   |   |
| 14                         |      |     | ● |     |   | ● | ● | ● |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |
| 15                         |      |     |   |     |   | ● | ● | ● | ● | ●  | ●  | ●  |    | ●  |    |    |    | ●  |    |    |    |    | ●  |    |    |    |     |   |   |
| 16                         |      |     |   |     |   | ● | ● | ● | ● | ●  | ●  | ●  |    | ●  |    |    |    |    |    |    |    |    | ●  |    |    |    |     |   |   |
| 18                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |
| 20                         |      |     |   |     |   | ● | ● | ● | ● | ●  | ●  | ●  |    | ●  |    |    | ●  | ●  | ●  |    |    | ●  |    |    | ●  |    |     |   |   |
| 25                         |      |     |   |     |   | ● | ● | ● | ● | ●  | ●  | ●  |    | ●  |    |    | ●  | ●  | ●  |    |    |    |    | ●  |    |    |     |   |   |
| 28                         |      |     |   |     |   |   |   |   |   |    | ●  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |
| 30                         |      |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    | ●  |    |     | ● |   |
| 31                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  |    |    |    | ●  |    |    |    |    |    | ●  |    |     | ● |   |
| 32                         |      |     |   |     |   | ● | ● | ● | ● | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    | ●  |    |    |    |    |    |    |    |     |   |   |
| 36                         |      |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    | ●  |    |    |    |    |     |   |   |
| 38                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |
| 40                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |
| 45                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |
| 50                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |
| 55                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |
| 63                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |
| 70                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |
| 80                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |
| 100                        |      |     |   |     |   |   |   |   |   |    |    |    |    | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |
| 120                        |      |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |
| 140                        |      |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |

Table19 Standard Combinations of Outer Diameters and Leads of the Screw Shafts (DIN Standard-Compliant Ball Screws)

Unit: mm

| Shaft diameter | Lead |    |    |
|----------------|------|----|----|
|                | 5    | 10 | 20 |
| 16             | ●    | —  | —  |
| 20             | ●    | —  | —  |
| 25             | ●    | ●  | —  |
| 32             | ●    | ●  | —  |
| 40             | ○    | ●  | ○* |
| 50             | —    | ○  | ○* |
| 63             | —    | ○  | ○* |

●: Ground shaft, CES shaft

○: Ground shaft only

\*: Model EB (no preload) only

## Combinations of Shaft Diameter and Lead for the Rolled Ball Screw

Table20 shows the combinations of shaft diameter and lead for the rolled ball screw.

Table20 Combinations of Screw Shaft Diameter and Lead (Rolled Ball Screw)

Unit: mm

| Screw shaft<br>outer diameter | Lead |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
|-------------------------------|------|---|---|---|---|---|----|----|----|----|----|----|----|----|----|----|----|----|----|-----|
|                               | 1    | 2 | 4 | 5 | 6 | 8 | 10 | 12 | 16 | 20 | 24 | 25 | 30 | 32 | 36 | 40 | 50 | 60 | 80 | 100 |
| 6                             | ●    |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 8                             | ●    | ● |   | ● |   | ● |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 10                            |      | ● | ● |   | ● |   | ●  |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 12                            |      | ● |   |   |   | ● |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 14                            |      | ● | ● | ● |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 15                            |      |   |   |   |   |   | ●  |    | ●  |    |    | ●  |    |    |    |    |    |    |    |     |
| 16                            |      |   |   | ● |   |   |    |    | ●  |    |    |    |    |    |    |    |    |    |    |     |
| 18                            |      |   |   |   |   | ● |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 20                            |      |   |   | ● |   |   | ●  |    | ●  |    |    |    |    |    |    | ●  |    |    |    |     |
| 25                            |      |   |   | ● |   |   | ●  |    |    |    |    | ●  |    |    |    |    | ●  |    |    |     |
| 28                            |      |   |   | ● | ● |   |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 30                            |      |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    | ●  |    |     |
| 32                            |      |   |   |   |   |   | ●  |    |    |    |    |    | ●  |    |    |    |    |    |    |     |
| 36                            |      |   |   |   |   |   | ●  |    | ●  | ●  |    |    |    | ●  |    |    |    |    |    |     |
| 40                            |      |   |   |   |   |   | ●  |    |    |    |    |    |    |    |    | ●  |    |    | ●  |     |
| 45                            |      |   |   |   |   |   |    | ●  |    |    |    |    |    |    |    |    |    |    |    |     |
| 50                            |      |   |   |   |   |   |    |    | ●  |    |    |    |    |    |    |    | ●  |    |    | ●   |

## Method for Mounting the Ball Screw Shaft

Fig.8 to Fig.11 show the representative mounting methods for the screw shaft.

The permissible axial load and the permissible rotational speed vary with mounting methods for the screw shaft. Therefore, it is necessary to select an appropriate mounting method according to the conditions.




Fig.8 Screw Shaft Mounting Method: Fixed - Free




Fig.9 Screw Shaft Mounting Method: Fixed - Supported

## Point of Selection

## Method for Mounting the Ball Screw Shaft




Fig.10 Screw Shaft Mounting Method: Fixed - Fixed




Fig.11 Screw Shaft Mounting Method for Rotary Nut Ball Screw: Fixed - Fixed

## Permissible Axial Load

### [Buckling Load on the Screw Shaft]

With the Ball Screw, it is necessary to select a screw shaft so that it will not buckle when the maximum compressive load is applied in the axial direction.

Fig.12 on **A15-31** shows the relationship between the screw shaft diameter and a buckling load.

If determining a buckling load by calculation, it can be obtained from the equation (5) below. Note that in this equation, a safety factor of 0.5 is multiplied to the result.

$$P_1 = \frac{\eta_1 \cdot \pi^2 \cdot E \cdot I}{\ell_a^2} \cdot 0.5 = \eta_2 \frac{d_1^4}{\ell_a^2} \cdot 10^4 \quad \dots\dots(5)$$

$P_1$  : Buckling load (N)

$\ell_a$  : Distance between two mounting surfaces (mm)

$E$  : Young's modulus ( $2.06 \times 10^5$  N/mm<sup>2</sup>)

$I$  : Minimum geometrical moment of inertia of the shaft (mm<sup>4</sup>)

$$I = \frac{\pi}{64} d_1^4 \quad d_1: \text{screw-shaft thread minor diameter (mm)}$$

$\eta_1, \eta_2$ =Factor according to the mounting method

Fixed - free             $\eta_1=0.25$      $\eta_2=1.3$

Fixed - supported     $\eta_1=2$          $\eta_2=10$

Fixed - fixed          $\eta_1=4$          $\eta_2=20$

### [Permissible Tensile Compressive Load on the Screw Shaft]

If an axial load is applied to the Ball Screw, it is necessary to take into account not only the buckling load but also the permissible tensile compressive load in relation to the yielding stress on the screw shaft.

The permissible tensile compressive load is obtained from the equation (6).

$$P_2 = \sigma \frac{\pi}{4} d_1^2 = 116d_1^2 \quad \dots\dots(6)$$

$P_2$  : Permissible tensile compressive load (N)

$\sigma$  : Permissible tensile compressive stress (147 MPa)

$d_1$  : Screw-shaft thread minor diameter (mm)




Fig.12 Permissible Tensile Compressive Load Diagram

## Permissible Rotational Speed

### [Critical Speed of the Screw Shaft]

When the rotational speed reaches a high magnitude, the Ball Screw may resonate and eventually become unable to operate due to the screw shaft's natural frequency. Therefore, it is necessary to select a model so that it is used below the resonance point (critical speed).

Fig.13 on **A15-34** shows the relationship between the screw shaft diameter and the critical speed.

If determining the critical speed by calculation, it can be obtained from the equation (7) below. Note that in this equation, a safety factor of 0.8 is multiplied to the result.

$$N_1 = \frac{60 \cdot \lambda_1^2}{2\pi \cdot \ell_b^2} \times \sqrt{\frac{E \times 10^3 \cdot I}{\gamma \cdot A}} \times 0.8 = \lambda_2 \cdot \frac{d_1}{\ell_b^2} \cdot 10^7 \dots\dots(7)$$

$N_1$  : Permissible rotational speed determined  
by the critical speed (min<sup>-1</sup>)

$\ell_b$  : Distance between two mounting surfaces  
(mm)

$E$  : Young's modulus (2.06 × 10<sup>5</sup> N/mm<sup>2</sup>)

$I$  : Minimum geometrical moment of inertia  
of the shaft (mm<sup>4</sup>)

$$I = \frac{\pi}{64} d_1^4 \quad d_1: \text{screw-shaft thread minor diameter (mm)}$$

$\gamma$  : Density (specific gravity)  
(7.85 × 10<sup>-6</sup> kg/mm<sup>3</sup>)

$A$  : Screw shaft cross-sectional area (mm<sup>2</sup>)

$$A = \frac{\pi}{4} d_1^2$$

$\lambda_1, \lambda_2$  : Factor according to the mounting method

Fixed - free  $\lambda_1=1.875$   $\lambda_2=3.4$

Supported - supported  $\lambda_1=3.142$   $\lambda_2=9.7$

Fixed - supported  $\lambda_1=3.927$   $\lambda_2=15.1$

Fixed - fixed  $\lambda_1=4.73$   $\lambda_2=21.9$



## Point of Selection

## Permissible Rotational Speed

## [DN Value]

The permissible rotational speed of the Ball Screw must be obtained from the critical speed of the screw shaft and the DN value. The permissible rotational speed determined by the DN value is obtained using the equations (8) to (17) below.

| Model No.                          |                         |   | Permissible rotational speed determined by the DN value<br>$N_2$ : |  |
|------------------------------------|-------------------------|---|--|--|
| Precision                          | Caged Ball              | Models SDAN-V and SDA-V   | Standard lead/ Super lead $N_2 = \frac{160000}{D}$ .....(8)        |  |
|                                    |                         | Model SBK (Medium)<br>(SBK3636, SBK4040, and SBK5050)                                   | Large lead $N_2 = \frac{210000}{D}$ .....(9-1)                     |  |
|                                    |                         | Model SBK (Medium)<br>(Other than the above model numbers and the small size model SBK) |  | $N_2 = \frac{160000}{D}$ .....(9-2)                  |
|                                    |                         | Model SBK (Small)   | $N_2 = \frac{130000}{D}$ .....(9-3)                                |  |
|                                    |                         | Models SBN-V (Medium), HBN-V  | Standard lead $N_2 = \frac{160000}{D}$ .....(10-1)                 |  |
|                                    |                         | Models SBN-V (Small), HBN, and SBKH   |  | $N_2 = \frac{130000}{D}$ .....(10-2)                 |
|                                    | Models HBN-K and HBN-KA | $N_2 = \frac{120000}{D}$ .....(10-3)  |  |  |
|                                    | Full-Complement Ball    | Models SDAN-VX and SDA-VZ<br>(shaft diameters $\phi 28$ to $63$ )                       | Standard lead/ Super lead $N_2 = \frac{130000}{D}$ .....(11-1)     |  |
|                                    |                         |   |  | Model SDA-VZ<br>(shaft diameters $\phi 10$ to $25$ ) |
|                                    |                         | Model WHF   | Super lead $N_2 = \frac{120000}{D}$ .....(12-1)                    |  |
|                                    |                         | Model WGF   |  | $N_2 = \frac{70000}{D}$ .....(12-2)                  |
|                                    |                         | Models BNS-V and NS-V   | Large lead $N_2 = \frac{100000}{D}$ .....(13-1)                    |  |
|                                    |                         | Models BLW, BLK, BLR, BNS-A, BNS, NS-A, and NS  |  | $N_2 = \frac{70000}{D}$ .....(13-2)                  |
|                                    |                         | Models BIF-V (Medium), BNFN-V (Medium), and BNF-V (Medium)                              | Standard lead $N_2 = \frac{130000}{D}$ .....(14-1)                 |  |
|                                    |                         | Models BIF-V (Small), BNFN-V (Small), and BNF-V (Small)                                 |  | $N_2 = \frac{100000}{D}$ .....(14-2)                 |
|                                    |                         | Models BIF, DIK, BNFN, DKN, BNF, BNT, DK, MDK, MBF, BNK, and DIR                        |  | $N_2 = \frac{70000}{D}$ .....(14-3)                  |
|                                    |                         | Full-Complement Ball<br>(DIN Standard Compliant)  | Models EPB-V, EBB-V (2806 to 8020)                                 | Standard lead $N_2 = \frac{130000}{D}$ .....(14-4)   |
| Models EPB-V, EBB-V (1605 to 2512) |                         |   |  |  |
| Rolled                             | Full-Complement Ball    | Models WTF and CNF  | Super lead $N_2 = \frac{70000}{D}$ .....(15)                       |  |
|                                    |                         | Models BLK and BLR  | Large lead $N_2 = \frac{70000}{D}$ .....(16)                       |  |
|                                    |                         | Model BTK-V   | Standard lead $N_2 = \frac{100000}{D}$ .....(17-1)                 |  |
|                                    |                         | Models JPF, BNT, and MTF  |  | $N_2 = \frac{50000}{D}$ .....(17-2)                  |

$N_2$  : Permissible rotational speed determined by the DN value ( $\text{min}^{-1}$ )

D : Ball center-to-center diameter

(indicated in the dimensional tables of the respective model numbers)

When considering the rotational speed, the permissible rotational speed is regarded as the lower of the following rotational speed guidelines: the critical speed of the screw shaft ( $N_1$ ) or the permissible rotational speed determined by the DN value ( $N_2$ ). Refer to the dimensional tables of the respective model numbers for the permissible rotational speed.

If the service rotational speed exceeds the guidelines for maximum rotational speed, contact THK.




Fig.13 Permissible Rotational Speed Diagram

## Studying the Caged Technology

### [Low Noise, Acceptable Running Sound]



The use of the ball cage eliminates the collision noise between the balls. Additionally, as balls are picked up in the tangential direction, the collision noise from the ball circulation has also been eliminated.

### [Long-term Maintenance-free Operation]

The friction between the balls has been eliminated, and the grease retention has been improved through the provision of grease pockets. As a result, the long-term maintenance-free operation (i.e., lubrication is unnecessary over a long period) is achieved.

### [Smooth Motion]

The use of a ball cage eliminates the friction between the balls and minimizes the torque fluctuation, thus allowing the smooth motion to be achieved.



## [Low Noise]

### ● Noise Level Data

Since the balls in the Ball Screw with the Ball Cage do not collide with each other, they do not produce a metallic sound and a low noise level is achieved.

### ■ Noise Measurement

[Conditions]

| Item        | Description   |
|-------------|---|
| Sample      | Caged ball screw<br>HBN3210-5<br>Conventional type: model<br>BNF3210-5            |
| Stroke      | 600mm   |
| Lubrication | Grease lubrication<br>(lithium-based grease containing<br>extreme pressure agent) |





Fig.14 Ball Screw Noise Level

**[Long-term Maintenance-free Operation]**● **High speed, Load-bearing Capacity**

Thanks to the ball circulating method supporting high speed and the caged ball technology, the Ball Screw with Ball Cage excels in high speed and load-bearing capacity.

■ **High Speed Durability Test**

[Test conditions]

| Item         | Description                                     |
|--------------|---|
| Sample       | High Speed Ball Screw with Ball Cage SDA3110V-5 |
| Speed        | 5000( $\text{min}^{-1}$ )(DN value*: 160,000)   |
| Stroke       | 500 mm  |
| Lubricant    | THK AFJ Grease                                  |
| Quantity     | 4 $\text{cm}^3$ (lubricated every 500 km)       |
| Applied load | 1.27 kN   |
| Acceleration | 0.5 G   |

\* DN value: Ball center-to-center diameter x revolutions per minute

[Test result]

Shows no deviation after running 6,000 km.

■ **Load Bearing Test**

[Test conditions]

| Item         | Description                                     |
|--------------|---|
| Sample       | High Speed Ball Screw with Ball Cage SBN5016V-5 |
| Speed        | 1500( $\text{min}^{-1}$ )(DN value*: 79,000)    |
| Stroke       | 400 mm  |
| Lubricant    | THK AFG Grease                                  |
| Quantity     | 57.7 $\text{cm}^3$ (Lubricated every 100 km)    |
| Applied load | 36.1 kN(0.38 Ca)                                |
| Acceleration | 0.5 G   |

[Test result]

Shows no deviation after running for the calculated service life

**[Smooth Motion]**● **Low Torque Fluctuation**

The caged ball technology allows smoother motion than the conventional type to be achieved, thus to reduce torque fluctuation.

[Conditions]

| Item                   | Description           |
|------------------------|-----------------------|
| Shaft diameter/lead    | 25/5 mm               |
| Shaft rotational speed | 100 $\text{min}^{-1}$ |




Fig.15 Torque Fluctuation Data


## Types and Features

[Preload Type]

### Model SBN-V

Specification Table⇒ [A15-110](#)


The circulation structure feature allows the balls to be picked up tangential to the direction of movement. The circulation components have been strengthened, increasing the DN value to 160,000 (small type: 130,000).



### Model SBK

Specification Table⇒ [A15-114](#)


As a result of adopting the offset preloading method, which shifts two rows of grooves of the ball screw nut, a compact structure is achieved.



### Model SDAN-V

Specification Table⇒ [A15-76](#)

The preload method utilizes a combination of two ball screw nuts preloaded with spacers to eliminate backlash. The nut dimensions conform to ISO standards (ISO 3408). This type has improved axial rigidity in comparison with the Model SDA-V.



### Model SDAN-VX

Specification Table⇒ [A15-76](#)

Full-Ball types are also available.


[Preload/No Preload Type]

## Model SDA-V

A ball screw with newly developed circulation components that give it an ideal ball circulation structure. (DN value: 160,000)

The nut dimensions conform to ISO standards (ISO 3408). Furthermore, the use of the newly developed thin film seal reduces the length of the nut, achieving a more compact design for the device.

Specification Table⇒ **A15-82**



## Model SDA-VZ


Full-Ball types are also available.(DN value: 130,000)

Specification Table⇒ **A15-82**

[No Preload Type]

## Models HBN-V/HBN-K/HBN-KA/HBN Specification Table⇒ **A15-224**


With the optimal design for high loads, this ball screw model achieves a rated load more than twice the conventional type.



## Model SBKH

Specification Table⇒ **A15-234**

Model SBKH is a ball screw that achieves a high load carrying capacity and is capable of high-speed operation (92 m/min at a maximum).





# Selecting a Nut

## Types of Nuts

The nuts of the Ball Screws are categorized by the ball circulation method into the return-pipe type, the deflector type and end cap type. These three nut types are described as follows.


In addition to the circulation methods, the Ball Screws are categorized also by the preloading method.

### [Types by Ball Circulation Method]

#### ● Return-Pipe Type

(Models SBN-V (Medium), BIF-V (Medium), BIF, BNF-V (Medium), BNF, BNFN-V (Medium), BNFN, BNT, BTK-V),  
Return-Piece Type  
(Models SBN-V (Small), HBN, BIF-V (Small), BNF-V (Small), BNFN-V (Small))

These are the most common types of nuts, which use a return pipe for ball circulation. The return pipe allows balls to be picked up, pass through the pipe and return piece, and return to their original positions to circulate endlessly.




Example of Structure of Return-Pipe Nut

#### ● Deflector Type

(Models EBB-V, EPB-V, DK, DKN, DIK, JPF, DIR and MDK)


These are the most compact type of nut. The balls change their traveling direction with a deflector, pass over the circumference of the screw shaft, and return to their original positions to complete an infinite motion.



Example of Structure of Simple Nut

#### ● End-cap Type: Large lead Nut (Models SBK, SBKH, WHF, BLK, WGF, BLW, WTF, CNF and BLR)

These nuts are most suitable for the fast feed. The balls are picked up with an end cap, pass through the through hole of the nut, and return to their original positions to complete an infinite motion.




Example of Structure of Large lead Nut

### [Types by Preloading Method]

#### ● Fixed-point Preloading

#### ■ Double-nut Preload (Models SDAN-V, BNFN-V, BNFN, DKN and BLW)

A spacer is inserted between two nuts to provide a preload.



Model SDAN-V



Models BNFN-V and BNFN




Model DKN



Model BLW

#### ■ Offset Preload (Models SBK, SBN-V, BIF-V, BIF, EPB-V, DIK and DIR)

More compact than the double-nut method, the offset preloading provides a preload by changing the groove pitch of the nut without using a spacer.



Model SBK



Model SBN-V



Models BIF-V and BIF



Model EPB-V



Model DIK




Model DIR

## Point of Selection

### Selecting a Nut

#### ● Constant Pressure Preloading (Model JPF)

With this method, a spring structure is installed almost in the middle of the nut, and it provides a preload by changing the groove pitch in the middle of the nut.



Model JPF

#### [Structure and Features of Offset Preload Type Simple-Nut Ball Screw]

The Simple-Nut Ball Screw is an offset preload type in which a phase is provided in the middle of a single ball screw nut, and an axial clearance is set at a below-zero value (under a preload).

The Simple-Nut Ball Screw has a more compact structure and allows smoother motion than the conventional double-nut type (spacer inserted between two nuts).

#### [Comparison between the Simple Nut and the Double-Nuts]



| Simple-Nut Ball Screw       | Conventional Double-Nut Type Ball Screw |
|-----------------------------|---|
|                             |   |
| <b>Preloading Structure</b> |   |
|                             |   |

## Simple-Nut Ball Screw

## Conventional Double-Nut Type Ball Screw


## Rotational Performance

The preload adjustment with Simple Nut Ball Screw is performed according to the ball diameter. This eliminates the inconsistency in the contact angle, which is the most important factor of the Ball Screw performance. It also ensures the high rigidity, the smooth motion and the high wobbling accuracy.




## Dimensions

Since Simple-Nut Ball Screw is based on a preloading mechanism that does not require a spacer, the overall nut length can be kept short. As a result, the whole nut can be lightly and compactly designed.



Simple-Nut









Double-Nut

## Point of Selection

Selecting a Nut

[Comparison between the Offset Preload Type of Simple-Nut Ball Screw and the Oversized-ball Preload Nut Ball Screw]

| Simple-Nut Ball Screw Model DIK   | Conventional Oversized-ball Preload Nut Ball Screw Model BNF  |
|---|---|
|  <p>Ball screw nut</p>   |  <p>Ball screw nut</p>   |
| <b>Preloading Structure</b>   |   |
|  <p>Preload    Preload</p> <p>Pitch    Pitch + preload    Pitch</p> <p>Ball screw nut</p> <p>Pitch    Pitch    Pitch</p> <p>Screw shaft</p>  |  <p>Pitch    Pitch    Pitch</p> <p>Ball screw nut</p> <p>Pitch    Pitch    Pitch</p> <p>Screw shaft</p>  |
| <b>Accuracy Life</b>  |   |
| <p>Simple-Nut Ball Screw model DIK has a similar preloading structure to that of the double-nut type although the former only has one ball screw nut. As a result, no differential slip or spin occurs, thus minimizing the increase in the rotational torque and the generation of heat. Accordingly, a high level of accuracy can be maintained over a long period.</p> <p>2 point contact structure</p>  <p><math>d_2</math>    <math>d_1</math>    Contact width</p> <p>Ball rotational axis</p> <p>Differential slip</p> <p>B    <math>d_1</math>    B'    <math>\pi \times d_1</math>    A'</p> <p>A    <math>d_2</math>    <math>\pi \times d_2</math></p> | <p>With the oversized-ball preload nut ball Screw, a preload is provided through each of the balls in contact with the raceway at four points. This causes differential slip and spin increasing the rotational torque, resulting in accelerated wear and heat generation. Therefore, the accuracy deteriorates in a short period.</p> <p>4 point contact structure</p>  <p>4 point contact structure</p> <p><math>d_2</math>    <math>d_1</math>    Contact width</p> <p>Ball rotational axis</p> <p>Differential slip</p> <p>B    <math>d_1</math>    B'    <math>\pi \times d_1</math>    A'</p> <p>A    <math>d_2</math>    <math>\pi \times d_2</math></p> |

# Selecting a Model Number

## Calculating the Axial Load

### [In Horizontal Mount]

With ordinary conveyance systems, the axial load ( $F_{a_n}$ ) applied when horizontally reciprocating the work is obtained in the equation below.

$$Fa_1 = \mu \cdot mg + f + m\alpha \quad \dots\dots\dots (18)$$

$$Fa_2 = \mu \cdot mg + f \quad \dots\dots\dots (19)$$

$$Fa_3 = \mu \cdot mg + f - m\alpha \quad \dots\dots\dots (20)$$

$$Fa_4 = -\mu \cdot mg - f - m\alpha \quad \dots\dots\dots (21)$$

$$Fa_5 = -\mu \cdot mg - f \quad \dots\dots\dots (22)$$

$$Fa_6 = -\mu \cdot mg - f + m\alpha \quad \dots\dots\dots (23)$$

$V_{max}$  : Maximum speed (m/s)

$t_1$  : Acceleration time (s)

$$\alpha = \frac{V_{max}}{t_1} : \text{Acceleration} \quad (m/s^2)$$


$Fa_1$  : Axial load during forward acceleration (N)

$Fa_2$  : Axial load during forward uniform motion (N)

$Fa_3$  : Axial load during forward deceleration (N)

$Fa_4$  : Axial load during backward acceleration (N)

$Fa_5$  : Axial load during uniform backward motion (N)



$Fa_6$  : Axial load during backward deceleration (N)

$m$  : Transferred mass (kg)

$\mu$  : Frictional coefficient of the guide surface (-)

$f$  : Guide surface resistance (without load) (N)

### [In Vertical Mount]

With ordinary conveyance systems, the axial load ( $F_{a_n}$ ) applied when vertically reciprocating the work is obtained in the equation below.

$$Fa_1 = mg + f + m\alpha \quad \dots\dots\dots (24)$$

$$Fa_2 = mg + f \quad \dots\dots\dots (25)$$

$$Fa_3 = mg + f - m\alpha \quad \dots\dots\dots (26)$$

$$Fa_4 = mg - f - m\alpha \quad \dots\dots\dots (27)$$

$$Fa_5 = mg - f \quad \dots\dots\dots (28)$$

$$Fa_6 = mg - f + m\alpha \quad \dots\dots\dots (29)$$

$V_{max}$  : Maximum speed (m/s)

$t_1$  : Acceleration time (s)

$$\alpha = \frac{V_{max}}{t_1} : \text{Acceleration} \quad (m/s^2)$$


$Fa_1$  : Axial load during upward acceleration (N)

$Fa_2$  : Axial load during uniform upward motion (N)

$Fa_3$  : Axial load during upward deceleration (N)

$Fa_4$  : Axial load during downward acceleration (N)

$Fa_5$  : Axial load during uniform downward motion (N)



$Fa_6$  : Axial load during downward deceleration (N)

$m$  : Transferred mass (kg)

$f$  : Guide surface resistance (without load) (N)

## Static Safety Factor

The basic static load rating ( $C_0a$ ) generally equals to the permissible axial load of a Ball Screw. Depending on the conditions, it is necessary to take into account the following static safety factor against the calculated load. When the Ball Screw is stationary or in motion, unexpected external force may be applied through an inertia caused by the impact or the start and stop.

$$F_{a_{\max}} = \frac{C_0a}{f_s} \dots\dots\dots(30)$$

$F_{a_{\max}}$  : Allowable Axial Load (kN)

$C_0a$  : Basic static load rating\* (kN)

$f_s$  : Static safety factor (see Table21)

Table21 Static Safety Factor ( $f_s$ )

| Machine using the LM system  | Load conditions             | Lower limit of $f_s$ |
|------------------------------|-----------------------------|----------------------|
| General industrial machinery | Without vibration or impact | 1.0 to 3.5           |
|                              | With vibration or impact    | 2.0 to 5.0           |
| Machine tool                 | Without vibration or impact | 1.0 to 4.0           |
|                              | With vibration or impact    | 2.5 to 7.0           |

\*The basic static load rating ( $C_0a$ ) is a static load with a constant direction and magnitude whereby the sum of the permanent deformation of the rolling element and that of the raceway on the contact area under the maximum stress is 0.0001 times the rolling element diameter. With the Ball Screw, it is defined as the axial load. (Specific values of each Ball Screw model are indicated in the specification tables for the corresponding model number.)

### [Permissible Load Safety Margin (Models HBN-V, HBN-K (KA), HBN, and SBKH)]

In comparison to previous ball screws, high-load ball screw models HBN-V, HBN-K (KA), HBN, and SBKH are designed to achieve longer service lives under high load conditions, and it is necessary to consider the permissible load  $F_p$  for the axial load. Permissible load  $F_p$  indicates the maximum axial load that the high-load ball screw can support, and this range should not be exceeded.

Permissible load  $F_p$  indicates the maxim axial load that the high load Ball Screw can receive, and this range should not be exceeded.

$$\frac{F_p}{F_a} > 1 \dots\dots\dots(31)$$

$F_p$  : Permissible Axial Load (kN)

$F_a$  : Applied Axial Load (kN)

## Studying the Service Life

### [Service Life of the Ball Screw]

A Ball Screw in motion under an external load receives repeated stress on its raceways and balls. When the stress reaches the limit, the raceways break from fatigue, and their surfaces flake like scales. This phenomenon is called flaking. The service life of the Ball Screw is the total number of revolutions until the first flaking occurs on any of the raceways or the balls as a result of rolling fatigue of the material.

The service life of the Ball Screw varies from unit to unit even if they are manufactured in the same process and used in the same operating conditions. For this reason, when determining the service life of a Ball Screw unit, the nominal life as defined below is used as a guideline.

The nominal life is the total number of revolutions that 90% of identical Ball Screw units in a group achieve without flaking after they independently operate in the same conditions.

### [Calculating the Rated Life]

The service life of the Ball Screw is calculated from the formula (32) below using the basic dynamic load rating (Ca) and the applied axial load.

#### ● Calculating the Nominal Life

The nominal life ( $L_{10}$ ) is obtained from the following formula using the basic dynamic load rating (Ca) and the applied load in the axial direction (Fa).

$$L_{10} = \left( \frac{Ca}{Fa} \right)^3 \times 10^6 \dots\dots\dots(32-1)$$

$L_{10}$  : Nominal life (rev.)  
 Ca : Basic dynamic load rating (N)  
 Fa : Applied axial load (N)

#### ● Calculating the Modified Nominal Life

During use, a ball screw may be subjected to vibrations and shocks as well as fluctuating loads, which are difficult to detect. Taking these factors into account, the modified nominal life ( $L_{10m}$ ) can be calculated according to the following formula (32-2).

•Modified factor  $\alpha$

$$\alpha = \frac{1}{f_w}$$

$\alpha$  : Modified factor  
 $f_w$  : Load factor (see Table22)

•Modified nominal life  $L_{10m}$

$$L_{10m} = \left( \alpha \times \frac{Ca}{Fa} \right)^3 \times 10^6 \dots\dots\dots(32-2)$$

$L_{10m}$  : Modified nominal life (rev.)  
 Ca : Basic dynamic load rating (N)  
 Fa : Applied axial load (N)

Table22 Load Factor ( $f_w$ )

| Vibrations/impact | Speed (V)                     | $f_w$      |
|-------------------|-------------------------------|------------|
| Faint             | Very low<br>$V \leq 0.25$ m/s | 1 to 1.2   |
| Weak              | Slow<br>$0.25 < V \leq 1$ m/s | 1.2 to 1.5 |
| Medium            | Medium<br>$1 < V \leq 2$ m/s  | 1.5 to 2   |
| Strong            | High<br>$V > 2$ m/s           | 2 to 3.5   |

\*The basic dynamic load rating (Ca) is used in calculations of service life when the ball screw is under an axial load. The basic dynamic load rating is defined as a load rating based on the movement of a set of identical ball screws with a rated life (L) of  $10^6$  revolutions, using a load applied in the axial direction that does not vary in either magnitude or direction. (The basic dynamic load ratings (Ca) for each model number are indicated in the specification tables.)

\*The rated service life is estimated by calculating the load on the premise that the product is set up in ideal mounting conditions with the assurance of good lubrication. The service life can be affected by the precision of the mounting materials used and any distortion.



### ● Service Life Time

If the revolutions per minute is determined, the service life time can be calculated from the equation (33) below using the nominal life ( $L_{10}$ ).

$$L_h = \frac{L_{10}}{60 \times N} = \frac{L_{10} \times Ph}{2 \times 60 \times n \times \ell_s} \dots\dots\dots(33)$$

|          |                                       |                       |
|----------|---------------------------------------|-----------------------|
| $L_h$    | : Service life time                   | (h)                   |
| $N$      | : Revolutions per minute              | ( $\text{min}^{-1}$ ) |
| $n$      | : Number of reciprocations per minute | ( $\text{min}^{-1}$ ) |
| $Ph$     | : Ball Screw lead                     | (mm)                  |
| $\ell_s$ | : Stroke length                       | (mm)                  |

### ● Service Life in Travel Distance

The service life in travel distance can be calculated from the equation (34) below using the nominal life ( $L_{10}$ ) and the Ball Screw lead.

$$L_s = \frac{L_{10} \times Ph}{10^6} \dots\dots\dots(34)$$

|       |                                   |      |
|-------|-----------------------------------|------|
| $L_s$ | : Service Life in Travel Distance | (km) |
| $Ph$  | : Ball Screw lead                 | (mm) |

### ● Applied Load and Service Life with a Preload Taken into Account

If the Ball Screw is used under a preload (medium preload), it is necessary to consider the applied preload in calculating the service life since the ball screw nut already receives an internal load. For details on applied preload for a specific model number, contact THK.

### ● Average Axial Load

If an axial load acting on the Ball Screw is present, it is necessary to calculate the service life by determining the average axial load.

The average axial load ( $F_m$ ) is a constant load that equals to the service life in fluctuating the load conditions.

If the load changes in steps, the average axial load can be obtained from the equation below.

$$F_m = \sqrt[3]{\frac{1}{\ell} (Fa_1^3 \ell_1 + Fa_2^3 \ell_2 + \dots + Fa_n^3 \ell_n)} \dots\dots\dots(35)$$

|          |  |     |
|----------|--|-----|
| $F_m$    | : Average Axial Load                     | (N) |
| $Fa_n$   | : Varying load                           | (N) |
| $\ell_n$ | : Distance traveled under load ( $F_n$ ) |     |
| $\ell$   | : Total travel distance                  |     |

To determine the average axial load using a rotational speed and time, instead of a distance, calculate the average axial load by determining the distance in the equation below.

$$l = l_1 + l_2 + \dots + l_n$$

$$l_1 = N_1 \cdot t_1$$

$$l_2 = N_2 \cdot t_2$$

$$l_n = N_n \cdot t_n$$


N: Rotational speed

t: Time

### ■When the Applied Load Sign Changes

If the sign (positive or negative) used for variable load is always the same, there are no problems with formula (35). However, if the variable load sign changes depending on the type of operation, calculate the average axial load for either positive or negative load, allowing for the load direction. (If the average axial load for positive load is calculated, the negative load is taken to be zero.) The larger of the two average axial loads is taken as the average axial load when the service life is calculated.

Example: Calculate the average axial load with the following load conditions.



| Operation No. | Varying load<br>$F_{a_i}$ (N) | Travel distance<br>$l_n$ (mm) |
|---------------|-------------------------------|-------------------------------|
| No.1          | 10                            | 10                            |
| No.2          | 50                            | 50                            |
| No.3          | -40                           | 10                            |
| No.4          | -10                           | 70                            |

\*The subscripts of the fluctuating load symbol and the travel distance symbol indicate operation numbers.

#### ● Average axial load of positive-sign load

\*To calculate the average axial load of the positive-sign load, assume  $F_{a_3}$  and  $F_{a_4}$  to be zero.

$$F_{m1} = \sqrt[3]{\frac{F_{a_1}^3 \times l_1 + F_{a_2}^3 \times l_2}{l_1 + l_2 + l_3 + l_4}} = 35.5 \text{ N}$$

#### ● Average axial load of negative-sign load

\*To calculate the average axial load of the negative-sign load, assume  $F_{a_1}$  and  $F_{a_2}$  to be zero.

$$F_{m2} = \sqrt[3]{\frac{|F_{a_3}|^3 \times l_3 + |F_{a_4}|^3 \times l_4}{l_1 + l_2 + l_3 + l_4}} = 17.2 \text{ N}$$

Accordingly, the average axial load of the positive-sign load ( $F_{m1}$ ) is adopted as the average axial load ( $F_m$ ) for calculating the service life.

## Studying the Rigidity

To increase the positioning accuracy of feed screws in NC machine tools or the precision machines, or to reduce the displacement caused by the cutting force, it is necessary to design the rigidity of the components in a well-balanced manner.

### Axial Rigidity of the Feed Screw System

When the axial rigidity of a feed screw system is  $K$ , the elastic displacement in the axial direction can be obtained using the equation (36) below.

$$\delta = \frac{F_a}{K} \quad \dots\dots(36)$$

- $\delta$  : Elastic displacement of a feed screw system in the axial direction ( $\mu\text{m}$ )  
 $F_a$  : Applied axial load (N)

The axial rigidity ( $K$ ) of the feed screw system is obtained using the equation (37) below.

$$\frac{1}{K} = \frac{1}{K_s} + \frac{1}{K_n} + \frac{1}{K_b} + \frac{1}{K_H} \quad \dots\dots(37)$$

- $K$  : Axial Rigidity of the Feed Screw System ( $\text{N}/\mu\text{m}$ )  
 $K_s$  : Axial rigidity of the screw shaft ( $\text{N}/\mu\text{m}$ )  
 $K_n$  : Axial rigidity of the nut ( $\text{N}/\mu\text{m}$ )  
 $K_b$  : Axial rigidity of the support bearing ( $\text{N}/\mu\text{m}$ )  
 $K_H$  : Rigidity of the nut bracket and the support bearing bracket ( $\text{N}/\mu\text{m}$ )

#### [Axial rigidity of the screw shaft]

The axial rigidity of a screw shaft varies depending on the method for mounting the shaft.

#### ● For Fixed-Supported (or -Free) Configuration


$$K_s = \frac{A \cdot E}{1000 \cdot L} \quad \dots\dots(38)$$

$A$  : Screw shaft cross-sectional area ( $\text{mm}^2$ )

$$A = \frac{\pi}{4} d_1^2$$

- $d_1$  : Screw-shaft thread minor diameter (mm)  
 $E$  : Young's modulus ( $2.06 \times 10^5 \text{ N}/\text{mm}^2$ )  
 $L$  : Distance between two mounting surfaces (mm)

Fig.16 on **A15-52** shows an axial rigidity diagram for the screw shaft.



● For Fixed-Fixed Configuration

$$K_s = \frac{A \cdot E \cdot L}{1000 \cdot a \cdot b} \dots\dots (39)$$

$K_s$  becomes the lowest and the elastic displacement in the axial direction is the greatest at the position of  $a = b = \frac{L}{2}$ .

$$K_s = \frac{4A \cdot E}{1000L}$$

Fig.17 on **A15-53** shows an axial rigidity diagram of the screw shaft in this configuration.





Fig.16 Axial Rigidity of the Screw Shaft (Fixed-Free, Fixed-Supported)




Fig.17 Axial Rigidity of the Screw Shaft (Fixed-Fixed)

**[Axial rigidity of the nut]**

The axial rigidity of the nut varies widely with preloads.

● **No Preload Type**

The logical rigidity in the axial direction when an axial load accounting for 30% of the basic dynamic load rating ( $C_a$ ) is applied is indicated in the specification tables of the corresponding model number. This value does not include the rigidity of the components related to the nut-mounting bracket. In general, set the rigidity at roughly 80% of the value in the table.

The rigidity when the applied axial load is not 30% of the basic dynamic load rating ( $C_a$ ) is calculated using the equation (40) below.

$$K_N = K \left( \frac{F_a}{0.3C_a} \right)^{\frac{1}{3}} \times 0.8 \quad \dots\dots(40)$$

$K_N$  : Axial rigidity of the nut (N/μm)

$K$  : Rigidity value in the specification tables (N/μm)

$F_a$  : Applied axial load (N)

$C_a$  : Basic dynamic load rating (N)

### ● Preload Type

The logical rigidity in the axial direction when an axial load accounting for 10% of the basic dynamic load rating (Ca) is applied is indicated in the dimensional table of the corresponding model number. This value does not include the rigidity of the components related to the nut-mounting bracket. In general, generally set the rigidity at roughly 80% of the value in the table.

The rigidity when the applied preload is not 10% of the basic dynamic load rating (Ca) is calculated using the equation (41) below.

$$K_N = K \left( \frac{Fa_0}{0.1Ca} \right)^{\frac{1}{3}} \times 0.8 \quad \dots\dots(41)$$

$K_N$  : Axial rigidity of the nut (N/ $\mu$ m)

$K$  : Rigidity value in the specification tables (N/ $\mu$ m)

$Fa_0$  : Applied preload (N)

$Ca$  : Basic dynamic load rating (N)

### [Axial rigidity of the support bearing]

The rigidity of the Ball Screw support bearing varies depending on the support bearing used.

The calculation of the rigidity with a representative angular contact ball bearing is shown in the equation (42) below.

$$K_B \doteq \frac{3Fa_0}{\delta a_0} \quad \dots\dots(42)$$

$K_B$  : Axial rigidity of the support bearing (N/ $\mu$ m)

$Fa_0$  : Applied preload of the support bearing (N)

$\delta a_0$  : Axial displacements ( $\mu$ m)

$$\delta a_0 = \frac{0.45}{\sin\alpha} \left( \frac{Q^2}{Da} \right)^{\frac{1}{3}}$$

$$Q = \frac{Fa_0}{Z\sin\alpha}$$

$Q$  : Axial load (N)

$Da$  : Ball diameter of the support bearing (mm)

$\alpha$  : Initial contact angle of the support bearing ( $^\circ$ )

$Z$  : Number of balls

For details of a specific support bearing, contact its manufacturer.

### [Axial Rigidity of the Nut Bracket and the Support Bearing Bracket]

Take this factor into consideration when designing your machine. Set the rigidity as high as possible.

# Studying the Positioning Accuracy

## Causes of Error in the Positioning Accuracy

The causes of error in the positioning accuracy include the lead angle accuracy, the axial clearance and the axial rigidity of the feed screw system. Other important factors include the thermal displacement from heat and the orientation change of the guide system during traveling.

## Studying the Lead Angle Accuracy

It is necessary to select the correct accuracy grade of the Ball Screw that satisfies the required positioning accuracy from the Ball Screw accuracies (Table1 on **A15-12**). Table23 on **A15-56** shows examples of selecting the accuracy grades by the application.

## Studying the Axial Clearance

The axial clearance is not a factor of positioning accuracy in single-directional feed. However, it will cause a backlash when the feed direction is inversed or the axial load is inversed. Select an axial clearance that meets the required backlash from Table10 and Table13 on **A15-19**.

Table23 Examples of Selecting Accuracy Grades by Application


| Applications                               |  | Shaft    | Accuracy grades |    |    |    |    |    |    |     |
|--|--|----------|-----------------|----|----|----|----|----|----|-----|
|  |  |          | C0              | C1 | C2 | C3 | C5 | C7 | C8 | C10 |
| NC machine tools                           | Lathe                                  | X        |                 | ●  | ●  | ●  | ●  |    |    |     |
|  |  | Z        |                 |    |    | ●  | ●  |    |    |     |
|  | Machining center                       | XY       |                 |    | ●  | ●  | ●  |    |    |     |
|  |  | Z        |                 |    | ●  | ●  | ●  |    |    |     |
|  | Drilling machine                       | XY       |                 |    |    | ●  | ●  |    |    |     |
|  |  | Z        |                 |    |    |    | ●  | ●  |    |     |
|  | Jig borer                              | XY       | ●               | ●  |    |    |    |    |    |     |
|  |  | Z        | ●               | ●  |    |    |    |    |    |     |
|  | Surface grinder                        | X        |                 |    |    | ●  | ●  |    |    |     |
|  |  | Y        |                 | ●  | ●  | ●  | ●  |    |    |     |
|  |  | Z        |                 | ●  | ●  | ●  | ●  |    |    |     |
|  | Cylindrical grinder                    | X        | ●               | ●  | ●  |    |    |    |    |     |
|  |  | Z        |                 | ●  | ●  | ●  |    |    |    |     |
|  | Electric discharge machine             | XY       | ●               | ●  | ●  |    |    |    |    |     |
|  |  | Z        |                 | ●  | ●  | ●  | ●  |    |    |     |
|  | Electric discharge machine             | XY       | ●               | ●  | ●  |    |    |    |    |     |
|  |  | Z        | ●               | ●  | ●  | ●  |    |    |    |     |
|  | Wire cutting machine                   | UV       |                 | ●  | ●  | ●  |    |    |    |     |
|  |  | XY       |                 |    |    | ●  | ●  | ●  |    |     |
|  | Laser beam machine                     | X        |                 |    |    | ●  | ●  | ●  |    |     |
| Z  |  |          |                 |    | ●  | ●  | ●  |    |    |     |
| Woodworking machine                        |  |          |                 |    |    | ●  | ●  | ●  | ●  |     |
| General-purpose machine; dedicated machine |  |          |                 |    | ●  | ●  | ●  | ●  | ●  |     |
| Industrial robot                           | Cartesian coordinate                   | Assembly |                 |    |    | ●  | ●  | ●  | ●  |     |
|  |  | Other    |                 |    |    |    | ●  | ●  | ●  |     |
|  | Vertical articulated type              | Assembly |                 |    |    |    | ●  | ●  | ●  |     |
|  |  | Other    |                 |    |    |    |    | ●  | ●  |     |
| Cylindrical coordinate                     |  |          |                 |    | ●  | ●  | ●  |    |    |     |
| Semiconductor manufacturing machine        | Photolithography machine               |          | ●               | ●  |    |    |    |    |    |     |
|  | Chemical treatment machine             |          |                 |    | ●  | ●  | ●  | ●  | ●  |     |
|  | Wire bonding machine                   |          |                 | ●  | ●  |    |    |    |    |     |
|  | Prober                                 |          | ●               | ●  | ●  | ●  |    |    |    |     |
|  | Printed circuit board drilling machine |          |                 | ●  | ●  | ●  | ●  | ●  |    |     |
| Electronic component inserter              |  |          |                 | ●  | ●  | ●  | ●  |    |    |     |
| 3D measuring instrument                    |  | ●        | ●               | ●  |    |    |    |    |    |     |
| Image processing machine                   |  | ●        | ●               | ●  |    |    |    |    |    |     |
| Injection molding machine                  |  |          |                 |    |    |    | ●  | ●  |    |     |
| Office equipment                           |  |          |                 |    |    | ●  | ●  | ●  |    |     |



## Studying the Axial Clearance of the Feed Screw System

Of the axial rigidities of the feed screw system, the axial rigidity of the screw shaft fluctuates according to the stroke position. When the axial rigidity is large, such change in the axial rigidity of the screw shaft will affect the positioning accuracy. Therefore, it is necessary to take into account the rigidity of the feed screw system (**A15-51** to **A15-54**).

Example: Positioning error due to the axial rigidity of the feed screw system during a vertical transfer



[Conditions]

Transferred weight: 1,000 N; table weight: 500 N

Ball Screw used: model BNF2512-2.5 (screw-shaft thread minor diameter  $d_1 = 21.9$  mm)

Stroke length: 600 mm ( $L=100$  mm to 700 mm)

Screw shaft mounting type: fixed-supported

[Consideration]

The difference in axial rigidity between  $L = 100$  mm and  $L = 700$  mm applied only to the axial rigidity of the screw shaft.

Therefore, positioning error due to the axial rigidity of the feed screw system equals to the difference in the axial displacement of the screw shaft between  $L = 100$  mm and  $L = 700$  mm.

**[Axial Rigidity of the Screw Shaft (see A15-51 and A15-52)]**

$$K_s = \frac{A \cdot E}{1000L} = \frac{376.5 \times 2.06 \times 10^5}{1000 \times L} = \frac{77.6 \times 10^3}{L}$$

$$A = \frac{\pi}{4} d_1^2 = \frac{\pi}{4} \times 21.9^2 = 376.5 \text{ mm}^2$$

$$E = 2.06 \times 10^5 \text{ N/mm}^2$$

(1) When  $L = 100 \text{ mm}$

$$K_{s1} = \frac{77.6 \times 10^3}{100} = 776 \text{ N}/\mu\text{m}$$

(2) When  $L = 700 \text{ mm}$

$$K_{s2} = \frac{77.6 \times 10^3}{700} = 111 \text{ N}/\mu\text{m}$$

**[Axial Displacement due to Axial Rigidity of the Screw Shaft]**

(1) When  $L = 100 \text{ mm}$

$$\delta_1 = \frac{Fa}{K_{s1}} = \frac{1000+500}{776} = 1.9 \mu\text{m}$$

(2) When  $L = 700 \text{ mm}$

$$\delta_2 = \frac{Fa}{K_{s2}} = \frac{1000+500}{111} = 13.5 \mu\text{m}$$

**[Positioning Error due to Axial Rigidity of the Feed Screw System]**

$$\begin{aligned} \text{Positioning accuracy} &= \delta_1 - \delta_2 = 1.9 - 13.5 \\ &= -11.6 \mu\text{m} \end{aligned}$$

Therefore, the positioning error due to the axial rigidity of the feed screw system is  $11.6 \mu\text{m}$ .

## Studying the Thermal Displacement through Heat Generation

If the temperature of the screw shaft increases during operation, the screw shaft is elongated due to heat thereby to lower the positioning accuracy. The expansion and contraction of the screw shaft is calculated using the equation (43) below.

$$\Delta l = \rho \times \Delta t \times l \dots\dots\dots(43)$$

- $\Delta l$  : Axial expansion/contraction of the screw shaft (mm)  
 $\rho$  : Thermal expansion coefficient ( $12 \times 10^{-6}/^{\circ}\text{C}$ )  
 $\Delta t$  : Temperature change in the screw shaft ( $^{\circ}\text{C}$ )  
 $l$  : Effective thread length (mm)

Thus, if the temperature of the screw shaft increases by  $1^{\circ}\text{C}$ , the screw shaft is elongated by  $12 \mu\text{m}$  per meter. Therefore, as the Ball Screw travels faster, the more heat is generated. So, as the temperature increases, the positioning accuracy lowers. Accordingly, if high accuracy is required, it is necessary to take measures to cope with the temperature increase.

### [Measures to Cope with the Temperature Rise]

#### ● Minimize the Heat Generation

- Minimize the preloads on the Ball Screw and the support bearing.
- Increase the Ball Screw lead and reduce the rotational speed.
- Select a correct lubricant. (See Accessories for Lubrication on **A24-2**.)
- Cool the circumference of the screw shaft with a lubricant or air.

#### ● Avoid Effect of Temperature Rise through Heat Generation

- Set a negative target value for the reference travel distance of the Ball Screw.  
 Generally, set a negative target value for the reference travel distance assuming a temperature increase of  $2^{\circ}\text{C}$  to  $5^{\circ}\text{C}$  by heat.  
 ( $-0.02 \text{ mm}$  to  $-0.06 \text{ mm/m}$ )
- Preload the shaft screw with tension. (See Fig.10 of the structure on **A15-29**.)

## Studying the Orientation Change during Traveling

The lead angle accuracy of the Ball Screw equals the positioning accuracy of the shaft center of the Ball Screw. Normally, the point where the highest positioning accuracy is required changes according to the ball screw center and the vertical or horizontal direction. Therefore, the orientation change during traveling affects the positioning accuracy.

The largest factor of orientation change affecting the positioning accuracy is pitching if the change occurs in the ball screw center and the vertical direction, and yawing if the change occurs in the horizontal direction.

Accordingly, it is necessary to study the orientation change (accuracy in pitching, yawing, etc.) during the traveling on the basis of the distance from the ball screw center to the location where positioning accuracy is required.

Positioning error due to pitching and yawing is obtained using the equation (44) below.

$$A = \ell \times \sin\theta \quad \dots\dots(44)$$

A : Positioning accuracy due to pitching (or yawing) (mm)

$\ell$  : Vertical (or horizontal) distance from the ball screw center (mm) (see Fig.18)

$\theta$  : Pitching (or yawing) ( $^{\circ}$ )




Fig.18

## Studying the Rotational Torque

The rotational torque required to convert rotational motion of the Ball Screw into straight motion is obtained using the equation (45) below.

### [During Uniform Motion]

$$\mathbf{T_t = (T_1 + T_2 + T_4) \cdot A} \dots\dots\dots(45)$$

- $T_t$  : Rotation torque required during uniform motion (N·mm)  
 $T_1$  : Friction torque due to an external load (N·mm)  
 $T_2$  : Preload torque of the Ball Screw (N·mm)  
 $T_4$  : Other torque (N·mm)  
 (frictional torque of the support bearing and oil seal)  
 $A$  : Reduction ratio

### [During Acceleration]

$$\mathbf{T_k = T_t + T_3} \dots\dots\dots(46)$$

- $T_k$  : Rotation torque required during acceleration (N·mm)  
 $T_3$  : Torque required for acceleration (N·mm)

### [During Deceleration]

$$\mathbf{T_g = T_t - T_3} \dots\dots\dots(47)$$

- $T_g$  : Rotational torque required for deceleration (N·mm)

---

## Frictional Torque Due to an External Load

---

Of the turning forces required for the Ball Screw, the rotational torque needed for an external load (guide surface resistance or external force) is obtained using the equation (48) below.

$$\mathbf{T_1 = \frac{F_a \cdot Ph}{2\pi \cdot \eta}} \dots\dots\dots(48)$$

- $T_1$  : Friction torque due to an external load (N·mm)  
 $F_a$  : Applied load (N)  
 $Ph$  : Ball Screw lead (mm)  
 $\eta$  : Ball Screw efficiency (0.9 to 0.95)

---

## Torque Due to a Preload on the Ball Screw

---

For a preload on the Ball Screw, see “Preload Torque” on **A15-22**.

## Torque Required for Acceleration

$$\mathbf{T}_3 = \mathbf{J} \times \omega' \times 10^3 \dots\dots(49)$$

$T_3$  : Torque required for acceleration (N·mm)

$J$  : Inertial moment (kg·m<sup>2</sup>)

$\omega'$  : Angular acceleration (rad/s<sup>2</sup>)

$$J = m \left( \frac{Ph}{2\pi} \right)^2 \cdot A^2 \cdot 10^{-6} + J_s \cdot A^2 + J_A \cdot A^2 + J_B$$

$m$  : Transferred mass (kg)

$Ph$  : Ball Screw lead (mm)

$J_s$  : Inertial moment of the screw shaft (kg·m<sup>2</sup>)  
(indicated in the specification tables of the respective model number)

$A$  : Reduction ratio

$J_A$  : Inertial moment of gears, etc. attached to the screw shaft side (kg·m<sup>2</sup>)

$J_B$  : Inertial moment of gears, etc. attached to the motor side (kg·m<sup>2</sup>)

$$\omega' = \frac{2\pi \cdot Nm}{60t}$$

$Nm$  : Motor revolutions per minute (min<sup>-1</sup>)

$t$  : Acceleration time (s)

[Ref.] Inertial moment of a round object

$$J = \frac{m \cdot D^2}{8 \cdot 10^6}$$

$J$  : Inertial moment (kg·m<sup>2</sup>)

$m$  : Mass of a round object (kg)

$D$  : Screw shaft outer diameter (mm)

## Investigating the Terminal Strength of Ball Screw Shafts

When torque is conveyed through the screw shaft in a ball screw, the strength of the screw shaft must be taken into consideration since it experiences both torsion load and bending load.

### [Screw shaft under torsion]

When torsion load is applied to the end of a ball screw shaft, use equation (50) to obtain the end diameter of the screw shaft.

$$T = \tau_a \cdot Z_P \quad \text{and} \quad Z_P = \frac{T}{\tau_a} \quad \dots\dots(50)$$


$T$  : Maximum torsion moment (N·mm)

$\tau_a$  : Permissible torsion stress of the screw shaft (49 N/mm<sup>2</sup>)

$Z_P$  : Section modulus (mm<sup>3</sup>)

$$Z_P = \frac{\pi \cdot d^3}{16}$$

T: Torsion moment



### [Screw shaft under bending]

When bending load is applied to the end of a ball screw shaft, use equation (51) to obtain the end diameter of the screw shaft.

$$M = \sigma \cdot Z \quad \text{and} \quad Z = \frac{M}{\sigma} \quad \dots\dots(51)$$


$M$  : Maximum bending moment (N·mm)

$\sigma$  : Permissible bending stress of the screw shaft (98 N/mm<sup>2</sup>)

$Z$  : Section Modulus (mm<sup>3</sup>)

$$Z = \frac{\pi \cdot d^3}{32}$$

M: Bending moment





## Point of Selection

### Studying the Rotational Torque

#### [If the shaft experiences both torsion and bending]

When torsion load and bending load are both applied simultaneously to the end of a ball screw shaft, calculate the diameter of the screw shaft separately for each, taking into consideration the corresponding bending moment ( $M_e$ ) and the corresponding torsion moment ( $T_e$ ). Then calculate the thickness of the screw shaft and use the largest of the values.

#### Equivalent bending moment

$$M_e = \frac{M + \sqrt{M^2 + T^2}}{2} = \frac{M}{2} \left\{ 1 + \sqrt{1 + \left(\frac{T}{M}\right)^2} \right\}$$

$$M_e = \sigma \cdot Z$$

#### Equivalent torsion moment

$$T_e = \sqrt{M^2 + T^2} = M \cdot \sqrt{1 + \left(\frac{T}{M}\right)^2}$$

$$T_e = \tau_a \cdot Z_P$$

## Studying the Driving Motor

When selecting a driving motor required to rotate the Ball Screw, normally take into account the rotational speed, rotational torque and minimum feed amount.

---

### When Using a Servomotor

---

#### [Rotational Speed]

The rotation speed required for the motor is obtained using the equation (52) based on the feed speed, Ball Screw lead and reduction ratio.

$$N_M = \frac{V \times 1000 \times 60}{Ph} \times \frac{1}{A} \dots\dots(52)$$

- $N_M$  : Required rotation speed of the motor ( $\text{min}^{-1}$ )  
 $V$  : Feeding speed (m/s)  
 $Ph$  : Ball Screw lead (mm)  
 $A$  : Reduction ratio

The rated rotational speed of the motor must be equal to or above the calculated value ( $N_M$ ) above.

$$N_M \leq N_R$$

- $N_R$  : The rated rotation speed of the motor ( $\text{min}^{-1}$ )

#### [Required Resolution]

Resolutions required for the encoder and the driver are obtained using the equation (53) based on the minimum feed amount, Ball Screw lead and reduction ratio.

$$B = \frac{Ph \cdot A}{S} \dots\dots(53)$$

- $B$  : Resolution required for the encoder and the driver (p/rev)  
 $Ph$  : Ball Screw lead (mm)  
 $A$  : Reduction ratio  
 $S$  : Minimum feed amount (mm)

**[Motor Torque]**

The torque required for the motor differs between uniform motion, acceleration and deceleration. To calculate the rotational torque, see “Studying the Rotational Torque” on **A15-61**.

a. Maximum torque

The maximum torque required for the motor must be equal to or below the maximum peak torque of the motor.

$$T_{\max} \leq T_{p\max}$$

$T_{\max}$  : Maximum torque acting on the motor

$T_{p\max}$  : Maximum peak torque of the motor

b. Effective torque value

The effective value of the torque required for the motor must be calculated. The effective value of the torque is obtained using the equation (54).

$$T_{\text{rms}} = \sqrt{\frac{T_1^2 \times t_1 + T_2^2 \times t_2 + T_3^2 \times t_3}{t}} \dots\dots\dots(54)$$

$T_{\text{rms}}$  : Effective torque value (N·mm)

$T_n$  : Fluctuating torque (N·mm)

$t_n$  : Time during which the torque  $T_n$  is applied (s)

$t$  : Cycle time (s)

$$(t=t_1+t_2+t_3)$$

The calculated effective value of the torque must be equal to or below the rated torque of the motor.

$$T_{\text{rms}} \leq T_R$$

$T_R$  : Rated torque of the motor (N·mm)

**[Inertial Moment]**

The inertial moment required for the motor is obtained using the equation (55).

$$J_M = \frac{J}{C} \dots\dots\dots(55)$$

$J_M$  : Inertial moment required for the motor (kg·m<sup>2</sup>)

$C$  : Factor determined by the motor and the driver

(It is normally between 3 to 10. However, it varies depending on the motor and the driver. Check the specific value in the catalog by the motor manufacturer.)

The inertial moment of the motor must be equal to or above the calculated  $J_M$  value.

## When Using a Stepping Motor (Pulse Motor)

### [Minimal Feed Amount(per Step)]

The step angle required for the motor and the driver is obtained using the equation (56) based on the minimum feed amount, Ball Screw lead and reduction ratio.

$$E = \frac{360S}{Ph \cdot A} \dots\dots(56)$$

- E : Step angle required for the motor and the driver (°)  
 S : Minimum feed amount (mm)  
 (per step)  
 Ph : Ball Screw lead (mm)  
 A : Reduction ratio

### [Pulse Speed and Motor Torque]

#### a. Pulse speed

The pulse speed is obtained using the equation (57) based on the feed speed and the minimum feed amount.

$$f = \frac{V \times 1000}{S} \dots\dots(57)$$

- f : Pulse speed (Hz)  
 V : Feeding speed (m/s)  
 S : Minimum feed amount (mm)

#### b. Torque required for the motor

The torque required for the motor differs between the uniform motion, the acceleration and the deceleration. To calculate the rotational torque, see “Studying the Rotational Torque” on **A15-61**.

Thus, the pulse speed required for the motor and the required torque can be calculated in the manner described above.

Although the torque varies depending on the motors, normally the calculated torque should be doubled to ensure safety. Check if the torque can be used in the motor’s speed-torque curve.

Ball Screw

## Features of Each Model

# Overview of THK Ball Screws

## Positioning Ball Screw

▲15-72

ISO 3408 compliant

## Positioning Ball Screw

▲15-102

Preload

Preload/  
No preload

Preload

Preload/  
No preload

No preload

### SDAN-V

Caged Ball

Double nut

High speed

Compact

### SDAN-VX

Double nut

High speed

Compact

### EPB-V

High speed

Compact

### SDA-V

Caged Ball

High speed

Various leads

Compact

### SDA-VZ

High speed

Various leads

Compact

### EBB-V

High speed

Compact

### SBN-V

Caged Ball

High speed

### SBK

Caged Ball

High speed

Large lead

### BIF-V

High speed

### BNFN-V

Double nut

High speed

### DIK

Compact

### DKN

Compact

Double nut

### BLW

Double nut

Large lead

### BNK

Standard to large lead

### MDK

### MBF

Miniature

### BNF-V

High speed

### DK

Compact

### WHF

High speed

Large lead


### BLK

### WGF







Large lead

### BNT

Flat nut



# Positioning, ISO 3408 compliant

| Series      | Type    |   | Features                               |  |
|-------------|---------|---|--|--|
| Positioning | SDAN-V  |    | Double-nut, Compact Nut, high DN value |  |
|             | SDAN-VX |    | Double-nut, Compact Nut, high DN value |  |
|             | SDA-V   |    | Compact Nut, high DN value             |  |
|             | SDA-VZ  |    | Compact Nut, high DN value             |  |
|             | EPB-V   |   | Compact nut                            |  |
|             | EBB-V   |  | Compact nut                            |  |



|  | Caged ball | Compact nut | Miniature | High load capacity | Offset Preload | Double-nut Preload | DN Value | Shaft diameter (mm) | Lead (mm) | Page No.      |
|--|------------|-------------|-----------|--------------------|----------------|--------------------|----------|---------------------|-----------|---------------|
|  | ✓          | ✓           |           |                    |                | ✓                  | 160000   | 31 to 50            | 10 to 40  | <b>A15-76</b> |
|  |            | ✓           |           |                    |                | ✓                  | 130000   | 31 to 63            | 10 to 40  | <b>A15-76</b> |
|  | ✓          | ✓           |           |                    |                |                    | 160000   | 14 to 50            | 4 to 50   | <b>A15-82</b> |
|  |            | ✓           |           |                    |                |                    | 100000   | 12 to 50            | 4 to 50   | <b>A15-82</b> |
|  |            |             |           |                    |                |                    | 130000   | 28 to 50            | 5 to 50   | <b>A15-82</b> |
|  |            | ✓           |           |                    | ✓              |                    | 130000   | 16 to 63            | 4 to 12   | <b>A15-94</b> |
|  |            | ✓           |           |                    |                |                    | 130000   | 16 to 80            | 4 to 20   | <b>A15-98</b> |

## Standard combinations of outer diameters and leads of the screw shafts


| Shaft diameter | Lead                    |                                   |                          |                           |                                   |                          |                  |  |
|----------------|-------------------------|-----------------------------------|--------------------------|---------------------------|-----------------------------------|--------------------------|------------------|--|
|                | 4                       | 5                                 | 6                        | 8                         | 10                                | 12                       | 16               |  |
| 10             | SDA-VZ                  | SDA-VZ                            |                          |                           | SDA-VZ                            |                          |                  |  |
| 12             |                         | SDA-VZ                            |                          |                           | SDA-VZ                            |                          |                  |  |
| 14             |                         | SDA-V                             |                          |                           |                                   |                          |                  |  |
| 15             |                         | SDA-V                             |                          |                           | SDA-V                             |                          |                  |  |
| 16             |                         | SDA-V<br>EBB-V<br>EPB-V           |                          |                           | SDA-V                             |                          | SDA-V            |  |
| 20             | SDA-V<br>EBB-V<br>EPB-V | SDA-V<br>EBB-V<br>EPB-V           | EBB-V<br>EPB-V           | EBB-V<br>EPB-V            | SDA-V<br>EBB-V<br>EPB-V           | EBB-V<br>EPB-V           |                  |  |
| 25             | EBB-V<br>EPB-V          | SDA-V<br>EBB-V<br>EPB-V           | EBB-V<br>EPB-V           | EBB-V<br>EPB-V            | SDA-V<br>EBB-V<br>EPB-V           | EBB-V<br>EPB-V           |                  |  |
| 28             |                         |                                   | SDA-V<br>EBB-V<br>EPB-V  |                           |                                   |                          |                  |  |
| 31             |                         |                                   |                          |                           | SDA-V<br>SDAN-V                   | SDA-V<br>SDAN-V          | SDA-V<br>SDAN-V  |  |
| 32             | EBB-V<br>EPB-V          | SDA-V<br>SDAN-V<br>EBB-V<br>EPB-V | SDAN-V<br>EBB-V<br>EPB-V | SDAN-V<br>EBB-V<br>EPB-V  | SDA-V<br>SDAN-V<br>EBB-V<br>EPB-V | SDAN-V                   | SDAN-V           |  |
| 36             | EBB-V<br>EPB-V          |                                   | SDAN-V<br>EBB-V<br>EPB-V | EBB-V<br>EPB-V            | SDA-V<br>SDAN-V                   | SDA-V<br>SDAN-V          | SDA-V<br>SDAN-V  |  |
| 38             |                         |                                   |                          |                           | SDA-V<br>SDAN-V                   | SDA-V<br>SDAN-V          | SDA-V<br>SDAN-V  |  |
| 40             | EBB-V<br>EPB-V          | EBB-V<br>EPB-V                    | EBB-V<br>EPB-V           | SDAN-VX<br>EBB-V<br>EPB-V | SDAN-V<br>EBB-V<br>EPB-V          | SDAN-V<br>EBB-V<br>EPB-V | SDAN-V           |  |
| 45             |                         |                                   |                          |                           | SDA-V<br>SDAN-V                   | SDA-V<br>SDAN-V          | SDA-V<br>SDAN-V  |  |
| 50             |                         | EBB-V<br>EPB-V                    |                          | EBB-V<br>EPB-V            | SDA-V<br>SDAN-V<br>EBB-V<br>EPB-V | SDA-V<br>SDAN-V          | SDA-V<br>SDAN-V  |  |
| 55             |                         |                                   |                          |                           | SDAN-VX                           | SDAN-VX                  | SDAN-VX          |  |
| 63             |                         |                                   |                          |                           | SDAN-VX<br>EBB-V<br>EPB-V         | SDAN-VX<br>EBB-V         | SDAN-VX<br>EBB-V |  |
| 80             |                         |                                   |                          |                           | EBB-V                             | EBB-V                    | EBB-V            |  |

Unit: mm

| Lead |                          |                 |                 |       |       |                 |       |
|------|--------------------------|-----------------|-----------------|-------|-------|-----------------|-------|
|      | 20                       | 25              | 30              | 32    | 36    | 40              | 50    |
|      | SDA-VZ                   |                 | SDA-VZ          |       |       |                 |       |
|      | SDA-V                    |                 | SDA-V           |       |       |                 |       |
|      | SDA-V                    |                 | SDA-V           |       |       | SDA-V           |       |
|      | SDA-V                    | SDA-V           | SDA-V           |       |       |                 | SDA-V |
|      | SDA-V<br>SDAN-V          |                 |                 | SDA-V |       |                 |       |
|      | SDAN-V                   |                 |                 |       |       |                 |       |
|      | SDA-V<br>SDAN-V          |                 |                 |       | SDA-V |                 |       |
|      | SDA-V<br>SDAN-V          | SDA-V           | SDA-V           |       |       | SDA-V           |       |
|      | SDAN-V<br>EBB-V          |                 |                 |       |       |                 |       |
|      | SDA-V<br>SDAN-V          | SDA-V           | SDA-V           |       |       | SDA-V           |       |
|      | SDA-V<br>SDAN-V<br>EBB-V | SDA-V<br>SDAN-V | SDA-V<br>SDAN-V |       |       | SDA-V<br>SDAN-V | SDA-V |
|      | SDAN-VX                  |                 |                 |       |       |                 |       |
|      | SDAN-VX<br>EBB-V         | SDAN-VX         | SDAN-VX         |       |       | SDAN-VX         |       |
|      | EBB-V                    |                 |                 |       |       |                 |       |

# SDAN-V With Preload/No Preload

|          |                     |        |
|----------|---------------------|--------|
| DN value | SDAN-V (Caged Ball) | 160000 |
|          | SDAN-VX (Full-Ball) | 130000 |



SDAN31V to 32V

Nut type I

Nut type II

| Model No.       | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Screw shaft thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating   |                 |                     |                 | Rigidity            |                     |
|-----------------|---------------------------------|------------|--------------------------------------|---|--|---------------------|-----------------|---------------------|-----------------|---------------------|---------------------|
|                 |                                 |            |                                      |   |  | SDAN-V (Caged Ball) |                 | SDAN-VX (Full-Ball) |                 | SDAN-V (Caged Ball) | SDAN-VX (Full-Ball) |
|                 |                                 |            |                                      |   |  | Ca                  | C <sub>0a</sub> | Ca                  | C <sub>0a</sub> | K                   | K                   |
|                 |                                 |            |                                      |   |  | kN                  | kN              | kN                  | kN              | N/μm                | N/μm                |
| SDAN 3110V-5    | 31                              | 10         | 32                                   | 25.4                                    | 1×5                                    | 57.1                | 94.7            | 54.4                | 99.7            | 1059                | 1108                |
| SDAN 3112V-5    | 31                              | 12         | 32                                   | 25.4                                    | 1×5                                    | 57                  | 94.7            | 54.3                | 99.9            | 1058                | 1109                |
| SDAN 3116V-5    | 31                              | 16         | 32                                   | 25.4                                    | 1×5                                    | 56.8                | 96              | 54.1                | 100.5           | 1068                | 1112                |
| SDAN 3120V-5    | 31                              | 20         | 32                                   | 25.4                                    | 1×5                                    | 56.6                | 90.3            | 53.9                | 95.1            | 1065                | 1116                |
| SDAN 3205V-4    | 32                              | 5          | 32.75                                | 29.5                                    | 1×4                                    | 18.8                | 38.5            | 17.9                | 41.7            | 776                 | 832                 |
| SDAN 3206V-5    | 32                              | 6          | 33                                   | 28.9                                    | 1×5                                    | 31.4                | 62.4            | 29.9                | 66.1            | 1027                | 1082                |
| SDAN 3208V-5    | 32                              | 8          | 33                                   | 28.9                                    | 1×5                                    | 31.4                | 62.4            | 29.9                | 66.2            | 1026                | 1082                |
| SDAN 3210V-5    | 32                              | 10         | 33                                   | 28.9                                    | 1×5                                    | 31.3                | 62.9            | 29.8                | 66.3            | 1033                | 1083                |
| SDAN 3210VA-5   | 32                              | 10         | 33                                   | 26.4                                    | 1×5                                    | 58.1                | 98.9            | 55.3                | 103.1           | 1097                | 1138                |
| SDAN 3212VA-5   | 32                              | 12         | 33                                   | 26.4                                    | 1×5                                    | 58                  | 98.9            | 55.3                | 103.3           | 1096                | 1139                |
| SDAN 3216VA-5   | 32                              | 16         | 33                                   | 26.4                                    | 1×5                                    | 57.8                | 98.9            | 55.1                | 103.8           | 1094                | 1141                |
| SDAN 3220VA-5   | 32                              | 20         | 33                                   | 26.4                                    | 1×5                                    | 57.6                | 94.3            | 54.9                | 98.2            | 1104                | 1145                |
| SDAN 3606V-4    | 36                              | 6          | 37                                   | 32.9                                    | 1×4                                    | 26.9                | 55.6            | 25.6                | 58.6            | 902                 | 945                 |
| SDAN 3610V-5    | 36                              | 10         | 37                                   | 30.4                                    | 1×5                                    | 61.7                | 110.6           | 58.8                | 116.4           | 1196                | 1252                |
| SDAN 3612V-5    | 36                              | 12         | 37                                   | 30.4                                    | 1×5                                    | 61.7                | 110.6           | 58.7                | 116.6           | 1195                | 1253                |
| SDAN 3616V-5    | 36                              | 16         | 37                                   | 30.4                                    | 1×5                                    | 61.5                | 111.9           | 58.6                | 117.1           | 1206                | 1255                |
| SDAN 3620V-5    | 36                              | 20         | 37                                   | 30.4                                    | 1×5                                    | 61.3                | 105.2           | 58.4                | 110.6           | 1203                | 1258                |
| SDAN 3810V-5    | 38                              | 10         | 39                                   | 32.4                                    | 1×5                                    | 63.4                | 117.7           | 60.4                | 123.1           | 1257                | 1308                |
| SDAN 3812V-5    | 38                              | 12         | 39                                   | 32.4                                    | 1×5                                    | 63.4                | 117.7           | 60.3                | 123.3           | 1256                | 1309                |
| SDAN 3816V-5    | 38                              | 16         | 39                                   | 32.4                                    | 1×5                                    | 63.2                | 117.7           | 60.2                | 123.7           | 1254                | 1311                |
| SDAN 3820V-5    | 38                              | 20         | 39                                   | 32.4                                    | 1×5                                    | 63.0                | 111.9           | 60.0                | 116.9           | 1265                | 1314                |
| * SDAN 4008VX-5 | 40                              | 8          | 41.25                                | 36.3                                    | 1×5                                    | —                   | —               | 42.2                | 99.4            | —                   | 1326                |
| SDAN 4010VA-5   | 40                              | 10         | 41.75                                | 35.2                                    | 1×5                                    | 65.6                | 126.4           | 62.5                | 132.3           | 1329                | 1384                |
| SDAN 4012VA-5   | 40                              | 12         | 41.75                                | 35.2                                    | 1×5                                    | 65.5                | 126.4           | 62.4                | 132.5           | 1328                | 1385                |
| SDAN 4016VA-5   | 40                              | 16         | 41.75                                | 35.2                                    | 1×5                                    | 65.4                | 126.4           | 62.3                | 132.9           | 1326                | 1387                |
| SDAN 4020VA-5   | 40                              | 20         | 41.75                                | 35.2                                    | 1×5                                    | 65.2                | 127.7           | 62.1                | 133.4           | 1336                | 1389                |

Note) Models marked with an asterisk (\*) in the specification table are only compatible with Model SDAN-VX (full-ball type).

## Model number coding


**SDAN3110V X -5 TT G0 +830L C5**

Model No. | Number of turns | Overall screw shaft length (in mm) | Accuracy symbol (\*2)

Full-ball type code (No code for caged ball type)

Contamination protection accessory symbol (\*1) | Symbol for clearance in the axial direction (G0 for all SDAN-V variations)

(\*1) See **A15-334**. (\*2) See **A15-12**.



SDAN36V to 40V

Nut type I

Nut type II

Unit: mm

| Nut type | Nut dimensions |                 |                |                  |                |                |                |                  |     |                |                     | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass                | Shaft mass | Permissible rotational speed |                   |                   |
|----------|----------------|-----------------|----------------|------------------|----------------|----------------|----------------|------------------|-----|----------------|---------------------|---|-------------------------|------------|------------------------------|-------------------|-------------------|
|          | Outer diameter | Flange diameter | Overall length | Spacer thickness |                |                |                | Lubrication hole |     |                | SDAN-V (Caged Ball) |   |                         |            | SDAN-VX (Full-Ball)          |                   |                   |
|          | D              | D <sub>1</sub>  | L <sub>1</sub> | H                | B <sub>1</sub> | B <sub>2</sub> | B <sub>3</sub> | B <sub>4</sub>   | PCD | d <sub>1</sub> | T <sub>w</sub>      | A   | kg·m <sup>2</sup> /mm   | kg         | kg/m                         | min <sup>-1</sup> | min <sup>-1</sup> |
| I        | 56             | 86              | 135            | 14               | 47             | 20             | 11             | 62               | 71  | 9              | 65                  | M6  | 7.07 × 10 <sup>-7</sup> | 1.83       | 5.02                         | 5000              | 4060              |
| I        | 56             | 86              | 158            | 14               | 56             | 20             | 15.6           | 72               | 71  | 9              | 65                  | M6  | 7.07 × 10 <sup>-7</sup> | 2.1        | 5.17                         | 5000              | 4060              |
| I        | 56             | 86              | 189            | 14               | 75             | 20             | 8.9            | 90               | 71  | 9              | 65                  | M6  | 7.07 × 10 <sup>-7</sup> | 2.5        | 5.36                         | 5000              | 4060              |
| I        | 56             | 86              | 232            | 14               | 94             | 20             | 14.1           | 109              | 71  | 9              | 65                  | M6  | 7.07 × 10 <sup>-7</sup> | 3.01       | 5.48                         | 5000              | 4060              |
| II       | 50             | 80              | 62             | 12               | 16.5           | 16.5           | 4.5            | 29               | 65  | 9              | 62                  | M6  | 8.08 × 10 <sup>-7</sup> | 0.66       | 5.89                         | 4880              | 3960              |
| II       | 50             | 80              | 84             | 12               | 27.2           | 27.2           | 5.8            | 39               | 65  | 9              | 62                  | M6  | 8.08 × 10 <sup>-7</sup> | 0.85       | 5.79                         | 4840              | 3930              |
| II       | 50             | 80              | 108            | 12               | 37             | 20             | 10.4           | 49               | 65  | 9              | 62                  | M6  | 8.08 × 10 <sup>-7</sup> | 1.03       | 5.87                         | 4840              | 3930              |
| II       | 50             | 80              | 121            | 12               | 46             | 20             | 5              | 58               | 65  | 9              | 62                  | M6  | 8.08 × 10 <sup>-7</sup> | 1.17       | 6                            | 4840              | 3930              |
| I        | 57             | 87              | 135            | 14               | 47             | 20             | 11             | 62               | 72  | 9              | 66                  | M6  | 8.08 × 10 <sup>-7</sup> | 1.87       | 5.38                         | 4840              | 3930              |
| I        | 57             | 87              | 158            | 14               | 56             | 20             | 15.6           | 72               | 72  | 9              | 66                  | M6  | 8.08 × 10 <sup>-7</sup> | 2.14       | 5.54                         | 4840              | 3930              |
| I        | 57             | 87              | 189            | 14               | 75             | 20             | 8.7            | 90               | 72  | 9              | 66                  | M6  | 8.08 × 10 <sup>-7</sup> | 2.56       | 5.73                         | 4840              | 3930              |
| I        | 57             | 87              | 232            | 14               | 94             | 20             | 13.9           | 109              | 72  | 9              | 66                  | M6  | 8.08 × 10 <sup>-7</sup> | 3.08       | 5.85                         | 4840              | 3930              |
| II       | 54             | 84              | 72             | 14               | 19.2           | 19.2           | 5.8            | 33               | 69  | 9              | 66                  | M6  | 1.29 × 10 <sup>-6</sup> | 0.84       | 7.4                          | 4320              | 3510              |
| I        | 61             | 91              | 135            | 14               | 47             | 20             | 11             | 62               | 76  | 9              | 68                  | M8×1  | 1.29 × 10 <sup>-6</sup> | 2          | 6.93                         | 4320              | 3510              |
| I        | 61             | 91              | 158            | 14               | 56             | 20             | 15.6           | 72               | 76  | 9              | 68                  | M8×1  | 1.29 × 10 <sup>-6</sup> | 2.31       | 7.11                         | 4320              | 3510              |
| I        | 61             | 91              | 189            | 14               | 75             | 20             | 8.8            | 90               | 76  | 9              | 68                  | M8×1  | 1.29 × 10 <sup>-6</sup> | 2.77       | 7.34                         | 4320              | 3510              |
| I        | 61             | 91              | 232            | 14               | 94             | 20             | 14             | 109              | 76  | 9              | 68                  | M8×1  | 1.29 × 10 <sup>-6</sup> | 3.33       | 7.47                         | 4320              | 3510              |
| I        | 63             | 93              | 135            | 14               | 47             | 20             | 11.1           | 62               | 78  | 9              | 70                  | M8×1  | 1.60 × 10 <sup>-6</sup> | 2.08       | 7.79                         | 4100              | 3330              |
| I        | 63             | 93              | 158            | 14               | 56             | 20             | 15.7           | 71               | 78  | 9              | 70                  | M8×1  | 1.60 × 10 <sup>-6</sup> | 2.4        | 7.97                         | 4100              | 3330              |
| I        | 63             | 93              | 189            | 14               | 75             | 20             | 8.9            | 90               | 78  | 9              | 70                  | M8×1  | 1.60 × 10 <sup>-6</sup> | 2.89       | 8.21                         | 4100              | 3330              |
| I        | 63             | 93              | 232            | 14               | 94             | 20             | 14.2           | 109              | 78  | 9              | 70                  | M8×1  | 1.60 × 10 <sup>-6</sup> | 3.44       | 8.35                         | 4100              | 3330              |
| II       | 61             | 91              | 111            | 14               | 38             | 20             | 7.4            | 52               | 76  | 9              | 68                  | M8×1  | 1.97 × 10 <sup>-6</sup> | 1.47       | 9.08                         | —                 | 3150              |
| I        | 70             | 100             | 135            | 14               | 47             | 20             | 10.9           | 62               | 85  | 9              | 75                  | M8×1  | 1.97 × 10 <sup>-6</sup> | 2.68       | 8.9                          | 3830              | 3110              |
| I        | 70             | 100             | 158            | 14               | 56             | 20             | 15.5           | 72               | 85  | 9              | 75                  | M8×1  | 1.97 × 10 <sup>-6</sup> | 3.1        | 9.06                         | 3830              | 3110              |
| I        | 70             | 100             | 189            | 14               | 75             | 20             | 8.7            | 90               | 85  | 9              | 75                  | M8×1  | 1.97 × 10 <sup>-6</sup> | 3.7        | 9.27                         | 3830              | 3110              |
| I        | 70             | 100             | 232            | 14               | 94             | 20             | 13.9           | 109              | 85  | 9              | 75                  | M8×1  | 1.97 × 10 <sup>-6</sup> | 4.45       | 9.39                         | 3830              | 3110              |

Axial Clearance

Unit: mm

| Clearance symbol | G0        |
|------------------|-----------|
| Axial clearance  | 0 or less |

Note) L<sub>1</sub>, B<sub>1</sub>, and B<sub>2</sub> dimensions are those when a thin film seal (TT) has been installed. Dimensions without the seal are shown in parentheses. It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.

Note: The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 3 times the applied preload, which itself is 10% of the basic axial dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the rigidity value in the table as the actual value.

If the axial load (Fa<sub>0</sub>) is not 0.1 Ca, the rigidity value (K<sub>N</sub>) is obtained from the following formula.


$$K_N = K \left( \frac{Fa_0}{0.1Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# SDAN-V

## With Preload/No Preload

|          |                     |        |
|----------|---------------------|--------|
| DN value | SDAN-V (Caged Ball) | 160000 |
|          | SDAN-VX (Full-Ball) | 130000 |



| Model No.     | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Screw shaft thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating   |                       |                     |                       | Rigidity            |                     |
|---------------|---------------------------------|------------|--------------------------------------|---|--|---------------------|-----------------------|---------------------|-----------------------|---------------------|---------------------|
|               |                                 |            |                                      |   |  | SDAN-V (Caged Ball) |                       | SDAN-VX (Full-Ball) |                       | SDAN-V (Caged Ball) | SDAN-VX (Full-Ball) |
|               |                                 |            |                                      |   |  | Ca<br>kN            | C <sub>0a</sub><br>kN | Ca<br>kN            | C <sub>0a</sub><br>kN | K<br>N/μm           | K<br>N/μm           |
| SDAN 4510V-5  | 45                              | 10         | 46                                   | 39.4                                    | 1×5                                    | 68.7                | 139.4                 | 65.4                | 146.5                 | 1434                | 1499                |
| SDAN 4510VA-5 | 45                              | 10         | 46.75                                | 40.2                                    | 1×5                                    | 69.2                | 142.2                 | 65.9                | 149                   | 1457                | 1519                |
| SDAN 4512V-5  | 45                              | 12         | 46                                   | 39.4                                    | 1×5                                    | 68.6                | 139.4                 | 65.4                | 146.7                 | 1433                | 1500                |
| SDAN 4512VA-5 | 45                              | 12         | 46.75                                | 40.2                                    | 1×5                                    | 69.2                | 142.2                 | 65.9                | 149.2                 | 1457                | 1519                |
| SDAN 4516V-5  | 45                              | 16         | 46                                   | 39.4                                    | 1×5                                    | 68.5                | 140.7                 | 65.3                | 147                   | 1444                | 1501                |
| SDAN 4516VA-5 | 45                              | 16         | 46.75                                | 40.2                                    | 1×5                                    | 69                  | 142.2                 | 65.8                | 149.5                 | 1455                | 1521                |
| SDAN 4520V-5  | 45                              | 20         | 46                                   | 39.4                                    | 1×5                                    | 68.4                | 140.7                 | 65.1                | 147.5                 | 1442                | 1504                |
| SDAN 4520VA-5 | 45                              | 20         | 46.75                                | 40.2                                    | 1×5                                    | 68.9                | 143.6                 | 65.6                | 150                   | 1465                | 1524                |
| SDAN 5010V-5  | 50                              | 10         | 51                                   | 44.4                                    | 1×5                                    | 72                  | 155.2                 | 68.6                | 163.2                 | 1559                | 1630                |
| SDAN 5010VA-5 | 50                              | 10         | 51.75                                | 45.2                                    | 1×5                                    | 72.5                | 158.1                 | 69                  | 165.7                 | 1582                | 1650                |
| SDAN 5012V-5  | 50                              | 12         | 51                                   | 44.4                                    | 1×5                                    | 72                  | 155.2                 | 68.5                | 163.3                 | 1559                | 1631                |
| SDAN 5012VA-5 | 50                              | 12         | 51.75                                | 45.2                                    | 1×5                                    | 72.4                | 158.1                 | 69                  | 165.9                 | 1582                | 1651                |
| SDAN 5016V-5  | 50                              | 16         | 51                                   | 44.4                                    | 1×5                                    | 71.9                | 156.6                 | 68.4                | 163.7                 | 1570                | 1633                |
| SDAN 5016VA-5 | 50                              | 16         | 51.75                                | 45.2                                    | 1×5                                    | 72.3                | 158.1                 | 68.9                | 166.2                 | 1580                | 1652                |
| SDAN 5020V-5  | 50                              | 20         | 51                                   | 44.4                                    | 1×5                                    | 71.7                | 156.6                 | 68.3                | 164.2                 | 1568                | 1635                |
| SDAN 5020VA-5 | 50                              | 20         | 51.75                                | 45.2                                    | 1×5                                    | 72.2                | 159.4                 | 68.8                | 166.7                 | 1591                | 1654                |
| SDAN 5025V-4  | 50                              | 25         | 51                                   | 44.4                                    | 1×4                                    | 58.2                | 123.6                 | 55.5                | 129.8                 | 1249                | 1304                |
| SDAN 5025VA-4 | 50                              | 25         | 51.75                                | 45.2                                    | 1×4                                    | 58.6                | 125.1                 | 55.8                | 131.7                 | 1260                | 1319                |
| SDAN 5030V-4  | 50                              | 30         | 51                                   | 44.4                                    | 1×4                                    | 58                  | 117.5                 | 55.3                | 122.6                 | 1258                | 1307                |
| SDAN 5030VA-4 | 50                              | 30         | 51.75                                | 45.2                                    | 1×4                                    | 58.4                | 118.9                 | 55.7                | 124.5                 | 1269                | 1322                |
| SDAN 5040V-3  | 50                              | 40         | 51                                   | 44.4                                    | 1×3                                    | 43.9                | 86.5                  | 41.8                | 90.7                  | 934                 | 974                 |
| SDAN 5040VA-3 | 50                              | 40         | 51.75                                | 45.2                                    | 1×3                                    | 44.2                | 87.9                  | 42.1                | 92                    | 946                 | 985                 |

### Model number coding


**SDAN4510V X -5 TT G0 +830L C5**

Model No.      Number of turns      Overall screw shaft length (in mm)      Accuracy symbol (\*2)

Full-ball type code (No code for caged ball type)

Contamination protection accessory symbol (\*1)      Symbol for clearance in the axial direction (G0 for all SDAN-V variations)

(\*1) See **A15-334**. (\*2) See **A15-12**.



Unit: mm

| Nut dimensions |                 |                |    |                |                |                  |                |                |                |                |                |                                    | Screw shaft inertial moment/mm <sup>3</sup> | Nut mass | Shaft mass        | Permissible rotational speed |                     |
|----------------|-----------------|----------------|----|----------------|----------------|------------------|----------------|----------------|----------------|----------------|----------------|------------------------------------|---|----------|-------------------|------------------------------|---------------------|
| Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | B <sub>2</sub> | Spacer thickness | B <sub>3</sub> | B <sub>4</sub> | PCD            | d <sub>1</sub> | T <sub>w</sub> | Lubrication hole                   |   |          |                   | SDAN-V (Caged Ball)          | SDAN-VX (Full-Ball) |
| D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | B <sub>3</sub>   | B <sub>4</sub> | PCD            | d <sub>1</sub> | T <sub>w</sub> | A              | kg·m <sup>2</sup> /mm <sup>3</sup> | kg  | kg/m     | min <sup>-1</sup> | min <sup>-1</sup>            |                     |
| 70             | 105             | 135            | 16 | 45             | 20             | 11               | 62             | 88             | 11             | 80             | M8×1           | 3.16×10 <sup>-6</sup>              | 2.47  | 11.16    | 3470              | 2820                         |                     |
| 75             | 110             | 135            | 16 | 45             | 20             | 11               | 62             | 93             | 11             | 85             | M8×1           | 3.16×10 <sup>-6</sup>              | 3.05  | 11.4     | 3420              | 2780                         |                     |
| 70             | 105             | 158            | 16 | 54             | 20             | 15.6             | 72             | 88             | 11             | 80             | M8×1           | 3.16×10 <sup>-6</sup>              | 2.84  | 11.38    | 3470              | 2820                         |                     |
| 75             | 110             | 158            | 16 | 54             | 20             | 15.6             | 72             | 93             | 11             | 85             | M8×1           | 3.16×10 <sup>-6</sup>              | 3.5   | 11.58    | 3420              | 2780                         |                     |
| 70             | 105             | 189            | 16 | 73             | 20             | 8.8              | 90             | 88             | 11             | 80             | M8×1           | 3.16×10 <sup>-6</sup>              | 3.36  | 11.67    | 3470              | 2820                         |                     |
| 75             | 110             | 189            | 16 | 73             | 20             | 8.8              | 90             | 93             | 11             | 85             | M8×1           | 3.16×10 <sup>-6</sup>              | 4.15  | 11.82    | 3420              | 2780                         |                     |
| 70             | 105             | 232            | 16 | 92             | 20             | 14               | 109            | 88             | 11             | 80             | M8×1           | 3.16×10 <sup>-6</sup>              | 4.03  | 11.84    | 3470              | 2820                         |                     |
| 75             | 110             | 232            | 16 | 92             | 20             | 14               | 109            | 93             | 11             | 85             | M8×1           | 3.16×10 <sup>-6</sup>              | 5   | 11.96    | 3420              | 2780                         |                     |
| 75             | 110             | 135            | 16 | 45             | 20             | 11               | 62             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup>              | 2.69  | 13.93    | 3130              | 2540                         |                     |
| 82             | 118             | 135            | 16 | 45             | 20             | 11               | 62             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup>              | 3.58  | 14.2     | 3090              | 2510                         |                     |
| 75             | 110             | 158            | 16 | 54             | 20             | 15.6             | 72             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup>              | 3.08  | 14.19    | 3130              | 2540                         |                     |
| 82             | 118             | 158            | 16 | 54             | 20             | 15.6             | 72             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup>              | 4.12  | 14.41    | 3090              | 2510                         |                     |
| 75             | 110             | 189            | 16 | 73             | 20             | 8.8              | 90             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup>              | 3.65  | 14.5     | 3130              | 2540                         |                     |
| 82             | 118             | 189            | 16 | 73             | 20             | 8.8              | 90             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup>              | 4.89  | 14.67    | 3090              | 2510                         |                     |
| 75             | 110             | 232            | 16 | 92             | 20             | 14               | 109            | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup>              | 4.39  | 14.69    | 3130              | 2540                         |                     |
| 82             | 118             | 232            | 16 | 92             | 20             | 14               | 109            | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup>              | 5.89  | 14.83    | 3090              | 2510                         |                     |
| 75             | 110             | 235            | 16 | 90             | 20             | 20.5             | 108            | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup>              | 4.41  | 14.82    | 3130              | 2540                         |                     |
| 82             | 118             | 235            | 16 | 90             | 20             | 20.5             | 108            | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup>              | 5.93  | 14.95    | 3090              | 2510                         |                     |
| 75             | 110             | 265            | 16 | 110            | 20             | 10.7             | 128            | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup>              | 4.96  | 14.92    | 3130              | 2540                         |                     |
| 82             | 118             | 265            | 16 | 110            | 20             | 10.6             | 128            | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup>              | 6.67  | 15.03    | 3090              | 2510                         |                     |
| 75             | 110             | 268            | 16 | 108            | 20             | 17.5             | 126            | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup>              | 4.98  | 15.06    | 3130              | 2540                         |                     |
| 82             | 118             | 269            | 16 | 108            | 20             | 17.3             | 126            | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup>              | 6.72  | 15.13    | 3090              | 2510                         |                     |

Axial Clearance

Unit: mm

|                  |           |
|------------------|-----------|
| Clearance symbol | G0        |
| Axial clearance  | 0 or less |

Note) L<sub>1</sub>, B<sub>1</sub>, and B<sub>2</sub> dimensions are those when a thin film seal (TT) has been installed. Dimensions without the seal are shown in parentheses. It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.

Note: The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 3 times the applied preload, which itself is 10% of the basic axial dynamic load rating (Ca). These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the rigidity value in the table as the actual value. If the axial load (Fa<sub>0</sub>) is not 0.1 Ca, the rigidity value (K<sub>N</sub>) is obtained from the following formula.


$$K_N = K \left( \frac{Fa_0}{0.1Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# SDAN-V

## With Preload/No Preload

|          |                     |        |
|----------|---------------------|--------|
| DN value | SDAN-VX (Full-Ball) | 130000 |
|----------|---------------------|--------|



| Model No.        | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Screw shaft thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating   |                       |                     |                       | Rigidity            |                     |
|------------------|---------------------------------|------------|--------------------------------------|---|--|---------------------|-----------------------|---------------------|-----------------------|---------------------|---------------------|
|                  |                                 |            |                                      |   |  | SDAN-V (Caged Ball) |                       | SDAN-VX (Full-Ball) |                       | SDAN-V (Caged Ball) | SDAN-VX (Full-Ball) |
|                  |                                 |            |                                      |   |  | Ca<br>kN            | C <sub>0a</sub><br>kN | Ca<br>kN            | C <sub>0a</sub><br>kN | K<br>N/μm           | K<br>N/μm           |
| * SDAN 5510VX-4  | 55                              | 10         | 56                                   | 49.4                                    | 1×4                                    | —                   | —                     | 58.2                | 141.6                 | —                   | 1400                |
| * SDAN 5510VAX-4 | 55                              | 10         | 56.75                                | 50.2                                    | 1×4                                    | —                   | —                     | 58.5                | 143.6                 | —                   | 1416                |
| * SDAN 5512VX-4  | 55                              | 12         | 56                                   | 49.4                                    | 1×4                                    | —                   | —                     | 58.1                | 141.7                 | —                   | 1401                |
| * SDAN 5512VAX-4 | 55                              | 12         | 56.75                                | 50.2                                    | 1×4                                    | —                   | —                     | 58.5                | 143.7                 | —                   | 1416                |
| * SDAN 5516VX-4  | 55                              | 16         | 56                                   | 49.4                                    | 1×4                                    | —                   | —                     | 58.1                | 142                   | —                   | 1402                |
| * SDAN 5516VAX-4 | 55                              | 16         | 56.75                                | 50.2                                    | 1×4                                    | —                   | —                     | 58.4                | 144                   | —                   | 1417                |
| * SDAN 5520VX-4  | 55                              | 20         | 56                                   | 49.4                                    | 1×4                                    | —                   | —                     | 58                  | 142.3                 | —                   | 1403                |
| * SDAN 5520VAX-4 | 55                              | 20         | 56.75                                | 50.2                                    | 1×4                                    | —                   | —                     | 58.3                | 144.3                 | —                   | 1419                |
| * SDAN 6310VX-4  | 63                              | 10         | 64                                   | 57.4                                    | 1×4                                    | —                   | —                     | 61.6                | 162.7                 | —                   | 1560                |
| * SDAN 6312VX-4  | 63                              | 12         | 65                                   | 57.6                                    | 1×4                                    | —                   | —                     | 72.9                | 185.2                 | —                   | 1603                |
| * SDAN 6316VX-4  | 63                              | 16         | 65                                   | 57.6                                    | 1×4                                    | —                   | —                     | 72.8                | 185.5                 | —                   | 1604                |
| * SDAN 6320VX-4  | 63                              | 20         | 65                                   | 57.6                                    | 1×4                                    | —                   | —                     | 72.7                | 185.8                 | —                   | 1606                |
| * SDAN 6325VX-4  | 63                              | 25         | 65                                   | 57.6                                    | 1×4                                    | —                   | —                     | 72.6                | 186.3                 | —                   | 1607                |
| * SDAN 6330VX-4  | 63                              | 30         | 65                                   | 57.6                                    | 1×4                                    | —                   | —                     | 72.5                | 186.9                 | —                   | 1610                |
| * SDAN 6340VX-3  | 63                              | 40         | 65                                   | 57.6                                    | 1×3                                    | —                   | —                     | 55                  | 129.2                 | —                   | 1197                |

Note) Models marked with an asterisk (\*) in the specification table are only compatible with Model SDAN-VX (full-ball type).


### Model number coding

**SDAN5510V X -4 TT G0 +830L C5**

|  |   |  |                      |
|--|---|--|----------------------|
| Model No.<br>Full-ball type code (No code for caged ball type) | Number of turns<br>Contamination protection accessory symbol (*1) | Overall screw shaft length (in mm)<br>Symbol for clearance in the axial direction (G0 for all SDAN-V variations) | Accuracy symbol (*2) |
|--|---|--|----------------------|

(\*1) See [A15-334](#). (\*2) See [A15-12](#).





Unit: mm

| Nut dimensions |                 |                |    |                |                |                  |                |                |                |                |                |                       | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass | Shaft mass        | Permissible rotational speed |    |
|----------------|-----------------|----------------|----|----------------|----------------|------------------|----------------|----------------|----------------|----------------|----------------|-----------------------|---|----------|-------------------|------------------------------|----|
| Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | B <sub>2</sub> | Spacer thickness | B <sub>3</sub> | B <sub>4</sub> | PCD            | d <sub>1</sub> | T <sub>w</sub> | Lubrication hole      |   |          |                   | kg·m <sup>2</sup> /mm        | kg |
| D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | B <sub>3</sub>   | B <sub>4</sub> | PCD            | d <sub>1</sub> | T <sub>w</sub> | A              | kg·m <sup>2</sup> /mm | kg  | kg/m     | min <sup>-1</sup> | min <sup>-1</sup>            |    |
| 80             | 118             | 115            | 18 | 33             | 20             | 11               | 52             | 100            | 11             | 92             | M8×1           | 7.05×10 <sup>-6</sup> | 2.54  | 17.02    | —                 | 2630                         |    |
| 82             | 120             | 115            | 18 | 33             | 20             | 11               | 52             | 102            | 11             | 94             | M8×1           | 7.05×10 <sup>-6</sup> | 2.73  | 17.32    | —                 | 2590                         |    |
| 80             | 118             | 134            | 18 | 40             | 20             | 15.6             | 60             | 100            | 11             | 92             | M8×1           | 7.05×10 <sup>-6</sup> | 2.89  | 17.3     | —                 | 2630                         |    |
| 82             | 120             | 134            | 18 | 40             | 20             | 15.6             | 60             | 102            | 11             | 94             | M8×1           | 7.05×10 <sup>-6</sup> | 3.11  | 17.55    | —                 | 2590                         |    |
| 80             | 118             | 157            | 18 | 55             | 20             | 8.8              | 74             | 100            | 11             | 92             | M8×1           | 7.05×10 <sup>-6</sup> | 3.35  | 17.65    | —                 | 2630                         |    |
| 82             | 120             | 157            | 18 | 55             | 20             | 8.8              | 74             | 102            | 11             | 94             | M8×1           | 7.05×10 <sup>-6</sup> | 3.6   | 17.84    | —                 | 2590                         |    |
| 80             | 118             | 192            | 18 | 70             | 20             | 14               | 89             | 100            | 11             | 92             | M8×1           | 7.05×10 <sup>-6</sup> | 4   | 17.86    | —                 | 2630                         |    |
| 82             | 120             | 192            | 18 | 70             | 20             | 14               | 89             | 102            | 11             | 94             | M8×1           | 7.05×10 <sup>-6</sup> | 4.3   | 18.01    | —                 | 2590                         |    |
| 90             | 125             | 115            | 18 | 33             | 20             | 11               | 52             | 108            | 11             | 95             | M8×1           | 1.21×10 <sup>-5</sup> | 2.97  | 22.61    | —                 | 2260                         |    |
| 95             | 135             | 135            | 20 | 39             | 25             | 14.6             | 61             | 115            | 13.5           | 100            | M8×1           | 1.21×10 <sup>-5</sup> | 4.18  | 22.89    | —                 | 2250                         |    |
| 95             | 135             | 158            | 20 | 54             | 25             | 7.8              | 75             | 115            | 13.5           | 100            | M8×1           | 1.21×10 <sup>-5</sup> | 4.84  | 23.3     | —                 | 2250                         |    |
| 95             | 135             | 193            | 20 | 69             | 25             | 13               | 90             | 115            | 13.5           | 100            | M8×1           | 1.21×10 <sup>-5</sup> | 5.8   | 23.55    | —                 | 2250                         |    |
| 95             | 135             | 237            | 20 | 88             | 25             | 19.3             | 109            | 115            | 13.5           | 100            | M8×1           | 1.21×10 <sup>-5</sup> | 7.02  | 23.74    | —                 | 2250                         |    |
| 95             | 135             | 266            | 20 | 107            | 25             | 10.2             | 128            | 115            | 13.5           | 100            | M8×1           | 1.21×10 <sup>-5</sup> | 7.84  | 23.87    | —                 | 2250                         |    |
| 95             | 135             | 269            | 20 | 105            | 25             | 17.2             | 126            | 115            | 13.5           | 100            | M8×1           | 1.21×10 <sup>-5</sup> | 7.87  | 24.04    | —                 | 2250                         |    |

## Axial Clearance

Unit: mm

| Clearance symbol | G0        |
|------------------|-----------|
| Axial clearance  | 0 or less |

Note) L<sub>1</sub>, B<sub>1</sub>, and B<sub>2</sub> dimensions are those when a thin film seal (TT) has been installed. Dimensions without the seal are shown in parentheses. It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.


Note: The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 3 times the applied preload, which itself is 10% of the basic axial dynamic load rating (Ca). These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the rigidity value in the table as the actual value. If the axial load (Fa) is not 0.1 Ca, the rigidity value (K<sub>v</sub>) is obtained from the following formula.

$$K_v = K \left( \frac{F_{a0}}{0.1Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# SDA-V/SDA-VZ With Preload/No Preload

|          |                    |        |
|----------|--------------------|--------|
| DN value | SDA-V (Caged Ball) | 160000 |
|          | SDA-VZ (Full-Ball) | 100000 |



SDA1004VZ/  
1005VZ/1010VZ

SDA1205VZ/1210VZ

SDA1220VZ/1230VZ

| Model No.      | Screw shaft outer diameter | Lead | Ball center-to-center diameter | Screw shaft thread minor diameter | No. of loaded circuits | Basic load rating  |                 |                    |                 | Rigidity           |                    |
|----------------|----------------------------|------|--------------------------------|-----------------------------------|------------------------|--------------------|-----------------|--------------------|-----------------|--------------------|--------------------|
|                |                            |      |                                |                                   |                        | SDA-V (Caged Ball) |                 | SDA-VZ (Full-Ball) |                 | SDA-V (Caged Ball) | SDA-VZ (Full-Ball) |
|                |                            |      |                                |                                   |                        | Ca                 | C <sub>0a</sub> | Ca                 | C <sub>0a</sub> | K                  | K                  |
|                | d                          | Ph   | dp                             | dc                                | Rows X turns           | kN                 | kN              | kN                 | kN              | N/μm               | N/μm               |
| * SDA 1004VZ-4 | 10                         | 4    | 10.4                           | 8.77                              | 1×4                    | —                  | —               | 3.54               | 5.42            | —                  | 143                |
| * SDA 1005VZ-4 | 10                         | 5    | 10.4                           | 8.77                              | 1×4                    | —                  | —               | 3.53               | 5.44            | —                  | 143                |
| * SDA 1010VZ-3 | 10                         | 10   | 10.4                           | 8.77                              | 1×3                    | —                  | —               | 2.63               | 3.86            | —                  | 108                |
| * SDA 1205VZ-3 | 12                         | 5    | 12.5                           | 10.1                              | 1×3                    | —                  | —               | 4.99               | 7.02            | —                  | 128                |
| * SDA 1210VZ-2 | 12                         | 10   | 12.5                           | 10.1                              | 1×2                    | —                  | —               | 3.31               | 4.25            | —                  | 83                 |
| * SDA 1220VZ-2 | 12                         | 20   | 12.5                           | 10.1                              | 1×2                    | —                  | —               | 3.13               | 4.63            | —                  | 87                 |
| * SDA 1230VZ-2 | 12                         | 30   | 12.5                           | 10.1                              | 1×2                    | —                  | —               | 2.92               | 4.14            | —                  | 91                 |
| SDA 1405V-4    | 14                         | 5    | 14.5                           | 12.1                              | 1×4                    | 7.4                | 10.1            | 7.1                | 11.3            | 178                | 196                |
| SDA 1505V-3    | 15                         | 5    | 15.5                           | 13.1                              | 1×3                    | 5.9                | 7.9             | 5.6                | 8.8             | 140                | 153                |
| SDA 1510V-3    | 15                         | 10   | 15.5                           | 13.1                              | 1×3                    | 5.8                | 7.6             | 5.5                | 8.4             | 141                | 154                |
| SDA 1520V-4    | 15                         | 20   | 15.5                           | 13.1                              | 2×2                    | 6.8                | 10.1            | 6.5                | 11.2            | 181                | 198                |
| SDA 1530V-4    | 15                         | 30   | 15.5                           | 13.1                              | 2×2                    | 6.5                | 8.8             | 6.2                | 9.7             | 188                | 205                |
| SDA 1605V-3    | 16                         | 5    | 16.5                           | 14.1                              | 1×3                    | 6                  | 8.4             | 5.8                | 9.4             | 147                | 162                |
| SDA 1610V-3    | 16                         | 10   | 16.5                           | 14.1                              | 1×3                    | 6                  | 8.1             | 5.7                | 9               | 148                | 163                |
| SDA 1616V-3    | 16                         | 16   | 16.5                           | 14.1                              | 1×3                    | 5.9                | 8.4             | 5.6                | 9.2             | 151                | 165                |


Note) Models marked with an asterisk (\*) in the dimension table are only compatible with Model SDA-VZ (full-ball type).

## Model number coding

**SDA1510V Z -3 TT G0 +600L C5**

|   |  |  |                      |
|---|--|--|----------------------|
| Model No.   | Number of turns                                | Overall screw shaft length (in mm)   | Accuracy symbol (*3) |
| Full-ball type code (No code for caged ball type) | Contamination protection accessory symbol (*1) | Axial direction clearance code (*2)<br>(Preloaded products: GO Clearance,<br>Non-preloaded products: GT Clearance) |                      |

(\*1) See **A15-334**. (\*2) See **A15-19**. (\*3) See **A15-12**.



SDA14V to 16V

Unit: mm

| Nut dimensions |                 |                |    |                |                |     |                |                |                  | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass | Shaft mass | Permissible rotational speed |                   |
|----------------|-----------------|----------------|----|----------------|----------------|-----|----------------|----------------|------------------|---|----------|------------|------------------------------|-------------------|
| Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | Lubrication hole |   |          |            | kg·m <sup>2</sup> /mm        | kg                |
| D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | A                | kg·m <sup>2</sup> /mm                       | kg       | kg/m       | min <sup>-1</sup>            | min <sup>-1</sup> |
| 19             | 36              | 24             | 6  | 16             | —              | 28  | 4.5            | 23             | φ 3              | 7.71 × 10 <sup>-9</sup>                     | 0.047    | 0.577      | —                            | 5000              |
| 19             | 36              | 28             | 6  | 20             | —              | 28  | 4.5            | 23             | φ 3              | 7.71 × 10 <sup>-9</sup>                     | 0.052    | 0.585      | —                            | 5000              |
| 19             | 36              | 37             | 6  | 29             | —              | 28  | 4.5            | 23             | φ 3              | 7.71 × 10 <sup>-9</sup>                     | 0.066    | 0.6        | —                            | 5000              |
| 24             | 40              | 25             | 8  | 17             | —              | 32  | 4.5            | 26             | φ 3              | 1.60 × 10 <sup>-8</sup>                     | 0.073    | 0.796      | —                            | 5000              |
| 24             | 40              | 29             | 8  | 21             | —              | 32  | 4.5            | 26             | φ 3              | 1.60 × 10 <sup>-8</sup>                     | 0.082    | 0.841      | —                            | 5000              |
| 24             | 40              | 47             | 8  | 39             | 20             | 32  | 4.5            | 26             | φ 3              | 1.60 × 10 <sup>-8</sup>                     | 0.126    | 0.863      | —                            | 5000              |
| 24             | 40              | 65             | 8  | 57             | 20             | 32  | 4.5            | 26             | φ 3              | 1.60 × 10 <sup>-8</sup>                     | 0.172    | 0.869      | —                            | 5000              |
| 26             | 48              | 30             | 10 | 20             | 10             | 38  | 5.5            | 40             | M6               | 2.96 × 10 <sup>-8</sup>                     | 0.14     | 1.1        | 5000                         | 5000              |
| 28             | 48              | 25             | 10 | 15             | 12.5           | 38  | 5.5            | 40             | M6               | 3.90 × 10 <sup>-8</sup>                     | 0.13     | 1.27       | 5000                         | 5000              |
| 28             | 48              | 38             | 10 | 28             | 25.5           | 38  | 5.5            | 40             | M6               | 3.90 × 10 <sup>-8</sup>                     | 0.17     | 1.33       | 5000                         | 5000              |
| 28             | 48              | 46             | 10 | 36             | 20             | 38  | 5.5            | 40             | M6               | 3.90 × 10 <sup>-8</sup>                     | 0.19     | 1.33       | 5000                         | 5000              |
| 28             | 48              | 65             | 10 | 55             | 20             | 38  | 5.5            | 40             | M6               | 3.90 × 10 <sup>-8</sup>                     | 0.25     | 1.34       | 5000                         | 5000              |
| 28             | 48              | 25             | 10 | 15             | 12.5           | 38  | 5.5            | 40             | M6               | 5.05 × 10 <sup>-8</sup>                     | 0.13     | 1.46       | 5000                         | 5000              |
| 28             | 48              | 39             | 10 | 29             | 26.5           | 38  | 5.5            | 40             | M6               | 5.05 × 10 <sup>-8</sup>                     | 0.16     | 1.52       | 5000                         | 5000              |
| 28             | 48              | 56             | 10 | 46             | 20             | 38  | 5.5            | 40             | M6               | 5.05 × 10 <sup>-8</sup>                     | 0.21     | 1.54       | 5000                         | 5000              |

Axial Clearance

Unit: mm

| Clearance symbol | G0        | GT         |
|------------------|-----------|------------|
| Axial clearance  | 0 or less | 0 to 0.005 |

Note) See **A15-19** for the axial direction clearance for models SDA1205VZ to SDA1230VZ.

The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.

The rigidity values (K) in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the rigidity value (K) in the table as the actual value.


If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>n</sub>) is obtained from the following equation.

$$K_n = K \left( \frac{Fa}{0.3Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# SDA-V/SDA-VZ With Preload/No Preload

|          |                    |        |
|----------|--------------------|--------|
| DN value | SDA-V (Caged Ball) | 160000 |
|          | SDA-VZ (Full-Ball) | 100000 |




| Model No.   | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Screw shaft thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating  |                       |                    |                       | Rigidity           |                    |
|-------------|---------------------------------|------------|--------------------------------------|---|--|--------------------|-----------------------|--------------------|-----------------------|--------------------|--------------------|
|             |                                 |            |                                      |   |  | SDA-V (Caged Ball) |                       | SDA-VZ (Full-Ball) |                       | SDA-V (Caged Ball) | SDA-VZ (Full-Ball) |
|             |                                 |            |                                      |   |  | Ca<br>kN           | C <sub>0a</sub><br>kN | Ca<br>kN           | C <sub>0a</sub><br>kN | K<br>N/μm          | K<br>N/μm          |
| SDA 2004V-4 | 20                              | 4          | 20.5                                 | 18.1                                    | 1×4                                    | 8.8                | 14.7                  | 8.3                | 16.2                  | 239                | 260                |
| SDA 2005V-3 | 20                              | 5          | 20.75                                | 17.1                                    | 1×3                                    | 11.7               | 17.7                  | 11.1               | 18.9                  | 200                | 213                |
| SDA 2006V-4 | 20                              | 6          | 20.75                                | 17.1                                    | 1×4                                    | 15.3               | 24.1                  | 14.5               | 25.9                  | 269                | 287                |
| SDA 2010V-3 | 20                              | 10         | 20.75                                | 17.1                                    | 1×3                                    | 11.6               | 17.7                  | 11                 | 19                    | 200                | 213                |
| SDA 2010V-6 | 20                              | 10         | 20.75                                | 17.1                                    | 2×3                                    | 21                 | 35.3                  | 20                 | 38.1                  | 386                | 413                |
| SDA 2020V-3 | 20                              | 20         | 20.75                                | 17.1                                    | 1×3                                    | 11.4               | 17.2                  | 10.8               | 18.5                  | 203                | 217                |
| SDA 2020V-6 | 20                              | 20         | 20.75                                | 17.1                                    | 2×3                                    | 20.6               | 34.5                  | 19.6               | 37                    | 394                | 420                |
| SDA 2030V-2 | 20                              | 30         | 20.75                                | 17.1                                    | 1×2                                    | 7.4                | 11.5                  | 7                  | 12.3                  | 135                | 143                |
| SDA 2040V-2 | 20                              | 40         | 20.75                                | 17.1                                    | 1×2                                    | 7.1                | 9.7                   | 6.8                | 10.4                  | 137                | 147                |
| SDA 2505V-3 | 25                              | 5          | 25.75                                | 22.1                                    | 1×3                                    | 12.9               | 22                    | 12.3               | 23.7                  | 237                | 254                |
| SDA 2510V-3 | 25                              | 10         | 25.75                                | 22.1                                    | 1×3                                    | 12.8               | 22                    | 12.2               | 23.8                  | 237                | 254                |
| SDA 2520V-3 | 25                              | 20         | 25.75                                | 22.1                                    | 1×3                                    | 12.7               | 21.3                  | 12.1               | 22.9                  | 241                | 257                |
| SDA 2525V-3 | 25                              | 25         | 25.75                                | 22.1                                    | 1×3                                    | 12.5               | 21.6                  | 11.9               | 23.3                  | 243                | 259                |
| SDA 2530V-2 | 25                              | 30         | 25.75                                | 22.1                                    | 1×2                                    | 8.3                | 13.9                  | 7.9                | 14.9                  | 158                | 168                |
| SDA 2530V-4 | 25                              | 30         | 25.75                                | 22.1                                    | 2×2                                    | 15.1               | 27.8                  | 14.4               | 29.8                  | 305                | 325                |
| SDA 2550V-2 | 25                              | 50         | 25.75                                | 22.1                                    | 1×2                                    | 7.8                | 12.1                  | 7.5                | 13.1                  | 163                | 176                |

## Model number coding

**SDA2005V Z -3 TT G0 +830L C5**

|  |   |  |                      |
|--|---|--|----------------------|
| Model No.<br>Full-ball type code (No code for caged ball type) | Number of turns<br>Contamination protection accessory symbol (*1) | Overall screw shaft length (in mm)<br>Axial direction clearance code (*2)<br>(Preloaded products: GO Clearance,<br>Non-preloaded products: GT Clearance) | Accuracy symbol (*3) |
|--|---|--|----------------------|

(\*1) See **A15-334**. (\*2) See **A15-19**. (\*3) See **A15-12**.



Unit: mm

| Nut dimensions |                 |                |    |                |                |     |                |                |    |                  | Screw shaft inertial moment/mm | Nut mass | Shaft mass | Permissible rotational speed |                   |      |                    |                    |
|----------------|-----------------|----------------|----|----------------|----------------|-----|----------------|----------------|----|------------------|--------------------------------|----------|------------|------------------------------|-------------------|------|--------------------|--------------------|
| Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | A  | Lubrication hole |                                |          |            | kg·m <sup>2</sup> /mm        | kg                | kg/m | SDA-V (Caged Ball) | SDA-VZ (Full-Ball) |
|                |                 |                |    |                |                |     |                |                |    |                  |                                |          |            |                              |                   |      | min <sup>-1</sup>  | min <sup>-1</sup>  |
| D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | A  |                  | kg·m <sup>2</sup> /mm          | kg       | kg/m       | min <sup>-1</sup>            | min <sup>-1</sup> |      |                    |                    |
| 32             | 58              | 27             | 10 | 17             | 14.5           | 47  | 6.6            | 44             | M6 |                  | 1.23 × 10 <sup>-7</sup>        | 0.17     | 2.27       | 5000                         | 4870              |      |                    |                    |
| 36             | 58              | 27             | 10 | 17             | 13.5           | 47  | 6.6            | 44             | M6 |                  | 1.23 × 10 <sup>-7</sup>        | 0.18     | 2.21       | 5000                         | 4810              |      |                    |                    |
| 36             | 58              | 35             | 10 | 25             | 22.2           | 47  | 6.6            | 44             | M6 |                  | 1.23 × 10 <sup>-7</sup>        | 0.22     | 2.23       | 5000                         | 4810              |      |                    |                    |
| 36             | 58              | 40             | 10 | 30             | 27             | 47  | 6.6            | 44             | M6 |                  | 1.23 × 10 <sup>-7</sup>        | 0.25     | 2.34       | 5000                         | 4810              |      |                    |                    |
| 36             | 58              | 40             | 10 | 30             | 27             | 47  | 6.6            | 44             | M6 |                  | 1.23 × 10 <sup>-7</sup>        | 0.25     | 2.18       | 5000                         | 4810              |      |                    |                    |
| 36             | 58              | 67             | 10 | 57             | 20             | 47  | 6.6            | 44             | M6 |                  | 1.23 × 10 <sup>-7</sup>        | 0.39     | 2.4        | 5000                         | 4810              |      |                    |                    |
| 36             | 58              | 67             | 10 | 57             | 20             | 47  | 6.6            | 44             | M6 |                  | 1.23 × 10 <sup>-7</sup>        | 0.38     | 2.31       | 5000                         | 4810              |      |                    |                    |
| 36             | 58              | 66             | 10 | 56             | 20             | 47  | 6.6            | 44             | M6 |                  | 1.23 × 10 <sup>-7</sup>        | 0.38     | 2.42       | 5000                         | 4810              |      |                    |                    |
| 36             | 58              | 84             | 10 | 74             | 20             | 47  | 6.6            | 44             | M6 |                  | 1.23 × 10 <sup>-7</sup>        | 0.47     | 2.43       | 5000                         | 4810              |      |                    |                    |
| 40             | 62              | 27             | 10 | 17             | 13.5           | 51  | 6.6            | 48             | M6 |                  | 3.01 × 10 <sup>-7</sup>        | 0.2      | 3.53       | 5000                         | 3880              |      |                    |                    |
| 40             | 62              | 40             | 10 | 30             | 27             | 51  | 6.6            | 48             | M6 |                  | 3.01 × 10 <sup>-7</sup>        | 0.28     | 3.7        | 5000                         | 3880              |      |                    |                    |
| 40             | 62              | 67             | 10 | 57             | 20             | 51  | 6.6            | 48             | M6 |                  | 3.01 × 10 <sup>-7</sup>        | 0.42     | 3.78       | 5000                         | 3880              |      |                    |                    |
| 40             | 62              | 82             | 10 | 72             | 20             | 51  | 6.6            | 48             | M6 |                  | 3.01 × 10 <sup>-7</sup>        | 0.5      | 3.79       | 5000                         | 3880              |      |                    |                    |
| 40             | 62              | 66             | 10 | 56             | 20             | 51  | 6.6            | 48             | M6 |                  | 3.01 × 10 <sup>-7</sup>        | 0.41     | 3.8        | 5000                         | 3880              |      |                    |                    |
| 40             | 62              | 66             | 10 | 56             | 20             | 51  | 6.6            | 48             | M6 |                  | 3.01 × 10 <sup>-7</sup>        | 0.41     | 3.71       | 5000                         | 3880              |      |                    |                    |
| 40             | 62              | 102            | 10 | 92             | 20             | 51  | 6.6            | 48             | M6 |                  | 3.01 × 10 <sup>-7</sup>        | 0.61     | 3.83       | 5000                         | 3880              |      |                    |                    |

Axial Clearance

Unit: mm

| Clearance symbol | G0        | GT         |
|------------------|-----------|------------|
| Axial clearance  | 0 or less | 0 to 0.005 |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details. It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.

The rigidity values (K) in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the rigidity value (K) in the table as the actual value.


If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>n</sub>) is obtained from the following equation.

$$K_n = K \left( \frac{F_a}{0.3 C_a} \right)^3$$

K: Rigidity value in the dimensional table

# SDA-V/SDA-VZ With Preload/No Preload

|          |                    |        |
|----------|--------------------|--------|
| DN value | SDA-V (Caged Ball) | 160000 |
|          | SDA-VZ (Full-Ball) | 130000 |



SDA28V to 32VA


| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Screw shaft thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating  |                       |                    |                       | Rigidity           |                    |
|--------------|---------------------------------|------------|--------------------------------------|---|--|--------------------|-----------------------|--------------------|-----------------------|--------------------|--------------------|
|              |                                 |            |                                      |   |  | SDA-V (Caged Ball) |                       | SDA-VZ (Full-Ball) |                       | SDA-V (Caged Ball) | SDA-VZ (Full-Ball) |
|              |                                 |            |                                      |   |  | Ca<br>kN           | C <sub>0a</sub><br>kN | Ca<br>kN           | C <sub>0a</sub><br>kN | K<br>N/μm          | K<br>N/μm          |
| SDA 2806V-5  | 28                              | 6          | 29                                   | 24.9                                    | 1×5                                    | 29.6               | 54.5                  | 28.2               | 57.7                  | 462                | 487                |
| SDA 3110V-5  | 31                              | 10         | 32                                   | 25.4                                    | 1×5                                    | 57.1               | 94.7                  | 54.4               | 99.7                  | 529                | 554                |
| SDA 3112V-5  | 31                              | 12         | 32                                   | 25.4                                    | 1×5                                    | 57                 | 94.7                  | 54.3               | 99.9                  | 529                | 555                |
| SDA 3116V-5  | 31                              | 16         | 32                                   | 25.4                                    | 1×5                                    | 56.8               | 96                    | 54.1               | 100.5                 | 534                | 556                |
| SDA 3120V-5  | 31                              | 20         | 32                                   | 25.4                                    | 1×5                                    | 56.6               | 90.3                  | 53.9               | 95.1                  | 533                | 558                |
| SDA 3132V-2  | 31                              | 32         | 32                                   | 25.4                                    | 1×2                                    | 23.2               | 33.8                  | 22.1               | 35.4                  | 206                | 214                |
| SDA 3205V-4  | 32                              | 5          | 32.75                                | 29.1                                    | 1×4                                    | 18.8               | 38.5                  | 17.9               | 41.7                  | 388                | 416                |
| SDA 3206V-5  | 32                              | 6          | 33                                   | 28.9                                    | 1×5                                    | 31.4               | 62.4                  | 29.9               | 66.1                  | 513                | 541                |
| SDA 3208V-5  | 32                              | 8          | 33                                   | 28.9                                    | 1×5                                    | 31.4               | 62.4                  | 29.9               | 66.2                  | 513                | 541                |
| SDA 3210V-5  | 32                              | 10         | 33                                   | 28.9                                    | 1×5                                    | 31.3               | 62.9                  | 29.8               | 66.3                  | 517                | 541                |
| SDA 3210VA-5 | 32                              | 10         | 33                                   | 26.4                                    | 1×5                                    | 58.1               | 98.9                  | 55.3               | 103.1                 | 548                | 569                |
| SDA 3212VA-5 | 32                              | 12         | 33                                   | 26.4                                    | 1×5                                    | 58                 | 98.9                  | 55.3               | 103.3                 | 548                | 569                |
| SDA 3216VA-5 | 32                              | 16         | 33                                   | 26.4                                    | 1×5                                    | 57.8               | 98.9                  | 55.1               | 103.8                 | 547                | 571                |
| SDA 3220VA-5 | 32                              | 20         | 33                                   | 26.4                                    | 1×5                                    | 57.6               | 94.3                  | 54.9               | 98.2                  | 552                | 572                |
| SDA 3232VA-2 | 32                              | 32         | 33                                   | 26.4                                    | 1×2                                    | 23.6               | 35.2                  | 22.5               | 36.5                  | 213                | 220                |
| SDA 3610V-5  | 36                              | 10         | 37                                   | 30.4                                    | 1×5                                    | 61.7               | 110.6                 | 58.8               | 116.4                 | 598                | 626                |
| SDA 3612V-5  | 36                              | 12         | 37                                   | 30.4                                    | 1×5                                    | 61.7               | 110.6                 | 58.7               | 116.6                 | 598                | 627                |
| SDA 3616V-5  | 36                              | 16         | 37                                   | 30.4                                    | 1×5                                    | 61.5               | 111.9                 | 58.6               | 117.1                 | 603                | 628                |
| SDA 3620V-5  | 36                              | 20         | 37                                   | 30.4                                    | 1×5                                    | 61.3               | 105.2                 | 58.4               | 110.6                 | 602                | 629                |
| SDA 3636V-2  | 36                              | 36         | 37                                   | 30.4                                    | 1×2                                    | 25.1               | 39.3                  | 23.9               | 41.3                  | 232                | 242                |

## Model number coding

**SDA3610V Z -5 TT G0 +830L C5**

|   |                 |  |                      |
|---|-----------------|--|----------------------|
| Model No.   | Number of turns | Overall screw shaft length (in mm)   | Accuracy symbol (*3) |
| Full-ball type code (No code for caged ball type) |                 |  |                      |
| Contamination protection accessory symbol (*1)    |                 | Axial direction clearance code (*2)<br>(Preloaded products: GO Clearance,<br>Non-preloaded products: GT Clearance) |                      |

(\*1) See **A15-334**. (\*2) See **A15-19**. (\*3) See **A15-12**.



SDA36V

Unit: mm

| Nut dimensions |                 |                |    |                |                |     |                |                |                  |                       | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass | Shaft mass        | Permissible rotational speed |      |
|----------------|-----------------|----------------|----|----------------|----------------|-----|----------------|----------------|------------------|-----------------------|---|----------|-------------------|------------------------------|------|
| Outer diameter | Flange diameter | Overall length |    |                |                |     |                |                | Lubrication hole | kg·m <sup>2</sup> /mm |   |          |                   | kg                           | kg/m |
| D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | A                |                       |   |          | min <sup>-1</sup> | min <sup>-1</sup>            |      |
| 46             | 80              | 42             | 12 | 30             | 27             | 65  | 9              | 62             | M6               | $4.74 \times 10^{-7}$ | 0.49  | 4.37     | 5000              | 4480                         |      |
| 56             | 86              | 65             | 14 | 50             | 20             | 71  | 9              | 65             | M6               | $7.07 \times 10^{-7}$ | 0.96  | 5.02     | 5000              | 4060                         |      |
| 56             | 86              | 74             | 14 | 59             | 20             | 71  | 9              | 65             | M6               | $7.07 \times 10^{-7}$ | 1.08  | 5.17     | 5000              | 4060                         |      |
| 56             | 86              | 93             | 14 | 78             | 20             | 71  | 9              | 65             | M6               | $7.07 \times 10^{-7}$ | 1.31  | 5.36     | 5000              | 4060                         |      |
| 56             | 86              | 112            | 14 | 97             | 20             | 71  | 9              | 65             | M6               | $7.07 \times 10^{-7}$ | 1.54  | 5.47     | 5000              | 4060                         |      |
| 56             | 86              | 73             | 14 | 58             | 20             | 71  | 9              | 65             | M6               | $7.07 \times 10^{-7}$ | 1.04  | 5.63     | 5000              | 4060                         |      |
| 50             | 80              | 32             | 12 | 20             | 17             | 65  | 9              | 62             | M6               | $8.08 \times 10^{-7}$ | 0.41  | 5.89     | 4880              | 3960                         |      |
| 50             | 80              | 42             | 12 | 30             | 10             | 65  | 9              | 62             | M6               | $8.08 \times 10^{-7}$ | 0.48  | 5.73     | 4840              | 3930                         |      |
| 50             | 80              | 52             | 12 | 40             | 20             | 65  | 9              | 62             | M6               | $8.08 \times 10^{-7}$ | 0.56  | 5.87     | 4840              | 3930                         |      |
| 50             | 80              | 61             | 12 | 49             | 20             | 65  | 9              | 62             | M6               | $8.08 \times 10^{-7}$ | 0.64  | 6        | 4840              | 3930                         |      |
| 57             | 87              | 65             | 14 | 50             | 20             | 72  | 9              | 66             | M6               | $8.08 \times 10^{-7}$ | 0.98  | 5.38     | 4840              | 3930                         |      |
| 57             | 87              | 74             | 14 | 59             | 20             | 72  | 9              | 66             | M6               | $8.08 \times 10^{-7}$ | 1.1   | 5.54     | 4840              | 3930                         |      |
| 57             | 87              | 93             | 14 | 78             | 20             | 72  | 9              | 66             | M6               | $8.08 \times 10^{-7}$ | 1.34  | 5.73     | 4840              | 3930                         |      |
| 57             | 87              | 112            | 14 | 97             | 20             | 72  | 9              | 66             | M6               | $8.08 \times 10^{-7}$ | 1.58  | 5.85     | 4840              | 3930                         |      |
| 57             | 87              | 73             | 14 | 58             | 20             | 72  | 9              | 66             | M6               | $8.08 \times 10^{-7}$ | 1.07  | 6.01     | 4840              | 3930                         |      |
| 61             | 91              | 65             | 14 | 50             | 20             | 76  | 9              | 68             | M8×1             | $1.29 \times 10^{-6}$ | 1.06  | 6.93     | 4320              | 3510                         |      |
| 61             | 91              | 74             | 14 | 59             | 20             | 76  | 9              | 68             | M8×1             | $1.29 \times 10^{-6}$ | 1.19  | 7.11     | 4320              | 3510                         |      |
| 61             | 91              | 93             | 14 | 78             | 20             | 76  | 9              | 68             | M8×1             | $1.29 \times 10^{-6}$ | 1.45  | 7.34     | 4320              | 3510                         |      |
| 61             | 91              | 112            | 14 | 97             | 20             | 76  | 9              | 68             | M8×1             | $1.29 \times 10^{-6}$ | 1.7   | 7.47     | 4320              | 3510                         |      |
| 61             | 91              | 81             | 14 | 66             | 20             | 76  | 9              | 68             | M8×1             | $1.29 \times 10^{-6}$ | 1.24  | 7.69     | 4320              | 3510                         |      |

Axial Clearance

Unit: mm

| Clearance symbol | G0        | GT         |
|------------------|-----------|------------|
| Axial clearance  | 0 or less | 0 to 0.005 |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details. It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.

The rigidity values (K) in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the rigidity value (K) in the table as the actual value.


If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>n</sub>) is obtained from the following equation.

$$K_n = K \left( \frac{F_a}{0.3 C_a} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# SDA-V/SDA-VZ With Preload/No Preload

|          |                    |        |
|----------|--------------------|--------|
| DN value | SDA-V (Caged Ball) | 160000 |
|          | SDA-VZ (Full-Ball) | 130000 |



| Model No.      | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Screw shaft thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating  |                       |                    |                       | Rigidity           |                    |
|----------------|---------------------------------|------------|--------------------------------------|---|--|--------------------|-----------------------|--------------------|-----------------------|--------------------|--------------------|
|                |                                 |            |                                      |   |  | SDA-V (Caged Ball) |                       | SDA-VZ (Full-Ball) |                       | SDA-V (Caged Ball) | SDA-VZ (Full-Ball) |
|                |                                 |            |                                      |   |  | Ca<br>kN           | C <sub>0a</sub><br>kN | Ca<br>kN           | C <sub>0a</sub><br>kN | K<br>N/μm          | K<br>N/μm          |
| SDA 3810V-5    | 38                              | 10         | 39                                   | 32.4                                    | 1×5                                    | 63.4               | 117.7                 | 60.4               | 123.1                 | 629                | 654                |
| SDA 3812V-5    | 38                              | 12         | 39                                   | 32.4                                    | 1×5                                    | 63.4               | 117.7                 | 60.3               | 123.3                 | 628                | 655                |
| SDA 3815V-5    | 38                              | 15         | 39                                   | 32.4                                    | 1×5                                    | 63.2               | 117.7                 | 60.2               | 123.6                 | 627                | 655                |
| SDA 3816V-5    | 38                              | 16         | 39                                   | 32.4                                    | 1×5                                    | 63.2               | 117.7                 | 60.2               | 123.7                 | 627                | 656                |
| SDA 3820V-5    | 38                              | 20         | 39                                   | 32.4                                    | 1×5                                    | 63.0               | 111.9                 | 60                 | 116.9                 | 632                | 657                |
| SDA 3825V-4    | 38                              | 25         | 39                                   | 32.4                                    | 1×4                                    | 51.1               | 87.8                  | 48.6               | 92.7                  | 500                | 525                |
| SDA 3830V-3    | 38                              | 30         | 39                                   | 32.4                                    | 1×3                                    | 38.7               | 64.9                  | 36.9               | 68.2                  | 373                | 390                |
| SDA 3840V-2    | 38                              | 40         | 39                                   | 32.4                                    | 1×2                                    | 25.7               | 42                    | 24.4               | 43.9                  | 244                | 253                |
| * SDA 4008VZ-5 | 40                              | 8          | 41.25                                | 36.4                                    | 1×5                                    | —                  | —                     | 42.2               | 99.4                  | —                  | 663                |
| SDA 4010VA-5   | 40                              | 10         | 41.75                                | 35.2                                    | 1×5                                    | 65.6               | 126.4                 | 62.5               | 132.3                 | 664                | 692                |
| SDA 4012VA-5   | 40                              | 12         | 41.75                                | 35.2                                    | 1×5                                    | 65.5               | 126.4                 | 62.4               | 132.5                 | 664                | 692                |
| SDA 4015VA-5   | 40                              | 15         | 41.75                                | 35.2                                    | 1×5                                    | 65.4               | 126.4                 | 62.3               | 132.8                 | 663                | 693                |
| SDA 4016VA-5   | 40                              | 16         | 41.75                                | 35.2                                    | 1×5                                    | 65.4               | 126.4                 | 62.3               | 132.9                 | 663                | 693                |
| SDA 4020VA-5   | 40                              | 20         | 41.75                                | 35.2                                    | 1×5                                    | 65.2               | 127.7                 | 62.1               | 133.4                 | 668                | 695                |
| SDA 4020VA-10  | 40                              | 20         | 41.75                                | 35.2                                    | 2×5                                    | 118.4              | 254.1                 | 112.8              | 266.9                 | 1288               | 1345               |
| SDA 4025VA-4   | 40                              | 25         | 41.75                                | 35.2                                    | 1×4                                    | 52.9               | 94.5                  | 50.4               | 99.4                  | 531                | 555                |
| SDA 4030VA-3   | 40                              | 30         | 41.75                                | 35.2                                    | 1×3                                    | 40.1               | 70.3                  | 38.2               | 73.1                  | 398                | 412                |
| SDA 4030VA-6   | 40                              | 30         | 41.75                                | 35.2                                    | 2×3                                    | 72.8               | 139.2                 | 69.4               | 146.1                 | 764                | 798                |
| SDA 4040VA-2   | 40                              | 40         | 41.75                                | 35.2                                    | 1×2                                    | 26.6               | 44.7                  | 25.4               | 46.9                  | 256                | 267                |
| SDA 4040VA-4   | 40                              | 40         | 41.75                                | 35.2                                    | 2×2                                    | 48.4               | 89.4                  | 46.1               | 93.8                  | 496                | 518                |


(Note) Models marked with an asterisk (\*) in the dimension table are only compatible with Model SDA-VZ (full-ball type).

## Model number coding

|            |   |  |                 |  |                                    |                      |           |
|------------|---|--|-----------------|--|------------------------------------|----------------------|-----------|
| <b>SDA</b> | <b>3810V</b>                                      | <b>Z</b>                                       | <b>-5</b>       | <b>TT</b>  | <b>G0</b>                          | <b>+830L</b>         | <b>C5</b> |
| Model No.  | Full-ball type code (No code for caged ball type) | Contamination protection accessory symbol (*1) | Number of turns | Axial direction clearance code (*2)<br>(Preloaded products: GO Clearance,<br>Non-preloaded products: GT Clearance) | Overall screw shaft length (in mm) | Accuracy symbol (*3) |           |

(\*1) See **A15-334**. (\*2) See **A15-19**. (\*3) See **A15-12**.





Unit: mm

|    | Nut dimensions |                 |                |                |                |                |                |                |                |                       | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass | Shaft mass        | Permissible rotational speed |                       |    |      |                    |                    |
|----|----------------|-----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----------------------|---|----------|-------------------|------------------------------|-----------------------|----|------|--------------------|--------------------|
|    | Outer diameter | Flange diameter | Overall length | H              | B <sub>1</sub> | B <sub>2</sub> | PCD            | d <sub>1</sub> | T <sub>w</sub> | A                     |   |          |                   | Lubrication hole             | kg·m <sup>2</sup> /mm | kg | kg/m | SDA-V (Caged Ball) | SDA-VZ (Full-Ball) |
|    |                |                 |                |                |                |                |                |                |                |                       |   |          |                   |                              |                       |    |      | min <sup>-1</sup>  | min <sup>-1</sup>  |
| D  | D <sub>1</sub> | L <sub>1</sub>  | H              | B <sub>1</sub> | B <sub>2</sub> | PCD            | d <sub>1</sub> | T <sub>w</sub> | A              | kg·m <sup>2</sup> /mm | kg  | kg/m     | min <sup>-1</sup> | min <sup>-1</sup>            |                       |    |      |                    |                    |
| 63 | 93             | 65              | 14             | 50             | 20             | 78             | 9              | 70             | M8×1           | 1.60×10 <sup>-6</sup> | 1.1   | 7.79     | 4100              | 3330                         |                       |    |      |                    |                    |
| 63 | 93             | 74              | 14             | 59             | 20             | 78             | 9              | 70             | M8×1           | 1.60×10 <sup>-6</sup> | 1.23  | 7.97     | 4100              | 3330                         |                       |    |      |                    |                    |
| 63 | 93             | 88              | 14             | 73             | 20             | 78             | 9              | 70             | M8×1           | 1.60×10 <sup>-6</sup> | 1.41  | 8.09     | 4100              | 3330                         |                       |    |      |                    |                    |
| 63 | 93             | 93              | 14             | 78             | 20             | 78             | 9              | 70             | M8×1           | 1.60×10 <sup>-6</sup> | 1.5   | 8.21     | 4100              | 3330                         |                       |    |      |                    |                    |
| 63 | 93             | 112             | 14             | 97             | 20             | 78             | 9              | 70             | M8×1           | 1.60×10 <sup>-6</sup> | 1.77  | 8.35     | 4100              | 3330                         |                       |    |      |                    |                    |
| 63 | 93             | 111             | 14             | 96             | 20             | 78             | 9              | 70             | M8×1           | 1.60×10 <sup>-6</sup> | 1.73  | 8.45     | 4100              | 3330                         |                       |    |      |                    |                    |
| 63 | 93             | 100             | 14             | 85             | 20             | 78             | 9              | 70             | M8×1           | 1.60×10 <sup>-6</sup> | 1.56  | 8.53     | 4100              | 3330                         |                       |    |      |                    |                    |
| 63 | 93             | 87              | 14             | 72             | 20             | 78             | 9              | 70             | M8×1           | 1.60×10 <sup>-6</sup> | 1.38  | 8.62     | 4100              | 3330                         |                       |    |      |                    |                    |
| 61 | 91             | 55              | 14             | 41             | 20             | 76             | 9              | 68             | M8×1           | 1.97×10 <sup>-6</sup> | 0.81  | 9.08     | —                 | 3150                         |                       |    |      |                    |                    |
| 70 | 100            | 65              | 14             | 50             | 20             | 85             | 9              | 75             | M8×1           | 1.97×10 <sup>-6</sup> | 1.38  | 8.9      | 3830              | 3110                         |                       |    |      |                    |                    |
| 70 | 100            | 74              | 14             | 59             | 20             | 85             | 9              | 75             | M8×1           | 1.97×10 <sup>-6</sup> | 1.55  | 9.06     | 3830              | 3110                         |                       |    |      |                    |                    |
| 70 | 100            | 88              | 14             | 74             | 20             | 85             | 9              | 75             | M8×1           | 1.97×10 <sup>-6</sup> | 1.79  | 9.14     | 3830              | 3110                         |                       |    |      |                    |                    |
| 70 | 100            | 93              | 14             | 78             | 20             | 85             | 9              | 75             | M8×1           | 1.97×10 <sup>-6</sup> | 1.9   | 9.27     | 3830              | 3110                         |                       |    |      |                    |                    |
| 70 | 100            | 112             | 14             | 97             | 20             | 85             | 9              | 75             | M8×1           | 1.97×10 <sup>-6</sup> | 2.25  | 9.39     | 3830              | 3110                         |                       |    |      |                    |                    |
| 70 | 100            | 112             | 14             | 97             | 20             | 85             | 9              | 75             | M8×1           | 1.97×10 <sup>-6</sup> | 2.22  | 8.81     | 3830              | 3110                         |                       |    |      |                    |                    |
| 70 | 100            | 112             | 14             | 97             | 20             | 85             | 9              | 75             | M8×1           | 1.97×10 <sup>-6</sup> | 2.22  | 9.49     | 3830              | 3110                         |                       |    |      |                    |                    |
| 70 | 100            | 101             | 14             | 86             | 20             | 85             | 9              | 75             | M8×1           | 1.97×10 <sup>-6</sup> | 2.01  | 9.55     | 3830              | 3110                         |                       |    |      |                    |                    |
| 70 | 100            | 101             | 14             | 86             | 20             | 85             | 9              | 75             | M8×1           | 1.97×10 <sup>-6</sup> | 1.97  | 9.13     | 3830              | 3110                         |                       |    |      |                    |                    |
| 70 | 100            | 88              | 14             | 73             | 20             | 85             | 9              | 75             | M8×1           | 1.97×10 <sup>-6</sup> | 1.77  | 9.63     | 3830              | 3110                         |                       |    |      |                    |                    |
| 70 | 100            | 88              | 14             | 73             | 20             | 85             | 9              | 75             | M8×1           | 1.97×10 <sup>-6</sup> | 1.75  | 9.29     | 3830              | 3110                         |                       |    |      |                    |                    |

## Axial Clearance

Unit: mm

| Clearance symbol | G0        | GT         |
|------------------|-----------|------------|
| Axial clearance  | 0 or less | 0 to 0.005 |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details. It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.

The rigidity values (K) in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the rigidity value (K) in the table as the actual value.


If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>n</sub>) is obtained from the following equation.

$$K_n = K \left( \frac{F_a}{0.3 C_a} \right)^3$$

K: Rigidity value in the dimensional table

# SDA-V/SDA-VZ With Preload/No Preload


|          |                    |        |
|----------|--------------------|--------|
| DN value | SDA-V (Caged Ball) | 160000 |
|          | SDA-VZ (Full-Ball) | 130000 |



| Model No.     | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Screw shaft thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating  |                       |                    |                       | Rigidity           |                    |
|---------------|---------------------------------|------------|--------------------------------------|---|--|--------------------|-----------------------|--------------------|-----------------------|--------------------|--------------------|
|               |                                 |            |                                      |   |  | SDA-V (Caged Ball) |                       | SDA-VZ (Full-Ball) |                       | SDA-V (Caged Ball) | SDA-VZ (Full-Ball) |
|               |                                 |            |                                      |   |  | Ca<br>kN           | C <sub>0a</sub><br>kN | Ca<br>kN           | C <sub>0a</sub><br>kN | K<br>N/μm          | K<br>N/μm          |
| SDA 4510V-5   | 45                              | 10         | 46                                   | 39.4                                    | 1×5                                    | 68.7               | 139.4                 | 65.4               | 146.5                 | 717                | 749                |
| SDA 4510VA-5  | 45                              | 10         | 46.75                                | 40.2                                    | 1×5                                    | 69.2               | 142.2                 | 65.9               | 149                   | 729                | 759                |
| SDA 4512V-5   | 45                              | 12         | 46                                   | 39.4                                    | 1×5                                    | 68.6               | 139.4                 | 65.4               | 146.7                 | 717                | 750                |
| SDA 4512VA-5  | 45                              | 12         | 46.75                                | 40.2                                    | 1×5                                    | 69.2               | 142.2                 | 65.9               | 149.2                 | 728                | 760                |
| SDA 4516V-5   | 45                              | 16         | 46                                   | 39.4                                    | 1×5                                    | 68.5               | 140.7                 | 65.3               | 147                   | 722                | 751                |
| SDA 4516VA-5  | 45                              | 16         | 46.75                                | 40.2                                    | 1×5                                    | 69                 | 142.2                 | 65.8               | 149.5                 | 727                | 761                |
| SDA 4520V-5   | 45                              | 20         | 46                                   | 39.4                                    | 1×5                                    | 68.4               | 140.7                 | 65.1               | 147.5                 | 721                | 752                |
| SDA 4520VA-5  | 45                              | 20         | 46.75                                | 40.2                                    | 1×5                                    | 68.9               | 143.6                 | 65.6               | 150                   | 733                | 762                |
| SDA 4520VA-10 | 45                              | 20         | 46.75                                | 40.2                                    | 2×5                                    | 125.1              | 285.8                 | 119.1              | 300.1                 | 1413               | 1475               |
| SDA 4525V-4   | 45                              | 25         | 46                                   | 39.4                                    | 1×4                                    | 55.5               | 104                   | 52.8               | 109.8                 | 572                | 600                |
| SDA 4525VA-4  | 45                              | 25         | 46.75                                | 40.2                                    | 1×4                                    | 55.9               | 106.7                 | 53.2               | 111.6                 | 584                | 608                |
| SDA 4530V-4   | 45                              | 30         | 46                                   | 39.4                                    | 1×4                                    | 55.2               | 105.3                 | 52.6               | 110.5                 | 577                | 602                |
| SDA 4530VA-4  | 45                              | 30         | 46.75                                | 40.2                                    | 1×4                                    | 55.7               | 106.7                 | 53                 | 112.3                 | 583                | 610                |
| SDA 4540V-3   | 45                              | 40         | 46                                   | 39.4                                    | 1×3                                    | 41.7               | 78.3                  | 39.7               | 81.9                  | 431                | 449                |
| SDA 4540VA-3  | 45                              | 40         | 46.75                                | 40.2                                    | 1×3                                    | 42.1               | 79.7                  | 40.1               | 83.2                  | 438                | 455                |

## Model number coding

|   |   |                 |  |  |                                    |                      |
|---|---|-----------------|--|--|------------------------------------|----------------------|
| <b>SDA4510V</b>   | <b>Z</b>  | <b>-5</b>       | <b>TT</b>                                      | <b>G0</b>  | <b>+830L</b>                       | <b>C5</b>            |
| Model No.   | Full-ball type code (No code for caged ball type) | Number of turns | Contamination protection accessory symbol (*1) | Axial direction clearance code (*2)<br>(Preloaded products: GO Clearance,<br>Non-preloaded products: GT Clearance) | Overall screw shaft length (in mm) | Accuracy symbol (*3) |
| (*1) See <b>A15-334</b> . (*2) See <b>A15-19</b> . (*3) See <b>A15-12</b> . |   |                 |  |  |                                    |                      |



Unit: mm

|    | Nut dimensions    |                    |                   |     |                |                |     |                |                |                       | Screw shaft<br>inertial<br>moment/mm | Nut<br>mass | Shaft<br>mass | Permissible rotational speed |    |      |                       |                       |
|----|-------------------|--------------------|-------------------|-----|----------------|----------------|-----|----------------|----------------|-----------------------|--------------------------------------|-------------|---------------|------------------------------|----|------|-----------------------|-----------------------|
|    | Outer<br>diameter | Flange<br>diameter | Overall<br>length | H   | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>i</sub> | T <sub>w</sub> | Lubrication<br>hole   |                                      |             |               | kg·m <sup>2</sup> /mm        | kg | kg/m | SDA-V<br>(Caged Ball) | SDA-VZ<br>(Full-Ball) |
|    |                   |                    |                   |     |                |                |     |                |                |                       |                                      |             |               |                              |    |      | D                     | D <sub>1</sub>        |
| 70 | 105               | 65                 | 16                | 48  | 20             | 88             | 11  | 80             | M8×1           | 3.16×10 <sup>-6</sup> | 1.35                                 | 11.16       | 3470          | 2820                         |    |      |                       |                       |
| 75 | 110               | 65                 | 16                | 48  | 20             | 93             | 11  | 85             | M8×1           | 3.16×10 <sup>-6</sup> | 1.62                                 | 11.4        | 3420          | 2780                         |    |      |                       |                       |
| 70 | 105               | 74                 | 16                | 57  | 20             | 88             | 11  | 80             | M8×1           | 3.16×10 <sup>-6</sup> | 1.5                                  | 11.38       | 3470          | 2820                         |    |      |                       |                       |
| 75 | 110               | 74                 | 16                | 57  | 20             | 93             | 11  | 85             | M8×1           | 3.16×10 <sup>-6</sup> | 1.81                                 | 11.58       | 3420          | 2780                         |    |      |                       |                       |
| 70 | 105               | 93                 | 16                | 76  | 20             | 88             | 11  | 80             | M8×1           | 3.16×10 <sup>-6</sup> | 1.81                                 | 11.67       | 3470          | 2820                         |    |      |                       |                       |
| 75 | 110               | 93                 | 16                | 76  | 20             | 93             | 11  | 85             | M8×1           | 3.16×10 <sup>-6</sup> | 2.19                                 | 11.82       | 3420          | 2780                         |    |      |                       |                       |
| 70 | 105               | 112                | 16                | 95  | 20             | 88             | 11  | 80             | M8×1           | 3.16×10 <sup>-6</sup> | 2.11                                 | 11.84       | 3470          | 2820                         |    |      |                       |                       |
| 75 | 110               | 112                | 16                | 95  | 20             | 93             | 11  | 85             | M8×1           | 3.16×10 <sup>-6</sup> | 2.57                                 | 11.96       | 3420          | 2780                         |    |      |                       |                       |
| 75 | 110               | 112                | 16                | 95  | 20             | 93             | 11  | 85             | M8×1           | 3.16×10 <sup>-6</sup> | 2.56                                 | 11.28       | 3420          | 2780                         |    |      |                       |                       |
| 70 | 105               | 110                | 16                | 93  | 20             | 88             | 11  | 80             | M8×1           | 3.16×10 <sup>-6</sup> | 2.04                                 | 11.95       | 3470          | 2820                         |    |      |                       |                       |
| 75 | 110               | 110                | 16                | 93  | 20             | 93             | 11  | 85             | M8×1           | 3.16×10 <sup>-6</sup> | 2.51                                 | 12.06       | 3420          | 2780                         |    |      |                       |                       |
| 70 | 105               | 130                | 16                | 113 | 20             | 88             | 11  | 80             | M8×1           | 3.16×10 <sup>-6</sup> | 2.36                                 | 12.04       | 3470          | 2820                         |    |      |                       |                       |
| 75 | 110               | 131                | 16                | 114 | 20             | 93             | 11  | 85             | M8×1           | 3.16×10 <sup>-6</sup> | 2.91                                 | 12.14       | 3420          | 2780                         |    |      |                       |                       |
| 70 | 105               | 129                | 16                | 112 | 20             | 88             | 11  | 80             | M8×1           | 3.16×10 <sup>-6</sup> | 2.33                                 | 12.16       | 3470          | 2820                         |    |      |                       |                       |
| 75 | 110               | 129                | 16                | 112 | 20             | 93             | 11  | 85             | M8×1           | 3.16×10 <sup>-6</sup> | 2.86                                 | 12.23       | 3420          | 2780                         |    |      |                       |                       |

Axial Clearance

Unit: mm

| Clearance symbol | G0        | GT         |
|------------------|-----------|------------|
| Axial clearance  | 0 or less | 0 to 0.005 |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.  
It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.

The rigidity values (K) in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the rigidity value (K) in the table as the actual value.


If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>n</sub>) is obtained from the following equation.

$$K_n = K \left( \frac{F_a}{0.3C_a} \right)^3$$

K: Rigidity value in the dimensional table

# SDA-V/SDA-VZ With Preload/No Preload


|          |                    |        |
|----------|--------------------|--------|
| DN value | SDA-V (Caged Ball) | 160000 |
|          | SDA-VZ (Full-Ball) | 130000 |



| Model No.     | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Screw shaft thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating  |                       |                    |                       | Rigidity           |                    |
|---------------|---------------------------------|------------|--------------------------------------|---|--|--------------------|-----------------------|--------------------|-----------------------|--------------------|--------------------|
|               |                                 |            |                                      |   |  | SDA-V (Caged Ball) |                       | SDA-VZ (Full-Ball) |                       | SDA-V (Caged Ball) | SDA-VZ (Full-Ball) |
|               |                                 |            |                                      |   |  | Ca<br>kN           | C <sub>0a</sub><br>kN | Ca<br>kN           | C <sub>0a</sub><br>kN | K<br>N/μm          | K<br>N/μm          |
| SDA 5010V-5   | 50                              | 10         | 51                                   | 44.4                                    | 1×5                                    | 72                 | 155.2                 | 68.6               | 163.2                 | 780                | 815                |
| SDA 5010VA-5  | 50                              | 10         | 51.75                                | 45.2                                    | 1×5                                    | 72.5               | 158.1                 | 69                 | 165.7                 | 791                | 825                |
| SDA 5012V-5   | 50                              | 12         | 51                                   | 44.4                                    | 1×5                                    | 72                 | 155.2                 | 68.5               | 163.3                 | 779                | 816                |
| SDA 5012VA-5  | 50                              | 12         | 51.75                                | 45.2                                    | 1×5                                    | 72.4               | 158.1                 | 69                 | 165.9                 | 791                | 825                |
| SDA 5016V-5   | 50                              | 16         | 51                                   | 44.4                                    | 1×5                                    | 71.9               | 156.6                 | 68.4               | 163.7                 | 785                | 816                |
| SDA 5016VA-5  | 50                              | 16         | 51.75                                | 45.2                                    | 1×5                                    | 72.3               | 158.1                 | 68.9               | 166.2                 | 790                | 826                |
| SDA 5020V-5   | 50                              | 20         | 51                                   | 44.4                                    | 1×5                                    | 71.7               | 156.6                 | 68.3               | 164.2                 | 784                | 817                |
| SDA 5020V-10  | 50                              | 20         | 51                                   | 44.4                                    | 2×5                                    | 130.2              | 313.2                 | 124                | 328.3                 | 1518               | 1583               |
| SDA 5020VA-5  | 50                              | 20         | 51.75                                | 45.2                                    | 1×5                                    | 72.2               | 159.4                 | 68.8               | 166.7                 | 795                | 827                |
| SDA 5020VA-10 | 50                              | 20         | 51.75                                | 45.2                                    | 2×5                                    | 131.1              | 317.5                 | 124.8              | 333.3                 | 1534               | 1602               |
| SDA 5025V-4   | 50                              | 25         | 51                                   | 44.4                                    | 1×4                                    | 58.2               | 123.6                 | 55.5               | 129.8                 | 624                | 652                |
| SDA 5025VA-4  | 50                              | 25         | 51.75                                | 45.2                                    | 1×4                                    | 58.6               | 125.1                 | 55.8               | 131.7                 | 630                | 660                |
| SDA 5025VA-8  | 50                              | 25         | 51.75                                | 45.2                                    | 2×4                                    | 106.4              | 251.5                 | 101.3              | 263.5                 | 1226               | 1277               |
| SDA 5030V-4   | 50                              | 30         | 51                                   | 44.4                                    | 1×4                                    | 58                 | 117.5                 | 55.3               | 122.6                 | 629                | 654                |
| SDA 5030VA-4  | 50                              | 30         | 51.75                                | 45.2                                    | 1×4                                    | 58.4               | 118.9                 | 55.7               | 124.5                 | 635                | 661                |
| SDA 5030VA-8  | 50                              | 30         | 51.75                                | 45.2                                    | 2×4                                    | 106.1              | 237.7                 | 101                | 248.9                 | 1229               | 1280               |
| SDA 5040V-3   | 50                              | 40         | 51                                   | 44.4                                    | 1×3                                    | 43.9               | 86.5                  | 41.8               | 90.7                  | 467                | 487                |
| SDA 5040VA-3  | 50                              | 40         | 51.75                                | 45.2                                    | 1×3                                    | 44.2               | 87.9                  | 42.1               | 92                    | 473                | 492                |
| SDA 5040VA-6  | 50                              | 40         | 51.75                                | 45.2                                    | 2×3                                    | 80.3               | 175.7                 | 76.4               | 184                   | 916                | 954                |
| SDA 5050V-2   | 50                              | 50         | 51                                   | 44.4                                    | 1×2                                    | 29.2               | 55.5                  | 27.8               | 58                    | 303                | 316                |
| SDA 5050VA-2  | 50                              | 50         | 51.75                                | 45.2                                    | 1×2                                    | 29.4               | 55.6                  | 28                 | 58.8                  | 303                | 319                |

## Model number coding

|  |          |  |           |  |              |                      |
|--|----------|--|-----------|--|--------------|----------------------|
| <b>SDA5010V</b>  | <b>Z</b> | <b>-5</b>                                      | <b>TT</b> | <b>G0</b>  | <b>+830L</b> | <b>C5</b>            |
| Model No.  |          | Number of turns                                |           | Overall screw shaft length (in mm)   |              | Accuracy symbol (*3) |
| Full-ball type code (No code for caged ball type)  |          | Contamination protection accessory symbol (*1) |           | Axial direction clearance code (*2)<br>(Preloaded products: G0 Clearance,<br>Non-preloaded products: GT Clearance) |              |                      |
| (*1) See <a href="#">A15-334</a> . (*2) See <a href="#">A15-19</a> . (*3) See <a href="#">A15-12</a> . |          |  |           |  |              |                      |



Unit: mm

|    | Nut dimensions |                 |                |                |                |                |                |                |                |                       | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass | Shaft mass        | Permissible rotational speed |    |      |                       |                       |
|----|----------------|-----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----------------------|---|----------|-------------------|------------------------------|----|------|-----------------------|-----------------------|
|    | Outer diameter | Flange diameter | Overall length | H              | B <sub>1</sub> | B <sub>2</sub> | PCD            | d <sub>i</sub> | T <sub>w</sub> | Lubrication hole      |   |          |                   | kg·m <sup>2</sup> /mm        | kg | kg/m | SDA-V<br>(Caged Ball) | SDA-VZ<br>(Full-Ball) |
|    |                |                 |                |                |                |                |                |                |                |                       |   |          |                   |                              |    |      | min <sup>-1</sup>     | min <sup>-1</sup>     |
| D  | D <sub>1</sub> | L <sub>1</sub>  | H              | B <sub>1</sub> | B <sub>2</sub> | PCD            | d <sub>i</sub> | T <sub>w</sub> | A              | kg·m <sup>2</sup> /mm | kg  | kg/m     | min <sup>-1</sup> | min <sup>-1</sup>            |    |      |                       |                       |
| 75 | 110            | 65              | 16             | 48             | 20             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup> | 1.46  | 13.93    | 3130              | 2540                         |    |      |                       |                       |
| 82 | 118            | 65              | 16             | 48             | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 1.89  | 14.2     | 3090              | 2510                         |    |      |                       |                       |
| 75 | 110            | 74              | 16             | 57             | 20             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup> | 1.63  | 14.19    | 3130              | 2540                         |    |      |                       |                       |
| 82 | 118            | 74              | 16             | 57             | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 2.12  | 14.41    | 3090              | 2510                         |    |      |                       |                       |
| 75 | 110            | 93              | 16             | 76             | 20             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup> | 1.96  | 14.5     | 3130              | 2540                         |    |      |                       |                       |
| 82 | 118            | 93              | 16             | 76             | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 2.57  | 14.67    | 3090              | 2510                         |    |      |                       |                       |
| 75 | 110            | 112             | 16             | 95             | 20             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup> | 2.29  | 14.69    | 3130              | 2540                         |    |      |                       |                       |
| 75 | 110            | 112             | 16             | 95             | 20             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup> | 2.25  | 13.79    | 3130              | 2540                         |    |      |                       |                       |
| 82 | 118            | 112             | 16             | 95             | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 3.02  | 14.83    | 3090              | 2510                         |    |      |                       |                       |
| 82 | 118            | 112             | 16             | 95             | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 2.98  | 14.06    | 3090              | 2510                         |    |      |                       |                       |
| 75 | 110            | 110             | 16             | 93             | 20             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup> | 2.22  | 14.82    | 3130              | 2540                         |    |      |                       |                       |
| 82 | 118            | 110             | 16             | 93             | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 2.95  | 14.95    | 3090              | 2510                         |    |      |                       |                       |
| 82 | 118            | 110             | 16             | 93             | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 2.92  | 14.31    | 3090              | 2510                         |    |      |                       |                       |
| 75 | 110            | 130             | 16             | 113            | 20             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup> | 2.57  | 14.92    | 3130              | 2540                         |    |      |                       |                       |
| 82 | 118            | 130             | 16             | 113            | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 3.42  | 15.03    | 3090              | 2510                         |    |      |                       |                       |
| 82 | 118            | 130             | 16             | 113            | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 3.39  | 14.47    | 3090              | 2510                         |    |      |                       |                       |
| 75 | 110            | 128             | 16             | 111            | 20             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup> | 2.52  | 15.06    | 3130              | 2540                         |    |      |                       |                       |
| 82 | 118            | 129             | 16             | 112            | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 3.37  | 15.13    | 3090              | 2510                         |    |      |                       |                       |
| 82 | 118            | 129             | 16             | 112            | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 3.32  | 14.68    | 3090              | 2510                         |    |      |                       |                       |
| 75 | 110            | 107             | 16             | 90             | 20             | 93             | 11             | 85             | M8×1           | 4.82×10 <sup>-6</sup> | 2.13  | 15.13    | 3130              | 2540                         |    |      |                       |                       |
| 82 | 118            | 107             | 16             | 90             | 20             | 100            | 11             | 92             | M8×1           | 4.82×10 <sup>-6</sup> | 2.84  | 15.2     | 3090              | 2510                         |    |      |                       |                       |

Axial Clearance

Unit: mm

| Clearance symbol | G0        | GT         |
|------------------|-----------|------------|
| Axial clearance  | 0 or less | 0 to 0.005 |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details. It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.

The rigidity values (K) in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the rigidity value (K) in the table as the actual value.


If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>a</sub>) is obtained from the following equation.

$$K_a = K \left( \frac{F_a}{0.3C_a} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# EPB-V With Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | Loaded circuits<br>Rows x turns | Basic load rating |                       | Rigidity<br>K<br>N/ $\mu$ m |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|---------------------------------|-------------------|-----------------------|-----------------------------|
|              |                                 |            |                                      |                             |                                 | Ca<br>kN          | C <sub>0a</sub><br>kN |                             |
| EPB 1605V-6  | 16                              | 5          | 16.75                                | 13.49                       | 3×1                             | 9.3               | 13.1                  | 315                         |
| EPB 2004V-8  | 20                              | 4          | 20.5                                 | 18.06                       | 4×1                             | 8.2               | 15.5                  | 503                         |
| EPB 2005V-6  | 20                              | 5          | 20.75                                | 17.49                       | 3×1                             | 10.6              | 17.3                  | 396                         |
| EPB 2006V-6  | 20                              | 6          | 21                                   | 16.93                       | 3×1                             | 13.8              | 20.4                  | 388                         |
| EPB 2008V-6  | 20                              | 8          | 21                                   | 16.93                       | 3×1                             | 13.7              | 20.4                  | 388                         |
| EPB 2010V-6  | 20                              | 10         | 21.25                                | 16.36                       | 3×1                             | 17.3              | 24.5                  | 398                         |
| EPB 2504V-8  | 25                              | 4          | 25.5                                 | 23.06                       | 4×1                             | 9.1               | 19.5                  | 602                         |
| EPB 2505V-6  | 25                              | 5          | 25.75                                | 22.49                       | 3×1                             | 12.1              | 22.6                  | 491                         |
| EPB 2506V-6  | 25                              | 6          | 26                                   | 21.93                       | 3×1                             | 16.0              | 27.1                  | 488                         |
| EPB 2508V-6  | 25                              | 8          | 26                                   | 21.93                       | 3×1                             | 15.9              | 27.1                  | 487                         |
| EPB 2510V-4  | 25                              | 10         | 26                                   | 21.93                       | 2×1                             | 11.3              | 18.0                  | 331                         |
| EPB 2512V-4  | 25                              | 12         | 26.25                                | 21.36                       | 2×1                             | 14.0              | 21.2                  | 332                         |
| EPB 2806V-6  | 28                              | 6          | 29                                   | 24.93                       | 3×1                             | 17.5              | 32.0                  | 560                         |
| EPB 3204V-10 | 32                              | 4          | 32.5                                 | 30.06                       | 5×1                             | 12.3              | 31.9                  | 921                         |
| EPB 3205V-6  | 32                              | 5          | 32.75                                | 29.49                       | 3×1                             | 13.9              | 30.2                  | 616                         |
| EPB 3205V-8  | 32                              | 5          | 32.75                                | 29.49                       | 4×1                             | 17.8              | 40.3                  | 811                         |
| EPB 3206V-8  | 32                              | 6          | 33                                   | 28.93                       | 4×1                             | 23.9              | 49.5                  | 826                         |
| EPB 3208V-8  | 32                              | 8          | 33.25                                | 28.36                       | 4×1                             | 29.2              | 55.2                  | 797                         |
| EPB 3210V-6  | 32                              | 10         | 33.75                                | 27.24                       | 3×1                             | 32.1              | 52.2                  | 602                         |
| EPB 3604V-6  | 36                              | 4          | 36.5                                 | 34.04                       | 3×1                             | 8.4               | 22.2                  | 636                         |
| EPB 3606V-8  | 36                              | 6          | 37                                   | 32.93                       | 4×1                             | 25.2              | 56.2                  | 914                         |
| EPB 3608V-8  | 36                              | 8          | 37.25                                | 32.36                       | 4×1                             | 31.6              | 64.8                  | 908                         |

Note) When the QZ Lubricator and W wiper ring are attached, the overall length of the nut dimensions will increase. Contact THK for details.

### Model number coding

**EPB3205V-6 RR G0 +650L C3**


Model No.

Clearance symbol

Accuracy symbol

Ball screw shaft length (mm)

Seal symbol (RR : Labyrinth seal, WW : Wiper ring.)



Unit: mm

|  | Nut dimensions |                 |                |    |                |                |     |                |                |                  | Nut mass<br>kg | Shaft mass<br>kg/m |
|--|----------------|-----------------|----------------|----|----------------|----------------|-----|----------------|----------------|------------------|----------------|--------------------|
|  | Outer diameter | Flange diameter | Overall length |    |                |                |     |                |                | Lubrication hole |                |                    |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | A                |                |                    |
|  | 28             | 48              | 65             | 10 | 50             | 12             | 38  | 5.5            | 40             | M6               | 0.23           | 1.35               |
|  | 36             | 58              | 69             | 10 | 54             | 12             | 47  | 6.6            | 44             | M6               | 0.31           | 2.26               |
|  | 36             | 58              | 65             | 10 | 50             | 12             | 47  | 6.6            | 44             | M6               | 0.37           | 2.17               |
|  | 36             | 58              | 73             | 10 | 58             | 12             | 47  | 6.6            | 44             | M6               | 0.40           | 2.11               |
|  | 36             | 58              | 87             | 10 | 72             | 15             | 47  | 6.6            | 44             | M6               | 0.47           | 2.20               |
|  | 36             | 58              | 102            | 10 | 87             | 15             | 47  | 6.6            | 44             | M6               | 0.52           | 2.14               |
|  | 40             | 62              | 70             | 10 | 55             | 12             | 51  | 6.6            | 48             | M6               | 0.34           | 3.58               |
|  | 40             | 62              | 66             | 10 | 51             | 12             | 51  | 6.6            | 48             | M6               | 0.40           | 3.48               |
|  | 40             | 62              | 74             | 10 | 59             | 12             | 51  | 6.6            | 48             | M6               | 0.42           | 3.40               |
|  | 40             | 62              | 88             | 10 | 73             | 15             | 51  | 6.6            | 48             | M6               | 0.50           | 3.51               |
|  | 40             | 62              | 81             | 10 | 66             | 18             | 51  | 6.6            | 48             | M6               | 0.48           | 3.57               |
|  | 40             | 62              | 91             | 10 | 76             | 18             | 51  | 6.6            | 48             | M6               | 0.49           | 3.50               |
|  | 42             | 71              | 72             | 12 | 60             | 15             | 57  | 6.6            | 55             | M6               | 0.51           | 4.32               |
|  | 50             | 80              | 81             | 12 | 64             | 15             | 65  | 9              | 62             | M6               | 0.81           | 5.95               |
|  | 50             | 80              | 67             | 12 | 50             | 12             | 65  | 9              | 62             | M6               | 0.67           | 5.82               |
|  | 50             | 80              | 78             | 12 | 61             | 12             | 65  | 9              | 62             | M6               | 0.75           | 5.82               |
|  | 50             | 80              | 95             | 12 | 78             | 15             | 65  | 9              | 62             | M6               | 0.88           | 5.71               |
|  | 50             | 80              | 117            | 12 | 100            | 18             | 65  | 9              | 62             | M6               | 1.00           | 5.63               |
|  | 50             | 80              | 108            | 12 | 91             | 18             | 65  | 9              | 62             | M6               | 0.86           | 5.45               |
|  | 56             | 86              | 58             | 14 | 44             | 15             | 70  | 9              | 65             | M6               | 0.96           | 7.58               |
|  | 56             | 86              | 92             | 14 | 78             | 15             | 70  | 9              | 65             | M6               | 1.09           | 7.31               |
|  | 56             | 86              | 112            | 14 | 98             | 20             | 70  | 9              | 65             | M6               | 1.22           | 7.21               |

Note) The rigidity values in the table represent spring constants each obtained from the load and the elastic deformation when providing a preload 8% of the basic dynamic load rating (Ca) and applying an axial load three times greater than the preload. These values do not include the rigidity of the components related to mounting the table. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.


If the applied preload (Fa0) is not 0.1 Ca, the rigidity value (K<sub>v</sub>) is obtained from the following equation.

$$K_v = K \left( \frac{Fa0}{0.1Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# EPB-V With Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | Loaded circuits<br>Rows x turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|---------------------------------|-------------------|-----------------------|-----------------------|
|              |                                 |            |                                      |                             |                                 | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| EPB 4004V-6  | 40                              | 4          | 40.5                                 | 38.06                       | 3×1                             | 8.8               | 24.7                  | 692                   |
| EPB 4005V-6  | 40                              | 5          | 40.75                                | 37.49                       | 3×1                             | 15.4              | 38.8                  | 751                   |
| EPB 4006V-12 | 40                              | 6          | 41                                   | 36.93                       | 6×1                             | 37.5              | 94.4                  | 1470                  |
| EPB 4008V-8  | 40                              | 8          | 41.25                                | 36.36                       | 4×1                             | 33.8              | 74.5                  | 1014                  |
| EPB 4010V-6  | 40                              | 10         | 41.75                                | 35.24                       | 3×1                             | 37.3              | 69.3                  | 756                   |
| EPB 4010V-8  | 40                              | 10         | 41.75                                | 35.24                       | 4×1                             | 47.6              | 92.4                  | 995                   |
| EPB 4012V-8  | 40                              | 12         | 41.75                                | 35.2                        | 4×1                             | 47.6              | 92.4                  | 995                   |
| EPB 5005V-12 | 50                              | 5          | 50.75                                | 47.49                       | 6×1                             | 30.9              | 99.1                  | 1764                  |
| EPB 5008V-8  | 50                              | 8          | 51.25                                | 46.36                       | 4×1                             | 37.2              | 93.9                  | 1216                  |
| EPB 5010V-8  | 50                              | 10         | 51.75                                | 45.24                       | 4×1                             | 54.3              | 120.5                 | 1234                  |
| EPB 6310V-4  | 63                              | 10         | 64.75                                | 58.2                        | 2×1                             | 34.5              | 80.1                  | 800                   |

Note) When the QZ Lubricator and W wiper ring are attached, the overall length of the nut dimensions will increase. Contact THK for details.

### Model number coding

**EPB4005V-6 RR G0 +650L C3**

Model No.


Clearance symbol

Accuracy symbol

Ball screw shaft length (mm)

Seal symbol (RR : Labyrinth seal, WW : Wiper ring.)





Unit: mm

|  | Nut dimensions |                 |                |    |                |                |     |                |                |                  | Nut mass<br>kg | Shaft mass<br>kg/m |
|--|----------------|-----------------|----------------|----|----------------|----------------|-----|----------------|----------------|------------------|----------------|--------------------|
|  | Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | Lubrication hole |                |                    |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | A                |                |                    |
|  | 63             | 93              | 59             | 14 | 45             | 12             | 78  | 9              | 70             | M8               | 0.96           | 9.40               |
|  | 63             | 93              | 65             | 14 | 51             | 12             | 78  | 9              | 70             | M8               | 1.01           | 9.23               |
|  | 63             | 93              | 117            | 14 | 103            | 18             | 78  | 9              | 70             | M8               | 1.61           | 9.09               |
|  | 63             | 93              | 113            | 14 | 99             | 18             | 78  | 9              | 70             | M8               | 1.54           | 8.98               |
|  | 63             | 93              | 105            | 14 | 91             | 20             | 78  | 9              | 70             | M8               | 1.37           | 8.76               |
|  | 63             | 93              | 129            | 14 | 115            | 20             | 78  | 9              | 70             | M8               | 1.64           | 8.76               |
|  | 63             | 93              | 152            | 14 | 138            | 20             | 78  | 9              | 70             | M8               | 1.79           | 8.97               |
|  | 75             | 110             | 104            | 16 | 88             | 18             | 93  | 11             | 85             | M8               | 2.08           | 14.59              |
|  | 75             | 110             | 115            | 16 | 99             | 18             | 93  | 11             | 85             | M8               | 2.16           | 14.28              |
|  | 75             | 110             | 131            | 16 | 115            | 18             | 93  | 11             | 85             | M8               | 2.30           | 14.00              |
|  | 90             | 125             | 89             | 18 | 71             | 18             | 108 | 11             | 95             | M8               | 2.10           | 22.64              |

Note) The rigidity values in the table represent spring constants each obtained from the load and the elastic deformation when providing a preload 8% of the basic dynamic load rating (Ca) and applying an axial load three times greater than the preload. These values do not include the rigidity of the components related to mounting the nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.

If the applied preload (Fa0) is not 0.1 Ca, the rigidity value (K<sub>n</sub>) is obtained from the following equation.


$$K_n = K \left( \frac{Fa0}{0.1Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# EBB-V

## Oversized-ball Preload / No Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | Loaded circuits<br>Rows x turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|---------------------------------|-------------------|-----------------------|-----------------------|
|              |                                 |            |                                      |                             |                                 | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| EBB 1605V-4  | 16                              | 5          | 16.75                                | 13.49                       | 4×1                             | 11.9              | 17.4                  | 207                   |
| EBB 2004V-8  | 20                              | 4          | 20.5                                 | 18.06                       | 8×1                             | 14.9              | 30.9                  | 487                   |
| EBB 2005V-3  | 20                              | 5          | 20.75                                | 17.49                       | 3×1                             | 10.6              | 17.3                  | 198                   |
| EBB 2006V-6  | 20                              | 6          | 21                                   | 16.93                       | 6×1                             | 25.0              | 40.8                  | 376                   |
| EBB 2008V-6  | 20                              | 8          | 21                                   | 16.93                       | 6×1                             | 24.9              | 40.8                  | 375                   |
| EBB 2010V-6  | 20                              | 10         | 21.25                                | 16.36                       | 6×1                             | 31.4              | 49.0                  | 385                   |
| EBB 2504V-8  | 25                              | 4          | 25.5                                 | 23.06                       | 8×1                             | 16.4              | 39.0                  | 583                   |
| EBB 2505V-3  | 25                              | 5          | 25.75                                | 22.49                       | 3×1                             | 12.1              | 22.6                  | 245                   |
| EBB 2506V-6  | 25                              | 6          | 26                                   | 21.93                       | 6×1                             | 29.0              | 54.1                  | 472                   |
| EBB 2508V-6  | 25                              | 8          | 26                                   | 21.93                       | 6×1                             | 28.9              | 54.1                  | 472                   |
| EBB 2510V-3  | 25                              | 10         | 26                                   | 21.93                       | 3×1                             | 15.9              | 27.0                  | 243                   |
| EBB 2510V-4  | 25                              | 10         | 26                                   | 21.93                       | 4×1                             | 20.9              | 37.6                  | 320                   |
| EBB 2512V-4  | 25                              | 12         | 26.25                                | 21.36                       | 4×1                             | 25.4              | 42.3                  | 322                   |
| EBB 2806V-6  | 28                              | 6          | 29                                   | 24.93                       | 6×1                             | 31.7              | 64.1                  | 542                   |
| EBB 3204V-10 | 32                              | 4          | 32.5                                 | 30.06                       | 10×1                            | 22.3              | 63.9                  | 892                   |
| EBB 3205V-3  | 32                              | 5          | 32.75                                | 29.49                       | 3×1                             | 13.9              | 30.2                  | 308                   |
| EBB 3205V-4  | 32                              | 5          | 32.75                                | 29.49                       | 4×1                             | 17.8              | 40.3                  | 405                   |
| EBB 3205V-6  | 32                              | 5          | 32.75                                | 29.49                       | 6×1                             | 25.1              | 60.4                  | 597                   |
| EBB 3206V-8  | 32                              | 6          | 33                                   | 28.93                       | 8×1                             | 43.3              | 98.9                  | 800                   |
| EBB 3208V-8  | 32                              | 8          | 33.25                                | 28.36                       | 8×1                             | 52.9              | 110.5                 | 772                   |
| EBB 3210V-3  | 32                              | 10         | 33.75                                | 27.24                       | 3×1                             | 32.1              | 52.2                  | 301                   |
| EBB 3210V-4  | 32                              | 10         | 33.75                                | 27.24                       | 4×1                             | 41.3              | 69.7                  | 396                   |
| EBB 3604V-6  | 36                              | 4          | 36.5                                 | 34.04                       | 6×1                             | 15.3              | 44.3                  | 616                   |
| EBB 3606V-8  | 36                              | 6          | 37                                   | 32.93                       | 8×1                             | 45.8              | 112.4                 | 885                   |
| EBB 3608V-8  | 36                              | 8          | 37.25                                | 32.36                       | 8×1                             | 57.4              | 129.7                 | 879                   |

Note) When the QZ Lubricator and W wiper ring are attached, the overall length of the nut dimensions will increase. Contact THK for details.

### Model number coding

**EBB3205V-6 RR G0 +650L C3**


Model No.

Clearance symbol

Accuracy symbol

Ball screw shaft length (mm)

Seal symbol (RR : Labyrinth seal, WW : Wiper ring.)



Unit: mm

|    | Nut dimensions |                 |                |     |                |                |     |                |                |                  | Nut mass<br>kg | Shaft mass<br>kg/m |
|----|----------------|-----------------|----------------|-----|----------------|----------------|-----|----------------|----------------|------------------|----------------|--------------------|
|    | Outer diameter | Flange diameter | Overall length | H   | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | Lubrication hole |                |                    |
|    | D              | D <sub>1</sub>  | L <sub>1</sub> | H   | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | A                |                |                    |
| 28 | 48             | 55              | 10             | 40  | 12             | 38             | 5.5 | 40             | M6             | 0.20             | 1.35           |                    |
| 36 | 58             | 69              | 10             | 54  | 12             | 47             | 6.6 | 44             | M6             | 0.31             | 2.26           |                    |
| 36 | 58             | 50              | 10             | 35  | 12             | 47             | 6.6 | 44             | M6             | 0.30             | 2.17           |                    |
| 36 | 58             | 73              | 10             | 58  | 12             | 47             | 6.6 | 44             | M6             | 0.40             | 2.11           |                    |
| 36 | 58             | 87              | 10             | 72  | 15             | 47             | 6.6 | 44             | M6             | 0.47             | 2.20           |                    |
| 36 | 58             | 102             | 10             | 87  | 15             | 47             | 6.6 | 44             | M6             | 0.52             | 2.14           |                    |
| 40 | 62             | 70              | 10             | 55  | 12             | 51             | 6.6 | 48             | M6             | 0.34             | 3.58           |                    |
| 40 | 62             | 50              | 10             | 35  | 12             | 51             | 6.6 | 48             | M6             | 0.32             | 3.48           |                    |
| 40 | 62             | 74              | 10             | 59  | 12             | 51             | 6.6 | 48             | M6             | 0.42             | 3.40           |                    |
| 40 | 62             | 88              | 10             | 73  | 15             | 51             | 6.6 | 48             | M6             | 0.50             | 3.51           |                    |
| 40 | 62             | 69              | 10             | 54  | 18             | 51             | 6.6 | 48             | M6             | 0.42             | 3.57           |                    |
| 40 | 62             | 81              | 10             | 66  | 18             | 51             | 6.6 | 48             | M6             | 0.48             | 3.57           |                    |
| 40 | 62             | 91              | 10             | 76  | 18             | 51             | 6.6 | 48             | M6             | 0.49             | 3.50           |                    |
| 42 | 71             | 72              | 12             | 60  | 15             | 57             | 6.6 | 55             | M6             | 0.51             | 4.32           |                    |
| 50 | 80             | 81              | 12             | 64  | 15             | 65             | 9   | 62             | M6             | 0.81             | 5.95           |                    |
| 50 | 80             | 52              | 12             | 35  | 12             | 65             | 9   | 62             | M6             | 0.56             | 5.82           |                    |
| 50 | 80             | 57              | 12             | 40  | 12             | 65             | 9   | 62             | M6             | 0.60             | 5.82           |                    |
| 50 | 80             | 67              | 12             | 50  | 12             | 65             | 9   | 62             | M6             | 0.67             | 5.82           |                    |
| 50 | 80             | 95              | 12             | 78  | 15             | 65             | 9   | 62             | M6             | 0.88             | 5.71           |                    |
| 50 | 80             | 117             | 12             | 100 | 18             | 65             | 9   | 62             | M6             | 1.00             | 5.63           |                    |
| 50 | 80             | 78              | 12             | 61  | 18             | 65             | 9   | 62             | M6             | 0.67             | 5.45           |                    |
| 50 | 80             | 90              | 12             | 73  | 18             | 65             | 9   | 62             | M6             | 0.75             | 5.45           |                    |
| 56 | 86             | 58              | 14             | 44  | 15             | 70             | 9   | 65             | M6             | 0.96             | 7.58           |                    |
| 56 | 86             | 92              | 14             | 78  | 15             | 70             | 9   | 65             | M6             | 1.09             | 7.31           |                    |
| 56 | 86             | 112             | 14             | 98  | 20             | 70             | 9   | 65             | M6             | 1.22             | 7.21           |                    |

Note) The rigidity values in the table represent spring constants each obtained from the load and the Elastic Deformation finish when providing an axial load 24% of the basic dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.

If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>N</sub>) is obtained from the following equation.


$$K_N = K \left( \frac{Fa}{0.3Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# EBB-V

## Oversized-ball Preload / No Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | Loaded circuits<br>Rows x turns | Basic load rating |          | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|---------------------------------|-------------------|----------|-----------------------|
|              |                                 |            |                                      |                             |                                 | Ca<br>kN          | Ca<br>kN |                       |
| EBB 4004V-6  | 40                              | 4          | 40.5                                 | 38.06                       | 6×1                             | 15.9              | 49.4     | 670                   |
| EBB 4005V-6  | 40                              | 5          | 40.75                                | 37.49                       | 6×1                             | 26.6              | 77.5     | 727                   |
| EBB 4006V-12 | 40                              | 6          | 41                                   | 36.93                       | 12×1                            | 68.1              | 188.7    | 1423                  |
| EBB 4008V-8  | 40                              | 8          | 41.25                                | 36.36                       | 8×1                             | 61.3              | 148.9    | 982                   |
| EBB 4010V-3  | 40                              | 10         | 41.75                                | 35.24                       | 3×1                             | 37.3              | 69.3     | 378                   |
| EBB 4010V-4  | 40                              | 10         | 41.75                                | 35.24                       | 4×1                             | 47.6              | 92.4     | 497                   |
| EBB 4012V-8  | 40                              | 12         | 41.75                                | 35.2                        | 8×1                             | 86.4              | 184.8    | 963                   |
| EBB 4020V-3  | 40                              | 20         | 41.75                                | 35.24                       | 3×1                             | 36.8              | 69.3     | 376                   |
| EBB 5005V-12 | 50                              | 5          | 50.75                                | 47.49                       | 12×1                            | 56.0              | 198.3    | 1708                  |
| EBB 5008V-8  | 50                              | 8          | 51.25                                | 46.36                       | 8×1                             | 67.5              | 187.7    | 1177                  |
| EBB 5010V-4  | 50                              | 10         | 51.75                                | 45.24                       | 4×1                             | 54.3              | 120.5    | 617                   |
| EBB 5020V-3  | 50                              | 20         | 52.25                                | 44.11                       | 3×1                             | 55.3              | 108.8    | 465                   |
| EBB 6310V-4  | 63                              | 10         | 64.75                                | 58.2                        | 4×1                             | 61.9              | 161.0    | 775                   |
| EBB 6312V-4  | 63                              | 12         | 65.25                                | 57.1                        | 4×1                             | 80.9              | 189.1    | 759                   |
| EBB 6316V-4  | 63                              | 16         | 65.7                                 | 56.0                        | 4×1                             | 134.0             | 306.4    | 970                   |
| EBB 6320V-3  | 63                              | 20         | 65.7                                 | 56.0                        | 3×1                             | 104.4             | 229.3    | 736                   |
| EBB 8010V-4  | 80                              | 10         | 81.75                                | 75.2                        | 4×1                             | 68.6              | 206.9    | 943                   |
| EBB 8012V-4  | 80                              | 12         | 82.25                                | 74.1                        | 4×1                             | 92.1              | 251.7    | 953                   |
| EBB 8016V-4  | 80                              | 16         | 82.7                                 | 73.0                        | 4×1                             | 154.7             | 413.2    | 1233                  |
| EBB 8020V-4  | 80                              | 20         | 82.7                                 | 73.0                        | 4×1                             | 154.5             | 413.2    | 1232                  |

Note) When the QZ Lubricator and W wiper ring are attached, the overall length of the nut dimensions will increase. Contact THK for details.

### Model number coding

**EBB4005V-6 RR G0 +650L C3**


Model No.

Clearance symbol

Accuracy symbol

Ball screw shaft length (mm)

Seal symbol (RR : Labyrinth seal, WW : Wiper ring.)



Unit: mm

|  | Nut dimensions |                 |                |    |                |                |     |                |                |                  | Nut mass<br>kg | Shaft mass<br>kg/m |
|--|----------------|-----------------|----------------|----|----------------|----------------|-----|----------------|----------------|------------------|----------------|--------------------|
|  | Outer diameter | Flange diameter | Overall length |    |                |                |     |                |                | Lubrication hole |                |                    |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | A                |                |                    |
|  | 63             | 93              | 59             | 14 | 45             | 12             | 78  | 9              | 70             | M8               | 0.96           | 9.40               |
|  | 63             | 93              | 65             | 14 | 51             | 12             | 78  | 9              | 70             | M8               | 1.01           | 9.23               |
|  | 63             | 93              | 117            | 14 | 103            | 18             | 78  | 9              | 70             | M8               | 1.61           | 9.09               |
|  | 63             | 93              | 113            | 14 | 99             | 18             | 78  | 9              | 70             | M8               | 1.54           | 8.98               |
|  | 63             | 93              | 75             | 14 | 61             | 20             | 78  | 9              | 70             | M8               | 1.03           | 8.76               |
|  | 63             | 93              | 85             | 14 | 71             | 20             | 78  | 9              | 70             | M8               | 1.15           | 8.76               |
|  | 63             | 93              | 152            | 14 | 138            | 20             | 78  | 9              | 70             | M8               | 1.79           | 8.97               |
|  | 63             | 93              | 122            | 14 | 98             | 27             | 78  | 9              | 70             | M8               | 1.62           | 9.28               |
|  | 75             | 110             | 104            | 16 | 88             | 18             | 93  | 11             | 85             | M8               | 2.08           | 14.59              |
|  | 75             | 110             | 115            | 16 | 99             | 18             | 93  | 11             | 85             | M8               | 2.16           | 14.28              |
|  | 75             | 110             | 87             | 16 | 71             | 18             | 93  | 11             | 85             | M8               | 1.65           | 14.00              |
|  | 75             | 110             | 117            | 16 | 101            | 27             | 93  | 11             | 85             | M8               | 2.07           | 14.32              |
|  | 90             | 125             | 89             | 18 | 71             | 18             | 108 | 11             | 95             | M8               | 2.10           | 22.64              |
|  | 95             | 135             | 104            | 20 | 84             | 25             | 115 | 13.5           | 100            | M8               | 2.93           | 22.21              |
|  | 95             | 135             | 125            | 20 | 105            | 25             | 115 | 13.5           | 100            | M8               | 3.27           | 22.07              |
|  | 95             | 135             | 122            | 20 | 102            | 27             | 115 | 13.5           | 100            | M8               | 3.48           | 22.52              |
|  | 105            | 145             | 93             | 20 | 73             | 18             | 125 | 13.5           | 110            | M8               | 2.60           | 37.07              |
|  | 125            | 165             | 110            | 25 | 85             | 25             | 145 | 13.5           | 130            | M8               | 6.06           | 36.51              |
|  | 125            | 165             | 131            | 25 | 106            | 25             | 145 | 13.5           | 130            | M8               | 7.15           | 36.33              |
|  | 125            | 165             | 149            | 25 | 124            | 25             | 145 | 13.5           | 130            | M8               | 8.13           | 36.90              |

Note) The rigidity values in the table represent spring constants each obtained from the load and the Elastic Deformation finish when providing an axial load 24% of the basic dynamic load rating (Ca).










These values do not include the rigidity of the components related to mounting the nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.

If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>N</sub>) is obtained from the following equation.

$$K_N = K \left( \frac{F_a}{0.3C_a} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table









# Positioning Ball Screw

| Series      | Type   |   | Features                              |
|-------------|--|---|---------------------------------------|
| Positioning | SBN-V  |    | Caged Ball, Single nut, high DN value |
|             | SBK  |    | High DN value, large lead             |
|             | BIF-V  |    | Single nut, high DN value             |
|             | BNFN-V                                       |    | Double nut, high DN value             |
|             | BNFN   |   | Double nut, large                     |
|             | DIK  |  | Compact nut, preload                  |
|             | DKN  |  | Compact nut                           |
|             | BLW  |  | Large lead                            |
|             | BNK<br>Standardized<br>finished<br>shaft end |  | Standard to Super Lead                |

## Positioning Ball Screw

|  | Caged ball | Compact nut | Miniature | High load capacity | Offset Preload | Double-nut Preload | DN Value | Shaft diameter (mm) | Lead (mm) | Page No.       |
|--|------------|-------------|-----------|--------------------|----------------|--------------------|----------|---------------------|-----------|----------------|
|  | ✓          |             |           |                    | ✓              |                    | 130000   | 16 to 32            | 4 to 10   | <b>A15-110</b> |
|  |            |             |           |                    |                |                    | 160000   | 25 to 50            | 8 to 20   | <b>A15-112</b> |
|  | ✓          |             |           |                    | ✓              |                    | 210000   | 36 to 50            | 36 to 50  | <b>A15-114</b> |
|  |            |             |           |                    |                |                    | 160000   | 15 to 55            | 10 to 36  | <b>A15-116</b> |
|  |            |             |           |                    | ✓              |                    | 100000   | 16 to 32            | 4 to 6    | <b>A15-118</b> |
|  |            |             |           |                    |                |                    | 130000   | 25 to 50            | 8 to 20   | <b>A15-120</b> |
|  |            |             |           | ✓                  |                | ✓                  | 100000   | 16 to 32            | 5 to 6    | <b>A15-124</b> |
|  |            |             |           |                    |                | ✓                  | 130000   | 28 to 50            | 10 to 16  | <b>A15-124</b> |
|  |            |             |           |                    |                | ✓                  | 70000    | 55 to 100           | 10 to 20  | <b>A15-126</b> |
|  |            | ✓           |           |                    | ✓              |                    | 70000    | 14 to 63            | 4 to 16   | <b>A15-130</b> |
|  |            | ✓           |           | ✓                  |                | ✓                  | 70000    | 40 to 63            | 20        | <b>A15-136</b> |
|  |            |             |           |                    |                | ✓                  | 70000    | 15 to 50            | 10 to 50  | <b>A15-138</b> |
|  |            |             |           |                    | ✓              |                    | 70000    | 4 to 25             | 1 to 20   | <b>A15-140</b> |

# Positioning Ball Screw

| Series      | Type                            |   | Features                        |
|-------------|---------------------------------|---|---------------------------------|
| Positioning | MDK<br>Unfinished<br>Shaft Ends |    | Compact nut, miniature          |
|             | MDK                             |   |                                 |
|             | MBF<br>Unfinished<br>Shaft Ends |    | Miniature                       |
|             | MBF                             |   |                                 |
|             | BNF-V                           |    | Single nut, high DN value       |
|             | BNF                             |   | Single nut, large               |
|             | DK                              |    | Compact nut, no preload         |
|             | WHF                             |   | Super large lead, high DN value |
|             | BLK                             |  | Large lead                      |
|             | WGF                             |  | Super large lead                |
|             | BNT                             |  | Flat nut                        |



## Positioning Ball Screw

|  | Caged ball | Compact nut | Miniature | High load capacity | Offset Preload | DN Value | Shaft diameter (mm) | Lead (mm) | Page No.   |
|--|------------|-------------|-----------|--------------------|----------------|----------|---------------------|-----------|--|
|  |            | ✓           | ✓         |                    |                | 70000    | 4 to 14             | 1 to 5    | <a href="#">A15-182</a><br><a href="#">A15-186</a> |
|  |            |             | ✓         |                    |                | 70000    | 4 to 14             | 1 to 4    | <a href="#">A15-188</a>                            |
|  |            |             |           |                    |                |          |                     | 1 to 5    | <a href="#">A15-190</a>                            |
|  |            |             |           |                    |                | 100000   | 16 to 32            | 4 to 6    | <a href="#">A15-192</a>                            |
|  |            |             |           |                    |                | 130000   | 25 to 50            | 8 to 20   | <a href="#">A15-194</a>                            |
|  |            |             |           |                    |                | 70000    | 55 to 100           | 10 to 20  | <a href="#">A15-198</a>                            |
|  |            | ✓           |           |                    |                | 70000    | 14 to 63            | 4 to 20   | <a href="#">A15-202</a>                            |
|  |            |             |           |                    |                | 120000   | 15 to 25            | 20 to 50  | <a href="#">A15-210</a>                            |
|  |            |             |           |                    |                | 70000    | 8 to 50             | 8 to 50   | <a href="#">A15-212</a>                            |
|  |            |             |           |                    |                | 70000    | 8 to 50             | 12 to 100 | <a href="#">A15-214</a>                            |
|  |            |             |           |                    |                | 70000    | 14 to 45            | 4 to 12   | <a href="#">A15-216</a>                            |

## Standard combinations of outer diameters and leads of the screw shafts

| Shaft diameter | Lead              |                   |     |                                       |   |  |                                      |  |     |     |    |                          |  |
|----------------|-------------------|-------------------|-----|---------------------------------------|---|--|--------------------------------------|--|-----|-----|----|--------------------------|--|
|                | 1                 | 2                 | 3   | 4                                     | 5   | 6  | 8                                    | 10   | 12  | 15  | 16 |                          |  |
| 4              | BNK<br>MBF<br>MDK |                   |     |                                       |   |  |                                      |  |     |     |    |                          |  |
| 5              | BNK               |                   |     |                                       |   |  |                                      |  |     |     |    |                          |  |
| 6              | BNK<br>MBF<br>MDK | MBF               |     |                                       |   |  |                                      |  |     |     |    |                          |  |
| 8              | BNK<br>MDK        | BNK<br>MBF<br>MDK | MBF | MBF                                   |   |  | BLK                                  | BNK  | WGF |     |    |                          |  |
| 10             | MBF               | BNK<br>MBF<br>MDK | MBF | BNK                                   | MBF   |  |                                      | BNK  |     | WGF |    |                          |  |
| 12             |                   | BNK<br>MBF<br>MDK | MBF | MBF                                   | BNK   |  | BNK                                  |  |     |     |    |                          |  |
| 13             |                   |                   |     |                                       |   |  |                                      |  |     |     |    |                          |  |
| 14             |                   | BNK<br>MBF<br>MDK |     | BNK<br>DIK<br>MBF<br>MDK<br>DK<br>BNT | MDK<br>BNT  |  | BNK                                  |  |     |     |    |                          |  |
| 15             |                   |                   |     |                                       |   |  |                                      | BNK<br>BLW<br>BLK                              |     |     |    |                          |  |
| 16             |                   |                   |     | SBN-V<br>BIF-V<br>BNF-V               | SBN-V<br>BIF-V<br>BNFN-V<br>DIK<br>BNF-V<br>DK<br>BNT |  |                                      |  |     |     |    | SBK<br>BNK<br>BLW<br>BLK |  |
| 18             |                   |                   |     |                                       |   |  | BNT                                  |  |     |     |    |                          |  |
| 20             |                   |                   |     | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK  | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK<br>BNT           | DIK<br>DK                                    | DIK<br>DK                            | SBN-V<br>BIF-V<br>BNK<br>BNF-V<br>BNT          |     |     |    |                          |  |
| 25             |                   |                   |     | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK  | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK<br>BNT           | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK         | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK<br>BNT    |     |     |    |                          |  |
| 28             |                   |                   |     |                                       | SBN-V<br>BIF-V<br>BNFN-V<br>DIK<br>BNF-V<br>DK        | BIF-V<br>BNFN-V<br>DIK<br>BNF-V<br>DK<br>BNT |                                      | SBN-V<br>BIF-V<br>BNFN-V<br>DIK<br>BNF-V<br>DK |     |     |    |                          |  |

## Positioning Ball Screw

Unit: mm

| Lead |                                 |    |                          |            |    |    |            |            |     |    |    |     |
|------|---------------------------------|----|--------------------------|------------|----|----|------------|------------|-----|----|----|-----|
|      | 20                              | 24 | 25                       | 30         | 32 | 36 | 40         | 50         | 60  | 80 | 90 | 100 |
|      |                                 |    |                          |            |    |    |            |            |     |    |    |     |
|      |                                 |    |                          |            |    |    |            |            |     |    |    |     |
|      |                                 |    |                          |            |    |    |            |            |     |    |    |     |
|      |                                 |    |                          |            |    |    |            |            |     |    |    |     |
|      |                                 |    |                          |            |    |    |            |            |     |    |    |     |
|      |                                 |    |                          |            |    |    |            |            |     |    |    |     |
|      | WGF                             |    |                          |            |    |    |            |            |     |    |    |     |
|      |                                 |    |                          |            |    |    |            |            |     |    |    |     |
|      |                                 |    |                          |            |    |    |            |            |     |    |    |     |
|      | SBK<br>BNK<br>WGF               |    |                          | WGF<br>WHF |    |    | WGF<br>WHF |            |     |    |    |     |
|      |                                 |    |                          |            |    |    |            |            |     |    |    |     |
|      |                                 |    |                          |            |    |    |            |            |     |    |    |     |
|      | SBK<br>BNK<br>BLW<br>BLK<br>WHF |    | WHF                      | SBK<br>WHF |    |    | WGF<br>WHF |            | WGF |    |    |     |
|      | SBK<br>BNK                      |    | SBK<br>BLW<br>BLK<br>WHF |            |    |    |            | WGF<br>WHF |     |    |    |     |
|      |                                 |    |                          |            |    |    |            |            |     |    |    |     |

Ball Screw

## Standard combinations of outer diameters and leads of the screw shafts

| Shaft diameter | Lead |   |           |  |                                      |   |   |                                      |    |  |  |
|----------------|------|---|-----------|--|--------------------------------------|---|---|--------------------------------------|----|--|--|
|                | 1    | 2 | 4         | 5  | 6                                    | 8 | 10  | 12                                   | 15 | 16   |  |
| 30             |      |   |           |  |                                      |   |   |                                      |    |  |  |
| 32             |      |   | DIK<br>DK | SBN-V<br>BIF-V<br>BNFN-V<br>DIK<br>BNF-V<br>DK | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK |   | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK<br>BNT     | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK |    | SBN-V<br>BIF-V<br>BNFN-V                       |  |
| 36             |      |   |           |  |                                      |   | SBN-V<br>BIF-V<br>BNFN-V<br>DIK<br>BNF-V<br>BNT | SBN-V<br>BIF-V<br>BNF-V<br>DK        |    | SBN-V<br>BIF-V<br>BNFN-V<br>BNF-V              |  |
| 40             |      |   |           |  |                                      |   | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK            | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK |    | SBN-V<br>BIF-V<br>BNFN-V<br>DIK<br>BNF-V<br>DK |  |
| 45             |      |   |           |  |                                      |   | SBN-V<br>BIF-V<br>BNFN-V<br>BNF-V               | SBN-V<br>BIF-V<br>BNF-V<br>BNT       |    | SBN-V<br>BIF-V                                 |  |
| 50             |      |   |           |  |                                      |   | SBN-V<br>BIF-V<br>BNFN-V<br>DIK<br>BNF-V<br>DK  | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK |    | SBN-V<br>BIF-V<br>DIK<br>BNF-V<br>DK           |  |
| 55             |      |   |           |  |                                      |   | BNFN<br>BNF                                     | BNFN<br>BNF                          |    | BNFN<br>BNF                                    |  |
| 63             |      |   |           |  |                                      |   | BNFN<br>DIK<br>BNF<br>DK                        | BNFN<br>DIK<br>BNF<br>DK             |    | BNFN<br>BNF                                    |  |
| 70             |      |   |           |  |                                      |   | BNFN<br>BNF                                     | BNFN<br>BNF                          |    |  |  |
| 80             |      |   |           |  |                                      |   | BNFN<br>BNF                                     | BNFN                                 |    |  |  |
| 100            |      |   |           |  |                                      |   |   |                                      |    |  |  |

## Positioning Ball Screw


Unit: mm

| Lead  |     |    |    |     |                   |                   |    |                   |     |    |     |     |
|---|-----|----|----|-----|-------------------|-------------------|----|-------------------|-----|----|-----|-----|
|   | 20  | 24 | 25 | 30  | 32                | 36                | 40 | 50                | 60  | 80 | 90  | 100 |
|   |     |    |    |     |                   |                   |    |                   | WGF |    | WGF |     |
| SBK   |     |    |    |     | SBK<br>BLW<br>BLK |                   |    |                   |     |    |     |     |
| SBN-V<br>SBK<br>BIF-V<br>BNF-V<br>BLK       | BLK |    |    |     |                   | SBK<br>BLW<br>BLK |    |                   |     |    |     |     |
| SBN-V<br>SBK<br>BIF-V<br>DKN<br>BNF-V<br>DK |     |    |    | SBK |                   | SBK<br>BLW<br>BLK |    |                   | WGF |    |     |     |
| SBN-V<br>BIF-V<br>BNF-V                     |     |    |    |     |                   |                   |    |                   |     |    |     |     |
| SBN-V<br>SBK<br>BIF-V<br>DKN<br>BNF-V<br>DK |     |    |    | SBK |                   | SBK               |    | SBK<br>BLW<br>BLK |     |    |     | WGF |
| SBK<br>BNFN<br>BNF                          |     |    |    | SBK |                   | SBK               |    |                   |     |    |     |     |
| BNFN<br>DKN<br>BNF<br>DK                    |     |    |    |     |                   |                   |    |                   |     |    |     |     |
| BNFN<br>BNF                                 |     |    |    |     |                   |                   |    |                   |     |    |     |     |
| BNFN<br>BNF                                 |     |    |    |     |                   |                   |    |                   |     |    |     |     |
| BNFN<br>BNF                                 |     |    |    |     |                   |                   |    |                   |     |    |     |     |

Ball Screw

# SBN-V Small With Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



| Model No.   | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|-------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|             |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| SBN 1604V-5 | 16                              | 4          | 16.5                                 | 13.8                        | 1×2.5                                  | 5.3               | 8                     | 281                   |
| SBN 1605V-5 | 16                              | 5          | 16.75                                | 13.2                        | 1×2.5                                  | 9.2               | 12.9                  | 309                   |
| SBN 2004V-5 | 20                              | 4          | 20.5                                 | 17.8                        | 1×2.5                                  | 5.9               | 10.1                  | 335                   |
| SBN 2005V-5 | 20                              | 5          | 20.75                                | 17.2                        | 1×2.5                                  | 10.3              | 16.2                  | 370                   |
| SBN 2010V-5 | 20                              | 10         | 20.75                                | 17.2                        | 1×2.5                                  | 10.2              | 16.4                  | 362                   |
| SBN 2504V-5 | 25                              | 4          | 25.5                                 | 22.8                        | 1×2.5                                  | 6.4               | 12.7                  | 400                   |
| SBN 2505V-5 | 25                              | 5          | 25.75                                | 22.2                        | 1×2.5                                  | 11.3              | 20.3                  | 442                   |
| SBN 2506V-5 | 25                              | 6          | 26                                   | 21.4                        | 1×2.5                                  | 15.4              | 25.4                  | 457                   |
| SBN 2805V-5 | 28                              | 5          | 28.75                                | 25.2                        | 1×2.5                                  | 11.8              | 22.8                  | 483                   |
| SBN 3205V-5 | 32                              | 5          | 32.75                                | 29.2                        | 1×2.5                                  | 12.6              | 26.1                  | 536                   |
| SBN 3206V-5 | 32                              | 6          | 33                                   | 28.4                        | 1×2.5                                  | 17.2              | 32.7                  | 555                   |

## Model number coding

**SBN1604V-5 QZ RR G0 +1200L C5**

Model No.

Contamination protection accessory symbol (\*1)


Accuracy symbol (\*2)

Overall screw shaft length (in mm)

With QZ lubricator  
(No code without QZ lubricator)

Symbol for Clearance in the axial direction  
(G0 for all SBN-V variations)

(\*1) See [A15-334](#). (\*2) See [A15-12](#).



Unit: mm

|  | Nut dimensions        |                                   |                                  |    |                |     |                                     |                       | Screw shaft inertial moment/mm<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-----------------------|-----------------------------------|----------------------------------|----|----------------|-----|-------------------------------------|-----------------------|---|----------------|--------------------|---|
|  | Outer diameter<br>Dg6 | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h | Lubrication hole<br>A |   |                |                    |   |
|  | 36                    | 59                                | 53                               | 11 | 42             | 47  | 5.5 × 9.5 × 5.5                     | M6                    | 5.05 × 10 <sup>-8</sup>                                 | 0.42           | 1.42               | 5000  |
|  | 40                    | 60                                | 56                               | 10 | 46             | 50  | 4.5 × 8 × 4.5                       | M6                    | 5.05 × 10 <sup>-8</sup>                                 | 0.5            | 1.37               | 5000  |
|  | 40                    | 63                                | 49                               | 11 | 38             | 51  | 5.5 × 9.5 × 5.5                     | M6                    | 1.23 × 10 <sup>-7</sup>                                 | 0.43           | 2.22               | 5000  |
|  | 44                    | 67                                | 56                               | 11 | 45             | 55  | 5.5 × 9.5 × 5.5                     | M6                    | 1.23 × 10 <sup>-7</sup>                                 | 0.61           | 2.6                | 5000  |
|  | 46                    | 74                                | 90                               | 15 | 75             | 59  | 5.5 × 9.5 × 5.5                     | M6                    | 1.23 × 10 <sup>-7</sup>                                 | 1.06           | 2.33               | 5000  |
|  | 46                    | 69                                | 48                               | 11 | 37             | 57  | 5.5 × 9.5 × 5.5                     | M6                    | 3.01 × 10 <sup>-7</sup>                                 | 0.55           | 3.6                | 5000  |
|  | 50                    | 73                                | 55                               | 11 | 44             | 61  | 5.5 × 9.5 × 5.5                     | M6                    | 3.01 × 10 <sup>-7</sup>                                 | 0.72           | 3.52               | 5000  |
|  | 53                    | 76                                | 62                               | 11 | 51             | 64  | 5.5 × 9.5 × 5.5                     | M6                    | 3.01 × 10 <sup>-7</sup>                                 | 0.9            | 3.43               | 5000  |
|  | 55                    | 85                                | 59                               | 12 | 47             | 69  | 6.6 × 11 × 6.5                      | M6                    | 4.74 × 10 <sup>-7</sup>                                 | 0.98           | 4.45               | 4520  |
|  | 58                    | 85                                | 56                               | 12 | 44             | 71  | 6.6 × 11 × 6.5                      | M6                    | 8.08 × 10 <sup>-7</sup>                                 | 0.96           | 5.88               | 3960  |
|  | 62                    | 89                                | 63                               | 12 | 51             | 75  | 6.6 × 11 × 6.5                      | M6                    | 8.08 × 10 <sup>-7</sup>                                 | 1.22           | 5.89               | 3930  |

Axial Clearance

Unit: mm

| Clearance symbol | G0        |
|------------------|-----------|
| Axial Clearance  | 0 or less |

Note)The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details. It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.

The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation when providing a preload equal to 10% of the basic axial dynamic load rating (Ca) and applying an axial load three times greater than the pre-load. These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.


If the applied preload (Fa<sub>0</sub>) is not 0.1 Ca, the rigidity value (K<sub>N</sub>) is obtained from the following equation.

$$K_N = K \left( \frac{F_{a0}}{0.1C_a} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# SBN-V Medium With Preload

|          |        |
|----------|--------|
| DN value | 160000 |
|----------|--------|



| Model No.   | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |           | Rigidity<br>K<br>N/μm |
|-------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------|-----------------------|
|             |                                 |            |                                      |                             |  | Ca<br>kN          | Coa<br>kN |                       |
| SBN 2508V-7 | 25                              | 8          | 26.25                                | 20.5                        | 1×3.5                                  | 26.2              | 43        | 650                   |
| SBN 2510V-5 | 25                              | 10         | 26.25                                | 21.5                        | 1×2.5                                  | 19.6              | 30.9      | 474                   |
| SBN 2810V-3 | 28                              | 10         | 29.75                                | 22.4                        | 1×1.5                                  | 19.5              | 27.8      | 332                   |
| SBN 3210V-7 | 32                              | 10         | 33.75                                | 26.4                        | 1×3.5                                  | 43                | 73.1      | 836.7                 |
| SBN 3212V-5 | 32                              | 12         | 34                                   | 26.1                        | 1×2.5                                  | 37.4              | 58.7      | 612.2                 |
| SBN 3216V-5 | 32                              | 16         | 33.75                                | 26.4                        | 1×2.5                                  | 31.9              | 52.2      | 592                   |
| SBN 3610V-7 | 36                              | 10         | 37.75                                | 30.4                        | 1×3.5                                  | 45.6              | 82.3      | 900                   |
| SBN 3612V-7 | 36                              | 12         | 38                                   | 30.1                        | 1×3.5                                  | 53.2              | 92.6      | 920                   |
| SBN 3616V-5 | 36                              | 16         | 38                                   | 30.1                        | 1×2.5                                  | 39.7              | 66.4      | 662                   |
| SBN 3620V-3 | 36                              | 20         | 37.75                                | 30.5                        | 1×1.5                                  | 21.6              | 32.9      | 398                   |
| SBN 4010V-5 | 40                              | 10         | 41.75                                | 34.4                        | 1×2.5                                  | 35.8              | 65.2      | 708                   |
| SBN 4012V-5 | 40                              | 12         | 42                                   | 34.1                        | 1×2.5                                  | 42                | 73.6      | 735.4                 |
| SBN 4016V-5 | 40                              | 16         | 42                                   | 34.1                        | 1×2.5                                  | 41.9              | 73.8      | 736.6                 |
| SBN 4020V-5 | 40                              | 20         | 41.75                                | 34.4                        | 1×2.5                                  | 35.4              | 65.2      | 706                   |
| SBN 4510V-5 | 45                              | 10         | 46.75                                | 39.5                        | 1×2.5                                  | 37.9              | 73.8      | 780                   |
| SBN 4512V-5 | 45                              | 12         | 47                                   | 39.2                        | 1×2.5                                  | 44.4              | 82.9      | 809.1                 |
| SBN 4516V-5 | 45                              | 16         | 47                                   | 39.2                        | 1×2.5                                  | 44.3              | 83.1      | 810.1                 |
| SBN 4520V-5 | 45                              | 20         | 47                                   | 39.2                        | 1×2.5                                  | 43.9              | 82.5      | 788                   |
| SBN 5010V-5 | 50                              | 10         | 51.75                                | 44.4                        | 1×2.5                                  | 39.4              | 81        | 838                   |
| SBN 5012V-5 | 50                              | 12         | 52.25                                | 43.3                        | 1×2.5                                  | 53.6              | 101.9     | 936                   |
| SBN 5016V-5 | 50                              | 16         | 52.7                                 | 42.9                        | 1×2.5                                  | 89                | 167.7     | 1228                  |
| SBN 5020V-5 | 50                              | 20         | 52.7                                 | 42.9                        | 1×2.5                                  | 88.7              | 167.7     | 1228                  |

## Model number coding

**SBN4012V-5 QZ RR G0 +1200L C5**

Model No.

Contamination protection accessory symbol (\*)

Accuracy symbol (\*)


Overall screw shaft length (in mm)

With QZ lubricator  
(No code without QZ lubricator)

Symbol for Clearance in the axial direction  
(G0 for all SBN-V variations)

(\*) See **A15-334**. (\*) See **A15-12**.





Unit: mm

|  | Nut dimensions        |                                   |                                  |    |                |     |                                     |                       | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass | Shaft mass | Permissible rotational speed |
|--|-----------------------|-----------------------------------|----------------------------------|----|----------------|-----|-------------------------------------|-----------------------|---|----------|------------|------------------------------|
|  | Outer diameter<br>Dg6 | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h | Lubrication hole<br>A |   |          |            |                              |
|  | 58                    | 85                                | 98                               | 15 | 83             | 71  | 6.6 × 11 × 6.5                      | M6                    | 3.01 × 10 <sup>-7</sup>                     | 1.5      | 3.51       | 5000                         |
|  | 58                    | 85                                | 100                              | 18 | 82             | 71  | 6.6 × 11 × 6.5                      | M6                    | 3.01 × 10 <sup>-7</sup>                     | 1.31     | 3.5        | 5000                         |
|  | 65                    | 106                               | 88                               | 18 | 70             | 85  | 11 × 17.5 × 11                      | M6                    | 4.74 × 10 <sup>-7</sup>                     | 2.41     | 4.15       | 5000                         |
|  | 74                    | 108                               | 120                              | 15 | 105            | 90  | 9 × 14 × 8.5                        | M6                    | 8.08 × 10 <sup>-7</sup>                     | 3.1      | 5.53       | 4740                         |
|  | 76                    | 121                               | 117                              | 18 | 99             | 98  | 11 × 17.5 × 11                      | M6                    | 8.08 × 10 <sup>-7</sup>                     | 3.7      | 5.7        | 4700                         |
|  | 74                    | 108                               | 139                              | 18 | 121            | 90  | 9 × 14 × 8.5                        | M6                    | 8.08 × 10 <sup>-7</sup>                     | 3.81     | 5.82       | 4740                         |
|  | 75                    | 120                               | 123                              | 18 | 105            | 98  | 11 × 17.5 × 11                      | M6                    | 1.29 × 10 <sup>-6</sup>                     | 3.82     | 7.1        | 4230                         |
|  | 78                    | 123                               | 140                              | 18 | 122            | 100 | 11 × 17.5 × 11                      | M6                    | 1.29 × 10 <sup>-6</sup>                     | 4.34     | 7.99       | 4210                         |
|  | 78                    | 123                               | 140                              | 18 | 122            | 100 | 11 × 17.5 × 11                      | M6                    | 1.29 × 10 <sup>-6</sup>                     | 4.31     | 7.99       | 4210                         |
|  | 75                    | 114                               | 122                              | 18 | 104            | 93  | 11 × 17.5 × 11                      | M6                    | 1.29 × 10 <sup>-6</sup>                     | 3.4      | 7.54       | 4230                         |
|  | 82                    | 124                               | 103                              | 18 | 85             | 102 | 11 × 17.5 × 11                      | M6                    | 1.97 × 10 <sup>-6</sup>                     | 3.61     | 8.87       | 3830                         |
|  | 84                    | 126                               | 119                              | 18 | 101            | 104 | 11 × 17.5 × 11                      | M6                    | 1.97 × 10 <sup>-6</sup>                     | 4.2      | 8.83       | 3800                         |
|  | 84                    | 126                               | 144                              | 18 | 126            | 104 | 11 × 17.5 × 11                      | M6                    | 1.97 × 10 <sup>-6</sup>                     | 4.9      | 9.09       | 3800                         |
|  | 82                    | 126                               | 162                              | 18 | 144            | 104 | 11 × 17.5 × 11                      | M6                    | 1.97 × 10 <sup>-6</sup>                     | 5.17     | 9.37       | 3830                         |
|  | 88                    | 132                               | 111                              | 18 | 93             | 110 | 11 × 17.5 × 11                      | Rc1/8<br>(PT1/8)      | 3.16 × 10 <sup>-6</sup>                     | 4.29     | 11.36      | 3420                         |
|  | 90                    | 130                               | 119                              | 18 | 101            | 110 | 11 × 17.5 × 11                      |                       | 3.16 × 10 <sup>-6</sup>                     | 4.6      | 11.32      | 3400                         |
|  | 90                    | 130                               | 140                              | 18 | 122            | 110 | 11 × 17.5 × 11                      |                       | 3.16 × 10 <sup>-6</sup>                     | 5.3      | 11.61      | 3400                         |
|  | 90                    | 130                               | 162                              | 18 | 144            | 110 | 11 × 17.5 × 11                      |                       | 3.16 × 10 <sup>-6</sup>                     | 5.96     | 11.1       | 3400                         |
|  | 93                    | 135                               | 103                              | 18 | 85             | 113 | 11 × 17.5 × 11                      |                       | 4.82 × 10 <sup>-6</sup>                     | 4.28     | 14.16      | 3090                         |
|  | 100                   | 146                               | 123                              | 22 | 101            | 122 | 14 × 20 × 13                        |                       | 4.82 × 10 <sup>-6</sup>                     | 6.12     | 13.82      | 3060                         |
|  | 105                   | 152                               | 164                              | 25 | 139            | 128 | 14 × 20 × 13                        |                       | 4.82 × 10 <sup>-6</sup>                     | 8.82     | 13.71      | 3030                         |
|  | 105                   | 152                               | 201                              | 28 | 173            | 128 | 14 × 20 × 13                        |                       | 4.82 × 10 <sup>-6</sup>                     | 10.63    | 14.05      | 3030                         |

Axial Clearance

Unit: mm

| Clearance symbol | G0        |
|------------------|-----------|
| Axial Clearance  | 0 or less |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.  
It is not possible to chamfer both ends of the screw shaft. When designing your system this way, contact THK.

The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation when providing a preload equal to 10% of the basic axial dynamic load rating (Ca) and applying an axial load three times greater than the pre-load.

These values do not include the rigidity of the components related to mounting the ball screw nut.

Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.


If the applied preload (Fa<sub>0</sub>) is not 0.1 Ca, the rigidity value (K<sub>w</sub>) is obtained from the following equation.

$$K_w = K \left( \frac{F_{a0}}{0.1 C_a} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# SBK Small With Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| SBK 1520-3.6 | 15                              | 20         | 15.75                                | 12.2                        | 1×1.8                                  | 5.8               | 7.8                   | 178                   |
| SBK 1616-3.6 | 16                              | 16         | 16.65                                | 13.5                        | 1×1.8                                  | 4.6               | 6.4                   | 182                   |
| SBK 2010-5.6 | 20                              | 10         | 20.75                                | 17.2                        | 1×2.8                                  | 10.7              | 17.3                  | 353                   |
| SBK 2020-3.6 | 20                              | 20         | 20.75                                | 17.2                        | 1×1.8                                  | 7                 | 10.5                  | 229                   |
| SBK 2030-3.6 | 20                              | 30         | 20.75                                | 17.2                        | 1×1.8                                  | 6.9               | 11.2                  | 236                   |
| SBK 2520-3.6 | 25                              | 20         | 26                                   | 21.5                        | 1×1.8                                  | 11                | 16.9                  | 292                   |
| SBK 2525-3.6 | 25                              | 25         | 26                                   | 21.5                        | 1×1.8                                  | 10.8              | 16.9                  | 290                   |
| SBK 3220-5.6 | 32                              | 20         | 33.25                                | 27.9                        | 1×2.8                                  | 23.6              | 41.1                  | 565                   |
| SBK 3232-5.6 | 32                              | 32         | 33.25                                | 27.9                        | 1×2.8                                  | 23.1              | 41.8                  | 567                   |

Axial Clearance

Unit: mm

|                  |           |
|------------------|-----------|
| Clearance symbol | G0        |
| Axial Clearance  | 0 or less |

## Model number coding

**SBK2525-3.6 QZ G0 +1200L C5**


Model Number

Overall screw shaft  
length (in mm)

Accuracy symbol (\*1)

Symbol for clearance in the axial direction  
(G0 for all SBK variations)With QZ Lubricator  
(no symbol if the model is without a QZ Lubricator)(\*1) See **A15-12**.

## Positioning Ball Screw



Unit: mm

|  | Nut dimensions      |                                   |                                  |    |                |     |                |                |                       | Screw shaft inertial moment/mm<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|---------------------|-----------------------------------|----------------------------------|----|----------------|-----|----------------|----------------|-----------------------|---|----------------|--------------------|---|
|  | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | Lubrication hole<br>A |   |                |                    |   |
|  | 38                  | 62                                | 54                               | 10 | 38.5           | 49  | 5.5            | 39             | M6                    | $3.90 \times 10^{-8}$                                   | 0.41           | 1.27               | 5000  |
|  | 33                  | 54                                | 45                               | 10 | 29.5           | 43  | 4.5            | 38             | M6                    | $5.05 \times 10^{-8}$                                   | 0.25           | 1.46               | 5000  |
|  | 40                  | 65                                | 45                               | 10 | 29.5           | 53  | 5.5            | 49             | M6                    | $1.23 \times 10^{-7}$                                   | 0.37           | 2.18               | 5000  |
|  | 40                  | 65                                | 54                               | 10 | 38.5           | 53  | 5.5            | 49             | M6                    | $1.23 \times 10^{-7}$                                   | 0.43           | 2.32               | 5000  |
|  | 40                  | 65                                | 71                               | 10 | 55.5           | 53  | 5.5            | 49             | M6                    | $1.23 \times 10^{-7}$                                   | 0.55           | 2.36               | 5000  |
|  | 47                  | 74                                | 57                               | 12 | 38             | 60  | 6.6            | 56             | M6                    | $3.01 \times 10^{-7}$                                   | 0.59           | 3.58               | 5000  |
|  | 47                  | 74                                | 68                               | 12 | 49             | 60  | 6.6            | 56             | M6                    | $3.01 \times 10^{-7}$                                   | 0.69           | 3.63               | 5000  |
|  | 58                  | 92                                | 82                               | 15 | 58             | 74  | 9              | 68             | M6                    | $8.08 \times 10^{-7}$                                   | 1.23           | 5.82               | 3900  |
|  | 58                  | 92                                | 118                              | 15 | 94             | 74  | 9              | 68             | M6                    | $8.08 \times 10^{-7}$                                   | 1.70           | 5.99               | 3900  |

Note) The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation when providing a preload equal to 10% of the basic axial dynamic load rating (Ca) and applying an axial load three times greater than the pre-load.

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.


If the applied preload (Fa<sub>0</sub>) is not 0.1 Ca, the rigidity value (K<sub>v</sub>) is obtained from the following equation.

$$K_v = K \left( \frac{Fa_0}{0.1Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# SBK Medium With Preload

|          |                           |        |
|----------|---------------------------|--------|
| DN value | SBK3636,4040,5050         | 210000 |
|          | All other Model SBK units | 160000 |



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                      | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|----------------------|-----------------------|
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>a</sub><br>kN |                       |
| SBK 3620-7.6 | 36                              | 20         | 37.75                                | 30.4                        | 1×3.8                                  | 48.5              | 85                   | 870                   |
| SBK 3636-5.6 | 36                              | 36         | 37.75                                | 31.4                        | 1×2.8                                  | 36.6              | 64.7                 | 460                   |
| SBK 4020-7.6 | 40                              | 20         | 42                                   | 34.1                        | 1×3.8                                  | 59.7              | 112.7                | 970                   |
| SBK 4030-7.6 | 40                              | 30         | 42                                   | 34.1                        | 1×3.8                                  | 59.2              | 107.5                | 970                   |
| SBK 4040-5.6 | 40                              | 40         | 42                                   | 34.9                        | 1×2.8                                  | 44.8              | 80.3                 | 520                   |
| SBK 5020-7.6 | 50                              | 20         | 52                                   | 44.1                        | 1×3.8                                  | 66.8              | 141.9                | 1170                  |
| SBK 5030-7.6 | 50                              | 30         | 52                                   | 44.1                        | 1×3.8                                  | 66.5              | 135                  | 1170                  |
| SBK 5036-7.6 | 50                              | 36         | 52                                   | 44.1                        | 1×3.8                                  | 65.9              | 135                  | 1170                  |
| SBK 5050-5.6 | 50                              | 50         | 52                                   | 44.9                        | 1×2.8                                  | 50.3              | 102.4                | 630                   |
| SBK 5520-7.6 | 55                              | 20         | 57                                   | 49.1                        | 1×3.8                                  | 69.8              | 156.4                | 1250                  |
| SBK 5530-7.6 | 55                              | 30         | 57                                   | 49.1                        | 1×3.8                                  | 69.2              | 147                  | 1250                  |
| SBK 5536-7.6 | 55                              | 36         | 57                                   | 49.1                        | 1×3.8                                  | 69.1              | 148.7                | 1260                  |

Note) With model SBK, the raising of both ends of the thread groove is not available. When designing your system this way, contact THK.

Axial Clearance

Unit: mm

|                  |           |
|------------------|-----------|
| Clearance symbol | G0        |
| Axial Clearance  | 0 or less |


### Model number coding

**SBK3620-7.6 RR G0 +1500L C5**

Model number    Seal symbol (\*1)    Overall screw shaft length (in mm)    Accuracy symbol (\*2)

Symbol for clearance in the axial direction (G0 for all SBK variations)

(\*1) See **A15-334**. (\*2) See **A15-12**.



Unit: mm

|    | Nut dimensions      |                                   |                                  |     |                |     |                |                  | Screw shaft inertial moment/mm<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|----|---------------------|-----------------------------------|----------------------------------|-----|----------------|-----|----------------|------------------|---|----------------|--------------------|---|
|    | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H   | B <sub>1</sub> | PCD | d <sub>1</sub> | T <sub>w</sub>   |   |                |                    |   |
| 73 | 114                 | 110                               | 18                               | 81  | 93             | 11  | 86             | Rc1/8<br>(PT1/8) | 1.29×10 <sup>-6</sup>                                   | 3.4            | 5.0                | 4230  |
| 73 | 114                 | 134                               | 18                               | 105 | 93             | 11  | 86             |                  | 1.29×10 <sup>-6</sup>                                   | 3.37           | 7.43               | 5000  |
| 80 | 136                 | 110                               | 20                               | 79  | 112            | 14  | 103            |                  | 1.97×10 <sup>-6</sup>                                   | 4.5            | 5.7                | 3800  |
| 80 | 136                 | 148                               | 20                               | 117 | 112            | 14  | 103            |                  | 1.97×10 <sup>-6</sup>                                   | 5.6            | 7.0                | 3800  |
| 80 | 136                 | 146                               | 20                               | 115 | 112            | 14  | 103            |                  | 1.97×10 <sup>-6</sup>                                   | 4.74           | 9.16               | 5000  |
| 90 | 146                 | 110                               | 22                               | 77  | 122            | 14  | 110            |                  | 4.82×10 <sup>-6</sup>                                   | 5.3            | 10.2               | 3070  |
| 90 | 146                 | 149                               | 22                               | 116 | 122            | 14  | 110            |                  | 4.82×10 <sup>-6</sup>                                   | 6.6            | 11.9               | 3070  |
| 90 | 146                 | 172                               | 22                               | 139 | 122            | 14  | 110            |                  | 4.82×10 <sup>-6</sup>                                   | 7.4            | 12.5               | 3070  |
| 90 | 146                 | 175                               | 22                               | 142 | 122            | 14  | 110            |                  | 4.82×10 <sup>-6</sup>                                   | 6.46           | 14.72              | 4030  |
| 96 | 152                 | 110                               | 22                               | 77  | 128            | 14  | 114            |                  | 7.05×10 <sup>-6</sup>                                   | 5.7            | 13.0               | 2800  |
| 96 | 152                 | 149                               | 22                               | 116 | 128            | 14  | 114            |                  | 7.05×10 <sup>-6</sup>                                   | 7.2            | 14.8               | 2800  |
| 96 | 152                 | 172                               | 22                               | 139 | 128            | 14  | 114            |                  | 7.05×10 <sup>-6</sup>                                   | 8.1            | 15.5               | 2800  |

Note) The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation when providing a preload equal to 10% of the basic axial dynamic load rating (Ca) and applying an axial load three times greater than the pre-load.

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.


If the applied preload (Fa<sub>0</sub>) is not 0.1 Ca, the rigidity value (K<sub>n</sub>) is obtained from the following equation.

$$K_n = K \left( \frac{Fa_0}{0.1Ca} \right)^{\frac{1}{3}}$$


K: Rigidity value in the dimensional table

# BIF-V Small With Preload

|          |        |
|----------|--------|
| DN value | 100000 |
|----------|--------|



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| BIF 1604V-5  | 16                              | 4          | 16.5                                 | 13.8                        | 1×2.5                                  | 4.3               | 8.7                   | 298                   |
| BIF 1605V-5  | 16                              | 5          | 16.75                                | 13.2                        | 1×2.5                                  | 7.4               | 13.9                  | 330                   |
| BIF 2004V-5  | 20                              | 4          | 20.5                                 | 17.8                        | 1×2.5                                  | 4.8               | 10.9                  | 360                   |
| BIF 2004V-10 | 20                              | 4          | 20.5                                 | 17.8                        | 2×2.5                                  | 8.6               | 21.8                  | 692                   |
| BIF 2005V-5  | 20                              | 5          | 20.75                                | 17.2                        | 1×2.5                                  | 8.3               | 17.5                  | 390                   |
| BIF 2005V-10 | 20                              | 5          | 20.75                                | 17.2                        | 2×2.5                                  | 15.1              | 35                    | 762                   |
| BIF 2010V-5  | 20                              | 10         | 20.75                                | 17.2                        | 1×2.5                                  | 8.3               | 17.6                  | 394                   |
| BIF 2504V-5  | 25                              | 4          | 25.5                                 | 22.8                        | 1×2.5                                  | 5.2               | 13.7                  | 426                   |
| BIF 2504V-10 | 25                              | 4          | 25.5                                 | 22.8                        | 2×2.5                                  | 9.5               | 27.4                  | 824                   |
| BIF 2505V-5  | 25                              | 5          | 25.75                                | 22.2                        | 1×2.5                                  | 9.2               | 21.9                  | 470                   |
| BIF 2505V-10 | 25                              | 5          | 25.75                                | 22.2                        | 2×2.5                                  | 16.7              | 43.9                  | 910                   |
| BIF 2506V-5  | 25                              | 6          | 26                                   | 21.4                        | 1×2.5                                  | 12.4              | 27.4                  | 482                   |
| BIF 2506V-10 | 25                              | 6          | 26                                   | 21.4                        | 2×2.5                                  | 22.6              | 54.8                  | 934                   |
| BIF 2805V-5  | 28                              | 5          | 28.75                                | 25.2                        | 1×2.5                                  | 9.7               | 24.6                  | 520                   |
| BIF 2805V-10 | 28                              | 5          | 28.75                                | 25.2                        | 2×2.5                                  | 17.5              | 49.2                  | 1000                  |
| BIF 2806V-5  | 28                              | 6          | 28.75                                | 25.2                        | 1×2.5                                  | 9.6               | 24.6                  | 520                   |
| BIF 2806V-10 | 28                              | 6          | 28.75                                | 25.2                        | 2×2.5                                  | 17.5              | 49.2                  | 1000                  |
| BIF 3205V-5  | 32                              | 5          | 32.75                                | 29.2                        | 1×2.5                                  | 10.2              | 28.1                  | 570                   |
| BIF 3205V-10 | 32                              | 5          | 32.75                                | 29.2                        | 2×2.5                                  | 18.5              | 56.3                  | 1110                  |
| BIF 3206V-5  | 32                              | 6          | 33                                   | 28.4                        | 1×2.5                                  | 13.9              | 35.2                  | 600                   |
| BIF 3206V-10 | 32                              | 6          | 33                                   | 28.4                        | 2×2.5                                  | 25.2              | 70.3                  | 1150                  |




Unit: mm

|    | Nut dimensions |                 |                |    |                |                 |                                     |                         | Screw shaft inertial moment/mm | Nut mass | Shaft mass | Permissible rotational speed |
|----|----------------|-----------------|----------------|----|----------------|-----------------|-------------------------------------|-------------------------|--------------------------------|----------|------------|------------------------------|
|    | Outer diameter | Flange diameter | Overall length |    |                |                 |                                     | Lubrication hole        |                                |          |            |                              |
|    | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | PCD             | d <sub>1</sub> × d <sub>2</sub> × h | A                       |                                |          |            |                              |
| 36 | 59             | 53              | 11             | 42 | 47             | 5.5 × 9.5 × 5.5 | M6                                  | 5.05 × 10 <sup>-8</sup> | 0.42                           | 1.42     | 5000       |                              |
| 40 | 60             | 56              | 10             | 46 | 50             | 4.5 × 8 × 4.5   | M6                                  | 5.05 × 10 <sup>-8</sup> | 0.56                           | 1.37     | 5000       |                              |
| 40 | 63             | 49              | 11             | 38 | 51             | 5.5 × 9.5 × 5.5 | M6                                  | 1.23 × 10 <sup>-7</sup> | 0.43                           | 2.22     | 4870       |                              |
| 40 | 63             | 73              | 11             | 62 | 51             | 5.5 × 9.5 × 5.5 | M6                                  | 1.23 × 10 <sup>-7</sup> | 0.55                           | 2.22     | 4870       |                              |
| 44 | 67             | 56              | 11             | 45 | 55             | 5.5 × 9.5 × 5.5 | M6                                  | 1.23 × 10 <sup>-7</sup> | 0.57                           | 2.19     | 4810       |                              |
| 44 | 67             | 86              | 11             | 75 | 55             | 5.5 × 9.5 × 5.5 | M6                                  | 1.23 × 10 <sup>-7</sup> | 0.79                           | 2.19     | 4810       |                              |
| 46 | 74             | 90              | 15             | 75 | 59             | 5.5 × 9.5 × 5.5 | M6                                  | 1.23 × 10 <sup>-7</sup> | 1.06                           | 2.46     | 4810       |                              |
| 46 | 69             | 48              | 11             | 37 | 57             | 5.5 × 9.5 × 5.5 | M6                                  | 3.01 × 10 <sup>-7</sup> | 0.55                           | 3.6      | 3920       |                              |
| 46 | 69             | 72              | 11             | 61 | 57             | 5.5 × 9.5 × 5.5 | M6                                  | 3.01 × 10 <sup>-7</sup> | 0.66                           | 3.6      | 3920       |                              |
| 50 | 73             | 55              | 11             | 44 | 61             | 5.5 × 9.5 × 5.5 | M6                                  | 3.01 × 10 <sup>-7</sup> | 0.75                           | 3.52     | 3880       |                              |
| 50 | 73             | 85              | 11             | 74 | 61             | 5.5 × 9.5 × 5.5 | M6                                  | 3.01 × 10 <sup>-7</sup> | 0.96                           | 3.52     | 3880       |                              |
| 53 | 76             | 62              | 11             | 51 | 64             | 5.5 × 9.5 × 5.5 | M6                                  | 3.01 × 10 <sup>-7</sup> | 0.9                            | 3.43     | 3840       |                              |
| 53 | 76             | 98              | 11             | 87 | 64             | 5.5 × 9.5 × 5.5 | M6                                  | 3.01 × 10 <sup>-7</sup> | 1.22                           | 3.43     | 3840       |                              |
| 55 | 85             | 59              | 12             | 47 | 69             | 6.6 × 11 × 6.5  | M6                                  | 4.74 × 10 <sup>-7</sup> | 0.98                           | 4.35     | 3470       |                              |
| 55 | 85             | 89              | 12             | 77 | 69             | 6.6 × 11 × 6.5  | M6                                  | 4.74 × 10 <sup>-7</sup> | 1.34                           | 4.35     | 3470       |                              |
| 55 | 85             | 68              | 12             | 56 | 69             | 6.6 × 11 × 6.5  | M6                                  | 4.74 × 10 <sup>-7</sup> | 1.09                           | 4.52     | 3470       |                              |
| 55 | 85             | 104             | 12             | 92 | 69             | 6.6 × 11 × 6.5  | M6                                  | 4.74 × 10 <sup>-7</sup> | 1.52                           | 4.52     | 3470       |                              |
| 58 | 85             | 56              | 12             | 44 | 71             | 6.6 × 11 × 6.5  | M6                                  | 8.08 × 10 <sup>-7</sup> | 0.94                           | 5.89     | 3050       |                              |
| 58 | 85             | 86              | 12             | 74 | 71             | 6.6 × 11 × 6.5  | M6                                  | 8.08 × 10 <sup>-7</sup> | 1.31                           | 5.89     | 3050       |                              |
| 62 | 89             | 63              | 12             | 51 | 75             | 6.6 × 11 × 6.5  | M6                                  | 8.08 × 10 <sup>-7</sup> | 1.21                           | 5.88     | 3030       |                              |
| 62 | 89             | 99              | 12             | 87 | 75             | 6.6 × 11 × 6.5  | M6                                  | 8.08 × 10 <sup>-7</sup> | 1.75                           | 5.88     | 3030       |                              |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.


# BIF-V Medium With Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| BIF 2508V-5  | 25                              | 8          | 26.25                                | 20.5                        | 1×2.5                                  | 15.8              | 32.9                  | 500                   |
| BIF 2508V-7  | 25                              | 8          | 26.25                                | 20.5                        | 1×3.5                                  | 21.1              | 46                    | 688                   |
| BIF 2508V-10 | 25                              | 8          | 26.25                                | 20.5                        | 2×2.5                                  | 28.7              | 65.7                  | 968                   |
| BIF 2510V-5  | 25                              | 10         | 26.25                                | 21.5                        | 1×2.5                                  | 15.8              | 32.9                  | 500                   |
| BIF 2810V-3  | 28                              | 10         | 29.75                                | 22.4                        | 1×1.5                                  | 15.6              | 29.4                  | 350                   |
| BIF 3210V-5  | 32                              | 10         | 33.75                                | 26.4                        | 1×2.5                                  | 26                | 56.2                  | 640                   |
| BIF 3210V-7  | 32                              | 10         | 33.75                                | 26.4                        | 1×3.5                                  | 34.8              | 78.6                  | 874                   |
| BIF 3210V-10 | 32                              | 10         | 33.75                                | 26.4                        | 2×2.5                                  | 47.3              | 112.3                 | 1128                  |
| BIF 3212V-5  | 32                              | 12         | 34                                   | 26.1                        | 1×2.5                                  | 30.2              | 63.2                  | 644                   |
| BIF 3212V-7  | 32                              | 12         | 34                                   | 26.1                        | 1×3.5                                  | 40.4              | 88.5                  | 888                   |
| BIF 3216V-5  | 32                              | 16         | 33.75                                | 26.4                        | 1×2.5                                  | 25.9              | 56.5                  | 636                   |
| BIF 3610V-5  | 36                              | 10         | 37.75                                | 30.5                        | 1×2.5                                  | 27.6              | 63.3                  | 696                   |
| BIF 3610V-7  | 36                              | 10         | 37.75                                | 30.5                        | 1×3.5                                  | 36.9              | 88.6                  | 700                   |
| BIF 3610V-10 | 36                              | 10         | 37.75                                | 30.5                        | 2×2.5                                  | 50.1              | 126.5                 | 1350                  |
| BIF 3612V-5  | 36                              | 12         | 38                                   | 30.1                        | 1×2.5                                  | 32.2              | 71.2                  | 708                   |
| BIF 3612V-7  | 36                              | 12         | 38                                   | 30.1                        | 1×3.5                                  | 43                | 99.6                  | 976                   |
| BIF 3612V-10 | 36                              | 12         | 38                                   | 30.1                        | 2×2.5                                  | 58.4              | 142.3                 | 1372                  |
| BIF 3616V-5  | 36                              | 16         | 38                                   | 30.1                        | 1×2.5                                  | 32.1              | 71.5                  | 710                   |
| BIF 3620V-3  | 36                              | 20         | 37.75                                | 30.5                        | 1×1.5                                  | 17.7              | 38.4                  | 430                   |
| BIF 4010V-5  | 40                              | 10         | 41.75                                | 34.4                        | 1×2.5                                  | 29                | 70.4                  | 750                   |
| BIF 4010V-7  | 40                              | 10         | 41.75                                | 34.4                        | 1×3.5                                  | 38.8              | 98.5                  | 1044                  |
| BIF 4010V-10 | 40                              | 10         | 41.75                                | 34.4                        | 2×2.5                                  | 52.7              | 140.7                 | 1470                  |
| BIF 4012V-5  | 40                              | 12         | 42                                   | 34.1                        | 1×2.5                                  | 33.9              | 79.2                  | 770                   |
| BIF 4012V-7  | 40                              | 12         | 42                                   | 34.1                        | 1×3.5                                  | 45.3              | 110.8                 | 1062                  |
| BIF 4012V-10 | 40                              | 12         | 42                                   | 34.1                        | 2×2.5                                  | 61.6              | 158.3                 | 1490                  |
| BIF 4016V-5  | 40                              | 16         | 42                                   | 34.1                        | 1×2.5                                  | 33.9              | 79.4                  | 772                   |
| BIF 4020V-5  | 40                              | 20         | 41.75                                | 34.4                        | 1×2.5                                  | 28.9              | 71                    | 760                   |






Unit: mm

|  | Nut dimensions |                 |                |    |                |     |                                     |                  | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass | Shaft mass | Permissible rotational speed |
|--|----------------|-----------------|----------------|----|----------------|-----|-------------------------------------|------------------|---|----------|------------|------------------------------|
|  | Outer diameter | Flange diameter | Overall length |    |                |     |                                     | Lubrication hole |   |          |            |                              |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h | A                |   |          |            |                              |
|  | 58             | 85              | 82             | 15 | 67             | 71  | 6.6 × 11 × 6.5                      | M6               | 3.01 × 10 <sup>-7</sup>                     | 1.52     | 3.51       | 4950                         |
|  | 58             | 85              | 98             | 15 | 83             | 71  | 6.6 × 11 × 6.5                      | M6               | 3.01 × 10 <sup>-7</sup>                     | 1.5      | 3.51       | 4950                         |
|  | 58             | 85              | 130            | 15 | 115            | 71  | 6.6 × 11 × 6.5                      | M6               | 3.01 × 10 <sup>-7</sup>                     | 1.93     | 3.51       | 4950                         |
|  | 58             | 85              | 100            | 18 | 82             | 71  | 6.6 × 11 × 6.5                      | M6               | 3.01 × 10 <sup>-7</sup>                     | 1.31     | 3.5        | 4950                         |
|  | 65             | 106             | 88             | 18 | 70             | 85  | 11 × 17.5 × 11                      | M6               | 4.74 × 10 <sup>-7</sup>                     | 2.33     | 4.15       | 4360                         |
|  | 74             | 108             | 100            | 15 | 85             | 90  | 9 × 14 × 8.5                        | M6               | 8.08 × 10 <sup>-7</sup>                     | 2.92     | 5.53       | 3850                         |
|  | 74             | 108             | 120            | 15 | 105            | 90  | 9 × 14 × 8.5                        | M6               | 8.08 × 10 <sup>-7</sup>                     | 3.1      | 5.53       | 3850                         |
|  | 74             | 108             | 160            | 15 | 145            | 90  | 9 × 14 × 8.5                        | M6               | 8.08 × 10 <sup>-7</sup>                     | 4.27     | 5.53       | 3850                         |
|  | 76             | 121             | 117            | 18 | 99             | 98  | 11 × 17.5 × 11                      | M6               | 8.08 × 10 <sup>-7</sup>                     | 3.7      | 5.7        | 3820                         |
|  | 76             | 121             | 146            | 18 | 128            | 98  | 11 × 17.5 × 11                      | M6               | 8.08 × 10 <sup>-7</sup>                     | 3.7      | 5.7        | 3820                         |
|  | 74             | 108             | 139            | 18 | 121            | 90  | 9 × 14 × 8.5                        | M6               | 8.08 × 10 <sup>-7</sup>                     | 3.81     | 5.82       | 3850                         |
|  | 75             | 120             | 111            | 18 | 93             | 98  | 11 × 17.5 × 11                      | M6               | 1.29 × 10 <sup>-6</sup>                     | 3.45     | 7.1        | 3440                         |
|  | 75             | 120             | 123            | 18 | 105            | 98  | 11 × 17.5 × 11                      | M6               | 1.29 × 10 <sup>-6</sup>                     | 3.82     | 7.1        | 3440                         |
|  | 75             | 120             | 171            | 18 | 153            | 98  | 11 × 17.5 × 11                      | M6               | 1.29 × 10 <sup>-6</sup>                     | 4.84     | 7.1        | 3440                         |
|  | 78             | 123             | 123            | 18 | 105            | 100 | 11 × 17.5 × 11                      | M6               | 1.29 × 10 <sup>-6</sup>                     | 4.69     | 7.99       | 3420                         |
|  | 78             | 123             | 140            | 18 | 122            | 100 | 11 × 17.5 × 11                      | M6               | 1.29 × 10 <sup>-6</sup>                     | 4.34     | 7.99       | 3420                         |
|  | 78             | 123             | 195            | 18 | 177            | 100 | 11 × 17.5 × 11                      | M6               | 1.29 × 10 <sup>-6</sup>                     | 5.67     | 7.99       | 3420                         |
|  | 78             | 123             | 140            | 18 | 122            | 100 | 11 × 17.5 × 11                      | M6               | 1.29 × 10 <sup>-6</sup>                     | 4.31     | 7.99       | 3420                         |
|  | 75             | 114             | 122            | 18 | 104            | 93  | 11 × 17.5 × 11                      | M6               | 1.29 × 10 <sup>-6</sup>                     | 3.4      | 7.54       | 3440                         |
|  | 82             | 124             | 103            | 18 | 85             | 102 | 11 × 17.5 × 11                      | M6               | 1.97 × 10 <sup>-6</sup>                     | 3.61     | 8.87       | 3110                         |
|  | 82             | 124             | 123            | 18 | 105            | 102 | 11 × 17.5 × 11                      | M6               | 1.97 × 10 <sup>-6</sup>                     | 3.97     | 8.87       | 3110                         |
|  | 82             | 124             | 163            | 18 | 145            | 102 | 11 × 17.5 × 11                      | M6               | 1.97 × 10 <sup>-6</sup>                     | 5.33     | 8.87       | 3110                         |
|  | 84             | 126             | 119            | 18 | 101            | 104 | 11 × 17.5 × 11                      | M6               | 1.97 × 10 <sup>-6</sup>                     | 4.36     | 8.83       | 3090                         |
|  | 84             | 126             | 143            | 18 | 125            | 104 | 11 × 17.5 × 11                      | M6               | 1.97 × 10 <sup>-6</sup>                     | 4.92     | 8.83       | 3090                         |
|  | 84             | 126             | 191            | 18 | 173            | 104 | 11 × 17.5 × 11                      | M6               | 1.97 × 10 <sup>-6</sup>                     | 6.47     | 8.83       | 3090                         |
|  | 84             | 126             | 144            | 18 | 126            | 104 | 11 × 17.5 × 11                      | M6               | 1.97 × 10 <sup>-6</sup>                     | 4.9      | 9.09       | 3090                         |
|  | 82             | 126             | 162            | 18 | 144            | 104 | 11 × 17.5 × 11                      | M6               | 1.97 × 10 <sup>-6</sup>                     | 5.17     | 9.37       | 3110                         |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.


# BIF-V Medium With Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| BIF 4510V-5  | 45                              | 10         | 46.75                                | 39.5                        | 1×2.5                                  | 30.6              | 79.3                  | 830                   |
| BIF 4510V-10 | 45                              | 10         | 46.75                                | 39.5                        | 2×2.5                                  | 55.6              | 158.5                 | 1610                  |
| BIF 4512V-5  | 45                              | 12         | 47                                   | 39.2                        | 1×2.5                                  | 35.9              | 89.2                  | 846                   |
| BIF 4512V-10 | 45                              | 12         | 47                                   | 39.2                        | 2×2.5                                  | 65.2              | 178.3                 | 1638                  |
| BIF 4516V-5  | 45                              | 16         | 47                                   | 39.2                        | 1×2.5                                  | 35.8              | 89.4                  | 846                   |
| BIF 4520V-5  | 45                              | 20         | 47                                   | 39.2                        | 1×2.5                                  | 35.8              | 89.7                  | 848                   |
| BIF 5010V-5  | 50                              | 10         | 51.75                                | 44.4                        | 1×2.5                                  | 32.1              | 88.1                  | 900                   |
| BIF 5010V-7  | 50                              | 10         | 51.75                                | 44.4                        | 1×3.5                                  | 42.9              | 123.4                 | 1244                  |
| BIF 5010V-10 | 50                              | 10         | 51.75                                | 44.4                        | 2×2.5                                  | 58.2              | 176.3                 | 1750                  |
| BIF 5012V-5  | 50                              | 12         | 52.25                                | 43.3                        | 1×2.5                                  | 43.4              | 110.1                 | 934                   |
| BIF 5012V-7  | 50                              | 12         | 52.25                                | 43.3                        | 1×3.5                                  | 58                | 154.1                 | 1286                  |
| BIF 5012V-10 | 50                              | 12         | 52.25                                | 43.3                        | 2×2.5                                  | 78.8              | 220.2                 | 1808                  |
| BIF 5016V-5  | 50                              | 16         | 52.7                                 | 42.9                        | 1×2.5                                  | 72.6              | 183.1                 | 1220                  |
| BIF 5016V-10 | 50                              | 16         | 52.7                                 | 42.9                        | 2×2.5                                  | 131.8             | 366.2                 | 2364                  |
| BIF 5020V-5  | 50                              | 20         | 52.7                                 | 42.9                        | 1×2.5                                  | 72.5              | 183.6                 | 1222                  |

## Positioning Ball Screw




Unit: mm

|  | Nut dimensions |                 |                |    |                |     |                                     | Screw shaft inertial moment/mm <sup>3</sup> | Nut mass                | Shaft mass | Permissible rotational speed |                   |
|--|----------------|-----------------|----------------|----|----------------|-----|-------------------------------------|---|-------------------------|------------|------------------------------|-------------------|
|  | Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h |   |                         |            |                              | Lubrication hole  |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h | A   | kg·m <sup>2</sup> /mm   | kg         | kg/m                         | min <sup>-1</sup> |
|  | 88             | 132             | 111            | 18 | 93             | 110 | 11 × 17.5 × 11                      | Rc1/8<br>(PT1/8)                            | 3.16 × 10 <sup>-6</sup> | 4.29       | 12.48                        | 2780              |
|  | 88             | 132             | 171            | 18 | 153            | 110 | 11 × 17.5 × 11                      |   | 3.16 × 10 <sup>-6</sup> | 5.97       | 12.48                        | 2780              |
|  | 90             | 130             | 119            | 18 | 101            | 110 | 11 × 17.5 × 11                      |   | 3.16 × 10 <sup>-6</sup> | 4.6        | 11.32                        | 2760              |
|  | 90             | 130             | 191            | 18 | 173            | 110 | 11 × 17.5 × 11                      |   | 3.16 × 10 <sup>-6</sup> | 6.67       | 11.32                        | 2760              |
|  | 90             | 130             | 140            | 18 | 122            | 110 | 11 × 17.5 × 11                      |   | 3.16 × 10 <sup>-6</sup> | 5.3        | 11.61                        | 2760              |
|  | 90             | 130             | 162            | 18 | 144            | 110 | 11 × 17.5 × 11                      |   | 3.16 × 10 <sup>-6</sup> | 5.96       | 11.1                         | 2760              |
|  | 93             | 135             | 103            | 18 | 85             | 113 | 11 × 17.5 × 11                      |   | 4.82 × 10 <sup>-6</sup> | 4.28       | 14.16                        | 2510              |
|  | 93             | 135             | 123            | 18 | 105            | 113 | 11 × 17.5 × 11                      |   | 4.82 × 10 <sup>-6</sup> | 4.94       | 14.16                        | 2510              |
|  | 93             | 135             | 163            | 18 | 145            | 113 | 11 × 17.5 × 11                      |   | 4.82 × 10 <sup>-6</sup> | 6.26       | 14.16                        | 2510              |
|  | 100            | 146             | 123            | 22 | 101            | 122 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 6.12       | 13.82                        | 2480              |
|  | 100            | 146             | 147            | 22 | 125            | 122 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 7.06       | 13.82                        | 2480              |
|  | 100            | 146             | 195            | 22 | 173            | 122 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 8.91       | 13.82                        | 2480              |
|  | 105            | 152             | 164            | 25 | 139            | 128 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 8.82       | 13.71                        | 2460              |
|  | 105            | 152             | 260            | 25 | 235            | 128 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 12.3       | 13.71                        | 2460              |
|  | 105            | 152             | 201            | 28 | 173            | 128 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 10.63      | 14.05                        | 2460              |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See [A15-344](#) for further details.

# BNFN-V Small/Medium With Preload

|          |        |        |
|----------|--------|--------|
| DN value | Small  | 100000 |
|          | Medium | 130000 |




<Small> BNFN1605V/2805V/2806V/3205V

| Model No.      | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                 | Rigidity<br>K<br>N/μm |
|----------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------|-----------------------|
|                |                                 |            |                                      |                             |  | Ca                | C <sub>0a</sub> |                       |
|                |                                 |            |                                      |                             |  | kN                | kN              |                       |
| BNFN 1605V-5   | 16                              | 5          | 16.75                                | 13.2                        | 2 × 2.5                                | 13.5              | 27.9            | 640                   |
| BNFN 2805V-7.5 | 28                              | 5          | 28.75                                | 25.2                        | 3 × 2.5                                | 24.8              | 73.8            | 1470                  |
| BNFN 2806V-7.5 | 28                              | 6          | 28.75                                | 25.2                        | 3 × 2.5                                | 24.8              | 73.8            | 1470                  |
| BNFN 3205V-7.5 | 32                              | 5          | 32.75                                | 29.2                        | 3 × 2.5                                | 26.2              | 84.4            | 1640                  |

| Model No.      | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                 | Rigidity<br>K<br>N/μm |
|----------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------|-----------------------|
|                |                                 |            |                                      |                             |  | Ca                | C <sub>0a</sub> |                       |
|                |                                 |            |                                      |                             |  | kN                | kN              |                       |
| BNFN 2810V-2.5 | 28                              | 10         | 29.75                                | 22.4                        | 1 × 2.5                                | 24.3              | 49              | 560                   |
| BNFN 3610V-7.5 | 36                              | 10         | 37.75                                | 30.5                        | 3 × 2.5                                | 71                | 189.8           | 1990                  |
| BNFN 3616V-5   | 36                              | 16         | 38                                   | 30.1                        | 2 × 2.5                                | 58.3              | 142.9           | 1380                  |
| BNFN 4016V-5   | 40                              | 16         | 42                                   | 34.1                        | 2 × 2.5                                | 61.5              | 158.8           | 1500                  |
| BNFN 4510V-7.5 | 45                              | 10         | 46.75                                | 39.5                        | 3 × 2.5                                | 78.8              | 237.8           | 2370                  |
| BNFN 5010V-7.5 | 50                              | 10         | 51.75                                | 44.4                        | 3 × 2.5                                | 82.5              | 264.4           | 2580                  |

## Positioning Ball Screw



&lt;Medium&gt; BNFN2810V/3610V/3616V/4016V/4510V/5010V


Unit: mm

|  | Nut dimensions      |                                   |                                  |    |                |     |                                   |                       | Screw shaft inertial moment/mm<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|---------------------|-----------------------------------|----------------------------------|----|----------------|-----|-----------------------------------|-----------------------|---|----------------|--------------------|---|
|  | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | Lubrication hole<br>A |   |                |                    |   |
|  | D                   | D <sub>1</sub>                    | L <sub>1</sub>                   | H  | B <sub>1</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | A                     |   |                |                    |   |
|  | 40                  | 60                                | 106                              | 10 | 96             | 50  | 4.5×8×4.5                         | M6                    | 5.05×10 <sup>-8</sup>                                   | 0.88           | 1.37               | 5000  |
|  | 55                  | 85                                | 134                              | 12 | 122            | 69  | 6.6×11×6.5                        | M6                    | 4.74×10 <sup>-7</sup>                                   | 1.88           | 4.45               | 3470  |
|  | 55                  | 85                                | 158                              | 12 | 149            | 69  | 6.6×11×6.5                        | M6                    | 4.74×10 <sup>-7</sup>                                   | 2.16           | 4.52               | 3470  |
|  | 58                  | 85                                | 136                              | 12 | 124            | 71  | 6.6×11×6.5                        | M6                    | 8.08×10 <sup>-7</sup>                                   | 1.93           | 5.89               | 3050  |
|  | Nut dimensions      |                                   |                                  |    |                |     |                                   |                       | Screw shaft inertial moment/mm<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|  | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | Lubrication hole<br>A |   |                |                    |   |
|  | D                   | D <sub>1</sub>                    | L <sub>1</sub>                   | H  | B <sub>1</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | A                     |   |                |                    |   |
|  | 65                  | 106                               | 146                              | 18 | 128            | 85  | 11×17.5×11                        | M6                    | 4.74×10 <sup>-7</sup>                                   | 3.41           | 4.15               | 4360  |
|  | 75                  | 120                               | 261                              | 18 | 243            | 98  | 11×17.5×11                        | M6                    | 1.29×10 <sup>-7</sup>                                   | 6.93           | 7.1                | 3440  |
|  | 78                  | 123                               | 268                              | 18 | 250            | 100 | 11×17.5×11                        | M6                    | 1.29×10 <sup>-7</sup>                                   | 7.8            | 7.99               | 3420  |
|  | 84                  | 126                               | 280                              | 22 | 258            | 104 | 11×17.5×11                        | M6                    | 1.97×10 <sup>-8</sup>                                   | 9.27           | 9.09               | 3090  |
|  | 88                  | 132                               | 261                              | 18 | 243            | 110 | 11×17.5×11                        | Rc1/8<br>(PT1/8)      | 3.16×10 <sup>-8</sup>                                   | 8.92           | 11.36              | 2780  |
|  | 93                  | 135                               | 253                              | 18 | 235            | 113 | 11×17.5×11                        |                       | 4.82×10 <sup>-8</sup>                                   | 9.19           | 14.16              | 2510  |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See [A15-344](#) for further details.


# BNFN With Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.      | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|----------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|                |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| BNFN 5510-2.5  | 55                              | 10         | 56.75                                | 49.5                        | 1×2.5                                  | 33.4              | 97                    | 970                   |
| BNFN 5510-5    | 55                              | 10         | 56.75                                | 49.5                        | 2×2.5                                  | 60.7              | 194                   | 1890                  |
| BNFN 5510-7.5  | 55                              | 10         | 56.75                                | 49.5                        | 3×2.5                                  | 85.9              | 291.1                 | 2770                  |
| BNFN 5512-2.5  | 55                              | 12         | 57                                   | 49.2                        | 1×2.5                                  | 39.3              | 108.8                 | 990                   |
| BNFN 5512-3    | 55                              | 12         | 57                                   | 49.2                        | 2×1.5                                  | 46                | 131.3                 | 1180                  |
| BNFN 5512-3.5  | 55                              | 12         | 57                                   | 49.2                        | 1×3.5                                  | 52.4              | 152.9                 | 1360                  |
| BNFN 5512-5    | 55                              | 12         | 57                                   | 49.2                        | 2×2.5                                  | 71.3              | 218.5                 | 1920                  |
| BNFN 5512-7.5  | 55                              | 12         | 57                                   | 49.2                        | 3×2.5                                  | 100.9             | 327.3                 | 2830                  |
| BNFN 5516-2.5  | 55                              | 16         | 57.7                                 | 47.9                        | 1×2.5                                  | 76.1              | 201.9                 | 1310                  |
| BNFN 5516-5    | 55                              | 16         | 57.7                                 | 47.9                        | 2×2.5                                  | 138.2             | 402.8                 | 2550                  |
| BNFN 5520-2.5  | 55                              | 20         | 57.7                                 | 47.9                        | 1×2.5                                  | 76                | 201.9                 | 1320                  |
| BNFN 5520-5    | 55                              | 20         | 57.7                                 | 47.9                        | 2×2.5                                  | 138.2             | 403.8                 | 2550                  |
| BNFN 6310-2.5  | 63                              | 10         | 64.75                                | 57.7                        | 1×2.5                                  | 35.4              | 111.7                 | 1090                  |
| BNFN 6310-5    | 63                              | 10         | 64.75                                | 57.7                        | 2×2.5                                  | 64.2              | 222.5                 | 2100                  |
| BNFN 6310-7.5  | 63                              | 10         | 64.75                                | 57.7                        | 3×2.5                                  | 90.9              | 334.2                 | 3090                  |
| BNFN 6312A-2.5 | 63                              | 12         | 65.25                                | 56.3                        | 1×2.5                                  | 48.1              | 139.2                 | 1120                  |
| BNFN 6312A-5   | 63                              | 12         | 65.25                                | 56.3                        | 2×2.5                                  | 87.4              | 278.3                 | 2160                  |
| BNFN 6316-2.5  | 63                              | 16         | 65.7                                 | 55.9                        | 1×2.5                                  | 81.1              | 231.3                 | 1470                  |
| BNFN 6316-5    | 63                              | 16         | 65.7                                 | 55.9                        | 2×2.5                                  | 147               | 462.6                 | 2840                  |
| BNFN 6320-2.5  | 63                              | 20         | 65.7                                 | 55.9                        | 1×2.5                                  | 81                | 231.3                 | 1470                  |
| BNFN 6320-5    | 63                              | 20         | 65.7                                 | 55.9                        | 2×2.5                                  | 147               | 463.5                 | 2640                  |

Note) The model numbers in dimmed type indicate semi-standard types.  
If desiring them, contact THK.




Unit: mm

|  | Nut dimensions      |                                   |                                  |    |                |     |                                   | Screw shaft inertial moment/mm <sup>2</sup><br>kg·m <sup>2</sup> /mm | Nut mass<br>kg        | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |                       |
|--|---------------------|-----------------------------------|----------------------------------|----|----------------|-----|-----------------------------------|--|-----------------------|--------------------|---|-----------------------|
|  | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h |  |                       |                    |   | Lubrication hole<br>A |
|  | 102                 | 144                               | 141                              | 18 | 123            | 122 | 11×17.5×11                        | Rc1/8<br>(PT1/8)   | 7.05×10 <sup>-6</sup> | 6.54               | 16.43   | 1230                  |
|  | 102                 | 144                               | 201                              | 18 | 183            | 122 | 11×17.5×11                        |  | 7.05×10 <sup>-6</sup> | 8.88               | 16.43   | 1230                  |
|  | 102                 | 144                               | 261                              | 18 | 243            | 122 | 11×17.5×11                        |  | 7.05×10 <sup>-6</sup> | 11.23              | 16.43   | 1230                  |
|  | 105                 | 147                               | 165                              | 18 | 147            | 125 | 11×17.5×11                        |  | 7.05×10 <sup>-6</sup> | 8.07               | 16.29   | 1220                  |
|  | 105                 | 147                               | 191                              | 18 | 173            | 125 | 11×17.5×11                        |  | 7.05×10 <sup>-6</sup> | 9.17               | 16.29   | 1220                  |
|  | 105                 | 147                               | 189                              | 18 | 171            | 125 | 11×17.5×11                        |  | 7.05×10 <sup>-6</sup> | 9.09               | 16.29   | 1220                  |
|  | 105                 | 147                               | 237                              | 18 | 219            | 125 | 11×17.5×11                        |  | 7.05×10 <sup>-6</sup> | 11.13              | 16.29   | 1220                  |
|  | 105                 | 147                               | 309                              | 18 | 291            | 125 | 11×17.5×11                        |  | 7.05×10 <sup>-6</sup> | 14.19              | 16.29   | 1220                  |
|  | 110                 | 158                               | 196                              | 25 | 171            | 133 | 14×20×13                          |  | 7.05×10 <sup>-6</sup> | 11.28              | 15.46   | 1210                  |
|  | 110                 | 158                               | 292                              | 25 | 267            | 133 | 14×20×13                          |  | 7.05×10 <sup>-6</sup> | 15.94              | 15.46   | 1210                  |
|  | 112                 | 158                               | 227                              | 28 | 199            | 134 | 14×20×13                          |  | 7.05×10 <sup>-6</sup> | 13.49              | 16.1  | 1210                  |
|  | 112                 | 158                               | 347                              | 28 | 319            | 134 | 14×20×13                          |  | 7.05×10 <sup>-6</sup> | 19.61              | 16.1  | 1210                  |
|  | 108                 | 154                               | 137                              | 22 | 115            | 130 | 14×20×13                          |  | 1.21×10 <sup>-5</sup> | 6.98               | 21.93   | 1080                  |
|  | 108                 | 154                               | 197                              | 22 | 175            | 130 | 14×20×13                          |  | 1.21×10 <sup>-5</sup> | 9.4                | 21.93   | 1080                  |
|  | 108                 | 154                               | 257                              | 22 | 235            | 130 | 14×20×13                          |  | 1.21×10 <sup>-5</sup> | 11.81              | 21.93   | 1080                  |
|  | 115                 | 161                               | 159                              | 22 | 137            | 137 | 14×20×13                          |  | 1.21×10 <sup>-5</sup> | 9.32               | 21.14   | 1070                  |
|  | 115                 | 161                               | 231                              | 22 | 209            | 137 | 14×20×13                          |  | 1.21×10 <sup>-5</sup> | 12.84              | 21.14   | 1070                  |
|  | 122                 | 184                               | 208                              | 24 | 184            | 152 | 18×26×17.5                        |  | 1.21×10 <sup>-5</sup> | 14.61              | 20.85   | 1060                  |
|  | 122                 | 184                               | 304                              | 24 | 280            | 152 | 18×26×17.5                        |  | 1.21×10 <sup>-5</sup> | 20.19              | 20.85   | 1060                  |
|  | 122                 | 180                               | 227                              | 28 | 199            | 150 | 18×26×17.5                        |  | 1.21×10 <sup>-5</sup> | 15.91              | 20.85   | 1060                  |
|  | 122                 | 180                               | 347                              | 28 | 319            | 150 | 18×26×17.5                        | 1.21×10 <sup>-5</sup>  | 22.88                 | 20.85              | 1060  |                       |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

# BNFN With Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|




| Model No.       | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|-----------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|                 |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| BNFN 7010-2.5   | 70                              | 10         | 71.75                                | 64.5                        | 1×2.5                                  | 36.8              | 123.5                 | 1180                  |
| BNFN 7010-5     | 70                              | 10         | 71.75                                | 64.5                        | 2×2.5                                  | 66.9              | 247                   | 2280                  |
| BNFN 7010-7.5   | 70                              | 10         | 71.75                                | 64.5                        | 3×2.5                                  | 94.9              | 371.4                 | 3350                  |
| BNFN 7012-2.5   | 70                              | 12         | 72                                   | 64.2                        | 1×2.5                                  | 43.5              | 139.2                 | 1200                  |
| BNFN 7012-5     | 70                              | 12         | 72                                   | 64.2                        | 2×2.5                                  | 78.9              | 278.3                 | 2320                  |
| BNFN 7012-7.5   | 70                              | 12         | 72                                   | 64.2                        | 3×2.5                                  | 111.7             | 417.5                 | 3420                  |
| BNFN 7020-5     | 70                              | 20         | 72.7                                 | 62.9                        | 2×2.5                                  | 153.9             | 514.5                 | 3090                  |
| BNFN 8010-2.5   | 80                              | 10         | 81.75                                | 75.2                        | 1×2.5                                  | 38.9              | 141.1                 | 1300                  |
| BNFN 8010-5     | 80                              | 10         | 81.75                                | 75.2                        | 2×2.5                                  | 70.6              | 283.2                 | 2530                  |
| BNFN 8010-7.5   | 80                              | 10         | 81.75                                | 75.2                        | 3×2.5                                  | 100               | 424.3                 | 3720                  |
| BNFN 8012-5     | 80                              | 12         | 82.3                                 | 74.1                        | 2×2.5                                  | 96.5              | 353.8                 | 2620                  |
| BNFN 8020A-2.5  | 80                              | 20         | 82.7                                 | 72.9                        | 1×2.5                                  | 90.1              | 294                   | 1770                  |
| BNFN 8020A-5    | 80                              | 20         | 82.7                                 | 72.9                        | 2×2.5                                  | 163.7             | 589                   | 3430                  |
| BNFN 10020A-2.5 | 100                             | 20         | 102.7                                | 92.9                        | 1×2.5                                  | 99                | 368.5                 | 2110                  |
| BNFN 10020A-5   | 100                             | 20         | 102.7                                | 92.9                        | 2×2.5                                  | 179.3             | 737                   | 4080                  |
| BNFN 10020A-7.5 | 100                             | 20         | 102.7                                | 92.9                        | 3×2.5                                  | 253.8             | 1105.4                | 6010                  |

Note) The model numbers in dimmed type indicate semi-standard types.  
If desiring them, contact THK.



## Positioning Ball Screw




Unit: mm

|  | Nut dimensions |                 |                |    |                |     |                                     | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass                | Shaft mass | Permissible rotational speed |                  |
|--|----------------|-----------------|----------------|----|----------------|-----|-------------------------------------|---|-------------------------|------------|------------------------------|------------------|
|  | Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h |   |                         |            |                              | Lubrication hole |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h | A   |                         |            |                              |                  |
|  | 125            | 167             | 141            | 18 | 123            | 145 | 11 × 17.5 × 11                      | Rc1/8<br>(PT1/8)                            | 1.85 × 10 <sup>-5</sup> | 9.19       | 27.4                         | 970              |
|  | 125            | 167             | 201            | 18 | 183            | 145 | 11 × 17.5 × 11                      |   | 1.85 × 10 <sup>-5</sup> | 12.57      | 27.4                         | 970              |
|  | 125            | 167             | 261            | 18 | 243            | 145 | 11 × 17.5 × 11                      |   | 1.85 × 10 <sup>-5</sup> | 15.96      | 27.4                         | 970              |
|  | 128            | 170             | 165            | 18 | 147            | 148 | 11 × 17.5 × 11                      |   | 1.85 × 10 <sup>-5</sup> | 11.26      | 27.24                        | 970              |
|  | 128            | 170             | 237            | 18 | 219            | 148 | 11 × 17.5 × 11                      |   | 1.85 × 10 <sup>-5</sup> | 15.63      | 27.24                        | 970              |
|  | 128            | 170             | 309            | 18 | 291            | 148 | 11 × 17.5 × 11                      |   | 1.85 × 10 <sup>-5</sup> | 20         | 27.24                        | 970              |
|  | 130            | 186             | 325            | 28 | 297            | 158 | 18 × 26 × 17.5                      |   | 1.85 × 10 <sup>-5</sup> | 23.4       | 27                           | 960              |
|  | 130            | 176             | 137            | 22 | 115            | 152 | 14 × 20 × 13                        |   | 3.16 × 10 <sup>-5</sup> | 9.15       | 36.26                        | 850              |
|  | 130            | 176             | 197            | 22 | 175            | 152 | 14 × 20 × 13                        |   | 3.16 × 10 <sup>-5</sup> | 12.41      | 36.26                        | 850              |
|  | 130            | 176             | 257            | 22 | 235            | 152 | 14 × 20 × 13                        |   | 3.16 × 10 <sup>-5</sup> | 15.67      | 36.26                        | 850              |
|  | 135            | 181             | 231            | 22 | 209            | 157 | 14 × 20 × 13                        |   | 3.16 × 10 <sup>-5</sup> | 16.02      | 35.26                        | 850              |
|  | 143            | 204             | 227            | 28 | 199            | 172 | 18 × 26 × 17.5                      |   | 3.16 × 10 <sup>-5</sup> | 20.08      | 35.81                        | 840              |
|  | 143            | 204             | 347            | 28 | 319            | 172 | 18 × 26 × 17.5                      |   | 3.16 × 10 <sup>-5</sup> | 28.97      | 35.81                        | 840              |
|  | 170            | 243             | 231            | 32 | 199            | 205 | 22 × 32 × 21.5                      |   | 7.71 × 10 <sup>-5</sup> | 28.15      | 57.13                        | 680              |
|  | 170            | 243             | 351            | 32 | 319            | 205 | 22 × 32 × 21.5                      |   | 7.71 × 10 <sup>-5</sup> | 39.99      | 57.13                        | 680              |
|  | 170            | 243             | 471            | 32 | 439            | 205 | 22 × 32 × 21.5                      |   | 7.71 × 10 <sup>-5</sup> | 51.84      | 57.13                        | 680              |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See [A15-344](#) for further details.


# DIK With Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.  | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|            |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| DIK 1404-4 | 14                              | 4          | 14.5                                 | 11.8                        | 2×1                                    | 3                 | 5.1                   | 190                   |
| DIK 1404-6 | 14                              | 4          | 14.5                                 | 11.8                        | 3×1                                    | 4.2               | 7.7                   | 280                   |
| DIK 1605-6 | 16                              | 5          | 16.75                                | 13.2                        | 3×1                                    | 7.4               | 13                    | 310                   |
| DIK 2004-6 | 20                              | 4          | 20.5                                 | 17.8                        | 3×1                                    | 5.2               | 11.6                  | 380                   |
| DIK 2004-8 | 20                              | 4          | 20.5                                 | 17.8                        | 4×1                                    | 6.6               | 15.5                  | 510                   |
| DIK 2005-6 | 20                              | 5          | 20.75                                | 17.2                        | 3×1                                    | 8.5               | 17.3                  | 310                   |
| DIK 2006-6 | 20                              | 6          | 21                                   | 16.4                        | 3×1                                    | 11.4              | 21.5                  | 410                   |
| DIK 2008-4 | 20                              | 8          | 21                                   | 16.4                        | 2×1                                    | 8.1               | 14.4                  | 280                   |
| DIK 2504-6 | 25                              | 4          | 25.5                                 | 22.8                        | 3×1                                    | 5.7               | 15                    | 470                   |
| DIK 2504-8 | 25                              | 4          | 25.5                                 | 22.8                        | 4×1                                    | 7.4               | 19.9                  | 620                   |
| DIK 2505-6 | 25                              | 5          | 25.75                                | 22.2                        | 3×1                                    | 9.7               | 22.6                  | 490                   |
| DIK 2506-4 | 25                              | 6          | 26                                   | 21.4                        | 2×1                                    | 9.1               | 18                    | 330                   |
| DIK 2506-6 | 25                              | 6          | 26                                   | 21.4                        | 3×1                                    | 12.8              | 27                    | 490                   |
| DIK 2508-4 | 25                              | 8          | 26                                   | 21.4                        | 2×1                                    | 9.2               | 18.8                  | 340                   |
| DIK 2508-6 | 25                              | 8          | 26                                   | 21.4                        | 3×1                                    | 13.1              | 28.1                  | 500                   |
| DIK 2510-4 | 25                              | 10         | 26                                   | 21.6                        | 2×1                                    | 9                 | 18                    | 330                   |

## Positioning Ball Screw




Unit: mm

|    | Nut dimensions |                 |                |    |                |                |             |                                   |    |                       | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|----|----------------|-----------------|----------------|----|----------------|----------------|-------------|-----------------------------------|----|-----------------------|---|----------------|--------------------|---|
|    | Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | B <sub>2</sub> | PCD         | d <sub>1</sub> ×d <sub>2</sub> ×h | Tw | Lubrication hole      |   |                |                    |   |
|    | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD         | d <sub>1</sub> ×d <sub>2</sub> ×h | Tw | A                     |   |                |                    |   |
| 26 | 45             | 48              | 10             | 38 | 10             | 35             | 4.5×8×4.5   | 29                                | M6 | 2.96×10 <sup>-8</sup> | 0.2   | 1              | 4820               |   |
| 26 | 45             | 60              | 10             | 50 | 10             | 35             | 4.5×8×4.5   | 29                                | M6 | 2.96×10 <sup>-8</sup> | 0.23  | 1              | 4820               |   |
| 30 | 49             | 60              | 10             | 50 | 10             | 39             | 4.5×8×4.5   | 31                                | M6 | 5.05×10 <sup>-8</sup> | 0.3   | 1.25           | 4170               |   |
| 32 | 56             | 62              | 11             | 51 | 15             | 44             | 5.5×9.5×5.5 | 35                                | M6 | 1.23×10 <sup>-7</sup> | 0.34  | 2.18           | 3410               |   |
| 32 | 56             | 70              | 11             | 59 | 15             | 44             | 5.5×9.5×5.5 | 35                                | M6 | 1.23×10 <sup>-7</sup> | 0.37  | 2.18           | 3410               |   |
| 34 | 58             | 61              | 11             | 50 | 10             | 46             | 5.5×9.5×5.5 | 36                                | M6 | 1.23×10 <sup>-7</sup> | 0.38  | 2.06           | 3370               |   |
| 35 | 58             | 76              | 11             | 65 | 15             | 46             | 5.5×9.5×5.5 | 36                                | M6 | 1.23×10 <sup>-7</sup> | 0.48  | 1.93           | 3330               |   |
| 35 | 58             | 69              | 11             | 58 | 15             | 46             | 5.5×9.5×5.5 | 36                                | M6 | 1.23×10 <sup>-7</sup> | 0.45  | 2.06           | 3330               |   |
| 38 | 63             | 63              | 11             | 52 | 15             | 51             | 5.5×9.5×5.5 | 39                                | M6 | 3.01×10 <sup>-7</sup> | 0.43  | 3.5            | 2740               |   |
| 38 | 63             | 71              | 11             | 60 | 15             | 51             | 5.5×9.5×5.5 | 39                                | M6 | 3.01×10 <sup>-7</sup> | 0.47  | 3.5            | 2740               |   |
| 40 | 63             | 61              | 11             | 50 | 10             | 51             | 5.5×9.5×5.5 | 41                                | M6 | 3.01×10 <sup>-7</sup> | 0.47  | 3.35           | 2710               |   |
| 40 | 63             | 60              | 11             | 49 | 10             | 51             | 5.5×9.5×5.5 | 41                                | M6 | 3.01×10 <sup>-7</sup> | 0.46  | 3.19           | 2690               |   |
| 40 | 63             | 72              | 11             | 61 | 15             | 51             | 5.5×9.5×5.5 | 41                                | M6 | 3.01×10 <sup>-7</sup> | 0.54  | 3.19           | 2690               |   |
| 40 | 63             | 71              | 12             | 59 | 15             | 51             | 5.5×9.5×5.5 | 41                                | M6 | 3.01×10 <sup>-7</sup> | 0.54  | 3.35           | 2690               |   |
| 40 | 63             | 94              | 12             | 82 | 25             | 51             | 5.5×9.5×5.5 | 41                                | M6 | 3.01×10 <sup>-7</sup> | 0.68  | 3.35           | 2690               |   |
| 40 | 63             | 85              | 15             | 70 | 20             | 51             | 5.5×9.5×5.5 | 41                                | M6 | 3.01×10 <sup>-7</sup> | 0.65  | 3.45           | 2690               |   |


Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

# DIK With Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.   | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|-------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|             |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| DIK 2805-6  | 28                              | 5          | 28.75                                | 25.2                        | 3 × 1                                  | 10.5              | 26.4                  | 560                   |
| DIK 2805-8  | 28                              | 5          | 28.75                                | 25.2                        | 4 × 1                                  | 13.4              | 35.2                  | 730                   |
| DIK 2806-6  | 28                              | 6          | 29                                   | 24.4                        | 3 × 1                                  | 14                | 32                    | 530                   |
| DIK 2810-4  | 28                              | 10         | 29.25                                | 23.6                        | 2 × 1                                  | 12.3              | 25                    | 380                   |
| DIK 3204-6  | 32                              | 4          | 32.5                                 | 30.1                        | 3 × 1                                  | 6.4               | 19.6                  | 580                   |
| DIK 3204-8  | 32                              | 4          | 32.5                                 | 30.1                        | 4 × 1                                  | 8.2               | 26.1                  | 760                   |
| DIK 3204-10 | 32                              | 4          | 32.5                                 | 30.1                        | 5 × 1                                  | 10                | 32.7                  | 940                   |
| DIK 3205-6  | 32                              | 5          | 32.75                                | 29.2                        | 3 × 1                                  | 11.1              | 30.2                  | 620                   |
| DIK 3205-8  | 32                              | 5          | 32.75                                | 29.2                        | 4 × 1                                  | 14.2              | 40.3                  | 810                   |
| DIK 3206-6  | 32                              | 6          | 33                                   | 28.4                        | 3 × 1                                  | 14.9              | 37.1                  | 630                   |
| DIK 3206-8  | 32                              | 6          | 33                                   | 28.4                        | 4 × 1                                  | 19.1              | 49.5                  | 820                   |
| DIK 3210-6  | 32                              | 10         | 33.75                                | 26.4                        | 3 × 1                                  | 25.7              | 52.2                  | 600                   |
| DIK 3212-4  | 32                              | 12         | 33.75                                | 26.4                        | 2 × 1                                  | 18.8              | 37                    | 430                   |
| DIK 3610-6  | 36                              | 10         | 37.75                                | 30.5                        | 3 × 1                                  | 28.8              | 63.8                  | 710                   |
| DIK 3610-8  | 36                              | 10         | 37.75                                | 30.5                        | 4 × 1                                  | 36.8              | 85                    | 940                   |
| DIK 3610-10 | 36                              | 10         | 37.75                                | 30.5                        | 5 × 1                                  | 44.6              | 106.3                 | 1160                  |




Unit: mm

|  | Nut dimensions |                 |                |    |                |                |     |                                   |    |                  | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass/kg | Shaft mass/kg/m | Permissible rotational speed/min <sup>-1</sup> |
|--|----------------|-----------------|----------------|----|----------------|----------------|-----|-----------------------------------|----|------------------|---|-------------|-----------------|--|
|  | Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | Tw | Lubrication hole |   |             |                 |  |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> |    |                |                |     |                                   |    |                  |   |             |                 |  |
|  | 43             | 71              | 69             | 12 | 57             | 15             | 57  | 6.6×11×6.5                        | 55 | M6               | 4.74×10 <sup>-7</sup>                       | 0.61        | 4.27            | 2430   |
|  | 43             | 71              | 79             | 12 | 67             | 20             | 57  | 6.6×11×6.5                        | 55 | M6               | 4.74×10 <sup>-7</sup>                       | 0.68        | 4.27            | 2430   |
|  | 43             | 71              | 73             | 12 | 61             | 15             | 57  | 6.6×11×6.5                        | 55 | M6               | 4.74×10 <sup>-7</sup>                       | 0.64        | 4.36            | 2410   |
|  | 45             | 71              | 84             | 15 | 69             | 20             | 57  | 6.6×11×6.5                        | 55 | M6               | 4.74×10 <sup>-7</sup>                       | 0.82        | 4.18            | 2390   |
|  | 45             | 76              | 64             | 11 | 53             | 15             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.57        | 5.86            | 2150   |
|  | 45             | 76              | 72             | 11 | 61             | 15             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.62        | 5.86            | 2150   |
|  | 45             | 76              | 80             | 11 | 69             | 20             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.66        | 5.86            | 2150   |
|  | 46             | 76              | 62             | 12 | 50             | 10             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.6         | 5.67            | 2130   |
|  | 46             | 76              | 73             | 12 | 61             | 15             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.67        | 5.67            | 2130   |
|  | 48             | 76              | 73             | 12 | 61             | 15             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.74        | 6.31            | 2120   |
|  | 48             | 76              | 87             | 12 | 75             | 20             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.85        | 6.31            | 2120   |
|  | 54             | 87              | 110            | 15 | 95             | 25             | 69  | 9×14×8.5                          | 66 | M6               | 8.08×10 <sup>-7</sup>                       | 1.57        | 4.98            | 2070   |
|  | 54             | 87              | 98             | 15 | 83             | 25             | 69  | 9×14×8.5                          | 66 | M6               | 8.08×10 <sup>-7</sup>                       | 1.43        | 5.2             | 2070   |
|  | 58             | 98              | 122            | 18 | 104            | 30             | 77  | 11×17.5×11                        | 75 | M6               | 1.29×10 <sup>-6</sup>                       | 2.03        | 6.51            | 1850   |
|  | 58             | 98              | 143            | 18 | 125            | 35             | 77  | 11×17.5×11                        | 75 | M6               | 1.29×10 <sup>-6</sup>                       | 2.3         | 6.51            | 1850   |
|  | 58             | 98              | 164            | 18 | 146            | 45             | 77  | 11×17.5×11                        | 75 | M6               | 1.29×10 <sup>-6</sup>                       | 2.57        | 6.51            | 1850   |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.


# DIK With Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.   | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|-------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|             |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| DIK 4010-6  | 40                              | 10         | 41.75                                | 34.7                        | 3 × 1                                  | 29.8              | 69.3                  | 750                   |
| DIK 4010-8  | 40                              | 10         | 41.75                                | 34.7                        | 4 × 1                                  | 38.1              | 92.4                  | 1000                  |
| DIK 4012-6  | 40                              | 12         | 41.75                                | 34.4                        | 3 × 1                                  | 30.6              | 72.3                  | 790                   |
| DIK 4012-8  | 40                              | 12         | 41.75                                | 34.4                        | 4 × 1                                  | 39.2              | 96.4                  | 1030                  |
| DIK 4016-4  | 40                              | 16         | 41.75                                | 34.4                        | 2 × 1                                  | 21.5              | 68.4                  | 540                   |
| DIK 5010-6  | 50                              | 10         | 51.75                                | 44.4                        | 3 × 1                                  | 33.9              | 90.7                  | 940                   |
| DIK 5010-8  | 50                              | 10         | 51.75                                | 44.4                        | 4 × 1                                  | 43.4              | 120.5                 | 1230                  |
| DIK 5010-10 | 50                              | 10         | 51.75                                | 44.4                        | 5 × 1                                  | 52.5              | 150.9                 | 1530                  |
| DIK 5012-6  | 50                              | 12         | 52.25                                | 43.3                        | 3 × 1                                  | 45.8              | 113                   | 970                   |
| DIK 5012-8  | 50                              | 12         | 52.25                                | 43.3                        | 4 × 1                                  | 58.6              | 150.6                 | 1270                  |
| DIK 5016-4  | 50                              | 16         | 52.25                                | 43.3                        | 2 × 1                                  | 32.3              | 75.5                  | 660                   |
| DIK 5016-6  | 50                              | 16         | 52.25                                | 43.3                        | 3 × 1                                  | 45.7              | 113.3                 | 970                   |
| DIK 6310-8  | 63                              | 10         | 64.75                                | 57.7                        | 4 × 1                                  | 49.5              | 160.7                 | 1550                  |
| DIK 6312-6  | 63                              | 12         | 65.25                                | 56.3                        | 3 × 1                                  | 51.9              | 147.4                 | 1200                  |
| DIK 6312-8  | 63                              | 12         | 65.25                                | 56.3                        | 4 × 1                                  | 66.4              | 196.6                 | 1570                  |

## Positioning Ball Screw




Unit: mm

|  | Nut dimensions |                 |                |    |                |                |     |                                   |     |                  | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass | Shaft mass | Permissible rotational speed |
|--|----------------|-----------------|----------------|----|----------------|----------------|-----|-----------------------------------|-----|------------------|---|----------|------------|------------------------------|
|  | Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | Tw  | Lubrication hole |   |          |            |                              |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | Tw  | A                | kg·m <sup>2</sup> /mm                       | kg       | kg/m       | min <sup>-1</sup>            |
|  | 62             | 104             | 113            | 18 | 95             | 25             | 82  | 11×17.5×11                        | 79  | Rc1/8<br>(PT1/8) | 1.97×10 <sup>-6</sup>                       | 2.09     | 8.22       | 1670                         |
|  | 62             | 104             | 137            | 18 | 119            | 35             | 82  | 11×17.5×11                        | 79  |                  | 1.97×10 <sup>-6</sup>                       | 2.42     | 8.22       | 1670                         |
|  | 62             | 104             | 138            | 18 | 120            | 35             | 82  | 11×17.5×11                        | 79  |                  | 1.97×10 <sup>-6</sup>                       | 2.44     | 8.5        | 1670                         |
|  | 62             | 104             | 163            | 18 | 145            | 45             | 82  | 11×17.5×11                        | 79  |                  | 1.97×10 <sup>-6</sup>                       | 2.78     | 8.5        | 1670                         |
|  | 62             | 104             | 120            | 18 | 102            | 30             | 82  | 11×17.5×11                        | 79  |                  | 1.97×10 <sup>-6</sup>                       | 2.19     | 8.83       | 1670                         |
|  | 72             | 123             | 114            | 18 | 96             | 30             | 101 | 11×17.5×11                        | 92  |                  | 4.82×10 <sup>-6</sup>                       | 2.65     | 13.38      | 1350                         |
|  | 72             | 123             | 137            | 18 | 119            | 35             | 101 | 11×17.5×11                        | 92  |                  | 4.82×10 <sup>-6</sup>                       | 3.03     | 13.38      | 1350                         |
|  | 72             | 123             | 160            | 18 | 142            | 45             | 101 | 11×17.5×11                        | 92  |                  | 4.82×10 <sup>-6</sup>                       | 3.41     | 13.38      | 1350                         |
|  | 75             | 129             | 145            | 22 | 123            | 35             | 105 | 14×20×13                          | 98  |                  | 4.82×10 <sup>-6</sup>                       | 3.83     | 12.74      | 1330                         |
|  | 75             | 129             | 170            | 22 | 148            | 45             | 105 | 14×20×13                          | 98  |                  | 4.82×10 <sup>-6</sup>                       | 4.31     | 12.74      | 1330                         |
|  | 75             | 129             | 129            | 22 | 107            | 30             | 105 | 14×20×13                          | 98  |                  | 4.82×10 <sup>-6</sup>                       | 3.52     | 13.41      | 1330                         |
|  | 75             | 129             | 175            | 22 | 153            | 45             | 105 | 14×20×13                          | 98  |                  | 4.82×10 <sup>-6</sup>                       | 4.41     | 13.41      | 1330                         |
|  | 85             | 146             | 141            | 22 | 119            | 35             | 122 | 14×20×13                          | 110 |                  | 1.21×10 <sup>-5</sup>                       | 4.16     | 21.93      | 1080                         |
|  | 90             | 146             | 146            | 22 | 124            | 35             | 122 | 14×20×13                          | 110 |                  | 1.21×10 <sup>-5</sup>                       | 4.93     | 21.14      | 1070                         |
|  | 90             | 146             | 171            | 22 | 149            | 45             | 122 | 14×20×13                          | 110 |                  | 1.21×10 <sup>-5</sup>                       | 5.56     | 21.14      | 1070                         |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See [A15-344](#) for further details.

# DKN With Preload


|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.  | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Rigidity<br>K<br>N/μm | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> |
|------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|---------------------|-----------------------------------|----------------------------------|
|            |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |                     |                                   |                                  |
| DKN 4020-3 | 40                              | 20         | 41.75                                | 34.7                        | 3 × 1                                  | 29.4              | 69.3                  | 750                   | 62                  | 104                               | 223                              |
| DKN 5020-3 | 50                              | 20         | 52.25                                | 43.6                        | 3 × 1                                  | 44.2              | 108.8                 | 930                   | 75                  | 129                               | 243                              |
| DKN 6320-3 | 63                              | 20         | 65.7                                 | 55.9                        | 3 × 1                                  | 83.5              | 229.3                 | 1470                  | 95                  | 159                               | 243                              |



## Positioning Ball Screw




Unit: mm

| Nut dimensions |                |                |     |                                     |     |                          | Screw shaft<br>inertial<br>moment/mm<br>kg·m <sup>2</sup> /mm | Nut<br>mass<br>kg | Shaft<br>mass<br>kg/m | Permissible<br>rotational<br>speed<br>min <sup>-1</sup> |
|----------------|----------------|----------------|-----|-------------------------------------|-----|--------------------------|---|-------------------|-----------------------|---|
| H              | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h | Tw  | Lubrication<br>hole<br>A |   |                   |                       |   |
| 18             | 205            | 25             | 82  | 11 × 17.5 × 11                      | 79  | Rc1/8<br>(PT1/8)         | 1.97 × 10 <sup>-6</sup>                                       | 3.61              | 9.03                  | 1670  |
| 28             | 215            | 30             | 105 | 14 × 20 × 13                        | 98  |                          | 4.82 × 10 <sup>-6</sup>                                       | 6.0               | 13.8                  | 1330  |
| 28             | 215            | 30             | 129 | 18 × 26 × 17.5                      | 121 |                          | 1.21 × 10 <sup>-6</sup>                                       | 9.5               | 20.85                 | 1060  |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See [A15-344](#) for further details.


# BLW With Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.    | Screw shaft outer diameter | Lead | Ball center-to-center diameter | Thread minor diameter | No. of loaded circuits | Basic load rating |      | Rigidity |     |                |                |                 |    |
|--------------|----------------------------|------|--------------------------------|-----------------------|------------------------|-------------------|------|----------|-----|----------------|----------------|-----------------|----|
|              | d                          |      |                                |                       |                        | Ph                | dp   |          | dc  | Rows × turns   | Ca             | C <sub>0a</sub> | K  |
|              | d                          | Ph   | dp                             | dc                    | Rows × turns           | kN                | kN   | N/μm     | D   | D <sub>1</sub> | D <sub>2</sub> | L <sub>1</sub>  | H  |
| BLW 1510-5.6 | 15                         | 10   | 15.75                          | 12.5                  | 2×2.8                  | 14.3              | 27.8 | 680      | 43  | 64             | 34             | 89              | 10 |
| BLW 1616-3.6 | 16                         | 16   | 16.65                          | 13.7                  | 2×1.8                  | 7.1               | 14.3 | 440      | 41  | 60             | 32             | 84.5            | 10 |
| BLW 2020-3.6 | 20                         | 20   | 20.75                          | 17.5                  | 2×1.8                  | 11.1              | 24.7 | 570      | 48  | 69             | 39             | 105             | 10 |
| BLW 2525-3.6 | 25                         | 25   | 26                             | 21.9                  | 2×1.8                  | 16.6              | 38.7 | 700      | 57  | 82             | 47             | 124.5           | 12 |
| BLW 3232-3.6 | 32                         | 32   | 33.25                          | 28.3                  | 2×1.8                  | 23.7              | 59.5 | 880      | 68  | 99             | 58             | 155             | 15 |
| BLW 3636-3.6 | 36                         | 36   | 37.4                           | 31.7                  | 2×1.8                  | 30.8              | 78   | 980      | 79  | 116            | 66             | 181             | 17 |
| BLW 4040-3.6 | 40                         | 40   | 41.75                          | 35.2                  | 2×1.8                  | 38.7              | 99.2 | 1090     | 84  | 121            | 73             | 191             | 17 |
| BLW 5050-3.6 | 50                         | 50   | 52.2                           | 44.1                  | 2×1.8                  | 57.8              | 155  | 1340     | 106 | 149            | 90             | 245             | 20 |

## Positioning Ball Screw



Unit: mm


| Nut dimensions |                |                |     |                |     |                |                          |                       | Screw shaft<br>inertial<br>moment/mm<br>kg·m <sup>2</sup> /mm | Nut<br>mass<br>kg | Shaft<br>mass<br>kg/m | Permissible<br>rotational<br>speed<br>min <sup>-1</sup> |
|----------------|----------------|----------------|-----|----------------|-----|----------------|--------------------------|-----------------------|---|-------------------|-----------------------|---|
| B <sub>1</sub> | B <sub>2</sub> | B <sub>3</sub> | PCD | d <sub>1</sub> | Tw  | N <sub>1</sub> | Lubrication<br>hole<br>A |                       |   |                   |                       |   |
| 69             | 18.7           | 28.6           | 52  | 5.5            | 46  | 5              | M6                       | $3.90 \times 10^{-8}$ | 0.81  | 1.07              | 4440                  |   |
| 65.5           | 18.1           | 27.1           | 49  | 4.5            | 44  | 6              | M6                       | $5.05 \times 10^{-8}$ | 0.67  | 1.42              | 4200                  |   |
| 84             | 25             | 36             | 57  | 5.5            | 50  | 5              | M6                       | $1.23 \times 10^{-7}$ | 0.54  | 2.25              | 3370                  |   |
| 101.5          | 33             | 44             | 68  | 6.6            | 60  | 5              | M6                       | $3.01 \times 10^{-7}$ | 0.94  | 3.52              | 2690                  |   |
| 127            | 42.4           | 55.4           | 81  | 9              | 70  | 6              | M6                       | $8.08 \times 10^{-7}$ | 3.19  | 5.83              | 2100                  |   |
| 147.9          | 49.4           | 65.4           | 95  | 11             | 82  | 7              | M6                       | $1.29 \times 10^{-6}$ | 5.99  | 7.34              | 1870                  |   |
| 158            | 54.5           | 70.5           | 100 | 11             | 87  | 7              | M6                       | $1.97 \times 10^{-6}$ | 6.16  | 9.01              | 1670                  |   |
| 203.8          | 70.7           | 91.7           | 126 | 14             | 108 | 8              | M6                       | $4.82 \times 10^{-6}$ | 9.06  | 14.08             | 1340                  |   |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.  
The Model BLW can be equipped with a brush seal depending on the model number. Contact THK if you would like to use one.

# BNK0401-3 Shaft diameter: 4; lead: 1

DN value

70000



| Model No.            | Stroke | Screw shaft length |                |                |
|----------------------|--------|--------------------|----------------|----------------|
|                      |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 0401-3G0+77LC3Y  | 20     | 45                 | 54             | 77             |
| BNK 0401-3G0+77LC5Y  |        |                    |                |                |
| BNK 0401-3G2+77LC7Y  |        |                    |                |                |
| BNK 0401-3G0+97LC3Y  | 40     | 65                 | 74             | 97             |
| BNK 0401-3G0+97LC5Y  |        |                    |                |                |
| BNK 0401-3G2+97LC7Y  |        |                    |                |                |
| BNK 0401-3G0+127LC3Y | 70     | 95                 | 104            | 127            |
| BNK 0401-3G0+127LC5Y |        |                    |                |                |
| BNK 0401-3G2+127LC7Y |        |                    |                |                |


Note) A stainless steel type is also available for model BNK0401. When placing an order, add symbol "M" to the end of the model number.

(Example) BNK0401-3G0+77LC3Y M

Symbol for stainless steel type

For accuracy grades C3 and C5, clearance GT is also available as standard.

## Positioning Ball Screw



X-X arrow view

| Ball Screw Specifications                    |                      |               |              |
|--|----------------------|---------------|--------------|
| Lead (mm)                                    | 1                    |               |              |
| BCD (mm)                                     | 4.15                 |               |              |
| Thread minor diameter (mm)                   | 3.4                  |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1         |               |              |
| No. of circuits                              | 1 turn × 3 rows      |               |              |
| Clearance symbol                             | G0                   | GT            | G2           |
| Axial clearance (mm)                         | 0                    | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 0.29                 | 0.29          | 0.29         |
| Basic static load rating $C_{0a}$ (kN)       | 0.42                 | 0.42          | 0.42         |
| Preload torque (N·m)                         | to $9.8 \times 10^3$ | —             | —            |
| Spacer ball                                  | None                 | None          | None         |
| Rigidity value (N/μm)                        | 35                   |               |              |
| Circulation method                           | Deflector            |               |              |


Unit: mm

|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.015                               | 0.009                                | 0.008                               | 0.008                                    | ±0.008                               | 0.008       | 0.01           | 0.07               | 3500  |
|  | 0.025                               | 0.012                                | 0.01                                | 0.01                                     | ±0.018                               | 0.018       | 0.01           | 0.07               | 3500  |
|  | 0.035                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.01           | 0.07               | 3500  |
|  | 0.02                                | 0.009                                | 0.008                               | 0.008                                    | ±0.008                               | 0.008       | 0.01           | 0.07               | 3500  |
|  | 0.025                               | 0.012                                | 0.01                                | 0.01                                     | ±0.018                               | 0.018       | 0.01           | 0.07               | 3500  |
|  | 0.035                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.01           | 0.07               | 3500  |
|  | 0.025                               | 0.009                                | 0.008                               | 0.008                                    | ±0.008                               | 0.008       | 0.01           | 0.07               | 3500  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.01                                     | ±0.018                               | 0.018       | 0.01           | 0.07               | 3500  |
|  | 0.05                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.01           | 0.07               | 3500  |

Ball Screw

# BNK0501-3 Shaft diameter: 5; lead: 1

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.            | Stroke | Screw shaft length |                |                |
|----------------------|--------|--------------------|----------------|----------------|
|                      |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 0501-3G0+77LC3Y  | 20     | 45                 | 54             | 77             |
| BNK 0501-3G0+77LC5Y  |        |                    |                |                |
| BNK 0501-3G2+77LC7Y  |        |                    |                |                |
| BNK 0501-3G0+97LC3Y  | 40     | 65                 | 74             | 97             |
| BNK 0501-3G0+97LC5Y  |        |                    |                |                |
| BNK 0501-3G2+97LC7Y  |        |                    |                |                |
| BNK 0501-3G0+127LC3Y | 70     | 95                 | 104            | 127            |
| BNK 0501-3G0+127LC5Y |        |                    |                |                |
| BNK 0501-3G2+127LC7Y |        |                    |                |                |


Note) A stainless steel type is also available for model BNK0501. When placing an order, add symbol "M" to the end of the model number.

(Example) BNK0501-3G0+77LC3Y M

Symbol for stainless steel type

For accuracy grades C3 and C5, clearance GT is also available as standard.

## Positioning Ball Screw



| Ball Screw Specifications                    |                         |               |              |
|--|-------------------------|---------------|--------------|
| Lead (mm)                                    | 1                       |               |              |
| BCD (mm)                                     | 5.15                    |               |              |
| Thread minor diameter (mm)                   | 4.4                     |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1            |               |              |
| No. of circuits                              | 1 turn × 3 rows         |               |              |
| Clearance symbol                             | G0                      | GT            | G2           |
| Axial clearance (mm)                         | 0                       | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 0.32                    | 0.32          | 0.32         |
| Basic static load rating $C_{0a}$ (kN)       | 0.55                    | 0.55          | 0.55         |
| Preload torque (N·m)                         | to $9.8 \times 10^{-3}$ | —             | —            |
| Spacer ball                                  | None                    | None          | None         |
| Rigidity value (N/μm)                        | 47                      |               |              |
| Circulation method                           | Deflector               |               |              |

Unit: mm


|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.015                               | 0.009                                | 0.008                               | 0.008                                    | ±0.008                               | 0.008       | 0.012          | 0.11               | 3500  |
|  | 0.025                               | 0.012                                | 0.01                                | 0.01                                     | ±0.018                               | 0.018       | 0.012          | 0.11               | 3500  |
|  | 0.035                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.012          | 0.11               | 3500  |
|  | 0.02                                | 0.009                                | 0.008                               | 0.008                                    | ±0.008                               | 0.008       | 0.012          | 0.11               | 3500  |
|  | 0.025                               | 0.012                                | 0.01                                | 0.01                                     | ±0.018                               | 0.018       | 0.012          | 0.11               | 3500  |
|  | 0.035                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.012          | 0.11               | 3500  |
|  | 0.025                               | 0.009                                | 0.008                               | 0.008                                    | ±0.008                               | 0.008       | 0.012          | 0.11               | 3500  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.01                                     | ±0.018                               | 0.018       | 0.012          | 0.11               | 3500  |
|  | 0.05                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.012          | 0.11               | 3500  |

Ball Screw

# BNK0601-3 Shaft diameter: 6; lead: 1

DN value

70000



| Model No.            | Stroke | Screw shaft length |                |                |
|----------------------|--------|--------------------|----------------|----------------|
|                      |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 0601-3G0+100LC3Y | 40     | 65                 | 75             | 100            |
| BNK 0601-3G0+100LC5Y |        |                    |                |                |
| BNK 0601-3G2+100LC7Y |        |                    |                |                |
| BNK 0601-3G0+130LC3Y | 70     | 95                 | 105            | 130            |
| BNK 0601-3G0+130LC5Y |        |                    |                |                |
| BNK 0601-3G2+130LC7Y |        |                    |                |                |
| BNK 0601-3G0+160LC3Y | 100    | 125                | 135            | 160            |
| BNK 0601-3G0+160LC5Y |        |                    |                |                |
| BNK 0601-3G2+160LC7Y |        |                    |                |                |

Note) A stainless steel type is also available for model BNK0601. When placing an order, add symbol "M" to the end of the model number.


(Example) BNK0601-3G0+100LC3Y M

Symbol for stainless steel type

For accuracy grades C3 and C5, clearance GT is also available as standard.



## Positioning Ball Screw



| Ball Screw Specifications                    |                      |               |              |
|--|----------------------|---------------|--------------|
| Lead (mm)                                    | 1                    |               |              |
| BCD (mm)                                     | 6.2                  |               |              |
| Thread minor diameter (mm)                   | 5.3                  |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1         |               |              |
| No. of circuits                              | 1 turn × 3 rows      |               |              |
| Clearance symbol                             | G0                   | GT            | G2           |
| Axial clearance (mm)                         | 0                    | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 0.54                 | 0.54          | 0.54         |
| Basic static load rating $C_{0a}$ (kN)       | 0.94                 | 0.94          | 0.94         |
| Preload torque (N·m)                         | to $1.3 \times 10^2$ | —             | —            |
| Spacer ball                                  | None                 | None          | None         |
| Rigidity value (N/μm)                        | 60                   |               |              |
| Circulation method                           | Deflector            |               |              |


Unit: mm

|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.015                               | 0.009                                | 0.008                               | 0.008                                    | ±0.008                               | 0.008       | 0.017          | 0.14               | 3500  |
|  | 0.025                               | 0.012                                | 0.01                                | 0.01                                     | ±0.018                               | 0.018       | 0.017          | 0.14               | 3500  |
|  | 0.035                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.017          | 0.14               | 3500  |
|  | 0.02                                | 0.009                                | 0.008                               | 0.008                                    | ±0.008                               | 0.008       | 0.017          | 0.14               | 3500  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.01                                     | ±0.018                               | 0.018       | 0.017          | 0.14               | 3500  |
|  | 0.05                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.017          | 0.14               | 3500  |
|  | 0.025                               | 0.009                                | 0.008                               | 0.008                                    | ±0.01                                | 0.008       | 0.017          | 0.14               | 3500  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.01                                     | ±0.02                                | 0.018       | 0.017          | 0.14               | 3500  |
|  | 0.05                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.017          | 0.14               | 3500  |

Ball Screw

# BNK0801-3 Shaft diameter: 8; lead: 1

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.            | Stroke | Screw shaft length |                |                |
|----------------------|--------|--------------------|----------------|----------------|
|                      |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 0801-3G0+115LC3Y | 40     | 66                 | 76             | 115            |
| BNK 0801-3G0+115LC5Y |        |                    |                |                |
| BNK 0801-3G2+115LC7Y |        |                    |                |                |
| BNK 0801-3G0+145LC3Y | 70     | 96                 | 106            | 145            |
| BNK 0801-3G0+145LC5Y |        |                    |                |                |
| BNK 0801-3G2+145LC7Y |        |                    |                |                |
| BNK 0801-3G0+175LC3Y | 100    | 126                | 136            | 175            |
| BNK 0801-3G0+175LC5Y |        |                    |                |                |
| BNK 0801-3G2+175LC7Y |        |                    |                |                |
| BNK 0801-3G0+225LC3Y | 150    | 176                | 186            | 225            |
| BNK 0801-3G0+225LC5Y |        |                    |                |                |
| BNK 0801-3G2+225LC7Y |        |                    |                |                |


Note) A stainless steel type is also available for model BNK0801. When placing an order, add symbol "M" to the end of the model number.

(Example) BNK0801-3G0+115LC3Y M

Symbol for stainless steel type

For accuracy grades C3 and C5, clearance GT is also available as standard.

## Positioning Ball Screw



X-X arrow view

| Ball Screw Specifications                    |                      |               |              |
|--|----------------------|---------------|--------------|
| Lead (mm)                                    | 1                    |               |              |
| BCD (mm)                                     | 8.2                  |               |              |
| Thread minor diameter (mm)                   | 7.3                  |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1         |               |              |
| No. of circuits                              | 1 turn × 3 rows      |               |              |
| Clearance symbol                             | G0                   | GT            | G2           |
| Axial clearance (mm)                         | 0                    | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 0.64                 | 0.64          | 0.64         |
| Basic static load rating $C_{0a}$ (kN)       | 1.4                  | 1.4           | 1.4          |
| Preload torque (N·m)                         | to $1.8 \times 10^2$ | —             | —            |
| Spacer ball                                  | None                 | None          | None         |
| Rigidity value (N/ $\mu$ m)                  | 80                   |               |              |
| Circulation method                           | Deflector            |               |              |

Unit: mm


|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.025                               | 0.009                                | 0.008                               | 0.008                                    | ±0.008                               | 0.008       | 0.024          | 0.29               | 3500  |
|  | 0.025                               | 0.012                                | 0.01                                | 0.01                                     | ±0.018                               | 0.018       | 0.024          | 0.29               | 3500  |
|  | 0.035                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.024          | 0.29               | 3500  |
|  | 0.03                                | 0.009                                | 0.008                               | 0.008                                    | ±0.008                               | 0.008       | 0.024          | 0.29               | 3500  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.01                                     | ±0.018                               | 0.018       | 0.024          | 0.29               | 3500  |
|  | 0.05                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.024          | 0.29               | 3500  |
|  | 0.03                                | 0.009                                | 0.008                               | 0.008                                    | ±0.01                                | 0.008       | 0.024          | 0.29               | 3500  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.01                                     | ±0.02                                | 0.018       | 0.024          | 0.29               | 3500  |
|  | 0.05                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.024          | 0.29               | 3500  |
|  | 0.035                               | 0.009                                | 0.008                               | 0.008                                    | ±0.01                                | 0.008       | 0.024          | 0.29               | 3500  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.01                                     | ±0.02                                | 0.018       | 0.024          | 0.29               | 3500  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.024          | 0.29               | 3500  |

Ball Screw

# BNK0802-3 Shaft diameter: 8; lead: 2

DN value

70000



| Model No.              | Stroke | Screw shaft length |                |                |
|------------------------|--------|--------------------|----------------|----------------|
|                        |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 0802-3RRG0+125LC3Y | 40     | 75                 | 86             | 125            |
| BNK 0802-3RRG0+125LC5Y |        |                    |                |                |
| BNK 0802-3RRG2+125LC7Y |        |                    |                |                |
| BNK 0802-3RRG0+155LC3Y | 70     | 105                | 116            | 155            |
| BNK 0802-3RRG0+155LC5Y |        |                    |                |                |
| BNK 0802-3RRG2+155LC7Y |        |                    |                |                |
| BNK 0802-3RRG0+185LC3Y | 100    | 135                | 146            | 185            |
| BNK 0802-3RRG0+185LC5Y |        |                    |                |                |
| BNK 0802-3RRG2+185LC7Y |        |                    |                |                |
| BNK 0802-3RRG0+235LC3Y | 150    | 185                | 196            | 235            |
| BNK 0802-3RRG0+235LC5Y |        |                    |                |                |
| BNK 0802-3RRG2+235LC7Y |        |                    |                |                |


Note) A stainless steel type is also available for model BNK0802. When placing an order, add symbol "M" to the end of the model number.

(Example) BNK0802-3RRG0+125LC3Y M

Symbol for stainless steel type

For accuracy grades C3 and C5, clearance GT is also available as standard.

## Positioning Ball Screw



X-X arrow view


| Ball Screw Specifications                    |                       |               |              |
|--|-----------------------|---------------|--------------|
| Lead (mm)                                    | 2                     |               |              |
| BCD (mm)                                     | 8.3                   |               |              |
| Thread minor diameter (mm)                   | 7                     |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1          |               |              |
| No. of circuits                              | 1 turn × 3 rows       |               |              |
| Clearance symbol                             | G0                    | GT            | G2           |
| Axial clearance (mm)                         | 0                     | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 1.4                   | 1.4           | 1.4          |
| Basic static load rating $C_{0a}$ (kN)       | 2.3                   | 2.3           | 2.3          |
| Preload torque (N·m)                         | to $2 \times 10^{-2}$ | —             | —            |
| Spacer ball                                  | None                  | None          | None         |
| Rigidity value (N/ $\mu$ m)                  | 100                   |               |              |
| Circulation method                           | Deflector             |               |              |

Unit: mm

|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.025                               | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.008$                          | 0.008       | 0.034          | 0.27               | 3500  |
|  | 0.025                               | 0.012                                | 0.01                                | 0.01                                     | $\pm 0.018$                          | 0.018       | 0.034          | 0.27               | 3500  |
|  | 0.035                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.034          | 0.27               | 3500  |
|  | 0.03                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.01$                           | 0.008       | 0.034          | 0.27               | 3500  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.01                                     | $\pm 0.02$                           | 0.018       | 0.034          | 0.27               | 3500  |
|  | 0.05                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.034          | 0.27               | 3500  |
|  | 0.03                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.01$                           | 0.008       | 0.034          | 0.27               | 3500  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.01                                     | $\pm 0.02$                           | 0.018       | 0.034          | 0.27               | 3500  |
|  | 0.05                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.034          | 0.27               | 3500  |
|  | 0.035                               | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.01$                           | 0.008       | 0.034          | 0.27               | 3500  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.01                                     | $\pm 0.02$                           | 0.018       | 0.034          | 0.27               | 3500  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.034          | 0.27               | 3500  |


# BNK0810-3 Shaft diameter: 8; lead: 10

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.            | Stroke | Screw shaft length |                |                |
|----------------------|--------|--------------------|----------------|----------------|
|                      |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 0810-3GT+205LC5Y | 100    | 154                | 166            | 205            |
| BNK 0810-3G2+205LC7Y |        |                    |                |                |
| BNK 0810-3GT+255LC5Y | 150    | 204                | 216            | 255            |
| BNK 0810-3G2+255LC7Y |        |                    |                |                |
| BNK 0810-3GT+305LC5Y | 200    | 254                | 266            | 305            |
| BNK 0810-3G2+305LC7Y |        |                    |                |                |
| BNK 0810-3GT+355LC5Y | 250    | 304                | 316            | 355            |
| BNK 0810-3G2+355LC7Y |        |                    |                |                |
| BNK 0810-3GT+405LC5Y | 300    | 354                | 366            | 405            |
| BNK 0810-3G2+405LC7Y |        |                    |                |                |

## Positioning Ball Screw



| Ball Screw Specifications                    |                    |              |
|--|--------------------|--------------|
| Lead (mm)                                    | 10                 |              |
| BCD (mm)                                     | 8.4                |              |
| Thread minor diameter (mm)                   | 6.7                |              |
| Threading direction, No. of threaded grooves | Rightward, 2       |              |
| No. of circuits                              | 1.5 turns × 2 rows |              |
| Clearance symbol                             | GT                 | G2           |
| Axial clearance (mm)                         | 0.005 or less      | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 2.16               | 2.16         |
| Basic static load rating $C_{0a}$ (kN)       | 3.82               | 3.82         |
| Preload torque (N·m)                         | —                  | —            |
| Spacer ball                                  | None               | None         |
| Rigidity value (N/μm)                        | 100                |              |
| Circulation method                           | End cap            |              |


Unit: mm

|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.05                                | 0.012                                | 0.01                                | 0.01                                     | ±0.02                                | 0.018       | 0.049          | 0.30               | 3500  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.049          | 0.30               | 3500  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.01                                     | ±0.023                               | 0.018       | 0.049          | 0.30               | 3500  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.049          | 0.30               | 3500  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.01                                     | ±0.023                               | 0.018       | 0.049          | 0.30               | 3500  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.049          | 0.30               | 3500  |
|  | 0.06                                | 0.012                                | 0.01                                | 0.01                                     | ±0.023                               | 0.018       | 0.049          | 0.30               | 3500  |
|  | 0.075                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.049          | 0.30               | 3500  |
|  | 0.07                                | 0.012                                | 0.01                                | 0.01                                     | ±0.025                               | 0.018       | 0.049          | 0.30               | 3500  |
|  | 0.09                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.049          | 0.30               | 3500  |

Ball Screw

# BNK1002-3 Shaft diameter: 10; lead: 2

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.              | Stroke | Screw shaft length |                |                |
|------------------------|--------|--------------------|----------------|----------------|
|                        |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 1002-3RRG0+143LC3Y | 50     | 85                 | 97             | 143            |
| BNK 1002-3RRG0+143LC5Y |        |                    |                |                |
| BNK 1002-3RRG2+143LC7Y |        |                    |                |                |
| BNK 1002-3RRG0+193LC3Y | 100    | 135                | 147            | 193            |
| BNK 1002-3RRG0+193LC5Y |        |                    |                |                |
| BNK 1002-3RRG2+193LC7Y |        |                    |                |                |
| BNK 1002-3RRG0+243LC3Y | 150    | 185                | 197            | 243            |
| BNK 1002-3RRG0+243LC5Y |        |                    |                |                |
| BNK 1002-3RRG2+243LC7Y |        |                    |                |                |
| BNK 1002-3RRG0+293LC3Y | 200    | 235                | 247            | 293            |
| BNK 1002-3RRG0+293LC5Y |        |                    |                |                |
| BNK 1002-3RRG2+293LC7Y |        |                    |                |                |

Note) A stainless steel type is also available for model BNK1002. When placing an order, add symbol "M" to the end of the model number.


(Example) BNK1002-3RRG0+143LC3Y M

Symbol for stainless steel type

For accuracy grades C3 and C5, clearance GT is also available as standard.



## Positioning Ball Screw



X-X arrow view

| Ball Screw Specifications                    |                      |               |              |
|--|----------------------|---------------|--------------|
| Lead (mm)                                    | 2                    |               |              |
| BCD (mm)                                     | 10.3                 |               |              |
| Thread minor diameter (mm)                   | 9                    |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1         |               |              |
| No. of circuits                              | 1 turn × 3 rows      |               |              |
| Clearance symbol                             | G0                   | GT            | G2           |
| Axial clearance (mm)                         | 0                    | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 1.5                  | 1.5           | 1.5          |
| Basic static load rating $C_{0a}$ (kN)       | 2.9                  | 2.9           | 2.9          |
| Preload torque (N·m)                         | to $2.5 \times 10^2$ | —             | —            |
| Spacer ball                                  | None                 | None          | None         |
| Rigidity value (N/ $\mu$ m)                  | 100                  |               |              |
| Circulation method                           | Deflector            |               |              |

Unit: mm


|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.02                                | 0.009                                | 0.008                               | 0.007                                    | ±0.008                               | 0.008       | 0.045          | 0.47               | 3500  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.011                                    | ±0.018                               | 0.018       | 0.045          | 0.47               | 3500  |
|  | 0.04                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.045          | 0.47               | 3500  |
|  | 0.03                                | 0.009                                | 0.008                               | 0.007                                    | ±0.01                                | 0.008       | 0.045          | 0.47               | 3500  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.011                                    | ±0.02                                | 0.018       | 0.045          | 0.47               | 3500  |
|  | 0.04                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.045          | 0.47               | 3500  |
|  | 0.03                                | 0.009                                | 0.008                               | 0.007                                    | ±0.01                                | 0.008       | 0.045          | 0.47               | 3500  |
|  | 0.04                                | 0.012                                | 0.01                                | 0.011                                    | ±0.02                                | 0.018       | 0.045          | 0.47               | 3500  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.045          | 0.47               | 3500  |
|  | 0.03                                | 0.009                                | 0.008                               | 0.007                                    | ±0.012                               | 0.008       | 0.045          | 0.47               | 3500  |
|  | 0.04                                | 0.012                                | 0.01                                | 0.011                                    | ±0.023                               | 0.018       | 0.045          | 0.47               | 3500  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.045          | 0.47               | 3500  |

Ball Screw

# BNK1004-2.5 Shaft diameter: 10; lead: 4

DN value


70000



| Model No.                | Stroke | Screw shaft length |                |                |
|--------------------------|--------|--------------------|----------------|----------------|
|                          |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 1004-2.5RRG0+180LC3Y | 50     | 110                | 125            | 180            |
| BNK 1004-2.5RRG0+180LC5Y |        |                    |                |                |
| BNK 1004-2.5RRG2+180LC7Y |        |                    |                |                |
| BNK 1004-2.5RRG0+230LC3Y | 100    | 160                | 175            | 230            |
| BNK 1004-2.5RRG0+230LC5Y |        |                    |                |                |
| BNK 1004-2.5RRG2+230LC7Y |        |                    |                |                |
| BNK 1004-2.5RRG0+280LC3Y | 150    | 210                | 225            | 280            |
| BNK 1004-2.5RRG0+280LC5Y |        |                    |                |                |
| BNK 1004-2.5RRG2+280LC7Y |        |                    |                |                |
| BNK 1004-2.5RRG0+330LC3Y | 200    | 260                | 275            | 330            |
| BNK 1004-2.5RRG0+330LC5Y |        |                    |                |                |
| BNK 1004-2.5RRG2+330LC7Y |        |                    |                |                |
| BNK 1004-2.5RRG0+380LC3Y | 250    | 310                | 325            | 380            |
| BNK 1004-2.5RRG0+380LC5Y |        |                    |                |                |
| BNK 1004-2.5RRG2+380LC7Y |        |                    |                |                |

Note) For accuracy grades C3 and C5, clearance GT is also available as standard.

## Positioning Ball Screw




| Ball Screw Specifications                    |  |               |              |
|--|--|---------------|--------------|
| Lead (mm)                                    | 4                                      |               |              |
| BCD (mm)                                     | 10.5                                   |               |              |
| Thread minor diameter (mm)                   | 7.8                                    |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1                           |               |              |
| No. of circuits                              | 2.5 turns $\times$ 1 row               |               |              |
| Clearance symbol                             | G0                                     | GT            | G2           |
| Axial clearance (mm)                         | 0                                      | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 2.1                                    | 3.4           | 3.4          |
| Basic static load rating $C_{0a}$ (kN)       | 2.7                                    | 5.4           | 5.4          |
| Preload torque (N·m)                         | $9.8 \times 10^3$ to $4.9 \times 10^2$ | —             | —            |
| Spacer ball                                  | 1 : 1                                  | None          | None         |
| Rigidity value (N/ $\mu$ m)                  | 50                                     | 100           |              |
| Circulation method                           | Return pipe                            |               |              |

Unit: mm

|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.02                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.01$                           | 0.008       | 0.15           | 0.32               | 5000  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.02$                           | 0.018       | 0.15           | 0.32               | 5000  |
|  | 0.04                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.15           | 0.32               | 5000  |
|  | 0.03                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.01$                           | 0.008       | 0.15           | 0.32               | 5000  |
|  | 0.04                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.02$                           | 0.018       | 0.15           | 0.32               | 5000  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.15           | 0.32               | 5000  |
|  | 0.03                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.012$                          | 0.008       | 0.15           | 0.32               | 5000  |
|  | 0.04                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.023$                          | 0.018       | 0.15           | 0.32               | 5000  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.15           | 0.32               | 5000  |
|  | 0.04                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.012$                          | 0.008       | 0.15           | 0.32               | 5000  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.023$                          | 0.018       | 0.15           | 0.32               | 5000  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.15           | 0.32               | 5000  |
|  | 0.04                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.012$                          | 0.008       | 0.15           | 0.32               | 5000  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.023$                          | 0.018       | 0.15           | 0.32               | 5000  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.15           | 0.32               | 5000  |



## Positioning Ball Screw



| Ball Screw Specifications                    |  |               |              |
|--|--|---------------|--------------|
| Lead (mm)                                    | 10                                     |               |              |
| BCD (mm)                                     | 10.5                                   |               |              |
| Thread minor diameter (mm)                   | 7.8                                    |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1                           |               |              |
| No. of circuits                              | 1.5 turns $\times$ 1 row               |               |              |
| Clearance symbol                             | G0                                     | GT            | G2           |
| Axial clearance (mm)                         | 0                                      | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 1.3                                    | 2.1           | 2.1          |
| Basic static load rating $C_{0a}$ (kN)       | 1.6                                    | 3.1           | 3.1          |
| Preload torque (N·m)                         | $9.8 \times 10^3$ to $4.9 \times 10^2$ | —             | —            |
| Spacer ball                                  | 1 : 1                                  | None          | None         |
| Rigidity value (N/ $\mu$ m)                  | 70                                     | 140           |              |
| Circulation method                           | Return pipe                            |               |              |

Unit: mm


|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.04                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.02$                           | 0.018       | 0.17           | 0.5                | 5000  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.17           | 0.5                | 5000  |
|  | 0.04                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.023$                          | 0.018       | 0.17           | 0.5                | 5000  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.17           | 0.5                | 5000  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.023$                          | 0.018       | 0.17           | 0.5                | 5000  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.17           | 0.5                | 5000  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.025$                          | 0.02        | 0.17           | 0.5                | 5000  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.17           | 0.5                | 5000  |
|  | 0.065                               | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.025$                          | 0.02        | 0.17           | 0.5                | 5000  |
|  | 0.08                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.17           | 0.5                | 5000  |

Ball Screw

# BNK1202-3 Shaft diameter: 12; lead: 2

DN value

70000



| Model No.              | Stroke | Screw shaft length |                |                |
|------------------------|--------|--------------------|----------------|----------------|
|                        |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 1202-3RRG0+154LC3Y | 50     | 85                 | 99             | 154            |
| BNK 1202-3RRG0+154LC5Y |        |                    |                |                |
| BNK 1202-3RRG2+154LC7Y |        |                    |                |                |
| BNK 1202-3RRG0+204LC3Y | 100    | 135                | 149            | 204            |
| BNK 1202-3RRG0+204LC5Y |        |                    |                |                |
| BNK 1202-3RRG2+204LC7Y |        |                    |                |                |
| BNK 1202-3RRG0+254LC3Y | 150    | 185                | 199            | 254            |
| BNK 1202-3RRG0+254LC5Y |        |                    |                |                |
| BNK 1202-3RRG2+254LC7Y |        |                    |                |                |
| BNK 1202-3RRG0+304LC3Y | 200    | 235                | 249            | 304            |
| BNK 1202-3RRG0+304LC5Y |        |                    |                |                |
| BNK 1202-3RRG2+304LC7Y |        |                    |                |                |
| BNK 1202-3RRG0+354LC3Y | 250    | 285                | 299            | 354            |
| BNK 1202-3RRG0+354LC5Y |        |                    |                |                |
| BNK 1202-3RRG2+354LC7Y |        |                    |                |                |


Note) A stainless steel type is also available for model BNK1202. When placing an order, add symbol "M" to the end of the model number.

(Example) BNK1202-3RRG0+154LC3Y M

Symbol for stainless steel type

For accuracy grades C3 and C5, clearance GT is also available as standard.

## Positioning Ball Screw



| Ball Screw Specifications                    |  |               |              |
|--|--|---------------|--------------|
| Lead (mm)                                    | 2                                      |               |              |
| BCD (mm)                                     | 12.3                                   |               |              |
| Thread minor diameter (mm)                   | 11                                     |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1                           |               |              |
| No. of circuits                              | 1 turn × 3 rows                        |               |              |
| Clearance symbol                             | G0                                     | GT            | G2           |
| Axial clearance (mm)                         | 0                                      | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 1.7                                    | 1.7           | 1.7          |
| Basic static load rating $C_{0a}$ (kN)       | 3.6                                    | 3.6           | 3.6          |
| Preload torque (N·m)                         | $4.0 \times 10^3$ to $3.4 \times 10^2$ | —             | —            |
| Spacer ball                                  | None                                   | None          | None         |
| Rigidity value (N/μm)                        | 120                                    |               |              |
| Circulation method                           | Deflector                              |               |              |


Unit: mm

|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.02                                | 0.01                                 | 0.008                               | 0.007                                    | ±0.008                               | 0.008       | 0.05           | 0.71               | 3500  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.011                                    | ±0.018                               | 0.018       | 0.05           | 0.71               | 3500  |
|  | 0.04                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.05           | 0.71               | 3500  |
|  | 0.03                                | 0.01                                 | 0.008                               | 0.007                                    | ±0.01                                | 0.008       | 0.05           | 0.71               | 3500  |
|  | 0.04                                | 0.012                                | 0.01                                | 0.011                                    | ±0.02                                | 0.018       | 0.05           | 0.71               | 3500  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.05           | 0.71               | 3500  |
|  | 0.03                                | 0.01                                 | 0.008                               | 0.007                                    | ±0.01                                | 0.008       | 0.05           | 0.71               | 3500  |
|  | 0.04                                | 0.012                                | 0.01                                | 0.011                                    | ±0.02                                | 0.018       | 0.05           | 0.71               | 3500  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.05           | 0.71               | 3500  |
|  | 0.04                                | 0.01                                 | 0.008                               | 0.007                                    | ±0.012                               | 0.008       | 0.05           | 0.71               | 3500  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.011                                    | ±0.023                               | 0.018       | 0.05           | 0.71               | 3500  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.05           | 0.71               | 3500  |
|  | 0.04                                | 0.01                                 | 0.008                               | 0.007                                    | ±0.012                               | 0.008       | 0.05           | 0.71               | 3500  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.011                                    | ±0.023                               | 0.018       | 0.05           | 0.71               | 3500  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.05           | 0.71               | 3500  |





## Positioning Ball Screw




| Ball Screw Specifications                    |  |               |              |
|--|--|---------------|--------------|
| Lead (mm)                                    | 5                                      |               |              |
| BCD (mm)                                     | 12.3                                   |               |              |
| Thread minor diameter (mm)                   | 9.6                                    |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1                           |               |              |
| No. of circuits                              | 2.5 turns $\times$ 1 row               |               |              |
| Clearance symbol                             | G0                                     | GT            | G2           |
| Axial clearance (mm)                         | 0                                      | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 2.3                                    | 3.7           | 3.7          |
| Basic static load rating $C_{0a}$ (kN)       | 3.2                                    | 6.4           | 6.4          |
| Preload torque (N·m)                         | $9.8 \times 10^3$ to $4.9 \times 10^2$ | —             | —            |
| Spacer ball                                  | 1 : 1                                  | None          | None         |
| Rigidity value (N/ $\mu$ m)                  | 60                                     | 120           |              |
| Circulation method                           | Return pipe                            |               |              |

Unit: mm

|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>$\text{min}^{-1}$ |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.02                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.01$                           | 0.008       | 0.22           | 0.61               | 5000  |
|  | 0.035                               | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.02$                           | 0.018       | 0.22           | 0.61               | 5000  |
|  | 0.04                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.22           | 0.61               | 5000  |
|  | 0.03                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.01$                           | 0.008       | 0.22           | 0.61               | 5000  |
|  | 0.04                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.02$                           | 0.018       | 0.22           | 0.61               | 5000  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.22           | 0.61               | 5000  |
|  | 0.03                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.012$                          | 0.008       | 0.22           | 0.61               | 5000  |
|  | 0.04                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.023$                          | 0.018       | 0.22           | 0.61               | 5000  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.22           | 0.61               | 5000  |
|  | 0.04                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.012$                          | 0.008       | 0.22           | 0.61               | 5000  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.023$                          | 0.018       | 0.22           | 0.61               | 5000  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.22           | 0.61               | 5000  |
|  | 0.04                                | 0.009                                | 0.008                               | 0.008                                    | $\pm 0.012$                          | 0.008       | 0.22           | 0.61               | 5000  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.011                                    | $\pm 0.023$                          | 0.018       | 0.22           | 0.61               | 5000  |
|  | 0.065                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.22           | 0.61               | 5000  |


# BNK1208-2.6 Shaft diameter: 12; lead: 8

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.                | Stroke | Screw shaft length |                |                |
|--------------------------|--------|--------------------|----------------|----------------|
|                          |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 1208-2.6RRG2+180LC7Y | 50     | 110                | 125            | 180            |
| BNK 1208-2.6RRG2+230LC7Y | 100    | 160                | 175            | 230            |
| BNK 1208-2.6RRG2+280LC7Y | 150    | 210                | 225            | 280            |
| BNK 1208-2.6RRG2+330LC7Y | 200    | 260                | 275            | 330            |
| BNK 1208-2.6RRG2+380LC7Y | 250    | 310                | 325            | 380            |

## Positioning Ball Screw




| Ball Screw Specifications                     |                   |
|---|-------------------|
| Lead (mm)                                     | 8                 |
| BCD (mm)                                      | 12.65             |
| Thread minor diameter (mm)                    | 9.7               |
| Threading direction, No. of threaded grooves  | Rightward, 1      |
| No. of circuits                               | 2.6 turns × 1 row |
| Clearance symbol                              | G2                |
| Axial clearance (mm)                          | 0.02 or less      |
| Basic dynamic load rating Ca (kN)             | 4.7               |
| Basic static load rating C <sub>0a</sub> (kN) | 7.5               |
| Preload torque (N·m)                          | —                 |
| Spacer ball                                   | None              |
| Rigidity value (N/μm)                         | 127               |
| Circulation method                            | Return pipe       |

Unit: mm

|  | Runout of the screw shaft axis | Runout of the nut circumference | Flange mounting surface runout | Runout of the thread groove surface | Lead angle accuracy        | Nut mass | Shaft mass | Permissible rotational speed |
|--|--------------------------------|---------------------------------|--------------------------------|-------------------------------------|----------------------------|----------|------------|------------------------------|
|  | D                              | H                               | I                              | J                                   |                            | kg       | kg/m       | min <sup>-1</sup>            |
|  | 0.04                           | 0.02                            | 0.014                          | 0.014                               | Travel distance: ±0.05/300 | 0.269    | 0.64       | 3500                         |
|  | 0.055                          | 0.02                            | 0.014                          | 0.014                               | Travel distance: ±0.05/300 | 0.269    | 0.64       | 3500                         |
|  | 0.055                          | 0.02                            | 0.014                          | 0.014                               | Travel distance: ±0.05/300 | 0.269    | 0.64       | 3500                         |
|  | 0.065                          | 0.02                            | 0.014                          | 0.014                               | Travel distance: ±0.05/300 | 0.269    | 0.64       | 3500                         |
|  | 0.065                          | 0.02                            | 0.014                          | 0.014                               | Travel distance: ±0.05/300 | 0.269    | 0.64       | 3500                         |

# BNK1402-3 Shaft diameter: 14; lead: 2

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.              | Stroke | Screw shaft length |                |                |
|------------------------|--------|--------------------|----------------|----------------|
|                        |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 1402-3RRG0+166LC3Y | 50     | 85                 | 99             | 166            |
| BNK 1402-3RRG0+166LC5Y |        |                    |                |                |
| BNK 1402-3RRG2+166LC7Y |        |                    |                |                |
| BNK 1402-3RRG0+216LC3Y | 100    | 135                | 149            | 216            |
| BNK 1402-3RRG0+216LC5Y |        |                    |                |                |
| BNK 1402-3RRG2+216LC7Y |        |                    |                |                |
| BNK 1402-3RRG0+266LC3Y | 150    | 185                | 199            | 266            |
| BNK 1402-3RRG0+266LC5Y |        |                    |                |                |
| BNK 1402-3RRG2+266LC7Y |        |                    |                |                |
| BNK 1402-3RRG0+316LC3Y | 200    | 235                | 249            | 316            |
| BNK 1402-3RRG0+316LC5Y |        |                    |                |                |
| BNK 1402-3RRG2+316LC7Y |        |                    |                |                |
| BNK 1402-3RRG0+416LC3Y | 300    | 335                | 349            | 416            |
| BNK 1402-3RRG0+416LC5Y |        |                    |                |                |
| BNK 1402-3RRG2+416LC7Y |        |                    |                |                |


Note) A stainless steel type is also available for model BNK1402. When placing an order, add symbol "M" to the end of the model number.

(Example) BNK1402-3RRG0+166LC3Y M

Symbol for stainless steel type

For accuracy grades C3 and C5, clearance GT is also available as standard.

## Positioning Ball Screw



X-X arrow view

| Ball Screw Specifications                    |  |               |              |
|--|--|---------------|--------------|
| Lead (mm)                                    | 2                                      |               |              |
| BCD (mm)                                     | 14.3                                   |               |              |
| Thread minor diameter (mm)                   | 13                                     |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1                           |               |              |
| No. of circuits                              | 1 turn × 3 rows                        |               |              |
| Clearance symbol                             | G0                                     | GT            | G2           |
| Axial clearance (mm)                         | 0                                      | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 1.8                                    | 1.8           | 1.8          |
| Basic static load rating $C_{0a}$ (kN)       | 4.3                                    | 4.3           | 4.3          |
| Preload torque (N·m)                         | $4.9 \times 10^3$ to $4.9 \times 10^2$ | —             | —            |
| Spacer ball                                  | None                                   | None          | None         |
| Rigidity value (N/μm)                        | 140                                    |               |              |
| Circulation method                           | Deflector                              |               |              |


Unit: mm

|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.02                                | 0.01                                 | 0.008                               | 0.009                                    | ±0.008                               | 0.008       | 0.15           | 1.0                | 3500  |
|  | 0.025                               | 0.012                                | 0.01                                | 0.012                                    | ±0.018                               | 0.018       | 0.15           | 1.0                | 3500  |
|  | 0.04                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.15           | 1.0                | 3500  |
|  | 0.025                               | 0.01                                 | 0.008                               | 0.009                                    | ±0.01                                | 0.008       | 0.15           | 1.0                | 3500  |
|  | 0.03                                | 0.012                                | 0.01                                | 0.012                                    | ±0.02                                | 0.018       | 0.15           | 1.0                | 3500  |
|  | 0.045                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.15           | 1.0                | 3500  |
|  | 0.025                               | 0.01                                 | 0.008                               | 0.009                                    | ±0.01                                | 0.008       | 0.15           | 1.0                | 3500  |
|  | 0.03                                | 0.012                                | 0.01                                | 0.012                                    | ±0.02                                | 0.018       | 0.15           | 1.0                | 3500  |
|  | 0.045                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.15           | 1.0                | 3500  |
|  | 0.03                                | 0.01                                 | 0.008                               | 0.009                                    | ±0.012                               | 0.008       | 0.15           | 1.0                | 3500  |
|  | 0.04                                | 0.012                                | 0.01                                | 0.012                                    | ±0.023                               | 0.018       | 0.15           | 1.0                | 3500  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.15           | 1.0                | 3500  |
|  | 0.04                                | 0.01                                 | 0.008                               | 0.009                                    | ±0.013                               | 0.01        | 0.15           | 1.0                | 3500  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.012                                    | ±0.025                               | 0.02        | 0.15           | 1.0                | 3500  |
|  | 0.06                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.15           | 1.0                | 3500  |

# BNK1404-3 Shaft diameter: 14; lead: 4

DN value

70000



| Model No.              | Stroke | Screw shaft length |                |                |
|------------------------|--------|--------------------|----------------|----------------|
|                        |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 1404-3RRG0+230LC3Y | 100    | 148                | 163            | 230            |
| BNK 1404-3RRG0+230LC5Y |        |                    |                |                |
| BNK 1404-3RRG2+230LC7Y |        |                    |                |                |
| BNK 1404-3RRG0+280LC3Y | 150    | 198                | 213            | 280            |
| BNK 1404-3RRG0+280LC5Y |        |                    |                |                |
| BNK 1404-3RRG2+280LC7Y |        |                    |                |                |
| BNK 1404-3RRG0+330LC3Y | 200    | 248                | 263            | 330            |
| BNK 1404-3RRG0+330LC5Y |        |                    |                |                |
| BNK 1404-3RRG2+330LC7Y |        |                    |                |                |
| BNK 1404-3RRG0+430LC3Y | 300    | 348                | 363            | 430            |
| BNK 1404-3RRG0+430LC5Y |        |                    |                |                |
| BNK 1404-3RRG2+430LC7Y |        |                    |                |                |
| BNK 1404-3RRG0+530LC3Y | 400    | 448                | 463            | 530            |
| BNK 1404-3RRG0+530LC5Y |        |                    |                |                |
| BNK 1404-3RRG2+530LC7Y |        |                    |                |                |


Note) A stainless steel type is also available for model BNK1404. When placing an order, add symbol "M" to the end of the model number.

(Example) BNK1404-3RRG0+230LC3Y M

Symbol for stainless steel type

For accuracy grades C3 and C5, clearance GT is also available as standard.

## Positioning Ball Screw



| Ball Screw Specifications                    |  |               |              |
|--|--|---------------|--------------|
| Lead (mm)                                    | 4                                      |               |              |
| BCD (mm)                                     | 14.65                                  |               |              |
| Thread minor diameter (mm)                   | 12.2                                   |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1                           |               |              |
| No. of circuits                              | 1 turn × 3 rows                        |               |              |
| Clearance symbol                             | G0                                     | GT            | G2           |
| Axial clearance (mm)                         | 0                                      | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 4.2                                    | 4.2           | 4.2          |
| Basic static load rating $C_{0a}$ (kN)       | 7.6                                    | 7.6           | 7.6          |
| Preload torque (N·m)                         | $9.8 \times 10^3$ to $6.9 \times 10^2$ | —             | —            |
| Spacer ball                                  | None                                   | None          | None         |
| Rigidity value (N/μm)                        | 190                                    |               |              |
| Circulation method                           | Deflector                              |               |              |

Unit: mm


|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.025                               | 0.01                                 | 0.008                               | 0.009                                    | ±0.01                                | 0.008       | 0.13           | 0.8                | 3500  |
|  | 0.03                                | 0.012                                | 0.01                                | 0.012                                    | ±0.02                                | 0.018       | 0.13           | 0.8                | 3500  |
|  | 0.045                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.13           | 0.8                | 3500  |
|  | 0.025                               | 0.01                                 | 0.008                               | 0.009                                    | ±0.01                                | 0.008       | 0.13           | 0.8                | 3500  |
|  | 0.03                                | 0.012                                | 0.01                                | 0.012                                    | ±0.02                                | 0.018       | 0.13           | 0.8                | 3500  |
|  | 0.045                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.13           | 0.8                | 3500  |
|  | 0.03                                | 0.01                                 | 0.008                               | 0.009                                    | ±0.012                               | 0.008       | 0.13           | 0.8                | 3500  |
|  | 0.04                                | 0.012                                | 0.01                                | 0.012                                    | ±0.023                               | 0.018       | 0.13           | 0.8                | 3500  |
|  | 0.055                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.13           | 0.8                | 3500  |
|  | 0.04                                | 0.01                                 | 0.008                               | 0.009                                    | ±0.013                               | 0.01        | 0.13           | 0.8                | 3500  |
|  | 0.05                                | 0.012                                | 0.01                                | 0.012                                    | ±0.025                               | 0.02        | 0.13           | 0.8                | 3500  |
|  | 0.06                                | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.13           | 0.8                | 3500  |
|  | 0.045                               | 0.01                                 | 0.008                               | 0.009                                    | ±0.015                               | 0.01        | 0.13           | 0.8                | 3500  |
|  | 0.055                               | 0.012                                | 0.01                                | 0.012                                    | ±0.027                               | 0.02        | 0.13           | 0.8                | 3500  |
|  | 0.075                               | 0.02                                 | 0.014                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.13           | 0.8                | 3500  |

Ball Screw

# BNK1408-2.5 Shaft diameter: 14; lead: 8

DN value

70000




| Model No.                | Stroke | Screw shaft length |                |                |
|--------------------------|--------|--------------------|----------------|----------------|
|                          |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 1408-2.5RRG0+321LC5Y | 150    | 239                | 254            | 321            |
| BNK 1408-2.5RRG2+321LC7Y |        |                    |                |                |
| BNK 1408-2.5RRG0+371LC5Y | 200    | 289                | 304            | 371            |
| BNK 1408-2.5RRG2+371LC7Y |        |                    |                |                |
| BNK 1408-2.5RRG0+421LC5Y | 250    | 339                | 354            | 421            |
| BNK 1408-2.5RRG2+421LC7Y |        |                    |                |                |
| BNK 1408-2.5RRG0+471LC5Y | 300    | 389                | 404            | 471            |
| BNK 1408-2.5RRG2+471LC7Y |        |                    |                |                |
| BNK 1408-2.5RRG0+521LC5Y | 350    | 439                | 454            | 521            |
| BNK 1408-2.5RRG2+521LC7Y |        |                    |                |                |
| BNK 1408-2.5RRG0+571LC5Y | 400    | 489                | 504            | 571            |
| BNK 1408-2.5RRG2+571LC7Y |        |                    |                |                |
| BNK 1408-2.5RRG0+621LC5Y | 450    | 539                | 554            | 621            |
| BNK 1408-2.5RRG2+621LC7Y |        |                    |                |                |
| BNK 1408-2.5RRG0+671LC5Y | 500    | 589                | 604            | 671            |
| BNK 1408-2.5RRG2+671LC7Y |        |                    |                |                |
| BNK 1408-2.5RRG0+721LC5Y | 550    | 639                | 654            | 721            |
| BNK 1408-2.5RRG2+721LC7Y |        |                    |                |                |
| BNK 1408-2.5RRG0+771LC5Y | 600    | 689                | 704            | 771            |
| BNK 1408-2.5RRG2+771LC7Y |        |                    |                |                |
| BNK 1408-2.5RRG0+871LC5Y | 700    | 789                | 804            | 871            |
| BNK 1408-2.5RRG2+871LC7Y |        |                    |                |                |

Note) For accuracy grade C5, clearance GT is also standardized.  
Plug the unused lubrication hole before using the product.



## Positioning Ball Screw



| Ball Screw Specifications                    |   |               |              |
|--|---|---------------|--------------|
| Lead (mm)                                    | 8                                       |               |              |
| BCD (mm)                                     | 14.75                                   |               |              |
| Thread minor diameter (mm)                   | 11.2                                    |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1                            |               |              |
| No. of circuits                              | 2.5 turns $\times$ 1 row                |               |              |
| Clearance symbol                             | G0                                      | GT            | G2           |
| Axial clearance (mm)                         | 0                                       | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 4.3                                     | 6.9           | 6.9          |
| Basic static load rating $C_{0a}$ (kN)       | 5.8                                     | 11.5          | 11.5         |
| Preload torque (N-m)                         | $2 \times 10^2$<br>to $7.8 \times 10^2$ | —             | —            |
| Spacer ball                                  | 1 : 1                                   | None          | None         |
| Rigidity value (N/ $\mu$ m)                  | 80                                      | 150           |              |
| Circulation method                           | Return pipe                             |               |              |

Unit: mm


|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.035                               | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.023$                          | 0.018       | 0.29           | 0.84               | 4740  |
|  | 0.055                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.29           | 0.84               | 4740  |
|  | 0.035                               | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.023$                          | 0.018       | 0.29           | 0.84               | 4740  |
|  | 0.055                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.29           | 0.84               | 4740  |
|  | 0.04                                | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.025$                          | 0.02        | 0.29           | 0.84               | 4740  |
|  | 0.06                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.29           | 0.84               | 4740  |
|  | 0.04                                | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.025$                          | 0.02        | 0.29           | 0.84               | 4740  |
|  | 0.06                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.29           | 0.84               | 4740  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.027$                          | 0.02        | 0.29           | 0.84               | 4740  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.29           | 0.84               | 4740  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.027$                          | 0.02        | 0.29           | 0.84               | 4740  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.29           | 0.84               | 4740  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.03$                           | 0.023       | 0.29           | 0.84               | 4740  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.29           | 0.84               | 4740  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.03$                           | 0.023       | 0.29           | 0.84               | 4740  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.29           | 0.84               | 4740  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.035$                          | 0.025       | 0.29           | 0.84               | 4740  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.29           | 0.84               | 4740  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.035$                          | 0.025       | 0.29           | 0.84               | 4740  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.29           | 0.84               | 4740  |
|  | 0.085                               | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.035$                          | 0.025       | 0.29           | 0.84               | 4740  |
|  | 0.12                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.29           | 0.84               | 4740  |

Ball Screw

# BNK1510-5.6 Shaft diameter: 15; lead: 10

|          |
|----------|
| DN value |
|----------|


|       |
|-------|
| 70000 |
|-------|



| Model No.              | Stroke | Screw shaft length |                |                |
|------------------------|--------|--------------------|----------------|----------------|
|                        |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 1510-5.6G0+321LC5Y | 150    | 239                | 254            | 321            |
| BNK 1510-5.6G2+321LC7Y |        |                    |                |                |
| BNK 1510-5.6G0+371LC5Y | 200    | 289                | 304            | 371            |
| BNK 1510-5.6G2+371LC7Y |        |                    |                |                |
| BNK 1510-5.6G0+421LC5Y | 250    | 339                | 354            | 421            |
| BNK 1510-5.6G2+421LC7Y |        |                    |                |                |
| BNK 1510-5.6G0+471LC5Y | 300    | 389                | 404            | 471            |
| BNK 1510-5.6G2+471LC7Y |        |                    |                |                |
| BNK 1510-5.6G0+521LC5Y | 350    | 439                | 454            | 521            |
| BNK 1510-5.6G2+521LC7Y |        |                    |                |                |
| BNK 1510-5.6G0+571LC5Y | 400    | 489                | 504            | 571            |
| BNK 1510-5.6G2+571LC7Y |        |                    |                |                |
| BNK 1510-5.6G0+621LC5Y | 450    | 539                | 554            | 621            |
| BNK 1510-5.6G2+621LC7Y |        |                    |                |                |
| BNK 1510-5.6G0+671LC5Y | 500    | 589                | 604            | 671            |
| BNK 1510-5.6G2+671LC7Y |        |                    |                |                |
| BNK 1510-5.6G0+721LC5Y | 550    | 639                | 654            | 721            |
| BNK 1510-5.6G2+721LC7Y |        |                    |                |                |
| BNK 1510-5.6G0+771LC5Y | 600    | 689                | 704            | 771            |
| BNK 1510-5.6G2+771LC7Y |        |                    |                |                |
| BNK 1510-5.6G0+871LC5Y | 700    | 789                | 804            | 871            |
| BNK 1510-5.6G2+871LC7Y |        |                    |                |                |
| BNK 1510-5.6G0+971LC5Y | 800    | 889                | 904            | 971            |
| BNK 1510-5.6G2+971LC7Y |        |                    |                |                |

Note) For accuracy grade C5, clearance GT is also standardized.

## Positioning Ball Screw



| Ball Screw Specifications                    |   |               |              |
|--|---|---------------|--------------|
| Lead (mm)                                    | 10                                      |               |              |
| BCD (mm)                                     | 15.75                                   |               |              |
| Thread minor diameter (mm)                   | 12.5                                    |               |              |
| Threading direction, No. of threaded grooves | Rightward, 2                            |               |              |
| No. of circuits                              | 2.8 turns × 2 rows                      |               |              |
| Clearance symbol                             | G0                                      | GT            | G2           |
| Axial clearance (mm)                         | 0                                       | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 9                                       | 14.3          | 14.3         |
| Basic static load rating $C_{0a}$ (kN)       | 13.9                                    | 27.9          | 27.9         |
| Preload torque (N·m)                         | $2 \times 10^2$<br>to $9.8 \times 10^2$ | —             | —            |
| Spacer ball                                  | 1 : 1                                   | None          | None         |
| Rigidity value (N/μm)                        | 190                                     | 350           |              |
| Circulation method                           | End cap                                 |               |              |

Unit: mm


|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.035                               | 0.015                                | 0.011                               | 0.012                                    | ±0.023                               | 0.018       | 0.22           | 0.76               | 4440  |
|  | 0.055                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |
|  | 0.035                               | 0.015                                | 0.011                               | 0.012                                    | ±0.023                               | 0.018       | 0.22           | 0.76               | 4440  |
|  | 0.055                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |
|  | 0.04                                | 0.015                                | 0.011                               | 0.012                                    | ±0.025                               | 0.02        | 0.22           | 0.76               | 4440  |
|  | 0.06                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |
|  | 0.04                                | 0.015                                | 0.011                               | 0.012                                    | ±0.025                               | 0.02        | 0.22           | 0.76               | 4440  |
|  | 0.06                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | ±0.027                               | 0.02        | 0.22           | 0.76               | 4440  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | ±0.027                               | 0.02        | 0.22           | 0.76               | 4440  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | ±0.03                                | 0.023       | 0.22           | 0.76               | 4440  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | ±0.03                                | 0.023       | 0.22           | 0.76               | 4440  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | ±0.035                               | 0.025       | 0.22           | 0.76               | 4440  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | ±0.035                               | 0.025       | 0.22           | 0.76               | 4440  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |
|  | 0.085                               | 0.015                                | 0.011                               | 0.012                                    | ±0.035                               | 0.025       | 0.22           | 0.76               | 4440  |
|  | 0.12                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |
|  | 0.085                               | 0.015                                | 0.011                               | 0.012                                    | ±0.04                                | 0.027       | 0.22           | 0.76               | 4440  |
|  | 0.12                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.22           | 0.76               | 4440  |

Ball Screw

# BNK1520-3 Shaft diameter: 15; lead: 20

DN value


70000



| Model No.            | Stroke | Screw shaft length |                |                |
|----------------------|--------|--------------------|----------------|----------------|
|                      |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 1520-3G0+321LC5Y | 150    | 236                | 254            | 321            |
| BNK 1520-3G2+321LC7Y |        |                    |                |                |
| BNK 1520-3G0+371LC5Y | 200    | 286                | 304            | 371            |
| BNK 1520-3G2+371LC7Y |        |                    |                |                |
| BNK 1520-3G0+421LC5Y | 250    | 336                | 354            | 421            |
| BNK 1520-3G2+421LC7Y |        |                    |                |                |
| BNK 1520-3G0+471LC5Y | 300    | 386                | 404            | 471            |
| BNK 1520-3G2+471LC7Y |        |                    |                |                |
| BNK 1520-3G0+521LC5Y | 350    | 436                | 454            | 521            |
| BNK 1520-3G2+521LC7Y |        |                    |                |                |
| BNK 1520-3G0+571LC5Y | 400    | 486                | 504            | 571            |
| BNK 1520-3G2+571LC7Y |        |                    |                |                |
| BNK 1520-3G0+621LC5Y | 450    | 536                | 554            | 621            |
| BNK 1520-3G2+621LC7Y |        |                    |                |                |
| BNK 1520-3G0+671LC5Y | 500    | 586                | 604            | 671            |
| BNK 1520-3G2+671LC7Y |        |                    |                |                |
| BNK 1520-3G0+721LC5Y | 550    | 636                | 654            | 721            |
| BNK 1520-3G2+721LC7Y |        |                    |                |                |
| BNK 1520-3G0+771LC5Y | 600    | 686                | 704            | 771            |
| BNK 1520-3G2+771LC7Y |        |                    |                |                |
| BNK 1520-3G0+871LC5Y | 700    | 786                | 804            | 871            |
| BNK 1520-3G2+871LC7Y |        |                    |                |                |
| BNK 1520-3G0+971LC5Y | 800    | 886                | 904            | 971            |
| BNK 1520-3G2+971LC7Y |        |                    |                |                |

Note) For accuracy grade C5, clearance GT is also standardized.

## Positioning Ball Screw



| Ball Screw Specifications                    |   |               |              |
|--|---|---------------|--------------|
| Lead (mm)                                    | 20                                      |               |              |
| BCD (mm)                                     | 15.75                                   |               |              |
| Thread minor diameter (mm)                   | 12.5                                    |               |              |
| Threading direction, No. of threaded grooves | Rightward, 2                            |               |              |
| No. of circuits                              | 1.5 turns × 2 rows                      |               |              |
| Clearance symbol                             | G0                                      | GT            | G2           |
| Axial clearance (mm)                         | 0                                       | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 5.1                                     | 8             | 8            |
| Basic static load rating $C_{0a}$ (kN)       | 7.9                                     | 15.8          | 15.8         |
| Preload torque (N·m)                         | $2 \times 10^2$<br>to $8.8 \times 10^2$ | —             | —            |
| Spacer ball                                  | 1 : 1                                   | None          | None         |
| Rigidity value (N/μm)                        | 110                                     | 200           |              |
| Circulation method                           | End cap                                 |               |              |

Unit: mm


|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.035                               | 0.015                                | 0.011                               | 0.012                                    | ±0.023                               | 0.018       | 0.32           | 1.05               | 4440  |
|  | 0.055                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |
|  | 0.035                               | 0.015                                | 0.011                               | 0.012                                    | ±0.023                               | 0.018       | 0.32           | 1.05               | 4440  |
|  | 0.055                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |
|  | 0.04                                | 0.015                                | 0.011                               | 0.012                                    | ±0.025                               | 0.02        | 0.32           | 1.05               | 4440  |
|  | 0.06                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |
|  | 0.04                                | 0.015                                | 0.011                               | 0.012                                    | ±0.025                               | 0.02        | 0.32           | 1.05               | 4440  |
|  | 0.06                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | ±0.027                               | 0.02        | 0.32           | 1.05               | 4440  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | ±0.027                               | 0.02        | 0.32           | 1.05               | 4440  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | ±0.03                                | 0.023       | 0.32           | 1.05               | 4440  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | ±0.03                                | 0.023       | 0.32           | 1.05               | 4440  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | ±0.035                               | 0.025       | 0.32           | 1.05               | 4440  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | ±0.035                               | 0.025       | 0.32           | 1.05               | 4440  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |
|  | 0.085                               | 0.015                                | 0.011                               | 0.012                                    | ±0.035                               | 0.025       | 0.32           | 1.05               | 4440  |
|  | 0.12                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |
|  | 0.085                               | 0.015                                | 0.011                               | 0.012                                    | ±0.04                                | 0.027       | 0.32           | 1.05               | 4440  |
|  | 0.12                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.32           | 1.05               | 4440  |

Ball Screw

# BNK1616-3.6 Shaft diameter: 16; lead: 16

DN value


70000



| Model No.              | Stroke | Screw shaft length |                |                |
|------------------------|--------|--------------------|----------------|----------------|
|                        |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 1616-3.6G0+321LC5Y | 150    | 234                | 254            | 321            |
| BNK 1616-3.6G2+321LC7Y |        |                    |                |                |
| BNK 1616-3.6G0+371LC5Y | 200    | 284                | 304            | 371            |
| BNK 1616-3.6G2+371LC7Y |        |                    |                |                |
| BNK 1616-3.6G0+421LC5Y | 250    | 334                | 354            | 421            |
| BNK 1616-3.6G2+421LC7Y |        |                    |                |                |
| BNK 1616-3.6G0+471LC5Y | 300    | 384                | 404            | 471            |
| BNK 1616-3.6G2+471LC7Y |        |                    |                |                |
| BNK 1616-3.6G0+521LC5Y | 350    | 434                | 454            | 521            |
| BNK 1616-3.6G2+521LC7Y |        |                    |                |                |
| BNK 1616-3.6G0+571LC5Y | 400    | 484                | 504            | 571            |
| BNK 1616-3.6G2+571LC7Y |        |                    |                |                |
| BNK 1616-3.6G0+621LC5Y | 450    | 534                | 554            | 621            |
| BNK 1616-3.6G2+621LC7Y |        |                    |                |                |
| BNK 1616-3.6G0+671LC5Y | 500    | 584                | 604            | 671            |
| BNK 1616-3.6G2+671LC7Y |        |                    |                |                |
| BNK 1616-3.6G0+721LC5Y | 550    | 634                | 654            | 721            |
| BNK 1616-3.6G2+721LC7Y |        |                    |                |                |
| BNK 1616-3.6G0+771LC5Y | 600    | 684                | 704            | 771            |
| BNK 1616-3.6G2+771LC7Y |        |                    |                |                |
| BNK 1616-3.6G0+871LC5Y | 700    | 784                | 804            | 871            |
| BNK 1616-3.6G2+871LC7Y |        |                    |                |                |
| BNK 1616-3.6G0+971LC5Y | 800    | 884                | 904            | 971            |
| BNK 1616-3.6G2+971LC7Y |        |                    |                |                |

Note) For accuracy grade C5, clearance GT is also standardized.

## Positioning Ball Screw



| Ball Screw Specifications                    |   |               |              |
|--|---|---------------|--------------|
| Lead (mm)                                    | 16                                      |               |              |
| BCD (mm)                                     | 16.65                                   |               |              |
| Thread minor diameter (mm)                   | 13.7                                    |               |              |
| Threading direction, No. of threaded grooves | Rightward, 2                            |               |              |
| No. of circuits                              | 1.8 turns × 2 rows                      |               |              |
| Clearance symbol                             | G0                                      | GT            | G2           |
| Axial clearance (mm)                         | 0                                       | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 4.4                                     | 7.1           | 7.1          |
| Basic static load rating $C_{0a}$ (kN)       | 7.2                                     | 14.3          | 14.3         |
| Preload torque (N-m)                         | $2 \times 10^2$<br>to $9.8 \times 10^2$ | —             | —            |
| Spacer ball                                  | 1 : 1                                   | None          | None         |
| Rigidity value (N/μm)                        | 120                                     | 230           |              |
| Circulation method                           | End cap                                 |               |              |

Unit: mm


|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.035                               | 0.015                                | 0.011                               | 0.012                                    | ±0.023                               | 0.018       | 0.2            | 1.25               | 4200  |
|  | 0.055                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.2            | 1.25               | 4200  |
|  | 0.035                               | 0.015                                | 0.011                               | 0.012                                    | ±0.023                               | 0.018       | 0.2            | 1.25               | 4200  |
|  | 0.055                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.2            | 1.25               | 4200  |
|  | 0.04                                | 0.015                                | 0.011                               | 0.012                                    | ±0.025                               | 0.02        | 0.2            | 1.25               | 4200  |
|  | 0.06                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.2            | 1.25               | 4200  |
|  | 0.04                                | 0.015                                | 0.011                               | 0.012                                    | ±0.025                               | 0.02        | 0.2            | 1.25               | 4200  |
|  | 0.06                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.2            | 1.25               | 4200  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | ±0.027                               | 0.02        | 0.2            | 1.25               | 4200  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.2            | 1.25               | 4200  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | ±0.027                               | 0.02        | 0.2            | 1.25               | 4200  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.2            | 1.25               | 4200  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | ±0.03                                | 0.023       | 0.2            | 1.25               | 4200  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.2            | 1.25               | 4200  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | ±0.03                                | 0.023       | 0.2            | 1.25               | 4200  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.2            | 1.25               | 4200  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | ±0.035                               | 0.025       | 0.2            | 1.25               | 4200  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.2            | 1.25               | 4200  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | ±0.035                               | 0.025       | 0.2            | 1.25               | 4200  |
|  | 0.12                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.2            | 1.25               | 4200  |
|  | 0.085                               | 0.015                                | 0.011                               | 0.012                                    | ±0.04                                | 0.027       | 0.2            | 1.25               | 4200  |
|  | 0.12                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.2            | 1.25               | 4200  |

Ball Screw

# BNK2010-2.5 Shaft diameter: 20; lead: 10

DN value

70000




| Model No.                 | Stroke | Screw shaft length |                |                |
|---------------------------|--------|--------------------|----------------|----------------|
|                           |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 2010-2.5RRG0+499LC5Y  | 300    | 389                | 414            | 499            |
| BNK 2010-2.5RRG2+499LC7Y  |        |                    |                |                |
| BNK 2010-2.5RRG0+599LC5Y  | 400    | 489                | 514            | 599            |
| BNK 2010-2.5RRG2+599LC7Y  |        |                    |                |                |
| BNK 2010-2.5RRG0+699LC5Y  | 500    | 589                | 614            | 699            |
| BNK 2010-2.5RRG2+699LC7Y  |        |                    |                |                |
| BNK 2010-2.5RRG0+799LC5Y  | 600    | 689                | 714            | 799            |
| BNK 2010-2.5RRG2+799LC7Y  |        |                    |                |                |
| BNK 2010-2.5RRG0+899LC5Y  | 700    | 789                | 814            | 899            |
| BNK 2010-2.5RRG2+899LC7Y  |        |                    |                |                |
| BNK 2010-2.5RRG0+999LC5Y  | 800    | 889                | 914            | 999            |
| BNK 2010-2.5RRG2+999LC7Y  |        |                    |                |                |
| BNK 2010-2.5RRG0+1099LC5Y | 900    | 989                | 1014           | 1099           |
| BNK 2010-2.5RRG2+1099LC7Y |        |                    |                |                |
| BNK 2010-2.5RRG0+1199LC5Y | 1000   | 1089               | 1114           | 1199           |
| BNK 2010-2.5RRG2+1199LC7Y |        |                    |                |                |
| BNK 2010-2.5RRG0+1299LC5Y | 1100   | 1189               | 1214           | 1299           |
| BNK 2010-2.5RRG2+1299LC7Y |        |                    |                |                |

Note) For accuracy grade C5, clearance GT is also standardized.  
Plug the unused lubrication hole before using the product.



## Positioning Ball Screw



| Ball Screw Specifications                    |   |               |              |
|--|---|---------------|--------------|
| Lead (mm)                                    | 10                                      |               |              |
| BCD (mm)                                     | 21                                      |               |              |
| Thread minor diameter (mm)                   | 16.4                                    |               |              |
| Threading direction, No. of threaded grooves | Rightward, 1                            |               |              |
| No. of circuits                              | 2.5 turns $\times$ 1 row                |               |              |
| Clearance symbol                             | G0                                      | GT            | G2           |
| Axial clearance (mm)                         | 0                                       | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 7                                       | 11.1          | 11.1         |
| Basic static load rating $C_{0a}$ (kN)       | 11                                      | 22            | 22           |
| Preload torque (N-m)                         | $2 \times 10^2$<br>to $9.8 \times 10^2$ | —             | —            |
| Spacer ball                                  | 1 : 1                                   | None          | None         |
| Rigidity value (N/ $\mu$ m)                  | 110                                     | 210           |              |
| Circulation method                           | Return pipe                             |               |              |


Unit: mm

|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.04                                | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.025$                          | 0.02        | 0.58           | 1.81               | 3330  |
|  | 0.06                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.58           | 1.81               | 3330  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.027$                          | 0.02        | 0.58           | 1.81               | 3330  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.58           | 1.81               | 3330  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.03$                           | 0.023       | 0.58           | 1.81               | 3330  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.58           | 1.81               | 3330  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.035$                          | 0.025       | 0.58           | 1.81               | 3330  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.58           | 1.81               | 3330  |
|  | 0.085                               | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.035$                          | 0.025       | 0.58           | 1.81               | 3330  |
|  | 0.12                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.58           | 1.81               | 3330  |
|  | 0.085                               | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.04$                           | 0.027       | 0.58           | 1.81               | 3330  |
|  | 0.12                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.58           | 1.81               | 3330  |
|  | 0.11                                | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.04$                           | 0.027       | 0.58           | 1.81               | 3330  |
|  | 0.15                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.58           | 1.81               | 3330  |
|  | 0.11                                | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.046$                          | 0.03        | 0.58           | 1.81               | 3330  |
|  | 0.15                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.58           | 1.81               | 3330  |
|  | 0.15                                | 0.015                                | 0.011                               | 0.012                                    | $\pm 0.046$                          | 0.03        | 0.58           | 1.81               | 3330  |
|  | 0.19                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: $\pm 0.05/300$      |             | 0.58           | 1.81               | 3330  |

Ball Screw

# BNK200-3.6 Shaft diameter: 20; lead: 20


|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.               | Stroke | Screw shaft length |                |                |
|-------------------------|--------|--------------------|----------------|----------------|
|                         |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 2020-3.6G0+520LC5Y  | 300    | 410                | 435            | 520            |
| BNK 2020-3.6G2+520LC7Y  |        |                    |                |                |
| BNK 2020-3.6G0+620LC5Y  | 400    | 510                | 535            | 620            |
| BNK 2020-3.6G2+620LC7Y  |        |                    |                |                |
| BNK 2020-3.6G0+720LC5Y  | 500    | 610                | 635            | 720            |
| BNK 2020-3.6G2+720LC7Y  |        |                    |                |                |
| BNK 2020-3.6G0+820LC5Y  | 600    | 710                | 735            | 820            |
| BNK 2020-3.6G2+820LC7Y  |        |                    |                |                |
| BNK 2020-3.6G0+920LC5Y  | 700    | 810                | 835            | 920            |
| BNK 2020-3.6G2+920LC7Y  |        |                    |                |                |
| BNK 2020-3.6G0+1020LC5Y | 800    | 910                | 935            | 1020           |
| BNK 2020-3.6G2+1020LC7Y |        |                    |                |                |
| BNK 2020-3.6G0+1120LC5Y | 900    | 1010               | 1035           | 1120           |
| BNK 2020-3.6G2+1120LC7Y |        |                    |                |                |
| BNK 2020-3.6G0+1220LC5Y | 1000   | 1110               | 1135           | 1220           |
| BNK 2020-3.6G2+1220LC7Y |        |                    |                |                |
| BNK 2020-3.6G0+1320LC5Y | 1100   | 1210               | 1235           | 1320           |
| BNK 2020-3.6G2+1320LC7Y |        |                    |                |                |

Note) For accuracy grade C5, clearance GT is also standardized.

## Positioning Ball Screw



| Ball Screw Specifications                    |   |               |              |
|--|---|---------------|--------------|
| Lead (mm)                                    | 20                                      |               |              |
| BCD (mm)                                     | 20.75                                   |               |              |
| Thread minor diameter (mm)                   | 17.5                                    |               |              |
| Threading direction, No. of threaded grooves | Rightward, 2                            |               |              |
| No. of circuits                              | 1.8 turns × 2 rows                      |               |              |
| Clearance symbol                             | G0                                      | GT            | G2           |
| Axial clearance (mm)                         | 0                                       | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 7                                       | 11.1          | 11.1         |
| Basic static load rating $C_{0a}$ (kN)       | 12.3                                    | 24.7          | 24.7         |
| Preload torque (N·m)                         | $2 \times 10^2$<br>to $9.8 \times 10^2$ | —             | —            |
| Spacer ball                                  | 1 : 1                                   | None          | None         |
| Rigidity value (N/μm)                        | 160                                     | 290           |              |
| Circulation method                           | End cap                                 |               |              |


Unit: mm

|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | ±0.027                               | 0.02        | 0.39           | 2.04               | 3370  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.39           | 2.04               | 3370  |
|  | 0.05                                | 0.015                                | 0.011                               | 0.012                                    | ±0.03                                | 0.023       | 0.39           | 2.04               | 3370  |
|  | 0.075                               | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.39           | 2.04               | 3370  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.012                                    | ±0.03                                | 0.023       | 0.39           | 2.04               | 3370  |
|  | 0.09                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.39           | 2.04               | 3370  |
|  | 0.085                               | 0.015                                | 0.011                               | 0.012                                    | ±0.035                               | 0.025       | 0.39           | 2.04               | 3370  |
|  | 0.12                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.39           | 2.04               | 3370  |
|  | 0.085                               | 0.015                                | 0.011                               | 0.012                                    | ±0.04                                | 0.027       | 0.39           | 2.04               | 3370  |
|  | 0.12                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.39           | 2.04               | 3370  |
|  | 0.11                                | 0.015                                | 0.011                               | 0.012                                    | ±0.04                                | 0.027       | 0.39           | 2.04               | 3370  |
|  | 0.15                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.39           | 2.04               | 3370  |
|  | 0.11                                | 0.015                                | 0.011                               | 0.012                                    | ±0.046                               | 0.03        | 0.39           | 2.04               | 3370  |
|  | 0.15                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.39           | 2.04               | 3370  |
|  | 0.11                                | 0.015                                | 0.011                               | 0.012                                    | ±0.046                               | 0.03        | 0.39           | 2.04               | 3370  |
|  | 0.15                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.39           | 2.04               | 3370  |
|  | 0.15                                | 0.015                                | 0.011                               | 0.012                                    | ±0.046                               | 0.03        | 0.39           | 2.04               | 3370  |
|  | 0.19                                | 0.03                                 | 0.018                               | 0.014                                    | Travel distance: ±0.05/300           |             | 0.39           | 2.04               | 3370  |

Ball Screw

# BNK2520-3.6 Shaft diameter: 25; lead: 20


|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.               | Stroke | Screw shaft length |                |                |
|-------------------------|--------|--------------------|----------------|----------------|
|                         |        | L <sub>1</sub>     | L <sub>2</sub> | L <sub>3</sub> |
| BNK 2520-3.6G0+751LC5Y  | 500    | 610                | 640            | 751            |
| BNK 2520-3.6G2+751LC7Y  |        |                    |                |                |
| BNK 2520-3.6G0+851LC5Y  | 600    | 710                | 740            | 851            |
| BNK 2520-3.6G2+851LC7Y  |        |                    |                |                |
| BNK 2520-3.6G0+1051LC5Y | 800    | 910                | 940            | 1051           |
| BNK 2520-3.6G2+1051LC7Y |        |                    |                |                |
| BNK 2520-3.6G0+1251LC5Y | 1000   | 1110               | 1140           | 1251           |
| BNK 2520-3.6G2+1251LC7Y |        |                    |                |                |
| BNK 2520-3.6G0+1451LC5Y | 1200   | 1310               | 1340           | 1451           |
| BNK 2520-3.6G2+1451LC7Y |        |                    |                |                |
| BNK 2520-3.6G0+1651LC5Y | 1400   | 1510               | 1540           | 1651           |
| BNK 2520-3.6G2+1651LC7Y |        |                    |                |                |
| BNK 2520-3.6G0+1851LC5Y | 1600   | 1710               | 1740           | 1851           |
| BNK 2520-3.6G2+1851LC7Y |        |                    |                |                |

Note) For accuracy grade C5, clearance GT is also standardized.

## Positioning Ball Screw



| Ball Screw Specifications                    |  |               |              |
|--|--|---------------|--------------|
| Lead (mm)                                    | 20                                     |               |              |
| BCD (mm)                                     | 26                                     |               |              |
| Thread minor diameter (mm)                   | 21.9                                   |               |              |
| Threading direction, No. of threaded grooves | Rightward, 2                           |               |              |
| No. of circuits                              | 1.8 turns × 2 rows                     |               |              |
| Clearance symbol                             | G0                                     | GT            | G2           |
| Axial clearance (mm)                         | 0                                      | 0.005 or less | 0.02 or less |
| Basic dynamic load rating $C_a$ (kN)         | 10.5                                   | 16.7          | 16.7         |
| Basic static load rating $C_{0a}$ (kN)       | 19                                     | 38            | 38           |
| Preload torque (N·m)                         | $4.9 \times 10^2$ to $2.2 \times 10^1$ | —             | —            |
| Spacer ball                                  | 1 : 1                                  | None          | None         |
| Rigidity value (N/μm)                        | 190                                    | 360           |              |
| Circulation method                           | End cap                                |               |              |


Unit: mm

|  | Runout of the screw shaft axis<br>D | Runout of the nut circumference<br>H | Flange mounting surface runout<br>I | Runout of the thread groove surface<br>J | Lead angle accuracy                  |             | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|-------------------------------------|--------------------------------------|-------------------------------------|--|--------------------------------------|-------------|----------------|--------------------|---|
|  |                                     |                                      |                                     |  | Representative travel distance error | Fluctuation |                |                    |   |
|  | 0.055                               | 0.015                                | 0.011                               | 0.013                                    | ±0.03                                | 0.023       | 0.53           | 3.03               | 2690  |
|  | 0.07                                | 0.03                                 | 0.018                               | 0.02                                     | Travel distance: ±0.05/300           |             | 0.53           | 3.03               | 2690  |
|  | 0.065                               | 0.015                                | 0.011                               | 0.013                                    | ±0.035                               | 0.025       | 0.53           | 3.03               | 2690  |
|  | 0.085                               | 0.03                                 | 0.018                               | 0.02                                     | Travel distance: ±0.05/300           |             | 0.53           | 3.03               | 2690  |
|  | 0.085                               | 0.015                                | 0.011                               | 0.013                                    | ±0.04                                | 0.027       | 0.53           | 3.03               | 2690  |
|  | 0.1                                 | 0.03                                 | 0.018                               | 0.02                                     | Travel distance: ±0.05/300           |             | 0.53           | 3.03               | 2690  |
|  | 0.11                                | 0.015                                | 0.011                               | 0.013                                    | ±0.046                               | 0.03        | 0.53           | 3.03               | 2690  |
|  | 0.13                                | 0.03                                 | 0.018                               | 0.02                                     | Travel distance: ±0.05/300           |             | 0.53           | 3.03               | 2690  |
|  | 0.11                                | 0.015                                | 0.011                               | 0.013                                    | ±0.054                               | 0.035       | 0.53           | 3.03               | 2690  |
|  | 0.13                                | 0.03                                 | 0.018                               | 0.02                                     | Travel distance: ±0.05/300           |             | 0.53           | 3.03               | 2690  |
|  | 0.14                                | 0.015                                | 0.011                               | 0.013                                    | ±0.054                               | 0.035       | 0.53           | 3.03               | 2690  |
|  | 0.17                                | 0.03                                 | 0.018                               | 0.02                                     | Travel distance: ±0.05/300           |             | 0.53           | 3.03               | 2690  |
|  | 0.14                                | 0.015                                | 0.011                               | 0.013                                    | ±0.065                               | 0.04        | 0.53           | 3.03               | 2690  |
|  | 0.17                                | 0.03                                 | 0.018                               | 0.02                                     | Travel distance: ±0.05/300           |             | 0.53           | 3.03               | 2690  |

Ball Screw

# MDK (Unfinished Shaft Ends) No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|

4- $\phi$  d<sub>1</sub> through hole

| Model No.  | Ball screw specifications  |      |                                |                       |                        |                   |                 | Nut            |                 |                |     |
|------------|----------------------------|------|--------------------------------|-----------------------|------------------------|-------------------|-----------------|----------------|-----------------|----------------|-----|
|            | Screw shaft outer diameter | Lead | Ball center-to-center diameter | Thread minor diameter | No. of loaded circuits | Basic load rating |                 | Outer diameter | Flange diameter | Overall length | Nut |
|            |                            |      |                                |                       |                        | Ca                | C <sub>0a</sub> |                |                 |                |     |
| d          | Ph                         | dp   | dc                             | Rows X turns          | kN                     | kN                | D               | D <sub>1</sub> | L <sub>1</sub>  | H              |     |
| MDK 0401-3 | 4                          | 1    | 4.15                           | 3.4                   | 3×1                    | 0.29              | 0.42            | 9              | 19              | 13             | 3   |
| MDK 0601-3 | 6                          | 1    | 6.2                            | 5.3                   | 3×1                    | 0.54              | 0.94            | 11             | 23              | 14.5           | 3.5 |
| MDK 0801-3 | 8                          | 1    | 8.2                            | 7.3                   | 3×1                    | 0.64              | 1.4             | 13             | 26              | 15             | 4   |
| MDK 0802-3 | 8                          | 2    | 8.3                            | 7                     | 3×1                    | 1.4               | 2.3             | 15             | 28              | 22             | 5   |
| MDK 1002-3 | 10                         | 2    | 10.3                           | 9                     | 3×1                    | 1.5               | 2.9             | 17             | 34              | 22             | 5   |

## Model number coding

**MDK0401-3 GT +95L C5 A**

Model No.


Overall screw shaft length (in mm)

Unfinished shaft ends code

Symbol for clearance in the axial direction (\*1) Accuracy symbol (\*2)

(\*1) See **A15-19**. (\*2) See **A15-12**.

## Positioning Ball Screw





Unit: mm

| Dimensions     |     |                |    |                           | Screw shaft dimensions |          |          |          |          |                |                |   | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|----------------|-----|----------------|----|---------------------------|------------------------|----------|----------|----------|----------|----------------|----------------|---|----------------|--------------------|---|
| B <sub>1</sub> | PCD | d <sub>1</sub> | Tw | Unfinished Shaft End Code | Overall length<br>L    | $\ell_0$ | $\ell_1$ | $\ell_2$ | $\ell_3$ | d <sub>3</sub> | d <sub>4</sub> | K |                |                    |   |
| 10             | 14  | 2.9            | 13 | A                         | 95                     | 47       | 10       | 35       | 50       | 6.2            | 3.2            | 3 | 0.01           | 0.07               | 3500  |
|                |     |                |    |                           | 115                    | 67       |          |          | 70       |                |                |   |                |                    |   |
|                |     |                |    |                           | 145                    | 97       |          |          | 100      |                |                |   |                |                    |   |
| 11             | 17  | 3.4            | 15 | A                         | 120                    | 67       | 10       | 40       | 70       | 8.2            | 5.3            | 3 | 0.02           | 0.14               | 3500  |
|                |     |                |    |                           | 150                    | 97       |          |          | 100      |                |                |   |                |                    |   |
|                |     |                |    |                           | 180                    | 127      |          |          | 130      |                |                |   |                |                    |   |
| 11             | 20  | 3.4            | 17 | A                         | 130                    | 67       | 15       | 45       | 70       | 10.2           | 7.3            | 3 | 0.02           | 0.29               | 3500  |
|                |     |                |    |                           | 160                    | 97       |          |          | 100      |                |                |   |                |                    |   |
|                |     |                |    |                           | 190                    | 127      |          |          | 130      |                |                |   |                |                    |   |
|                |     |                |    |                           | 240                    | 177      |          |          | 180      |                |                |   |                |                    |   |
| 17             | 22  | 3.4            | 19 | A                         | 140                    | 76       | 15       | 45       | 80       | 10.2           | 7              | 4 | 0.04           | 0.27               | 3500  |
|                |     |                |    |                           | 170                    | 106      |          |          | 110      |                |                |   |                |                    |   |
|                |     |                |    |                           | 200                    | 136      |          |          | 140      |                |                |   |                |                    |   |
|                |     |                |    |                           | 250                    | 186      |          |          | 190      |                |                |   |                |                    |   |
| 17             | 26  | 4.5            | 21 | A                         | 160                    | 86       | 15       | 55       | 90       | 12.2           | 9              | 4 | 0.05           | 0.47               | 3500  |
|                |     |                |    |                           | 210                    | 136      |          |          | 140      |                |                |   |                |                    |   |
|                |     |                |    |                           | 260                    | 186      |          |          | 190      |                |                |   |                |                    |   |
|                |     |                |    |                           | 310                    | 236      |          |          | 240      |                |                |   |                |                    |   |

Note) Models MDK 0401, 0601, and 0801 are not provided with a labyrinth seal.

# MDK (Unfinished Shaft Ends) No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|

4- $\phi d_1$  through hole

MDK1202/1402/1404

| Model No.  | Ball screw specifications  |      |                                |                       |                        |                   |                 | Nut            |                 |                |     |
|------------|----------------------------|------|--------------------------------|-----------------------|------------------------|-------------------|-----------------|----------------|-----------------|----------------|-----|
|            | Screw shaft outer diameter | Lead | Ball center-to-center diameter | Thread minor diameter | No. of loaded circuits | Basic load rating |                 | Outer diameter | Flange diameter | Overall length | Nut |
|            |                            |      |                                |                       |                        | Ca                | C <sub>0a</sub> |                |                 |                |     |
| d          | Ph                         | dp   | dc                             | Rows X turns          | kN                     | kN                | D               | D <sub>1</sub> | L <sub>1</sub>  | H              |     |
| MDK 1202-3 | 12                         | 2    | 12.3                           | 11                    | 3×1                    | 1.7               | 3.6             | 19             | 36              | 22             | 5   |
| MDK 1402-3 | 14                         | 2    | 14.3                           | 13                    | 3×1                    | 1.8               | 4.3             | 21             | 40              | 23             | 6   |
| MDK 1404-3 | 14                         | 4    | 14.65                          | 12.2                  | 3×1                    | 4.2               | 7.6             | 26             | 45              | 33             | 6   |
| MDK 1405-3 | 14                         | 5    | 14.75                          | 11.2                  | 3×1                    | 7                 | 11.6            | 26             | 45              | 42             | 10  |

Model number coding


## MDK1202-3 RR GT +165L C5 A

|           |  |                                    |                            |
|-----------|--|------------------------------------|----------------------------|
| Model No. | Seal symbol (*1)                                 | Overall screw shaft length (in mm) | Unfinished shaft ends code |
|           | Symbol for clearance in the axial direction (*2) | Accuracy symbol (*3)               |                            |

(\*1) See [A15-334](#). (\*2) See [A15-19](#). (\*3) See [A15-12](#).



## Positioning Ball Screw



MDK1405


Unit: mm

| Dimensions     |     |                |    |                           | Screw shaft dimensions |                |                |                |                |                |                |   |      | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|----------------|-----|----------------|----|---------------------------|------------------------|----------------|----------------|----------------|----------------|----------------|----------------|---|------|----------------|--------------------|---|
| B <sub>1</sub> | PCD | d <sub>1</sub> | Tw | Unfinished Shaft End Code | Overall length<br>L    | ℓ <sub>0</sub> | ℓ <sub>1</sub> | ℓ <sub>2</sub> | ℓ <sub>3</sub> | d <sub>3</sub> | d <sub>4</sub> | K |      |                |                    |   |
| 17             | 28  | 4.5            | 23 | A                         | 165                    | 86             | 15             | 60             | 90             | 14.2           | 11             | 4 | 0.05 | 0.71           | 3500               |   |
|                |     |                |    |                           | 215                    | 136            |                |                | 140            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 265                    | 186            |                |                | 190            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 315                    | 236            |                |                | 240            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 365                    | 286            |                |                | 290            |                |                |   |      |                |                    |   |
| 17             | 31  | 5.5            | 26 | A                         | 175                    | 86             | 25             | 60             | 90             | 15.2           | 13             | 4 | 0.07 | 1              | 3500               |   |
|                |     |                |    |                           | 225                    | 136            |                |                | 140            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 275                    | 186            |                |                | 190            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 325                    | 236            |                |                | 240            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 425                    | 336            |                |                | 340            |                |                |   |      |                |                    |   |
| 27             | 36  | 5.5            | 28 | A                         | 240                    | 150            | 25             | 60             | 155            | 15.2           | 11.9           | 5 | 0.14 | 0.8            | 3500               |   |
|                |     |                |    |                           | 290                    | 200            |                |                | 205            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 340                    | 250            |                |                | 255            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 440                    | 350            |                |                | 355            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 540                    | 450            |                |                | 455            |                |                |   |      |                |                    |   |
| 32             | 36  | 5.5            | 28 | A                         | 250                    | 160            | 25             | 60             | 165            | 14             | 11.2           | 5 | 0.19 | 1.2            | 4740               |   |
|                |     |                |    |                           | 300                    | 210            |                |                | 215            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 350                    | 260            |                |                | 265            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 450                    | 360            |                |                | 365            |                |                |   |      |                |                    |   |
|                |     |                |    |                           | 550                    | 460            |                |                | 465            |                |                |   |      |                |                    |   |

Ball Screw


# MDK No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.  | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |          | Rigidity<br>K<br>N/μm |                     |                                   |                                  |
|------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|----------|-----------------------|---------------------|-----------------------------------|----------------------------------|
|            |                                 |            |                                      |                             |  | Ca<br>kN          | Ca<br>kN |                       | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> |
|            |                                 |            |                                      |                             |  | Ca<br>kN          | Ca<br>kN | D                     | D <sub>1</sub>      | L <sub>1</sub>                    |                                  |
| MDK 0401-3 | 4                               | 1          | 4.15                                 | 3.4                         | 3×1                                    | 0.29              | 0.42     | 35                    | 9                   | 19                                | 13                               |
| MDK 0601-3 | 6                               | 1          | 6.2                                  | 5.3                         | 3×1                                    | 0.54              | 0.94     | 60                    | 11                  | 23                                | 14.5                             |
| MDK 0801-3 | 8                               | 1          | 8.2                                  | 7.3                         | 3×1                                    | 0.64              | 1.4      | 80                    | 13                  | 26                                | 15                               |
| MDK 0802-3 | 8                               | 2          | 8.3                                  | 7                           | 3×1                                    | 1.4               | 2.3      | 80                    | 15                  | 28                                | 22                               |
| MDK 1002-3 | 10                              | 2          | 10.3                                 | 9                           | 3×1                                    | 1.5               | 2.9      | 100                   | 17                  | 34                                | 22                               |
| MDK 1202-3 | 12                              | 2          | 12.3                                 | 11                          | 3×1                                    | 1.7               | 3.6      | 120                   | 19                  | 36                                | 22                               |
| MDK 1402-3 | 14                              | 2          | 14.3                                 | 13                          | 3×1                                    | 1.8               | 4.3      | 190                   | 21                  | 40                                | 23                               |
| MDK 1404-3 | 14                              | 4          | 14.65                                | 12.2                        | 3×1                                    | 4.2               | 7.6      | 190                   | 26                  | 45                                | 33                               |
| MDK 1405-3 | 14                              | 5          | 14.75                                | 11.2                        | 3×1                                    | 7                 | 11.6     | 140                   | 26                  | 45                                | 42                               |

## Positioning Ball Screw



Unit: mm


| Nut dimensions |                |     |                |    |                          |                        | Screw shaft<br>inertial<br>moment/mm<br>kg·m <sup>2</sup> /mm | Nut<br>mass<br>kg | Shaft<br>mass<br>kg/m | Permissible<br>rotational<br>speed<br>min <sup>-1</sup> |
|----------------|----------------|-----|----------------|----|--------------------------|------------------------|---|-------------------|-----------------------|---|
| H              | B <sub>1</sub> | PCD | d <sub>1</sub> | Tw | Lubrication<br>hole<br>A |                        |   |                   |                       |   |
| 3              | 10             | 14  | 2.9            | 13 | —                        | $1.97 \times 10^{-10}$ | 0.01  | 0.07              | 3500                  |   |
| 3.5            | 11             | 17  | 3.4            | 15 | —                        | $9.99 \times 10^{-10}$ | 0.017   | 0.14              | 3500                  |   |
| 4              | 11             | 20  | 3.4            | 17 | —                        | $3.16 \times 10^{-9}$  | 0.024   | 0.29              | 3500                  |   |
| 5              | 17             | 22  | 3.4            | 19 | —                        | $3.16 \times 10^{-9}$  | 0.034   | 0.27              | 3500                  |   |
| 5              | 17             | 26  | 4.5            | 21 | —                        | $7.71 \times 10^{-9}$  | 0.045   | 0.47              | 3500                  |   |
| 5              | 17             | 28  | 4.5            | 23 | —                        | $1.60 \times 10^{-8}$  | 0.05  | 0.71              | 3500                  |   |
| 6              | 17             | 31  | 5.5            | 26 | —                        | $2.96 \times 10^{-8}$  | 0.15  | 1                 | 3500                  |   |
| 6              | 27             | 36  | 5.5            | 28 | —                        | $2.96 \times 10^{-8}$  | 0.13  | 0.8               | 3500                  |   |
| 10             | 32             | 36  | 5.5            | 28 | M6                       | $2.96 \times 10^{-8}$  | 0.18  | 0.91              | 4740                  |   |

Note) Models MDK0401, 0601 and 0801 are not provided with a seal.

# MBF (Unfinished Shaft Ends) No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|

2- $\phi$  d<sub>1</sub> through hole,  $\phi$  d<sub>2</sub> counter bore depth h



| Model No.    | Ball screw specifications       |            |                                      |                             |  |                   |                       | Nut                 |                                   |                                  |          |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|---------------------|-----------------------------------|----------------------------------|----------|
|              | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Outer diameter<br>D | Flange diameter<br>D <sub>f</sub> | Overall length<br>L <sub>1</sub> | Nut<br>H |
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                     |                                   |                                  |          |
| MBF 0401-3.7 | 4                               | 1          | 4.15                                 | 3.3                         | 1×3.7                                  | 0.59              | 0.93                  | 11                  | 24                                | 18                               | 4        |
| MBF 0601-3.7 | 6                               | 1          | 6.15                                 | 5.3                         | 1×3.7                                  | 0.74              | 1.5                   | 13                  | 30                                | 21                               | 5        |
| MBF 0802-3.7 | 8                               | 2          | 8.3                                  | 6.6                         | 1×3.7                                  | 2.5               | 4.2                   | 20                  | 40                                | 28                               | 6        |
| MBF 1002-3.7 | 10                              | 2          | 10.3                                 | 8.6                         | 1×3.7                                  | 2.8               | 5.3                   | 23                  | 43                                | 28                               | 6        |
| MBF 1202-3.7 | 12                              | 2          | 12.3                                 | 10.6                        | 1×3.7                                  | 3                 | 6.5                   | 25                  | 47                                | 30                               | 8        |
| MBF 1402-3.7 | 14                              | 2          | 14.3                                 | 12.6                        | 1×3.7                                  | 3.3               | 7.5                   | 26                  | 48                                | 30                               | 8        |
| MBF 1404-3.7 | 14                              | 4          | 14.3                                 | 11.8                        | 1×3.7                                  | 5.7               | 11.1                  | 30                  | 54                                | 38                               | 8        |

## Model number coding

**MBF0802-3.7 RR GT +218L C5 A**

Model No.

Seal symbol (\*1)

Overall screw shaft length (in mm)


Unfinished shaft ends code

Symbol for clearance in the axial direction (\*2)

Accuracy symbol (\*3)

(\*1) See **A15-334**. (\*2) See **A15-19**. (\*3) See **A15-12**.

## Positioning Ball Screw



Unit: mm


| Dimensions     |      |                |                |     |    |                           | Screw shaft dimensions |                |                |                |                |                |                | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |      |
|----------------|------|----------------|----------------|-----|----|---------------------------|------------------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|--------------------|---|------|
| B <sub>1</sub> | PCD  | d <sub>1</sub> | d <sub>2</sub> | h   | Tw | Unfinished Shaft End Code | Overall length<br>L    | l <sub>0</sub> | l <sub>1</sub> | l <sub>2</sub> | l <sub>3</sub> | d <sub>3</sub> | d <sub>4</sub> |                |                    |   | K    |
| 14             | 17   | 3.4            | 6.5            | 2.5 | 13 | A                         | 90                     | 48             | 10             | 30             | 50             | 4.3            | 3.2            | 2              | 0.02               | 0.07  | 3500 |
|                |      |                |                |     |    |                           | 110                    | 68             |                |                | 70             |                |                |                |                    |   |      |
|                |      |                |                |     |    |                           | 130                    | 88             |                |                | 90             |                |                |                |                    |   |      |
| 16             | 21.5 | 3.4            | 6.5            | 3   | 17 | A                         | 131                    | 58             | 20             | 50             | 61             | 6.3            | 5.2            | 3              | 0.04               | 0.14  | 3500 |
|                |      |                |                |     |    |                           | 161                    | 88             |                |                | 91             |                |                |                |                    |   |      |
|                |      |                |                |     |    |                           | 201                    | 128            |                |                | 131            |                |                |                |                    |   |      |
| 22             | 30   | 4.5            | 8              | 4   | 24 | A                         | 168                    | 85             | 25             | 55             | 88             | 8.3            | 6.2            | 3              | 0.1                | 0.19  | 3500 |
|                |      |                |                |     |    |                           | 193                    | 110            |                |                | 113            |                |                |                |                    |   |      |
|                |      |                |                |     |    |                           | 218                    | 135            |                |                | 138            |                |                |                |                    |   |      |
| 22             | 33   | 4.5            | 8              | 4   | 27 | A                         | 183                    | 95             | 25             | 60             | 98             | 10.3           | 8.2            | 3              | 0.11               | 0.36  | 3500 |
|                |      |                |                |     |    |                           | 223                    | 135            |                |                | 138            |                |                |                |                    |   |      |
|                |      |                |                |     |    |                           | 273                    | 185            |                |                | 188            |                |                |                |                    |   |      |
| 22             | 36   | 5.5            | 9.5            | 5.5 | 29 | A                         | 210                    | 117            | 30             | 60             | 120            | 12.3           | 10.2           | 3              | 0.15               | 0.58  | 3500 |
|                |      |                |                |     |    |                           | 235                    | 142            |                |                | 145            |                |                |                |                    |   |      |
|                |      |                |                |     |    |                           | 285                    | 192            |                |                | 195            |                |                |                |                    |   |      |
| 22             | 37   | 5.5            | 9.5            | 5.5 | 32 | A                         | 205                    | 102            | 40             | 60             | 105            | 14.3           | 12.2           | 3              | 0.16               | 0.85  | 3500 |
|                |      |                |                |     |    |                           | 245                    | 142            |                |                | 145            |                |                |                |                    |   |      |
|                |      |                |                |     |    |                           | 295                    | 192            |                |                | 195            |                |                |                |                    |   |      |
|                |      |                |                |     |    |                           | 345                    | 242            |                |                | 245            |                |                |                |                    |   |      |
| 30             | 42   | 5.5            | 9.5            | 5.5 | 34 | A                         | 233                    | 129            | 40             | 60             | 133            | 14.3           | 11.2           | 4              | 0.25               | 1.2   | 3500 |
|                |      |                |                |     |    |                           | 293                    | 189            |                |                | 193            |                |                |                |                    |   |      |
|                |      |                |                |     |    |                           | 353                    | 249            |                |                | 253            |                |                |                |                    |   |      |
|                |      |                |                |     |    |                           | 413                    | 309            |                |                | 313            |                |                |                |                    |   |      |

Note) The standard specification for the Model MBF is with no seal. Please contact THK if you are interested in attaching a seal.

# MBF No Preload


|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|

2- $\phi$  d<sub>1</sub> through hole,  
 $\phi$  d<sub>2</sub> counter bore depth h



Nut type I

2- $\phi$  d<sub>1</sub> through hole




Nut type II

| Model No.     | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                 | Rigidity<br>K<br>N/μm |
|---------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------|-----------------------|
|               |                                 |            |                                      |                             |  | Ca                | C <sub>0a</sub> |                       |
|               |                                 |            |                                      |                             |  | kN                | kN              |                       |
| MBF0401-3.7   | 4                               | 1          | 4.15                                 | 3.3                         | 1×3.7                                  | 0.59              | 0.93            | 54                    |
| MBF0601-3.7   | 6                               | 1          | 6.15                                 | 5.3                         | 1×3.7                                  | 0.74              | 1.5             | 75                    |
| MBF0602-2.7   | 6                               | 2          | 6.2                                  | 5.1                         | 1×2.7                                  | 0.75              | 1.2             | 58                    |
| MBF0602.5-2.7 | 6                               | 2.5        | 6.2                                  | 5.1                         | 1×2.7                                  | 0.75              | 1.2             | 59                    |
| MBF0801.5-3.7 | 8                               | 1.5        | 8.2                                  | 7.1                         | 1×3.7                                  | 1.1               | 2.2             | 99                    |
| MBF0802-3.7   | 8                               | 2          | 8.3                                  | 6.6                         | 1×3.7                                  | 2.5               | 4.2             | 111                   |
| MBF0802.5-3.7 | 8                               | 2.5        | 8.3                                  | 6.6                         | 1×3.7                                  | 2.4               | 4.1             | 111                   |
| MBF0803-2.7   | 8                               | 3          | 8.3                                  | 6.2                         | 1×2.7                                  | 2.6               | 4.2             | 85                    |
| MBF0804-2.7   | 8                               | 4          | 8.3                                  | 6.2                         | 1×2.7                                  | 2.6               | 4.2             | 84                    |
| MBF1001-3.7   | 10                              | 1          | 10.15                                | 9.3                         | 1×3.7                                  | 0.84              | 2               | 113                   |
| MBF1001.5-3.7 | 10                              | 1.5        | 10.2                                 | 9.1                         | 1×3.7                                  | 1.25              | 2.8             | 120                   |
| MBF1002-3.7   | 10                              | 2          | 10.3                                 | 8.6                         | 1×3.7                                  | 2.8               | 5.3             | 134                   |
| MBF1002.5-3.7 | 10                              | 2.5        | 10.3                                 | 8.6                         | 1×3.7                                  | 2.7               | 5.3             | 133                   |
| MBF1003-3.7   | 10                              | 3          | 10.3                                 | 8.2                         | 1×3.7                                  | 3.9               | 7.2             | 140                   |
| MBF1005-2.7   | 10                              | 5          | 10.3                                 | 8.2                         | 1×2.7                                  | 3                 | 5.2             | 103                   |
| MBF1202-3.7   | 12                              | 2          | 12.3                                 | 10.6                        | 1×3.7                                  | 3                 | 6.5             | 156                   |
| MBF1202.5-3.7 | 12                              | 2.5        | 12.3                                 | 10.6                        | 1×3.7                                  | 3                 | 6.4             | 156                   |
| MBF1203-3.7   | 12                              | 3          | 12.3                                 | 10.2                        | 1×3.7                                  | 4.3               | 8.7             | 162                   |
| MBF1204-3.7   | 12                              | 4          | 12.3                                 | 9.8                         | 1×3.7                                  | 5.4               | 10.2            | 165                   |
| MBF1402-3.7   | 14                              | 2          | 14.3                                 | 12.6                        | 1×3.7                                  | 3.3               | 7.5             | 176                   |
| MBF1404-3.7   | 14                              | 4          | 14.3                                 | 11.8                        | 1×3.7                                  | 5.7               | 11.1            | 187                   |

Note) The standard specification for the Model MBF is with no seal. Please contact THK if you are interested in attaching a seal.

The Model MBF can support an axial clearance of 0 or less. Please contact THK if you would like to use it in this manner.

## Positioning Ball Screw




Unit: mm

|  | Nut dimensions      |                                   |                                  |   |                |      |                |                |     |          |    | Screw shaft inertial moment/mm<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|---------------------|-----------------------------------|----------------------------------|---|----------------|------|----------------|----------------|-----|----------|----|---|----------------|--------------------|---|
|  | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H | B <sub>1</sub> | PCD  | d <sub>1</sub> | d <sub>2</sub> | h   | Nut type | Tw |   |                |                    |   |
|  | 11                  | 24                                | 18                               | 4 | 14             | 17   | 3.4            | 6.5            | 2.5 | I        | 13 | 1.97 × 10 <sup>-10</sup>                                | 0.02           | 0.07               | 3500  |
|  | 13                  | 30                                | 21                               | 5 | 16             | 21.5 | 3.4            | 6.5            | 3   | I        | 17 | 9.99 × 10 <sup>-10</sup>                                | 0.04           | 0.14               | 3500  |
|  | 15                  | 29                                | 17                               | 4 | 13             | 23   | 3.4            | —              | —   | II       | 17 | 9.99 × 10 <sup>-10</sup>                                | 0.03           | 0.21               | 3500  |
|  | 15                  | 29                                | 18                               | 4 | 14             | 23   | 3.4            | —              | —   | II       | 17 | 9.99 × 10 <sup>-10</sup>                                | 0.03           | 0.21               | 3500  |
|  | 16                  | 30                                | 19                               | 4 | 15             | 24   | 3.4            | —              | —   | II       | 18 | 3.16 × 10 <sup>-9</sup>                                 | 0.03           | 0.36               | 3500  |
|  | 20                  | 40                                | 28                               | 6 | 22             | 30   | 4.5            | 8              | 4   | I        | 24 | 3.16 × 10 <sup>-9</sup>                                 | 0.1            | 0.19               | 3500  |
|  | 20                  | 38                                | 26                               | 5 | 21             | 30   | 4.5            | —              | —   | II       | 22 | 3.16 × 10 <sup>-9</sup>                                 | 0.07           | 0.34               | 3500  |
|  | 20                  | 38                                | 25                               | 5 | 20             | 30   | 4.5            | —              | —   | II       | 22 | 3.16 × 10 <sup>-9</sup>                                 | 0.06           | 0.32               | 3500  |
|  | 21                  | 39                                | 28                               | 5 | 23             | 31   | 4.5            | —              | —   | II       | 23 | 3.16 × 10 <sup>-9</sup>                                 | 0.08           | 0.34               | 3500  |
|  | 19                  | 37                                | 18                               | 5 | 13             | 29   | 4.5            | —              | —   | II       | 21 | 7.71 × 10 <sup>-9</sup>                                 | 0.04           | 0.57               | 3500  |
|  | 19                  | 37                                | 20                               | 5 | 15             | 29   | 4.5            | —              | —   | II       | 21 | 7.71 × 10 <sup>-9</sup>                                 | 0.04           | 0.57               | 3500  |
|  | 23                  | 43                                | 28                               | 6 | 22             | 33   | 4.5            | 8              | 4   | I        | 27 | 7.71 × 10 <sup>-9</sup>                                 | 0.11           | 0.36               | 3500  |
|  | 24                  | 44                                | 27                               | 6 | 21             | 35   | 5.5            | —              | —   | II       | 26 | 7.71 × 10 <sup>-9</sup>                                 | 0.09           | 0.55               | 3500  |
|  | 24                  | 44                                | 30                               | 6 | 24             | 35   | 5.5            | —              | —   | II       | 26 | 7.71 × 10 <sup>-9</sup>                                 | 0.1            | 0.52               | 3500  |
|  | 24                  | 44                                | 34                               | 6 | 28             | 35   | 5.5            | —              | —   | II       | 26 | 7.71 × 10 <sup>-9</sup>                                 | 0.12           | 0.56               | 3500  |
|  | 25                  | 47                                | 30                               | 8 | 22             | 36   | 5.5            | 9.5            | 5.5 | I        | 29 | 1.60 × 10 <sup>-8</sup>                                 | 0.15           | 0.58               | 3500  |
|  | 26                  | 46                                | 27                               | 6 | 21             | 37   | 5.5            | —              | —   | II       | 28 | 1.60 × 10 <sup>-8</sup>                                 | 0.11           | 0.8                | 3500  |
|  | 28                  | 48                                | 30                               | 6 | 24             | 39   | 5.5            | —              | —   | II       | 30 | 1.60 × 10 <sup>-8</sup>                                 | 0.14           | 0.77               | 3500  |
|  | 28                  | 48                                | 33                               | 6 | 27             | 39   | 5.5            | —              | —   | II       | 30 | 1.60 × 10 <sup>-8</sup>                                 | 0.15           | 0.76               | 3500  |
|  | 26                  | 48                                | 30                               | 8 | 22             | 37   | 5.5            | 9.5            | 5.5 | I        | 32 | 2.96 × 10 <sup>-8</sup>                                 | 0.16           | 0.85               | 3500  |
|  | 30                  | 54                                | 38                               | 8 | 30             | 42   | 5.5            | 9.5            | 5.5 | I        | 34 | 2.96 × 10 <sup>-8</sup>                                 | 0.25           | 1.2                | 3500  |


# BNF-V Small No Preload

|          |        |
|----------|--------|
| DN value | 100000 |
|----------|--------|



| Model No.     | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|---------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|               |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| BNF 1604V-5   | 16                              | 4          | 16.5                                 | 13.8                        | 2×2.5                                  | 7.8               | 17.4                  | 290                   |
| BNF 1605V-2.5 | 16                              | 5          | 16.75                                | 13.2                        | 1×2.5                                  | 7.4               | 13.9                  | 170                   |
| BNF 1605V-5   | 16                              | 5          | 16.75                                | 13.2                        | 2×2.5                                  | 13.5              | 27.9                  | 320                   |
| BNF 2004V-2.5 | 20                              | 4          | 20.5                                 | 17.8                        | 1×2.5                                  | 4.8               | 10.9                  | 180                   |
| BNF 2004V-5   | 20                              | 4          | 20.5                                 | 17.8                        | 2×2.5                                  | 8.6               | 21.8                  | 350                   |
| BNF 2005V-2.5 | 20                              | 5          | 20.75                                | 17.2                        | 1×2.5                                  | 8.3               | 17.5                  | 200                   |
| BNF 2005V-5   | 20                              | 5          | 20.75                                | 17.2                        | 2×2.5                                  | 15.1              | 35                    | 380                   |
| BNF 2010V-2.5 | 20                              | 10         | 20.75                                | 17.2                        | 1×2.5                                  | 8.3               | 17.6                  | 197                   |
| BNF 2504V-2.5 | 25                              | 4          | 25.5                                 | 22.8                        | 1×2.5                                  | 5.2               | 13.7                  | 210                   |
| BNF 2504V-5   | 25                              | 4          | 25.5                                 | 22.8                        | 2×2.5                                  | 9.5               | 27.4                  | 410                   |
| BNF 2505V-2.5 | 25                              | 5          | 25.75                                | 22.2                        | 1×2.5                                  | 9.2               | 21.9                  | 240                   |
| BNF 2505V-5   | 25                              | 5          | 25.75                                | 22.2                        | 2×2.5                                  | 16.7              | 43.9                  | 460                   |
| BNF 2506V-2.5 | 25                              | 6          | 26                                   | 21.4                        | 1×2.5                                  | 12.4              | 27.4                  | 250                   |
| BNF 2506V-5   | 25                              | 6          | 26                                   | 21.4                        | 2×2.5                                  | 22.6              | 54.8                  | 470                   |
| BNF 2805V-2.5 | 28                              | 5          | 28.75                                | 25.2                        | 1×2.5                                  | 9.7               | 24.6                  | 250                   |
| BNF 2805V-5   | 28                              | 5          | 28.75                                | 25.2                        | 2×2.5                                  | 17.5              | 49.2                  | 500                   |
| BNF 2805V-7.5 | 28                              | 5          | 28.75                                | 25.2                        | 3×2.5                                  | 24.8              | 73.8                  | 740                   |
| BNF 2806V-2.5 | 28                              | 6          | 28.75                                | 25.2                        | 1×2.5                                  | 9.6               | 24.6                  | 250                   |
| BNF 2806V-5   | 28                              | 6          | 28.75                                | 25.2                        | 2×2.5                                  | 17.5              | 49.2                  | 500                   |
| BNF 2806V-7.5 | 28                              | 6          | 28.75                                | 25.2                        | 3×2.5                                  | 24.8              | 73.8                  | 740                   |
| BNF 3205V-2.5 | 32                              | 5          | 32.75                                | 29.2                        | 1×2.5                                  | 10.2              | 28.1                  | 280                   |
| BNF 3205V-5   | 32                              | 5          | 32.75                                | 29.2                        | 2×2.5                                  | 18.5              | 56.3                  | 560                   |
| BNF 3205V-7.5 | 32                              | 5          | 32.75                                | 29.2                        | 3×2.5                                  | 26.2              | 84.4                  | 810                   |
| BNF 3206V-2.5 | 32                              | 6          | 33                                   | 28.4                        | 1×2.5                                  | 13.9              | 35.2                  | 290                   |
| BNF 3206V-5   | 32                              | 6          | 33                                   | 28.4                        | 2×2.5                                  | 25.2              | 70.3                  | 580                   |






Unit: mm

|  | Nut dimensions |                 |                |    |                |     |                                   |                  | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass | Shaft mass | Permissible rotational speed |
|--|----------------|-----------------|----------------|----|----------------|-----|-----------------------------------|------------------|---|----------|------------|------------------------------|
|  | Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | Lubrication hole |   |          |            |                              |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | A                | kg·m <sup>2</sup> /mm                       | kg       | kg/m       | min <sup>-1</sup>            |
|  | 36             | 59              | 53             | 11 | 42             | 47  | 5.5×9.5×5.5                       | M6               | 5.05×10 <sup>-8</sup>                       | 0.42     | 1.42       | 5000                         |
|  | 40             | 60              | 41             | 10 | 31             | 50  | 4.5×8×4.5                         | M6               | 5.05×10 <sup>-8</sup>                       | 0.37     | 1.37       | 5000                         |
|  | 40             | 60              | 56             | 10 | 46             | 50  | 4.5×8×4.5                         | M6               | 5.05×10 <sup>-8</sup>                       | 0.49     | 1.37       | 5000                         |
|  | 40             | 63              | 37             | 11 | 26             | 51  | 5.5×9.5×5.5                       | M6               | 1.23×10 <sup>-7</sup>                       | 0.3      | 2.22       | 4870                         |
|  | 40             | 63              | 49             | 11 | 38             | 51  | 5.5×9.5×5.5                       | M6               | 1.23×10 <sup>-7</sup>                       | 0.49     | 2.22       | 4870                         |
|  | 44             | 67              | 41             | 11 | 30             | 55  | 5.5×9.5×5.5                       | M6               | 1.23×10 <sup>-7</sup>                       | 0.46     | 2.19       | 4810                         |
|  | 44             | 67              | 56             | 11 | 45             | 55  | 5.5×9.5×5.5                       | M6               | 1.23×10 <sup>-7</sup>                       | 0.6      | 2.19       | 4810                         |
|  | 46             | 74              | 58             | 15 | 43             | 59  | 5.5×9.5×5.5                       | M6               | 1.23×10 <sup>-7</sup>                       | 0.68     | 2.46       | 4810                         |
|  | 46             | 69              | 36             | 11 | 25             | 57  | 5.5×9.5×5.5                       | M6               | 3.01×10 <sup>-7</sup>                       | 0.21     | 3.6        | 3920                         |
|  | 46             | 69              | 48             | 11 | 37             | 57  | 5.5×9.5×5.5                       | M6               | 3.01×10 <sup>-7</sup>                       | 0.55     | 3.6        | 3920                         |
|  | 50             | 73              | 40             | 11 | 29             | 61  | 5.5×9.5×5.5                       | M6               | 3.01×10 <sup>-7</sup>                       | 0.52     | 3.52       | 3880                         |
|  | 50             | 73              | 55             | 11 | 44             | 61  | 5.5×9.5×5.5                       | M6               | 3.01×10 <sup>-7</sup>                       | 0.68     | 3.52       | 3880                         |
|  | 53             | 76              | 44             | 11 | 33             | 64  | 5.5×9.5×5.5                       | M6               | 3.01×10 <sup>-7</sup>                       | 0.61     | 3.43       | 3840                         |
|  | 53             | 76              | 62             | 11 | 51             | 64  | 5.5×9.5×5.5                       | M6               | 3.01×10 <sup>-7</sup>                       | 0.91     | 3.43       | 3840                         |
|  | 55             | 85              | 44             | 12 | 32             | 69  | 6.6×11×6.5                        | M6               | 4.74×10 <sup>-7</sup>                       | 1.02     | 4.45       | 3470                         |
|  | 55             | 85              | 59             | 12 | 47             | 69  | 6.6×11×6.5                        | M6               | 4.74×10 <sup>-7</sup>                       | 1.06     | 4.45       | 3470                         |
|  | 55             | 85              | 74             | 12 | 62             | 69  | 6.6×11×6.5                        | M6               | 4.74×10 <sup>-7</sup>                       | 1.16     | 4.45       | 3470                         |
|  | 55             | 85              | 50             | 12 | 38             | 69  | 6.6×11×6.5                        | M6               | 4.74×10 <sup>-7</sup>                       | 0.87     | 4.52       | 3470                         |
|  | 55             | 85              | 68             | 12 | 56             | 69  | 6.6×11×6.5                        | M6               | 4.74×10 <sup>-7</sup>                       | 1.09     | 4.52       | 3470                         |
|  | 55             | 85              | 86             | 12 | 74             | 69  | 6.6×11×6.5                        | M6               | 4.74×10 <sup>-7</sup>                       | 1.3      | 4.52       | 3470                         |
|  | 58             | 85              | 41             | 12 | 29             | 71  | 6.6×11×6.5                        | M6               | 8.08×10 <sup>-7</sup>                       | 0.76     | 5.89       | 3050                         |
|  | 58             | 85              | 56             | 12 | 44             | 71  | 6.6×11×6.5                        | M6               | 8.08×10 <sup>-7</sup>                       | 0.94     | 5.89       | 3050                         |
|  | 58             | 85              | 71             | 12 | 59             | 71  | 6.6×11×6.5                        | M6               | 8.08×10 <sup>-7</sup>                       | 1.13     | 5.89       | 3050                         |
|  | 62             | 89              | 45             | 12 | 33             | 75  | 6.6×11×6.5                        | M6               | 8.08×10 <sup>-7</sup>                       | 0.94     | 5.88       | 3030                         |
|  | 62             | 89              | 63             | 12 | 51             | 75  | 6.6×11×6.5                        | M6               | 8.08×10 <sup>-7</sup>                       | 1.21     | 5.88       | 3030                         |

Note)The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.


# BNF-V Medium No Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



| Model No.     | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                      | Rigidity<br>K<br>N/μm |
|---------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|----------------------|-----------------------|
|               |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>a</sub><br>kN |                       |
| BNF 2508V-2.5 | 25                              | 8          | 26.25                                | 20.5                        | 1×2.5                                  | 15.8              | 32.9                 | 250                   |
| BNF 2508V-3.5 | 25                              | 8          | 26.25                                | 20.5                        | 1×3.5                                  | 21.1              | 46                   | 340                   |
| BNF 2508V-5   | 25                              | 8          | 26.25                                | 20.5                        | 2×2.5                                  | 28.7              | 65.7                 | 480                   |
| BNF 2510V-2.5 | 25                              | 10         | 26.25                                | 21.5                        | 1×2.5                                  | 15.8              | 32.9                 | 250                   |
| BNF 2810V-2.5 | 28                              | 10         | 29.75                                | 22.4                        | 1×2.5                                  | 24.3              | 49                   | 280                   |
| BNF 3210V-2.5 | 32                              | 10         | 33.75                                | 26.4                        | 1×2.5                                  | 26                | 56.2                 | 310                   |
| BNF 3210V-3.5 | 32                              | 10         | 33.75                                | 26.4                        | 1×3.5                                  | 34.8              | 78.6                 | 440                   |
| BNF 3210V-5   | 32                              | 10         | 33.75                                | 26.4                        | 2×2.5                                  | 47.3              | 112.3                | 620                   |
| BNF 3212V-3.5 | 32                              | 12         | 34                                   | 26.1                        | 1×3.5                                  | 40.4              | 88.5                 | 440                   |
| BNF 3216V-5   | 32                              | 16         | 33.75                                | 26.4                        | 2×2.5                                  | 47.1              | 113.1                | 616                   |
| BNF 3610V-2.5 | 36                              | 10         | 37.75                                | 30.5                        | 1×2.5                                  | 27.6              | 63.3                 | 350                   |
| BNF 3610V-5   | 36                              | 10         | 37.75                                | 30.5                        | 2×2.5                                  | 50.1              | 126.5                | 680                   |
| BNF 3610V-7.5 | 36                              | 10         | 37.75                                | 30.5                        | 3×2.5                                  | 71                | 189.8                | 990                   |
| BNF 3612V-2.5 | 36                              | 12         | 38                                   | 30.1                        | 1×2.5                                  | 32.2              | 71.2                 | 350                   |
| BNF 3612V-5   | 36                              | 12         | 38                                   | 30.1                        | 2×2.5                                  | 58.4              | 142.3                | 690                   |
| BNF 3616V-2.5 | 36                              | 16         | 38                                   | 30.1                        | 1×2.5                                  | 32.1              | 71.5                 | 350                   |
| BNF 3620V-1.5 | 36                              | 20         | 37.75                                | 30.5                        | 1×1.5                                  | 17.7              | 38.4                 | 215                   |
| BNF 4010V-2.5 | 40                              | 10         | 41.75                                | 34.4                        | 1×2.5                                  | 29                | 70.4                 | 380                   |
| BNF 4010V-3.5 | 40                              | 10         | 41.75                                | 34.4                        | 1×3.5                                  | 38.8              | 98.5                 | 520                   |
| BNF 4010V-5   | 40                              | 10         | 41.75                                | 34.4                        | 2×2.5                                  | 52.7              | 140.7                | 740                   |
| BNF 4012V-2.5 | 40                              | 12         | 42                                   | 34.1                        | 1×2.5                                  | 33.9              | 79.2                 | 390                   |
| BNF 4012V-3.5 | 40                              | 12         | 42                                   | 34.1                        | 1×3.5                                  | 45.3              | 110.8                | 530                   |
| BNF 4012V-5   | 40                              | 12         | 42                                   | 34.1                        | 2×2.5                                  | 61.6              | 158.3                | 750                   |
| BNF 4016V-5   | 40                              | 16         | 42                                   | 34.1                        | 2×2.5                                  | 61.5              | 158.8                | 740                   |
| BNF 4020V-5   | 40                              | 20         | 41.75                                | 34.4                        | 2×2.5                                  | 52.4              | 142                  | 736                   |

## Positioning Ball Screw




Unit: mm

|  | Nut dimensions |                 |                |    |                |     |                                   |                  | Screw shaft inertial moment/mm | Nut mass | Shaft mass | Permissible rotational speed |
|--|----------------|-----------------|----------------|----|----------------|-----|-----------------------------------|------------------|--------------------------------|----------|------------|------------------------------|
|  | Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | Lubrication hole |                                |          |            |                              |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | A                | kg·m <sup>2</sup> /mm          | kg       | kg/m       | min <sup>-1</sup>            |
|  | 58             | 85              | 58             | 15 | 43             | 71  | 6.6×11×6.5                        | M6               | 3.01×10 <sup>-7</sup>          | 1.07     | 3.51       | 4950                         |
|  | 58             | 85              | 66             | 15 | 51             | 71  | 6.6×11×6.5                        | M6               | 3.01×10 <sup>-7</sup>          | 1.29     | 3.51       | 4950                         |
|  | 58             | 85              | 82             | 15 | 67             | 71  | 6.6×11×6.5                        | M6               | 3.01×10 <sup>-7</sup>          | 1.44     | 3.51       | 4950                         |
|  | 58             | 85              | 70             | 18 | 52             | 71  | 6.6×11×6.5                        | M6               | 3.01×10 <sup>-7</sup>          | 1.43     | 3.5        | 4950                         |
|  | 65             | 106             | 86             | 18 | 68             | 85  | 11×17.5×11                        | M6               | 4.74×10 <sup>-8</sup>          | 2.3      | 4.15       | 4360                         |
|  | 74             | 108             | 70             | 15 | 55             | 90  | 9×14×8.5                          | M6               | 8.08×10 <sup>-7</sup>          | 2.2      | 5.53       | 3850                         |
|  | 74             | 108             | 80             | 15 | 65             | 90  | 9×14×8.5                          | M6               | 8.08×10 <sup>-7</sup>          | 2.44     | 5.53       | 3850                         |
|  | 74             | 108             | 100            | 15 | 85             | 90  | 9×14×8.5                          | M6               | 8.08×10 <sup>-7</sup>          | 2.92     | 5.53       | 3850                         |
|  | 76             | 121             | 98             | 18 | 80             | 98  | 11×17.5×11                        | M6               | 8.08×10 <sup>-7</sup>          | 3.4      | 5.7        | 3820                         |
|  | 74             | 108             | 139            | 18 | 121            | 90  | 9×14×8.5                          | M6               | 8.08×10 <sup>-7</sup>          | 3.81     | 5.82       | 3850                         |
|  | 75             | 120             | 81             | 18 | 63             | 98  | 11×17.5×11                        | M6               | 1.29×10 <sup>-6</sup>          | 2.75     | 7.1        | 3440                         |
|  | 75             | 120             | 111            | 18 | 93             | 98  | 11×17.5×11                        | M6               | 1.29×10 <sup>-6</sup>          | 3.45     | 7.1        | 3440                         |
|  | 75             | 120             | 141            | 18 | 123            | 98  | 11×17.5×11                        | M6               | 1.29×10 <sup>-6</sup>          | 4.15     | 7.1        | 3440                         |
|  | 78             | 123             | 87             | 18 | 69             | 100 | 11×17.5×11                        | M6               | 1.29×10 <sup>-6</sup>          | 3.14     | 7.99       | 3420                         |
|  | 78             | 123             | 123            | 18 | 105            | 100 | 11×17.5×11                        | M6               | 1.29×10 <sup>-6</sup>          | 4.07     | 7.99       | 3420                         |
|  | 78             | 123             | 92             | 18 | 74             | 100 | 11×17.5×11                        | M6               | 1.29×10 <sup>-6</sup>          | 3.27     | 7.99       | 3420                         |
|  | 75             | 114             | 82             | 18 | 64             | 93  | 11×17.5×11                        | M6               | 1.29×10 <sup>-6</sup>          | 2.38     | 7.54       | 3440                         |
|  | 82             | 124             | 73             | 18 | 55             | 102 | 11×17.5×11                        | M6               | 1.97×10 <sup>-6</sup>          | 2.86     | 8.87       | 3110                         |
|  | 82             | 124             | 83             | 18 | 65             | 102 | 11×17.5×11                        | M6               | 1.97×10 <sup>-6</sup>          | 3.14     | 8.87       | 3110                         |
|  | 82             | 124             | 103            | 18 | 85             | 102 | 11×17.5×11                        | M6               | 1.97×10 <sup>-6</sup>          | 3.69     | 8.87       | 3110                         |
|  | 84             | 126             | 83             | 18 | 65             | 104 | 11×17.5×11                        | M6               | 1.97×10 <sup>-6</sup>          | 3.31     | 8.83       | 3090                         |
|  | 84             | 126             | 95             | 18 | 77             | 104 | 11×17.5×11                        | M6               | 1.97×10 <sup>-6</sup>          | 3.66     | 8.83       | 3090                         |
|  | 84             | 126             | 119            | 18 | 101            | 104 | 11×17.5×11                        | M6               | 1.97×10 <sup>-6</sup>          | 4.36     | 8.83       | 3090                         |
|  | 84             | 126             | 144            | 18 | 126            | 104 | 11×17.5×11                        | M6               | 1.97×10 <sup>-6</sup>          | 5.52     | 9.09       | 3090                         |
|  | 82             | 126             | 162            | 18 | 144            | 104 | 11×17.5×11                        | M6               | 1.97×10 <sup>-6</sup>          | 5.17     | 9.37       | 3110                         |


Note)The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

# BNF-V Medium No Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



| Model No.     | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                      | Rigidity<br>K<br>N/μm |
|---------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|----------------------|-----------------------|
|               |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>a</sub><br>kN |                       |
| BNF 4510V-2.5 | 45                              | 10         | 46.75                                | 39.5                        | 1×2.5                                  | 30.6              | 79.3                 | 420                   |
| BNF 4510V-3   | 45                              | 10         | 46.75                                | 39.5                        | 2×1.5                                  | 35.8              | 95.1                 | 500                   |
| BNF 4510V-5   | 45                              | 10         | 46.75                                | 39.5                        | 2×2.5                                  | 55.6              | 158.5                | 800                   |
| BNF 4510V-7.5 | 45                              | 10         | 46.75                                | 39.5                        | 3×2.5                                  | 78.8              | 237.8                | 1190                  |
| BNF 4512V-5   | 45                              | 12         | 47                                   | 39.2                        | 2×2.5                                  | 65.2              | 178.3                | 820                   |
| BNF 4520V-2.5 | 45                              | 20         | 47                                   | 39.2                        | 1×2.5                                  | 35.8              | 89.7                 | 424                   |
| BNF 5010V-2.5 | 50                              | 10         | 51.75                                | 44.4                        | 1×2.5                                  | 32.1              | 88.1                 | 450                   |
| BNF 5010V-3.5 | 50                              | 10         | 51.75                                | 44.4                        | 1×3.5                                  | 42.9              | 123.4                | 620                   |
| BNF 5010V-5   | 50                              | 10         | 51.75                                | 44.4                        | 2×2.5                                  | 58.2              | 176.3                | 880                   |
| BNF 5010V-7.5 | 50                              | 10         | 51.75                                | 44.4                        | 3×2.5                                  | 82.5              | 264.4                | 1290                  |
| BNF 5012V-2.5 | 50                              | 12         | 52.25                                | 43.3                        | 1×2.5                                  | 43.4              | 110.1                | 470                   |
| BNF 5012V-3.5 | 50                              | 12         | 52.25                                | 43.3                        | 1×3.5                                  | 58                | 154.1                | 640                   |
| BNF 5012V-5   | 50                              | 12         | 52.25                                | 43.3                        | 2×2.5                                  | 78.8              | 220.2                | 910                   |
| BNF 5016V-2.5 | 50                              | 16         | 52.7                                 | 42.9                        | 1×2.5                                  | 72.6              | 183.1                | 620                   |
| BNF 5016V-5   | 50                              | 16         | 52.7                                 | 42.9                        | 2×2.5                                  | 131.8             | 366.2                | 1180                  |
| BNF 5020V-2.5 | 50                              | 20         | 52.7                                 | 42.9                        | 1×2.5                                  | 72.5              | 183.6                | 620                   |




Unit: mm

|  | Nut dimensions |                 |                |    |                |     |                                     | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass                | Shaft mass | Permissible rotational speed |                   |
|--|----------------|-----------------|----------------|----|----------------|-----|-------------------------------------|---|-------------------------|------------|------------------------------|-------------------|
|  | Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h |   |                         |            |                              | Lubrication hole  |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h | A   | kg·m <sup>2</sup> /mm   | kg         | kg/m                         | min <sup>-1</sup> |
|  | 88             | 132             | 81             | 18 | 63             | 110 | 11 × 17.5 × 11                      | Rc1/8<br>(PT1/8)                            | 3.16 × 10 <sup>-6</sup> | 3.43       | 11.36                        | 2780              |
|  | 88             | 132             | 94             | 18 | 76             | 110 | 11 × 17.5 × 11                      |   | 3.16 × 10 <sup>-6</sup> | 3.83       | 11.36                        | 2780              |
|  | 88             | 132             | 111            | 18 | 93             | 110 | 11 × 17.5 × 11                      |   | 3.16 × 10 <sup>-6</sup> | 4.35       | 11.36                        | 2780              |
|  | 88             | 132             | 141            | 18 | 123            | 110 | 11 × 17.5 × 11                      |   | 3.16 × 10 <sup>-6</sup> | 5.26       | 11.36                        | 2780              |
|  | 90             | 130             | 119            | 18 | 101            | 110 | 11 × 17.5 × 11                      |   | 3.16 × 10 <sup>-6</sup> | 4.74       | 11.32                        | 2760              |
|  | 90             | 130             | 102            | 18 | 84             | 110 | 11 × 17.5 × 11                      |   | 3.16 × 10 <sup>-6</sup> | 4.28       | 11.1                         | 2760              |
|  | 93             | 135             | 73             | 18 | 55             | 113 | 11 × 17.5 × 11                      |   | 4.82 × 10 <sup>-6</sup> | 3.33       | 14.16                        | 2510              |
|  | 93             | 135             | 83             | 18 | 65             | 113 | 11 × 17.5 × 11                      |   | 4.82 × 10 <sup>-6</sup> | 3.66       | 14.16                        | 2510              |
|  | 93             | 135             | 103            | 18 | 85             | 113 | 11 × 17.5 × 11                      |   | 4.82 × 10 <sup>-6</sup> | 4.31       | 14.16                        | 2510              |
|  | 93             | 135             | 133            | 18 | 115            | 113 | 11 × 17.5 × 11                      |   | 4.82 × 10 <sup>-6</sup> | 5.28       | 14.16                        | 2510              |
|  | 100            | 146             | 87             | 22 | 65             | 122 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 4.57       | 13.82                        | 2480              |
|  | 100            | 146             | 99             | 22 | 77             | 122 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 5.05       | 13.82                        | 2480              |
|  | 100            | 146             | 123            | 22 | 101            | 122 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 6.02       | 13.82                        | 2480              |
|  | 105            | 152             | 116            | 25 | 91             | 128 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 6.98       | 13.71                        | 2460              |
|  | 105            | 152             | 164            | 25 | 139            | 128 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 9.18       | 13.71                        | 2460              |
|  | 105            | 152             | 141            | 28 | 113            | 128 | 14 × 20 × 13                        |   | 4.82 × 10 <sup>-6</sup> | 8.32       | 14.05                        | 2460              |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

# BNF No Preload


|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.     | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|---------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|               |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| BNF 5510-2.5  | 55                              | 10         | 56.75                                | 49.5                        | 1×2.5                                  | 33.4              | 97                    | 490                   |
| BNF 5510-5    | 55                              | 10         | 56.75                                | 49.5                        | 2×2.5                                  | 60.7              | 194                   | 950                   |
| BNF 5510-7.5  | 55                              | 10         | 56.75                                | 49.5                        | 3×2.5                                  | 85.9              | 291.1                 | 1390                  |
| BNF 5512-2.5  | 55                              | 12         | 57                                   | 49.2                        | 1×2.5                                  | 39.3              | 108.8                 | 500                   |
| BNF 5512-3    | 55                              | 12         | 57                                   | 49.2                        | 2×1.5                                  | 46                | 131.3                 | 590                   |
| BNF 5512-3.5  | 55                              | 12         | 57                                   | 49.2                        | 1×3.5                                  | 52.4              | 152.9                 | 680                   |
| BNF 5512-5    | 55                              | 12         | 57                                   | 49.2                        | 2×2.5                                  | 71.3              | 218.5                 | 960                   |
| BNF 5512-7.5  | 55                              | 12         | 57                                   | 49.2                        | 3×2.5                                  | 100.9             | 327.3                 | 1420                  |
| BNF 5516-2.5  | 55                              | 16         | 57.7                                 | 47.9                        | 1×2.5                                  | 76.1              | 201.9                 | 650                   |
| BNF 5516-5    | 55                              | 16         | 57.7                                 | 47.9                        | 2×2.5                                  | 138.2             | 402.8                 | 1280                  |
| BNF 5520-2.5  | 55                              | 20         | 57.7                                 | 47.9                        | 1×2.5                                  | 76                | 201.9                 | 660                   |
| BNF 5520-5    | 55                              | 20         | 57.7                                 | 47.9                        | 2×2.5                                  | 138.2             | 403.8                 | 1280                  |
| BNF 6310-2.5  | 63                              | 10         | 64.75                                | 57.7                        | 1×2.5                                  | 35.4              | 111.7                 | 550                   |
| BNF 6310-5    | 63                              | 10         | 64.75                                | 57.7                        | 2×2.5                                  | 64.2              | 222.5                 | 1050                  |
| BNF 6310-7.5  | 63                              | 10         | 64.75                                | 57.7                        | 3×2.5                                  | 90.9              | 334.2                 | 1550                  |
| BNF 6312A-2.5 | 63                              | 12         | 65.25                                | 56.3                        | 1×2.5                                  | 48.1              | 139.2                 | 560                   |
| BNF 6312A-5   | 63                              | 12         | 65.25                                | 56.3                        | 2×2.5                                  | 87.4              | 278.3                 | 1090                  |
| BNF 6316-5    | 63                              | 16         | 65.7                                 | 55.9                        | 2×2.5                                  | 147               | 462.6                 | 1420                  |
| BNF 6320-2.5  | 63                              | 20         | 65.7                                 | 55.9                        | 1×2.5                                  | 81                | 231.3                 | 740                   |
| BNF 6320-5    | 63                              | 20         | 65.7                                 | 55.9                        | 2×2.5                                  | 147               | 463.5                 | 1420                  |

Note) The model numbers in dimmed type indicate semi-standard types.  
If desiring them, contact THK.

## Positioning Ball Screw




Unit: mm

|  | Nut dimensions      |                                   |                                  |    |                |     |                                     | Lubrication hole<br>A | Screw shaft inertial moment/mm <sup>2</sup><br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|---------------------|-----------------------------------|----------------------------------|----|----------------|-----|-------------------------------------|-----------------------|--|----------------|--------------------|---|
|  | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h |                       |  |                |                    |   |
|  | 102                 | 144                               | 81                               | 18 | 63             | 122 | 11 × 17.5 × 11                      | Rc1/8<br>(PT1/8)      | 7.05 × 10 <sup>-6</sup>  | 4.19           | 16.43              | 1230  |
|  | 102                 | 144                               | 111                              | 18 | 93             | 122 | 11 × 17.5 × 11                      |                       | 7.05 × 10 <sup>-6</sup>  | 5.36           | 16.43              | 1230  |
|  | 102                 | 144                               | 141                              | 18 | 123            | 122 | 11 × 17.5 × 11                      |                       | 7.05 × 10 <sup>-6</sup>  | 6.54           | 16.43              | 1230  |
|  | 105                 | 147                               | 93                               | 18 | 75             | 125 | 11 × 17.5 × 11                      |                       | 7.05 × 10 <sup>-6</sup>  | 5.01           | 16.29              | 1220  |
|  | 105                 | 147                               | 107                              | 18 | 89             | 125 | 11 × 17.5 × 11                      |                       | 7.05 × 10 <sup>-6</sup>  | 5.6            | 16.29              | 1220  |
|  | 105                 | 147                               | 105                              | 18 | 87             | 125 | 11 × 17.5 × 11                      |                       | 7.05 × 10 <sup>-6</sup>  | 5.52           | 16.29              | 1220  |
|  | 105                 | 147                               | 129                              | 18 | 111            | 125 | 11 × 17.5 × 11                      |                       | 7.05 × 10 <sup>-6</sup>  | 6.54           | 16.29              | 1220  |
|  | 105                 | 147                               | 165                              | 18 | 147            | 125 | 11 × 17.5 × 11                      |                       | 7.05 × 10 <sup>-6</sup>  | 8.07           | 16.29              | 1220  |
|  | 110                 | 158                               | 116                              | 25 | 91             | 133 | 14 × 20 × 13                        |                       | 7.05 × 10 <sup>-6</sup>  | 7.4            | 15.46              | 1210  |
|  | 110                 | 158                               | 164                              | 25 | 139            | 133 | 14 × 20 × 13                        |                       | 7.05 × 10 <sup>-6</sup>  | 9.73           | 15.46              | 1210  |
|  | 112                 | 158                               | 127                              | 28 | 99             | 134 | 14 × 20 × 13                        |                       | 7.05 × 10 <sup>-6</sup>  | 8.4            | 16.1               | 1210  |
|  | 112                 | 158                               | 187                              | 28 | 159            | 134 | 14 × 20 × 13                        |                       | 7.05 × 10 <sup>-6</sup>  | 11.45          | 16.1               | 1210  |
|  | 108                 | 154                               | 77                               | 22 | 55             | 130 | 14 × 20 × 13                        |                       | 1.21 × 10 <sup>-5</sup>  | 4.57           | 21.93              | 1080  |
|  | 108                 | 154                               | 107                              | 22 | 85             | 130 | 14 × 20 × 13                        |                       | 1.21 × 10 <sup>-5</sup>  | 5.77           | 21.93              | 1080  |
|  | 108                 | 154                               | 137                              | 22 | 115            | 130 | 14 × 20 × 13                        |                       | 1.21 × 10 <sup>-5</sup>  | 6.98           | 21.93              | 1080  |
|  | 115                 | 161                               | 87                               | 22 | 65             | 137 | 14 × 20 × 13                        |                       | 1.21 × 10 <sup>-5</sup>  | 5.8            | 21.14              | 1070  |
|  | 115                 | 161                               | 123                              | 22 | 101            | 137 | 14 × 20 × 13                        |                       | 1.21 × 10 <sup>-5</sup>  | 7.56           | 21.14              | 1070  |
|  | 122                 | 184                               | 160                              | 24 | 136            | 152 | 18 × 26 × 17.5                      |                       | 1.21 × 10 <sup>-5</sup>  | 11.82          | 20.85              | 1060  |
|  | 122                 | 180                               | 127                              | 28 | 99             | 150 | 18 × 26 × 17.5                      |                       | 1.21 × 10 <sup>-5</sup>  | 10.1           | 21.57              | 1060  |
|  | 122                 | 180                               | 187                              | 28 | 159            | 150 | 18 × 26 × 17.5                      |                       | 1.21 × 10 <sup>-5</sup>  | 13.58          | 21.57              | 1060  |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

# BNF No Preload

|          |      |
|----------|------|
| DN value | 7000 |
|----------|------|




| Model No.      | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Rigidity<br>K<br>N/ $\mu$ m |
|----------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------------|
|                |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                             |
| BNF 7010-2.5   | 70                              | 10         | 71.75                                | 64.5                        | 1×2.5                                  | 36.8              | 123.5                 | 590                         |
| BNF 7010-5     | 70                              | 10         | 71.75                                | 64.5                        | 2×2.5                                  | 66.9              | 247                   | 1140                        |
| BNF 7010-7.5   | 70                              | 10         | 71.75                                | 64.5                        | 3×2.5                                  | 94.9              | 371.4                 | 1680                        |
| BNF 7012-2.5   | 70                              | 12         | 72                                   | 64.2                        | 1×2.5                                  | 43.5              | 139.2                 | 600                         |
| BNF 7012-5     | 70                              | 12         | 72                                   | 64.2                        | 2×2.5                                  | 78.9              | 278.3                 | 1160                        |
| BNF 7012-7.5   | 70                              | 12         | 72                                   | 64.2                        | 3×2.5                                  | 111.7             | 417.5                 | 1710                        |
| BNF 7020-5     | 70                              | 20         | 72.7                                 | 62.9                        | 2×2.5                                  | 153.9             | 514.5                 | 1550                        |
| BNF 8010-2.5   | 80                              | 10         | 81.75                                | 75.2                        | 1×2.5                                  | 38.9              | 141.1                 | 650                         |
| BNF 8010-5     | 80                              | 10         | 81.75                                | 75.2                        | 2×2.5                                  | 70.6              | 283.2                 | 1270                        |
| BNF 8010-7.5   | 80                              | 10         | 81.75                                | 75.2                        | 3×2.5                                  | 100               | 424.3                 | 1860                        |
| BNF 8020A-2.5  | 80                              | 20         | 82.7                                 | 72.9                        | 1×2.5                                  | 90.1              | 294                   | 890                         |
| BNF 8020A-5    | 80                              | 20         | 82.7                                 | 72.9                        | 2×2.5                                  | 163.7             | 589                   | 1720                        |
| BNF 8020A-7.5  | 80                              | 20         | 82.7                                 | 72.9                        | 3×2.5                                  | 231.6             | 883.2                 | 2520                        |
| BNF 10020A-2.5 | 100                             | 20         | 102.7                                | 92.9                        | 1×2.5                                  | 99                | 368.5                 | 2110                        |
| BNF 10020A-5   | 100                             | 20         | 102.7                                | 92.9                        | 2×2.5                                  | 179.3             | 737                   | 4080                        |
| BNF 10020A-7.5 | 100                             | 20         | 102.7                                | 92.9                        | 3×2.5                                  | 253.8             | 1105.4                | 6010                        |

Note) The model numbers in dimmed type indicate semi-standard types.  
If desiring them, contact THK.



## Positioning Ball Screw




Unit: mm

|  | Nut dimensions      |                                   |                                  |    |                |     |                                     | Lubrication hole<br>A | Screw shaft inertial moment/mm <sup>2</sup><br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|---------------------|-----------------------------------|----------------------------------|----|----------------|-----|-------------------------------------|-----------------------|--|----------------|--------------------|---|
|  | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h |                       |  |                |                    |   |
|  | 125                 | 167                               | 81                               | 18 | 63             | 145 | 11 × 17.5 × 11                      | Rc1/8<br>(PT1/8)      | 1.85 × 10 <sup>-5</sup>  | 5.8            | 27.4               | 970   |
|  | 125                 | 167                               | 111                              | 18 | 93             | 145 | 11 × 17.5 × 11                      |                       | 1.85 × 10 <sup>-5</sup>  | 7.49           | 27.4               | 970   |
|  | 125                 | 167                               | 141                              | 18 | 123            | 145 | 11 × 17.5 × 11                      |                       | 1.85 × 10 <sup>-5</sup>  | 9.19           | 27.4               | 970   |
|  | 128                 | 170                               | 93                               | 18 | 75             | 148 | 11 × 17.5 × 11                      |                       | 1.85 × 10 <sup>-5</sup>  | 6.89           | 27.24              | 970   |
|  | 128                 | 170                               | 129                              | 18 | 111            | 148 | 11 × 17.5 × 11                      |                       | 1.85 × 10 <sup>-5</sup>  | 9.08           | 27.24              | 970   |
|  | 128                 | 170                               | 165                              | 18 | 147            | 148 | 11 × 17.5 × 11                      |                       | 1.85 × 10 <sup>-5</sup>  | 11.26          | 27.24              | 970   |
|  | 130                 | 186                               | 185                              | 28 | 157            | 158 | 18 × 26 × 17.5                      |                       | 1.85 × 10 <sup>-5</sup>  | 14.5           | 27                 | 960   |
|  | 130                 | 176                               | 77                               | 22 | 55             | 152 | 14 × 20 × 13                        |                       | 3.16 × 10 <sup>-5</sup>  | 5.9            | 36.26              | 850   |
|  | 130                 | 176                               | 107                              | 22 | 85             | 152 | 14 × 20 × 13                        |                       | 3.16 × 10 <sup>-5</sup>  | 7.53           | 36.26              | 850   |
|  | 130                 | 176                               | 137                              | 22 | 115            | 152 | 14 × 20 × 13                        |                       | 3.16 × 10 <sup>-5</sup>  | 9.15           | 36.26              | 850   |
|  | 143                 | 204                               | 127                              | 28 | 99             | 172 | 18 × 26 × 17.5                      |                       | 3.16 × 10 <sup>-5</sup>  | 12.68          | 35.81              | 840   |
|  | 143                 | 204                               | 187                              | 28 | 159            | 172 | 18 × 26 × 17.5                      |                       | 3.16 × 10 <sup>-5</sup>  | 17.12          | 35.81              | 840   |
|  | 143                 | 204                               | 247                              | 28 | 219            | 172 | 18 × 26 × 17.5                      |                       | 3.16 × 10 <sup>-5</sup>  | 21.56          | 35.81              | 840   |
|  | 170                 | 243                               | 131                              | 32 | 99             | 205 | 22 × 32 × 21.5                      |                       | 7.71 × 10 <sup>-5</sup>  | 18.28          | 57.13              | 680   |
|  | 170                 | 243                               | 191                              | 32 | 159            | 205 | 22 × 32 × 21.5                      |                       | 7.71 × 10 <sup>-5</sup>  | 24.2           | 57.13              | 680   |
|  | 170                 | 243                               | 251                              | 32 | 219            | 205 | 22 × 32 × 21.5                      |                       | 7.71 × 10 <sup>-5</sup>  | 30.12          | 57.13              | 680   |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.


# DK No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No. | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|-----------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|           |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| DK 1404-4 | 14                              | 4          | 14.5                                 | 11.8                        | 4 × 1                                  | 5.4               | 10.2                  | 180                   |
| DK 1404-6 | 14                              | 4          | 14.5                                 | 11.8                        | 6 × 1                                  | 7.7               | 15.4                  | 270                   |
| DK 1605-3 | 16                              | 5          | 16.75                                | 13.1                        | 3 × 1                                  | 7.4               | 13                    | 160                   |
| DK 1605-4 | 16                              | 5          | 16.75                                | 13.1                        | 4 × 1                                  | 9.5               | 17.4                  | 210                   |
| DK 2004-3 | 20                              | 4          | 20.5                                 | 17.8                        | 3 × 1                                  | 5.2               | 11.6                  | 190                   |
| DK 2004-4 | 20                              | 4          | 20.5                                 | 17.8                        | 4 × 1                                  | 6.6               | 15.5                  | 250                   |
| DK 2005-3 | 20                              | 5          | 20.75                                | 17.1                        | 3 × 1                                  | 8.5               | 17.3                  | 200                   |
| DK 2005-4 | 20                              | 5          | 20.75                                | 17.1                        | 4 × 1                                  | 11                | 23.1                  | 260                   |
| DK 2006-3 | 20                              | 6          | 21                                   | 16.4                        | 3 × 1                                  | 11.4              | 21.5                  | 410                   |
| DK 2006-4 | 20                              | 6          | 21                                   | 16.4                        | 4 × 1                                  | 14.6              | 28.6                  | 540                   |
| DK 2008-4 | 20                              | 8          | 21                                   | 16.4                        | 4 × 1                                  | 14.6              | 28.8                  | 270                   |

## Positioning Ball Screw




Unit: mm

|  | Nut dimensions |                 |                |    |                |                |     |                                     |    |                       | Screw shaft inertial moment/mm <sup>3</sup> | Nut mass | Shaft mass        | Permissible rotational speed |
|--|----------------|-----------------|----------------|----|----------------|----------------|-----|-------------------------------------|----|-----------------------|---|----------|-------------------|------------------------------|
|  | Outer diameter | Flange diameter | Overall length |    |                |                |     |                                     |    | Lubrication hole      |   |          |                   |                              |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h | Tw | A                     |   |          |                   |                              |
|  |                |                 |                |    |                |                |     |                                     |    | kg·m <sup>2</sup> /mm | kg  | kg/m     | min <sup>-1</sup> |                              |
|  | 26             | 45              | 48             | 10 | 38             | 10             | 35  | 4.5 × 8 × 4.5                       | 29 | M6                    | 2.96 × 10 <sup>-8</sup>                     | 0.2      | 1                 | 4820                         |
|  | 26             | 45              | 60             | 10 | 50             | 10             | 35  | 4.5 × 8 × 4.5                       | 29 | M6                    | 2.96 × 10 <sup>-8</sup>                     | 0.23     | 1                 | 4820                         |
|  | 30             | 49              | 45             | 10 | 35             | 10             | 39  | 4.5 × 8 × 4.5                       | 31 | M6                    | 5.05 × 10 <sup>-8</sup>                     | 0.24     | 1.25              | 4170                         |
|  | 30             | 49              | 50             | 10 | 40             | 10             | 39  | 4.5 × 8 × 4.5                       | 31 | M6                    | 5.05 × 10 <sup>-8</sup>                     | 0.26     | 1.25              | 4170                         |
|  | 32             | 56              | 42             | 11 | 31             | 10             | 44  | 5.5 × 9.5 × 5.5                     | 35 | M6                    | 1.23 × 10 <sup>-7</sup>                     | 0.26     | 2.18              | 3410                         |
|  | 32             | 56              | 46             | 11 | 35             | 10             | 44  | 5.5 × 9.5 × 5.5                     | 35 | M6                    | 1.23 × 10 <sup>-7</sup>                     | 0.27     | 2.18              | 3410                         |
|  | 34             | 58              | 46             | 11 | 35             | 10             | 46  | 5.5 × 9.5 × 5.5                     | 36 | M6                    | 1.23 × 10 <sup>-7</sup>                     | 0.31     | 2.06              | 3370                         |
|  | 34             | 58              | 51             | 11 | 40             | 10             | 46  | 5.5 × 9.5 × 5.5                     | 36 | M6                    | 1.23 × 10 <sup>-7</sup>                     | 0.34     | 2.06              | 3370                         |
|  | 35             | 58              | 52             | 11 | 41             | 10             | 46  | 5.5 × 9.5 × 5.5                     | 36 | M6                    | 1.23 × 10 <sup>-7</sup>                     | 0.36     | 1.93              | 3330                         |
|  | 35             | 58              | 59             | 11 | 48             | 10             | 46  | 5.5 × 9.5 × 5.5                     | 36 | M6                    | 1.23 × 10 <sup>-7</sup>                     | 0.39     | 1.93              | 3330                         |
|  | 35             | 58              | 69             | 11 | 58             | 15             | 46  | 5.5 × 9.5 × 5.5                     | 36 | M6                    | 1.23 × 10 <sup>-7</sup>                     | 0.45     | 2.06              | 3330                         |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.


# DK No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



DK2504 to 2510

| Model No. | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |          | Rigidity<br>K<br>N/μm |
|-----------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|----------|-----------------------|
|           |                                 |            |                                      |                             |  | Ca<br>kN          | Ca<br>kN |                       |
| DK 2504-3 | 25                              | 4          | 25.5                                 | 22.8                        | 3×1                                    | 5.7               | 15       | 230                   |
| DK 2504-4 | 25                              | 4          | 25.5                                 | 22.8                        | 4×1                                    | 7.4               | 19.9     | 310                   |
| DK 2505-3 | 25                              | 5          | 25.75                                | 22.1                        | 3×1                                    | 9.7               | 22.6     | 250                   |
| DK 2505-4 | 25                              | 5          | 25.75                                | 22.1                        | 4×1                                    | 12.4              | 30.3     | 320                   |
| DK 2506-3 | 25                              | 6          | 26                                   | 21.4                        | 3×1                                    | 12.8              | 27       | 250                   |
| DK 2506-4 | 25                              | 6          | 26                                   | 21.4                        | 4×1                                    | 16.8              | 37.4     | 330                   |
| DK 2508-3 | 25                              | 8          | 26                                   | 21.4                        | 3×1                                    | 13.1              | 28.1     | 500                   |
| DK 2508-4 | 25                              | 8          | 26                                   | 21.4                        | 4×1                                    | 16.8              | 37.5     | 330                   |
| DK 2510-3 | 25                              | 10         | 26                                   | 21.6                        | 3×1                                    | 12.7              | 27       | 250                   |
| DK 2510-4 | 25                              | 10         | 26                                   | 21.6                        | 4×1                                    | 16.7              | 37.6     | 330                   |
| DK 2805-3 | 28                              | 5          | 28.75                                | 25.2                        | 3×1                                    | 10.5              | 26.4     | 270                   |
| DK 2805-4 | 28                              | 5          | 28.75                                | 25.2                        | 4×1                                    | 13.4              | 35.2     | 360                   |
| DK 2806-3 | 28                              | 6          | 29                                   | 24.4                        | 3×1                                    | 14                | 32       | 280                   |
| DK 2806-4 | 28                              | 6          | 29                                   | 24.4                        | 4×1                                    | 18                | 42.5     | 370                   |
| DK 2810-4 | 28                              | 10         | 29.25                                | 23.6                        | 4×1                                    | 22.4              | 50       | 370                   |



DK2805 to 2810


Unit: mm

|  | Nut dimensions   |                                |                               |    |                |                |     |                                     |    |                    | Screw shaft inertial moment/mm <sup>3</sup> | Nut mass kg | Shaft mass kg/m | Permissible rotational speed min <sup>-1</sup> |
|--|------------------|--------------------------------|-------------------------------|----|----------------|----------------|-----|-------------------------------------|----|--------------------|---|-------------|-----------------|--|
|  | Outer diameter D | Flange diameter D <sub>1</sub> | Overall length L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h | Tw | Lubrication hole A |   |             |                 |  |
|  | 38               | 63                             | 43                            | 11 | 32             | 10             | 51  | 5.5 × 9.5 × 5.5                     | 39 | M6                 | 3.01 × 10 <sup>-7</sup>                     | 0.33        | 3.5             | 2740   |
|  | 38               | 63                             | 47                            | 11 | 36             | 10             | 51  | 5.5 × 9.5 × 5.5                     | 39 | M6                 | 3.01 × 10 <sup>-7</sup>                     | 0.35        | 3.5             | 2740   |
|  | 40               | 63                             | 46                            | 11 | 35             | 10             | 51  | 5.5 × 9.5 × 5.5                     | 41 | M6                 | 3.01 × 10 <sup>-7</sup>                     | 0.38        | 3.35            | 2710   |
|  | 40               | 63                             | 51                            | 11 | 40             | 10             | 51  | 5.5 × 9.5 × 5.5                     | 41 | M6                 | 3.01 × 10 <sup>-7</sup>                     | 0.41        | 3.35            | 2710   |
|  | 40               | 63                             | 52                            | 11 | 41             | 10             | 51  | 5.5 × 9.5 × 5.5                     | 41 | M6                 | 3.01 × 10 <sup>-7</sup>                     | 0.41        | 3.19            | 2690   |
|  | 40               | 63                             | 60                            | 11 | 49             | 10             | 51  | 5.5 × 9.5 × 5.5                     | 41 | M6                 | 3.01 × 10 <sup>-7</sup>                     | 0.46        | 3.19            | 2690   |
|  | 40               | 63                             | 62                            | 12 | 50             | 10             | 51  | 5.5 × 9.5 × 5.5                     | 41 | M6                 | 3.01 × 10 <sup>-7</sup>                     | 0.48        | 3.35            | 2690   |
|  | 40               | 63                             | 71                            | 12 | 59             | 15             | 51  | 5.5 × 9.5 × 5.5                     | 41 | M6                 | 3.01 × 10 <sup>-7</sup>                     | 0.54        | 3.35            | 2690   |
|  | 40               | 63                             | 80                            | 15 | 65             | 15             | 51  | 5.5 × 9.5 × 5.5                     | 41 | M6                 | 3.01 × 10 <sup>-7</sup>                     | 0.62        | 3.45            | 2690   |
|  | 40               | 63                             | 85                            | 15 | 70             | 20             | 51  | 5.5 × 9.5 × 5.5                     | 41 | M6                 | 3.01 × 10 <sup>-7</sup>                     | 0.65        | 3.45            | 2690   |
|  | 43               | 71                             | 49                            | 12 | 37             | 10             | 57  | 6.6 × 11 × 6.5                      | 55 | M6                 | 4.74 × 10 <sup>-7</sup>                     | 0.48        | 4.27            | 2430   |
|  | 43               | 71                             | 54                            | 12 | 42             | 10             | 57  | 6.6 × 11 × 6.5                      | 55 | M6                 | 4.74 × 10 <sup>-7</sup>                     | 0.51        | 4.27            | 2430   |
|  | 43               | 71                             | 53                            | 12 | 41             | 10             | 57  | 6.6 × 11 × 6.5                      | 55 | M6                 | 4.74 × 10 <sup>-7</sup>                     | 0.5         | 4.36            | 2410   |
|  | 43               | 71                             | 61                            | 12 | 49             | 10             | 57  | 6.6 × 11 × 6.5                      | 55 | M6                 | 4.74 × 10 <sup>-7</sup>                     | 0.56        | 4.36            | 2410   |
|  | 45               | 71                             | 84                            | 15 | 69             | 20             | 57  | 6.6 × 11 × 6.5                      | 55 | M6                 | 4.74 × 10 <sup>-7</sup>                     | 0.82        | 4.18            | 2390   |


Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

# DK No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No. | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|-----------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|           |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| DK 3204-3 | 32                              | 4          | 32.5                                 | 30.1                        | 3 × 1                                  | 6.4               | 19.6                  | 290                   |
| DK 3204-4 | 32                              | 4          | 32.5                                 | 30.1                        | 4 × 1                                  | 8.2               | 26.1                  | 380                   |
| DK 3205-3 | 32                              | 5          | 32.75                                | 29.2                        | 3 × 1                                  | 11.1              | 30.2                  | 300                   |
| DK 3205-4 | 32                              | 5          | 32.75                                | 29.2                        | 4 × 1                                  | 14.2              | 40.3                  | 400                   |
| DK 3205-6 | 32                              | 5          | 32.75                                | 29.2                        | 6 × 1                                  | 20.1              | 60.4                  | 600                   |
| DK 3206-3 | 32                              | 6          | 33                                   | 28.4                        | 3 × 1                                  | 14.9              | 37.1                  | 310                   |
| DK 3206-4 | 32                              | 6          | 33                                   | 28.4                        | 4 × 1                                  | 19.1              | 49.5                  | 410                   |
| DK 3210-3 | 32                              | 10         | 33.75                                | 26.4                        | 3 × 1                                  | 25.7              | 52.2                  | 300                   |
| DK 3210-4 | 32                              | 10         | 33.75                                | 26.4                        | 4 × 1                                  | 33                | 69.7                  | 390                   |
| DK 3212-4 | 32                              | 12         | 33.75                                | 26.4                        | 4 × 1                                  | 34.2              | 73.9                  | 420                   |
| DK 3610-3 | 36                              | 10         | 37.75                                | 30.5                        | 3 × 1                                  | 28.8              | 63.8                  | 350                   |
| DK 3610-4 | 36                              | 10         | 37.75                                | 30.5                        | 4 × 1                                  | 36.8              | 85                    | 470                   |
| DK 4010-3 | 40                              | 10         | 41.75                                | 34.4                        | 3 × 1                                  | 29.8              | 69.3                  | 380                   |
| DK 4010-4 | 40                              | 10         | 41.75                                | 34.4                        | 4 × 1                                  | 38.1              | 92.4                  | 500                   |
| DK 4012-3 | 40                              | 12         | 41.75                                | 34.4                        | 3 × 1                                  | 30.6              | 72.3                  | 390                   |
| DK 4012-4 | 40                              | 12         | 41.75                                | 34.4                        | 4 × 1                                  | 39.2              | 96.4                  | 520                   |
| DK 4016-4 | 40                              | 16         | 41.75                                | 34.4                        | 4 × 1                                  | 39.1              | 96.8                  | 520                   |
| DK 4020-3 | 40                              | 20         | 41.75                                | 34.7                        | 3 × 1                                  | 29.4              | 69.3                  | 750                   |




Unit: mm

|  | Nut dimensions |                 |                |    |                |                |     |                                   |    |                  | Screw shaft inertial moment/mm <sup>3</sup> | Nut mass | Shaft mass | Permissible rotational speed |
|--|----------------|-----------------|----------------|----|----------------|----------------|-----|-----------------------------------|----|------------------|---|----------|------------|------------------------------|
|  | Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | Tw | Lubrication hole |   |          |            |                              |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | Tw | A                | kg·m <sup>2</sup> /mm                       | kg       | kg/m       | min <sup>-1</sup>            |
|  | 45             | 76              | 44             | 11 | 33             | 10             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.44     | 5.86       | 2150                         |
|  | 45             | 76              | 48             | 11 | 37             | 10             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.47     | 5.86       | 2150                         |
|  | 46             | 76              | 47             | 12 | 35             | 10             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.5      | 5.67       | 2130                         |
|  | 46             | 76              | 52             | 12 | 40             | 10             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.53     | 5.67       | 2130                         |
|  | 46             | 76              | 62             | 12 | 50             | 10             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.6      | 5.67       | 2130                         |
|  | 48             | 76              | 53             | 12 | 41             | 10             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.58     | 6.31       | 2120                         |
|  | 48             | 76              | 61             | 12 | 49             | 10             | 63  | 6.6×11×6.5                        | 59 | M6               | 8.08×10 <sup>-7</sup>                       | 0.65     | 6.31       | 2120                         |
|  | 54             | 87              | 80             | 15 | 65             | 15             | 69  | 9×14×8.5                          | 66 | M6               | 8.08×10 <sup>-7</sup>                       | 1.22     | 4.98       | 2070                         |
|  | 54             | 87              | 90             | 15 | 75             | 20             | 69  | 9×14×8.5                          | 66 | M6               | 8.08×10 <sup>-7</sup>                       | 1.34     | 4.98       | 2070                         |
|  | 54             | 87              | 98             | 15 | 83             | 25             | 69  | 9×14×8.5                          | 66 | M6               | 8.08×10 <sup>-7</sup>                       | 1.43     | 5.2        | 2070                         |
|  | 58             | 98              | 82             | 18 | 64             | 15             | 77  | 11×17.5×11                        | 75 | M6               | 1.29×10 <sup>-6</sup>                       | 1.52     | 6.51       | 1850                         |
|  | 58             | 98              | 93             | 18 | 75             | 20             | 77  | 11×17.5×11                        | 75 | M6               | 1.29×10 <sup>-6</sup>                       | 1.66     | 6.51       | 1850                         |
|  | 62             | 104             | 83             | 18 | 65             | 15             | 82  | 11×17.5×11                        | 79 | Rc1/8<br>(PT1/8) | 1.97×10 <sup>-6</sup>                       | 3.14     | 8.22       | 1670                         |
|  | 62             | 104             | 93             | 18 | 75             | 20             | 82  | 11×17.5×11                        | 79 |                  | 1.97×10 <sup>-6</sup>                       | 3.41     | 8.22       | 1670                         |
|  | 62             | 104             | 90             | 18 | 72             | 20             | 82  | 11×17.5×11                        | 79 |                  | 1.97×10 <sup>-6</sup>                       | 1.77     | 8.5        | 1670                         |
|  | 62             | 104             | 103            | 18 | 85             | 25             | 82  | 11×17.5×11                        | 79 |                  | 1.97×10 <sup>-6</sup>                       | 1.95     | 8.5        | 1670                         |
|  | 62             | 104             | 120            | 18 | 102            | 30             | 82  | 11×17.5×11                        | 79 |                  | 1.97×10 <sup>-6</sup>                       | 2.19     | 8.83       | 1670                         |
|  | 62             | 104             | 123            | 18 | 105            | 30             | 82  | 11×17.5×11                        | 79 |                  | 1.97×10 <sup>-6</sup>                       | 2.23     | 9.03       | 1670                         |

Note)The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

# DK No Preload


|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No. | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|-----------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|           |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| DK 5010-3 | 50                              | 10         | 51.75                                | 44.4                        | 3 × 1                                  | 33.9              | 90.7                  | 470                   |
| DK 5010-4 | 50                              | 10         | 51.75                                | 44.4                        | 4 × 1                                  | 43.4              | 120.5                 | 610                   |
| DK 5010-6 | 50                              | 10         | 51.75                                | 44.4                        | 6 × 1                                  | 62.7              | 186.8                 | 930                   |
| DK 5012-3 | 50                              | 12         | 52.25                                | 43.3                        | 3 × 1                                  | 45.8              | 113                   | 490                   |
| DK 5012-4 | 50                              | 12         | 52.25                                | 43.3                        | 4 × 1                                  | 58.6              | 150.6                 | 640                   |
| DK 5016-3 | 50                              | 16         | 52.25                                | 43.3                        | 3 × 1                                  | 45.7              | 113.3                 | 490                   |
| DK 5016-4 | 50                              | 16         | 52.25                                | 43.3                        | 4 × 1                                  | 58.5              | 151                   | 640                   |
| DK 5020-3 | 50                              | 20         | 52.25                                | 43.6                        | 3 × 1                                  | 44.2              | 108.8                 | 470                   |
| DK 6310-4 | 63                              | 10         | 64.75                                | 57.7                        | 4 × 1                                  | 49.5              | 160.7                 | 780                   |
| DK 6310-6 | 63                              | 10         | 64.75                                | 57.7                        | 6 × 1                                  | 70.3              | 242.1                 | 1140                  |
| DK 6312-3 | 63                              | 12         | 65.25                                | 56.3                        | 3 × 1                                  | 51.9              | 147.4                 | 600                   |
| DK 6312-4 | 63                              | 12         | 65.25                                | 56.3                        | 4 × 1                                  | 66.4              | 196.6                 | 785                   |
| DK 6320-3 | 63                              | 20         | 65.7                                 | 55.9                        | 3 × 1                                  | 83.5              | 229.3                 | 1470                  |



## Positioning Ball Screw




Unit: mm

|  | Nut dimensions |                 |                |    |                |                |     |                                   |     |                  | Screw shaft inertial moment/mm <sup>3</sup><br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|----------------|-----------------|----------------|----|----------------|----------------|-----|-----------------------------------|-----|------------------|--|----------------|--------------------|---|
|  | Outer diameter | Flange diameter | Overall length | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> ×d <sub>2</sub> ×h | Tw  | Lubrication hole |  |                |                    |   |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> |    |                |                |     |                                   | A   |                  |  |                |                    |   |
|  | 72             | 123             | 83             | 18 | 65             | 15             | 101 | 11×17.5×11                        | 92  | Rc1/8<br>(PT1/8) | 4.82×10 <sup>-6</sup>  | 2.14           | 13.38              | 1350  |
|  | 72             | 123             | 93             | 18 | 75             | 20             | 101 | 11×17.5×11                        | 92  |                  | 4.82×10 <sup>-6</sup>  | 2.3            | 13.38              | 1350  |
|  | 72             | 123             | 114            | 18 | 96             | 30             | 101 | 11×17.5×11                        | 92  |                  | 4.82×10 <sup>-6</sup>  | 2.65           | 13.38              | 1350  |
|  | 75             | 129             | 97             | 22 | 75             | 20             | 105 | 14×20×13                          | 98  |                  | 4.82×10 <sup>-6</sup>  | 2.91           | 12.74              | 1330  |
|  | 75             | 129             | 110            | 22 | 88             | 25             | 105 | 14×20×13                          | 98  |                  | 4.82×10 <sup>-6</sup>  | 3.16           | 12.74              | 1330  |
|  | 75             | 129             | 111            | 22 | 89             | 25             | 105 | 14×20×13                          | 98  |                  | 4.82×10 <sup>-6</sup>  | 3.18           | 13.41              | 1330  |
|  | 75             | 129             | 129            | 22 | 107            | 30             | 105 | 14×20×13                          | 98  |                  | 4.82×10 <sup>-6</sup>  | 3.52           | 13.41              | 1330  |
|  | 75             | 129             | 136            | 28 | 108            | 30             | 105 | 14×20×13                          | 98  |                  | 4.82×10 <sup>-6</sup>  | 3.94           | 13.8               | 1330  |
|  | 85             | 146             | 97             | 22 | 75             | 20             | 122 | 14×20×13                          | 110 |                  | 1.21×10 <sup>-5</sup>  | 3.28           | 21.93              | 1080  |
|  | 85             | 146             | 118            | 22 | 96             | 30             | 122 | 14×20×13                          | 110 |                  | 1.21×10 <sup>-5</sup>  | 3.7            | 21.93              | 1080  |
|  | 90             | 146             | 98             | 22 | 76             | 20             | 122 | 14×20×13                          | 110 |                  | 1.21×10 <sup>-5</sup>  | 3.71           | 21.14              | 1070  |
|  | 90             | 146             | 111            | 22 | 89             | 25             | 122 | 14×20×13                          | 110 |                  | 1.21×10 <sup>-5</sup>  | 4.04           | 21.14              | 1070  |
|  | 95             | 159             | 136            | 28 | 108            | 30             | 129 | 18×26×17.5                        | 121 |                  | 1.21×10 <sup>-5</sup>  | 6.17           | 21.57              | 1060  |


Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

# WHF No Preload

|          |        |
|----------|--------|
| DN value | 120000 |
|----------|--------|




WHF1530/1540/2020/2025/  
2030/2040/2550



WHF2525

| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Rigidity<br>K<br>N/μm | Nut dimensions      |                                   |                                  |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|---------------------|-----------------------------------|----------------------------------|
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> |
| WHF 1530-3.4 | 15                              | 30         | 15.75                                | 12.5                        | 2×1.7                                  | 8                 | 14.4                  | 195                   | 32                  | 53                                | 64.5                             |
| WHF 1540-3.4 | 15                              | 40         | 15.75                                | 12.5                        | 2×1.7                                  | 7.7               | 16.3                  | 209                   | 34                  | 57                                | 81.6                             |
| WHF 2020-3.4 | 20                              | 20         | 20.75                                | 17.5                        | 2×1.7                                  | 9.6               | 21                    | 225                   | 42                  | 64                                | 47.1                             |
| WHF 2025-3.4 | 20                              | 25         | 20.75                                | 17.6                        | 2×1.7                                  | 9.8               | 22.3                  | 236                   | 39                  | 62                                | 56.2                             |
| WHF 2030-3.4 | 20                              | 30         | 20.75                                | 17.6                        | 2×1.7                                  | 9.9               | 23.5                  | 243                   | 39                  | 62                                | 65.3                             |
| WHF 2040-3.4 | 20                              | 40         | 20.75                                | 17.5                        | 2×1.7                                  | 9.6               | 20.3                  | 256                   | 37                  | 57                                | 82.7                             |
| WHF 2525-3.4 | 25                              | 25         | 26                                   | 21.9                        | 2×1.7                                  | 14.5              | 33.1                  | 285                   | 50                  | 77                                | 58.8                             |
| WHF 2550-3.4 | 25                              | 50         | 26                                   | 21.9                        | 2×1.7                                  | 14.4              | 31.9                  | 323                   | 45                  | 69                                | 103.3                            |

## Positioning Ball Screw



Unit: mm


| Nut dimensions |                |     |                |    |                |                       |                       | Screw shaft inertial moment/mm<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|----------------|----------------|-----|----------------|----|----------------|-----------------------|-----------------------|---|----------------|--------------------|---|
| H              | B <sub>1</sub> | PCD | d <sub>1</sub> | Tw | N <sub>1</sub> | Lubrication hole<br>A |                       |   |                |                    |   |
| 10             | 47.5           | 43  | 5.5            | 33 | 5              | M6                    | $3.9 \times 10^{-8}$  | 0.38  | 1.26           | 5000               |   |
| 10             | 64.6           | 45  | 5.5            | 40 | 5              | M6                    | $3.9 \times 10^{-8}$  | 0.48  | 1.28           | 5000               |   |
| 10             | 24.1           | 53  | 5.5            | 46 | 5              | M6                    | $1.23 \times 10^{-7}$ | 0.49  | 2.25           | 5000               |   |
| 10             | 33.2           | 50  | 5.5            | 46 | 5              | M6                    | $1.23 \times 10^{-7}$ | 0.51  | 2.26           | 5000               |   |
| 10             | 43.3           | 50  | 5.5            | 46 | 5              | M6                    | $1.23 \times 10^{-7}$ | 0.55  | 2.28           | 5000               |   |
| 10             | 65.7           | 47  | 5.5            | 38 | 5              | M6                    | $1.23 \times 10^{-7}$ | 0.58  | 2.34           | 5000               |   |
| 12             | 31.3           | 63  | 6.6            | 56 | 6              | M6                    | $3.01 \times 10^{-7}$ | 0.65  | 3.52           | 4610               |   |
| 12             | 79.3           | 57  | 6.6            | 46 | 6              | M6                    | $3.01 \times 10^{-7}$ | 0.72  | 3.66           | 4610               |   |

Note) The Model WHF can be equipped with a brush seal depending on the model number. Contact THK if you would like to use one.

The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.


# BLK (Precision Ball Screw) No Preload

|          |      |
|----------|------|
| DN value | 7000 |
|----------|------|



BLK0808

| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| BLK 0808-3.2 | 8                               | 8          | 8.4                                  | 6.7                         | 2×1.6                                  | 2.2               | 3.8                   | 95                    |
| BLK 1510-5.6 | 15                              | 10         | 15.75                                | 12.5                        | 2×2.8                                  | 14.3              | 27.8                  | 340                   |
| BLK 1616-2.8 | 16                              | 16         | 16.65                                | 13.7                        | 1×2.8                                  | 5.2               | 9.9                   | 180                   |
| BLK 1616-3.6 | 16                              | 16         | 16.65                                | 13.7                        | 2×1.8                                  | 7.1               | 14.3                  | 220                   |
| BLK 2020-2.8 | 20                              | 20         | 20.75                                | 17.5                        | 1×2.8                                  | 8.1               | 17.2                  | 230                   |
| BLK 2020-3.6 | 20                              | 20         | 20.75                                | 17.5                        | 2×1.8                                  | 11.1              | 24.7                  | 290                   |
| BLK 2525-2.8 | 25                              | 25         | 26                                   | 21.9                        | 1×2.8                                  | 12.2              | 26.9                  | 270                   |
| BLK 2525-3.6 | 25                              | 25         | 26                                   | 21.9                        | 2×1.8                                  | 16.6              | 38.7                  | 350                   |
| BLK 3232-2.8 | 32                              | 32         | 33.25                                | 28.3                        | 1×2.8                                  | 17.3              | 41.4                  | 340                   |
| BLK 3232-3.6 | 32                              | 32         | 33.25                                | 28.3                        | 2×1.8                                  | 23.7              | 59.5                  | 440                   |
| BLK 3620-5.6 | 36                              | 20         | 37.75                                | 31.2                        | 2×2.8                                  | 54.9              | 134.3                 | 760                   |
| BLK 3624-5.6 | 36                              | 24         | 38                                   | 30.7                        | 2×2.8                                  | 63.8              | 151.9                 | 770                   |
| BLK 3636-2.8 | 36                              | 36         | 37.4                                 | 31.7                        | 1×2.8                                  | 22.4              | 54.1                  | 390                   |
| BLK 3636-3.6 | 36                              | 36         | 37.4                                 | 31.7                        | 2×1.8                                  | 30.8              | 78                    | 490                   |
| BLK 4040-2.8 | 40                              | 40         | 41.75                                | 35.2                        | 1×2.8                                  | 28.2              | 68.9                  | 430                   |
| BLK 4040-3.6 | 40                              | 40         | 41.75                                | 35.2                        | 2×1.8                                  | 38.7              | 99.2                  | 550                   |
| BLK 5050-2.8 | 50                              | 50         | 52.2                                 | 44.1                        | 1×2.8                                  | 42.2              | 107.8                 | 530                   |
| BLK 5050-3.6 | 50                              | 50         | 52.2                                 | 44.1                        | 2×1.8                                  | 57.8              | 155                   | 670                   |



Unit: mm


|  | Nut dimensions      |                                   |                                  |    |                |     |                |     |                |                       | Screw shaft inertial moment/mm <sup>3</sup><br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|---------------------|-----------------------------------|----------------------------------|----|----------------|-----|----------------|-----|----------------|-----------------------|--|----------------|--------------------|---|
|  | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | B <sub>1</sub> | PCD | d <sub>1</sub> | Tw  | N <sub>1</sub> | Lubrication hole<br>A |  |                |                    |   |
|  | 18                  | 31                                | 20                               | 4  | 10             | 25  | 3.4            | 20  | —              | —                     | 3.16 × 10 <sup>-9</sup>  | 0.03           | 0.36               | 3500  |
|  | 34                  | 57                                | 44                               | 10 | 24             | 45  | 5.5            | 40  | 5              | M6                    | 3.9 × 10 <sup>-8</sup>   | 0.34           | 0.31               | 4440  |
|  | 32                  | 53                                | 54                               | 10 | 37.5           | 42  | 4.5            | 38  | 5              | M6                    | 5.05 × 10 <sup>-8</sup>  | 0.32           | 1.41               | 4200  |
|  | 32                  | 53                                | 38                               | 10 | 21.5           | 42  | 4.5            | 38  | 5              | M6                    | 5.05 × 10 <sup>-8</sup>  | 0.21           | 1.41               | 4200  |
|  | 39                  | 62                                | 65                               | 10 | 47.5           | 50  | 5.5            | 46  | 5              | M6                    | 1.23 × 10 <sup>-7</sup>  | 0.49           | 2.25               | 3370  |
|  | 39                  | 62                                | 45                               | 10 | 27.5           | 50  | 5.5            | 46  | 5              | M6                    | 1.23 × 10 <sup>-7</sup>  | 0.35           | 2.25               | 3370  |
|  | 47                  | 74                                | 80                               | 12 | 60             | 60  | 6.6            | 56  | 6              | M6                    | 3.01 × 10 <sup>-7</sup>  | 0.89           | 3.52               | 2690  |
|  | 47                  | 74                                | 55                               | 12 | 35             | 60  | 6.6            | 56  | 6              | M6                    | 3.01 × 10 <sup>-7</sup>  | 0.64           | 3.52               | 2690  |
|  | 58                  | 92                                | 102                              | 15 | 77             | 74  | 9              | 68  | 7.5            | M6                    | 8.08 × 10 <sup>-7</sup>  | 1.78           | 5.83               | 2100  |
|  | 58                  | 92                                | 70                               | 15 | 45             | 74  | 9              | 68  | 7.5            | M6                    | 8.08 × 10 <sup>-7</sup>  | 1.32           | 5.83               | 2100  |
|  | 70                  | 110                               | 78                               | 17 | 45             | 90  | 11             | 80  | 8.5            | M6                    | 1.29 × 10 <sup>-6</sup>  | 2.23           | 6.49               | 1850  |
|  | 75                  | 115                               | 94                               | 18 | 59             | 94  | 11             | 86  | 9              | M6                    | 1.29 × 10 <sup>-6</sup>  | 3.05           | 6.39               | 1840  |
|  | 66                  | 106                               | 113                              | 17 | 86             | 85  | 11             | 76  | 8.5            | M6                    | 1.29 × 10 <sup>-6</sup>  | 2.61           | 7.34               | 1870  |
|  | 66                  | 106                               | 77                               | 17 | 50             | 85  | 11             | 76  | 8.5            | M6                    | 1.29 × 10 <sup>-6</sup>  | 1.93           | 7.34               | 1870  |
|  | 73                  | 114                               | 125                              | 17 | 96.5           | 93  | 11             | 84  | 8.5            | M6                    | 1.97 × 10 <sup>-6</sup>  | 3.4            | 9.01               | 1670  |
|  | 73                  | 114                               | 85                               | 17 | 56.5           | 93  | 11             | 84  | 8.5            | M6                    | 1.97 × 10 <sup>-6</sup>  | 2.48           | 9.01               | 1670  |
|  | 90                  | 135                               | 156                              | 20 | 122            | 112 | 14             | 104 | 10             | M6                    | 4.82 × 10 <sup>-6</sup>  | 6.18           | 14.08              | 1340  |
|  | 90                  | 135                               | 106                              | 20 | 72             | 112 | 14             | 104 | 10             | M6                    | 4.82 × 10 <sup>-6</sup>  | 4.45           | 14.08              | 1340  |

Note) The Model BLK can be equipped with a brush seal depending on the model number. Contact THK if you would like to use one.

The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.


# WGF No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
|              |                                 |            |                                      |                             |  | WGF 0812-3        | 8                     | 12                    |
| WGF 1015-3   | 10                              | 15         | 10.5                                 | 8.3                         | 2×1.65                                 | 3.3               | 6.2                   | 140                   |
| WGF 1320-3   | 13                              | 20         | 13.5                                 | 10.8                        | 2×1.65                                 | 4.7               | 9.6                   | 180                   |
| WGF 1520-1.5 | 15                              | 20         | 15.75                                | 12.5                        | 1×1.5                                  | 4.4               | 7.9                   | 100                   |
| WGF 1520-3   | 15                              | 20         | 15.75                                | 12.5                        | 2×1.5                                  | 8.1               | 15.8                  | 190                   |
| WGF 1530-1   | 15                              | 30         | 15.75                                | 12.5                        | 2×0.6                                  | 3.5               | 5.4                   | 90                    |
| WGF 1530-3   | 15                              | 30         | 15.75                                | 12.5                        | 2×1.6                                  | 8.1               | 14.6                  | 220                   |
| WGF 1540-1.5 | 15                              | 40         | 15.75                                | 12.5                        | 2×0.75                                 | 3.9               | 7.4                   | 110                   |
| WGF 2040-1   | 20                              | 40         | 20.75                                | 17.5                        | 2×0.65                                 | 4.3               | 8                     | 110                   |
| WGF 2040-3   | 20                              | 40         | 20.75                                | 17.5                        | 2×1.65                                 | 9.5               | 20.2                  | 280                   |
| WGF 2060-1.5 | 20                              | 60         | 20.75                                | 17.5                        | 2×0.75                                 | 4.5               | 11                    | 140                   |
| WGF 2550-1   | 25                              | 50         | 26                                   | 21.9                        | 2×0.65                                 | 6.4               | 12.5                  | 140                   |
| WGF 2550-3   | 25                              | 50         | 26                                   | 21.9                        | 2×1.65                                 | 14.3              | 31.7                  | 340                   |
| WGF 3060-1   | 30                              | 60         | 31.25                                | 26.4                        | 2×0.65                                 | 8.9               | 18                    | 170                   |
| WGF 3060-3   | 30                              | 60         | 31.25                                | 26.4                        | 2×1.65                                 | 19.9              | 45.7                  | 410                   |
| WGF 3090-1.5 | 30                              | 90         | 31.25                                | 26.4                        | 2×0.75                                 | 9.8               | 25.8                  | 200                   |
| WGF 4080-1   | 40                              | 80         | 41.75                                | 35.2                        | 2×0.65                                 | 15                | 32.1                  | 220                   |
| WGF 4080-3   | 40                              | 80         | 41.75                                | 35.2                        | 2×1.65                                 | 33.4              | 81.4                  | 530                   |
| WGF 50100-1  | 50                              | 100        | 52.2                                 | 44.1                        | 2×0.65                                 | 22.4              | 50.1                  | 270                   |
| WGF 50100-3  | 50                              | 100        | 52.2                                 | 44.1                        | 2×1.65                                 | 49.9              | 127.2                 | 650                   |

## Positioning Ball Screw



Unit: mm


|  | Nut dimensions    |                    |                   |    |                |     |                |    |                |                     | Screw shaft<br>inertial<br>moment/mm<br>kg·m <sup>2</sup> /mm | Nut<br>mass<br>kg | Shaft<br>mass<br>kg/m | Permissible<br>rotational<br>speed<br>min <sup>-1</sup> |
|--|-------------------|--------------------|-------------------|----|----------------|-----|----------------|----|----------------|---------------------|---|-------------------|-----------------------|---|
|  | Outer<br>diameter | Flange<br>diameter | Overall<br>length | H  | B <sub>1</sub> | PCD | d <sub>i</sub> | Tw | N <sub>1</sub> | Lubrication<br>hole |   |                   |                       |   |
|  | D                 | D <sub>1</sub>     | L <sub>1</sub>    |    |                |     |                |    |                | A                   |   |                   |                       |   |
|  | 18                | 31                 | 27                | 4  | 17             | 25  | 3.4            | 20 | —              | —                   | 3.16 × 10 <sup>-9</sup>                                       | 0.054             | 0.35                  | 3500  |
|  | 23                | 40                 | 33                | 5  | 22             | 32  | 4.5            | 25 | —              | —                   | 7.71 × 10 <sup>-9</sup>                                       | 0.11              | 0.55                  | 3500  |
|  | 28                | 45                 | 43                | 5  | 29             | 37  | 4.5            | 30 | —              | —                   | 2.2 × 10 <sup>-8</sup>  | 0.18              | 0.96                  | 3500  |
|  | 32                | 53                 | 45                | 10 | 28             | 43  | 5.5            | 33 | 5              | M6                  | 3.9 × 10 <sup>-8</sup>  | 0.29              | 1.22                  | 4440  |
|  | 32                | 53                 | 45                | 10 | 28             | 43  | 5.5            | 33 | 5              | M6                  | 3.9 × 10 <sup>-8</sup>  | 0.29              | 1.22                  | 4440  |
|  | 32                | 53                 | 33                | 10 | 17             | 43  | 5.5            | 33 | 5              | M6                  | 3.9 × 10 <sup>-8</sup>  | 0.23              | 1.26                  | 4440  |
|  | 32                | 53                 | 63                | 10 | 47             | 43  | 5.5            | 33 | 5              | M6                  | 3.9 × 10 <sup>-8</sup>  | 0.38              | 1.26                  | 4440  |
|  | 32                | 53                 | 42                | 10 | 26.3           | 43  | 5.5            | 33 | 5              | M6                  | 3.9 × 10 <sup>-8</sup>  | 0.28              | 1.28                  | 4440  |
|  | 37                | 57                 | 41                | 10 | 25             | 47  | 5.5            | 38 | 5.5            | M6                  | 1.23 × 10 <sup>-7</sup>                                       | 0.24              | 2.34                  | 3370  |
|  | 37                | 57                 | 81                | 10 | 65             | 47  | 5.5            | 38 | 5.5            | M6                  | 1.23 × 10 <sup>-7</sup>                                       | 0.48              | 2.34                  | 3370  |
|  | 37                | 57                 | 60                | 10 | 40.1           | 47  | 5.5            | 38 | 5.5            | M6                  | 1.23 × 10 <sup>-7</sup>                                       | 0.4               | 2.37                  | 3370  |
|  | 45                | 69                 | 52                | 12 | 31.5           | 57  | 6.6            | 46 | 7              | M6                  | 3.01 × 10 <sup>-7</sup>                                       | 0.43              | 3.66                  | 2690  |
|  | 45                | 69                 | 102               | 12 | 81.5           | 57  | 6.6            | 46 | 7              | M6                  | 3.01 × 10 <sup>-7</sup>                                       | 0.85              | 3.66                  | 2690  |
|  | 55                | 89                 | 62                | 15 | 37             | 71  | 9              | 56 | 9              | M6                  | 6.24 × 10 <sup>-7</sup>                                       | 1.11              | 5.28                  | 2240  |
|  | 55                | 89                 | 122               | 15 | 97             | 71  | 9              | 56 | 9              | M6                  | 6.24 × 10 <sup>-7</sup>                                       | 1.9               | 5.28                  | 2240  |
|  | 55                | 89                 | 92                | 15 | 61.3           | 71  | 9              | 56 | 9              | M6                  | 6.24 × 10 <sup>-7</sup>                                       | 1.51              | 5.34                  | 2240  |
|  | 73                | 114                | 79                | 17 | 50.5           | 93  | 11             | 74 | 9              | M6                  | 1.97 × 10 <sup>-6</sup>                                       | 2.34              | 9.38                  | 1670  |
|  | 73                | 114                | 159               | 17 | 130.5          | 93  | 11             | 74 | 9              | M6                  | 1.97 × 10 <sup>-6</sup>                                       | 4.18              | 9.38                  | 1670  |
|  | 90                | 135                | 98                | 20 | 64             | 112 | 14             | 92 | 10             | M6                  | 4.82 × 10 <sup>-6</sup>                                       | 4.18              | 14.66                 | 1340  |
|  | 90                | 135                | 198               | 20 | 164            | 112 | 14             | 92 | 10             | M6                  | 4.82 × 10 <sup>-6</sup>                                       | 7.63              | 14.66                 | 1340  |

Note) The Model WGF can be equipped with a brush seal depending on the model number. Contact THK if you would like to use one.

The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

# BNT No Preload


|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------------------|
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |                       |
| BNT 1404-3.6 | 14                              | 4          | 14.4                                 | 11.5                        | 1×3.65                                 | 6.8               | 12.6                  | 190                   |
| BNT 1405-2.6 | 14                              | 5          | 14.5                                 | 11.2                        | 1×2.65                                 | 7.2               | 12.6                  | 150                   |
| BNT 1605-2.6 | 16                              | 5          | 16.75                                | 13.5                        | 1×2.65                                 | 7.8               | 14.7                  | 170                   |
| BNT 1808-3.6 | 18                              | 8          | 19.3                                 | 14.4                        | 1×3.65                                 | 18.2              | 34.4                  | 270                   |
| BNT 2005-2.6 | 20                              | 5          | 20.5                                 | 17.2                        | 1×2.65                                 | 8.7               | 18.3                  | 200                   |
| BNT 2010-2.6 | 20                              | 10         | 21.25                                | 16.4                        | 1×2.65                                 | 14.7              | 27.8                  | 220                   |
| BNT 2505-2.6 | 25                              | 5          | 25.5                                 | 22.2                        | 1×2.65                                 | 9.6               | 23                    | 240                   |
| BNT 2510-5.3 | 25                              | 10         | 26.8                                 | 20.2                        | 2×2.65                                 | 43.4              | 92.8                  | 520                   |
| BNT 2806-2.6 | 28                              | 6          | 28.5                                 | 25.2                        | 1×2.65                                 | 10.1              | 25.8                  | 270                   |
| BNT 2806-5.3 | 28                              | 6          | 28.5                                 | 25.2                        | 2×2.65                                 | 18.3              | 51.6                  | 510                   |
| BNT 3210-2.6 | 32                              | 10         | 33.75                                | 27.2                        | 1×2.65                                 | 27.3              | 59.5                  | 330                   |
| BNT 3210-5.3 | 32                              | 10         | 33.75                                | 27.2                        | 2×2.65                                 | 49.6              | 118.9                 | 640                   |
| BNT 3610-2.6 | 36                              | 10         | 37                                   | 30.5                        | 1×2.65                                 | 28.7              | 65.6                  | 360                   |
| BNT 3610-5.3 | 36                              | 10         | 37                                   | 30.5                        | 2×2.65                                 | 52.1              | 131.2                 | 700                   |
| BNT 4512-5.3 | 45                              | 12         | 46.5                                 | 39.2                        | 2×2.65                                 | 68.1              | 186.7                 | 860                   |



## Positioning Ball Screw







Unit: mm

|     | Nut dimensions |                    |                                  |               |        |     |                |      |    |                |                | Screw shaft inertial moment/mm <sup>3</sup> | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |                       |
|-----|----------------|--------------------|----------------------------------|---------------|--------|-----|----------------|------|----|----------------|----------------|---|----------------|--------------------|---|-----------------------|
|     | Width<br>W     | Center height<br>F | Overall length<br>L <sub>1</sub> | Mounting hole |        |     | W <sub>1</sub> | T    | M  | N <sub>1</sub> | N <sub>2</sub> |   |                |                    |   | Lubrication hole<br>A |
|     |                |                    |                                  | B             | C      | S×ℓ |                |      |    |                |                |   |                |                    |   |                       |
| 34  | 13             | 35                 | 26                               | 22            | M4×7   | 17  | 6              | 30   | 6  | 2              | M6             | 2.96×10 <sup>-8</sup>                       | 0.15           | 0.93               | 4860  |                       |
| 34  | 13             | 35                 | 26                               | 22            | M4×7   | 17  | 6              | 31   | 6  | 2              | M6             | 2.96×10 <sup>-8</sup>                       | 0.15           | 0.92               | 4820  |                       |
| 42  | 16             | 36                 | 32                               | 22            | M5×8   | 21  | 21.5           | 32.5 | 6  | 2              | M6             | 5.05×10 <sup>-8</sup>                       | 0.3            | 1.24               | 4170  |                       |
| 48  | 17             | 56                 | 35                               | 35            | M6×10  | 24  | 10             | 44   | 8  | 3              | M6             | 8.09×10 <sup>-8</sup>                       | 0.47           | 1.46               | 3620  |                       |
| 48  | 17             | 35                 | 35                               | 22            | M6×10  | 24  | 9              | 39   | 5  | 3              | M6             | 1.23×10 <sup>-7</sup>                       | 0.28           | 2.06               | 3410  |                       |
| 48  | 18             | 58                 | 35                               | 35            | M6×10  | 24  | 9              | 46   | 10 | 2              | M6             | 1.23×10 <sup>-7</sup>                       | 0.5            | 1.99               | 3290  |                       |
| 60  | 20             | 35                 | 40                               | 22            | M8×12  | 30  | 9.5            | 45   | 7  | 5              | M6             | 3.01×10 <sup>-7</sup>                       | 0.41           | 3.35               | 2740  |                       |
| 60  | 23             | 94                 | 40                               | 60            | M8×12  | 30  | 10             | 55   | 10 | —              | M6             | 3.01×10 <sup>-7</sup>                       | 1.18           | 2.79               | 2610  |                       |
| 60  | 22             | 42                 | 40                               | 18            | M8×12  | 30  | 10             | 50   | 8  | —              | M6             | 4.74×10 <sup>-7</sup>                       | 0.81           | 4.42               | 2450  |                       |
| 60  | 22             | 67                 | 40                               | 40            | M8×12  | 30  | 10             | 50   | 8  | —              | M6             | 4.74×10 <sup>-7</sup>                       | 0.78           | 4.42               | 2450  |                       |
| 70  | 26             | 64                 | 50                               | 45            | M8×12  | 35  | 12             | 62   | 10 | —              | M6             | 8.08×10 <sup>-7</sup>                       | 1.3            | 4.98               | 2070  |                       |
| 70  | 26             | 94                 | 50                               | 60            | M8×12  | 35  | 12             | 62   | 10 | —              | M6             | 8.08×10 <sup>-7</sup>                       | 2              | 4.98               | 2070  |                       |
| 86  | 29             | 64                 | 60                               | 45            | M10×16 | 43  | 17             | 67   | 11 | —              | M6             | 1.29×10 <sup>-6</sup>                       | 1.8            | 6.54               | 1890  |                       |
| 86  | 29             | 96                 | 60                               | 60            | M10×16 | 43  | 17             | 67   | 11 | —              | M6             | 1.29×10 <sup>-6</sup>                       | 2.4            | 6.54               | 1890  |                       |
| 100 | 36             | 115                | 75                               | 75            | M12×20 | 50  | 20.5           | 80   | 13 | —              | M6             | 3.16×10 <sup>-6</sup>                       | 4.1            | 10.56              | 1500  |                       |

Note) The Model BNT can be equipped with a brush seal depending on the model number. Contact THK if you would like to use one.

The overall length of the nut will increase when equipping the QZ lubricating device. See [A15-344](#) for further details.

# High-Thrust Ball Screw

| Series      | Type            |   | Features              |  |
|-------------|-----------------|---|-----------------------|--|
| High-Thrust | HBN-V           |  | High load             |  |
|             | HBN-K<br>HBN-KA |  | High load             |  |
|             | HBN             |  | High load             |  |
|             | SBKH            |  | High load, large lead |  |

## High-Thrust Ball Screw

|  | Caged ball | Compact nut | Miniature | High load capacity | Offset Preload | DN Value | Shaft diameter (mm) | Lead (mm) | Page No.       |
|--|------------|-------------|-----------|--------------------|----------------|----------|---------------------|-----------|----------------|
|  | ✓          |             |           | ✓                  |                | 160000   | 50 to 80            | 10 to 25  | <b>A15-224</b> |
|  | ✓          |             |           | ✓                  |                | 120000   | 63 to 140           | 16 to 50  | <b>A15-226</b> |
|  | ✓          |             |           | ✓                  |                | 130000   | 32 to 63            | 10 to 20  | <b>A15-232</b> |
|  | ✓          |             |           | ✓                  |                | 130000   | 63 to 120           | 32 to 60  | <b>A15-234</b> |

## Standard combinations of outer diameters and leads of the screw shafts

| Shaft diameter | Lead |   |   |              |              |                 |                 |  |
|----------------|------|---|---|--------------|--------------|-----------------|-----------------|--|
|                | 4    | 5 | 6 | 10           | 12           | 16              | 20              |  |
| 32             |      |   |   | HBN          |              |                 |                 |  |
| 36             |      |   |   | HBN          | HBN          |                 |                 |  |
| 40             |      |   |   | HBN          | HBN          |                 |                 |  |
| 50             |      |   |   | HBN-V<br>HBN | HBN-V<br>HBN | HBN-V<br>HBN    |                 |  |
| 63             |      |   |   |              |              | HBN-V<br>HBN    | HBN-V<br>HBN    |  |
| 80             |      |   |   |              |              | HBN-V           | HBN-V           |  |
| 100            |      |   |   |              |              | HBN-K<br>HBN-KA | HBN-K<br>HBN-KA |  |
| 120            |      |   |   |              |              |                 | HBN-K<br>HBN-KA |  |
| 140            |      |   |   |              |              |                 |                 |  |

## High-Thrust Ball Screw

Unit: mm


| Lead |                 |    |                 |       |    |                 |       |                         |      |
|------|-----------------|----|-----------------|-------|----|-----------------|-------|-------------------------|------|
|      | 25              | 30 | 32              | 35    | 36 | 40              | 42    | 50                      | 60   |
|      |                 |    |                 |       |    |                 |       |                         |      |
|      |                 |    |                 |       |    |                 |       |                         |      |
|      |                 |    |                 |       |    |                 |       |                         |      |
|      |                 |    |                 |       |    |                 |       |                         |      |
|      | HBN-V           |    | SBKH            | HBN-K |    | SBKH            | HBN-K | HBN-K                   |      |
|      | HBN-V           |    |                 |       |    | HBN-K<br>HBN-KA |       | HBN-K<br>HBN-KA<br>SBKH | SBKH |
|      | HBN-K<br>HBN-KA |    |                 |       |    |                 |       | SBKH                    | SBKH |
|      | HBN-K<br>HBN-KA |    |                 |       |    |                 |       |                         | SBKH |
|      | HBN-K<br>HBN-KA |    | HBN-K<br>HBN-KA |       |    | HBN-K<br>HBN-KA |       |                         |      |

Ball Screw


## Examples of Assembling Models HBN-V, HBN-K, HBN-KA, HBN, and SBKH

If using models HBN-V, HBN-K, HBN-KA, HBN, or SBKH under a large load, arrange the nut flange and the fixed-side support unit in relation to the loading direction as indicated in the figures below while taking into account the load balance of the balls. In addition, be sure not to apply a tensile load to the bolts while the unit is operating. If you intend to use this product in configurations other than those below, contact THK.

### Example Assembly of Models HBN-V, HBN-K, HBN-KA, HBN, and SBKH (Recommended)



### Example Assembly of Models HBN-V, HBN-K, HBN-KA, HBN, and SBKH (Not Recommended)






# HBN-V

## No Preload

|          |        |
|----------|--------|
| DN value | 160000 |
|----------|--------|



| Model No.     | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Permissible load*<br>F <sub>P</sub><br>kN | Rigidity<br>K<br>N/μm |
|---------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|---|-----------------------|
|               |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |   |                       |
|               |                                 |            |                                      |                             |  |                   |                       | F <sub>P</sub><br>kN                      | K<br>N/μm             |
| HBN5010V-7.5  | 50                              | 10         | 52                                   | 44                          | 3×2.5                                  | 189               | 506                   | 71  | 1977                  |
| HBN5012V-7.5  | 50                              | 12         | 52.4                                 | 43.2                        | 3×2.5                                  | 250               | 624                   | 87  | 2056                  |
| HBN5016V-7.5  | 50                              | 16         | 53                                   | 39.6                        | 3×2.5                                  | 410               | 902                   | 126                                       | 2516                  |
| HBN6316V-7.5  | 63                              | 16         | 66                                   | 52.6                        | 3×2.5                                  | 459               | 1134                  | 159                                       | 3010                  |
| HBN6316V-10.5 | 63                              | 16         | 66                                   | 52.6                        | 3×3.5                                  | 598               | 1544                  | 216                                       | 4040                  |
| HBN6320V-7.5  | 63                              | 20         | 66.5                                 | 49.8                        | 3×2.5                                  | 613               | 1410                  | 197                                       | 3098                  |
| HBN6325V-10.5 | 63                              | 25         | 66.5                                 | 49.8                        | 3×3.5                                  | 797               | 1920                  | 269                                       | 4154                  |
| HBN8016V-7.5  | 80                              | 16         | 83                                   | 70.2                        | 3×2.5                                  | 510               | 1440                  | 202                                       | 3626                  |
| HBN8016V-10.5 | 80                              | 16         | 83                                   | 70.2                        | 3×3.5                                  | 668               | 1970                  | 276                                       | 4888                  |
| HBN8020V-7.5  | 80                              | 20         | 83.5                                 | 66.8                        | 3×2.5                                  | 688               | 1787                  | 250                                       | 3730                  |
| HBN8020V-10.5 | 80                              | 20         | 83.5                                 | 66.8                        | 3×3.5                                  | 899               | 2442                  | 342                                       | 5022                  |
| HBN8025V-7.5  | 80                              | 25         | 84                                   | 63.6                        | 3×2.5                                  | 872               | 2135                  | 299                                       | 3819                  |
| HBN8025V-10.5 | 80                              | 25         | 84                                   | 63.6                        | 3×3.5                                  | 1139              | 2912                  | 408                                       | 5133                  |

Note 1) The permissible load F<sub>P</sub>\* indicates the maximum axial load that the Ball Screw can receive.

This model is capable of achieving a longer service life than the conventional Ball Screw under a high load.

Note 2) Certain precautions are necessary regarding the assembly method. (See [A15-222](#).)

Note 3) For high-load ball screws, the standard maximum length of the screw shaft is 3000 mm. For lengths greater than this, please contact THK.

Axial Clearance

Unit: mm

|                  |           |
|------------------|-----------|
| Clearance symbol | G2        |
| Axial Clearance  | 0 to 0.02 |

### Model number coding

**HBN6320V-7.5 RR G2 +1400L C7**

Model number

Seal symbol (\*1)

Accuracy symbol (\*2)

Overall screw shaft length (in mm)

Symbol for clearance in the axial direction


(For the axial clearance, this model has clearance G2 as standard.)

Other clearance is also available at your request. Contact THK for details.)

(\*1) See [A15-334](#). (\*2) See [A15-12](#).



## High-Thrust Ball Screw



Unit: mm

| Nut dimensions |                 |                |    |     |                |      |     |                  |                  |                  |                  |                       | Screw shaft inertial moment/mm | Nut mass | Shaft mass        | Permissible rotational speed |
|----------------|-----------------|----------------|----|-----|----------------|------|-----|------------------|------------------|------------------|------------------|-----------------------|--------------------------------|----------|-------------------|------------------------------|
| Outer diameter | Flange diameter | Overall length | H  | PCD | d <sub>i</sub> | T1   | T2  | U <sub>MAX</sub> | V <sub>MAX</sub> | R <sub>MAX</sub> | Lubrication hole |                       |                                |          |                   |                              |
| D              | D <sub>1</sub>  | L <sub>1</sub> | H  | PCD | d <sub>i</sub> | T1   | T2  | U <sub>MAX</sub> | V <sub>MAX</sub> | R <sub>MAX</sub> | A                | kg·m <sup>2</sup> /mm | kg                             | kg/m     | min <sup>-1</sup> |                              |
| 75             | 109             | 143            | 18 | 92  | 9              | 31   | 30  | 50               | 48               | 52               | M6               | 4.82×10 <sup>-6</sup> | 3.0                            | 13.7     | 3070              |                              |
| 80             | 114             | 163            | 18 | 96  | 9              | 35   | 36  | 54               | 48               | 55               | M6               | 4.82×10 <sup>-6</sup> | 4.0                            | 13.4     | 3050              |                              |
| 95             | 129             | 213            | 28 | 112 | 9              | 43   | 48  | 64               | 48               | 65               | Rc1/8<br>(PT1/8) | 4.82×10 <sup>-6</sup> | 8.7                            | 12.1     | 3010              |                              |
| 105            | 139             | 213            | 28 | 122 | 9              | 43   | 48  | 71               | 57               | 71.5             |                  | 1.21×10 <sup>-5</sup> | 9.4                            | 20.2     | 2420              |                              |
| 105            | 139             | 261            | 28 | 122 | 9              | 59   | 64  | 71               | 57               | 71.5             |                  | 1.21×10 <sup>-5</sup> | 11.4                           | 20.2     | 2420              |                              |
| 117            | 157             | 257            | 32 | 137 | 11             | 51   | 60  | 78               | 57               | 79               |                  | 1.21×10 <sup>-5</sup> | 15.5                           | 19.1     | 2400              |                              |
| 117            | 157             | 377            | 32 | 137 | 11             | 83.5 | 100 | 78               | 57               | 79               |                  | 1.21×10 <sup>-5</sup> | 22.4                           | 25.2     | 2400              |                              |
| 120            | 154             | 219            | 32 | 137 | 9              | 43   | 48  | 79               | 70               | 80               |                  | 3.16×10 <sup>-5</sup> | 10.9                           | 33.9     | 1920              |                              |
| 120            | 154             | 267            | 32 | 137 | 9              | 59   | 64  | 79               | 70               | 80               |                  | 3.16×10 <sup>-5</sup> | 13.2                           | 33.9     | 1920              |                              |
| 130            | 170             | 257            | 32 | 150 | 11             | 50   | 60  | 86               | 69               | 87               |                  | 3.16×10 <sup>-5</sup> | 16.7                           | 32.5     | 1910              |                              |
| 130            | 170             | 317            | 32 | 150 | 11             | 70   | 80  | 86               | 69               | 87               |                  | 3.16×10 <sup>-5</sup> | 20.5                           | 32.5     | 1910              |                              |
| 145            | 185             | 315            | 40 | 165 | 11             | 60   | 75  | 95               | 68               | 95               |                  | 3.16×10 <sup>-5</sup> | 27.9                           | 31.4     | 1900              |                              |
| 145            | 185             | 391            | 40 | 165 | 11             | 85.5 | 100 | 95               | 69               | 96               |                  | 3.16×10 <sup>-5</sup> | 34.4                           | 31.4     | 1900              |                              |

Note) The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.


If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>ax</sub>) is obtained from the following equation.

$$K_{ax} = K \left( \frac{Fa}{0.3Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# HBN-K and HBN-KA No Preload

|          |        |
|----------|--------|
| DN value | 120000 |
|----------|--------|



Models HBN6335K to HBN8050K (two rows)

| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Threads | Basic load rating |                       | Permissible load*<br>F <sub>p</sub><br>kN | Rigidity<br>K<br>N/μm |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|---------|-------------------|-----------------------|---|-----------------------|
|              |                                 |            |                                      |                             |  |         | Ca<br>kN          | C <sub>0a</sub><br>kN |   |                       |
| HBN6335K-10  | 63                              | 35         | 66                                   | 52.6                        | 4 × 2.5                                | 2       | 548               | 1376                  | 169                                       | 3935                  |
| HBN6335K-15  | 63                              | 35         | 66                                   | 52.6                        | 6 × 2.5                                | 2       | 776               | 2064                  | 240                                       | 5791                  |
| HBN6342K-3   | 63                              | 42         | 66.5                                 | 49.6                        | 2 × 1.5                                | 2       | 259               | 526                   | 80  | 1289                  |
| HBN6350K-10  | 63                              | 50         | 66.5                                 | 49.6                        | 4 × 2.5                                | 2       | 719               | 1723                  | 222                                       | 4011                  |
| HBN8040K-5   | 80                              | 40         | 83.5                                 | 66.6                        | 2 × 2.5                                | 2       | 451               | 1105                  | 154                                       | 2503                  |
| HBN8040KA-5  | 80                              | 40         | 83.5                                 | 66.6                        | 2 × 2.5                                | 2       | 451               | 1105                  | 154                                       | 2503                  |
| HBN8050K-15  | 80                              | 50         | 83.5                                 | 66.6                        | 6 × 2.5                                | 2       | 1171              | 3376                  | 472                                       | 7270                  |
| HBN8050KA-15 | 80                              | 50         | 83.5                                 | 66.6                        | 6 × 2.5                                | 2       | 1171              | 3376                  | 472                                       | 7270                  |

Note 1) The permissible load F<sub>p</sub>\* indicates the maximum axial load that the Ball Screw can receive.

This model is capable of achieving a longer service life than the conventional Ball Screw under a high load.

Note 2) Certain precautions are necessary regarding the assembly method. (See [A15-222](#).)

Note 3) For high-load ball screws, the standard maximum length of the screw shaft is 3000 mm. For lengths greater than this, please contact THK.

Axial Clearance

Unit: mm

|                  |           |
|------------------|-----------|
| Clearance symbol | G2        |
| Axial Clearance  | 0 to 0.02 |

## Model number coding

**HBN6335K-10 RR G2 +1200L C7**

Model number

Seal symbol (\*1)

Accuracy symbol (\*2)

Overall screw shaft length (in mm)


Symbol for clearance in the axial direction

(For the axial clearance, this model has clearance G2 as standard.)

Other clearance is also available at your request. Contact THK for details.)

(\*1) See [A15-334](#). (\*2) See [A15-12](#).

## High-Thrust Ball Screw



Models HBN8040KA and HBN8050KA (two rows)

Unit: mm

| Nut dimensions      |                                   |                                  |    |     |                |      |     |                  |                  |                  |                       | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass | Shaft mass | Permissible rotational speed |
|---------------------|-----------------------------------|----------------------------------|----|-----|----------------|------|-----|------------------|------------------|------------------|-----------------------|---|----------|------------|------------------------------|
| Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | PCD | d <sub>1</sub> | T1   | T2  | U <sub>MAX</sub> | V <sub>MAX</sub> | R <sub>MAX</sub> | Lubrication hole<br>A |   |          |            |                              |
| 105                 | 139                               | 271                              | 28 | 122 | 9              | 72.5 | 105 | 70.5             | 82               | 73               | Rc1/8<br>(PT1/8)      | $1.21 \times 10^{-5}$                       | 10.5     | 24         | 1810                         |
| 105                 | 139                               | 376                              | 28 | 122 | 9              | 72.5 | 105 | 70.5             | 82               | 73               |                       | $1.21 \times 10^{-5}$                       | 14.5     | 24         | 1810                         |
| 117                 | 157                               | 156                              | 32 | 137 | 11             | 39.5 | —   | 79               | 84               | 80               |                       | $1.21 \times 10^{-5}$                       | 8.3      | 24         | 1800                         |
| 117                 | 157                               | 358                              | 32 | 137 | 11             | 94   | 150 | 78.5             | 84               | 80               |                       | $1.21 \times 10^{-5}$                       | 19.2     | 24         | 1800                         |
| 134                 | 174                               | 185                              | 32 | 154 | 11             | 81   | —   | 88               | 102              | 93               |                       | $3.16 \times 10^{-5}$                       | 11       | 39         | 1430                         |
| 130                 | 174                               | 185                              | 32 | 154 | 11             | 81   | —   | 88               | 102              | 93               |                       | $3.16 \times 10^{-5}$                       | 10.2     | 39         | 1430                         |
| 134                 | 174                               | 519                              | 32 | 154 | 11             | 92   | 150 | 89               | 101              | 90               |                       | $3.16 \times 10^{-5}$                       | 31.9     | 39         | 1430                         |
| 130                 | 174                               | 519                              | 32 | 154 | 11             | 92   | 150 | 89               | 102              | 90               |                       | $3.16 \times 10^{-5}$                       | 29.2     | 39         | 1430                         |

Note) The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.



If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>N</sub>) is obtained from the following equation.

$$K_N = K \left( \frac{F_a}{0.3Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# HBN-K and HBN-KA No Preload

|          |        |
|----------|--------|
| DN value | 120000 |
|----------|--------|



Models HBN10016K to 10025K

| Model No.       | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X Turns | Threads | Basic load rating |                       | Permissible load*<br>F <sub>p</sub><br>kN | Rigidity<br>K<br>N/μm |
|-----------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|---------|-------------------|-----------------------|---|-----------------------|
|                 |                                 |            |                                      |                             |  |         | Ca<br>kN          | C <sub>0a</sub><br>kN |   |                       |
| HBN10016K-10    | 100                             | 16         | 103                                  | 89.6                        | 4×2.5                                  | 1       | 673               | 2244                  | 314                                       | 5619                  |
| HBN10016KA-10   | 100                             | 16         | 103                                  | 89.6                        | 4×2.5                                  | 1       | 673               | 2244                  | 314                                       | 5619                  |
| HBN10020K-7.5   | 100                             | 20         | 103.5                                | 86.6                        | 3×2.5                                  | 1       | 717               | 2107                  | 295                                       | 4432                  |
| HBN10020KA-7.5  | 100                             | 20         | 103.5                                | 86.6                        | 3×2.5                                  | 1       | 717               | 2107                  | 295                                       | 4432                  |
| HBN10020K-10    | 100                             | 20         | 103.5                                | 86.6                        | 4×2.5                                  | 1       | 919               | 2810                  | 393                                       | 5830                  |
| HBN10020KA-10   | 100                             | 20         | 103.5                                | 86.6                        | 4×2.5                                  | 1       | 919               | 2810                  | 393                                       | 5830                  |
| HBN10020K-12.5  | 100                             | 20         | 103.5                                | 86.6                        | 5×2.5                                  | 1       | 1114              | 3512                  | 491                                       | 7212                  |
| HBN10020KA-12.5 | 100                             | 20         | 103.5                                | 86.6                        | 5×2.5                                  | 1       | 1114              | 3512                  | 491                                       | 7212                  |
| HBN10020K-7     | 100                             | 20         | 103.5                                | 86.6                        | 2×3.5                                  | 1       | 674               | 1956                  | 273                                       | 4129                  |
| HBN10020KA-7    | 100                             | 20         | 103.5                                | 86.6                        | 2×3.5                                  | 1       | 674               | 1956                  | 273                                       | 4129                  |
| HBN10020K-10.5  | 100                             | 20         | 103.5                                | 86.6                        | 3×3.5                                  | 1       | 955               | 2934                  | 410                                       | 6077                  |
| HBN10020KA-10.5 | 100                             | 20         | 103.5                                | 86.6                        | 3×3.5                                  | 1       | 955               | 2934                  | 410                                       | 6077                  |
| HBN10025K-7.5   | 100                             | 25         | 104                                  | 83.6                        | 3×2.5                                  | 1       | 921               | 2532                  | 354                                       | 4565                  |
| HBN10025KA-7.5  | 100                             | 25         | 104                                  | 83.6                        | 3×2.5                                  | 1       | 921               | 2532                  | 354                                       | 4565                  |
| HBN10025K-10    | 100                             | 25         | 104                                  | 83.6                        | 4×2.5                                  | 1       | 1180              | 3376                  | 472                                       | 6005                  |
| HBN10025KA-10   | 100                             | 25         | 104                                  | 83.6                        | 4×2.5                                  | 1       | 1180              | 3376                  | 472                                       | 6005                  |
| HBN10025K-12.5  | 100                             | 25         | 104                                  | 83.6                        | 5×2.5                                  | 1       | 1429              | 4220                  | 590                                       | 7429                  |
| HBN10025KA-12.5 | 100                             | 25         | 104                                  | 83.6                        | 5×2.5                                  | 1       | 1429              | 4220                  | 590                                       | 7429                  |
| HBN10025K-7     | 100                             | 25         | 104                                  | 83.6                        | 2×3.5                                  | 1       | 866               | 2355                  | 329                                       | 4261                  |
| HBN10025KA-7    | 100                             | 25         | 104                                  | 83.6                        | 2×3.5                                  | 1       | 866               | 2355                  | 329                                       | 4261                  |
| HBN10025K-10.5  | 100                             | 25         | 104                                  | 83.6                        | 3×3.5                                  | 1       | 1227              | 3533                  | 494                                       | 6273                  |
| HBN10025KA-10.5 | 100                             | 25         | 104                                  | 83.6                        | 3×3.5                                  | 1       | 1227              | 3533                  | 494                                       | 6273                  |
| HBN10025K-14    | 100                             | 25         | 104                                  | 83.6                        | 4×3.5                                  | 1       | 1572              | 4711                  | 659                                       | 8252                  |
| HBN10025KA-14   | 100                             | 25         | 104                                  | 83.6                        | 4×3.5                                  | 1       | 1572              | 4711                  | 659                                       | 8252                  |

Note 1) The permissible load F<sub>p</sub>\* indicates the maximum axial load that the Ball Screw can receive.

This model is capable of achieving a longer service life than the conventional Ball Screw under a high load.

Note 2) Certain precautions are necessary regarding the assembly method. (See [A15-222](#).)

Note 3) For high-load ball screws, the standard maximum length of the screw shaft is 3000 mm. For lengths greater than this, please contact THK.

Axial Clearance

Unit: mm

|                  |           |
|------------------|-----------|
| Clearance symbol | G2        |
| Axial Clearance  | 0 to 0.02 |

## Model number coding

# HBN10016K-10 RR G2 +1200L C7

Model number

Seal symbol (\*1)

Accuracy symbol (\*2)

Symbol for clearance in the axial direction


Overall screw shaft length (in mm)

(For the axial clearance, this model has clearance G2 as standard.)

Other clearance is also available at your request. Contact THK for details.)

(\*1) See [A15-334](#). (\*2) See [A15-12](#).

## High-Thrust Ball Screw



Models HBN10016KA to 10025KA

Unit: mm

| Nut dimensions      |                                   |                                  |    |     |                |                |                |                  |                  |                  |                       | Screw shaft inertial moment/mm <sup>4</sup> | Nut mass | Shaft mass | Permissible rotational speed |
|---------------------|-----------------------------------|----------------------------------|----|-----|----------------|----------------|----------------|------------------|------------------|------------------|-----------------------|---|----------|------------|------------------------------|
| Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | PCD | d <sub>1</sub> | T <sub>1</sub> | T <sub>2</sub> | U <sub>MAX</sub> | V <sub>MAX</sub> | R <sub>MAX</sub> | Lubrication hole A    |   |          |            |                              |
| 150                 | 190                               | 263                              | 32 | 170 | 11             | 37.5           | 48             | 92               | 119              | 98.5             | Rc1/8<br>(PT1/8)      | $7.71 \times 10^{-5}$                       | 18.1     | 61         | 1160                         |
| 145                 | 190                               | 263                              | 32 | 170 | 11             | 37.5           | 48             | 92               | 119              | 98.5             |                       | $7.71 \times 10^{-5}$                       | 16.3     | 61         | 1160                         |
| 154                 | 194                               | 252                              | 32 | 174 | 11             | 44             | 60             | 96               | 123              | 101              |                       | $7.71 \times 10^{-5}$                       | 18.9     | 61         | 1150                         |
| 145                 | 194                               | 252                              | 32 | 174 | 11             | 44             | 60             | 96               | 123              | 101              |                       | $7.71 \times 10^{-5}$                       | 15.6     | 61         | 1150                         |
| 154                 | 194                               | 312                              | 32 | 174 | 11             | 44             | 60             | 96               | 123              | 101              |                       | $7.71 \times 10^{-5}$                       | 23.4     | 61         | 1150                         |
| 145                 | 194                               | 312                              | 32 | 174 | 11             | 44             | 60             | 96               | 123              | 101              |                       | $7.71 \times 10^{-5}$                       | 19.2     | 61         | 1150                         |
| 154                 | 194                               | 372                              | 32 | 174 | 11             | 44             | 60             | 96               | 123              | 101              |                       | $7.71 \times 10^{-5}$                       | 27.9     | 61         | 1150                         |
| 145                 | 194                               | 372                              | 32 | 174 | 11             | 44             | 60             | 96               | 123              | 101              |                       | $7.71 \times 10^{-5}$                       | 22.8     | 61         | 1150                         |
| 154                 | 194                               | 232                              | 32 | 174 | 11             | 44             | 80             | 97               | 128              | 105              |                       | $7.71 \times 10^{-5}$                       | 23.4     | 61         | 1150                         |
| 145                 | 194                               | 232                              | 32 | 174 | 11             | 44             | 80             | 97               | 128              | 105              |                       | $7.71 \times 10^{-5}$                       | 20.5     | 61         | 1150                         |
| 154                 | 194                               | 312                              | 32 | 174 | 11             | 44             | 80             | 97               | 128              | 105              |                       | $7.71 \times 10^{-5}$                       | 29.4     | 61         | 1150                         |
| 145                 | 194                               | 312                              | 32 | 174 | 11             | 44             | 80             | 97               | 128              | 105              |                       | $7.71 \times 10^{-5}$                       | 25.3     | 61         | 1150                         |
| 167                 | 207                               | 322                              | 40 | 187 | 11             | 55.5           | 75             | 105              | 127              | 109.5            |                       | $7.71 \times 10^{-5}$                       | 32       | 61         | 1150                         |
| 159                 | 207                               | 322                              | 40 | 187 | 11             | 55.5           | 75             | 105              | 127              | 109.5            |                       | $7.71 \times 10^{-5}$                       | 28.2     | 61         | 1150                         |
| 167                 | 207                               | 397                              | 40 | 187 | 11             | 55.5           | 75             | 105              | 127              | 109.5            |                       | $7.71 \times 10^{-5}$                       | 39.4     | 61         | 1150                         |
| 159                 | 207                               | 397                              | 40 | 187 | 11             | 55.5           | 75             | 105              | 127              | 109.5            |                       | $7.71 \times 10^{-5}$                       | 34.5     | 61         | 1150                         |
| 167                 | 207                               | 472                              | 40 | 187 | 11             | 55.5           | 75             | 105              | 127              | 109.5            |                       | $7.71 \times 10^{-5}$                       | 46.9     | 61         | 1150                         |
| 159                 | 207                               | 472                              | 40 | 187 | 11             | 55.5           | 75             | 105              | 127              | 109.5            |                       | $7.71 \times 10^{-5}$                       | 41       | 61         | 1150                         |
| 167                 | 207                               | 297                              | 40 | 187 | 11             | 55.5           | 100            | 105              | 127              | 109.5            |                       | $7.71 \times 10^{-5}$                       | 29.5     | 61         | 1150                         |
| 159                 | 207                               | 297                              | 40 | 187 | 11             | 55.5           | 100            | 105              | 127              | 109.5            |                       | $7.71 \times 10^{-5}$                       | 26.3     | 61         | 1150                         |
| 167                 | 207                               | 397                              | 40 | 187 | 11             | 55.5           | 100            | 105              | 127              | 109.5            | $7.71 \times 10^{-5}$ | 39.4  | 61       | 1150       |                              |
| 159                 | 207                               | 397                              | 40 | 187 | 11             | 55.5           | 100            | 105              | 127              | 109.5            | $7.71 \times 10^{-5}$ | 34.8  | 61       | 1150       |                              |
| 167                 | 207                               | 497                              | 40 | 187 | 11             | 55.5           | 100            | 105              | 127              | 109.5            | $7.71 \times 10^{-5}$ | 49.3  | 61       | 1150       |                              |
| 159                 | 207                               | 497                              | 40 | 187 | 11             | 55.5           | 100            | 105              | 127              | 109.5            | $7.71 \times 10^{-5}$ | 43.3  | 61       | 1150       |                              |

Note) The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).



These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.

If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>N</sub>) is obtained from the following equation.

$$K_N = K \left( \frac{F_a}{0.3C_a} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# HBN-K and HBN-KA No Preload



Models HBN12020K to 14040K

| Model No.       | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Threads | Basic load rating |                       | Permissible load*<br>F <sub>P</sub><br>kN | Rigidity<br>K<br>N/μm |
|-----------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|---------|-------------------|-----------------------|---|-----------------------|
|                 |                                 |            |                                      |                             |  |         | Ca<br>kN          | C <sub>0a</sub><br>kN |   |                       |
| HBN12020K-10    | 120                             | 20         | 123.5                                | 106.6                       | 4×2.5                                  | 1       | 995               | 3389                  | 474                                       | 6746                  |
| HBN12020KA-10   | 120                             | 20         | 123.5                                | 106.6                       | 4×2.5                                  | 1       | 995               | 3389                  | 474                                       | 6746                  |
| HBN12025K-7.5   | 120                             | 25         | 124                                  | 103.6                       | 3×2.5                                  | 1       | 996               | 3034                  | 424                                       | 5254                  |
| HBN12025KA-7.5  | 120                             | 25         | 124                                  | 103.6                       | 3×2.5                                  | 1       | 996               | 3034                  | 424                                       | 5254                  |
| HBN12025K-10    | 120                             | 25         | 124                                  | 103.6                       | 4×2.5                                  | 1       | 1276              | 4045                  | 566                                       | 6912                  |
| HBN12025KA-10   | 120                             | 25         | 124                                  | 103.6                       | 4×2.5                                  | 1       | 1276              | 4045                  | 566                                       | 6912                  |
| HBN12025K-12.5  | 120                             | 25         | 124                                  | 103.6                       | 5×2.5                                  | 1       | 1546              | 5057                  | 708                                       | 8550                  |
| HBN12025KA-12.5 | 120                             | 25         | 124                                  | 103.6                       | 5×2.5                                  | 1       | 1546              | 5057                  | 708                                       | 8550                  |
| HBN12025K-14    | 120                             | 25         | 124                                  | 103.6                       | 4×3.5                                  | 1       | 1698              | 5632                  | 788                                       | 9479                  |
| HBN12025KA-14   | 120                             | 25         | 124                                  | 103.6                       | 4×3.5                                  | 1       | 1698              | 5632                  | 788                                       | 9479                  |
| HBN14025K-10    | 140                             | 25         | 144                                  | 123.6                       | 4×2.5                                  | 1       | 1360              | 4714                  | 660                                       | 7781                  |
| HBN14025KA-10   | 140                             | 25         | 144                                  | 123.6                       | 4×2.5                                  | 1       | 1360              | 4714                  | 660                                       | 7781                  |
| HBN14032K-10.5  | 140                             | 32         | 145                                  | 119.6                       | 3×3.5                                  | 1       | 2089              | 6510                  | 911                                       | 7997                  |
| HBN14032KA-10.5 | 140                             | 32         | 145                                  | 119.6                       | 3×3.5                                  | 1       | 2089              | 6510                  | 911                                       | 7997                  |
| HBN14040K-7.5   | 140                             | 40         | 144                                  | 123.6                       | 3×2.5                                  | 1       | 1058              | 3527                  | 493                                       | 5909                  |
| HBN14040KA-7.5  | 140                             | 40         | 144                                  | 123.6                       | 3×2.5                                  | 1       | 1058              | 3527                  | 493                                       | 5909                  |

Note 1) The permissible load F<sub>P</sub>\* indicates the maximum axial load that the Ball Screw can receive.

This model is capable of achieving a longer service life than the conventional Ball Screw under a high load.

Note 2) Certain precautions are necessary regarding the assembly method. (See [A15-222](#).)

Note 3) For high-load ball screws, the standard maximum length of the screw shaft is 3000 mm. For lengths greater than this, please contact THK.

Axial Clearance

Unit: mm

|                  |           |
|------------------|-----------|
| Clearance symbol | G2        |
| Axial Clearance  | 0 to 0.02 |

## Model number coding

### HBN12025K-10 RR G2 +1200L C7

Model number

Seal symbol (\*1)

Accuracy symbol (\*2)

Overall screw shaft length (in mm)


Symbol for clearance in the axial direction

(For the axial clearance, this model has clearance G2 as standard.)

Other clearance is also available at your request. Contact THK for details.)

(\*1) See [A15-334](#). (\*2) See [A15-12](#).

## High-Thrust Ball Screw



Models HBN12020KA to 14040KA

Unit: mm

| Nut dimensions      |                                   |                                  |    |     |                |                |                |                   |                   |                   |                       | Screw shaft inertial moment/mm <sup>4</sup> | Nut mass | Shaft mass | Permissible rotational speed |
|---------------------|-----------------------------------|----------------------------------|----|-----|----------------|----------------|----------------|-------------------|-------------------|-------------------|-----------------------|---|----------|------------|------------------------------|
| Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | PCD | d <sub>1</sub> | T <sub>1</sub> | T <sub>2</sub> | U <sub>MAX.</sub> | V <sub>MAX.</sub> | R <sub>MAX.</sub> | Lubrication hole<br>A |   |          |            |                              |
| 190                 | 230                               | 322                              | 40 | 210 | 11             | 46             | 60             | 110               | 142               | 117               | Rc1/8<br>(PT1/8)      | $1.59 \times 10^{-4}$                       | 38.1     | 88         | 970                          |
| 173                 | 230                               | 322                              | 40 | 210 | 11             | 46             | 60             | 110               | 143               | 117               |                       | $1.59 \times 10^{-4}$                       | 28.7     | 88         | 970                          |
| 195                 | 235                               | 322                              | 40 | 215 | 11             | 54.5           | 75             | 115               | 147               | 122               |                       | $1.59 \times 10^{-4}$                       | 42.6     | 88         | 960                          |
| 173                 | 235                               | 322                              | 40 | 215 | 11             | 54.5           | 75             | 115               | 147               | 122               |                       | $1.59 \times 10^{-4}$                       | 30.2     | 88         | 960                          |
| 195                 | 235                               | 397                              | 40 | 215 | 11             | 54.5           | 75             | 115               | 147               | 122               |                       | $1.59 \times 10^{-4}$                       | 52.6     | 88         | 960                          |
| 173                 | 235                               | 397                              | 40 | 215 | 11             | 54.5           | 75             | 115               | 147               | 122               |                       | $1.59 \times 10^{-4}$                       | 36.9     | 88         | 960                          |
| 195                 | 235                               | 472                              | 40 | 215 | 11             | 54.5           | 75             | 115               | 147               | 122               |                       | $1.59 \times 10^{-4}$                       | 62.5     | 88         | 960                          |
| 173                 | 235                               | 472                              | 40 | 215 | 11             | 54.5           | 75             | 115               | 147               | 122               |                       | $1.59 \times 10^{-4}$                       | 43.5     | 88         | 960                          |
| 195                 | 235                               | 497                              | 40 | 215 | 11             | 54.5           | 100            | 115               | 147               | 122               |                       | $1.59 \times 10^{-4}$                       | 65.8     | 88         | 960                          |
| 173                 | 235                               | 497                              | 40 | 215 | 11             | 54.5           | 100            | 115               | 147               | 122               |                       | $1.59 \times 10^{-4}$                       | 45.8     | 88         | 960                          |
| 230                 | 290                               | 397                              | 40 | 260 | 18             | 54.5           | 75             | 140               | 175               | 148               |                       | $2.96 \times 10^{-4}$                       | 77.6     | 120        | 830                          |
| 204                 | 290                               | 397                              | 40 | 260 | 18             | 54.5           | 75             | 140               | 175               | 148               |                       | $2.96 \times 10^{-4}$                       | 54.1     | 120        | 830                          |
| 230                 | 290                               | 480                              | 40 | 260 | 18             | 67             | 128            | 147               | 175               | 154               |                       | $2.96 \times 10^{-4}$                       | 96.8     | 120        | 820                          |
| 222                 | 290                               | 480                              | 40 | 260 | 18             | 67             | 128            | 147               | 175               | 154               |                       | $2.96 \times 10^{-4}$                       | 89.2     | 120        | 820                          |
| 230                 | 290                               | 470                              | 40 | 260 | 18             | 95             | 120            | 140               | 170               | 140               |                       | $2.96 \times 10^{-4}$                       | 88.2     | 120        | 830                          |
| 204                 | 290                               | 470                              | 40 | 260 | 18             | 95             | 120            | 140               | 170               | 140               |                       | $2.96 \times 10^{-4}$                       | 59.9     | 120        | 830                          |

Note) The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.


If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>N</sub>) is obtained from the following equation.

$$K_N = K \left( \frac{F_a}{0.3C_a} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# HBN No Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



Models HBN3210 to 3612

| Model No.     | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                       | Permissible load*<br>F <sub>P</sub><br>kN | Rigidity<br>K<br>N/μm |
|---------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|---|-----------------------|
|               |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |   |                       |
| HBN 3210-5    | 32                              | 10         | 34                                   | 26                          | 2×2.5                                  | 102.9             | 191.3                 | 31.9                                      | 1077                  |
| HBN 3610-5    | 36                              | 10         | 38                                   | 30                          | 2×2.5                                  | 108.2             | 220.4                 | 33.5                                      | 1176                  |
| HBN 3612-5    | 36                              | 12         | 38.4                                 | 29                          | 2×2.5                                  | 141.1             | 267.7                 | 43.7                                      | 1207                  |
| HBN 4010-7.5  | 40                              | 10         | 42                                   | 34                          | 3×2.5                                  | 162.6             | 366                   | 50.4                                      | 1910                  |
| HBN 4012-7.5  | 40                              | 12         | 42.4                                 | 33                          | 3×2.5                                  | 212.4             | 441.6                 | 65.8                                      | 1922                  |
| HBN 5010-7.5  | 50                              | 10         | 52                                   | 44                          | 3×2.5                                  | 179.1             | 462.7                 | 55.5                                      | 2279                  |
| HBN 5012-7.5  | 50                              | 12         | 52.4                                 | 43                          | 3×2.5                                  | 235.7             | 572.2                 | 73.1                                      | 2345                  |
| HBN 5016-7.5  | 50                              | 16         | 53                                   | 39.6                        | 3×2.5                                  | 379.6             | 820.9                 | 117.7                                     | 2392                  |
| HBN 6316-7.5  | 63                              | 16         | 66                                   | 52.6                        | 3×2.5                                  | 427.1             | 1043.8                | 132.4                                     | 2898                  |
| HBN 6316-10.5 | 63                              | 16         | 66                                   | 52.6                        | 3×3.5                                  | 577.1             | 1461.3                | 178.9                                     | 4029                  |
| HBN 6320-7.5  | 63                              | 20         | 66.5                                 | 49.6                        | 3×2.5                                  | 578.8             | 1283.1                | 179.4                                     | 3030                  |

Note 1) The permissible load F<sub>P</sub>\* indicates the maximum axial load that the Ball Screw can receive.

This model is capable of achieving a longer service life than the conventional Ball Screw under a high load.

Note 2) Certain precautions are necessary regarding the assembly method. (See [A15-222](#).)

Note 3) For high-load ball screws, the standard maximum length of the screw shaft is 3000 mm. For lengths greater than this, please contact THK.

Axial Clearance

Unit: mm

|                  |           |
|------------------|-----------|
| Clearance symbol | G2        |
| Axial Clearance  | 0 to 0.02 |

## Model number coding

### HBN3210-5 RR G2 +1200L C7

Model number

Seal symbol (\*1)

Accuracy symbol (\*2)

Overall screw shaft length (in mm)

Symbol for clearance in the axial direction


(For the axial clearance, this model has clearance G2 as standard.)

Other clearance is also available at your request. Contact THK for details.)

(\*1) See [A15-334](#). (\*2) See [A15-12](#).



## High-Thrust Ball Screw



Models HBN4010 to 6320

Unit: mm

|  | Nut dimensions |                 |                |    |     |                |      |    |                  |                  |                  |                  | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass | Shaft mass | Permissible rotational speed |
|--|----------------|-----------------|----------------|----|-----|----------------|------|----|------------------|------------------|------------------|------------------|---|----------|------------|------------------------------|
|  | Outer diameter | Flange diameter | Overall length | H  | PCD | d <sub>i</sub> | T1   | T2 | U <sub>MAX</sub> | V <sub>MAX</sub> | R <sub>MAX</sub> | Lubrication hole |   |          |            |                              |
|  | D              | D <sub>1</sub>  | L <sub>1</sub> |    |     |                |      |    |                  |                  |                  | A                | kg·m <sup>2</sup> /mm                       | kg       | kg/m       | min <sup>-1</sup>            |
|  | 58             | 85              | 98             | 15 | 71  | 6.6            | 22   | 30 | 43               | 46               | 43.5             | M6               | 8.08 × 10 <sup>-7</sup>                     | 1.8      | 5.26       | 3820                         |
|  | 62             | 89              | 98             | 15 | 75  | 6.6            | 22   | 30 | 45               | 50               | 46               | M6               | 1.29 × 10 <sup>-6</sup>                     | 1.9      | 6.79       | 3420                         |
|  | 66             | 100             | 116            | 18 | 82  | 9              | 26   | 36 | 49               | 52.5             | 50               | M6               | 1.29 × 10 <sup>-6</sup>                     | 2.8      | 6.55       | 3380                         |
|  | 66             | 100             | 135            | 18 | 82  | 9              | 23.5 | 30 | 46.5             | 54               | 48               | M6               | 1.97 × 10 <sup>-6</sup>                     | 2.9      | 8.52       | 3090                         |
|  | 70             | 104             | 152            | 18 | 86  | 9              | 26   | 36 | 51               | 56               | 52               | M6               | 1.97 × 10 <sup>-6</sup>                     | 3.7      | 5.24       | 3060                         |
|  | 78             | 112             | 135            | 18 | 94  | 9              | 23.5 | 30 | 52               | 63.5             | 54.5             | M6               | 4.82 × 10 <sup>-6</sup>                     | 3.7      | 13.7       | 2500                         |
|  | 80             | 114             | 152            | 18 | 96  | 9              | 26   | 36 | 56               | 66               | 58.5             | M6               | 4.82 × 10 <sup>-6</sup>                     | 4.4      | 13.34      | 2480                         |
|  | 95             | 135             | 211            | 28 | 113 | 9              | 37.5 | 48 | 64.5             | 69.6             | 65.2             | Rc1/8<br>(PT1/8) | 4.82 × 10 <sup>-6</sup>                     | 10.0     | 12.1       | 2450                         |
|  | 105            | 139             | 211            | 28 | 122 | 9              | 37.5 | 48 | 70.5             | 82               | 72.5             |                  | 1.21 × 10 <sup>-5</sup>                     | 10.6     | 20.2       | 1960                         |
|  | 105            | 139             | 259            | 28 | 122 | 9              | 53.5 | 64 | 70.5             | 82               | 73               |                  | 1.21 × 10 <sup>-5</sup>                     | 17.4     | 20.2       | 1960                         |
|  | 117            | 157             | 252            | 32 | 137 | 11             | 44   | 60 | 79               | 86.5             | 80               |                  | 1.21 × 10 <sup>-5</sup>                     | 17.2     | 19.13      | 1950                         |

Note) The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.


If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>ax</sub>) is obtained from the following equation.

$$K_{ax} = K \left( \frac{Fa}{0.3Ca} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# SBKH No Preload

|          |        |
|----------|--------|
| DN value | 130000 |
|----------|--------|



| Model No.      | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Screw shaft Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Permissible load*<br>F <sub>P</sub><br>kN | Rigidity<br>K<br>N/μm |
|----------------|---------------------------------|------------|--------------------------------------|---|--|-------------------|-----------------------|---|-----------------------|
|                |                                 |            |                                      |   |  | Ca<br>kN          | C <sub>0a</sub><br>kN |   |                       |
| SBKH 6332-3.8  | 63                              | 32         | 66.5                                 | 49.8                                    | 1×3.8                                  | 304               | 631                   | 88  | 1435                  |
| SBKH 6340-7.6  | 63                              | 40         | 66.0                                 | 52.6                                    | 2×3.8                                  | 413               | 967                   | 135                                       | 2723                  |
| SBKH 8050-7.6  | 80                              | 50         | 84.0                                 | 63.6                                    | 2×3.8                                  | 777               | 1788                  | 250                                       | 3402                  |
| SBKH 8060-7.6  | 80                              | 60         | 84.0                                 | 63.6                                    | 2×3.8                                  | 780               | 1824                  | 255                                       | 3452                  |
| SBKH 10050-7.6 | 100                             | 50         | 104.0                                | 83.6                                    | 2×3.8                                  | 876               | 2401                  | 336                                       | 4098                  |
| SBKH 10060-7.6 | 100                             | 60         | 104.0                                | 83.6                                    | 2×3.8                                  | 880               | 2294                  | 321                                       | 4149                  |
| SBKH 12060-7.6 | 120                             | 60         | 124.0                                | 103.6                                   | 2×3.8                                  | 962               | 2941                  | 411                                       | 4809                  |

Note 1) The permissible load F<sub>P</sub>\* indicates the maximum axial load that the Ball Screw can receive.

If desiring both ends of the screw shaft to be larger than the screw shaft diameter, contact THK.

Note 2) Certain precautions are necessary regarding the assembly method. (See [A15-222](#).)

Note 3) For high-load ball screws, the standard maximum length of the screw shaft is 3000 mm. For lengths greater than this, please contact THK.

### Axial Clearance

Unit: mm

| Clearance symbol | G1        | G2        | G3        |
|------------------|-----------|-----------|-----------|
| Axial Clearance  | 0 to 0.01 | 0 to 0.02 | 0 to 0.05 |

### Model number coding

**SBKH8050-7.6 RR G2 +1200L C7**

Model Number

Accuracy symbol (\*2)

Overall screw shaft length (in mm)


Axial clearance symbol  
(clearance in the axial direction must be: G1, G2 or G3.  
Clearance G0 and GT are not supported.)

Seal symbol(\*1)

(RR: labyrinth seal on both sides)

(\*1) See [A15-334](#). (\*2) See [A15-12](#).

## High-Thrust Ball Screw



Unit: mm

| Nut dimensions   |                                |                             |                               |    |                |                |     |                |                |                    | Screw shaft inertial moment/mm <sup>2</sup> | Nut mass kg | Shaft mass* <sup>1</sup> kg/m | Permissible rotational speed min <sup>-1</sup> |
|------------------|--------------------------------|-----------------------------|-------------------------------|----|----------------|----------------|-----|----------------|----------------|--------------------|---|-------------|-------------------------------|--|
| Outer diameter D | Flange diameter D <sub>1</sub> | Cap diameter D <sub>2</sub> | Overall length L <sub>1</sub> | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> | N <sub>1</sub> | Lubrication hole A |   |             |                               |  |
| 140              | 205                            | (140)                       | 190                           | 28 | 143            | (19)           | 173 | 22             | 14             | Rc1/8<br>(PT1/8)   | 1.21 × 10 <sup>-5</sup>                     | 17.2        | 21                            | 1950   |
| 127              | 191                            | (127)                       | 209                           | 30 | 163            | (16)           | 159 | 22             | 15             |                    | 1.21 × 10 <sup>-5</sup>                     | 15.5        | 21                            | 1960   |
| 175              | 253                            | (175)                       | 268                           | 32 | 213            | (23)           | 214 | 26             | 16             |                    | 3.16 × 10 <sup>-5</sup>                     | 36.9        | 31.3                          | 1540   |
| 175              | 253                            | (175)                       | 306                           | 40 | 243            | (23)           | 214 | 26             | 20             |                    | 3.16 × 10 <sup>-5</sup>                     | 43.5        | 32.5                          | 1540   |
| 195              | 273                            | (195)                       | 269                           | 40 | 206            | (23)           | 234 | 26             | 20             |                    | 7.71 × 10 <sup>-5</sup>                     | 44.5        | 51.3                          | 1250   |
| 195              | 273                            | (195)                       | 307                           | 40 | 244            | (23)           | 234 | 26             | 20             |                    | 7.71 × 10 <sup>-5</sup>                     | 50.5        | 52.9                          | 1250   |
| 210              | 288                            | (210)                       | 308                           | 45 | 240            | (23)           | 249 | 26             | 22.5           |                    | 1.60 × 10 <sup>-4</sup>                     | 53.7        | 78.1                          | 1040   |

Note1) There will be no dimensional change after the seal is attached.

Note2) The rigidity values (K) in the table represent spring constants, each obtained from the load and the elastic deformation under an axial load equal to 30% of the basic axial dynamic load rating (Ca).








These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the rigidity value (K) in the table as the actual value.

If the axial load (Fa) is not 0.3 Ca, the rigidity value (K<sub>N</sub>) is obtained from the following equation.

$$K_N = K \left( \frac{F_a}{0.3C_a} \right)^{\frac{1}{3}}$$

K: Rigidity value in the dimensional table

# Transport Ball Screw

| Series    | Type                            |   | Features               |  |
|-----------|---------------------------------|---|------------------------|--|
| Transport | JPF                             |    | Fixed-point Preloading |  |
|           | BTK-V                           |    | High DN value          |  |
|           | BNT                             |    | Flat nut               |  |
|           | BLK                             |    | Large lead             |  |
|           | WTF                             |   | Super large lead       |  |
|           | CNF                             |  | Super large lead       |  |
|           | MTF<br>Unfinished<br>Shaft Ends |  | Miniature              |  |
|           | MTF                             |   |                        |  |

## Transport Ball Screw

|  | Caged ball | Compact nut | Miniature | High load capacity | Preload | DN Value | Shaft diameter (mm) | Lead (mm) | Page No.       |
|--|------------|-------------|-----------|--------------------|---------|----------|---------------------|-----------|----------------|
|  |            |             |           |                    | ✓       | 50000    | 14 to 40            | 4 to 10   | <b>A15-240</b> |
|  |            |             |           |                    |         | 100000   | 10 to 50            | 6 to 16   | <b>A15-242</b> |
|  |            |             |           |                    |         | 50000    | 14 to 45            | 4 to 12   | <b>A15-244</b> |
|  |            |             |           |                    |         | 70000    | 15 to 50            | 10 to 50  | <b>A15-246</b> |
|  |            |             |           |                    |         | 70000    | 15 to 50            | 20 to 100 | <b>A15-248</b> |
|  |            |             |           |                    |         | 70000    | 15 to 30            | 30 to 60  | <b>A15-250</b> |
|  |            |             | ✓         |                    |         | 50000    | 6 to 12             | 1 to 2    | <b>A15-252</b> |
|  |            |             |           |                    |         | 70000    | 6 to 14             | 1 to 5    | <b>A15-254</b> |


## Standard combinations of outer diameters and leads of the screw shafts

| Shaft diameter | Lead |     |                     |                     |                     |              |                     |              |       |     |  |
|----------------|------|-----|---------------------|---------------------|---------------------|--------------|---------------------|--------------|-------|-----|--|
|                | 1    | 2   | 4                   | 5                   | 6                   | 8            | 10                  | 12           | 16    | 20  |  |
| 6              | MTF  |     |                     |                     |                     |              |                     |              |       |     |  |
| 8              | MTF  | MTF |                     | MTF                 |                     | BLK          |                     |              |       |     |  |
| 10             |      | MTF | MTF                 |                     | BTK-V               |              | BLK                 |              |       |     |  |
| 12             |      | MTF |                     |                     |                     | BTK-V        |                     |              |       |     |  |
| 14             |      | MTF | JPF<br>BTK-V<br>BNT | JPF<br>BTK-V<br>BNT |                     |              |                     |              |       |     |  |
| 15             |      |     |                     |                     |                     |              | BLK                 |              |       | WTF |  |
| 16             |      |     |                     | JPF<br>BTK-V<br>BNT |                     |              |                     |              | BLK   |     |  |
| 18             |      |     |                     |                     |                     | BTK-V<br>BNT |                     |              |       |     |  |
| 20             |      |     |                     | JPF<br>BTK-V<br>BNT |                     |              | BTK-V<br>BNT        |              |       | BLK |  |
| 25             |      |     |                     | JPF<br>BTK-V<br>BNT |                     |              | JPF<br>BTK-V<br>BNT |              |       |     |  |
| 28             |      |     |                     | JPF                 | JPF<br>BTK-V<br>BNT |              |                     |              |       |     |  |
| 30             |      |     |                     |                     |                     |              |                     |              |       |     |  |
| 32             |      |     |                     |                     |                     |              | JPF<br>BTK-V<br>BNT |              |       |     |  |
| 36             |      |     |                     |                     |                     |              | JPF<br>BTK-V<br>BNT |              |       | BLK |  |
| 40             |      |     |                     |                     |                     |              | JPF<br>BTK-V        |              |       |     |  |
| 45             |      |     |                     |                     |                     |              |                     | BTK-V<br>BNT |       |     |  |
| 50             |      |     |                     |                     |                     |              |                     |              | BTK-V |     |  |



# JPF With Preload

|          |       |
|----------|-------|
| DN value | 50000 |
|----------|-------|



| Model No.  | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating    |                       | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Outer diameter<br>D <sub>2</sub> |
|------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|----------------------|-----------------------|---------------------|-----------------------------------|----------------------------------|
|            |                                 |            |                                      |                             |  | C <sub>a</sub><br>kN | C <sub>0a</sub><br>kN |                     |                                   |                                  |
| JPF 1404-4 | 14                              | 4          | 14.4                                 | 11.5                        | 2×1                                    | 2.8                  | 5.1                   | 26                  | 46                                | 25.5                             |
| JPF 1405-4 | 14                              | 5          | 14.5                                 | 11.2                        | 2×1                                    | 3.9                  | 8.6                   | 26                  | 46                                | 25.5                             |
| JPF 1605-4 | 16                              | 5          | 16.75                                | 13.5                        | 2×1                                    | 3.7                  | 8.2                   | 30                  | 49                                | 29.5                             |
| JPF 2005-6 | 20                              | 5          | 20.5                                 | 17.2                        | 3×1                                    | 6                    | 16                    | 34                  | 57                                | 33.5                             |
| JPF 2505-6 | 25                              | 5          | 25.5                                 | 22.2                        | 3×1                                    | 6.9                  | 20.8                  | 40                  | 66                                | 39.5                             |
| JPF 2510-4 | 25                              | 10         | 26.8                                 | 20.2                        | 2×1                                    | 11.4                 | 24.5                  | 47                  | 72                                | 46.5                             |
| JPF 2805-6 | 28                              | 5          | 28.75                                | 25.2                        | 3×1                                    | 7.3                  | 23.9                  | 43                  | 69                                | 42.5                             |
| JPF 2806-6 | 28                              | 6          | 28.5                                 | 25.2                        | 3×1                                    | 7.3                  | 23.9                  | 43                  | 69                                | 42.5                             |
| JPF 3210-6 | 32                              | 10         | 33.75                                | 27.2                        | 3×1                                    | 19.3                 | 49.9                  | 54                  | 88                                | 53.5                             |
| JPF 3610-6 | 36                              | 10         | 37                                   | 30.5                        | 3×1                                    | 20.6                 | 56.2                  | 58                  | 98                                | 57.5                             |
| JPF 4010-6 | 40                              | 10         | 41.75                                | 35.2                        | 3×1                                    | 22.2                 | 65.3                  | 62                  | 104                               | 61.5                             |

### Model number coding

**JPF1404-4 RR G0 +500L C7 T**


Model No.    Seal symbol (\*1)    Overall screw shaft length (in mm)    Symbol for rolled shaft

Symbol for clearance in the axial direction    Accuracy symbol (\*2)

(\*1) See [A15-334](#). (\*2) See [A15-12](#).



## Transport Ball Screw



Unit: mm

| Nut dimensions    |    |                |                |     |                                     |                     |                         | Screw shaft<br>inertial moment | Nut<br>mass | Shaft<br>mass     | Permissible<br>rotational<br>speed |
|-------------------|----|----------------|----------------|-----|-------------------------------------|---------------------|-------------------------|--------------------------------|-------------|-------------------|------------------------------------|
| Overall<br>length | H  | B <sub>1</sub> | B <sub>2</sub> | PCD | d <sub>1</sub> × d <sub>2</sub> × h | Lubrication<br>hole |                         |                                |             |                   |                                    |
| L <sub>1</sub>    |    |                |                |     |                                     | A                   | kg·m <sup>2</sup> /mm   | kg                             | kg/m        | min <sup>-1</sup> |                                    |
| 52                | 10 | 42             | 16.5           | 36  | 4.5 × 8 × 4.5                       | M6                  | 2.96 × 10 <sup>-8</sup> | 0.22                           | 1           | 3470              |                                    |
| 60                | 10 | 50             | 20             | 36  | 4.5 × 8 × 4.5                       | M6                  | 2.96 × 10 <sup>-8</sup> | 0.24                           | 0.99        | 3440              |                                    |
| 60                | 10 | 50             | 19.5           | 39  | 4.5 × 8 × 4.5                       | M6                  | 5.05 × 10 <sup>-8</sup> | 0.3                            | 1.34        | 2980              |                                    |
| 80                | 11 | 69             | 26.5           | 45  | 5.5 × 9.5 × 5.5                     | M6                  | 1.23 × 10 <sup>-7</sup> | 0.46                           | 2.15        | 2430              |                                    |
| 80                | 11 | 69             | 26             | 51  | 5.5 × 9.5 × 5.5                     | M6                  | 3.01 × 10 <sup>-7</sup> | 0.6                            | 3.45        | 1960              |                                    |
| 112               | 12 | 100            | 42             | 58  | 6.6 × 11 × 6.5                      | M6                  | 3.01 × 10 <sup>-7</sup> | 1.2                            | 3.26        | 1860              |                                    |
| 80                | 12 | 68             | 25             | 55  | 6.6 × 11 × 6.5                      | M6                  | 4.74 × 10 <sup>-7</sup> | 0.66                           | 4.27        | 1730              |                                    |
| 90                | 12 | 78             | 35             | 55  | 6.6 × 11 × 6.5                      | M6                  | 4.74 × 10 <sup>-7</sup> | 0.72                           | 4.44        | 1750              |                                    |
| 135               | 15 | 120            | 53.5           | 70  | 9 × 14 × 8.5                        | M6                  | 8.08 × 10 <sup>-7</sup> | 1.84                           | 5.49        | 1480              |                                    |
| 138               | 18 | 120            | 53.5           | 77  | 11 × 17.5 × 11                      | M6                  | 1.29 × 10 <sup>-6</sup> | 2.22                           | 6.91        | 1350              |                                    |
| 138               | 18 | 120            | 53.5           | 82  | 11 × 17.5 × 11                      | Rc1/8<br>(PT1/8)    | 1.97 × 10 <sup>-6</sup> | 2.42                           | 8.81        | 1190              |                                    |


Note) The ball screw nut and the screw shaft of model JPF are not sold separately.

The basic load rating corresponds to the recommended loading direction.


If a load is applied in the opposite direction, the value must be  $0.1 \times C_a$  or less during use.

# BTK-V No Preload

|          |        |
|----------|--------|
| DN value | 100000 |
|----------|--------|



BTK1006V/1208V



BTK1404V to 5016V


| Model No.     | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating    |                       | Rigidity<br>K | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length |    |
|---------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|----------------------|-----------------------|---------------|---------------------|-----------------------------------|----------------|----|
|               |                                 |            |                                      |                             |  | C <sub>a</sub><br>kN | C <sub>0a</sub><br>kN |               |                     |                                   | L <sub>1</sub> | H  |
| BTK 1006V-2.6 | 10                              | 6          | 10.5                                 | 7.8                         | 1×2.65                                 | 2.8                  | 4.9                   | 88            | 26                  | 42                                | 36             | 8  |
| BTK 1208V-2.6 | 12                              | 8          | 12.65                                | 9.7                         | 1×2.65                                 | 3.8                  | 6.8                   | 108           | 29                  | 45                                | 44             | 8  |
| BTK 1404V-3.6 | 14                              | 4          | 14.4                                 | 11.5                        | 1×3.65                                 | 5.5                  | 11.5                  | 150           | 31                  | 50                                | 40             | 10 |
| BTK 1405V-2.6 | 14                              | 5          | 14.5                                 | 11.2                        | 1×2.65                                 | 5                    | 11.4                  | 116           | 32                  | 50                                | 40             | 10 |
| BTK 1605V-2.6 | 16                              | 5          | 16.75                                | 13.5                        | 1×2.65                                 | 5.4                  | 13.3                  | 130           | 34                  | 54                                | 40             | 10 |
| BTK 1808V-3.6 | 18                              | 8          | 19.3                                 | 14.4                        | 1×3.65                                 | 13.1                 | 31                    | 210           | 50                  | 80                                | 61             | 12 |
| BTK 2005V-2.6 | 20                              | 5          | 20.5                                 | 17.2                        | 1×2.65                                 | 6                    | 16.5                  | 150           | 40                  | 60                                | 40             | 10 |
| BTK 2010V-2.6 | 20                              | 10         | 21.25                                | 16.4                        | 1×2.65                                 | 10.6                 | 25.1                  | 160           | 52                  | 82                                | 61             | 12 |
| BTK 2505V-2.6 | 25                              | 5          | 25.5                                 | 22.2                        | 1×2.65                                 | 6.7                  | 20.8                  | 180           | 43                  | 67                                | 40             | 10 |
| BTK 2510V-5.3 | 25                              | 10         | 26.8                                 | 20.2                        | 2×2.65                                 | 31.2                 | 83.7                  | 400           | 60                  | 96                                | 98             | 15 |
| BTK 2806V-2.6 | 28                              | 6          | 28.5                                 | 25.2                        | 1×2.65                                 | 7                    | 23.4                  | 200           | 50                  | 80                                | 47             | 12 |
| BTK 2806V-5.3 | 28                              | 6          | 28.5                                 | 25.2                        | 2×2.65                                 | 12.8                 | 46.8                  | 390           | 50                  | 80                                | 65             | 12 |
| BTK 3210V-2.6 | 32                              | 10         | 33.75                                | 27.2                        | 1×2.65                                 | 19.8                 | 53.8                  | 250           | 67                  | 103                               | 68             | 15 |
| BTK 3210V-5.3 | 32                              | 10         | 33.75                                | 27.2                        | 2×2.65                                 | 36                   | 107.5                 | 490           | 67                  | 103                               | 98             | 15 |
| BTK 3610V-2.6 | 36                              | 10         | 37                                   | 30.5                        | 1×2.65                                 | 20.8                 | 59.8                  | 270           | 70                  | 110                               | 70             | 17 |
| BTK 3610V-5.3 | 36                              | 10         | 37                                   | 30.5                        | 2×2.65                                 | 37.8                 | 118.7                 | 530           | 70                  | 110                               | 100            | 17 |
| BTK 4010V-5.3 | 40                              | 10         | 41.75                                | 35.2                        | 2×2.65                                 | 40.3                 | 134.9                 | 590           | 76                  | 116                               | 100            | 17 |
| BTK 4512V-5.3 | 45                              | 12         | 46.5                                 | 39.2                        | 2×2.65                                 | 49.5                 | 169                   | 650           | 82                  | 128                               | 118            | 20 |
| BTK 5016V-5.3 | 50                              | 16         | 52.7                                 | 42.9                        | 2×2.65                                 | 93.8                 | 315.2                 | 930           | 102                 | 162                               | 145            | 25 |

## Model number coding


# BTK1405V-2.6 ZZ +500L C7 T H1K

|           |  |                                    |                         |                      |                                   |
|-----------|--|------------------------------------|-------------------------|----------------------|-----------------------------------|
| Model No. | Contamination protection accessory symbol (*1) | Overall screw shaft length (in mm) | Symbol for rolled shaft | Accuracy symbol (*2) | Recommended shaft ends shape code |
|-----------|--|------------------------------------|-------------------------|----------------------|-----------------------------------|

(\*1) See [A15-334](#). (\*2) See [A15-12](#).



BTK1006V/1208V



BTK1404V to 5016V


Unit: mm

| Nut dimensions |     |                |                |                  |                  | Axial clearance | Standard shaft length                 | Screw shaft inertial moment<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|----------------|-----|----------------|----------------|------------------|------------------|-----------------|---------------------------------------|--|----------------|--------------------|---|
| B <sub>1</sub> | PCD | d <sub>1</sub> | T <sub>w</sub> | Lubrication hole |                  |                 |                                       |  |                |                    |   |
|                |     |                |                | N <sub>1</sub>   | A                |                 |                                       |  |                |                    |   |
| 28             | 34  | 4.5            | 29             | —                | 3                | 0.05            | 200, 300, 500, 1000                   | $7.71 \times 10^{-9}$                                | 0.12           | 0.48               | 5000  |
| 36             | 37  | 4.5            | 32             | —                | 3                | 0.05            | 200, 300, 500, 1000                   | $1.60 \times 10^{-8}$                                | 0.18           | 0.72               | 5000  |
| 30             | 40  | 4.5            | 37             | 5                | M6               | 0.1             | 500, 1000                             | $2.96 \times 10^{-8}$                                | 0.23           | 1                  | 5000  |
| 30             | 40  | 4.5            | 38             | 5                | M6               | 0.1             | 500, 1000                             | $2.96 \times 10^{-8}$                                | 0.22           | 0.99               | 5000  |
| 30             | 44  | 4.5            | 40             | 5                | M6               | 0.1             | 500, 1000, 1500                       | $5.05 \times 10^{-8}$                                | 0.24           | 1.34               | 5000  |
| 49             | 65  | 6.6            | 60             | 5                | M6               | 0.1             | 500, 1000, 1500                       | $8.09 \times 10^{-8}$                                | 0.84           | 1.71               | 5000  |
| 30             | 50  | 4.5            | 46             | 5                | M6               | 0.1             | 500, 1000, 1500, 2000                 | $1.23 \times 10^{-7}$                                | 0.32           | 2.15               | 4870  |
| 49             | 67  | 6.6            | 64             | 5                | M6               | 0.1             | 500, 1000, 1500, 2000                 | $1.23 \times 10^{-7}$                                | 0.93           | 2.16               | 4700  |
| 30             | 55  | 5.5            | 50             | 5                | M6               | 0.1             | 500, 1000, 1500, 2000                 | $3.01 \times 10^{-7}$                                | 0.34           | 3.45               | 3920  |
| 83             | 78  | 9              | 72             | 5                | M6               | 0.1             | 500, 1000, 1500, 2000                 | $3.01 \times 10^{-7}$                                | 1.83           | 3.26               | 3730  |
| 35             | 65  | 6.6            | 60             | 6                | M6               | 0.1             | 500, 1000, 2000, 2500                 | $4.74 \times 10^{-7}$                                | 0.59           | 4.44               | 3500  |
| 53             | 65  | 6.6            | 60             | 6                | M6               | 0.1             | 500, 1000, 2000, 2500                 | $4.74 \times 10^{-7}$                                | 0.75           | 4.44               | 3500  |
| 53             | 85  | 9              | 78             | 5                | M6               | 0.14            | 500, 1000, 1500, 2000, 2500, 3000     | $8.08 \times 10^{-7}$                                | 1.56           | 5.49               | 2960  |
| 83             | 85  | 9              | 78             | 5                | M6               | 0.14            | 500, 1000, 1500, 2000, 2500, 3000     | $8.08 \times 10^{-7}$                                | 2.1            | 5.49               | 2960  |
| 53             | 90  | 11             | 82             | 7                | M6               | 0.17            | 500, 1000, 2000, 2500, 3000           | $1.29 \times 10^{-6}$                                | 1.78           | 6.91               | 2700  |
| 83             | 90  | 11             | 82             | 7                | M6               | 0.17            | 500, 1000, 2000, 2500, 3000           | $1.29 \times 10^{-6}$                                | 2.35           | 6.91               | 2700  |
| 83             | 96  | 11             | 88             | 7                | M6               | 0.17            | 1000, 1500, 2000, 2500, 3000, 3500    | $1.97 \times 10^{-6}$                                | 2.6            | 8.81               | 2390  |
| 98             | 104 | 14             | 94             | 8                | M6               | 0.17            | 1000, 1500, 2000, 3000, 3500, 4000    | $3.16 \times 10^{-6}$                                | 3.48           | 11.08              | 2150  |
| 120            | 132 | 18             | 104            | 12.5             | Rc1/8<br>(PT1/8) | 0.2             | 1000, 1500, 2000, 3000,<br>3500, 4000 | $4.82 \times 10^{-6}$                                | 6.52           | 13.66              | 1890  |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See [A15-344](#) for further details.

# BNT (Rolled Ball Screw) No Preload

|          |      |
|----------|------|
| DN value | 5000 |
|----------|------|




| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       |           | Rigidity   |                    |                                  |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|-----------|------------|--------------------|----------------------------------|
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN | K<br>N/μm | Width<br>W | Center height<br>F | Overall length<br>L <sub>1</sub> |
| BNT 1404-3.6 | 14                              | 4          | 14.4                                 | 11.5                        | 1×3.65                                 | 5.5               | 11.5                  | 150       | 34         | 13                 | 35                               |
| BNT 1405-2.6 | 14                              | 5          | 14.5                                 | 11.2                        | 1×2.65                                 | 5                 | 11.4                  | 110       | 34         | 13                 | 35                               |
| BNT 1605-2.6 | 16                              | 5          | 16.75                                | 13.5                        | 1×2.65                                 | 5.4               | 13.3                  | 130       | 42         | 16                 | 36                               |
| BNT 1808-3.6 | 18                              | 8          | 19.3                                 | 14.4                        | 1×3.65                                 | 13.1              | 31                    | 210       | 48         | 17                 | 56                               |
| BNT 2005-2.6 | 20                              | 5          | 20.5                                 | 17.2                        | 1×2.65                                 | 6                 | 16.5                  | 150       | 48         | 17                 | 35                               |
| BNT 2010-2.6 | 20                              | 10         | 21.25                                | 16.4                        | 1×2.65                                 | 10.6              | 25.1                  | 160       | 48         | 18                 | 58                               |
| BNT 2505-2.6 | 25                              | 5          | 25.5                                 | 22.2                        | 1×2.65                                 | 6.7               | 20.8                  | 180       | 60         | 20                 | 35                               |
| BNT 2510-5.3 | 25                              | 10         | 26.8                                 | 20.2                        | 2×2.65                                 | 31.2              | 83.7                  | 400       | 60         | 23                 | 94                               |
| BNT 2806-2.6 | 28                              | 6          | 28.5                                 | 25.2                        | 1×2.65                                 | 7                 | 23.4                  | 200       | 60         | 22                 | 42                               |
| BNT 2806-5.3 | 28                              | 6          | 28.5                                 | 25.2                        | 2×2.65                                 | 12.8              | 46.8                  | 390       | 60         | 22                 | 67                               |
| BNT 3210-2.6 | 32                              | 10         | 33.75                                | 27.2                        | 1×2.65                                 | 19.8              | 53.8                  | 250       | 70         | 26                 | 64                               |
| BNT 3210-5.3 | 32                              | 10         | 33.75                                | 27.2                        | 2×2.65                                 | 36                | 107.5                 | 490       | 70         | 26                 | 94                               |
| BNT 3610-2.6 | 36                              | 10         | 37                                   | 30.5                        | 1×2.65                                 | 20.8              | 59.3                  | 270       | 86         | 29                 | 64                               |
| BNT 3610-5.3 | 36                              | 10         | 37                                   | 30.5                        | 2×2.65                                 | 37.8              | 118.7                 | 530       | 86         | 29                 | 96                               |
| BNT 4512-5.3 | 45                              | 12         | 46.5                                 | 39.2                        | 2×2.65                                 | 49.5              | 169                   | 650       | 100        | 36                 | 115                              |

## Model number coding

**BNT2010-2.6 ZZ +1000L C7 T H1K**

|           |  |                                    |                      |                         |                                   |
|-----------|--|------------------------------------|----------------------|-------------------------|-----------------------------------|
| Model No. | Contamination protection accessory symbol (*1) | Overall screw shaft length (in mm) | Accuracy symbol (*2) | Symbol for rolled shaft | Recommended shaft ends shape code |
|-----------|--|------------------------------------|----------------------|-------------------------|-----------------------------------|

(\*1) See **A15-334**. (\*2) See **A15-12**.




Unit: mm

| Nut dimensions |    |          |                |      |      |                |                |    |      | Axial clearance         | Screw shaft inertial moment<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|----------------|----|----------|----------------|------|------|----------------|----------------|----|------|-------------------------|--|----------------|--------------------|---|
| Mounting hole  |    |          | W <sub>1</sub> | T    | M    | N <sub>1</sub> | N <sub>2</sub> | A  |      |                         |  |                |                    |   |
| B              | C  | S × ℓ    |                |      |      |                |                |    |      |                         |  |                |                    |   |
| 26             | 22 | M4 × 7   | 17             | 6    | 30   | 6              | 2              | M6 | 0.1  | 2.96 × 10 <sup>-8</sup> | 0.15   | 1              | 4860               |   |
| 26             | 22 | M4 × 7   | 17             | 6    | 31   | 6              | 2              | M6 | 0.1  | 2.96 × 10 <sup>-8</sup> | 0.15   | 0.99           | 4820               |   |
| 32             | 22 | M5 × 8   | 21             | 21.5 | 32.5 | 6              | 2              | M6 | 0.1  | 5.05 × 10 <sup>-8</sup> | 0.3  | 1.34           | 4170               |   |
| 35             | 35 | M6 × 10  | 24             | 10   | 44   | 8              | 3              | M6 | 0.1  | 8.09 × 10 <sup>-8</sup> | 0.47   | 1.71           | 3620               |   |
| 35             | 22 | M6 × 10  | 24             | 9    | 39   | 5              | 3              | M6 | 0.1  | 1.23 × 10 <sup>-7</sup> | 0.28   | 2.15           | 3410               |   |
| 35             | 35 | M6 × 10  | 24             | 9    | 46   | 10             | 2              | M6 | 0.1  | 1.23 × 10 <sup>-7</sup> | 0.5  | 2.16           | 3290               |   |
| 40             | 22 | M8 × 12  | 30             | 9.5  | 45   | 7              | 5              | M6 | 0.1  | 3.01 × 10 <sup>-7</sup> | 0.41   | 3.45           | 2740               |   |
| 40             | 60 | M8 × 12  | 30             | 10   | 55   | 10             | —              | M6 | 0.1  | 3.01 × 10 <sup>-7</sup> | 1.18   | 3.26           | 2610               |   |
| 40             | 18 | M8 × 12  | 30             | 10   | 50   | 8              | —              | M6 | 0.1  | 4.74 × 10 <sup>-7</sup> | 0.81   | 4.44           | 2450               |   |
| 40             | 40 | M8 × 12  | 30             | 10   | 50   | 8              | —              | M6 | 0.1  | 4.74 × 10 <sup>-7</sup> | 0.78   | 4.44           | 2450               |   |
| 50             | 45 | M8 × 12  | 35             | 12   | 62   | 10             | —              | M6 | 0.14 | 8.08 × 10 <sup>-7</sup> | 1.3  | 5.49           | 2070               |   |
| 50             | 60 | M8 × 12  | 35             | 12   | 62   | 10             | —              | M6 | 0.14 | 8.08 × 10 <sup>-7</sup> | 2  | 5.49           | 2070               |   |
| 60             | 45 | M10 × 16 | 43             | 17   | 67   | 11             | —              | M6 | 0.17 | 1.29 × 10 <sup>-6</sup> | 1.8  | 6.91           | 1890               |   |
| 60             | 60 | M10 × 16 | 43             | 17   | 67   | 11             | —              | M6 | 0.17 | 1.29 × 10 <sup>-6</sup> | 2.4  | 6.91           | 1890               |   |
| 75             | 75 | M12 × 20 | 50             | 20.5 | 80   | 13             | —              | M6 | 0.2  | 3.16 × 10 <sup>-6</sup> | 4.1  | 11.08          | 1500               |   |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See [A15-344](#) for further details.

# BLK (Rolled Ball Screw) No Preload

|          |      |
|----------|------|
| DN value | 7000 |
|----------|------|



BLK0808/1010


| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                       | Rigidity<br>K | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------------|---------------|---------------------|-----------------------------------|----------------------------------|----|
|              |                                 |            |                                      |                             |  | Ca<br>kN          | C <sub>0a</sub><br>kN |               |                     |                                   |                                  |    |
| BLK 0808-3.2 | 8                               | 8          | 8.4                                  | 6.7                         | 2×1.6                                  | 2.2               | 3.8                   | 95            | 18                  | 31                                | 20                               | 4  |
| BLK 1010-3.2 | 10                              | 10         | 10.5                                 | 8.4                         | 2×1.6                                  | 3.3               | 5.9                   | 117           | 23                  | 40                                | 24                               | 5  |
| BLK 1510-5.6 | 15                              | 10         | 15.75                                | 12.5                        | 2×2.8                                  | 9.8               | 25.2                  | 260           | 34                  | 57                                | 44                               | 10 |
| BLK 1616-3.6 | 16                              | 16         | 16.65                                | 13.7                        | 2×1.8                                  | 5.8               | 12.9                  | 170           | 32                  | 53                                | 38                               | 10 |
| BLK 1616-7.2 | 16                              | 16         | 16.65                                | 13.7                        | 4×1.8                                  | 10.5              | 25.9                  | 340           | 32                  | 53                                | 38                               | 10 |
| BLK 2020-3.6 | 20                              | 20         | 20.75                                | 17.5                        | 2×1.8                                  | 7.7               | 22.3                  | 210           | 39                  | 62                                | 45                               | 10 |
| BLK 2020-7.2 | 20                              | 20         | 20.75                                | 17.5                        | 4×1.8                                  | 13.9              | 44.6                  | 410           | 39                  | 62                                | 45                               | 10 |
| BLK 2525-3.6 | 25                              | 25         | 26                                   | 21.9                        | 2×1.8                                  | 12.1              | 35                    | 270           | 47                  | 74                                | 55                               | 12 |
| BLK 2525-7.2 | 25                              | 25         | 26                                   | 21.9                        | 4×1.8                                  | 21.9              | 69.9                  | 520           | 47                  | 74                                | 55                               | 12 |
| BLK 3232-3.6 | 32                              | 32         | 33.25                                | 28.3                        | 2×1.8                                  | 17.3              | 53.9                  | 330           | 58                  | 92                                | 70                               | 15 |
| BLK 3232-7.2 | 32                              | 32         | 33.25                                | 28.3                        | 4×1.8                                  | 31.3              | 107.8                 | 650           | 58                  | 92                                | 70                               | 15 |
| BLK 3620-5.6 | 36                              | 20         | 37.75                                | 31.2                        | 2×2.8                                  | 39.8              | 121.7                 | 570           | 70                  | 110                               | 78                               | 17 |
| BLK 3624-5.6 | 36                              | 24         | 38                                   | 30.7                        | 2×2.8                                  | 46.2              | 137.4                 | 590           | 75                  | 115                               | 94                               | 18 |
| BLK 3636-3.6 | 36                              | 36         | 37.4                                 | 31.7                        | 2×1.8                                  | 22.4              | 70.5                  | 370           | 66                  | 106                               | 77                               | 17 |
| BLK 3636-7.2 | 36                              | 36         | 37.4                                 | 31.7                        | 4×1.8                                  | 40.6              | 141.1                 | 730           | 66                  | 106                               | 77                               | 17 |
| BLK 4040-3.6 | 40                              | 40         | 41.75                                | 35.2                        | 2×1.8                                  | 28.1              | 89.8                  | 420           | 73                  | 114                               | 85                               | 17 |
| BLK 4040-7.2 | 40                              | 40         | 41.75                                | 35.2                        | 4×1.8                                  | 51.1              | 179.6                 | 810           | 73                  | 114                               | 85                               | 17 |
| BLK 5050-3.6 | 50                              | 50         | 52.2                                 | 44.1                        | 2×1.8                                  | 42.1              | 140.4                 | 510           | 90                  | 135                               | 106                              | 20 |
| BLK 5050-7.2 | 50                              | 50         | 52.2                                 | 44.1                        | 4×1.8                                  | 76.3              | 280.7                 | 1000          | 90                  | 135                               | 106                              | 20 |

## Model number coding

**BLK3232-3.6 ZZ +1500L C7 T H1K**

|           |  |                                    |                      |                         |                                   |
|-----------|--|------------------------------------|----------------------|-------------------------|-----------------------------------|
| Model No. | Contamination protection accessory symbol (*1) | Overall screw shaft length (in mm) | Accuracy symbol (*2) | Symbol for rolled shaft | Recommended shaft ends shape code |
|-----------|--|------------------------------------|----------------------|-------------------------|-----------------------------------|

(\*1) See **A15-334**. (\*2) See **A15-12**.



BLK1510~5050


Unit: mm

| Nut dimensions |     |                |     |                  |    |                        | Axial clearance | Standard shaft length              | Screw shaft inertial moment<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|----------------|-----|----------------|-----|------------------|----|------------------------|-----------------|------------------------------------|--|----------------|--------------------|---|
| B <sub>1</sub> | PCD | d <sub>1</sub> | Tw  | Lubrication hole |    | Seal<br>M <sub>1</sub> |                 |                                    |  |                |                    |   |
|                |     |                |     | N <sub>1</sub>   | A  |                        |                 |                                    |  |                |                    |   |
| 10             | 25  | 3.4            | 20  | —                | —  | —                      | 0.1             | —                                  | $3.16 \times 10^{-9}$                                | 0.03           | 0.36               | 3500  |
| 13             | 32  | 4.5            | 25  | —                | —  | —                      | 0.1             | —                                  | $7.71 \times 10^{-9}$                                | 0.06           | 0.55               | 3500  |
| 24             | 45  | 5.5            | 40  | 5                | M6 | 3.5                    | 0.1             | 500, 1000                          | $3.90 \times 10^{-8}$                                | 0.26           | 1.16               | 4440  |
| 21.5           | 42  | 4.5            | 38  | 5                | M6 | 3.5                    | 0.1             | 500, 1000, 1500                    | $5.05 \times 10^{-8}$                                | 0.21           | 1.35               | 4200  |
| 21.5           | 42  | 4.5            | 38  | 5                | M6 | 3.5                    | 0.1             | 500, 1000, 1500                    | $5.05 \times 10^{-8}$                                | 0.25           | 1.35               | 4200  |
| 27.5           | 50  | 5.5            | 46  | 5                | M6 | 3.5                    | 0.1             | 500, 1000, 1500                    | $1.23 \times 10^{-7}$                                | 0.35           | 2.18               | 3370  |
| 27.5           | 50  | 5.5            | 46  | 5                | M6 | 3.5                    | 0.1             | 500, 1000, 1500                    | $1.23 \times 10^{-7}$                                | 0.35           | 2.18               | 3370  |
| 35             | 60  | 6.6            | 56  | 6                | M6 | 3.5                    | 0.1             | 500, 1000, 1500, 2000, 2500        | $3.01 \times 10^{-7}$                                | 0.64           | 3.41               | 2690  |
| 35             | 60  | 6.6            | 56  | 6                | M6 | 3.5                    | 0.1             | 500, 1000, 1500, 2000, 2500        | $3.01 \times 10^{-7}$                                | 0.64           | 3.41               | 2690  |
| 45             | 74  | 9              | 68  | 7.5              | M6 | 3.8                    | 0.14            | 1000, 1500, 2000, 2500, 3000       | $8.08 \times 10^{-7}$                                | 1.14           | 5.69               | 2100  |
| 45             | 74  | 9              | 68  | 7.5              | M6 | 3.8                    | 0.14            | 1000, 1500, 2000, 2500, 3000       | $8.08 \times 10^{-7}$                                | 1.14           | 5.69               | 2100  |
| 45             | 90  | 11             | 80  | 8.5              | M6 | 5                      | 0.17            | 1000, 1500, 2000, 2500, 3000       | $1.29 \times 10^{-6}$                                | 1.74           | 7.09               | 1850  |
| 59             | 94  | 11             | 86  | 9                | M6 | 5                      | 0.17            | 1000, 1500, 2000, 2500, 3000       | $1.29 \times 10^{-6}$                                | 2.42           | 7.02               | 1840  |
| 50             | 85  | 11             | 76  | 8.5              | M6 | 5                      | 0.17            | 1000, 1500, 2000, 2500, 3000       | $1.29 \times 10^{-6}$                                | 1.74           | 7.12               | 1870  |
| 50             | 85  | 11             | 76  | 8.5              | M6 | 5                      | 0.17            | 1000, 1500, 2000, 2500, 3000       | $1.29 \times 10^{-6}$                                | 1.74           | 7.12               | 1870  |
| 56.5           | 93  | 11             | 84  | 8.5              | M6 | 5.4                    | 0.17            | 1000, 1500, 2000, 2500, 3000, 4000 | $1.97 \times 10^{-6}$                                | 2.16           | 8.76               | 1670  |
| 56.5           | 93  | 11             | 84  | 8.5              | M6 | 5.4                    | 0.17            | 1000, 1500, 2000, 2500, 3000, 4000 | $1.97 \times 10^{-6}$                                | 2.16           | 8.76               | 1670  |
| 72             | 112 | 14             | 104 | 10               | M6 | 5.4                    | 0.2             | 1000, 1500, 2000, 3000, 4000       | $4.82 \times 10^{-6}$                                | 3.89           | 13.79              | 1340  |
| 72             | 112 | 14             | 104 | 10               | M6 | 5.4                    | 0.2             | 1000, 1500, 2000, 3000, 4000       | $4.82 \times 10^{-6}$                                | 3.86           | 13.79              | 1340  |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

# WTF No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.   | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                 | Rigidity<br>K | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  |
|-------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------|---------------|---------------------|-----------------------------------|----------------------------------|----|
|             |                                 |            |                                      |                             |  | Ca                | C <sub>0a</sub> |               |                     |                                   |                                  |    |
|             |                                 |            |                                      |                             |  | kN                | kN              | N/μm          |                     |                                   |                                  |    |
| WTF 1520-3  | 15                              | 20         | 15.75                                | 12.5                        | 2X1.5                                  | 5.5               | 14.2            | 140           | 32                  | 53                                | 45                               | 10 |
| WTF 1520-6  | 15                              | 20         | 15.75                                | 12.5                        | 4X1.5                                  | 10.1              | 28.5            | 280           | 32                  | 53                                | 45                               | 10 |
| WTF 1530-2  | 15                              | 30         | 15.75                                | 12.5                        | 4X0.6                                  | 4.3               | 9.3             | 120           | 32                  | 53                                | 33                               | 10 |
| WTF 1530-3  | 15                              | 30         | 15.75                                | 12.5                        | 2X1.6                                  | 5.6               | 12.4            | 160           | 32                  | 53                                | 63                               | 10 |
| WTF 2040-2  | 20                              | 40         | 20.75                                | 17.5                        | 4X0.65                                 | 5.4               | 13.6            | 160           | 37                  | 57                                | 41.5                             | 10 |
| WTF 2040-3  | 20                              | 40         | 20.75                                | 17.5                        | 2X1.65                                 | 6.6               | 17.2            | 200           | 37                  | 57                                | 81.5                             | 10 |
| WTF 2550-2  | 25                              | 50         | 26                                   | 21.9                        | 4X0.65                                 | 8.5               | 21.2            | 200           | 45                  | 69                                | 52                               | 12 |
| WTF 2550-3  | 25                              | 50         | 26                                   | 21.9                        | 2X1.65                                 | 10.4              | 26.9            | 260           | 45                  | 69                                | 102                              | 12 |
| WTF 3060-2  | 30                              | 60         | 31.25                                | 26.4                        | 4X0.65                                 | 11.8              | 30.6            | 240           | 55                  | 89                                | 62.5                             | 15 |
| WTF 3060-3  | 30                              | 60         | 31.25                                | 26.4                        | 2X1.65                                 | 14.5              | 38.9            | 310           | 55                  | 89                                | 122.5                            | 15 |
| WTF 4080-2  | 40                              | 80         | 41.75                                | 35.2                        | 4X0.65                                 | 19.8              | 54.5            | 320           | 73                  | 114                               | 79                               | 17 |
| WTF 4080-3  | 40                              | 80         | 41.75                                | 35.2                        | 2X1.65                                 | 24.3              | 69.2            | 400           | 73                  | 114                               | 159                              | 17 |
| WTF 50100-2 | 50                              | 100        | 52.2                                 | 44.1                        | 4X0.65                                 | 29.6              | 85.2            | 390           | 90                  | 135                               | 98                               | 20 |
| WTF 50100-3 | 50                              | 100        | 52.2                                 | 44.1                        | 2X1.65                                 | 36.3              | 108.1           | 500           | 90                  | 135                               | 198                              | 20 |


## Model number coding

**WTF3060-3 ZZ +1500L C7 T H1K**

|           |  |                                    |                         |                      |                                   |
|-----------|--|------------------------------------|-------------------------|----------------------|-----------------------------------|
| Model No. | Contamination protection accessory symbol (*1) | Overall screw shaft length (in mm) | Symbol for rolled shaft | Accuracy symbol (*2) | Recommended shaft ends shape code |
|-----------|--|------------------------------------|-------------------------|----------------------|-----------------------------------|

(\*1) See **A15-334**. (\*2) See **A15-12**.






Unit: mm

| Nut dimensions |     |                |    |                  |    |                | Seal | Axial clearance        | Standard shaft length | Screw shaft inertial moment<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|----------------|-----|----------------|----|------------------|----|----------------|------|------------------------|-----------------------|--|----------------|--------------------|---|
| B <sub>1</sub> | PCD | d <sub>1</sub> | Tw | Lubrication hole |    | M <sub>1</sub> |      |                        |                       |  |                |                    |   |
|                |     |                |    | N <sub>1</sub>   | A  |                |      |                        |                       |  |                |                    |   |
| 28             | 43  | 5.5            | 33 | 5                | M6 | 3.5            | 0.1  | 500, 1000              | $3.90 \times 10^{-8}$ | 0.2  | 1.17           | 4440               |   |
| 28             | 43  | 5.5            | 33 | 5                | M6 | 3.5            | 0.1  | 500, 1000              | $3.90 \times 10^{-8}$ | 0.2  | 1.17           | 4440               |   |
| 17             | 43  | 5.5            | 33 | 5                | M6 | 3.5            | 0.1  | 500, 1000, 1500        | $3.90 \times 10^{-8}$ | 0.22   | 1.19           | 4440               |   |
| 47             | 43  | 5.5            | 33 | 5                | M6 | 3.5            | 0.1  | 500, 1000, 1500        | $3.90 \times 10^{-8}$ | 0.4  | 1.19           | 4440               |   |
| 25.5           | 47  | 5.5            | 38 | 5.5              | M6 | 3.5            | 0.1  | 500, 1000, 1500, 2000  | $1.23 \times 10^{-7}$ | 0.25   | 2.12           | 3370               |   |
| 65.5           | 47  | 5.5            | 38 | 5.5              | M6 | 3.5            | 0.1  | 500, 1000, 1500, 2000  | $1.23 \times 10^{-7}$ | 0.5  | 2.12           | 3370               |   |
| 31.5           | 57  | 6.6            | 46 | 7                | M6 | 3.5            | 0.1  | 1000, 1500, 2000, 3000 | $3.01 \times 10^{-7}$ | 0.45   | 3.34           | 2690               |   |
| 81.5           | 57  | 6.6            | 46 | 7                | M6 | 3.5            | 0.1  | 1000, 1500, 2000, 3000 | $3.01 \times 10^{-7}$ | 0.85   | 3.34           | 2690               |   |
| 37.5           | 71  | 9              | 56 | 9                | M6 | 3.8            | 0.14 | 1000, 2000, 3000, 4000 | $6.24 \times 10^{-7}$ | 0.8  | 4.84           | 2240               |   |
| 97.5           | 71  | 9              | 56 | 9                | M6 | 3.8            | 0.14 | 1000, 2000, 3000, 4000 | $6.24 \times 10^{-7}$ | 1.7  | 4.84           | 2240               |   |
| 50.5           | 93  | 11             | 74 | 9                | M6 | 5.4            | 0.17 | 1000, 1500, 2000, 3000 | $1.97 \times 10^{-6}$ | 2.1  | 8.66           | 1670               |   |
| 130.5          | 93  | 11             | 74 | 9                | M6 | 5.4            | 0.17 | 1000, 1500, 2000, 3000 | $1.97 \times 10^{-6}$ | 3.67   | 8.66           | 1670               |   |
| 64             | 112 | 14             | 92 | 10               | M6 | 5.4            | 0.2  | 1500, 3000             | $4.82 \times 10^{-6}$ | 3.5  | 13.86          | 1340               |   |
| 164            | 112 | 14             | 92 | 10               | M6 | 5.4            | 0.2  | 1500, 3000             | $4.82 \times 10^{-6}$ | 6.4  | 13.86          | 1340               |   |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **■15-344** for further details.

# CNF No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.  | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows × turns | Basic load rating |                 | Rigidity<br>K | Nut dimensions      |                                   |                                  |    |                |
|------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------|---------------|---------------------|-----------------------------------|----------------------------------|----|----------------|
|            |                                 |            |                                      |                             |  | Ca                | C <sub>0a</sub> |               | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | H  | B <sub>1</sub> |
|            |                                 |            |                                      |                             |  | kN                | kN              | N/μm          |                     |                                   |                                  |    |                |
| CNF 1530-6 | 15                              | 30         | 15.75                                | 12.5                        | 4 × 1.6                                | 10.1              | 24.7            | 310           | 32                  | 53                                | 63                               | 10 | 47             |
| CNF 2040-6 | 20                              | 40         | 20.75                                | 17.5                        | 4 × 1.65                               | 12                | 34.4            | 400           | 37                  | 57                                | 81                               | 10 | 65             |
| CNF 2550-6 | 25                              | 50         | 26                                   | 21.9                        | 4 × 1.65                               | 18.9              | 53.9            | 460           | 45                  | 69                                | 102                              | 12 | 81.5           |
| CNF 3060-6 | 30                              | 60         | 31.25                                | 26.4                        | 4 × 1.65                               | 26.2              | 77.7            | 600           | 55                  | 89                                | 122                              | 15 | 97             |


## Model number coding

**CNF2040-6 ZZ +1500L C7 T H1K**

|           |   |                                    |                                 |                         |                                   |
|-----------|---|------------------------------------|---------------------------------|-------------------------|-----------------------------------|
| Model No. | Contamination protection accessory symbol <sup>(*)1</sup> | Overall screw shaft length (in mm) | Accuracy symbol <sup>(*)2</sup> | Symbol for rolled shaft | Recommended shaft ends shape code |
|-----------|---|------------------------------------|---------------------------------|-------------------------|-----------------------------------|

(\*)1 See **A15-334**. (\*)2 See **A15-12**.

## Transport Ball Screw




Unit: mm

|  | Nut dimensions |                |                  |    |                        | Axial clearance | Standard shaft length  | Screw shaft inertial moment<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|----------------|----------------|------------------|----|------------------------|-----------------|------------------------|--|----------------|--------------------|---|
|  | PCD            | d <sub>1</sub> | Lubrication hole |    | Seal<br>M <sub>1</sub> |                 |                        |  |                |                    |   |
|  |                |                | N <sub>1</sub>   | A  |                        |                 |                        |  |                |                    |   |
|  | 43             | 5.5            | 5                | M6 | 3.5                    | 0.1             | 500, 1000, 1500        | $3.90 \times 10^{-8}$                                | 0.42           | 1.19               | 4440  |
|  | 47             | 5.5            | 5.5              | M6 | 3.5                    | 0.1             | 500, 1000, 1500, 2000  | $1.23 \times 10^{-8}$                                | 0.5            | 2.12               | 3370  |
|  | 57             | 6.6            | 7                | M6 | 3.5                    | 0.1             | 1000, 1500, 2000, 3000 | $3.01 \times 10^{-7}$                                | 0.85           | 3.34               | 2690  |
|  | 71             | 9              | 9                | M6 | 3.8                    | 0.14            | 1000, 2000, 3000, 4000 | $6.24 \times 10^{-7}$                                | 1.7            | 4.84               | 2240  |

Note) The overall length of the nut will increase when equipping the QZ lubricating device. See **A15-344** for further details.

# MTF (Unfinished Shaft Ends) No Preload

|          |       |
|----------|-------|
| DN value | 50000 |
|----------|-------|



| Model No.    | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows×turns | Basic load rating |           | Rigidity<br>K<br>N/μm |                     |                                   |
|--------------|---------------------------------|------------|--------------------------------------|-----------------------------|--------------------------------------|-------------------|-----------|-----------------------|---------------------|-----------------------------------|
|              |                                 |            |                                      |                             |                                      | Ca<br>kN          | Cca<br>kN |                       | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> |
| MTF 0601-3.7 | 6                               | 1          | 6.15                                 | 5.3                         | 1×3.7                                | 0.7               | 1.2       | 70                    | 13                  | 30                                |
| MTF 0802-3.7 | 8                               | 2          | 8.3                                  | 6.6                         | 1×3.7                                | 2.1               | 3.8       | 90                    | 20                  | 40                                |
| MTF 1002-3.7 | 10                              | 2          | 10.3                                 | 8.6                         | 1×3.7                                | 2.3               | 4.8       | 110                   | 23                  | 43                                |
| MTF 1202-3.7 | 12                              | 2          | 12.3                                 | 10.6                        | 1×3.7                                | 2.5               | 5.8       | 130                   | 25                  | 47                                |

## Model number coding

**MTF 08 02 -3.7 +250L C7 T**

Model No.

Screw shaft  
outer diameter  
(in mm)

Lead  
(in mm)


Overall shaft length  
(in mm)

Symbol for ball screw shaft

Accuracy symbol (No symbol for Normal Grade)

Note) Model MTF is only sold as sets (ball screw nut and screw shaft).  
Model MTF is applied only with anti-rust oil.

# Transport Ball Screw




Unit: mm


| Nut dimensions          |   |       |      |       |       |      | Axial clearance | Standard shaft length | $l_1$                  | Screw shaft inertial moment<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|-------------------------|---|-------|------|-------|-------|------|-----------------|-----------------------|------------------------|--|----------------|--------------------|---|
| Overall length<br>$L_1$ | H | $B_1$ | PCD  | $d_1$ | $T_w$ |      |                 |                       |                        |  |                |                    |   |
| 21                      | 5 | 16    | 21.5 | 3.4   | 17    | 0.05 | 150             | 100                   | $9.99 \times 10^{-10}$ | 0.03   | 0.19           | 3500               |   |
|                         |   |       |      |       |       |      | 250             | 200                   |                        |  |                |                    |   |
| 28                      | 6 | 22    | 30   | 4.5   | 24    | 0.05 | 150             | 95                    | $3.16 \times 10^{-9}$  | 0.08   | 0.31           | 3500               |   |
|                         |   |       |      |       |       |      | 250             | 195                   |                        |  |                |                    |   |
| 28                      | 6 | 22    | 33   | 4.5   | 27    | 0.05 | 200             | 140                   | $7.71 \times 10^{-9}$  | 0.1  | 0.52           | 3500               |   |
|                         |   |       |      |       |       |      | 300             | 240                   |                        |  |                |                    |   |
| 30                      | 8 | 22    | 36   | 5.5   | 29    | 0.05 | 200             | 140                   | $1.6 \times 10^{-8}$   | 0.13   | 0.77           | 3500               |   |
|                         |   |       |      |       |       |      | 300             | 240                   |                        |  |                |                    |   |

# MTF No Preload

|          |       |
|----------|-------|
| DN value | 50000 |
|----------|-------|



Nut type I



Nut type II

| Model No.      | Screw shaft outer diameter<br>d | Lead<br>Ph | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | No. of loaded circuits<br>Rows X turns | Basic load rating |                 | Rigidity<br>K | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> |
|----------------|---------------------------------|------------|--------------------------------------|-----------------------------|--|-------------------|-----------------|---------------|---------------------|-----------------------------------|----------------------------------|
|                |                                 |            |                                      |                             |  | Ca                | C <sub>0a</sub> |               |                     |                                   |                                  |
|                |                                 |            |                                      |                             |  | kN                | kN              | N/μm          |                     |                                   |                                  |
| * MTF 0601-3.7 | 6                               | 1          | 6.15                                 | 5.3                         | 1×3.7                                  | 0.7               | 1.2             | 70            | 13                  | 30                                | 21                               |
| MTF 0801-3.7   | 8                               | 1          | 8.15                                 | 7.3                         | 1×3.7                                  | 0.78              | 1.65            | 95            | 16                  | 29                                | 17                               |
| * MTF 0802-3.7 | 8                               | 2          | 8.3                                  | 6.6                         | 1×3.7                                  | 2.1               | 3.8             | 90            | 20                  | 40                                | 28                               |
| MTF 0805-2.7   | 8                               | 5          | 8.3                                  | 6.6                         | 1×2.7                                  | 1.85              | 3               | 82            | 18                  | 31                                | 28                               |
| * MTF 1002-3.7 | 10                              | 2          | 10.3                                 | 8.6                         | 1×3.7                                  | 2.3               | 4.8             | 110           | 23                  | 43                                | 28                               |
| MTF 1004-2.7   | 10                              | 4          | 10.3                                 | 8.2                         | 1×2.7                                  | 3                 | 5.2             | 104           | 24                  | 41                                | 28                               |
| * MTF 1202-3.7 | 12                              | 2          | 12.3                                 | 10.6                        | 1×3.7                                  | 2.5               | 5.8             | 130           | 25                  | 47                                | 30                               |
| MTF 1402-3.7   | 14                              | 2          | 14.3                                 | 12.6                        | 1×3.7                                  | 3.2               | 7.5             | 176           | 26                  | 45                                | 25                               |

### Model number coding

**MTF 0802-3.7 +250L C7 T**


Model No.

Overall screw shaft length (in mm)

Symbol for rolled shaft

Accuracy code: (No code for Normal Grade)

## Transport Ball Screw



Unit: mm

| Nut dimensions |                |      |                |    |          |      | Axial clearance | Standard shaft length  | Screw shaft inertial moment<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|----------------|----------------|------|----------------|----|----------|------|-----------------|------------------------|--|----------------|--------------------|---|
| H              | B <sub>1</sub> | PCD  | d <sub>1</sub> | Tw | Nut type |      |                 |                        |  |                |                    |   |
| 5              | 16             | 21.5 | 3.4            | 17 | I        | 0.05 | 150, 250        | $9.99 \times 10^{-10}$ | 0.03   | 0.19           | 3500               |   |
| 4              | 13             | 23   | 3.4            | 18 | II       | 0.05 | —               | $3.16 \times 10^{-9}$  | 0.02   | 0.36           | 3500               |   |
| 6              | 22             | 30   | 4.5            | 24 | I        | 0.05 | 150, 250        | $3.16 \times 10^{-9}$  | 0.08   | 0.31           | 3500               |   |
| 4              | 24             | 25   | 3.4            | 20 | II       | 0.05 | —               | $3.16 \times 10^{-9}$  | 0.05   | 0.33           | 3500               |   |
| 6              | 22             | 33   | 4.5            | 27 | I        | 0.05 | 200, 300        | $7.71 \times 10^{-9}$  | 0.1  | 0.52           | 3500               |   |
| 5              | 23             | 33   | 4.5            | 26 | II       | 0.05 | —               | $7.71 \times 10^{-9}$  | 0.09   | 0.52           | 3500               |   |
| 8              | 22             | 36   | 5.5            | 29 | I        | 0.05 | 200, 300        | $1.60 \times 10^{-8}$  | 0.13   | 0.77           | 3500               |   |
| 6              | 19             | 36   | 5.5            | 28 | II       | 0.05 | —               | $2.96 \times 10^{-8}$  | 0.08   | 1.07           | 3500               |   |






Note) Model MTF cannot be attached with seal.

For the MTF models marked with an asterisk in the specification table, nuts are processed with AP-C Treatment as standard. For details, see [B0-20](#).

Model MTF is only sold as sets (ball screw nut and screw shaft).

Model MTF is applied only with anti-rust oil.

# Rotary Nut Ball Screw

| Series     | Type            |  | Features                 |  |
|------------|-----------------|--|--------------------------|--|
| Rotary Nut | DIR             |   | Nut rotation, preload    |  |
|            | BLR             |   | Nut rotation, no preload |  |
|            | BLR<br>(Rolled) |   | Nut rotation, no preload |  |
|            | BNS             |   | Ball screw / spline      |  |
|            | NS              |  |                          |  |



## Rotary Nut Ball Screw

|  | Caged ball | Compact Nut | Miniature | High load capacity | Offset Preload | DN Value | Shaft diameter (mm) | Lead (mm) | Page No.       |
|--|------------|-------------|-----------|--------------------|----------------|----------|---------------------|-----------|----------------|
|  |            |             |           |                    |                | 70000    | 16 to 40            | 5 to 12   | <b>A15-274</b> |
|  |            |             |           |                    |                | 70000    | 16 to 50            | 16 to 50  | <b>A15-276</b> |
|  |            |             |           |                    |                | 70000    | 16 to 50            | 16 to 50  | <b>A15-278</b> |
|  |            |             |           |                    |                | 70000    | 8 to 50             | 12 to 50  | <b>A15-284</b> |
|  |            |             |           |                    | <b>A15-286</b> |          |                     |           |                |

## Standard combinations of outer diameters and leads of the screw shafts

| Shaft diameter | Lead |     |     |     |           |           |                                 |  |
|----------------|------|-----|-----|-----|-----------|-----------|---------------------------------|--|
|                | 4    | 5   | 6   | 10  | 12        | 15        | 16                              |  |
| 8              |      |     |     |     | BNS<br>NS |           |                                 |  |
| 10             |      |     |     |     |           | BNS<br>NS |                                 |  |
| 14             |      |     |     |     |           |           |                                 |  |
| 16             |      | DIR |     |     |           |           | BLR<br>BLR(Rolled)<br>BNS<br>NS |  |
| 20             |      | DIR |     |     |           |           |                                 |  |
| 25             |      | DIR |     | DIR |           |           |                                 |  |
| 28             |      |     |     |     |           |           |                                 |  |
| 32             |      | DIR | DIR | DIR |           |           |                                 |  |
| 36             |      |     |     | DIR |           |           |                                 |  |
| 40             |      |     |     | DIR | DIR       |           |                                 |  |
| 50             |      |     |     |     |           |           |                                 |  |

## Rotary Nut Ball Screw

Unit: mm


| Lead |                                 |                                 |    |                                 |                    |                                 |                                 |
|------|---------------------------------|---------------------------------|----|---------------------------------|--------------------|---------------------------------|---------------------------------|
|      | 20                              | 25                              | 30 | 32                              | 36                 | 40                              | 50                              |
|      |                                 |                                 |    |                                 |                    |                                 |                                 |
|      |                                 |                                 |    |                                 |                    |                                 |                                 |
|      |                                 |                                 |    |                                 |                    |                                 |                                 |
|      |                                 |                                 |    |                                 |                    |                                 |                                 |
|      | BLR<br>BLR(Rolled)<br>BNS<br>NS |                                 |    |                                 |                    |                                 |                                 |
|      |                                 | BLR<br>BLR(Rolled)<br>BNS<br>NS |    |                                 |                    |                                 |                                 |
|      |                                 |                                 |    |                                 |                    |                                 |                                 |
|      |                                 |                                 |    | BLR<br>BLR(Rolled)<br>BNS<br>NS |                    |                                 |                                 |
|      |                                 |                                 |    |                                 | BLR<br>BLR(Rolled) |                                 |                                 |
|      |                                 |                                 |    |                                 |                    | BLR<br>BLR(Rolled)<br>BNS<br>NS |                                 |
|      |                                 |                                 |    |                                 |                    |                                 | BLR<br>BLR(Rolled)<br>BNS<br>NS |

Ball Screw

## Accuracy Standards

### [Model DIR]

The accuracy of model DIR is compliant with the JIS standard JIS B 1192(ISO 3408) except for the radial runout of the circumference of the ball screw nut from the screw axis (D) and the perpendicularity of the flange-mounting surface against the screw axis (C).




Unit: mm

| Accuracy grades | C3    |       | C5    |       | C7    |       |
|-----------------|-------|-------|-------|-------|-------|-------|
|                 | C     | D     | C     | D     | C     | D     |
| DIR 16□□        | 0.013 | 0.017 | 0.016 | 0.020 | 0.023 | 0.035 |
| DIR 20□□        | 0.013 | 0.017 | 0.016 | 0.020 | 0.023 | 0.035 |
| DIR 25□□        | 0.015 | 0.020 | 0.018 | 0.024 | 0.023 | 0.035 |
| DIR 32□□        | 0.015 | 0.020 | 0.018 | 0.024 | 0.023 | 0.035 |
| DIR 36□□        | 0.016 | 0.021 | 0.019 | 0.025 | 0.024 | 0.036 |
| DIR 40□□        | 0.018 | 0.026 | 0.021 | 0.033 | 0.026 | 0.036 |


**[Model BLR]**

The accuracy of model BLR is compliant with the JIS standard JIS B 1192(ISO 3408) except for the radial runout of the circumference of the ball screw nut from the screw axis (D) and the perpendicularity of the flange-mounting surface against the screw axis (C).



Unit: mm

| Lead angle accuracy | C3    |       | C5    |       | C7    |       |
|---------------------|-------|-------|-------|-------|-------|-------|
| Accuracy grades     | C3    |       | C5    |       | C7    |       |
| Model No.           | C     | D     | C     | D     | C     | D     |
| BLR 1616            | 0.013 | 0.017 | 0.016 | 0.020 | 0.023 | 0.035 |
| BLR 2020            | 0.013 | 0.017 | 0.016 | 0.020 | 0.023 | 0.035 |
| BLR 2525            | 0.015 | 0.020 | 0.018 | 0.024 | 0.023 | 0.035 |
| BLR 3232            | 0.015 | 0.020 | 0.018 | 0.024 | 0.023 | 0.035 |
| BLR 3636            | 0.016 | 0.021 | 0.019 | 0.025 | 0.024 | 0.036 |
| BLR 4040            | 0.018 | 0.026 | 0.021 | 0.033 | 0.026 | 0.046 |
| BLR 5050            | 0.018 | 0.026 | 0.021 | 0.033 | 0.026 | 0.046 |



Unit: mm

| Lead angle accuracy | C7, C8, C10 |       |
|---------------------|-------------|-------|
| Accuracy grades     | C10         |       |
| Model No.           | C           | D     |
| BLR 1616            | 0.035       | 0.065 |
| BLR 2020            | 0.035       | 0.065 |
| BLR 2525            | 0.035       | 0.065 |
| BLR 3232            | 0.035       | 0.065 |
| BLR 3636            | 0.036       | 0.066 |
| BLR 4040            | 0.046       | 0.086 |
| BLR 5050            | 0.046       | 0.086 |

### ● Model BNS-V/NS-V

The Ball Screw/Spline is manufactured with the following specifications.

#### [Ball Screw]

Axial clearance : 0 mm to 0.01 mm (G1)

Lead angle accuracy : C5

(For detailed specifications, see **A15-12**, **A15-19**.)

#### [Ball Spline]

Clearance in the rotational direction : 0 or less (CL: light preload)

(For detailed specifications, see **A3-30**.)

Accuracy grade : class H

(For detailed specifications, see **A3-34**.)




Table 1: Radial Runout of the Spline Nut Outer Diameter in Relation to the Shaft Journals

Unit: mm

| Overall shaft length |       | Shaft diameter    |           |
|----------------------|-------|-------------------|-----------|
| Above                | Up to | $\phi 16/\phi 20$ | $\phi 25$ |
| —                    | 200   | 0.034             | 0.032     |
| 200                  | 315   | 0.045             | 0.039     |
| 315                  | 400   | 0.053             | 0.044     |
| 400                  | 500   | 0.062             | 0.050     |
| 500                  | 630   | 0.075             | 0.057     |
| 630                  | 800   | 0.092             | 0.068     |

## ● Model BNS/NS

### [Ball Screw]

Axial clearance : 0 or less

Lead angle accuracy : C5

(For detailed specifications, see **A15-12**, **A15-19**.)


### [Ball Spline]

Clearance in the rotational direction : 0 or less (CL: light preload)


(For detailed specifications, see **A3-30**.)

Accuracy grade : class H

(For detailed specifications, see **A3-34**.)



Model BNS



Model NS


Unit: mm

| Model No.           | C     | D     | E     | F     | H     | I     |
|---------------------|-------|-------|-------|-------|-------|-------|
| BNS 0812<br>NS 0812 | 0.014 | 0.016 | 0.014 | 0.017 | 0.010 | 0.013 |
| BNS 1015<br>NS 1015 | 0.014 | 0.016 | 0.014 | 0.017 | 0.010 | 0.013 |
| BNS 1616<br>NS 1616 | 0.016 | 0.020 | 0.018 | 0.021 | 0.013 | 0.016 |
| BNS 2020<br>NS 2020 | 0.016 | 0.020 | 0.018 | 0.021 | 0.013 | 0.016 |
| BNS 2525<br>NS 2525 | 0.018 | 0.024 | 0.021 | 0.021 | 0.016 | 0.016 |
| BNS 3232<br>NS 3232 | 0.018 | 0.024 | 0.021 | 0.021 | 0.016 | 0.016 |
| BNS 4040<br>NS 4040 | 0.021 | 0.033 | 0.025 | 0.025 | 0.019 | 0.019 |
| BNS 5050<br>NS 5050 | 0.021 | 0.033 | 0.025 | 0.025 | 0.019 | 0.019 |




## Example of Assembly

### [Example of Mounting Ball Screw Nut Model DIR]



Installation to the housing can be performed on the end face of the outer ring flange.

### [Example of Mounting Ball Screw Nut Model BLR]



Standard installation method


Inverted flange

Note) If the flange is to be inverted, indicate "K" in the model number. (applicable only to model BLR)

Example: BLR 2020-3.6 K UU

Symbol for inverted flange (No symbol for standard flange orientation)

### [Important note concerning model BLR]



Note) Since the outer rings are separable, it is necessary to include an internal diameter tolerance in the nut bracket so that the outer ring on the side opposite from the flange does not shift. (H7 is recommended.)

### [Example of Mounting Model BLR on the Table]

- (1) Screw shaft free, ball screw nut fixed  
(Suitable for a long table)




Fig.1 Example of Installation on the Table (Ball Screw Nut Fixed)

- (2) Ball screw nut free, screw shaft fixed  
(Suitable for a short table and a long stroke)





Fig.2 Example of Installation on the Table (Screw Shaft Fixed)

Note) A design incorporating a tension mechanism is needed when using a timing belt. For belt tensions, see the belt manufacturer's catalog. When used with a long stroke, apply tension to the screw shaft to reduce oscillations.


## Action Patterns

### [Model BNS Basic Actions]







| Motion          | Action direction                           | Input               |                             | Shaft motion                              |  |
|-----------------|--|---------------------|-----------------------------|---|--|
|                 |  | Ball screw pulley   | Ball spline pulley          | Vertical direction (speed)                | Rotational direction (rotation speed)        |
| 1. Vertical<br> | (1) Vertical direction $\rightarrow$ down  | $N_1$<br>(Forward)  | 0                           | $V = N_1 \cdot \ell$<br>( $N_1 \neq 0$ )  | 0  |
|                 | Rotational direction $\rightarrow$ 0       |                     |                             |   |  |
|                 | (2) Vertical direction $\rightarrow$ up    | $-N_1$<br>(Reverse) | 0                           | $V = -N_1 \cdot \ell$<br>( $N_1 \neq 0$ ) | 0  |
|                 | Rotational direction $\rightarrow$ 0       |                     |                             |   |  |
| 2. Rotation<br> | (1) Vertical direction $\rightarrow$ 0     | $N_1$               | $N_2$<br>(Forward)          | 0   | $N_2$ (Forward)<br>( $N_1 = N_2 \neq 0$ )    |
|                 | Rotational direction $\rightarrow$ forward |                     |                             |   |  |
|                 | (2) Vertical direction $\rightarrow$ 0     | $-N_1$              | $-N_2$<br>(Reverse)         | 0   | $-N_2$ (Reverse)<br>( $-N_1 = -N_2 \neq 0$ ) |
|                 | Rotational direction $\rightarrow$ reverse |                     |                             |   |  |
| 3. Spiral<br>   | (1) Vertical direction $\rightarrow$ up    | 0                   | $N_2$<br>( $N_2 \neq 0$ )   | $V = N_2 \cdot \ell$                      | $N_2$<br>(Forward)                           |
|                 | Rotational direction $\rightarrow$ forward |                     |                             |   |  |
|                 | (2) Vertical direction $\rightarrow$ down  | 0                   | $-N_2$<br>( $-N_2 \neq 0$ ) | $V = -N_2 \cdot \ell$                     | $-N_2$<br>(Reverse)                          |
|                 | Rotational direction $\rightarrow$ reverse |                     |                             |   |  |

## [Model NS Basic Actions]





| Motion          | Action direction | Input                       | Shaft motion               |   |
|-----------------|------------------|-----------------------------|----------------------------|---|
|                 |                  | Ball screw pulley           | Vertical direction (speed) |   |
| 1. Vertical<br> | (1)              | Vertical direction<br>→down | $N_1$<br>(Forward)         | $V=N_1 \cdot \ell$<br>( $N_1 \neq 0$ )  |
|                 | (2)              | Vertical direction<br>→up   | $-N_1$<br>(Reverse)        | $V=-N_1 \cdot \ell$<br>( $N_1 \neq 0$ ) |

## [Model BNS Extended Actions]



| Motion  | Action direction | Input  |                              | Shaft motion                                |   |   |
|---|------------------|--|------------------------------|---|---|---|
|   |                  | Ball screw pulley                                      | Ball spline pulley           | Vertical direction (speed)                  | Rotational direction (rotational speed) |   |
| 1. Up→down→forward<br>→up→down→reverse<br> | (1)              | Vertical direction→up<br>-N <sub>1</sub><br>(Reverse)  | 0                            | V=-N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0) | 0                                       |   |
|   | (2)              | Vertical direction→down<br>N <sub>1</sub><br>(Forward) | 0                            | V=N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0)  | 0                                       |   |
|   | (3)              | Rotational direction→forward<br>N <sub>1</sub>         | N <sub>2</sub><br>(Forward)  | 0   | 0                                       | N <sub>2</sub> (Forward)<br>(N <sub>1</sub> =N <sub>2</sub> ≠0)   |
|   | (4)              | Vertical direction→up<br>-N <sub>1</sub>               | 0                            | V=-N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0) | 0                                       |   |
|   | (5)              | Vertical direction→down<br>N <sub>1</sub>              | 0                            | V=N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0)  | 0                                       |   |
|   | (6)              | Rotational direction→reverse<br>-N <sub>1</sub>        | -N <sub>2</sub><br>(Reverse) | 0   | 0                                       | -N <sub>2</sub> (Reverse)<br>(-N <sub>1</sub> =N <sub>2</sub> ≠0) |
| 2. Down→up→forward<br>→down→up→reverse<br> | (1)              | Vertical direction→down<br>N <sub>1</sub>              | 0                            | V=N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0)  | 0                                       |   |
|   | (2)              | Vertical direction→up<br>-N <sub>1</sub>               | 0                            | V=-N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0) | 0                                       |   |
|   | (3)              | Rotational direction→forward<br>N <sub>1</sub>         | N <sub>2</sub>               | 0   | 0                                       | N <sub>2</sub><br>(N <sub>1</sub> =N <sub>2</sub> ≠0)             |
|   | (4)              | Vertical direction→down<br>N <sub>1</sub>              | 0                            | V=N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0)  | 0                                       |   |
|   | (5)              | Vertical direction→up<br>-N <sub>1</sub>               | 0                            | V=-N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0) | 0                                       |   |
|   | (6)              | Rotational direction→reverse<br>-N <sub>1</sub>        | -N <sub>2</sub>              | 0   | 0                                       | -N <sub>2</sub><br>(-N <sub>1</sub> =N <sub>2</sub> ≠0)           |
| 3. Down→forward<br>→up→reverse<br>       | (1)              | Vertical direction→down<br>N <sub>1</sub>              | 0                            | V=N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0)  | 0                                       |   |
|   | (2)              | Rotational direction→forward<br>N <sub>1</sub>         | N <sub>2</sub>               | 0   | 0                                       | N <sub>2</sub><br>(N <sub>1</sub> =N <sub>2</sub> ≠0)             |
|   | (3)              | Vertical direction→up<br>-N <sub>1</sub>               | 0                            | V=-N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0) | 0                                       |   |
|   | (4)              | Rotational direction→reverse<br>-N <sub>1</sub>        | -N <sub>2</sub>              | 0   | 0                                       | -N <sub>2</sub><br>(-N <sub>1</sub> =N <sub>2</sub> ≠0)           |
| 4. Down→up<br>→reverse→forward<br>       | (1)              | Vertical direction→down<br>N <sub>1</sub>              | 0                            | V=N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0)  | 0                                       |   |
|   | (2)              | Vertical direction→up<br>-N <sub>1</sub>               | 0                            | V=-N <sub>1</sub> •ℓ<br>(N <sub>1</sub> ≠0) | 0                                       |   |
|   | (3)              | Rotational direction→reverse<br>-N <sub>1</sub>        | -N <sub>2</sub>              | 0   | 0                                       | -N <sub>2</sub><br>(-N <sub>1</sub> =N <sub>2</sub> ≠0)           |
|   | (4)              | Rotational direction→forward<br>N <sub>1</sub>         | N <sub>2</sub>               | 0   | 0                                       | N <sub>2</sub><br>(N <sub>1</sub> =N <sub>2</sub> ≠0)             |

## Example of Assembly



- Example of installing the ball screw nut input pulley and the spline nut input pulley, both outside the housing. The housing length is minimized.
- Example of installing the ball screw nut pulley inside the housing.

Fig.3 Example of Assembling Model BNS



- Example of installing the ball screw nut pulley outside the housing. The housing length is minimized.
- Example of installing the ball screw nut pulley inside the housing.

Fig.4 Example of Assembling Model NS

## Example of Use





Fig.5 Example of Using Model BNS

## Precautions on Use


### [Lubrication]

When lubricating the Rotary Ball Screw, attach the lubrication plate to the housing in advance.



Lubrication Methods

When lubricating the Ball Screw/Spline, attach the lubrication plate to the housing in advance.



Lubrication Methods



## Permissible Rotational Speeds for Rotary Ball Screws

The permissible rotational speeds for models DIR and BLR and rotary ball screws is restricted to whichever is lower of the support bearing permissible rotational speed, the DN value (70,000) and the critical speed of the screw. When using the product, do not exceed the permissible rotational speed.

Table1 Model DIR permissible rotational speed

Unit: min<sup>-1</sup>

| Model No. | Permissible Rotational Speed  |                           |                    |                 |
|-----------|-------------------------------|---------------------------|--------------------|-----------------|
|           | Ball Screw Unit               |                           | Support bearing    |                 |
|           | Calculated using shaft length | Calculated using DN value | Grease Lubrication | Oil Lubrication |
| DIR1605   | see <b>A15-32.</b>            | 4170                      | 4000               | 5400            |
| DIR2005   |                               | 3370                      | 3500               | 4700            |
| DIR2505   |                               | 2710                      | 2900               | 3900            |
| DIR2510   |                               | 2690                      | 2900               | 3900            |
| DIR3205   |                               | 2130                      | 2400               | 3300            |
| DIR3206   |                               | 2120                      | 2400               | 3300            |
| DIR3210   |                               | 2070                      | 2400               | 3300            |
| DIR3610   |                               | 1850                      | 2100               | 2800            |
| DIR4010   |                               | 1670                      | 1900               | 2600            |
| DIR4012   |                               | 1670                      | 1900               | 2600            |


Table2 Model BLR permissible rotational speed

Unit: min<sup>-1</sup>

| Model No. | Permissible Rotational Speed  |                           |                    |                 |
|-----------|-------------------------------|---------------------------|--------------------|-----------------|
|           | Ball Screw Unit               |                           | Support bearing    |                 |
|           | Calculated using shaft length | Calculated using DN value | Grease Lubrication | Oil Lubrication |
| BLR1616   | see <b>A15-32.</b>            | 4200                      | 4000               | 5400            |
| BLR2020   |                               | 3370                      | 3200               | 4300            |
| BLR2525   |                               | 2690                      | 2800               | 3700            |
| BLR3232   |                               | 2100                      | 2400               | 3300            |
| BLR3636   |                               | 1870                      | 2000               | 2700            |
| BLR4040   |                               | 1670                      | 1600               | 2200            |
| BLR5050   |                               | 1340                      | 1400               | 2000            |

# DIR With Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|




| Model No.  | Screw shaft outer diameter | Thread minor diameter | Lead | Ball center-to-center diameter | Basic load rating |                 | Rigidity |     |                |                 |                |                |
|------------|----------------------------|-----------------------|------|--------------------------------|-------------------|-----------------|----------|-----|----------------|-----------------|----------------|----------------|
|            |                            |                       |      |                                | Ca                | C <sub>0a</sub> |          | K   | Outer diameter | Flange diameter | Overall length | D <sub>3</sub> |
|            |                            |                       |      |                                |                   |                 |          |     |                |                 |                |                |
| DIR 1605-6 | 16                         | 13.2                  | 5    | 16.75                          | 7.4               | 13              | 310      | 48  | 64             | 79              | 36             |                |
| DIR 2005-6 | 20                         | 17.2                  | 5    | 20.75                          | 8.5               | 17.3            | 310      | 56  | 72             | 80              | 43.5           |                |
| DIR 2505-6 | 25                         | 22.2                  | 5    | 25.75                          | 9.7               | 22.6            | 490      | 66  | 86             | 88              | 52             |                |
| DIR 2510-4 | 25                         | 21.6                  | 10   | 26                             | 9                 | 18              | 330      | 66  | 86             | 106             | 52             |                |
| DIR 3205-6 | 32                         | 29.2                  | 5    | 32.75                          | 11.1              | 30.2            | 620      | 78  | 103            | 86              | 63             |                |
| DIR 3206-6 | 32                         | 28.4                  | 6    | 33                             | 14.9              | 37.1            | 630      | 78  | 103            | 97              | 63             |                |
| DIR 3210-6 | 32                         | 26.4                  | 10   | 33.75                          | 25.7              | 52.2            | 600      | 78  | 103            | 131             | 63             |                |
| DIR 3610-6 | 36                         | 30.5                  | 10   | 37.75                          | 28.8              | 63.8            | 710      | 92  | 122            | 151             | 72             |                |
| DIR 4010-6 | 40                         | 34.7                  | 10   | 41.75                          | 29.8              | 69.3            | 750      | 100 | 130            | 142             | 79.5           |                |
| DIR 4012-6 | 40                         | 34.4                  | 12   | 41.75                          | 30.6              | 72.3            | 790      | 100 | 130            | 167             | 79.5           |                |

## Model number coding

**DIR2005-6 RR G0 +520L C1**

Model number    Seal symbol (\*1)    Overall screw shaft length (in mm)  
 Symbol for clearance in the axial direction (\*2)    Accuracy symbol (\*3)

(\*1) See [A15-334](#). (\*2) See [A15-19](#). (\*3) See [A15-12](#).



Unit: mm

| Ball screw dimensions |                |                |                |                |                |    |                |    |    |                |  | Support bearing basic load rating |                 | Nut inertial moment   | Nut mass | Shaft mass | Permissible rotational speed |
|-----------------------|----------------|----------------|----------------|----------------|----------------|----|----------------|----|----|----------------|--|-----------------------------------|-----------------|-----------------------|----------|------------|------------------------------|
| D <sub>2</sub>        | B <sub>5</sub> | B <sub>4</sub> | B <sub>3</sub> | P <sub>1</sub> | P <sub>2</sub> | H  | B <sub>1</sub> | S  | t  | d <sub>1</sub> |  | Ca                                | C <sub>0a</sub> | kg·m <sup>2</sup>     | kg       | kg/m       | min <sup>-1</sup>            |
|                       |                |                |                |                |                |    |                |    |    |                |  | kN                                | kN              |                       |          |            |                              |
| 30                    | 8              | 21             | 50             | 56             | 30             | 6  | 15             | M4 | 6  | 4.5            |  | 8.7                               | 10.5            | 6.10×10 <sup>-5</sup> | 0.49     | 1.24       | 4170                         |
| 34                    | 9              | 21             | 50             | 64             | 36             | 6  | 15             | M5 | 8  | 4.5            |  | 9.7                               | 13.4            | 1.18×10 <sup>-4</sup> | 0.68     | 2.05       | 3370                         |
| 40                    | 13             | 25             | 50             | 75             | 43             | 7  | 18             | M6 | 10 | 5.5            |  | 12.7                              | 18.2            | 2.65×10 <sup>-4</sup> | 1.07     | 3.34       | 2710                         |
| 40                    | 11             | 25             | 70             | 75             | 43             | 7  | 18             | M6 | 10 | 5.5            |  | 12.7                              | 18.2            | 2.84×10 <sup>-4</sup> | 1.16     | 3.52       | 2690                         |
| 46                    | 11             | 25             | 50             | 89             | 53             | 8  | 17             | M6 | 10 | 6.6            |  | 13.6                              | 22.3            | 5.10×10 <sup>-4</sup> | 1.39     | 5.67       | 2130                         |
| 48                    | 11             | 25             | 61             | 89             | 53             | 8  | 17             | M6 | 10 | 6.6            |  | 13.6                              | 22.3            | 5.68×10 <sup>-4</sup> | 1.54     | 5.47       | 2120                         |
| 54                    | 11             | 25             | 95             | 89             | 53             | 8  | 17             | M6 | 10 | 6.6            |  | 13.6                              | 22.3            | 8.13×10 <sup>-4</sup> | 2.16     | 4.98       | 2070                         |
| 58                    | 14             | 33             | 104            | 105            | 61             | 10 | 23             | M8 | 12 | 9              |  | 20.4                              | 32.3            | 1.47×10 <sup>-3</sup> | 3.25     | 6.51       | 1850                         |
| 62                    | 14             | 33             | 95             | 113            | 67             | 10 | 23             | M8 | 12 | 9              |  | 21.5                              | 36.8            | 2.06×10 <sup>-3</sup> | 3.55     | 8.22       | 1670                         |
| 62                    | 14             | 33             | 120            | 113            | 67             | 10 | 23             | M8 | 12 | 9              |  | 21.5                              | 36.8            | 2.25×10 <sup>-3</sup> | 3.9      | 8.5        | 1670                         |

Note) The rigidity values in the table represent spring constants, each obtained from the load and the elastic deformation when providing a preload equal to 10% of the basic axial dynamic load rating (Ca) and applying an axial load three times greater than the pre-load.

These values do not include the rigidity of the components related to mounting the ball screw nut. Therefore, it is normally appropriate to regard roughly 80% of the value in the table as the actual value.


If the applied preload (Fa<sub>0</sub>) is not 0.1 Ca, the rigidity value (K<sub>n</sub>) is obtained from the following equation.

$$K_n = K \left( \frac{F_{a0}}{0.1C_a} \right)^3$$

K: Rigidity value in the dimensional table

# BLR (Precision Ball Screw) No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.    | Screw shaft outer diameter<br>d | Thread minor diameter<br>dc | Lead<br>Ph | Ball center-to-center diameter<br>dp | Basic load rating |                       | Outer diameter<br>D                | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | D <sub>3</sub>                     |
|--------------|---------------------------------|-----------------------------|------------|--------------------------------------|-------------------|-----------------------|------------------------------------|-----------------------------------|----------------------------------|------------------------------------|
|              |                                 |                             |            |                                      | Ca<br>kN          | C <sub>0a</sub><br>kN |                                    |                                   |                                  |                                    |
| BLR 1616-3.6 | 16                              | 13.7                        | 16         | 16.65                                | 7.1               | 14.3                  | 52 <sup>0</sup> <sub>-0.007</sub>  | 68                                | 43.5                             | 40 <sup>0</sup> <sub>-0.025</sub>  |
| BLR 2020-3.6 | 20                              | 17.5                        | 20         | 20.75                                | 11.1              | 24.7                  | 62 <sup>0</sup> <sub>-0.007</sub>  | 78                                | 54                               | 50 <sup>0</sup> <sub>-0.025</sub>  |
| BLR 2525-3.6 | 25                              | 21.9                        | 25         | 26                                   | 16.6              | 38.7                  | 72 <sup>0</sup> <sub>-0.007</sub>  | 92                                | 65                               | 58 <sup>0</sup> <sub>-0.03</sub>   |
| BLR 3232-3.6 | 32                              | 28.3                        | 32         | 33.25                                | 23.7              | 59.5                  | 80 <sup>0</sup> <sub>-0.007</sub>  | 105                               | 80                               | 66 <sup>0</sup> <sub>-0.03</sub>   |
| BLR 3636-3.6 | 36                              | 31.7                        | 36         | 37.4                                 | 30.8              | 78                    | 100 <sup>0</sup> <sub>-0.008</sub> | 130                               | 93                               | 80 <sup>0</sup> <sub>-0.03</sub>   |
| BLR 4040-3.6 | 40                              | 35.2                        | 40         | 41.75                                | 38.7              | 99.2                  | 110 <sup>0</sup> <sub>-0.008</sub> | 140                               | 98                               | 90 <sup>0</sup> <sub>-0.035</sub>  |
| BLR 5050-3.6 | 50                              | 44.1                        | 50         | 52.2                                 | 57.8              | 155                   | 120 <sup>0</sup> <sub>-0.008</sub> | 156                               | 126                              | 100 <sup>0</sup> <sub>-0.035</sub> |


## Model number coding

**BLR2020-3.6 K UU G1 +1000L C5**

Model number | Flange orientation symbol | Symbol for clearance in the axial direction<sup>(\*)2</sup> | Accuracy symbol<sup>(\*)3</sup>  
 Symbol for support bearing seal<sup>(\*)1</sup> | Overall screw shaft length (in mm)

(\*)1 UU: Seal attached on both ends No symbol: Without seal. (\*)2 See **A15-19**. (\*)3 See **A15-12**.

## Rotary Nut Ball Screw




Unit: mm

| Ball screw dimensions             |    |                |                |                |                |                |     |    |                |    |                      | Support bearing basic load rating |                         | Nut inertial moment<br>kg·m <sup>2</sup> | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|-----------------------------------|----|----------------|----------------|----------------|----------------|----------------|-----|----|----------------|----|----------------------|-----------------------------------|-------------------------|--|----------------|--------------------|---|
| D <sub>4</sub>                    | H  | B <sub>4</sub> | B <sub>5</sub> | T <sub>e</sub> | P <sub>1</sub> | P <sub>2</sub> | S   | t  | d <sub>1</sub> | θ° | C <sub>a</sub><br>kN | C <sub>0a</sub><br>kN             |                         |  |                |                    |   |
| 32 <sup>+0.025</sup> <sub>0</sub> | 5  | 27.5           | 9              | 2              | 60             | 25             | M4  | 12 | 4.5            | 40 | 19.4                 | 19.2                              | 4.80 × 10 <sup>-6</sup> | 0.38                                     | 1.41           | 4200               |   |
| 39 <sup>+0.025</sup> <sub>0</sub> | 6  | 34             | 11             | 2              | 70             | 31             | M5  | 16 | 4.5            | 40 | 26.8                 | 29.3                              | 1.44 × 10 <sup>-4</sup> | 0.68                                     | 2.25           | 3370               |   |
| 47 <sup>+0.025</sup> <sub>0</sub> | 8  | 43             | 12.5           | 3              | 81             | 38             | M6  | 19 | 5.5            | 40 | 28.2                 | 33.3                              | 3.23 × 10 <sup>-4</sup> | 1.1                                      | 3.52           | 2690               |   |
| 58 <sup>+0.03</sup> <sub>0</sub>  | 9  | 55             | 14             | 3              | 91             | 48             | M6  | 19 | 6.6            | 40 | 30                   | 39                                | 6.74 × 10 <sup>-4</sup> | 1.74                                     | 5.83           | 2100               |   |
| 66 <sup>+0.03</sup> <sub>0</sub>  | 11 | 62             | 17             | 3              | 113            | 54             | M8  | 22 | 9              | 40 | 56.4                 | 65.2                              | 1.68 × 10 <sup>-3</sup> | 3.2                                      | 7.34           | 1870               |   |
| 73 <sup>+0.03</sup> <sub>0</sub>  | 11 | 68             | 16.5           | 3              | 123            | 61             | M8  | 22 | 9              | 50 | 59.3                 | 74.1                              | 2.79 × 10 <sup>-3</sup> | 3.95                                     | 9.01           | 1670               |   |
| 90 <sup>+0.035</sup> <sub>0</sub> | 12 | 80             | 25             | 4              | 136            | 75             | M10 | 28 | 11             | 50 | 62.2                 | 83                                | 5.82 × 10 <sup>-3</sup> | 6.22                                     | 14.08          | 1340               |   |

Ball Screw

# BLR (Rolled Ball Screw) No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



| Model No.    | Screw shaft outer diameter<br>d | Thread minor diameter<br>dc | Lead<br>Ph | Ball center-to-center diameter<br>dp | Basic load rating |                 | Outer diameter<br>D                | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | D <sub>3</sub>                     |
|--------------|---------------------------------|-----------------------------|------------|--------------------------------------|-------------------|-----------------|------------------------------------|-----------------------------------|----------------------------------|------------------------------------|
|              |                                 |                             |            |                                      | Ca                | C <sub>0a</sub> |                                    |                                   |                                  |                                    |
|              |                                 |                             |            |                                      | kN                | kN              |                                    |                                   |                                  |                                    |
| BLR 1616-3.6 | 16                              | 13.7                        | 16         | 16.65                                | 5.8               | 12.9            | 52 <sup>0</sup> <sub>-0.007</sub>  | 68                                | 43.5                             | 40 <sup>0</sup> <sub>-0.025</sub>  |
| BLR 2020-3.6 | 20                              | 17.5                        | 20         | 20.75                                | 7.7               | 22.3            | 62 <sup>0</sup> <sub>-0.007</sub>  | 78                                | 54                               | 50 <sup>0</sup> <sub>-0.025</sub>  |
| BLR 2525-3.6 | 25                              | 21.9                        | 25         | 26                                   | 12.1              | 35              | 72 <sup>0</sup> <sub>-0.007</sub>  | 92                                | 65                               | 58 <sup>0</sup> <sub>-0.03</sub>   |
| BLR 3232-3.6 | 32                              | 28.3                        | 32         | 33.25                                | 17.3              | 53.9            | 80 <sup>0</sup> <sub>-0.007</sub>  | 105                               | 80                               | 66 <sup>0</sup> <sub>-0.03</sub>   |
| BLR 3636-3.6 | 36                              | 31.7                        | 36         | 37.4                                 | 22.4              | 70.5            | 100 <sup>0</sup> <sub>-0.008</sub> | 130                               | 93                               | 80 <sup>0</sup> <sub>-0.03</sub>   |
| BLR 4040-3.6 | 40                              | 35.2                        | 40         | 41.75                                | 28.1              | 89.8            | 110 <sup>0</sup> <sub>-0.008</sub> | 140                               | 98                               | 90 <sup>0</sup> <sub>-0.035</sub>  |
| BLR 5050-3.6 | 50                              | 44.1                        | 50         | 52.2                                 | 42.1              | 140.4           | 120 <sup>0</sup> <sub>-0.008</sub> | 156                               | 126                              | 100 <sup>0</sup> <sub>-0.035</sub> |

## Model number coding


**BLR2020-3.6 K UU +1000L C7 T**

|              |                                      |                                    |                              |
|--------------|--------------------------------------|------------------------------------|------------------------------|
| Model number | Flange orientation symbol            | Overall screw shaft length (in mm) | Symbol for rolled Ball Screw |
|              | Symbol for support bearing seal (*1) | Accuracy symbol (*2)               |                              |

(\*1) UU: seal attached on both ends; No symbol: without seal. (\*2) See **A15-12**.

Note) For clearance in the axial direction, see **A15-19**.

## Rotary Nut Ball Screw




Unit: mm

| Ball screw dimensions             |    |                |                |                |                |                |     |    |                |    |                      | Support bearing basic load rating |                         | Nut inertial moment<br>kg·m <sup>2</sup> | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|-----------------------------------|----|----------------|----------------|----------------|----------------|----------------|-----|----|----------------|----|----------------------|-----------------------------------|-------------------------|--|----------------|--------------------|---|
| D <sub>4</sub>                    | H  | B <sub>4</sub> | B <sub>5</sub> | T <sub>e</sub> | P <sub>1</sub> | P <sub>2</sub> | S   | t  | d <sub>1</sub> | θ° | C <sub>a</sub><br>kN | C <sub>0a</sub><br>kN             |                         |  |                |                    |   |
| 32 <sup>+0.025</sup> <sub>0</sub> | 5  | 27.5           | 9              | 2              | 60             | 25             | M4  | 12 | 4.5            | 40 | 19.4                 | 19.2                              | 4.80 × 10 <sup>-6</sup> | 0.38                                     | 1.35           | 4200               |   |
| 39 <sup>+0.025</sup> <sub>0</sub> | 6  | 34             | 11             | 2              | 70             | 31             | M5  | 16 | 4.5            | 40 | 26.8                 | 29.3                              | 1.44 × 10 <sup>-4</sup> | 0.68                                     | 2.17           | 3370               |   |
| 47 <sup>+0.025</sup> <sub>0</sub> | 8  | 43             | 12.5           | 3              | 81             | 38             | M6  | 19 | 5.5            | 40 | 28.2                 | 33.3                              | 3.23 × 10 <sup>-4</sup> | 1.1                                      | 3.41           | 2690               |   |
| 58 <sup>+0.03</sup> <sub>0</sub>  | 9  | 55             | 14             | 3              | 91             | 48             | M6  | 19 | 6.6            | 40 | 30                   | 39                                | 6.74 × 10 <sup>-4</sup> | 1.74                                     | 5.69           | 2100               |   |
| 66 <sup>+0.03</sup> <sub>0</sub>  | 11 | 62             | 17             | 3              | 113            | 54             | M8  | 22 | 9              | 40 | 56.4                 | 65.2                              | 1.68 × 10 <sup>-3</sup> | 3.2                                      | 7.12           | 1870               |   |
| 73 <sup>+0.03</sup> <sub>0</sub>  | 11 | 68             | 16.5           | 3              | 123            | 61             | M8  | 22 | 9              | 50 | 59.3                 | 74.1                              | 2.79 × 10 <sup>-3</sup> | 3.95                                     | 8.76           | 1670               |   |
| 90 <sup>+0.035</sup> <sub>0</sub> | 12 | 80             | 25             | 4              | 136            | 75             | M10 | 28 | 11             | 50 | 62.2                 | 83                                | 5.82 × 10 <sup>-3</sup> | 6.22                                     | 13.79          | 1340               |   |

Ball Screw

# BNS-V Compact Type: Linear-Rotary Motion No Preload

|          |        |
|----------|--------|
| DN value | 100000 |
|----------|--------|



Ball screw unit

## Ball screw unit

| Model No. | Screw shaft outer diameter<br>d | Screw shaft inner diameter<br>db | Lead<br>Ph | Ball screw dimensions |                       |                                      |                             |                     |                                   |                                  |                |    |      |   |
|-----------|---------------------------------|----------------------------------|------------|-----------------------|-----------------------|--------------------------------------|-----------------------------|---------------------|-----------------------------------|----------------------------------|----------------|----|------|---|
|           |                                 |                                  |            | Basic load rating     |                       | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | D <sub>3</sub> | AE | BE   | H |
|           |                                 |                                  |            | Ca<br>kN              | C <sub>0a</sub><br>kN |                                      |                             |                     |                                   |                                  |                |    |      |   |
| BNS 1616V | 16                              | 11                               | 16         | 4.6                   | 6.8                   | 16.65                                | 13.7                        | 42                  | 54                                | 38                               | 32.5           | 31 | 31   | 4 |
| BNS 2020V | 20                              | 14                               | 20         | 7.3                   | 11.7                  | 20.75                                | 17.5                        | 48                  | 64                                | 45                               | 39.5           | 37 | 36   | 6 |
| BNS 2525V | 25                              | 18                               | 25         | 8                     | 14.4                  | 25.35                                | 22.1                        | 56                  | 72                                | 55                               | 43.5           | 42 | 41.6 | 6 |

## Ball spline

| Model No. | Ball spline dimensions |                      |  |                       |                        |  |                                   |                                  |                |                 |                 |                |
|-----------|------------------------|----------------------|--|-----------------------|------------------------|--|-----------------------------------|----------------------------------|----------------|-----------------|-----------------|----------------|
|           | Basic load rating      |                      | Static permissible moment<br>M <sub>A</sub><br>N·m | Basic torque rating   |                        | Outer diameter<br>D <sub>7</sub><br>g6 | Flange diameter<br>D <sub>5</sub> | Overall length<br>L <sub>2</sub> | D <sub>6</sub> | AE <sub>1</sub> | BE <sub>1</sub> | H <sub>1</sub> |
|           | C<br>kN                | C <sub>0</sub><br>kN |  | C <sub>T</sub><br>N·m | C <sub>0T</sub><br>N·m |  |                                   |                                  |                |                 |                 |                |
| BNS 1616V | 8.4                    | 13.4                 | 77.4   | 42.9                  | 68.6                   | 42                                     | 54                                | 46.4                             | 32.5           | 27.5            | 28              | 4              |
| BNS 2020V | 10.5                   | 18.6                 | 144  | 66.4                  | 117.2                  | 48                                     | 64                                | 59                               | 36             | 31.5            | 32              | 6              |
| BNS 2525V | 15.9                   | 26.2                 | 230  | 125.3                 | 207                    | 56                                     | 72                                | 67                               | 43.5           | 39.5            | 40              | 6              |

Note) For K hollow shaft, please refer to the db dimension for the inner bore diameter of the shaft. If requested solid shaft is also available. See "Ball Spline" **A3-118** for details.

### Model number coding


## BNS2020V +500L C5

Model number    Overall shaft length (in mm)    Accuracy symbol (\*1)

(\*1) See **A15-12**.



## Rotary Nut Ball Screw




Unit: mm

|  | B <sub>4</sub> | B <sub>5</sub> | P <sub>1</sub> | P <sub>2</sub> | S  | t <sub>1</sub> | t <sub>2</sub> | d <sub>1</sub> | B <sub>6</sub> | d <sub>0</sub> | A <sub>1</sub> | Support bearing basic load rating |                       | Nut inertial moment<br>kg·m <sup>2</sup> | Screw shaft inertial moment<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|----------------|----------------|----------------|----------------|----|----------------|----------------|----------------|----------------|----------------|----------------|-----------------------------------|-----------------------|--|--|----------------|--------------------|---|
|  |                |                |                |                |    |                |                |                |                |                |                | C <sub>a</sub><br>kN              | C <sub>0a</sub><br>kN |  |  |                |                    |   |
|  | 18             | 9.7            | 48             | 25.5           | M3 | 8.2            | 6              | 3.4            | 5.8            | 2              | 35°            | 6.7                               | 8.6                   | 2.00 × 10 <sup>-5</sup>                  | 3.21 × 10 <sup>-8</sup>                              | 0.21           | 0.8                | 5000  |
|  | 21             | 12.2           | 56             | 31             | M4 | 10.2           | 8              | 4.5            | 7.2            | 2              | 35°            | 7.3                               | 10.6                  | 6.50 × 10 <sup>-5</sup>                  | 8.04 × 10 <sup>-8</sup>                              | 0.39           | 1.21               | 4810  |
|  | 21             | 13.2           | 64             | 36             | M5 | 10.2           | 8              | 4.5            | 15.3           | 3              | 35°            | 9.7                               | 13.4                  | 1.02 × 10 <sup>-4</sup>                  | 1.91 × 10 <sup>-7</sup>                              | 0.51           | 1.79               | 3940  |


Unit: mm

|  | B <sub>7</sub> | B <sub>8</sub> | P <sub>3</sub> | P <sub>4</sub> | S <sub>1</sub> | t <sub>3</sub> | t <sub>4</sub> | ds <sub>1</sub> | A <sub>2</sub> | B <sub>9</sub> | ds <sub>0</sub> | Support bearing basic load rating |                      | Nut inertial moment<br>kg·m <sup>2</sup> | Nut mass<br>kg |
|--|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-----------------|----------------|----------------|-----------------|-----------------------------------|----------------------|--|----------------|
|  |                |                |                |                |                |                |                |                 |                |                |                 | C <sub>a</sub><br>kN              | C <sub>0</sub><br>kN |  |                |
|  | 18             | 13             | 48             | 25             | M3             | 11.5           | 6              | 3.4             | 20°            | 5              | 2               | 5.2                               | 5.1                  | 1.80 × 10 <sup>-5</sup>                  | 0.19           |
|  | 21             | 15.8           | 56             | 30             | M4             | 11.8           | 6              | 4.5             | 25°            | 5.4            | 2               | 6.7                               | 6.4                  | 4.20 × 10 <sup>-5</sup>                  | 0.33           |
|  | 21             | 19.2           | 64             | 36             | M5             | 15.2           | 8              | 4.5             | 25°            | 7.6            | 3               | 7.4                               | 7.8                  | 9.80 × 10 <sup>-5</sup>                  | 0.49           |




# BNS-A Compact Type: Linear-Rotary Motion No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



Ball screw unit  
(Models BNS 1616A to 4040A)



Ball screw unit  
(Models BNS 0812A and 1015A)

## Ball screw unit

| Model No. | Screw shaft outer diameter<br>d | Screw shaft inner diameter<br>db | Lead<br>Ph | Ball screw dimensions |                       |                                      |                             |                     |                                   |                                  |                      |                      |
|-----------|---------------------------------|----------------------------------|------------|-----------------------|-----------------------|--------------------------------------|-----------------------------|---------------------|-----------------------------------|----------------------------------|----------------------|----------------------|
|           |                                 |                                  |            | Basic load rating     |                       | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | D <sub>3</sub><br>h7 | D <sub>4</sub><br>H7 |
|           |                                 |                                  |            | C <sub>a</sub><br>kN  | C <sub>0a</sub><br>kN |                                      |                             |                     |                                   |                                  |                      |                      |
| BNS 0812A | 8                               | —                                | 12         | 1.1                   | 1.8                   | 8.4                                  | 6.6                         | 32                  | 44                                | 28.5                             | 22                   | 19                   |
| BNS 1015A | 10                              | —                                | 15         | 1.7                   | 2.7                   | 10.5                                 | 8.3                         | 36                  | 48                                | 34.5                             | 26                   | 23                   |
| BNS 1616A | 16                              | 11                               | 16         | 3.9                   | 7.2                   | 16.65                                | 13.7                        | 48                  | 64                                | 40                               | 36                   | 32                   |
| BNS 2020A | 20                              | 14                               | 20         | 6.1                   | 12.3                  | 20.75                                | 17.5                        | 56                  | 72                                | 48                               | 43.5                 | 39                   |
| BNS 2525A | 25                              | 18                               | 25         | 9.1                   | 19.3                  | 26                                   | 21.9                        | 66                  | 86                                | 58                               | 52                   | 47                   |
| BNS 3232A | 32                              | 23                               | 32         | 13                    | 29.8                  | 33.25                                | 28.3                        | 78                  | 103                               | 72                               | 63                   | 58                   |
| BNS 4040A | 40                              | 29                               | 40         | 21.4                  | 49.7                  | 41.75                                | 35.2                        | 100                 | 130                               | 88                               | 79.5                 | 73                   |

## Ball spline

| Model No. | Ball spline dimensions |                      |  |                       |                        |  |                                   |                                  |                      |                 |
|-----------|------------------------|----------------------|--|-----------------------|------------------------|--|-----------------------------------|----------------------------------|----------------------|-----------------|
|           | Basic load rating      |                      | Static permissible moment<br>M <sub>A</sub><br>N·m | Basic torque rating   |                        | Outer diameter<br>D <sub>7</sub><br>g6 | Flange diameter<br>D <sub>5</sub> | Overall length<br>L <sub>2</sub> | D <sub>6</sub><br>h7 | BE <sub>1</sub> |
|           | C<br>kN                | C <sub>0</sub><br>kN |  | C <sub>T</sub><br>N·m | C <sub>0T</sub><br>N·m |  |                                   |                                  |                      |                 |
| BNS 0812A | 1.5                    | 2.6                  | 5.9  | 2                     | 2.9                    | 32                                     | 44                                | 25                               | 24                   | 16              |
| BNS 1015A | 2.7                    | 4.9                  | 15.7   | 3.9                   | 7.8                    | 36                                     | 48                                | 33                               | 28                   | 21              |
| BNS 1616A | 7.1                    | 12.6                 | 67.6   | 31.4                  | 34.3                   | 48                                     | 64                                | 50                               | 36                   | 31              |
| BNS 2020A | 10.2                   | 17.8                 | 118  | 56.8                  | 55.8                   | 56                                     | 72                                | 63                               | 43.5                 | 35              |
| BNS 2525A | 15.2                   | 25.8                 | 210  | 105                   | 103                    | 66                                     | 86                                | 71                               | 52                   | 42              |
| BNS 3232A | 20.5                   | 34                   | 290  | 180                   | 157                    | 78                                     | 103                               | 80                               | 63                   | 52              |
| BNS 4040A | 37.8                   | 60.5                 | 687  | 418                   | 377                    | 100                                    | 130                               | 100                              | 79.5                 | 64              |

Note) For K hollow shaft, please refer to the db dimension for the inner bore diameter of the shaft. If requested solid shaft is also available. See "Ball Spline" **A3-118** for details.


### Model number coding

## BNS2020A +500L C5

Model number      Overall shaft length (in mm)      Accuracy symbol (\*1)

(\*1) See **A15-12**.

## Rotary Nut Ball Screw




Unit: mm

|  | BE | H  | B <sub>4</sub> | B <sub>5</sub> | T <sub>e</sub> | P <sub>1</sub> | P <sub>2</sub> | S    | t    | d <sub>1</sub> | Support bearing basic load rating |                 | Nut inertial moment<br>kg·m <sup>2</sup> | Screw shaft inertial moment<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|----|----|----------------|----------------|----------------|----------------|----------------|------|------|----------------|-----------------------------------|-----------------|--|--|----------------|--------------------|---|
|  |    |    |                |                |                |                |                |      |      |                | Ca                                | C <sub>0a</sub> |  |  |                |                    |   |
|  | 19 | 3  | 10.5           | 7              | 1.5            | 38             | 14.5           | M2.6 | 10   | 3.4            | 0.8                               | 0.5             | 3.00×10 <sup>-6</sup>                    | 3.16×10 <sup>-9</sup>                                | 0.08           | 0.35               | 3500  |
|  | 23 | 3  | 10.5           | 8              | 1.5            | 42             | 18             | M3   | 11.5 | 3.4            | 0.9                               | 0.7             | 8.00×10 <sup>-6</sup>                    | 7.71×10 <sup>-9</sup>                                | 0.15           | 0.52               | 3500  |
|  | 32 | 6  | 21             | 10             | 2              | 56             | 25             | M4   | 13.5 | 4.5            | 8.7                               | 10.5            | 3.50×10 <sup>-6</sup>                    | 3.92×10 <sup>-8</sup>                                | 0.31           | 0.8                | 4200  |
|  | 39 | 6  | 21             | 11             | 2.5            | 64             | 31             | M5   | 16.5 | 4.5            | 9.7                               | 13.4            | 8.50×10 <sup>-6</sup>                    | 9.37×10 <sup>-8</sup>                                | 0.54           | 1.21               | 3370  |
|  | 47 | 7  | 25             | 13             | 3              | 75             | 38             | M6   | 20   | 5.5            | 12.7                              | 18.2            | 2.12×10 <sup>-4</sup>                    | 2.20×10 <sup>-7</sup>                                | 0.88           | 1.79               | 2690  |
|  | 58 | 8  | 25             | 14             | 3              | 89             | 48             | M6   | 21   | 6.6            | 13.6                              | 22.3            | 5.42×10 <sup>-4</sup>                    | 5.92×10 <sup>-7</sup>                                | 1.39           | 2.96               | 2100  |
|  | 73 | 10 | 33             | 16.5           | 3              | 113            | 61             | M8   | 24.5 | 9              | 21.5                              | 36.8            | 1.72×10 <sup>-3</sup>                    | 1.43×10 <sup>-8</sup>                                | 3.16           | 4.51               | 1670  |


Unit: mm

|  | H <sub>1</sub> | B <sub>6</sub> | B <sub>7</sub> | H <sub>2</sub> | P <sub>3</sub> | P <sub>4</sub> | S <sub>1</sub> ×t <sub>1</sub> | ds <sub>1</sub> | Support bearing basic load rating |                | Nut inertial moment<br>kg·m <sup>2</sup> | Nut mass<br>kg |
|--|----------------|----------------|----------------|----------------|----------------|----------------|--------------------------------|-----------------|-----------------------------------|----------------|--|----------------|
|  |                |                |                |                |                |                |                                |                 | C                                 | C <sub>0</sub> |  |                |
|  | 3              | 10.5           | 6              | 3              | 38             | 19             | M2.6×3                         | 3.4             | 0.69                              | 0.24           | 3.00×10 <sup>-6</sup>                    | 0.08           |
|  | 3              | 10.5           | 9              | —              | 42             | 23             | M3×4                           | 3.4             | 0.77                              | 0.3            | 8.00×10 <sup>-6</sup>                    | 0.13           |
|  | 6              | 21             | 10             | —              | 56             | 30             | M4×6                           | 4.5             | 6.7                               | 6.4            | 4.40×10 <sup>-6</sup>                    | 0.35           |
|  | 6              | 21             | 12             | —              | 64             | 36             | M5×8                           | 4.5             | 7.4                               | 7.8            | 9.90×10 <sup>-6</sup>                    | 0.51           |
|  | 7              | 25             | 13             | —              | 75             | 44             | M5×8                           | 5.5             | 9.7                               | 10.6           | 2.20×10 <sup>-4</sup>                    | 0.79           |
|  | 8              | 25             | 17             | —              | 89             | 54             | M6×10                          | 6.6             | 10.5                              | 12.5           | 5.17×10 <sup>-4</sup>                    | 1.25           |
|  | 10             | 33             | 20             | —              | 113            | 68             | M6×10                          | 9               | 16.5                              | 20.7           | 1.61×10 <sup>-3</sup>                    | 2.51           |



# BNS Heavy Load Type: Linear-Rotary Motion No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



Ball screw unit

## Ball screw unit

| Model No. | Screw shaft outer diameter<br>d | Screw shaft inner diameter<br>db | Lead<br>Ph | Ball screw dimensions |                 |                                      |                             |                                    |                                   |                                  |                |
|-----------|---------------------------------|----------------------------------|------------|-----------------------|-----------------|--------------------------------------|-----------------------------|------------------------------------|-----------------------------------|----------------------------------|----------------|
|           |                                 |                                  |            | Basic load rating     |                 | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | Outer diameter<br>D                | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | D <sub>3</sub> |
|           |                                 |                                  |            | Ca                    | C <sub>0a</sub> |                                      |                             |                                    |                                   |                                  |                |
| BNS 1616  | 16                              | 11                               | 16         | 3.9                   | 7.2             | 16.65                                | 13.7                        | 52 <sup>0</sup> <sub>-0.007</sub>  | 68                                | 43.5                             | 40             |
| BNS 2020  | 20                              | 14                               | 20         | 6.1                   | 12.3            | 20.75                                | 17.5                        | 62 <sup>0</sup> <sub>-0.007</sub>  | 78                                | 54                               | 50             |
| BNS 2525  | 25                              | 18                               | 25         | 9.1                   | 19.3            | 26                                   | 21.9                        | 72 <sup>0</sup> <sub>-0.007</sub>  | 92                                | 65                               | 58             |
| BNS 3232  | 32                              | 23                               | 32         | 13                    | 29.8            | 33.25                                | 28.3                        | 80 <sup>0</sup> <sub>-0.007</sub>  | 105                               | 80                               | 66             |
| BNS 4040  | 40                              | 29                               | 40         | 21.4                  | 49.7            | 41.75                                | 35.2                        | 110 <sup>0</sup> <sub>-0.008</sub> | 140                               | 98                               | 90             |
| BNS 5050  | 50                              | 36                               | 50         | 31.8                  | 77.6            | 52.2                                 | 44.1                        | 120 <sup>0</sup> <sub>-0.008</sub> | 156                               | 126                              | 100            |

## Ball spline

| Model No. | Ball spline dimensions |                |  |                     |                 |                                    |                                   |                                  |
|-----------|------------------------|----------------|--|---------------------|-----------------|------------------------------------|-----------------------------------|----------------------------------|
|           | Basic load rating      |                | Static permissible moment<br>M <sub>s</sub><br>N·m | Basic torque rating |                 | Outer diameter<br>D <sub>7</sub>   | Flange diameter<br>D <sub>5</sub> | Overall length<br>L <sub>2</sub> |
|           | C                      | C <sub>0</sub> |  | C <sub>T</sub>      | C <sub>0T</sub> |                                    |                                   |                                  |
| BNS 1616  | 7.1                    | 12.6           | 67.6   | 31.4                | 34.3            | 52 <sup>0</sup> <sub>-0.007</sub>  | 68                                | 50                               |
| BNS 2020  | 10.2                   | 17.8           | 118  | 56.8                | 55.8            | 56 <sup>0</sup> <sub>-0.007</sub>  | 72                                | 63                               |
| BNS 2525  | 15.2                   | 25.8           | 210  | 105                 | 103             | 62 <sup>0</sup> <sub>-0.007</sub>  | 78                                | 71                               |
| BNS 3232  | 20.5                   | 34             | 290  | 180                 | 157             | 80 <sup>0</sup> <sub>-0.007</sub>  | 105                               | 80                               |
| BNS 4040  | 37.8                   | 60.5           | 687  | 418                 | 377             | 100 <sup>0</sup> <sub>-0.008</sub> | 130                               | 100                              |
| BNS 5050  | 60.9                   | 94.5           | 1340   | 842                 | 768             | 120 <sup>0</sup> <sub>-0.008</sub> | 156                               | 125                              |

Note) Dimension U indicates the length from the head of the hexagonal-socket-head type bolt to the ball screw nut end.

For K hollow shaft, please refer to the db dimension for the inner bore diameter of the shaft. If requested solid shaft is also available. See "Ball Spline" **A3-118** for details.


## Model number coding

## BNS2525 +600L C5

Model number    Overall shaft length (in mm)    Accuracy symbol (\*1)

(\*1) See **A15-12**.

## Rotary Nut Ball Screw




Unit: mm

|  | D <sub>4</sub> | H  | B <sub>4</sub> | B <sub>5</sub> | Te | P <sub>1</sub> | P <sub>2</sub> | S   | t  | d <sub>1</sub> | θ° | Support bearing basic load rating |                 | Nut inertial moment     | Screw shaft inertial moment | Nut mass | Shaft mass | Permissible rotational speed |
|--|----------------|----|----------------|----------------|----|----------------|----------------|-----|----|----------------|----|-----------------------------------|-----------------|-------------------------|-----------------------------|----------|------------|------------------------------|
|  |                |    |                |                |    |                |                |     |    |                |    | Ca                                | C <sub>0a</sub> |                         |                             |          |            |                              |
|  |                |    |                |                |    |                |                |     |    |                |    | kN                                | kN              |                         |                             |          |            |                              |
|  | 32             | 5  | 27.5           | 9              | 2  | 60             | 25             | M4  | 12 | 4.5            | 40 | 19.4                              | 19.2            | 4.80 × 10 <sup>-5</sup> | 3.92 × 10 <sup>-8</sup>     | 0.38     | 0.8        | 4200                         |
|  | 39             | 6  | 34             | 11             | 2  | 70             | 31             | M5  | 16 | 4.5            | 40 | 26.8                              | 29.3            | 1.44 × 10 <sup>-4</sup> | 9.37 × 10 <sup>-8</sup>     | 0.68     | 1.21       | 3370                         |
|  | 47             | 8  | 43             | 12.5           | 3  | 81             | 38             | M6  | 19 | 5.5            | 40 | 28.2                              | 33.3            | 3.23 × 10 <sup>-4</sup> | 2.20 × 10 <sup>-7</sup>     | 1.1      | 1.79       | 2690                         |
|  | 58             | 9  | 55             | 14             | 3  | 91             | 48             | M6  | 19 | 6.6            | 40 | 30                                | 39              | 6.74 × 10 <sup>-4</sup> | 5.92 × 10 <sup>-7</sup>     | 1.74     | 2.96       | 2100                         |
|  | 73             | 11 | 68             | 16.5           | 3  | 123            | 61             | M8  | 22 | 9              | 50 | 59.3                              | 74.1            | 2.79 × 10 <sup>-3</sup> | 1.43 × 10 <sup>-6</sup>     | 3.95     | 4.51       | 1670                         |
|  | 90             | 12 | 80             | 25             | 4  | 136            | 75             | M10 | 28 | 11             | 50 | 62.2                              | 83              | 5.82 × 10 <sup>-3</sup> | 3.52 × 10 <sup>-6</sup>     | 6.22     | 7.16       | 1340                         |


Unit: mm

|  | D <sub>6</sub> | H <sub>1</sub> | B <sub>6</sub> | B <sub>7</sub> | P <sub>3</sub> | P <sub>4</sub> | S <sub>1</sub> × t <sub>1</sub> | ds <sub>1</sub> | U  | Support bearing basic load rating |                | Nut inertial moment     | Nut mass |
|--|----------------|----------------|----------------|----------------|----------------|----------------|---------------------------------|-----------------|----|-----------------------------------|----------------|-------------------------|----------|
|  |                |                |                |                |                |                |                                 |                 |    | C                                 | C <sub>0</sub> |                         |          |
|  |                |                |                |                |                |                |                                 |                 |    | kN                                | kN             |                         |          |
|  | 39.5           | 5              | 37             | 10             | 60             | 32             | M5 × 8                          | 4.5             | 5  | 12.7                              | 11.8           | 5.20 × 10 <sup>-5</sup> | 0.51     |
|  | 43.5           | 6              | 48             | 12             | 64             | 36             | M5 × 8                          | 4.5             | 7  | 16.3                              | 15.5           | 8.70 × 10 <sup>-5</sup> | 0.7      |
|  | 53             | 6              | 55             | 13             | 70             | 45             | M6 × 8                          | 4.5             | 8  | 17.6                              | 18             | 1.72 × 10 <sup>-4</sup> | 0.93     |
|  | 65.5           | 9              | 60             | 17             | 91             | 55             | M6 × 10                         | 6.6             | 10 | 20.1                              | 24             | 5.61 × 10 <sup>-4</sup> | 1.8      |
|  | 79.5           | 11             | 74             | 23             | 113            | 68             | M6 × 10                         | 9               | 13 | 37.2                              | 42.5           | 1.47 × 10 <sup>-3</sup> | 3.9      |
|  | 99.5           | 12             | 97             | 25             | 136            | 85             | M10 × 15                        | 11              | 13 | 41.7                              | 54.1           | 6.25 × 10 <sup>-3</sup> | 6.7      |



# NS-V Compact Type: Linear Motion No Preload

|          |        |
|----------|--------|
| DN value | 100000 |
|----------|--------|



Ball screw unit

## Ball screw unit

| Model No. | Screw shaft outer diameter<br>d | Screw shaft inner diameter<br>db | Lead<br>Ph | Ball screw dimensions |                       |                                      |                             |                     |                                   |                                  |                |    |      |   |
|-----------|---------------------------------|----------------------------------|------------|-----------------------|-----------------------|--------------------------------------|-----------------------------|---------------------|-----------------------------------|----------------------------------|----------------|----|------|---|
|           |                                 |                                  |            | Basic load rating     |                       | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | D <sub>3</sub> | AE | BE   | H |
|           |                                 |                                  |            | Ca<br>kN              | C <sub>0a</sub><br>kN |                                      |                             |                     |                                   |                                  |                |    |      |   |
| NS 1616V  | 16                              | 11                               | 16         | 4.6                   | 6.8                   | 16.65                                | 13.7                        | 42                  | 54                                | 38                               | 32.5           | 31 | 31   | 4 |
| NS 2020V  | 20                              | 14                               | 20         | 7.3                   | 11.7                  | 20.75                                | 17.5                        | 48                  | 64                                | 45                               | 39.5           | 37 | 36   | 6 |
| NS 2525V  | 25                              | 18                               | 25         | 8                     | 14.4                  | 25.35                                | 22.1                        | 56                  | 72                                | 55                               | 43.5           | 42 | 41.6 | 6 |

## Ball spline

| Model No. | Ball spline dimensions |                      |  |                       |                        |                                   |                                   |
|-----------|------------------------|----------------------|--|-----------------------|------------------------|-----------------------------------|-----------------------------------|
|           | Basic load rating      |                      | Static permissible moment<br>M <sub>A</sub><br>N·m | Basic torque rating   |                        | Outer diameter<br>D <sub>7</sub>  | Flange diameter<br>D <sub>5</sub> |
|           | C<br>kN                | C <sub>0</sub><br>kN |  | C <sub>T</sub><br>N·m | C <sub>0T</sub><br>N·m |                                   |                                   |
| NS 1616V  | 8.4                    | 13.4                 | 77.4   | 42.9                  | 68.6                   | 28 <sup>0</sup> <sub>-0.013</sub> | 48                                |
| NS 2020V  | 10.5                   | 18.6                 | 144  | 66.4                  | 117.2                  | 32 <sup>0</sup> <sub>-0.016</sub> | 54                                |
| NS 2525V  | 15.9                   | 26.2                 | 230  | 125.3                 | 207                    | 40 <sup>0</sup> <sub>-0.016</sub> | 62                                |

Note) For K hollow shaft, please refer to the db dimension for the inner bore diameter of the shaft. If requested solid shaft is also available. See "Ball Spline" **A3-118** for details.


### Model number coding

## NS2020V +500L C5

Model number    Overall shaft length (in mm)    Accuracy symbol (\*1)

(\*1) See **A15-12**.

## Rotary Nut Ball Screw




Unit: mm

|  | B <sub>4</sub> | B <sub>5</sub> | P <sub>1</sub> | P <sub>2</sub> | S  | t <sub>1</sub> | t <sub>2</sub> | d <sub>1</sub> | B <sub>6</sub> | d <sub>0</sub> | A <sub>1</sub> | Support bearing basic load rating |                 | Nut inertial moment<br>kg·m <sup>2</sup> | Screw shaft inertial moment<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|----------------|----------------|----------------|----------------|----|----------------|----------------|----------------|----------------|----------------|----------------|-----------------------------------|-----------------|--|--|----------------|--------------------|---|
|  |                |                |                |                |    |                |                |                |                |                |                | Ca                                | C <sub>0a</sub> |  |  |                |                    |   |
|  | 18             | 9.7            | 48             | 25.5           | M3 | 8.2            | 6              | 3.4            | 5.8            | 2              | 35°            | 6.7                               | 8.6             | 2.00 × 10 <sup>-5</sup>                  | 3.21 × 10 <sup>-8</sup>                              | 0.21           | 0.8                | 5000  |
|  | 21             | 12.2           | 56             | 31             | M4 | 10.2           | 8              | 4.5            | 7.2            | 2              | 35°            | 7.3                               | 10.6            | 6.50 × 10 <sup>-5</sup>                  | 8.04 × 10 <sup>-8</sup>                              | 0.39           | 1.21               | 4810  |
|  | 21             | 13.2           | 64             | 36             | M5 | 10.2           | 8              | 4.5            | 15.3           | 3              | 35°            | 9.7                               | 13.4            | 1.02 × 10 <sup>-4</sup>                  | 1.91 × 10 <sup>-7</sup>                              | 0.51           | 1.79               | 3940  |


Unit: mm

| Overall length<br>L <sub>2</sub> | H <sub>1</sub> | B <sub>7</sub> | ds <sub>0</sub> | P <sub>3</sub> | Mounting hole   |                 |     | Nut mass<br>kg |
|----------------------------------|----------------|----------------|-----------------|----------------|-----------------|-----------------|-----|----------------|
|                                  |                |                |                 |                | ds <sub>1</sub> | ds <sub>2</sub> | h   |                |
| 46.4                             | 6              | 11.7           | 2               | 38             | 4.5             | 8               | 4.4 | 0.13           |
| 59                               | 8              | 15.7           | 2               | 43             | 5.5             | 9.5             | 5.4 | 0.21           |
| 67                               | 8              | 18.3           | 3               | 51             | 5.5             | 9.5             | 5.4 | 0.34           |




# NS-A Compact Type: Linear Motion No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



Ball screw unit  
(Models NS 1616A to 4040A)



Ball screw unit  
(Models NS 0812A and 1015A)

## Ball screw unit

| Model No. | Screw shaft outer diameter<br>d | Screw shaft inner diameter<br>db | Lead<br>Ph | Ball screw dimensions |                       |                                      |                             |                     |                                   |                                  |                      |                      |  |
|-----------|---------------------------------|----------------------------------|------------|-----------------------|-----------------------|--------------------------------------|-----------------------------|---------------------|-----------------------------------|----------------------------------|----------------------|----------------------|--|
|           |                                 |                                  |            | Basic load rating     |                       | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | Outer diameter<br>D | Flange diameter<br>D <sub>1</sub> | Overall length<br>L <sub>1</sub> | D <sub>3</sub><br>h7 | D <sub>4</sub><br>H7 |  |
|           |                                 |                                  |            | Ca<br>kN              | C <sub>0a</sub><br>kN |                                      |                             |                     |                                   |                                  |                      |                      |  |
| NS 0812A  | 8                               | —                                | 12         | 1.1                   | 1.8                   | 8.4                                  | 6.6                         | 32                  | 44                                | 28.5                             | 22                   | 19                   |  |
| NS 1015A  | 10                              | —                                | 15         | 1.7                   | 2.7                   | 10.5                                 | 8.3                         | 36                  | 48                                | 34.5                             | 26                   | 23                   |  |
| NS 1616A  | 16                              | 11                               | 16         | 3.9                   | 7.2                   | 16.65                                | 13.7                        | 48                  | 64                                | 40                               | 36                   | 32                   |  |
| NS 2020A  | 20                              | 14                               | 20         | 6.1                   | 12.3                  | 20.75                                | 17.5                        | 56                  | 72                                | 48                               | 43.5                 | 39                   |  |
| NS 2525A  | 25                              | 18                               | 25         | 9.1                   | 19.3                  | 26                                   | 21.9                        | 66                  | 86                                | 58                               | 52                   | 47                   |  |
| NS 3232A  | 32                              | 23                               | 32         | 13                    | 29.8                  | 33.25                                | 28.3                        | 78                  | 103                               | 72                               | 63                   | 58                   |  |
| NS 4040A  | 40                              | 29                               | 40         | 21.4                  | 49.7                  | 41.75                                | 35.2                        | 100                 | 130                               | 88                               | 79.5                 | 73                   |  |

## Ball spline

| Model No. | Ball spline dimensions |                      |  |                       |                        |                                   |   |
|-----------|------------------------|----------------------|--|-----------------------|------------------------|-----------------------------------|---|
|           | Basic load rating      |                      | Static permissible moment<br>M <sub>A</sub><br>N·m | Basic torque rating   |                        | Outer diameter<br>D <sub>7</sub>  | Flange diameter<br>D <sub>5</sub><br><sup>0</sup> <sub>-0.2</sub> |
|           | C<br>kN                | C <sub>0</sub><br>kN |  | C <sub>T</sub><br>N·m | C <sub>0T</sub><br>N·m |                                   |   |
| NS 0812A  | 1.5                    | 2.6                  | 5.9  | 2                     | 2.9                    | 16 <sup>0</sup> <sub>-0.011</sub> | 32  |
| NS 1015A  | 2.8                    | 4.9                  | 15.7   | 3.9                   | 7.8                    | 21 <sup>0</sup> <sub>-0.013</sub> | 42  |
| NS 1616A  | 7.1                    | 12.6                 | 67.6   | 31.4                  | 34.3                   | 31 <sup>0</sup> <sub>-0.013</sub> | 51  |
| NS 2020A  | 10.2                   | 17.8                 | 118  | 56.8                  | 55.8                   | 35 <sup>0</sup> <sub>-0.016</sub> | 58  |
| NS 2525A  | 15.2                   | 25.8                 | 210  | 105                   | 103                    | 42 <sup>0</sup> <sub>-0.016</sub> | 65  |
| NS 3232A  | 20.5                   | 34                   | 290  | 180                   | 157                    | 49 <sup>0</sup> <sub>-0.016</sub> | 77  |
| NS 4040A  | 37.8                   | 60.5                 | 687  | 418                   | 377                    | 64 <sup>0</sup> <sub>-0.019</sub> | 100   |

Note) For K hollow shaft, please refer to the db dimension for the inner bore diameter of the shaft. If requested solid shaft is also available. See "Ball Spline" **A3-118** for details.

### Model number coding


## NS2020A +500L C5

Model number    Overall shaft length (in mm)    Accuracy symbol (\*1)

(\*1) See **A15-12**.




# Rotary Nut Ball Screw




Ball screw unit  
(Models NS 1616A to 4040A)

Ball spline  
(Models NS 1616A to 4040A)




Ball spline  
(Models NS 1616A to 4040A)



Ball screw unit  
(Models NS 0812A and 1015A)

Ball spline  
(Models NS 0812A and 1015A)




Ball spline  
(Models NS 0812A and 1015A)

Unit: mm

|  | BE | H  | B <sub>4</sub> | B <sub>5</sub> | T <sub>e</sub> | P <sub>1</sub> | P <sub>2</sub> | S    | t    | d <sub>1</sub> | Support bearing basic load rating |                 | Nut inertial moment<br>kg·m <sup>2</sup> | Screw shaft inertial moment<br>kg·m <sup>2</sup> /mm | Nut mass<br>kg | Shaft mass<br>kg/m | Permissible rotational speed<br>min <sup>-1</sup> |
|--|----|----|----------------|----------------|----------------|----------------|----------------|------|------|----------------|-----------------------------------|-----------------|--|--|----------------|--------------------|---|
|  |    |    |                |                |                |                |                |      |      |                | C <sub>a</sub>                    | C <sub>0a</sub> |  |  |                |                    |   |
|  | 19 | 3  | 10.5           | 7              | 1.5            | 38             | 14.5           | M2.6 | 10   | 3.4            | 0.8                               | 0.5             | 3.00×10 <sup>-6</sup>                    | 3.16×10 <sup>-9</sup>                                | 0.08           | 0.35               | 3500  |
|  | 23 | 3  | 10.5           | 8              | 1.5            | 42             | 18             | M3   | 11.5 | 3.4            | 0.9                               | 0.7             | 8.00×10 <sup>-6</sup>                    | 7.71×10 <sup>-9</sup>                                | 0.15           | 0.52               | 3500  |
|  | 32 | 6  | 21             | 10             | 2              | 56             | 25             | M4   | 13.5 | 4.5            | 8.7                               | 10.5            | 3.50×10 <sup>-5</sup>                    | 3.92×10 <sup>-6</sup>                                | 0.31           | 0.8                | 4200  |
|  | 39 | 6  | 21             | 11             | 2.5            | 64             | 31             | M5   | 16.5 | 4.5            | 9.7                               | 13.4            | 8.50×10 <sup>-5</sup>                    | 9.37×10 <sup>-6</sup>                                | 0.54           | 1.21               | 3370  |
|  | 47 | 7  | 25             | 13             | 3              | 75             | 38             | M6   | 20   | 5.5            | 12.7                              | 18.2            | 2.12×10 <sup>-4</sup>                    | 2.20×10 <sup>-7</sup>                                | 0.88           | 1.79               | 2690  |
|  | 58 | 8  | 25             | 14             | 3              | 89             | 48             | M6   | 21   | 6.6            | 13.6                              | 22.3            | 5.42×10 <sup>-4</sup>                    | 5.92×10 <sup>-7</sup>                                | 1.39           | 2.96               | 2100  |
|  | 73 | 10 | 33             | 16.5           | 3              | 113            | 61             | M8   | 24.5 | 9              | 21.5                              | 36.8            | 1.72×10 <sup>-3</sup>                    | 1.43×10 <sup>-6</sup>                                | 3.16           | 4.51               | 1670  |


Unit: mm

|  | Overall length<br>L <sub>2</sub>    | H <sub>1</sub> | B <sub>6</sub> | r   | Lubrication hole<br>d <sub>0</sub> | P <sub>3</sub> | Mounting hole   |                |     | Nut mass<br>kg |
|--|-------------------------------------|----------------|----------------|-----|------------------------------------|----------------|-----------------|----------------|-----|----------------|
|  |                                     |                |                |     |                                    |                | ds <sub>1</sub> | d <sub>2</sub> | h   |                |
|  | 25                                  | 5              | 7.5            | 0.5 | 1.5                                | 24             | 3.4             | 6.5            | 3.3 | 0.04           |
|  | 33                                  | 6              | 10.5           | 0.5 | 1.5                                | 32             | 4.5             | 8              | 4.4 | 0.09           |
|  | 50 <sup>+0.2</sup> <sub>-0.2</sub>  | 7              | 18             | 0.5 | 2                                  | 40             | 4.5             | 8              | 4.4 | 0.23           |
|  | 63 <sup>+0.3</sup> <sub>-0.3</sub>  | 9              | 22.5           | 0.5 | 2                                  | 45             | 5.5             | 9.5            | 5.4 | 0.33           |
|  | 71 <sup>+0.3</sup> <sub>-0.3</sub>  | 9              | 26.5           | 0.5 | 3                                  | 52             | 5.5             | 9.5            | 5.4 | 0.45           |
|  | 80 <sup>+0.3</sup> <sub>-0.3</sub>  | 10             | 30             | 0.5 | 3                                  | 62             | 6.6             | 11             | 6.5 | 0.58           |
|  | 100 <sup>+0.3</sup> <sub>-0.3</sub> | 14             | 36             | 0.5 | 4                                  | 82             | 9               | 14             | 8.6 | 1.46           |



# NS Heavy Load Type: Linear Motion No Preload

|          |       |
|----------|-------|
| DN value | 70000 |
|----------|-------|



## Ball screw unit

| Model No. | Screw shaft outer diameter<br>d | Screw shaft inner diameter<br>db | Lead<br>Ph | Ball screw dimensions |                       |                                      |                             |                                    |                                   |                                  |                      |
|-----------|---------------------------------|----------------------------------|------------|-----------------------|-----------------------|--------------------------------------|-----------------------------|------------------------------------|-----------------------------------|----------------------------------|----------------------|
|           |                                 |                                  |            | Basic load rating     |                       | Ball center-to-center diameter<br>dp | Thread minor diameter<br>dc | Outer diameter<br>D                | Flange diameter<br>D <sub>f</sub> | Overall length<br>L <sub>1</sub> | D <sub>3</sub><br>h7 |
|           |                                 |                                  |            | Ca<br>kN              | C <sub>0a</sub><br>kN |                                      |                             |                                    |                                   |                                  |                      |
| NS 1616   | 16                              | 11                               | 16         | 3.9                   | 7.2                   | 16.65                                | 13.7                        | 52 <sup>0</sup> <sub>-0.007</sub>  | 68                                | 43.5                             | 40                   |
| NS 2020   | 20                              | 14                               | 20         | 6.1                   | 12.3                  | 20.75                                | 17.5                        | 62 <sup>0</sup> <sub>-0.007</sub>  | 78                                | 54                               | 50                   |
| NS 2525   | 25                              | 18                               | 25         | 9.1                   | 19.3                  | 26                                   | 21.9                        | 72 <sup>0</sup> <sub>-0.007</sub>  | 92                                | 65                               | 58                   |
| NS 3232   | 32                              | 23                               | 32         | 13                    | 29.8                  | 33.25                                | 28.3                        | 80 <sup>0</sup> <sub>-0.007</sub>  | 105                               | 80                               | 66                   |
| NS 4040   | 40                              | 29                               | 40         | 21.4                  | 49.7                  | 41.75                                | 35.2                        | 110 <sup>0</sup> <sub>-0.008</sub> | 140                               | 98                               | 90                   |
| NS 5050   | 50                              | 36                               | 50         | 31.8                  | 77.6                  | 52.2                                 | 44.1                        | 120 <sup>0</sup> <sub>-0.008</sub> | 156                               | 126                              | 100                  |

## Ball spline

| Model No. | Ball spline dimensions |                      |  |                       |                        |                                   |
|-----------|------------------------|----------------------|--|-----------------------|------------------------|-----------------------------------|
|           | Basic load rating      |                      | Static permissible moment<br>M <sub>k</sub><br>N·m | Basic torque rating   |                        | Outer diameter<br>D <sub>7</sub>  |
|           | C<br>kN                | C <sub>0</sub><br>kN |  | C <sub>T</sub><br>N·m | C <sub>0T</sub><br>N·m |                                   |
| NS 1616   | 7.1                    | 12.6                 | 67.6   | 31.4                  | 34.3                   | 31 <sup>0</sup> <sub>-0.013</sub> |
| NS 2020   | 10.2                   | 17.8                 | 118  | 56.9                  | 55.9                   | 35 <sup>0</sup> <sub>-0.016</sub> |
| NS 2525   | 15.2                   | 25.8                 | 210  | 105                   | 103                    | 42 <sup>0</sup> <sub>-0.016</sub> |
| NS 3232   | 20.5                   | 34                   | 290  | 180                   | 157                    | 49 <sup>0</sup> <sub>-0.016</sub> |
| NS 4040   | 37.8                   | 60.5                 | 687  | 419                   | 377                    | 64 <sup>0</sup> <sub>-0.019</sub> |
| NS 5050   | 60.9                   | 94.5                 | 1340   | 842                   | 769                    | 80 <sup>0</sup> <sub>-0.019</sub> |

Note) For K hollow shaft, please refer to the db dimension for the inner bore diameter of the shaft. If requested solid shaft is also available. See "Ball Spline" **A3-118** for details.


### Model number coding

## NS2525 +600L C5

Model number    Overall shaft length (in mm)    Accuracy symbol (\*1)

(\*1) See **A15-12**.

## Rotary Nut Ball Screw




Unit: mm

| D <sub>4</sub> | H  | B <sub>4</sub> | B <sub>5</sub> | T <sub>e</sub> | P <sub>1</sub> | P <sub>2</sub> | S   | t  | d <sub>1</sub> | θ° | Support bearing basic load rating |      | Nut inertial moment   | Screw shaft inertial moment | Nut mass | Shaft mass | Permissible rotational speed |
|----------------|----|----------------|----------------|----------------|----------------|----------------|-----|----|----------------|----|-----------------------------------|------|-----------------------|-----------------------------|----------|------------|------------------------------|
|                |    |                |                |                |                |                |     |    |                |    | Ca                                | C:a  |                       |                             |          |            |                              |
| 32             | 5  | 27.5           | 9              | 2              | 60             | 25             | M4  | 12 | 4.5            | 40 | 19.4                              | 19.2 | $4.80 \times 10^{-5}$ | $3.92 \times 10^{-8}$       | 0.38     | 0.8        | 4200                         |
| 39             | 6  | 34             | 11             | 2              | 70             | 31             | M5  | 16 | 4.5            | 40 | 26.8                              | 29.3 | $1.44 \times 10^{-4}$ | $9.37 \times 10^{-8}$       | 0.68     | 1.21       | 3370                         |
| 47             | 8  | 43             | 12.5           | 3              | 81             | 38             | M6  | 19 | 5.5            | 40 | 28.2                              | 33.3 | $3.23 \times 10^{-4}$ | $2.20 \times 10^{-7}$       | 1.1      | 1.79       | 2690                         |
| 58             | 9  | 55             | 14             | 3              | 91             | 48             | M6  | 19 | 6.6            | 40 | 30                                | 39   | $6.74 \times 10^{-4}$ | $5.92 \times 10^{-7}$       | 1.74     | 2.96       | 2100                         |
| 73             | 11 | 68             | 16.5           | 3              | 123            | 61             | M8  | 22 | 9              | 50 | 59.3                              | 74.1 | $2.79 \times 10^{-3}$ | $1.43 \times 10^{-6}$       | 3.95     | 4.51       | 1670                         |
| 90             | 12 | 80             | 25             | 4              | 136            | 75             | M10 | 28 | 11             | 50 | 62.2                              | 83   | $5.82 \times 10^{-3}$ | $3.52 \times 10^{-6}$       | 6.22     | 7.16       | 1340                         |

Unit: mm

| Flange diameter | Overall length                   | H <sub>1</sub> | B <sub>6</sub> | r   | Lubrication hole | P <sub>3</sub> | Mounting hole   |                |     | Nut mass |
|-----------------|----------------------------------|----------------|----------------|-----|------------------|----------------|-----------------|----------------|-----|----------|
|                 |                                  |                |                |     |                  |                | ds <sub>1</sub> | d <sub>2</sub> | h   |          |
| D <sub>5</sub>  | L <sub>2</sub>                   |                |                |     | d <sub>0</sub>   |                | ds <sub>1</sub> | d <sub>2</sub> | h   | kg       |
| 51              | 50 <sup>0</sup> <sub>-0.2</sub>  | 7              | 18             | 0.5 | 2                | 40             | 4.5             | 8              | 4.4 | 0.23     |
| 58              | 63 <sup>0</sup> <sub>-0.2</sub>  | 9              | 22.5           | 0.5 | 2                | 45             | 5.5             | 9.5            | 5.4 | 0.33     |
| 65              | 71 <sup>0</sup> <sub>-0.3</sub>  | 9              | 26.5           | 0.5 | 3                | 52             | 5.5             | 9.5            | 5.4 | 0.45     |
| 77              | 80 <sup>0</sup> <sub>-0.3</sub>  | 10             | 30             | 0.5 | 3                | 62             | 6.6             | 11             | 6.5 | 0.58     |
| 100             | 100 <sup>0</sup> <sub>-0.3</sub> | 14             | 36             | 0.5 | 4                | 82             | 9               | 14             | 8.6 | 1.46     |
| 124             | 125 <sup>0</sup> <sub>-0.3</sub> | 16             | 46.5           | 1   | 4                | 102            | 11              | 17.5           | 11  | 2.76     |



## Ball Screw/Spline Permissible Rotational Speeds

The permissible rotational speed of the ball screw/spline is limited by the lower of the critical speed of the ball screw, the DN value, or the permissible speed of the support bearing. Do not exceed the permissible rotational speed when operating.

Table 1: Permissible rotational speed for the Model BNS-V

Unit: min<sup>-1</sup>

| Model No. | Ball screw                   |                          | Support bearing    |                 |                    |                 |
|-----------|------------------------------|--------------------------|--------------------|-----------------|--------------------|-----------------|
|           | Calculated from shaft length | Calculated from DN value | Ball screw         |                 | Ball spline        |                 |
|           |                              |                          | Grease lubrication | Oil lubrication | Grease lubrication | Oil lubrication |
| BNS1616V  | see <b>A15-32</b> .          | 5000                     | 4400               | 6100            | 4400               | 6100            |
| BNS2020V  |                              | 4810                     | 3900               | 5100            | 4000               | 5400            |
| BNS2525V  |                              | 3940                     | 3500               | 4700            | 3500               | 4700            |

Table 2: Permissible rotational speed for the Model BNS-A

Unit: min<sup>-1</sup>

| Model No. | Ball screw                   |                          | Support bearing    |                 |                    |                 |
|-----------|------------------------------|--------------------------|--------------------|-----------------|--------------------|-----------------|
|           | Calculated from shaft length | Calculated from DN value | Ball screw         |                 | Ball spline        |                 |
|           |                              |                          | Grease lubrication | Oil lubrication | Grease lubrication | Oil lubrication |
| BNS0812A  | see <b>A15-32</b> .          | 3500                     | —                  | —               | 6900               | 9300            |
| BNS1015A  |                              | 3500                     | —                  | —               | 5900               | 7900            |
| BNS1616A  |                              | 4200                     | 4000               | 5400            | 4000               | 5400            |
| BNS2020A  |                              | 3370                     | 3500               | 4700            | 3500               | 4700            |
| BNS2525A  |                              | 2690                     | 2900               | 3900            | 2900               | 3900            |
| BNS3232A  |                              | 2100                     | 2400               | 3300            | 2400               | 3300            |
| BNS4040A  |                              | 1670                     | 1900               | 2600            | 1900               | 2600            |

Table 3: Permissible rotational speed for the Model BNS

Unit: min<sup>-1</sup>

| Model No. | Ball screw                   |                          | Support bearing    |                 |                    |                 |
|-----------|------------------------------|--------------------------|--------------------|-----------------|--------------------|-----------------|
|           | Calculated from shaft length | Calculated from DN value | Ball screw         |                 | Ball spline        |                 |
|           |                              |                          | Grease lubrication | Oil lubrication | Grease lubrication | Oil lubrication |
| BNS1616   | see <b>A15-32</b> .          | 4200                     | 4000               | 5600            | 4000               | 5400            |
| BNS2020   |                              | 3370                     | 3200               | 4300            | 3600               | 4900            |
| BNS2525   |                              | 2690                     | 2800               | 3700            | 3200               | 4300            |
| BNS3232   |                              | 2100                     | 2400               | 3300            | 2400               | 3300            |
| BNS4040   |                              | 1670                     | 1800               | 2400            | 2000               | 2700            |
| BNS5050   |                              | 1340                     | 1600               | 2200            | 1600               | 2200            |

# Rotary Nut Ball Screw

Table 4: Permissible rotational speed for the Model NS-V

Unit: min<sup>-1</sup>

| Model No. | Ball screw                   |                          | Support bearing    |                 |
|-----------|------------------------------|--------------------------|--------------------|-----------------|
|           | Calculated from shaft length | Calculated from DN value | Ball screw         |                 |
|           |                              |                          | Grease lubrication | Oil lubrication |
| NS1616V   | see <b>A15-32.</b>           | 5000                     | 4400               | 6100            |
| NS2020V   |                              | 4810                     | 3900               | 5100            |
| NS2525V   |                              | 3940                     | 3500               | 4700            |

Table 5: Permissible rotational speed for the Model NS-A

Unit: min<sup>-1</sup>

| Model No. | Ball screw                   |                          | Support bearing    |                 |
|-----------|------------------------------|--------------------------|--------------------|-----------------|
|           | Calculated from shaft length | Calculated from DN value | Ball screw         |                 |
|           |                              |                          | Grease lubrication | Oil lubrication |
| NS0812A   | see <b>A15-32.</b>           | 3500                     | —                  | —               |
| NS1015A   |                              | 3500                     | —                  | —               |
| NS1616A   |                              | 4200                     | 4000               | 5400            |
| NS2020A   |                              | 3370                     | 3500               | 4700            |
| NS2525A   |                              | 2690                     | 2900               | 3900            |
| NS3232A   |                              | 2100                     | 2400               | 3300            |
| NS4040A   |                              | 1670                     | 1900               | 2600            |

Table 6: Permissible rotational speed for the Model NS

Unit: min<sup>-1</sup>

| Model No. | Ball screw                   |                          | Support bearing    |                 |
|-----------|------------------------------|--------------------------|--------------------|-----------------|
|           | Calculated from shaft length | Calculated from DN value | Ball screw         |                 |
|           |                              |                          | Grease lubrication | Oil lubrication |
| NS1616    | see <b>A15-32.</b>           | 4200                     | 4000               | 5600            |
| NS2020    |                              | 3370                     | 3200               | 4300            |
| NS2525    |                              | 2690                     | 2800               | 3700            |
| NS3232    |                              | 2100                     | 2400               | 3300            |
| NS4040    |                              | 1670                     | 1800               | 2400            |
| NS5050    |                              | 1340                     | 1600               | 2200            |

## Maximum Manufacturing Length of the Screw Shaft

Table1, Table2, and Table3 show the maximum manufacturing lengths of precision ball screws by accuracy grade. Table5, Table6, Table7, and Table8 show the maximum manufacturing lengths of rolled ball screws by accuracy grade.

Table1 Maximum Manufacturing Length of Precision Ball Screws by Accuracy Grade

Unit: mm

| Screw shaft<br>outer diameter | Overall screw shaft length |      |      |       |       |       |
|-------------------------------|----------------------------|------|------|-------|-------|-------|
|                               | C0                         | C1   | C2   | C3    | C5    | C7    |
| 4                             | 90                         | 110  | 120  | 120   | 120   | 120   |
| 6                             | 150                        | 170  | 210  | 210   | 210   | 210   |
| 8                             | 230                        | 270  | 340  | 340   | 340   | 340   |
| 10                            | 350                        | 400  | 500  | 500   | 500   | 500   |
| 12                            | 440                        | 500  | 630  | 680   | 680   | 680   |
| 13                            | 440                        | 500  | 630  | 680   | 680   | 680   |
| 14                            | 530                        | 620  | 770  | 870   | 890   | 890   |
| 15                            | 570                        | 670  | 830  | 950   | 980   | 1100  |
| 16                            | 620                        | 730  | 900  | 1050  | 1100  | 1400  |
| 18                            | 720                        | 840  | 1050 | 1220  | 1350  | 1600  |
| 20                            | 820                        | 950  | 1200 | 1400  | 1600  | 1800  |
| 25                            | 1100                       | 1400 | 1600 | 1800  | 2000  | 2400  |
| 28                            | 1300                       | 1600 | 1900 | 2100  | 2350  | 2700  |
| 30                            | 1450                       | 1700 | 2050 | 2300  | 2570  | 2950  |
| 32                            | 1600                       | 1800 | 2200 | 2500  | 2800  | 3200  |
| 36                            | 2000                       | 2100 | 2550 | 2950  | 3250  | 3650  |
| 40                            | 2000                       | 2400 | 2900 | 3400  | 3700  | 4300  |
| 45                            | 2000                       | 2750 | 3350 | 3950  | 4350  | 5050  |
| 50                            | 2000                       | 3100 | 3800 | 4500  | 5000  | 5800  |
| 55                            | 2000                       | 3450 | 4150 | 5300  | 6050  | 6500  |
| 63                            | 2000                       | 4000 | 5200 | 5800  | 6700  | 7700  |
| 70                            | 2000                       | 4000 | 6300 | 6450  | 7650  | 9000  |
| 80                            | 2000                       | 4000 | 6300 | 7900  | 9000  | 11000 |
| 100                           | 2000                       | 4000 | 6300 | 11000 | 11000 | 11000 |

\*For ball screw models HBN-V, HBN-K, HBN-KA, HBN, and SBKH, the standard maximum length of the screw shaft is 3000 mm. For lengths greater than this, please contact THK.

Table2 Maximum Manufacturing Lengths of Precision Ball Screws  
(Model MBF without Preload) by Model Number

Unit: mm

| Screw shaft outer diameter | C0  | C1  | C2  | C3  | C5  | C7  |
|----------------------------|-----|-----|-----|-----|-----|-----|
| MBF0401-3.7                | 90  | 110 | 120 | 120 | 120 | 120 |
| MBF0601-3.7                | 150 | 170 | 210 | 210 | 210 | 210 |
| MBF0602-2.7                | 140 | 160 | —   | 230 | 280 | 290 |
| MBF0602.5-2.7              | 140 | 160 | —   | 230 | 280 | 290 |
| MBF0801.5-3.7              | 200 | 250 | —   | 330 | 350 | 350 |
| MBF0802-3.7                | 230 | 270 | 340 | 340 | 340 | 340 |
| MBF0802.5-3.7              | 200 | 200 | —   | 320 | 320 | 320 |
| MBF0803-2.7                | 200 | 200 | —   | 320 | 320 | 320 |
| MBF0804-2.7                | 200 | 200 | —   | 320 | 320 | 320 |
| MBF1001-3.7                | 260 | 260 | —   | 460 | 460 | 460 |
| MBF1001.5-3.7              | 260 | 260 | —   | 460 | 460 | 460 |
| MBF1002-3.7                | 350 | 400 | 500 | 500 | 500 | 500 |
| MBF1002.5-3.7              | 260 | 260 | —   | 380 | 420 | 500 |
| MBF1003-3.7                | 260 | 260 | —   | 380 | 420 | 500 |
| MBF1005-2.7                | 260 | 260 | —   | 380 | 420 | 500 |
| MBF1202-3.7                | 440 | 500 | 630 | 680 | 680 | 680 |
| MBF1202.5-3.7              | 320 | 350 | —   | 510 | 510 | 510 |
| MBF1203-3.7                | 320 | 450 | —   | 600 | 620 | 680 |
| MBF1204-3.7                | 320 | 450 | —   | 600 | 620 | 680 |
| MBF1402-3.7                | 530 | 620 | 770 | 870 | 890 | 890 |
| MBF1404-3.7                | 530 | 620 | 770 | 870 | 890 | 890 |

Table3 Maximum Manufacturing Lengths of Precision Ball Screws  
(Model BLK without Preload) by Model Number

Unit: mm

| Screw shaft outer diameter | C0   | C1   | C2   | C3   | C5   | C7   |
|----------------------------|------|------|------|------|------|------|
| BLK0808-3.2                | —    | —    | —    | 300  | 410  | 410  |
| BLK1510-5.6                | 570  | 670  | 830  | 950  | 980  | 1100 |
| BLK1616-2.8                | 620  | 730  | 900  | 1050 | 1100 | 1400 |
| BLK1616-3.6                | 620  | 730  | 900  | 1050 | 1100 | 1400 |
| BLK2020-2.8                | 820  | 950  | 1200 | 1400 | 1600 | 1800 |
| BLK2020-3.6                | 820  | 950  | 1200 | 1400 | 1600 | 1800 |
| BLK2525-2.8                | 1100 | 1400 | 1600 | 1800 | 2000 | 2400 |
| BLK2525-3.6                | 1100 | 1400 | 1600 | 1800 | 2000 | 2400 |
| BLK3232-2.8                | 1600 | 1800 | 2200 | 2500 | 2800 | 3200 |
| BLK3232-3.6                | 1600 | 1800 | 2200 | 2500 | 2800 | 3200 |
| BLK3620-5.6                | 2000 | 2100 | 2550 | 2950 | 3250 | 3650 |
| BLK3624-5.6                | 2000 | 2100 | 2550 | 2950 | 3250 | 3650 |
| BLK3636-2.8                | 2000 | 2100 | 2550 | 2950 | 3250 | 3650 |
| BLK3636-3.6                | 2000 | 2100 | 2550 | 2950 | 3250 | 3650 |
| BLK4040-2.8                | 2000 | 2400 | 2900 | 3400 | 3700 | 4300 |
| BLK4040-3.6                | 2000 | 2400 | 2900 | 3400 | 3700 | 4300 |
| BLK5050-2.8                | 2000 | 3100 | 3800 | 4500 | 5000 | 5800 |
| BLK5050-3.6                | 2000 | 3100 | 3800 | 4500 | 5000 | 5800 |

\* BLK0808-3.2 is only compatible with accuracy grades C3, C5, and C7. Contact THK if you would like to use accuracy grades C0 or C1.

Table4 Maximum Manufacturing Length of Precision Ball Screws (DIN Standard-Compliant Ball Screws)

Unit: mm

| Shaft diameter | Ground shaft |      |      | CES shaft |      |      |      |
|----------------|--------------|------|------|-----------|------|------|------|
|                | C3           | C5   | C7   | Cp3       | Cp5  | Ct5  | Ct7  |
| 16             | 1050         | 1100 | 1400 | 1050      | 1100 | 1100 | 1400 |
| 20             | 1400         | 1600 | 1800 | 1400      | 1600 | 1600 | 1800 |
| 25             | 1800         | 2000 | 2400 | 1800      | 2000 | 2000 | 2400 |
| 32             | 2500         | 2800 | 3200 | 2500      | 2800 | 2800 | 3200 |
| 40             | 3400         | 3700 | 4300 | 3400      | 3700 | 3700 | 4300 |
| 50             | 4500         | 5000 | 5800 | —         | —    | —    | —    |
| 63             | 5800         | 6700 | 7700 | —         | —    | —    | —    |

Table5 Maximum Manufacturing Length of Rolled Ball Screws by Accuracy Grade

Unit: mm

| Screw shaft outer diameter | Overall screw shaft length |      |      |
|----------------------------|----------------------------|------|------|
|                            | C7                         | C8   | C10  |
| 6 to 8                     | 320                        | 320  | —    |
| 10 to 12                   | 500                        | 1000 | —    |
| 14 to 15                   | 1500                       | 1500 | 1500 |
| 16 to 18                   | 1500                       | 1800 | 1800 |
| 20                         | 2000                       | 2200 | 2200 |
| 25                         | 2000                       | 3000 | 3000 |
| 28                         | 3000                       | 3000 | 3000 |
| 30                         | 3000                       | 3000 | 4000 |
| 32 to 36                   | 3000                       | 4000 | 4000 |
| 40                         | 3000                       | 5000 | 5000 |
| 45                         | 3000                       | 5500 | 5500 |
| 50                         | 3000                       | 6000 | 6000 |

Table6 Maximum Manufacturing Lengths of Rolled Ball Screws (Model JPF with Preload) by Model Number

Unit: mm

| Model     | Overall screw shaft length |
|-----------|----------------------------|
| JPF1404-4 | 1000                       |
| JPF1405-4 |                            |
| JPF1605-4 |                            |
| JPF2005-6 | 2000                       |
| JPF2505-6 |                            |
| JPF2510-4 |                            |
| JPF2805-6 |                            |
| JPF2806-6 | 3000                       |
| JPF3210-6 |                            |
| JPF3610-6 |                            |
| JPF4010-6 |                            |

Table7 Maximum Manufacturing Lengths of Rolled Ball Screws (Model MTF with Preload) by Model Number

Unit: mm

| Screw shaft outer diameter | C7  | C8   | C10 |
|----------------------------|-----|------|-----|
| MTF0601-3.7                | 320 | 320  | —   |
| MTF0801-3.7                | 320 | —    | 450 |
| MTF0802-3.7                | 320 | 320  | —   |
| MTF0805-2.7                | 320 | —    | 450 |
| MTF1002-3.7                | 500 | 1000 | —   |
| MTF1004-2.7                | 500 | —    | 650 |
| MTF1202-3.7                | 500 | 1000 | —   |
| MTF1402-3.7                | 700 | —    | 700 |

Table8 Maximum Manufacturing Lengths of Rolled Ball Screws (Model BLK with Preload) by Model Number

Unit: mm

| Screw shaft outer diameter | C7   | C8   | C10  |
|----------------------------|------|------|------|
| BLK0808-3.2                | 320  | —    | 450  |
| BLK1010-3.2                | 500  | —    | 650  |
| BLK1510-5.6                | 1500 | 1500 | 1500 |
| BLK1616-3.6                | 1500 | 1800 | 1800 |
| BLK1616-7.2                | 1500 | 1800 | 1800 |
| BLK2020-3.6                | 2000 | 2200 | 2200 |
| BLK2020-7.2                | 2000 | 2200 | 2200 |
| BLK2525-3.6                | 2000 | 3000 | 3000 |
| BLK2525-7.2                | 2000 | 3000 | 3000 |
| BLK3232-3.6                | 3000 | 4000 | 4000 |
| BLK3232-7.2                | 3000 | 4000 | 4000 |
| BLK3620-5.6                | 3000 | 4000 | 4000 |
| BLK3624-5.6                | 3000 | 4000 | 4000 |
| BLK3636-3.6                | 3000 | 4000 | 4000 |
| BLK3636-7.2                | 3000 | 4000 | 4000 |
| BLK4040-3.6                | 3000 | 5000 | 5000 |
| BLK4040-7.2                | 3000 | 5000 | 5000 |
| BLK5050-3.6                | 3000 | 6000 | 6000 |
| BLK5050-7.2                | 3000 | 6000 | 6000 |



**Ball Screw**

# **Ball Screw Peripherals**

# Support Unit

Models EK, BK, FK, EF, BF and FF




Fig.1 Structure of the Support Unit

## Structure and Features

The support unit comes in six types: models EK, FK, EF, and FF, which are tailored to model BNK precision ball screw with finished shaft ends, and models BK and BF, which are standardized for general ball screws.

The support unit on the fixed side includes a JIS Class 5-compliant angular bearing provided with an adjusted preload.

The Support Unit on the supported side uses a deep-groove ball bearing.

The internal bearings of the Support Unit models EK, FK and BK contain an appropriate amount of lithium soap-group grease that is sealed with a special seal. Thus, these models are capable of operating over a long period.

**[Uses the Optimal Bearing]**


To ensure the rigidity balance with the Ball Screw, the Support Unit uses an angular bearing (contact angle: 30°; DF configuration) with a high rigidity and a low torque. Miniature Support Unit models EK/FK 4, 5 and 6 are incorporated with a miniature angular bearing with a contact angle of 45° developed exclusively for miniature Ball Screws. This bearing has a greater contact angle of 45° and an increased number of balls with a smaller diameter. The high rigidity and accuracy of the miniature angular bearing provides the stable rotational performance.

**[Support Unit Shapes]**


The square and round shapes are available for the Support Unit to allow the selection according to the intended use.

Example of Installation

Square Type



Round Type

**[Compact and Easy Installation]**


The Support Unit is compactly designed to accommodate the space in the installation site. As the bearing is provided with an appropriately adjusted preload, the Support Unit can be assembled with a Ball Screw unit with no further machining. Accordingly, the required man-hours in the assembly can be reduced and the assembly accuracy can be increased.

## Type

[For the Fixed Side]

### Square Type Model EK


Specification Table⇒ **A** 15-308



(Inner diameter:  $\phi 4$  to  $\phi 20$ )

### Square Type Model BK


Specification Table⇒ **A** 15-310



(Inner diameter:  $\phi 10$  to  $\phi 40$ )

### Round Type Model FK

Specification Table⇒ **A** 15-312




(Inner diameter:  $\phi 4$  to  $\phi 30$ )

[For the Supported Side]

### Square Type Model EF


Specification Table⇒ **A** 15-316



(Inner diameter:  $\phi 6$  to  $\phi 20$ )

### Square Type Model BF


Specification Table⇒ **A** 15-318



(Inner diameter:  $\phi 8$  to  $\phi 40$ )

### Round Type Model FF

Specification Table⇒ **A** 15-320



(Inner diameter:  $\phi 6$  to  $\phi 30$ )

## Types of Support Units and Applicable Screw Shaft Outer Diameters

| Inner diameter of fixed-side Support Unit (mm) | Inner diameter of supported-side Support Unit (mm) | Applicable Model No. of fixed-side Support Unit | Applicable model No. of the supported side Support Unit | Type BNK with Unfinished Shaft Ends(Applicable Model No.)      | Recommended Shapes of Shaft Ends(Applicable Shaft Outer Diameter $\phi D$ ) |                                     |
|--|--|---|---|--|---|-------------------------------------|
|  |  |   |   |  | Shaft End H (mm)  | Shaft End J (mm)                    |
| 4  | —  | EK 4<br>FK 4                                    | —   | BNK0401<br>BNK0501   | $\phi 6$  | —                                   |
| 5  | —  | EK 5<br>FK 5                                    | —   | BNK0601  | $\phi 8$  | —                                   |
| 6  | 6  | EK 6<br>FK 6                                    | EF 6<br>FF 6  | BNK0801<br>BNK0802<br>BNK0810                                  | $\phi 8$<br>$\phi 10$   | —                                   |
| 8  | 6  | EK 8<br>FK 8                                    | EF 8<br>FF 6  | BNK1002  | $\phi 12$   | —                                   |
| 10   | 8  | EK 10<br>FK 10<br>BK 10                         | EF 10<br>FF 10<br>BF 10                                 | BNK1004<br>BNK1010<br>BNK1202<br>BNK1205<br>BNK1208            | $\phi 14$<br>$\phi 15$  | $\phi 14$<br>$\phi 15$              |
| 12   | 10   | EK 12<br>FK 12<br>BK 12                         | EF 12<br>FF 12<br>BF 12                                 | BNK1402<br>BNK1404<br>BNK1408<br>BNK1510<br>BNK1520<br>BNK1616 | $\phi 16$<br>$\phi 18$  | $\phi 16$<br>$\phi 18$              |
| 15   | 15   | EK 15<br>FK 15                                  | EF 15<br>FF 15  | BNK2010<br>BNK2020   | $\phi 20$<br>$\phi 25$  | —                                   |
|  |  | BK 15   | BF 15   | —  | —   | $\phi 20$                           |
| 17   | 17   | BK 17   | BF 17   | —  | —   | $\phi 25$                           |
| 20   | 20   | EK 20<br>FK 20                                  | EF 20<br>FF 20  | BNK2520  | $\phi 28$<br>$\phi 30$<br>$\phi 32$   | —                                   |
|  |  | BK 20   | BF 20   | —  | —   | $\phi 28$<br>$\phi 30$<br>$\phi 32$ |
| 25   | 25   | FK 25   | FF 25   | —  | $\phi 36$   | —                                   |
|  |  | BK 25   | BF 25   | —  | —   | $\phi 36$                           |
| 30   | 30   | FK 30   | FF 30   | —  | $\phi 40$   | $\phi 40$                           |
|  |  | BK 30   | BF 30   | —  |   |                                     |
| 35   | 35   | BK 35   | BF 35   | —  | —   | $\phi 45$                           |
| 40   | 40   | BK 40   | BF 40   | —  | —   | $\phi 50$<br>$\phi 55$              |

Note1) The Supports Units in this table apply only to those Ball Screw models with recommended shaft ends shapes H, J and K, indicated on **A15-306**.

Note2) For Recommended Shapes of Shaft Ends H, J, and K; refer to pages **A15-322** to **A15-327**.

## Model Numbers of Bearings and Characteristic Values

| Angular ball bearing on the fixed side |                         |                                   |                             |                       | Deep-groove ball bearing on the supported side |                   |                                 |                                 |
|--|-------------------------|-----------------------------------|-----------------------------|-----------------------|--|-------------------|---------------------------------|---------------------------------|
| Support Unit model No.                 | Bearing                 | Axial direction                   |                             |                       | Support Unit model No.                         | Bearing model No. | Radial direction                |                                 |
|  |                         | Basic dynamic load rating Ca (kN) | Note) Permissible load (kN) | Rigidity (N/ $\mu$ m) |  |                   | Basic dynamic load rating C(kN) | Basic static load rating Co(kN) |
| EK 4<br>FK 4                           | 704 equivalent (DF P5)  | 0.93                              | 1.1                         | 27                    | —  | —                 | —                               | —                               |
| EK 5<br>FK 5                           | 705 equivalent (DF P5)  | 1                                 | 1.24                        | 29                    | —  | —                 | —                               | —                               |
| EK 6<br>FK 6                           | 706 equivalent (DF P5)  | 1.38                              | 1.76                        | 35                    | EF 6<br>FF 6                                   | 606ZZ             | 2.19                            | 0.87                            |
| EK 8<br>FK 8                           | 798 equivalent (DF P5)  | 2.93                              | 2.15                        | 49                    | EF 8   | 606ZZ             | 2.19                            | 0.87                            |
| EK 10<br>FK 10<br>BK 10                | 7000 equivalent (DF P5) | 6.08                              | 3.1                         | 65                    | EF 10<br>FF 10<br>BF 10                        | 608ZZ             | 3.35                            | 1.4                             |
| EK 12<br>FK 12<br>BK 12                | 7001 equivalent (DF P5) | 6.66                              | 3.25                        | 88                    | EF 12<br>FF 12<br>BF 12                        | 6000ZZ            | 4.55                            | 1.96                            |
| EK 15<br>FK 15<br>BK 15                | 7002 equivalent (DF P5) | 7.6                               | 4                           | 100                   | EF 15<br>FF 15<br>BF 15                        | 6002ZZ            | 5.6                             | 2.84                            |
| BK 17                                  | 7203 equivalent (DF P5) | 13.7                              | 5.85                        | 125                   | BF 17  | 6203ZZ            | 9.6                             | 4.6                             |
| EK 20<br>FK 20                         | 7204 equivalent (DF P5) | 17.9                              | 9.5                         | 170                   | EF 20<br>FF 20                                 | 6204ZZ            | 12.8                            | 6.65                            |
| BK 20                                  | 7004 equivalent (DF P5) | 12.7                              | 7.55                        | 140                   | BF 20  | 6004ZZ            | 9.4                             | 5.05                            |
| FK 25<br>BK 25                         | 7205 equivalent (DF P5) | 20.2                              | 11.5                        | 190                   | FF 25<br>BF 25                                 | 6205ZZ            | 14                              | 7.85                            |
| FK 30<br>BK 30                         | 7206 equivalent (DF P5) | 28                                | 16.3                        | 195                   | FF 30<br>BF 30                                 | 6206ZZ            | 19.5                            | 11.3                            |
| BK 35                                  | 7207 equivalent (DF P5) | 37.2                              | 21.9                        | 255                   | BF 35  | 6207ZZ            | 25.7                            | 15.3                            |
| BK 40                                  | 7208 equivalent (DF P5) | 44.1                              | 27.1                        | 270                   | BF 40  | 6208ZZ            | 29.1                            | 17.8                            |

Note) "Permissible load" indicates the static permissible load.

## Example of Installation

### [Square Type Support Unit]




Fig.2 Example of Installing a Square Type Support Unit

### [Round Type Support Unit]




Fig.3 Example of Installing a Round Type Support Unit

## Mounting Procedure


### [Installing the Support Unit]

- (1) Install the fixed side Support Unit with the screw shaft.
- (2) After inserting the fixed side Support Unit, secure the lock nut using the fastening set piece and the hexagonal socket-head setscrews.
- (3) Attach the supported side bearing to the screw shaft and secure the bearing using the snap ring, and then install the assembly to the housing on the supported side.

Note1) Do not disassemble the Support Unit.


Note2) When inserting the screw shaft to the Support Unit, take care not to let the oil seal lip turn outward.

Note3) When securing the set piece with a hexagonal socket-head setscrew, apply an adhesive to the hexagonal socket-head setscrew before tightening it in order to prevent the screw from loosening. If planning to use the product in a harsh environment, it is also necessary to take a measure to prevent other components/parts from loosening. Contact THK for details.



### [Installation onto the Table and the Base]


- (1) If using a bracket when mounting the ball screw nut to the table, insert the nut into the bracket and temporarily fasten it.
- (2) Temporarily fasten the fixed side Support Unit to the base. In doing so, press the table toward the fixed side Support Unit to align the axial center, and adjust the table so that it can travel freely.
  - If using the fixed side Support Unit as the reference point, secure a clearance between the ball screw nut and the table or inside the bracket when making adjustment.
  - If using the table as the reference point, make the adjustment either by using the shim (for a square type Support Unit), or securing the clearance between the outer surface of the nut and the inner surface of the mounting section (for a round type Support Unit).
- (3) Press the table toward the fixed-side Support Unit to align the axial center. Make the adjustment by reciprocating the table several times so that the nut travels smoothly throughout the whole stroke, and temporarily secure the Support Unit to the base.





### [Checking the Accuracy and Fully Fastening the Support Unit]

While checking the runout of the ball screw shaft end and the axial clearance using a dial gauge, fully fasten the ball screw nut, the nut bracket, the fixed side Support Unit and the supported-side Support Unit, in this order.




### [Connection with the Motor]

- (1) Mount the motor bracket to the base.
- (2) Connect the motor and the ball screw using a coupling.


Note) Make sure the mounting accuracy is maintained.

- (3) Thoroughly perform the break-in for the system.




## Types of Recommended Shapes of the Shaft Ends

To ensure speedy estimates and manufacturing of Ball Screws, THK has standardized the shaft end shapes of the screw shafts. The recommended shapes of shaft ends consist of shapes H, K and J, which allow standard Support Units to be used.

| Mounting method | Symbol for shaft end shape | Shape   | Supported Support Unit |
|-----------------|----------------------------|---|------------------------|
| Fixed           | H J                        | H1  | FK<br>EK               |
|                 |                            | J1  | BK                     |
|                 |                            | H2  | FK<br>EK               |
|                 |                            | J2  | BK                     |
|                 |                            | H3  | FK<br>EK               |
|                 |                            | J3  | BK                     |
| Supported       | K                          |  | FF<br>EF<br>BF         |



## EK Square Type Support Unit on the Fixed Side




Models EK 4 and 5

Models EK 6 and 8

| Model No. | Shaft diameter<br>d | L    | L <sub>1</sub> | L <sub>2</sub> | L <sub>3</sub> | B  | H  | b<br>±0.02 |
|-----------|---------------------|------|----------------|----------------|----------------|----|----|------------|
| EK 4      | 4                   | 15   | 5.5            | 17.5           | 3              | 34 | 19 | 17         |
| EK 5      | 5                   | 16.5 | 5.5            | 18.5           | 3.5            | 36 | 21 | 18         |
| EK 6      | 6                   | 20   | 5.5            | 22             | 3.5            | 42 | 25 | 21         |
| EK 8      | 8                   | 23   | 7              | 26             | 4              | 52 | 32 | 26         |
| EK 10     | 10                  | 24   | 6              | 29.5           | 6              | 70 | 43 | 35         |
| EK 12     | 12                  | 24   | 6              | 29.5           | 6              | 70 | 43 | 35         |
| EK 15     | 15                  | 25   | 6              | 36             | 5              | 80 | 49 | 40         |
| EK 20     | 20                  | 42   | 10             | 50             | 10             | 95 | 58 | 47.5       |

Models EK 4 to 8

| Part No. | Part name  | No. of units |
|----------|--|--------------|
| 1        | Housing  | 1            |
| 2        | Bearing  | 1 set        |
| 3        | Set nut  | 1            |
| 4        | Collar   | 2            |
| 5        | Seal   | 1            |
| 6        | Lock Nut   | 1            |
| 7        | Hexagonal socket-head setscrew<br>(with a set piece) | 1            |



Models EK 10 to 20


Unit: mm

| $h_1$<br>$\pm 0.02$ | $B_1$ | $H_1$ | P  | $d_1$ | $d_2$ | h  | M    | T  | D    | t   | Bearing used            | Mass<br>kg |
|---------------------|-------|-------|----|-------|-------|----|------|----|------|-----|-------------------------|------------|
| 10                  | 18    | 7     | 26 | 4.5   | —     | —  | M2.6 | 10 | 6    | 4.5 | 704 equivalent (DF P5)  | 0.06       |
| 11                  | 20    | 8     | 28 | 4.5   | —     | —  | M2.6 | 11 | 8    | 5.5 | 705 equivalent (DF P5)  | 0.08       |
| 13                  | 18    | 20    | 30 | 5.5   | 9.5   | 11 | M3   | 12 | 9.5  | 7   | 706 equivalent (DF P5)  | 0.14       |
| 17                  | 25    | 26    | 38 | 6.6   | 11    | 12 | M3   | 14 | 11.5 | 7.5 | 798 equivalent (DF P5)  | 0.24       |
| 25                  | 36    | 24    | 52 | 9     | —     | —  | M3   | 16 | 13.9 | 5.5 | 7000 equivalent (DF P5) | 0.46       |
| 25                  | 36    | 24    | 52 | 9     | —     | —  | M3   | 19 | 14.9 | 5.5 | 7001 equivalent (DF P5) | 0.44       |
| 30                  | 41    | 25    | 60 | 11    | —     | —  | M3   | 22 | 19.5 | 10  | 7002 equivalent (DF P5) | 0.55       |
| 30                  | 56    | 25    | 75 | 11    | —     | —  | M4   | 30 | 25   | 11  | 7204 equivalent (DF P5) | 1.35       |


Models EK 10 to 20

| Part No. | Part name  | No. of units |
|----------|--|--------------|
| 1        | Housing  | 1            |
| 2        | Bearing  | 1 set        |
| 3        | Holding lid  | 1            |
| 4        | Collar   | 2            |
| 5        | Seal   | 2            |
| 6        | Lock Nut   | 1            |
| 7        | Hexagonal socket-head setscrew<br>(with a set piece) | 1            |

## BK Square Type Support Unit on the Fixed Side



| Model No. | Shaft diameter | L  | L <sub>1</sub> | L <sub>2</sub> | L <sub>3</sub> | B   | H   | b<br>±0.02 | h <sub>1</sub><br>±0.02 | B <sub>1</sub> | H <sub>1</sub> |
|-----------|----------------|----|----------------|----------------|----------------|-----|-----|------------|-------------------------|----------------|----------------|
|           | d              |    |                |                |                |     |     |            |                         |                |                |
| BK 10     | 10             | 25 | 5              | 29             | 5              | 60  | 39  | 30         | 22                      | 34             | 32.5           |
| BK 12     | 12             | 25 | 5              | 29             | 5              | 60  | 43  | 30         | 25                      | 35             | 32.5           |
| BK 15     | 15             | 27 | 6              | 32             | 6              | 70  | 48  | 35         | 28                      | 40             | 38             |
| BK 17     | 17             | 35 | 9              | 44             | 7              | 86  | 64  | 43         | 39                      | 50             | 55             |
| BK 20     | 20             | 35 | 8              | 43             | 8              | 88  | 60  | 44         | 34                      | 52             | 50             |
| BK 25     | 25             | 42 | 12             | 54             | 9              | 106 | 80  | 53         | 48                      | 64             | 70             |
| BK 30     | 30             | 45 | 14             | 61             | 9              | 128 | 89  | 64         | 51                      | 76             | 78             |
| BK 35     | 35             | 50 | 14             | 67             | 12             | 140 | 96  | 70         | 52                      | 88             | 79             |
| BK 40     | 40             | 61 | 18             | 76             | 15             | 160 | 110 | 80         | 60                      | 100            | 90             |




Collar details

Unit: mm

|  | P   | C <sub>1</sub> | C <sub>2</sub> | d <sub>1</sub> | d <sub>2</sub> | h    | M  | T  | D    | t  | Bearing used            | Mass<br>kg |
|--|-----|----------------|----------------|----------------|----------------|------|----|----|------|----|-------------------------|------------|
|  | 46  | 13             | 6              | 6.6            | 10.8           | 5    | M3 | 16 | 13.9 | 5  | 7000 equivalent (DF P5) | 0.39       |
|  | 46  | 13             | 6              | 6.6            | 10.8           | 1.5  | M3 | 19 | 14.9 | 5  | 7001 equivalent (DF P5) | 0.41       |
|  | 54  | 15             | 6              | 6.6            | 11             | 6.5  | M3 | 22 | 19.5 | 6  | 7002 equivalent (DF P5) | 0.57       |
|  | 68  | 19             | 8              | 9              | 14             | 8.5  | M4 | 24 | 23.4 | 7  | 7203 equivalent (DF P5) | 1.27       |
|  | 70  | 19             | 8              | 9              | 14             | 8.5  | M4 | 30 | 27.4 | 8  | 7004 equivalent (DF P5) | 1.19       |
|  | 85  | 22             | 10             | 11             | 17.5           | 11   | M5 | 35 | 31.3 | 9  | 7205 equivalent (DF P5) | 2.3        |
|  | 102 | 23             | 11             | 14             | 20             | 13   | M6 | 40 | 37.3 | 9  | 7206 equivalent (DF P5) | 3.32       |
|  | 114 | 26             | 12             | 14             | 20             | 13   | M8 | 50 | 44.3 | 12 | 7207 equivalent (DF P5) | 4.33       |
|  | 130 | 33             | 14             | 18             | 26             | 17.5 | M8 | 50 | 49.4 | 15 | 7208 equivalent (DF P5) | 6.5        |


| Part No. | Part name  | No. of units |
|----------|--|--------------|
| 1        | Housing  | 1            |
| 2        | Bearing  | 1 set        |
| 3        | Holding lid  | 1            |
| 4        | Collar   | 2            |
| 5        | Seal   | 2            |
| 6        | Lock Nut   | 1            |
| 7        | Hexagonal socket-head setscrew<br>(with a set piece) | 1            |

# FK Round Type Support Unit on the Fixed Side



Mounting method A

4- $\phi$  d1 through hole,  
 $\phi$  d2 counter bore depth h  
 (90° equidistant)




Models FK 4 to 8


| Model No. | Shaft diameter | L    | H | F    | E    | D                      | A  | PCD | B  |
|-----------|----------------|------|---|------|------|------------------------|----|-----|----|
|           | d              |      |   |      |      |                        |    |     |    |
| FK 4      | 4              | 15   | 6 | 9    | 17.5 | 18<br>-0.006<br>-0.017 | 32 | 24  | 25 |
| FK 5      | 5              | 16.5 | 6 | 10.5 | 18.5 | 20<br>-0.007<br>-0.02  | 34 | 26  | 26 |
| FK 6      | 6              | 20   | 7 | 13   | 22   | 22<br>-0.007<br>-0.02  | 36 | 28  | 28 |
| FK 8      | 8              | 23   | 9 | 14   | 26   | 28<br>-0.007<br>-0.02  | 43 | 35  | 35 |

Note) When using a Model BNK finished shaft end precision ball screw, use mounting method A only.





Mounting method B




Collar details

Unit: mm

|  | Installation procedure A |       | Installation procedure B |       | $d_1$ | $d_2$ | h | M    | T  | D    | t   | Bearing used           | Mass<br>kg |
|--|--------------------------|-------|--------------------------|-------|-------|-------|---|------|----|------|-----|------------------------|------------|
|  | $L_1$                    | $T_1$ | $L_2$                    | $T_2$ |       |       |   |      |    |      |     |                        |            |
|  | 5.5                      | 3     | 6.5                      | 4     | 3.4   | 6.5   | 4 | M2.6 | 10 | 6    | 4.5 | 704 equivalent (DF P5) | 0.05       |
|  | 5.5                      | 3.5   | 7                        | 5     | 3.4   | 6.5   | 4 | M2.6 | 11 | 8    | 5.5 | 705 equivalent (DF P5) | 0.06       |
|  | 5.5                      | 3.5   | 8.5                      | 6.5   | 3.4   | 6.5   | 4 | M3   | 12 | 9.5  | 7   | 706 equivalent (DF P5) | 0.08       |
|  | 7                        | 4     | 10                       | 7     | 3.4   | 6.5   | 4 | M3   | 14 | 11.5 | 7.5 | 798 equivalent (DF P5) | 0.15       |


| Part No. | Part name  | No. of units |
|----------|--|--------------|
| 1        | Housing  | 1            |
| 2        | Bearing  | 1 set        |
| 3        | Set nut  | 1            |
| 4        | Collar   | 2            |
| 5        | Seal   | 1            |
| 6        | Lock Nut   | 1            |
| 7        | Hexagonal socket-head setscrew<br>(with a set piece) | 1            |

# FK Round Type Support Unit on the Fixed Side




Mounting method A

4- $\phi d_1$  through hole,  
 $\phi d_2$  counter bore depth h  
 (90° equidistant)




Models FK 10 to 30

| Model No. | Shaft diameter | L  | H  | F  | E    | D                      | A   | PCD | B  |
|-----------|----------------|----|----|----|------|------------------------|-----|-----|----|
|           | d              |    |    |    |      |                        |     |     |    |
| FK 10     | 10             | 27 | 10 | 17 | 29.5 | 34<br>-0.009<br>-0.025 | 52  | 42  | 42 |
| FK 12     | 12             | 27 | 10 | 17 | 29.5 | 36<br>-0.009<br>-0.025 | 54  | 44  | 44 |
| FK 15     | 15             | 32 | 15 | 17 | 36   | 40<br>-0.009<br>-0.025 | 63  | 50  | 52 |
| FK 20     | 20             | 52 | 22 | 30 | 50   | 57<br>-0.01<br>-0.029  | 85  | 70  | 68 |
| FK 25     | 25             | 57 | 27 | 30 | 60   | 63<br>-0.01<br>-0.029  | 98  | 80  | 79 |
| FK 30     | 30             | 62 | 30 | 32 | 61   | 75<br>-0.01<br>-0.029  | 117 | 95  | 93 |



Mounting method B




Collar details

Unit: mm

|  | Installation procedure A |       | Installation procedure B |       | $d_1$ | $d_2$ | $h$ | M  | T  | D    | $t$ | Bearing used            | Mass<br>kg |
|--|--------------------------|-------|--------------------------|-------|-------|-------|-----|----|----|------|-----|-------------------------|------------|
|  | $L_1$                    | $T_1$ | $L_2$                    | $T_2$ |       |       |     |    |    |      |     |                         |            |
|  | 7.5                      | 5     | 8.5                      | 6     | 4.5   | 8     | 4   | M3 | 16 | 13.9 | 5.5 | 7000 equivalent (DF P5) | 0.21       |
|  | 7.5                      | 5     | 8.5                      | 6     | 4.5   | 8     | 4   | M3 | 19 | 14.9 | 5.5 | 7001 equivalent (DF P5) | 0.22       |
|  | 10                       | 6     | 12                       | 8     | 5.5   | 9.5   | 6   | M3 | 22 | 19.5 | 10  | 7002 equivalent (DF P5) | 0.39       |
|  | 8                        | 10    | 12                       | 14    | 6.6   | 11    | 10  | M4 | 30 | 25   | 11  | 7204 equivalent (DF P5) | 1.09       |
|  | 13                       | 10    | 20                       | 17    | 9     | 15    | 13  | M5 | 35 | 31.3 | 15  | 7205 equivalent (DF P5) | 1.49       |
|  | 11                       | 12    | 17                       | 18    | 11    | 17.5  | 15  | M6 | 40 | 37.3 | 9   | 7206 equivalent (DF P5) | 2.32       |

| Part No. | Part name  | No. of units |
|----------|--|--------------|
| 1        | Housing  | 1            |
| 2        | Bearing  | 1 set        |
| 3        | Holding lid  | 1            |
| 4        | Collar   | 2            |
| 5        | Seal   | 2            |
| 6        | Lock Nut   | 1            |
| 7        | Hexagonal socket-head setscrew<br>(with a set piece) | 1            |


## EF Square Type Support Unit on the Supported Side



Models EF 6 and 8

| Model No. | Shaft diameter<br>d | L  | B  | H  | b<br>±0.02 | h <sub>1</sub><br>±0.02 | B <sub>1</sub> |
|-----------|---------------------|----|----|----|------------|-------------------------|----------------|
| EF 6      | 6                   | 12 | 42 | 25 | 21         | 13                      | 18             |
| EF 8      | 6                   | 14 | 52 | 32 | 26         | 17                      | 25             |
| EF 10     | 8                   | 20 | 70 | 43 | 35         | 25                      | 36             |
| EF 12     | 10                  | 20 | 70 | 43 | 35         | 25                      | 36             |
| EF 15     | 15                  | 20 | 80 | 49 | 40         | 30                      | 41             |
| EF 20     | 20                  | 26 | 95 | 58 | 47.5       | 30                      | 56             |

Note) The area marked with "\*" is imprinted with a numeric character(s) as part of the model number.



Models EF 10 to 20


Unit: mm

|  | $H_1$ | P  | $d_1$ | $d_2$ | h  | Bearing used | Snap ring size | Mass kg |
|--|-------|----|-------|-------|----|--------------|----------------|---------|
|  | 20    | 30 | 5.5   | 9.5   | 11 | 606ZZ        | C6             | 0.07    |
|  | 26    | 38 | 6.6   | 11    | 12 | 606ZZ        | C6             | 0.13    |
|  | 24    | 52 | 9     | —     | —  | 608ZZ        | C8             | 0.33    |
|  | 24    | 52 | 9     | —     | —  | 6000ZZ       | C10            | 0.32    |
|  | 25    | 60 | 9     | —     | —  | 6002ZZ       | C15            | 0.38    |
|  | 25    | 75 | 11    | —     | —  | 6204ZZ       | C20            | 0.63    |

| Part No. | Part name | No. of units |
|----------|-----------|--------------|
| 1        | Housing   | 1            |
| 2        | Bearing   | 1            |
| 3        | Snap ring | 1            |


## BF Square Type Support Unit on the Supported Side

2- $\phi$  d<sub>1</sub> through hole,  
 $\phi$  d<sub>2</sub> counter bore depth h



| Model No. | Shaft diameter<br>d | L  | B   | H   | b<br>$\pm 0.02$ | h <sub>1</sub><br>$\pm 0.02$ | B <sub>1</sub> | H <sub>1</sub> |
|-----------|---------------------|----|-----|-----|-----------------|------------------------------|----------------|----------------|
| BF 10     | 8                   | 20 | 60  | 39  | 30              | 22                           | 34             | 32.5           |
| BF 12     | 10                  | 20 | 60  | 43  | 30              | 25                           | 35             | 32.5           |
| BF 15     | 15                  | 20 | 70  | 48  | 35              | 28                           | 40             | 38             |
| BF 17     | 17                  | 23 | 86  | 64  | 43              | 39                           | 50             | 55             |
| BF 20     | 20                  | 26 | 88  | 60  | 44              | 34                           | 52             | 50             |
| BF 25     | 25                  | 30 | 106 | 80  | 53              | 48                           | 64             | 70             |
| BF 30     | 30                  | 32 | 128 | 89  | 64              | 51                           | 76             | 78             |
| BF 35     | 35                  | 32 | 140 | 96  | 70              | 52                           | 88             | 79             |
| BF 40     | 40                  | 37 | 160 | 110 | 80              | 60                           | 100            | 90             |

Note) The area marked with "\*" is imprinted with a numeric character(s) as part of the model number.




Unit: mm

|  | P   | $d_1$ | $d_2$ | h    | Bearing used | Snap ring used | Mass<br>kg |
|--|-----|-------|-------|------|--------------|----------------|------------|
|  | 46  | 6.6   | 10.8  | 5    | 608ZZ        | C8             | 0.29       |
|  | 46  | 6.6   | 10.8  | 1.5  | 6000ZZ       | C10            | 0.3        |
|  | 54  | 6.6   | 11    | 6.5  | 6002ZZ       | C15            | 0.38       |
|  | 68  | 9     | 14    | 8.5  | 6203ZZ       | C17            | 0.74       |
|  | 70  | 9     | 14    | 8.5  | 6004ZZ       | C20            | 0.76       |
|  | 85  | 11    | 17.5  | 11   | 6205ZZ       | C25            | 1.42       |
|  | 102 | 14    | 20    | 13   | 6206ZZ       | C30            | 1.97       |
|  | 114 | 14    | 20    | 13   | 6207ZZ       | C35            | 2.22       |
|  | 130 | 18    | 26    | 17.5 | 6208ZZ       | C40            | 3.27       |

| Part No. | Part name | No. of units |
|----------|-----------|--------------|
| 1        | Housing   | 1            |
| 2        | Bearing   | 1            |
| 3        | Snap ring | 1            |


## FF Round Type Support Unit on the Supported Side

4- $\phi$  d1 through hole,  
 $\phi$  d2 counter bore depth h  
 (90° equidistant)



| Model No. | Shaft diameter | L  | H  | F  | D                      | A   |
|-----------|----------------|----|----|----|------------------------|-----|
|           | d              |    |    |    |                        |     |
| FF 6      | 6              | 10 | 6  | 4  | 22<br>-0.007<br>-0.02  | 36  |
| FF 10     | 8              | 12 | 7  | 5  | 28<br>-0.007<br>-0.02  | 43  |
| FF 12     | 10             | 15 | 7  | 8  | 34<br>-0.009<br>-0.025 | 52  |
| FF 15     | 15             | 17 | 9  | 8  | 40<br>-0.009<br>-0.025 | 63  |
| FF 20     | 20             | 20 | 11 | 9  | 57<br>-0.01<br>-0.029  | 85  |
| FF 25     | 25             | 24 | 14 | 10 | 63<br>-0.01<br>-0.029  | 98  |
| FF 30     | 30             | 27 | 18 | 9  | 75<br>-0.01<br>-0.029  | 117 |






Unit: mm

|  | PCD | B  | $d_1$ | $d_2$ | h   | Bearing used | Snap ring used | Mass<br>kg |
|--|-----|----|-------|-------|-----|--------------|----------------|------------|
|  | 28  | 28 | 3.4   | 6.5   | 4   | 606ZZ        | C6             | 0.04       |
|  | 35  | 35 | 3.4   | 6.5   | 4   | 608ZZ        | C8             | 0.07       |
|  | 42  | 42 | 4.5   | 8     | 4   | 6000ZZ       | C10            | 0.11       |
|  | 50  | 52 | 5.5   | 9.5   | 5.5 | 6002ZZ       | C15            | 0.2        |
|  | 70  | 68 | 6.6   | 11    | 6.5 | 6204ZZ       | C20            | 0.27       |
|  | 80  | 79 | 9     | 14    | 8.5 | 6205ZZ       | C25            | 0.67       |
|  | 95  | 93 | 11    | 17.5  | 11  | 6206ZZ       | C30            | 1.07       |

| Part No. | Part name | No. of units |
|----------|-----------|--------------|
| 1        | Housing   | 1            |
| 2        | Bearing   | 1            |
| 3        | Snap ring | 1            |

## Recommended Shapes of Shaft Ends - Shape H (H1, H2 and H3) (For Support Unit Models FK and EK)




| Support Unit model No. |          | Ball screw shaft outer diameter<br>d | Shaft outer diameter of the bearing<br>A | B  | E  | F  | Metric screw thread |    |
|------------------------|----------|--------------------------------------|--|----|----|----|---------------------|----|
| Model FK               | Model EK |                                      |  |    |    |    | M                   | S  |
| FK4                    | EK4      | 6                                    | 4  | 3  | 23 | 5  | M4×0.5              | 7  |
| FK5                    | EK5      | 8                                    | 5  | 4  | 25 | 6  | M5×0.5              | 7  |
| FK6                    | EK6      | 10*1                                 | 6  | 4  | 30 | 8  | M6×0.75             | 8  |
| FK8                    | EK8      | 12                                   | 8  | 6  | 35 | 9  | M8×1                | 10 |
| FK10                   | EK10     | 14                                   | 10                                       | 8  | 36 | 15 | M10×1               | 11 |
| FK10                   | EK10     | 15                                   | 10                                       | 8  | 36 | 15 | M10×1               | 11 |
| FK12                   | EK12     | 16                                   | 12                                       | 10 | 36 | 15 | M12×1               | 11 |
| FK12                   | EK12     | 18                                   | 12                                       | 10 | 36 | 15 | M12×1               | 11 |
| FK15                   | EK15     | 20                                   | 15                                       | 12 | 49 | 20 | M15×1               | 13 |
| FK15                   | EK15     | 25                                   | 15                                       | 12 | 49 | 20 | M15×1               | 13 |
| FK20                   | EK20     | 28                                   | 20                                       | 17 | 64 | 25 | M20×1               | 17 |
| FK20                   | EK20     | 30                                   | 20                                       | 17 | 64 | 25 | M20×1               | 17 |
| FK20                   | EK20     | 32                                   | 20                                       | 17 | 64 | 25 | M20×1               | 17 |
| FK25                   | —        | 36                                   | 25                                       | 20 | 76 | 30 | M25×1.5             | 20 |
| FK30                   | —        | 40                                   | 30                                       | 25 | 72 | 38 | M30×1.5             | 25 |

Note) Support Units are designed to have dimensions so that combinations of models FK and FF, models EK and EF or models BK and BF are used on the same shaft.  
If desiring the shaft end to be machined at THK, add the shape symbol in the end of the Ball Screw model number.  
(Example) TS2505+500L-H2K

(Shape H2 on the fixed side; shape K on the supported side)

For the permissible radial runout of the shaft bearing end face, refer to JIS B 1192 (ISO 3408).

\*1 FK6 and EK6 also support  $\phi 8$  mm outer diameter ball screws. Contact THK for details.



Unit: mm


|  | Width across flat |    |    | Shape H2<br>Keyway |                |    | Shape H3<br>Cut flat on two side |    | Support Unit position |                |          |
|--|-------------------|----|----|--------------------|----------------|----|----------------------------------|----|-----------------------|----------------|----------|
|  |                   |    |    |                    |                |    |                                  |    | Model FK              |                | Model EK |
|  | J                 | N  | H  | G<br>N9            | T<br>+0.1<br>0 | P  | R                                | P  | K <sub>1</sub>        | K <sub>2</sub> |          |
|  | 4                 | 4  | 4  | —                  | —              | —  | 2.7                              | 4  | 1.5                   | 0.5            | 1.5      |
|  | 5                 | 4  | 4  | —                  | —              | —  | 3.7                              | 5  | 2                     | 0.5            | 2        |
|  | 5                 | 4  | 4  | —                  | —              | —  | 3.7                              | 6  | 3.5                   | 0.5            | 3.5      |
|  | 8                 | 5  | 5  | —                  | —              | —  | 5.6                              | 7  | 3.5                   | 0.5            | 3.5      |
|  | 10                | 5  | 7  | 2                  | 1.2            | 11 | 7.5                              | 11 | 0.5                   | -0.5           | -0.5     |
|  | 10                | 5  | 7  | 2                  | 1.2            | 11 | 7.5                              | 11 | 0.5                   | -0.5           | -0.5     |
|  | 13                | 6  | 8  | 3                  | 1.8            | 12 | 9.5                              | 12 | 0.5                   | -0.5           | -0.5     |
|  | 13                | 6  | 8  | 3                  | 1.8            | 12 | 9.5                              | 12 | 0.5                   | -0.5           | -0.5     |
|  | 16                | 6  | 9  | 4                  | 2.5            | 16 | 11.3                             | 16 | 4                     | 2              | 5        |
|  | 18                | 7  | 10 | 4                  | 2.5            | 16 | 11.3                             | 16 | 4                     | 2              | 5        |
|  | 21                | 8  | 11 | 5                  | 3              | 21 | 16                               | 21 | 1                     | -3             | 1        |
|  | 24                | 8  | 12 | 5                  | 3              | 21 | 16                               | 21 | 1                     | -3             | 1        |
|  | 27                | 9  | 13 | 5                  | 3              | 21 | 16                               | 21 | 1                     | -3             | 1        |
|  | 27                | 10 | 13 | 6                  | 3.5            | 25 | 19                               | 25 | 5                     | -2             | —        |
|  | 32                | 10 | 15 | 8                  | 4              | 32 | 23.5                             | 32 | -3                    | -9             | —        |

Note) The ball nut flange faces the fixed side unless otherwise specified.

If desiring the flange to face the supported side, add symbol G in the end of the Ball Screw model number when placing an order.

(Example) BIF2505-5RRGO+420LC5-H2KG

## Recommended Shapes of Shaft Ends - Shape J (J1, J2 and J3) (For Support Unit Model BK)



Model BK

| Support Unit model No.<br><br>Model BK | Ball screw shaft outer diameter<br><br>d | Shaft outer diameter of the bearing<br><br>A | B  | E  | F  | Metric screw thread |
|--|--|--|----|----|----|---------------------|
|  |  |  |    |    |    | M                   |
| BK10                                   | 14                                       | 10   | 8  | 39 | 15 | M10×1               |
| BK10                                   | 15                                       | 10   | 8  | 39 | 15 | M10×1               |
| BK12                                   | 16                                       | 12   | 10 | 39 | 15 | M12×1               |
| BK12                                   | 18                                       | 12   | 10 | 39 | 15 | M12×1               |
| BK15                                   | 20                                       | 15   | 12 | 40 | 20 | M15×1               |
| BK17                                   | 25                                       | 17   | 15 | 53 | 23 | M17×1               |
| BK20                                   | 28                                       | 20   | 17 | 53 | 25 | M20×1               |
| BK20                                   | 30                                       | 20   | 17 | 53 | 25 | M20×1               |
| BK20                                   | 32                                       | 20   | 17 | 53 | 25 | M20×1               |
| BK25                                   | 36                                       | 25   | 20 | 65 | 30 | M25×1.5             |
| BK30                                   | 40                                       | 30   | 25 | 72 | 38 | M30×1.5             |
| BK35                                   | 45                                       | 35   | 30 | 83 | 45 | M35×1.5             |
| BK40                                   | 50                                       | 40   | 35 | 98 | 50 | M40×1.5             |
| BK40                                   | 55                                       | 40   | 35 | 98 | 50 | M40×1.5             |


Note) Support Units are designed to have dimensions so that combinations of models FK and FF, models EK and EF or models BK and BF are used on the same shaft.

If desiring the shaft end to be machined at THK, add the shape symbol in the end of the Ball Screw model number.

(Example) TS2505+500L-J2K

(Shape J2 on the fixed side; shape K on the supported side)

For the permissible radial runout of the shaft bearing end face, refer to JIS B 1192 (ISO 3408).



Unit: mm


|  | Width across flat |    |    |    | Shape J2<br>Keyway |                |    | Shape J3<br>Cut flat on two side |    |
|--|-------------------|----|----|----|--------------------|----------------|----|----------------------------------|----|
|  | S                 | J  | N  | H  | G<br>N9            | T<br>+0.1<br>0 | P  | R                                | P  |
|  | 16                | 10 | 5  | 7  | 2                  | 1.2            | 11 | 7.5                              | 11 |
|  | 16                | 10 | 5  | 7  | 2                  | 1.2            | 11 | 7.5                              | 11 |
|  | 14                | 13 | 6  | 8  | 3                  | 1.8            | 12 | 9.5                              | 12 |
|  | 14                | 13 | 6  | 8  | 3                  | 1.8            | 12 | 9.5                              | 12 |
|  | 12                | 16 | 6  | 9  | 4                  | 2.5            | 16 | 11.3                             | 16 |
|  | 17                | 18 | 7  | 10 | 5                  | 3              | 21 | 14.3                             | 21 |
|  | 15                | 21 | 8  | 11 | 5                  | 3              | 21 | 16                               | 21 |
|  | 15                | 24 | 8  | 12 | 5                  | 3              | 21 | 16                               | 21 |
|  | 15                | 27 | 9  | 13 | 5                  | 3              | 21 | 16                               | 21 |
|  | 18                | 27 | 10 | 13 | 6                  | 3.5            | 25 | 19                               | 25 |
|  | 25                | 32 | 10 | 15 | 8                  | 4              | 32 | 23.5                             | 32 |
|  | 28                | 36 | 12 | 15 | 8                  | 4              | 40 | 28.5                             | 40 |
|  | 35                | 41 | 14 | 19 | 10                 | 5              | 45 | 33                               | 45 |
|  | 35                | 46 | 14 | 20 | 10                 | 5              | 45 | 33                               | 45 |

Note) The ball nut flange faces the fixed side unless otherwise specified.


If desiring the flange to face the supported side, add symbol G in the end of the Ball Screw model number when placing an order.

(Example) BIF2505-5RRGO+420LC5-J2KG


## Recommended Shapes of Shaft Ends - Shape K (For Support Unit Models FF, EF and BF)



Model FF



Model FF



Model EF

Model BF

| Support Unit model No. |          |          | Ball screw shaft<br>outer diameter | Shaft outer diameter<br>of the bearing |
|------------------------|----------|----------|------------------------------------|--|
| Model FF               | Model EF | Model BF |                                    |  |
| FF6                    | EF6      | —        | 8                                  | 6                                      |
| —                      | EF8      | —        | 12                                 | 6                                      |
| FF10                   | EF10     | BF10     | 14                                 | 8                                      |
| FF10                   | EF10     | BF10     | 15                                 | 8                                      |
| FF12                   | EF12     | BF12     | 16                                 | 10                                     |
| FF12                   | EF12     | BF12     | 18                                 | 10                                     |
| FF15                   | EF15     | BF15     | 20                                 | 15                                     |
| FF15                   | EF15     | BF15     | 25                                 | 15                                     |
| —                      | —        | BF17 *   |                                    | 17                                     |
| FF20                   | EF20     | BF20 **  | 28                                 | 20                                     |
| FF20                   | EF20     | BF20 **  | 30                                 | 20                                     |
| FF20                   | EF20     | BF20 **  | 32                                 | 20                                     |
| FF25                   | —        | BF25     | 36                                 | 25                                     |
| FF30                   | —        | BF30     | 40                                 | 30                                     |
| —                      | —        | BF35     | 45                                 | 35                                     |
| —                      | —        | BF40     | 50                                 | 40                                     |
| —                      | —        | BF40     | 55                                 | 40                                     |


Note) Support Units are designed to have dimensions so that combinations of models FK and FF, models EK and EF or models BK and BF are used on the same shaft.

If desiring the shaft end to be machined at THK, add the shape symbol in the end of the Ball Screw model number.

(Example) TS2505+500L-H2K

(Shape H2 on the fixed side; shape K on the supported side)

For the permissible radial runout of the shaft bearing end face, refer to JIS B 1192 (ISO 3408).



Unit: mm

|  | E       | Snap ring groove |               |      |
|--|---------|------------------|---------------|------|
|  |         | B                | F             | G    |
|  | 9       | 5.7              | 6.8           | 0.8  |
|  | 9       | 5.7              | 6.8           | 0.8  |
|  | 10      | 7.6              | 7.9           | 0.9  |
|  | 10      | 7.6              | 7.9           | 0.9  |
|  | 11      | 9.6              | 9.15          | 1.15 |
|  | 11      | 9.6              | 9.15          | 1.15 |
|  | 13      | 14.3             | 10.15         | 1.15 |
|  | 13      | 14.3             | 10.15         | 1.15 |
|  | 16      | 16.2             | 13.15         | 1.15 |
|  | 19 (16) | 19               | 15.35 (13.35) | 1.35 |
|  | 19 (16) | 19               | 15.35 (13.35) | 1.35 |
|  | 19 (16) | 19               | 15.35 (13.35) | 1.35 |
|  | 20      | 23.9             | 16.35         | 1.35 |
|  | 21      | 28.6             | 17.75         | 1.75 |
|  | 22      | 33               | 18.75         | 1.75 |
|  | 23      | 38               | 19.95         | 1.95 |
|  | 23      | 38               | 19.95         | 1.95 |

Note) \*When model BK17 (shaft end shape: J) is used on the fixed side for a Ball Screw with a shaft outer diameter of 25 mm, the shaft end shape on the supported side is that for model BF17.

\*\*The dimensions in the parentheses in the table above are that of model BF20. They differ from those of models FF20 and EF20. When placing an order, be sure to specify the model number of the Support Unit to be used.

# Nut Bracket

Model MC




Fig.1 Structure of the Nut Bracket


## Structure and Features

The model MC nut bracket is designed for use with BNK finished shaft end precision ball screw nuts. Its low height and the fact that it can be assembled using only bolts means devices can be compact and reduces how long they take to put together.

## Type

### Nut Bracket Model MC


Specification Table⇒ [A15-329](#)





## Nut Bracket

| Model No. | Supported Ball Screw models        |
|-----------|------------------------------------|
| MC 1004   | BNK1004, BNK1010                   |
| MC 1205   | BNK1205                            |
| MC 1408   | BNK1408, BNK1510, BNK1520, BNK1616 |
| MC 2010   | BNK2010                            |
| MC 2020   | BNK2020                            |



Unit: mm

| Model No. | Width<br>$W$ | $W_1$ | $B$ | $B_1$ | Overall length<br>$L$ | $C$ | $C_1$ | $F$  | $K$  |
|-----------|--------------|-------|-----|-------|-----------------------|-----|-------|------|------|
| MC 1004   | 48           | 24    | 40  | 4     | 32                    | 16  | 10    | 20   | 32.5 |
| MC 1205   | 60           | 30    | 47  | 6.5   | 36                    | 24  | 6     | 21   | 37   |
| MC 1408   | 60           | 30    | 50  | 5     | 36                    | 20  | 10    | 21.5 | 37   |
| MC 2010   | 86           | 43    | 70  | 8     | 50                    | 30  | 10    | 31   | 54   |
| MC 2020   | 86           | 43    | 70  | 8     | 40                    | 24  | 8     | 28   | 51   |

| Model No. | $T$ | $D$  | $PCD$ | $S \times \ell$ | $S_1 \times \ell_1$ | Mass<br>kg |
|-----------|-----|------|-------|-----------------|---------------------|------------|
| MC 1004   | 9   | 26.4 | 36    | M5 $\times$ 10  | M4 $\times$ 7       | 0.24       |
| MC 1205   | 9   | 30.4 | 40    | M6 $\times$ 12  | M4 $\times$ 7       | 0.38       |
| MC 1408   | 9   | 34.4 | 45    | M6 $\times$ 12  | M5 $\times$ 7       | 0.34       |
| MC 2010   | 16  | 46.4 | 59    | M10 $\times$ 20 | M6 $\times$ 10      | 1.04       |
| MC 2020   | 16  | 39.4 | 59    | M10 $\times$ 20 | M6 $\times$ 10      | 0.83       |

# Lock Nut

## Model RN




Fig.1 Structure of the Lock Nut

## Structure and Features

The model RN ball screw lock nut is used for fixing the angular bearings that set into ball screws. Available in sizes M4 to M40. Screw pitches must be narrow.


## Type

## Lock Nut Model RN

Specification Table⇒ [A15-331](#)



## Lock Nut



Unit: mm

| Model No. | M       | m    | D    | d  | L   | t   | T  | Mass<br>kg |
|-----------|---------|------|------|----|-----|-----|----|------------|
| RN 4      | M4×0.5  | M2.6 | 11.5 | 8  | 5   | 2.7 | 10 | 0.003      |
| RN 5      | M5×0.5  | M2.6 | 13.5 | 9  | 5   | 2.7 | 11 | 0.004      |
| RN 6      | M6×0.75 | M3   | 14.5 | 10 | 5   | 2.7 | 12 | 0.005      |
| RN 8      | M8×1    | M3   | 17   | 13 | 6.5 | 4   | 14 | 0.008      |
| RN 10     | M10×1   | M3   | 20   | 15 | 8   | 5.5 | 16 | 0.013      |
| RN 12     | M12×1   | M3   | 22   | 17 | 8   | 5.5 | 19 | 0.014      |
| RN 15     | M15×1   | M3   | 25   | 21 | 8   | 4.5 | 22 | 0.017      |
| RN 17     | M17×1   | M4   | 30   | 25 | 13  | 9   | 24 | 0.042      |
| RN 20     | M20×1   | M4   | 35   | 26 | 11  | 7   | 30 | 0.048      |
| RN 25     | M25×1.5 | M5   | 43   | 33 | 15  | 10  | 35 | 0.096      |
| RN 30     | M30×1.5 | M6   | 48   | 39 | 20  | 14  | 40 | 0.145      |
| RN 35     | M35×1.5 | M8   | 60   | 46 | 21  | 14  | 50 | 0.261      |
| RN 40     | M40×1.5 | M8   | 63   | 51 | 25  | 18  | 50 | 0.304      |







# Ball Screw Options

## Contaminaton Protection



If foreign material enters the interior of the ball screw, abnormal levels of abrasion and ball clogging are more likely to occur. This can also shorten the overall lifespan of the product.

As such, foreign material needs to be prevented from entering. If there is a chance that foreign material may get in, it is important to choose an effective contamination protection product that suits the usage conditions.

|   |  |
|---|--|
| <p>Labyrinth seal<br/>(Precision Ball Screw)<br/>(Rolled Ball Screw Model JPF)<br/>Symbol: RR</p> |  <p style="text-align: right;"><b>A15-336</b></p>   |
| <p>Brush seal<br/>(Rolled Ball Screw)<br/>Symbol: ZZ</p>  |  <p style="text-align: right;"><b>A15-336</b></p>   |
| <p>Wiper ring<br/>Symbol: WW</p>  |  <p style="text-align: right;"><b>A15-337~</b></p> |
| <p>Thin film seal<br/>(SDA-V, SDA-VZ, SDAN-V only)<br/>Symbol: TT</p>                             |   |

## Options

## Lubrication

|   |   |
|---|---|
| <p>Canvas seal<br/>(SDA-V, SDAN-V, HBN-V only)<br/>Symbol: CC</p> |  <p style="text-align: right;"><b>▲15-339~</b></p> |
| <p>Dust cover<br/>Bellows<br/>Screw cover</p>                     |  <p style="text-align: right;"><b>▲15-341</b></p>  |


Ball Screw (Options)

## Lubrication

To maximize the performance of the Ball Screw, it is necessary to select a lubricant and a lubrication method according to the conditions.

For types of lubricants, characteristics of lubricants and lubrication methods, see the section on “Accessories for Lubrication” on **▲24-2**.

Also, QZ Lubricator is available as an optional accessory that significantly increases the maintenance interval.



## Corrosion Resistance (Surface Treatment, etc.)

Depending on the service environment, the Ball Screw requires corrosion resistance treatment or a different material. For details of corrosion resistance treatment and material change, contact THK. (see **■0-18**)

## Contamination Protection Seal for Ball Screws


If the Ball Screw is used in an atmosphere free from foreign material but with suspended dust, a labyrinth seal (with symbol RR) and a brush seal (with symbol ZZ) can be used as contamination protection accessories.

The labyrinth seal is designed to maintain a slight clearance between the seal and the screw shaft raceway so that torque does not develop and no heat is generated, though its effect in contamination protection is limited.

With Ball Screws except the large lead and super lead types, there is no difference in nut dimensions between those with and without a seal.

### Labyrinth seal


Symbol: RR (Precision Ball Screw)  
(Rolled Ball Screw Model JPF)



Labyrinth seal

### Brush seal

Symbol: ZZ (Rolled Ball Screw)




Brush seal



# Wiper Ring W

● For the supported models and the ball screw nut dimension with Wiper ring W attached, see [A15-344](#) to [A15-352](#).

With the wiper ring W, special resin with high wear resistance and low dust generation removes foreign material and prevents foreign material from entering the ball screw nut while elastically contacting the circumference of the ball screw shaft and the screw thread.




## [Features]

- A total of eight slits on the circumference remove foreign materials in succession, and prevent entrance of foreign material.
- Contacts the ball screw shaft to reduce the flowing out of grease.
- Contacts the ball screw shaft at a constant pressure level using a spring, thus to minimize the heat generation.
- Since the material is highly resistant to the wear and the chemicals, its performance will not easily be deteriorated even if it is used over a long period.

Can be attached together with QZ Lubricator.

For the applicable models and the ball screw nut dimensions after wiper ring W is attached, see [A15-344](#).



QZ Lubricator + Wiper ring

## Model number coding

**BIF2505V-5 QZ WW G0 +1000L C5**

With QZ  
Lubricator

With wiper ring W


(\*) See [A15-344](#).

## ● Test in an environment exposed to contaminated environment

[Test conditions]



| Item                                 | Description   |
|--------------------------------------|---|
| Model No.                            | BIF3210V-5G0+1500LC5  |
| Maximum rotational speed             | 1000 min <sup>-1</sup>  |
| Maximum speed                        | 10 m/min  |
| Maximum circumferential speed        | 1.8 m/s   |
| Time constant                        | 60 ms   |
| Dowel                                | 1 s   |
| Stroke                               | 900 mm  |
| Load (through internal load)         | 1.31 kN   |
| Grease                               | THK AFG Grease 8 cm <sup>3</sup><br>(Initial lubrication to the ball screw nut only.) |
| Foundry dust                         | FCD400 average particle diameter: 250 μm  |
| Volume of foreign material per shaft | 5 g/h   |

[Test result]



- Type with wiper ring  
Slight flaking occurred in the ball screw shaft at travel distant of 1,000 km.
- Type with labyrinth seal  
Flaking occurred throughout the circumference of the screw shaft raceway at travel distance of 200 km.  
Flaking occurred on the balls after traveling 1,500 km.

Change in the ball after traveling 2000 km




- Type with wiper ring  
Wear of balls at a travel distance of 2,000 km: 1.4 μm.
- Type with labyrinth seal  
Starts to be worn rapidly after 500 km, and the ball wear amount at the travel distance of 2,000 km: 11 μm.

### ● Heat Generation Test

[Test conditions]

| Item                          | Description   |
|-------------------------------|---|
| Model No.                     | BLK3232-3.6G0+1426LC5   |
| Maximum rotational speed      | 1000 min <sup>-1</sup>  |
| Maximum speed                 | 32 m/min  |
| Maximum circumferential speed | 1.7 m/s   |
| Time constant                 | 100 ms  |
| Stroke                        | 1000 mm   |
| Load (through internal load)  | 0.98 kN   |
| Grease                        | THK AFG Grease 5 cm <sup>3</sup><br>(contained in the ball screw nut) |

[Test result]





| Item                        | With wiper ring | Without seal |
|-----------------------------|-----------------|--------------|
| Heat generation temperature | 37.1            | 34.5         |
| Temperature rise            | 12.2            | 8.9          |

## Canvas seal CC

● See [A15-353](#) for compatible models and ball screw nut dimensions after canvas seal installation.

Canvas seals are made from resin with high slidability and superior wear resistance. They prevent foreign material from entering the nut through elastic contact with the outer diameter of the ball screw shaft and the groove.



### [Features]

- The seal is in contact with the ball screw shaft, so it prevents the intrusion of foreign material and reduces the discharge of grease.
- The rubber base and high slidability resin used on the part that slides along the shaft minimizes heat generation despite the seal coming in contact with the shaft.

### Model number coding

SDA2505V-3 CC G0 +1000L C5


With canvas seal

## ● Foreign material test

[Test conditions]

| Item                         | Description   |
|------------------------------|---|
| Test pieces                  | Precision Ball Screw $\phi$ 40                                      |
| Maximum rotational speed     | 100 min <sup>-1</sup>   |
| Maximum speed                | 3 m/min   |
| Stroke                       | 800 mm  |
| Load (through internal load) | 2.25 kN   |
| Grease                       | THK AFJ Grease 12 cm <sup>3</sup> (contained in the ball screw nut) |
| Applied test material        | Steel powder and grease mixture<br>Powder-to-grease ratio = 1:2     |
| Test material amount         | 0.1 g   |
| Run time                     | 1 h   |

[Test result]




## ● Heat generation test

[Test conditions]

| Item                         | Description   |
|------------------------------|---|
| Test pieces                  | Precision Ball Screw $\phi$ 40                                      |
| Maximum rotational speed     | 2500 min <sup>-1</sup>  |
| Maximum speed                | 75 m/min  |
| Stroke                       | 800 mm  |
| Load (through internal load) | 2.25 kN   |
| Grease                       | THK AFJ Grease 12 cm <sup>3</sup> (contained in the ball screw nut) |

[Test result]




| Item                        | With canvas seal | Without seal |
|-----------------------------|------------------|--------------|
| Heat generation temperature | 45.8             | 43.6         |
| Temperature rise            | 25.7             | 24.1         |

## ● Grease sealing test

[Test conditions]

| Item                         | Description   |
|------------------------------|---|
| Test pieces                  | Precision Ball Screw $\phi$ 40                                      |
| Maximum rotational speed     | 100 min <sup>-1</sup>   |
| Maximum speed                | 3 m/min   |
| Stroke                       | 800 mm  |
| Load (through internal load) | 2.25 kN   |
| Grease                       | THK AFJ Grease 12 cm <sup>3</sup> (contained in the ball screw nut) |
| Run time                     | 1 h   |


[Test result]



# Dust Cover for Ball Screws

## Bellows/Screw cover

In the case of an environment with much dust and foreign material, be sure to prevent intrusion of foreign material by using bellows, a screw cover or the like. The contamination protection can be increased by also using a contamination protection seal. For details, contact THK. When conferring with us, please use the bellows specifications (▲15-356).




# QZ Lubricator


● For the supported models and the ball screw nut dimension with QZ attached, see [A15-344](#) to [A15-352](#).

QZ Lubricator feeds a right amount of lubricant to the raceway of the ball screw shaft. This allows an oil film to be constantly formed between the balls and the raceway, improves lubricity and significantly extends the lubrication maintenance interval.

The structure of QZ Lubricator consists of three major components: (1) a heavily oil-impregnated fiber net (stores the lubricant), (2) a high-density fiber net (applies the lubricant to the raceway) and (3) an oil-control plate (adjusts the oil flow). The lubricant contained in the QZ Lubricator is fed by the capillary phenomenon, which is used also in felt pens and many other products.



Appearance Drawing



Structural Drawing

## [Features]

- Since it supplements an oil loss, the lubrication maintenance interval can be significantly extended.
- Since the right amount of lubricant is applied to the ball raceway, an environmentally friendly lubrication system that does not contaminate the surroundings is achieved.

Note) Some types of QZ have a vent hole. Be careful not to block the hole with grease or other obstructions.

## Model number coding

**BIF2505V-5 QZ WW G0 +1000L C5**


With QZ  
Lubricator

With wiper ring W

(\* See [A15-344](#).)

### ● Significantly extended maintenance interval

Since QZ Lubricator continuously feeds a lubricant over a long period, the maintenance interval can be significantly extended.




[Test conditions]

| Item                     | Description            |
|--------------------------|------------------------|
| Ball Screw               | BIF2510V               |
| Maximum rotational speed | 2500 min <sup>-1</sup> |
| Maximum speed            | 25 m/min               |
| Stroke                   | 500 mm                 |
| Load                     | Internal preload only  |

### ● Environmentally friendly lubrication system

Since QZ Lubricator feeds the right amount of lubricant directly to the raceway, the lubricant can effectively be used without waste.



**QZ Lubricator + THK AFA Grease**

**32 cm<sup>3</sup>**

(QZ Lubricator attached to both ends of the ball screw nut)




**Forced lubrication**

**0.25 cm<sup>3</sup>/3 min × 24 h × 125 d  
= 15000 cm<sup>3</sup>**

Reduced to approx.  $\frac{1}{470}$

# Dimensions of Each Model with an Option Attached

## Dimensions of the Ball Screw Nut Attached with Wiper Ring W and QZ Lubricator



Note) For models BLW, BLK (precision and rolled), WGF, BNK1510 or higher (excluding BNK2010), WTF, and CNF, a wiper ring is attached to the outside of the nut.

Unit: mm

| Model No. | WW availability | QZ availability | Dimensions including WW |     | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |
|-----------|-----------------|-----------------|-------------------------|-----|---------------------------------------|---|--------------------------------|
|           |                 |                 | L                       | QWL |                                       |   |                                |
| EBB       | 1605V-4         | ○               | ○                       | 55  | 25                                    | 27  | 111                            |
|           | 2004V-8         | ○               | ×                       | 69  | —                                     | —   | —                              |
|           | 2005V-3         | ○               | ○                       | 50  | 26.5                                  | 33  | 109                            |
|           | 2006V-6         | ○               | ○                       | 74  | 30                                    | 34  | 139                            |
|           | 2008V-6         | ○               | ○                       | 88  | 25                                    | 34  | 143                            |
|           | 2010V-6         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 2504V-8         | ○               | ○                       | 70  | 34                                    | 37  | 134                            |
|           | 2505V-3         | ○               | ○                       | 50  | 27.6                                  | 39  | 102.2                          |
|           | 2506V-6         | ○               | ○                       | 74  | 28.3                                  | 39  | 127.6                          |
|           | 2508V-6         | ○               | ○                       | 90  | 29.6                                  | 39  | 143.2                          |
|           | 2510V-3         | ○               | ○                       | 73  | 31.6                                  | 39  | 131.2                          |
|           | 2510V-4         | ○               | ○                       | 85  | 31.6                                  | 39  | 143.2                          |
|           | 2512V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 2806V-6         | ×               | ○                       | —   | 31                                    | 42  | 135                            |
|           | 3204V-10        | ○               | ×                       | 82  | —                                     | —   | —                              |
|           | 3205V-3         | ○               | ○                       | 52  | 35                                    | 45  | 118                            |
|           | 3205V-4         | ○               | ○                       | 57  | 35                                    | 45  | 123                            |
|           | 3205V-6         | ○               | ○                       | 67  | 35                                    | 45  | 133                            |
|           | 3206V-8         | ○               | ○                       | 96  | 35                                    | 47  | 160                            |
|           | 3208V-8         | ○               | ×                       | 119 | —                                     | —   | —                              |
|           | 3210V-3         | ○               | ○                       | 82  | 40                                    | 49  | 154                            |
|           | 3210V-4         | ○               | ○                       | 94  | 40                                    | 49  | 166                            |
|           | 3604V-6         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 3606V-8         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 3608V-8         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 4004V-6         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 4005V-6         | ○               | ○                       | 65  | 28.5                                  | 61  | 122                            |
|           | 4006V-12        | ○               | ×                       | 124 | —                                     | —   | —                              |
|           | 4008V-8         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 4010V-3         | ○               | ○                       | 83  | 44                                    | 61  | 166                            |
|           | 4010V-4         | ○               | ○                       | 94  | 44                                    | 61  | 177                            |
|           | 4012V-8         | ○               | ○                       | 163 | 44                                    | 61  | 251                            |
|           | 4020V-3         | ○               | ○                       | 129 | 47                                    | 61  | 213                            |
| 5005V-12  | ○               | ×               | 111                     | —   | —                                     | —   |                                |
| 5008V-8   | ○               | ×               | 123                     | —   | —                                     | —   |                                |
| 5010V-4   | ○               | ○               | 96                      | 37  | 71                                    | 163   |                                |
| 5020V-3   | ○               | ○               | 129                     | 40  | 71                                    | 197   |                                |
| 6310V-4   | ○               | ○               | 92                      | 39  | 84                                    | 169   |                                |
| 6312V-4   | ○               | ○               | 109                     | 32  | 89                                    | 170   |                                |
| 6316V-4   | ×               | ×               | —                       | —   | —                                     | —   |                                |

Unit: mm

| Model No. | WW availability | QZ availability | Dimensions including WW |     | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |
|-----------|-----------------|-----------------|-------------------------|-----|---------------------------------------|---|--------------------------------|
|           |                 |                 | L                       | QWL |                                       |   |                                |
| EBB       | 6320V-3         | ○               | ○                       | 133 | 30.5                                  | 94  | 184                            |
|           | 8010V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 8012V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 8016V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 8020V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 1605V-6         | ○               | ○                       | 65  | 25                                    | 27  | 121                            |
|           | 2004V-8         | ○               | ×                       | 69  | —                                     | —   | —                              |
|           | 2005V-6         | ○               | ○                       | 65  | 26.5                                  | 33  | 124                            |
|           | 2006V-6         | ○               | ○                       | 74  | 30                                    | 34  | 139                            |
|           | 2008V-6         | ○               | ○                       | 88  | 25                                    | 34  | 143                            |
| EPB       | 2010V-6         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 2504V-8         | ○               | ○                       | 70  | 34                                    | 37  | 134                            |
|           | 2505V-6         | ○               | ○                       | 66  | 27.6                                  | 39  | 118.2                          |
|           | 2506V-6         | ○               | ○                       | 74  | 28.3                                  | 39  | 127.6                          |
|           | 2508V-6         | ○               | ○                       | 90  | 29.6                                  | 39  | 143.2                          |
|           | 2510V-4         | ○               | ○                       | 85  | 31.6                                  | 39  | 143.2                          |
|           | 2512V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 2806V-6         | ×               | ○                       | —   | 31                                    | 42  | 135                            |
|           | 3204V-10        | ○               | ×                       | 82  | —                                     | —   | —                              |
|           | 3205V-6         | ○               | ○                       | 67  | 35                                    | 45  | 133                            |
|           | 3205V-8         | ○               | ○                       | 78  | 35                                    | 45  | 144                            |
|           | 3206V-8         | ○               | ○                       | 96  | 35                                    | 47  | 160                            |
|           | 3208V-8         | ○               | ×                       | 119 | —                                     | —   | —                              |
|           | 3210V-6         | ○               | ○                       | 112 | 40                                    | 49  | 185                            |
|           | 3604V-6         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 3606V-8         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 3608V-8         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 4004V-6         | ×               | ×                       | —   | —                                     | —   | —                              |
|           | 4005V-6         | ○               | ○                       | 65  | 28.5                                  | 61  | 122                            |
|           | 4006V-12        | ○               | ×                       | 124 | —                                     | —   | —                              |
| 4008V-8   | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 4010V-6   | ○               | ○               | 114                     | 44  | 61                                    | 197   |                                |
| 4010V-8   | ○               | ○               | 138                     | 44  | 61                                    | 221   |                                |
| 4012V-8   | ○               | ○               | 163                     | 44  | 61                                    | 251   |                                |
| 5005V-12  | ○               | ×               | 111                     | —   | —                                     | —   |                                |
| 5008V-8   | ○               | ×               | 123                     | —   | —                                     | —   |                                |
| 5010V-8   | ○               | ○               | 140                     | 37  | 71                                    | 207   |                                |
| 6310V-4   | ○               | ○               | 92                      | 39  | 84                                    | 169   |                                |

○ : Available △ : Available per request × : Not available  
 \*Please contact THK for more information regarding the model numbers that do not support WW and QZ.  
 Parentheses indicate the dimensions with QZ but without WW.



## Options

## Dimensions of Each Model with an Option Attached

Unit: mm

| Model No.            | WW availability       | QZ availability | Dimensions including WW | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached |     | Dimensions including QZ and WW |
|----------------------|-----------------------|-----------------|-------------------------|---------------------------------------|---|-----|--------------------------------|
|                      |                       |                 |                         |                                       | L   | QWL |                                |
| SBN<br>(Small, cage) | 1604V-5               | ○               | ○                       | 53                                    | 29  | 31  | 111                            |
|                      | 1605V-5               | ○               | ○                       | 56                                    | 29  | 31  | 114                            |
|                      | 2004V-5               | ○               | ○                       | 49                                    | 27.5  | 39  | 104                            |
|                      | 2005V-5               | ○               | ○                       | 56                                    | 27.5  | 43  | 111                            |
|                      | 2010V-5               | △               | △                       | —                                     | —   | —   | —                              |
|                      | 2504V-5               | ○               | ○                       | 48                                    | 32.5  | 45  | 113                            |
|                      | 2505V-5               | ○               | ○                       | 55                                    | 32.5  | 45  | 120                            |
|                      | 2506V-5               | ○               | ○                       | 62                                    | 33  | 45  | 128                            |
|                      | 2805V-5               | ○               | ○                       | 59                                    | 22  | 54  | 103                            |
|                      | 3205V-5               | ○               | ○                       | 56                                    | 32  | 57  | 120                            |
|                      | 3206V-5               | ○               | ○                       | 63                                    | 32  | 57  | 127                            |
|                      | SBN<br>(Medium, cage) | 2508V-7         | ○                       | ○                                     | 98  | 34  | 45                             |
| 2510V-5              |                       | ○               | ○                       | 100                                   | 37  | 45  | 174                            |
| 2810V-3              |                       | ○               | △                       | 88                                    | —   | —   | 154                            |
| 3210V-7              |                       | ○               | ○                       | 120                                   | 31  | 73  | 182                            |
| 3212V-5              |                       | ○               | ○                       | 117                                   | 33  | 73  | 183                            |
| 3216V-5              |                       | △               | △                       | —                                     | —   | —   | —                              |
| 3610V-7              |                       | ○               | ○                       | 123                                   | 33  | 64  | 189                            |
| 3612V-7              |                       | ○               | ○                       | 140                                   | 35  | 64  | 210                            |
| 3616V-5              |                       | ○               | ○                       | 140                                   | 32  | 64  | 204                            |
| 3620V-3              |                       | ○               | ○                       | 122                                   | 32  | 64  | 186                            |
| 4010V-5              |                       | ○               | ○                       | 103                                   | 37  | 66  | 177                            |
| 4012V-5              |                       | ○               | ○                       | 119                                   | 38  | 66  | 195                            |
| 4016V-5              |                       | ○               | ○                       | 144                                   | 42  | 66  | 228                            |
| 4020V-5              |                       | △               | △                       | —                                     | —   | —   | —                              |
| 4510V-5              |                       | ○               | △                       | 111                                   | —   | —   | —                              |
| 4512V-5              |                       | ○               | ○                       | 119                                   | 35.5  | 79  | 190                            |
| 4516V-5              |                       | ○               | ○                       | 140                                   | 35.5  | 79  | 211                            |
| 4520V-5              |                       | △               | △                       | —                                     | —   | —   | —                              |
| 5010V-5              |                       | ○               | ○                       | 103                                   | 37.5  | 79  | 178                            |
| 5012V-5              |                       | ○               | ○                       | 123                                   | 38.5  | 79  | 200                            |
| 5016V-5              | ○                     | ○               | 164                     | 38.5                                  | 79  | 241 |                                |
| 5020V-5              | ○                     | ○               | 201                     | 40.5                                  | 79  | 282 |                                |
| SBK<br>(Cage)        | 1520-3.6              | △               | ○                       | —                                     | 22  | 31  | 98                             |
|                      | 1616-3.6              | △               | ×                       | —                                     | —   | —   | —                              |
|                      | 2010-5.6              | △               | ○                       | —                                     | 27  | 36  | 99                             |
|                      | 2020-3.6              | ○               | ○                       | 54                                    | 27  | 36  | 108                            |
|                      | 2030-3.6              | △               | ○                       | —                                     | 27  | 36  | 125                            |
|                      | 2520-3.6              | ○               | ○                       | 57                                    | 35.5  | 44  | 128                            |
|                      | 2525-3.6              | ○               | ○                       | 68                                    | 35.5  | 44  | 139                            |
|                      | 3220-5.6              | ○               | ○                       | 82                                    | 34.5  | 53  | 151                            |
|                      | 3232-5.6              | △               | ○                       | —                                     | 34.5  | 53  | 187                            |
|                      | 3620-7.6              | ○               | ○                       | 110                                   | 28  | 69  | 166                            |
|                      | 3636-5.6              | ○               | ○                       | 134                                   | 28  | 69  | 190                            |
|                      | 4020-7.6              | ○               | ○                       | 110                                   | 30.5  | 79  | 171                            |
|                      | 4030-7.6              | ○               | ○                       | 148                                   | 30.4  | 79  | 208.8                          |
|                      | 4040-5.6              | ○               | ○                       | 146                                   | 30.4  | 79  | 206.8                          |
|                      | 5020-7.6              | ○               | ○                       | 110                                   | 35  | 89  | 180                            |
|                      | 5030-7.6              | ○               | ○                       | 149                                   | 35  | 89  | 219                            |
|                      | 5036-7.6              | ○               | ○                       | 172                                   | 35  | 89  | 242                            |
|                      | 5050-5.6              | ○               | ○                       | 175                                   | 35  | 89  | 245                            |
|                      | 5520-7.6              | ○               | ○                       | 110                                   | 32  | 95  | 174                            |
|                      | 5530-7.6              | ○               | ○                       | 149                                   | 32  | 95  | 213                            |
| 5536-7.6             | ○                     | ○               | 172                     | 32                                    | 95  | 236 |                                |
| SDAN<br>(Cage)       | 3110V-5               | ×               | ×                       | —                                     | —   | —   | —                              |
|                      | 3112V-5               | ×               | ×                       | —                                     | —   | —   | —                              |

Unit: mm

| Model No.      | WW availability | QZ availability | Dimensions including WW | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached |     | Dimensions including QZ and WW |
|----------------|-----------------|-----------------|-------------------------|---------------------------------------|---|-----|--------------------------------|
|                |                 |                 |                         |                                       | L   | QWL |                                |
| SDAN<br>(Cage) | 3116V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3120V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3205V-4         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3206V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3208V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3210V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3210VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3212VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3216VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3220VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3606V-4         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3610V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3612V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3616V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3620V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3810V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3812V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3816V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 3820V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4008VX-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4010VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4012VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4016VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4020VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4510V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4510VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4512V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4512VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4516V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4516VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4520V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 4520VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 5010V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 5010VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 5012V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 5012VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 5016V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 5016VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 5020V-5         | ×               | ×                       | —                                     | —   | —   | —                              |
|                | 5020VA-5        | ×               | ×                       | —                                     | —   | —   | —                              |
| 5025V-4        | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5025VA-4       | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5030V-4        | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5030VA-4       | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5040V-3        | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5040VA-3       | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5510VX-4       | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5510VAX-4      | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5512VX-4       | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5512VAX-4      | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5516VX-4       | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5516VAX-4      | ×               | ×               | —                       | —                                     | —   | —   |                                |
| 5520VX-4       | ×               | ×               | —                       | —                                     | —   | —   |                                |

○ : Available △ : Available per request × : Not available  
 \*Please contact THK for more information regarding the model numbers that do not support WW and QZ.  
 Parentheses indicate the dimensions with QZ but without WW.

Unit: mm

| Model No.      | WW availability | QZ availability | Dimensions including WW |     | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |
|----------------|-----------------|-----------------|-------------------------|-----|---------------------------------------|---|--------------------------------|
|                |                 |                 | L                       | QWL |                                       |   |                                |
| SDAN<br>(Cage) | 5520VAX-4       | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 6310VX-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 6312VX-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 6316VX-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 6320VX-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 6325VX-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 6330VX-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 6340VX-3        | ×               | ×                       | —   | —                                     | —   | —                              |
| SDA<br>(Cage)  | 1004VZ-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1005VZ-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1010VZ-3        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1205VZ-3        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1210VZ-2        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1220VZ-2        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1230VZ-2        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1405V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1505V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1510V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1520V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1530V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1605V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1610V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 1616V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2004V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2005V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2006V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2010V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2010V-6         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2020V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2020V-6         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2030V-2         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2040V-2         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2505V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2510V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2520V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2525V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2530V-2         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2530V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2550V-2         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 2806V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3110V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3112V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3116V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3120V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3132V-2         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3205V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3206V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3208V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3210V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3210VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3212VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3216VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3220VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|                | 3232VA-2        | ×               | ×                       | —   | —                                     | —   | —                              |
| 3610V-5        | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 3612V-5        | ×               | ×               | —                       | —   | —                                     | —   |                                |

Unit: mm

| Model No.     | WW availability | QZ availability | Dimensions including WW |     | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |
|---------------|-----------------|-----------------|-------------------------|-----|---------------------------------------|---|--------------------------------|
|               |                 |                 | L                       | QWL |                                       |   |                                |
| SDA<br>(Cage) | 3616V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 3620V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 3636V-2         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 3810V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 3812V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 3815V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 3816V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 3820V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 3825V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 3830V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 3840V-2         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4008VZ-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4010VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4012VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4015VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4016VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4020VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4020VA-10       | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4025VA-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4030VA-3        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4030VA-6        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4040VA-2        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4040VA-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4510V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4510VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4512V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4512VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4516V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4516VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4520V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4520VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4520VA-10       | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4525V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4525VA-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4530V-4         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4530VA-4        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4540V-3         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 4540VA-3        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 5010V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 5010VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 5012V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 5012VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 5016V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 5016VA-5        | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 5020V-5         | ×               | ×                       | —   | —                                     | —   | —                              |
|               | 5020V-10        | ×               | ×                       | —   | —                                     | —   | —                              |
| 5020VA-5      | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 5020VA-10     | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 5025V-4       | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 5025VA-4      | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 5025VA-8      | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 5030V-4       | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 5030VA-4      | ×               | ×               | —                       | —   | —                                     | —   |                                |

○ : Available △ : Available per request × : Not available  
 \*Please contact THK for more information regarding the model numbers that do not support WW and QZ.  
 Parentheses indicate the dimensions with QZ but without WW.

## Options

## Dimensions of Each Model with an Option Attached

Unit: mm

| Model No.   | WW availability | QZ availability | Dimensions including WW |     | Length of protrusion with QZ attached |    | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |   |
|-------------|-----------------|-----------------|-------------------------|-----|---------------------------------------|----|---|--------------------------------|---|
|             |                 |                 | L                       | QWL | QWD                                   | AL |   |                                |   |
| SDA (Cage)  | 5030VA-8        | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 5040V-3         | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 5040VA-3        | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 5040VA-6        | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 5050V-2         | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
| 5050VA-2    | ×               | ×               | —                       | —   | —                                     | —  | —   | —                              |   |
| HBN (Cage)  | 5010V-7.5       | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 5012V-7.5       | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 5016V-7.5       | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 6316V-7.5       | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 6316V-10.5      | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 6320V-7.5       | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 6325V-10.5      | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 8016V-7.5       | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 8016V-10.5      | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 8020V-7.5       | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 8020V-10.5      | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 8025V-7.5       | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 8025V-10.5      | ×               | ×                       | —   | —                                     | —  | —   | —                              | — |
|             | 6335K-10        | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 6335K-15        | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 6342K-3         | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 6350K-10        | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 8040K-5         | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 8040KA-5        | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 8050K-15        | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 8050KA-15       | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10016K-10       | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10016KA-10      | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10020K-7.5      | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10020KA-7.5     | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10020K-10       | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10020KA-10      | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10020K-12.5     | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10020KA-12.5    | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10020K-7        | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10020KA-7       | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10020K-10.5     | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10020KA-10.5    | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025K-7.5      | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025KA-7.5     | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025K-10       | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025KA-10      | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025K-12.5     | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025KA-12.5    | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025K-7        | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025KA-7       | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025K-10.5     | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025KA-10.5    | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025K-14       | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
|             | 10025KA-14      | ×               | △                       | —   | —                                     | —  | —   | —                              | — |
| 12020K-10   | ×               | △               | —                       | —   | —                                     | —  | —   | —                              |   |
| 12020KA-10  | ×               | △               | —                       | —   | —                                     | —  | —   | —                              |   |
| 12025K-7.5  | ×               | △               | —                       | —   | —                                     | —  | —   | —                              |   |
| 12025KA-7.5 | ×               | △               | —                       | —   | —                                     | —  | —   | —                              |   |
| 12025K-10   | ×               | △               | —                       | —   | —                                     | —  | —   | —                              |   |

Unit: mm

| Model No.    | WW availability | QZ availability | Dimensions including WW |      | Length of protrusion with QZ attached |     | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |   |
|--------------|-----------------|-----------------|-------------------------|------|---------------------------------------|-----|---|--------------------------------|---|
|              |                 |                 | L                       | QWL  | QWD                                   | AL  |   |                                |   |
| HBN (Cage)   | 12025KA-10      | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 12025K-12.5     | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 12025KA-12.5    | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 12025K-14       | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 12025KA-14      | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 14025K-10       | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 14025KA-10      | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 14032K-10.5     | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 14032KA-10.5    | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 14040K-7.5      | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 14040KA-7.5     | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 3210-5          | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 3610-5          | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 3612-5          | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 4010-7.5        | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 4012-7.5        | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 5010-7.5        | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 5012-7.5        | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 5016-7.5        | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 6316-7.5        | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
| 6316-10.5    | ×               | △               | —                       | —    | —                                     | —   | —   | —                              |   |
| 6320-7.5     | ×               | △               | —                       | —    | —                                     | —   | —   | —                              |   |
| SBKH (Cage)  | 6332-3.8        | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 6340-7.6        | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 8050-7.6        | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 8060-7.6        | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 10050-7.6       | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 10060-7.6       | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 12060-7.6       | ×               | △                       | —    | —                                     | —   | —   | —                              | — |
|              | 1604V-5         | ○               | ○                       | 53   | 29                                    | 31  | 111   | —                              | — |
|              | 1605V-5         | ○               | ○                       | 56   | 29                                    | 31  | 114   | —                              | — |
|              | 2004V-5         | ○               | ○                       | 49   | 27.5                                  | 39  | 104   | —                              | — |
| 2004V-10     | ○               | ○               | 73                      | 27.5 | 39                                    | 128 | —   | —                              |   |
| 2005V-5      | ○               | ○               | 56                      | 27.5 | 43                                    | 111 | —   | —                              |   |
| 2005V-10     | ○               | ○               | 86                      | 27.5 | 43                                    | 141 | —   | —                              |   |
| 2010V-5      | △               | △               | —                       | —    | —                                     | —   | —   | —                              |   |
| 2504V-5      | ○               | ○               | 48                      | 32.5 | 45                                    | 113 | —   | —                              |   |
| 2504V-10     | ○               | ○               | 72                      | 32.5 | 45                                    | 137 | —   | —                              |   |
| 2505V-5      | ○               | ○               | 55                      | 32.5 | 45                                    | 120 | —   | —                              |   |
| 2505V-10     | ○               | ○               | 85                      | 32.5 | 45                                    | 150 | —   | —                              |   |
| 2506V-5      | ○               | ○               | 62                      | 33   | 45                                    | 128 | —   | —                              |   |
| 2506V-10     | ○               | ○               | 98                      | 33   | 45                                    | 164 | —   | —                              |   |
| 2805V-5      | ○               | ○               | 59                      | 22   | 54                                    | 103 | —   | —                              |   |
| 2805V-10     | ○               | ○               | 89                      | 22   | 54                                    | 133 | —   | —                              |   |
| 2806V-5      | ○               | △               | 68                      | —    | —                                     | —   | —   | —                              |   |
| 2806V-10     | ○               | △               | 104                     | —    | —                                     | —   | —   | —                              |   |
| 3205V-5      | ○               | ○               | 56                      | 32   | 57                                    | 120 | —   | —                              |   |
| 3205V-10     | ○               | ○               | 86                      | 32   | 57                                    | 150 | —   | —                              |   |
| 3206V-5      | ○               | ○               | 63                      | 32   | 57                                    | 127 | —   | —                              |   |
| 3206V-10     | ○               | ○               | 99                      | 32   | 57                                    | 163 | —   | —                              |   |
| BIF (Medium) | 2508V-5         | ○               | ○                       | 82   | 34                                    | 45  | 150   | —                              | — |
|              | 2508V-7         | ○               | ○                       | 98   | 34                                    | 45  | 166   | —                              | — |
|              | 2508V-10        | ○               | ○                       | 130  | 34                                    | 45  | 198   | —                              | — |

○ : Available △ : Available per request × : Not available  
 \*Please contact THK for more information regarding the model numbers that do not support WW and QZ.  
 Parentheses indicate the dimensions with QZ but without WW.

Unit: mm

| Model No. | WW availability | QZ availability | Dimensions including WW |     | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |    |
|-----------|-----------------|-----------------|-------------------------|-----|---------------------------------------|---|--------------------------------|----|
|           |                 |                 | L                       | QWL |                                       |   | QWD                            | AL |
|           | 2510V-5         | ○               | ○                       | 100 | 37                                    | 45  | 174                            |    |
|           | 2810V-3         | ○               | △                       | 88  | —                                     | —   | —                              |    |
|           | 3210V-5         | ○               | ○                       | 100 | 31                                    | 73  | 162                            |    |
|           | 3210V-7         | ○               | ○                       | 120 | 31                                    | 73  | 182                            |    |
|           | 3210V-10        | ○               | ○                       | 160 | 31                                    | 73  | 222                            |    |
|           | 3212V-5         | ○               | ○                       | 117 | 33                                    | 73  | 183                            |    |
|           | 3212V-7         | ○               | ○                       | 146 | 33                                    | 73  | 212                            |    |
|           | 3216V-5         | △               | △                       | —   | —                                     | —   | —                              |    |
|           | 3610V-5         | ○               | ○                       | 111 | 33                                    | 64  | 177                            |    |
|           | 3610V-7         | ○               | ○                       | 123 | 33                                    | 64  | 189                            |    |
|           | 3610V-10        | ○               | ○                       | 171 | 33                                    | 64  | 237                            |    |
|           | 3612V-5         | ○               | ○                       | 123 | 35                                    | 64  | 193                            |    |
|           | 3612V-7         | ○               | ○                       | 140 | 35                                    | 64  | 210                            |    |
|           | 3612V-10        | ○               | ○                       | 195 | 35                                    | 64  | 265                            |    |
|           | 3616V-5         | ○               | ○                       | 140 | 32                                    | 64  | 204                            |    |
|           | 3620V-3         | ○               | ○                       | 122 | 32                                    | 64  | 186                            |    |
|           | 4010V-5         | ○               | ○                       | 103 | 37                                    | 66  | 177                            |    |
|           | 4010V-7         | ○               | ○                       | 123 | 37                                    | 66  | 197                            |    |
|           | 4010V-10        | ○               | ○                       | 163 | 37                                    | 66  | 237                            |    |
|           | 4012V-5         | ○               | ○                       | 119 | 38                                    | 66  | 195                            |    |
|           | 4012V-7         | ○               | ○                       | 143 | 38                                    | 66  | 219                            |    |
|           | 4012V-10        | ○               | ○                       | 191 | 38                                    | 66  | 267                            |    |
|           | 4016V-5         | ○               | ○                       | 144 | 42                                    | 66  | 228                            |    |
|           | 4020V-5         | △               | △                       | —   | —                                     | —   | —                              |    |
|           | 4510V-5         | ○               | △                       | 111 | —                                     | —   | —                              |    |
|           | 4510V-10        | ○               | △                       | 171 | —                                     | —   | —                              |    |
|           | 4512V-5         | ○               | ○                       | 119 | 35.5                                  | 79  | 190                            |    |
|           | 4512V-10        | ○               | ○                       | 191 | 35.5                                  | 79  | 262                            |    |
|           | 4516V-5         | ○               | ○                       | 140 | 35.5                                  | 79  | 211                            |    |
|           | 4520V-5         | △               | △                       | —   | —                                     | —   | —                              |    |
|           | 5010V-5         | ○               | ○                       | 103 | 37.5                                  | 79  | 178                            |    |
|           | 5010V-7         | ○               | ○                       | 123 | 37.5                                  | 79  | 198                            |    |
|           | 5010V-10        | ○               | ○                       | 163 | 37.5                                  | 79  | 238                            |    |
|           | 5012V-5         | ○               | ○                       | 123 | 38.5                                  | 79  | 200                            |    |
|           | 5012V-7         | ○               | ○                       | 147 | 38.5                                  | 79  | 224                            |    |
|           | 5012V-10        | ○               | ○                       | 195 | 38.5                                  | 79  | 272                            |    |
|           | 5016V-5         | ○               | ○                       | 164 | 38.5                                  | 79  | 241                            |    |
|           | 5016V-10        | ○               | ○                       | 260 | 38.5                                  | 79  | 337                            |    |
|           | 5020V-5         | ○               | ○                       | 201 | 40.5                                  | 79  | 282                            |    |
|           | 1404-4          | △               | ×                       | —   | —                                     | —   | —                              |    |
|           | 1404-6          | △               | ×                       | —   | —                                     | —   | —                              |    |
|           | 1605-6          | ○               | △                       | 60  | —                                     | —   | —                              |    |
|           | 2004-6          | ○               | ×                       | 62  | —                                     | —   | —                              |    |
|           | 2004-8          | ○               | ×                       | 70  | —                                     | —   | —                              |    |
|           | 2005-6          | ○               | △                       | 61  | —                                     | —   | —                              |    |
|           | 2006-6          | △               | △                       | —   | —                                     | —   | —                              |    |
|           | 2008-4          | △               | △                       | —   | —                                     | —   | —                              |    |
|           | 2504-6          | ○               | △                       | 63  | —                                     | —   | —                              |    |
|           | 2504-8          | ○               | △                       | 71  | —                                     | —   | —                              |    |
|           | 2505-6          | ○               | △                       | 61  | —                                     | —   | —                              |    |
|           | 2506-4          | ○               | △                       | 60  | —                                     | —   | —                              |    |
|           | 2506-6          | ○               | △                       | 72  | —                                     | —   | —                              |    |
|           | 2508-4          | ○               | △                       | 71  | —                                     | —   | —                              |    |
|           | 2508-6          | ○               | △                       | 94  | —                                     | —   | —                              |    |
|           | 2510-4          | ○               | △                       | 85  | —                                     | —   | —                              |    |
|           | 2805-6          | ○               | △                       | 69  | —                                     | —   | —                              |    |

Unit: mm

| Model No. | WW availability | QZ availability | Dimensions including WW |     | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |    |
|-----------|-----------------|-----------------|-------------------------|-----|---------------------------------------|---|--------------------------------|----|
|           |                 |                 | L                       | QWL |                                       |   | QWD                            | AL |
|           | 2805-8          | ○               | △                       | 79  | —                                     | —   | —                              |    |
|           | 2806-6          | ○               | △                       | 73  | —                                     | —   | —                              |    |
|           | 2810-4          | ○               | △                       | 84  | —                                     | —   | —                              |    |
|           | 3204-6          | ○               | △                       | 64  | —                                     | —   | —                              |    |
|           | 3204-8          | ○               | △                       | 72  | —                                     | —   | —                              |    |
|           | 3204-10         | ○               | △                       | 80  | —                                     | —   | —                              |    |
|           | 3205-6          | ○               | △                       | 62  | —                                     | —   | —                              |    |
|           | 3205-8          | ○               | △                       | 73  | —                                     | —   | —                              |    |
|           | 3206-6          | ○               | △                       | 73  | —                                     | —   | —                              |    |
|           | 3206-8          | ○               | △                       | 87  | —                                     | —   | —                              |    |
|           | 3210-6          | ○               | △                       | 110 | —                                     | —   | —                              |    |
|           | 3212-4          | ○               | △                       | 98  | —                                     | —   | —                              |    |
|           | 3610-6          | ○               | △                       | 122 | —                                     | —   | —                              |    |
|           | 3610-8          | ○               | △                       | 143 | —                                     | —   | —                              |    |
|           | 3610-10         | ○               | △                       | 164 | —                                     | —   | —                              |    |
|           | 4010-6          | ○               | ○                       | 113 | 44                                    | 61  | 201                            |    |
|           | 4010-8          | ○               | ○                       | 137 | 44                                    | 61  | 225                            |    |
|           | 4012-6          | ○               | ○                       | 138 | 44                                    | 61  | 226                            |    |
|           | 4012-8          | ○               | ○                       | 163 | 44                                    | 61  | 251                            |    |
|           | 4016-4          | ○               | ○                       | 120 | 44                                    | 61  | 208                            |    |
|           | 5010-6          | ○               | △                       | 114 | —                                     | —   | —                              |    |
|           | 5010-8          | ○               | △                       | 137 | —                                     | —   | —                              |    |
|           | 5010-10         | ○               | △                       | 160 | —                                     | —   | —                              |    |
|           | 5012-6          | ○               | △                       | 145 | —                                     | —   | —                              |    |
|           | 5012-8          | ○               | △                       | 170 | —                                     | —   | —                              |    |
|           | 5016-4          | ○               | △                       | 129 | —                                     | —   | —                              |    |
|           | 5016-6          | ○               | △                       | 175 | —                                     | —   | —                              |    |
|           | 6310-8          | △               | △                       | —   | —                                     | —   | —                              |    |
|           | 6312-6          | △               | △                       | —   | —                                     | —   | —                              |    |
|           | 6312-8          | △               | △                       | —   | —                                     | —   | —                              |    |
|           | 1605V-5         | ○               | ○                       | 106 | 29                                    | 31  | 164                            |    |
|           | 2805V-7.5       | ○               | ○                       | 134 | 22                                    | 54  | 178                            |    |
|           | 2806V-7.5       | ○               | △                       | 158 | —                                     | —   | —                              |    |
|           | 3205V-7.5       | ○               | ○                       | 136 | 32                                    | 57  | 200                            |    |
|           | 2810V-2.5       | ○               | △                       | 146 | —                                     | —   | 212                            |    |
|           | 3610V-7.5       | ○               | ○                       | 261 | 33                                    | 64  | 327                            |    |
|           | 3616V-5         | ○               | ○                       | 268 | 32                                    | 64  | 332                            |    |
|           | 4016V-5         | ○               | ○                       | 280 | 42                                    | 66  | 364                            |    |
|           | 4510V-7.5       | ○               | △                       | 261 | —                                     | —   | 332                            |    |
|           | 5010V-7.5       | ○               | ○                       | 253 | 37.5                                  | 79  | 328                            |    |
|           | 5510-2.5        | ○               | △                       | 141 | —                                     | —   | —                              |    |
|           | 5510-5          | ○               | △                       | 201 | —                                     | —   | —                              |    |
|           | 5510-7.5        | ○               | △                       | 261 | —                                     | —   | —                              |    |
|           | 5512-2.5        | ○               | △                       | 165 | —                                     | —   | —                              |    |
|           | 5512-3          | ○               | △                       | 191 | —                                     | —   | —                              |    |
|           | 5512-3.5        | ○               | △                       | 189 | —                                     | —   | —                              |    |
|           | 5512-5          | ○               | △                       | 237 | —                                     | —   | —                              |    |
|           | 5512-7.5        | ○               | △                       | 309 | —                                     | —   | —                              |    |
|           | 5516-2.5        | ○               | △                       | 196 | —                                     | —   | —                              |    |
|           | 5516-5          | ○               | △                       | 292 | —                                     | —   | —                              |    |
|           | 5520-2.5        | ○               | △                       | 227 | —                                     | —   | —                              |    |
|           | 5520-5          | ○               | △                       | 347 | —                                     | —   | —                              |    |
|           | 6310-2.5        | ○               | △                       | 137 | —                                     | —   | —                              |    |

○ : Available △ : Available per request × : Not available  
 \*Please contact THK for more information regarding the model numbers that do not support WW and QZ.  
 Parentheses indicate the dimensions with QZ but without WW.

## Options

## Dimensions of Each Model with an Option Attached

Unit: mm

| Model No.   |           | WW availability | QZ availability | Dimensions including WW | Length of protrusion with QZ attached |     | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |
|-------------|-----------|-----------------|-----------------|-------------------------|---------------------------------------|-----|---|--------------------------------|
|             |           |                 |                 |                         | L                                     | QWL |   |                                |
| BNFN        | 6310-5    | ○               | △               | 197                     | —                                     | —   | —   | —                              |
|             | 6310-7.5  | ○               | △               | 257                     | —                                     | —   | —   | —                              |
|             | 6312A-2.5 | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 6312A-5   | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 6316-2.5  | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 6316-5    | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 6320-2.5  | ○               | △               | 227                     | —                                     | —   | —   | —                              |
|             | 6320-5    | ○               | △               | 347                     | —                                     | —   | —   | —                              |
|             | 7010-2.5  | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 7010-5    | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 7010-7.5  | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 7012-2.5  | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 7012-5    | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 7012-7.5  | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 7020-5    | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 8010-2.5  | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 8010-5    | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 8010-7.5  | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 8012-5    | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 8020A-2.5 | △               | △               | —                       | —                                     | —   | —   | —                              |
| 8020A-5     | △         | △               | —               | —                       | —                                     | —   | —   |                                |
| 10020A-2.5  | ○         | △               | 231             | —                       | —                                     | —   | —   |                                |
| 10020A-5    | ○         | △               | 351             | —                       | —                                     | —   | —   |                                |
| 10020A-7.5  | ○         | △               | 471             | —                       | —                                     | —   | —   |                                |
| DKN         | 4020-3    | ○               | ○               | 223                     | 47                                    | 61  | 317   | —                              |
|             | 5020-3    | ○               | △               | 243                     | —                                     | —   | —   | —                              |
|             | 6320-3    | △               | △               | —                       | —                                     | —   | —   | —                              |
| BLW         | 1510-5.6  | ○               | ○               | 96                      | 25.5                                  | 31  | 140   | —                              |
|             | 1616-3.6  | △               | ○               | —                       | 25.5                                  | 31  | (135.5)                                       | —                              |
|             | 2020-3.6  | ○               | △               | 112                     | —                                     | —   | —   | —                              |
|             | 2525-3.6  | ○               | △               | 131.5                   | —                                     | —   | —   | —                              |
|             | 3232-3.6  | ○               | ○               | 162.6                   | 37.5                                  | 53  | 230   | —                              |
|             | 3636-3.6  | ○               | △               | 191                     | —                                     | —   | —   | —                              |
|             | 4040-3.6  | ○               | △               | 201.8                   | —                                     | —   | —   | —                              |
| 5050-3.6    | ○         | △               | 255.8           | —                       | —                                     | —   | —   |                                |
| BNF (Small) | 1604V-5   | ○               | ○               | 53                      | 29                                    | 31  | 111   | —                              |
|             | 1605V-2.5 | ○               | ○               | 41                      | 29                                    | 31  | 99  | —                              |
|             | 1605V-5   | ○               | ○               | 56                      | 29                                    | 31  | 114   | —                              |
|             | 2004V-2.5 | ○               | ○               | 37                      | 27.5                                  | 39  | 92  | —                              |
|             | 2004V-5   | ○               | ○               | 49                      | 27.5                                  | 39  | 104   | —                              |
|             | 2005V-2.5 | ○               | ○               | 41                      | 27.5                                  | 43  | 96  | —                              |
|             | 2005V-5   | ○               | ○               | 56                      | 27.5                                  | 43  | 111   | —                              |
|             | 2010V-2.5 | △               | △               | —                       | —                                     | —   | —   | —                              |
|             | 2504V-2.5 | ○               | ○               | 36                      | 32.5                                  | 45  | 101   | —                              |
|             | 2504V-5   | ○               | ○               | 48                      | 32.5                                  | 45  | 113   | —                              |
|             | 2505V-2.5 | ○               | ○               | 40                      | 32.5                                  | 45  | 105   | —                              |
|             | 2505V-5   | ○               | ○               | 55                      | 32.5                                  | 45  | 120   | —                              |
|             | 2506V-2.5 | ○               | ○               | 44                      | 33                                    | 45  | 110   | —                              |
|             | 2506V-5   | ○               | ○               | 62                      | 33                                    | 45  | 128   | —                              |
|             | 2805V-2.5 | ○               | ○               | 44                      | 22                                    | 54  | 88  | —                              |
|             | 2805V-5   | ○               | ○               | 59                      | 22                                    | 54  | 103   | —                              |
|             | 2805V-7.5 | ○               | ○               | 74                      | 22                                    | 54  | 118   | —                              |
|             | 2806V-2.5 | ○               | △               | 50                      | —                                     | —   | —   | —                              |
|             | 2806V-5   | ○               | △               | 68                      | —                                     | —   | —   | —                              |
|             | 2806V-7.5 | ○               | △               | 86                      | —                                     | —   | —   | —                              |
| 3205V-2.5   | ○         | ○               | 41              | 32                      | 57                                    | 105 | —   |                                |

Unit: mm

| Model No.   |           | WW availability | QZ availability | Dimensions including WW | Length of protrusion with QZ attached |     | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |
|-------------|-----------|-----------------|-----------------|-------------------------|---------------------------------------|-----|---|--------------------------------|
|             |           |                 |                 |                         | L                                     | QWL |   |                                |
| BNF (Small) | 3205V-5   | ○               | ○               | 56                      | 32                                    | 57  | 120   | —                              |
|             | 3205V-7.5 | ○               | ○               | 71                      | 32                                    | 57  | 135   | —                              |
|             | 3206V-2.5 | ○               | ○               | 45                      | 32                                    | 57  | 109   | —                              |
|             | 3206V-5   | ○               | ○               | 63                      | 32                                    | 57  | 127   | —                              |
|             | 2508V-2.5 | ○               | ○               | 58                      | 34                                    | 45  | 126   | —                              |
| 2508V-3.5   | ○         | ○               | 66              | 34                      | 45                                    | 134 | —   |                                |
| 2508V-5     | ○         | ○               | 82              | 34                      | 45                                    | 150 | —   |                                |
| 2510V-2.5   | ○         | ○               | 70              | 37                      | 45                                    | 144 | —   |                                |
| 2810V-2.5   | ○         | △               | 86              | —                       | —                                     | —   | —   |                                |
| 3210V-2.5   | ○         | ○               | 70              | 31                      | 73                                    | 132 | —   |                                |
| 3210V-3.5   | ○         | ○               | 80              | 31                      | 73                                    | 142 | —   |                                |
| 3210V-5     | ○         | ○               | 100             | 31                      | 73                                    | 162 | —   |                                |
| 3212V-3.5   | ○         | ○               | 98              | 33                      | 73                                    | 164 | —   |                                |
| 3216V-5     | △         | △               | —               | —                       | —                                     | —   | —   |                                |
| 3610V-2.5   | ○         | ○               | 81              | 33                      | 64                                    | 147 | —   |                                |
| 3610V-5     | ○         | ○               | 111             | 33                      | 64                                    | 177 | —   |                                |
| 3610V-7.5   | ○         | ○               | 141             | 33                      | 64                                    | 207 | —   |                                |
| 3612V-2.5   | ○         | ○               | 87              | 35                      | 64                                    | 157 | —   |                                |
| 3612V-5     | ○         | ○               | 123             | 35                      | 64                                    | 193 | —   |                                |
| 3616V-2.5   | ○         | ○               | 92              | 32                      | 64                                    | 156 | —   |                                |
| 3620V-1.5   | ○         | ○               | 82              | 32                      | 64                                    | 146 | —   |                                |
| 4010V-2.5   | ○         | ○               | 73              | 37                      | 66                                    | 147 | —   |                                |
| 4010V-3.5   | ○         | ○               | 83              | 37                      | 66                                    | 157 | —   |                                |
| 4010V-5     | ○         | ○               | 103             | 37                      | 66                                    | 177 | —   |                                |
| 4012V-2.5   | ○         | ○               | 83              | 38                      | 66                                    | 159 | —   |                                |
| 4012V-3.5   | ○         | ○               | 95              | 38                      | 66                                    | 171 | —   |                                |
| 4012V-5     | ○         | ○               | 119             | 38                      | 66                                    | 195 | —   |                                |
| 4016V-5     | ○         | ○               | 144             | 42                      | 66                                    | 228 | —   |                                |
| 4020V-5     | △         | △               | —               | —                       | —                                     | —   | —   |                                |
| 4510V-2.5   | ○         | △               | 81              | —                       | —                                     | —   | 152   |                                |
| 4510V-3     | ○         | △               | 94              | —                       | —                                     | —   | 165   |                                |
| 4510V-5     | ○         | △               | 111             | —                       | —                                     | —   | 182   |                                |
| 4510V-7.5   | ○         | △               | 141             | —                       | —                                     | —   | 212   |                                |
| 4512V-5     | ○         | ○               | 119             | 35.5                    | 79                                    | 190 | —   |                                |
| 4520V-2.5   | △         | △               | —               | —                       | —                                     | —   | —   |                                |
| 5010V-2.5   | ○         | ○               | 73              | 37.5                    | 79                                    | 148 | —   |                                |
| 5010V-3.5   | ○         | ○               | 83              | 37.5                    | 79                                    | 158 | —   |                                |
| 5010V-5     | ○         | ○               | 103             | 37.5                    | 79                                    | 178 | —   |                                |
| 5010V-7.5   | ○         | ○               | 133             | 37.5                    | 79                                    | 208 | —   |                                |
| 5012V-2.5   | ○         | ○               | 87              | 38.5                    | 79                                    | 164 | —   |                                |
| 5012V-3.5   | ○         | ○               | 99              | 38.5                    | 79                                    | 176 | —   |                                |
| 5012V-5     | ○         | ○               | 123             | 38.5                    | 79                                    | 200 | —   |                                |
| 5016V-2.5   | ○         | ○               | 116             | 38.5                    | 79                                    | 193 | —   |                                |
| 5016V-5     | ○         | ○               | 164             | 38.5                    | 79                                    | 241 | —   |                                |
| 5020V-2.5   | ○         | ○               | 141             | 40.5                    | 79                                    | 222 | —   |                                |
| BNF         | 5510-2.5  | ○               | △               | 81                      | —                                     | —   | —   | —                              |
|             | 5510-5    | ○               | △               | 111                     | —                                     | —   | —   | —                              |
|             | 5510-7.5  | ○               | △               | 141                     | —                                     | —   | —   | —                              |
|             | 5512-2.5  | ○               | △               | 93                      | —                                     | —   | —   | —                              |
|             | 5512-3    | ○               | △               | 107                     | —                                     | —   | —   | —                              |
|             | 5512-3.5  | ○               | △               | 105                     | —                                     | —   | —   | —                              |
|             | 5512-5    | ○               | △               | 129                     | —                                     | —   | —   | —                              |
| 5512-7.5    | ○         | △               | 165             | —                       | —                                     | —   | —   |                                |

○ : Available △ : Available per request × : Not available  
 \*Please contact THK for more information regarding the model numbers that do not support WW and QZ.  
 Parentheses indicate the dimensions with QZ but without WW.

Unit: mm

| Model No. | WW availability | QZ availability | Dimensions including WW |     | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |     |
|-----------|-----------------|-----------------|-------------------------|-----|---------------------------------------|---|--------------------------------|-----|
|           |                 |                 | L                       | QWL |                                       |   |                                | QWD |
| BNF       | 5516-2.5        | ○               | △                       | 116 | —                                     | —   | —                              |     |
|           | 5516-5          | ○               | △                       | 164 | —                                     | —   | —                              |     |
|           | 5520-2.5        | ○               | △                       | 127 | —                                     | —   | —                              |     |
|           | 5520-5          | ○               | △                       | 187 | —                                     | —   | —                              |     |
|           | 6310-2.5        | ○               | △                       | 77  | —                                     | —   | —                              |     |
|           | 6310-5          | ○               | △                       | 107 | —                                     | —   | —                              |     |
|           | 6310-7.5        | ○               | △                       | 137 | —                                     | —   | —                              |     |
|           | 6312A-2.5       | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 6312A-5         | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 6316-5          | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 6320-2.5        | ○               | △                       | 127 | —                                     | —   | —                              |     |
|           | 6320-5          | ○               | △                       | 187 | —                                     | —   | —                              |     |
|           | 7010-2.5        | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 7010-5          | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 7010-7.5        | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 7012-2.5        | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 7012-5          | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 7012-7.5        | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 7020-5          | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 8010-2.5        | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 8010-5          | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 8010-7.5        | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 8020A-2.5       | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 8020A-5         | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 8020A-7.5       | △               | △                       | —   | —                                     | —   | —                              |     |
|           | 10020A-2.5      | ○               | △                       | 131 | —                                     | —   | —                              |     |
|           | 10020A-5        | ○               | △                       | 191 | —                                     | —   | —                              |     |
|           | 10020A-7.5      | ○               | △                       | 251 | —                                     | —   | —                              |     |
|           | DK              | 1404-4          | △                       | ×   | —                                     | —   | —                              | —   |
|           |                 | 1404-6          | △                       | ×   | —                                     | —   | —                              | —   |
| 1605-3    |                 | ○               | △                       | 45  | —                                     | —   | —                              |     |
| 1605-4    |                 | ○               | △                       | 50  | —                                     | —   | —                              |     |
| 2004-3    |                 | ○               | ×                       | 42  | —                                     | —   | —                              |     |
| 2004-4    |                 | ○               | ×                       | 46  | —                                     | —   | —                              |     |
| 2005-3    |                 | ○               | △                       | 46  | —                                     | —   | —                              |     |
| 2005-4    |                 | ○               | △                       | 51  | —                                     | —   | —                              |     |
| 2006-3    |                 | △               | △                       | —   | —                                     | —   | —                              |     |
| 2006-4    |                 | △               | △                       | —   | —                                     | —   | —                              |     |
| 2008-4    |                 | △               | △                       | —   | —                                     | —   | —                              |     |
| 2504-3    |                 | ○               | △                       | 43  | —                                     | —   | —                              |     |
| 2504-4    |                 | ○               | △                       | 47  | —                                     | —   | —                              |     |
| 2505-3    |                 | ○               | △                       | 46  | —                                     | —   | —                              |     |
| 2505-4    |                 | ○               | △                       | 51  | —                                     | —   | —                              |     |
| 2506-3    |                 | ○               | △                       | 52  | —                                     | —   | —                              |     |
| 2506-4    |                 | ○               | △                       | 60  | —                                     | —   | —                              |     |
| 2508-3    |                 | ○               | △                       | 62  | —                                     | —   | —                              |     |
| 2508-4    |                 | ○               | △                       | 71  | —                                     | —   | —                              |     |
| 2510-3    |                 | ○               | △                       | 80  | —                                     | —   | —                              |     |
| 2510-4    |                 | ○               | △                       | 85  | —                                     | —   | —                              |     |
| 2805-3    |                 | ○               | △                       | 49  | —                                     | —   | —                              |     |
| 2805-4    |                 | ○               | △                       | 54  | —                                     | —   | —                              |     |
| 2806-3    |                 | ○               | △                       | 53  | —                                     | —   | —                              |     |
| 2806-4    |                 | ○               | △                       | 61  | —                                     | —   | —                              |     |
| 2810-4    |                 | ○               | △                       | 84  | —                                     | —   | —                              |     |
| 3204-3    |                 | ○               | ×                       | 44  | —                                     | —   | —                              |     |
| 3204-4    |                 | ○               | ×                       | 48  | —                                     | —   | —                              |     |

Unit: mm

| Model No.  | WW availability | QZ availability | Dimensions including WW |     | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |
|------------|-----------------|-----------------|-------------------------|-----|---------------------------------------|---|--------------------------------|
|            |                 |                 | L                       | QWL |                                       |   |                                |
| DK         | 3205-3          | ○               | △                       | 47  | —                                     | —   | —                              |
|            | 3205-4          | ○               | △                       | 52  | —                                     | —   | —                              |
|            | 3205-6          | ○               | △                       | 62  | —                                     | —   | —                              |
|            | 3206-3          | ○               | △                       | 53  | —                                     | —   | —                              |
|            | 3206-4          | ○               | △                       | 61  | —                                     | —   | —                              |
|            | 3210-3          | ○               | △                       | 80  | —                                     | —   | —                              |
|            | 3210-4          | ○               | △                       | 90  | —                                     | —   | —                              |
|            | 3212-4          | ○               | △                       | 98  | —                                     | —   | —                              |
|            | 3610-3          | ○               | △                       | 82  | —                                     | —   | —                              |
|            | 3610-4          | ○               | △                       | 93  | —                                     | —   | —                              |
|            | 4010-3          | ○               | ○                       | 83  | 44                                    | 61  | 171                            |
|            | 4010-4          | ○               | ○                       | 93  | 44                                    | 61  | 181                            |
|            | 4012-3          | ○               | ○                       | 90  | 44                                    | 61  | 178                            |
|            | 4012-4          | ○               | ○                       | 103 | 44                                    | 61  | 191                            |
|            | 4016-4          | ○               | ○                       | 120 | 44                                    | 61  | 208                            |
|            | 4020-3          | ○               | ○                       | 123 | 47                                    | 61  | 217                            |
|            | 5010-3          | ○               | △                       | 83  | —                                     | —   | —                              |
|            | 5010-4          | ○               | △                       | 93  | —                                     | —   | —                              |
|            | 5010-6          | ○               | △                       | 114 | —                                     | —   | —                              |
|            | 5012-3          | ○               | △                       | 97  | —                                     | —   | —                              |
|            | 5012-4          | ○               | △                       | 110 | —                                     | —   | —                              |
|            | 5016-3          | ○               | △                       | 111 | —                                     | —   | —                              |
|            | 5016-4          | ○               | △                       | 129 | —                                     | —   | —                              |
|            | 5020-3          | ○               | △                       | 136 | —                                     | —   | —                              |
|            | 6310-4          | △               | △                       | —   | —                                     | —   | —                              |
|            | 6310-6          | △               | △                       | —   | —                                     | —   | —                              |
|            | 6312-3          | △               | △                       | —   | —                                     | —   | —                              |
|            | 6312-4          | △               | △                       | —   | —                                     | —   | —                              |
|            | 6320-3          | △               | △                       | —   | —                                     | —   | —                              |
|            | MBF             | 0401-3.7        | ×                       | ×   | —                                     | —   | —                              |
| 0601-3.7   |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 0602-2.7   |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 0602.5-2.7 |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 0801.5-3.7 |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 0802-3.7   |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 0802.5-3.7 |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 0803-2.7   |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 0804-2.7   |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 1001-3.7   |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 1001.5-3.7 |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 1002-3.7   |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 1002.5-3.7 |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 1003-3.7   |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 1005-2.7   |                 | ×               | ×                       | —   | —                                     | —   | —                              |
| 1202-3.7   | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 1202.5-3.7 | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 1203-3.7   | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 1204-3.7   | ×               | ×               | —                       | —   | —                                     | —   |                                |
| 1402-3.7   | △               | ×               | —                       | —   | —                                     | —   |                                |
| 1404-3.7   | △               | ×               | —                       | —   | —                                     | —   |                                |
| WHF        | 1530-3.4        | ×               | ○                       | —   | 25.5                                  | 31  | 115.5                          |
|            | 1540-3.4        | ×               | ○                       | —   | 25.5                                  | 31  | 132.6                          |
|            | 2020-3.4        | ×               | △                       | —   | —                                     | —   | —                              |

○ : Available △ : Available per request × : Not available  
 \*Please contact THK for more information regarding the model numbers that do not support WW and QZ.  
 Parentheses indicate the dimensions with QZ but without WW.

## Options

## Dimensions of Each Model with an Option Attached

Unit: mm

| Model No.       | WW availability | QZ availability | Dimensions including WW | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |       |
|-----------------|-----------------|-----------------|-------------------------|---------------------------------------|---|--------------------------------|-------|
|                 |                 |                 |                         |                                       |   | L                              | AL    |
| WHF             | 2025-3.4        | ×               | △                       | —                                     | —   | —                              | —     |
|                 | 2030-3.4        | ×               | △                       | —                                     | —   | —                              | —     |
|                 | 2040-3.4        | ×               | △                       | —                                     | —   | —                              | —     |
|                 | 2525-3.4        | ×               | △                       | —                                     | —   | —                              | —     |
|                 | 2550-3.4        | ×               | △                       | —                                     | —   | —                              | —     |
| 0808-3.2        | ×               | ×               | —                       | —                                     | —   | —                              |       |
| BLK (Precision) | 1510-5.6        | ○               | ○                       | 51                                    | 25.5  | 31                             | 95    |
|                 | 1616-2.8        | △               | ○                       | —                                     | 25.5  | 31                             | (105) |
|                 | 1616-3.6        | △               | ○                       | —                                     | 25.5  | 31                             | (89)  |
|                 | 2020-2.8        | ○               | △                       | 72                                    | —   | —                              | —     |
|                 | 2020-3.6        | ○               | △                       | 52                                    | —   | —                              | —     |
|                 | 2525-2.8        | ○               | △                       | 87                                    | —   | —                              | —     |
|                 | 2525-3.6        | ○               | △                       | 62                                    | —   | —                              | —     |
|                 | 3232-2.8        | ○               | ○                       | 109.6                                 | 37.5  | 53                             | 177   |
|                 | 3232-3.6        | ○               | ○                       | 77.6                                  | 37.5  | 53                             | 145   |
|                 | 3620-5.6        | ○               | △                       | 88                                    | —   | —                              | —     |
|                 | 3624-5.6        | △               | △                       | —                                     | —   | —                              | —     |
|                 | 3636-2.8        | ○               | △                       | 123                                   | —   | —                              | —     |
|                 | 3636-3.6        | ○               | △                       | 87                                    | —   | —                              | —     |
|                 | 4040-2.8        | ○               | △                       | 135.8                                 | —   | —                              | —     |
|                 | 4040-3.6        | ○               | △                       | 95.8                                  | —   | —                              | —     |
| 5050-2.8        | ○               | △               | 166.8                   | —                                     | —   | —                              |       |
| 5050-3.6        | ○               | △               | 116.8                   | —                                     | —   | —                              |       |
| WGF             | 0812-3          | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 1015-3          | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 1320-3          | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 1520-1.5        | ○               | ○                       | 52                                    | 25.5  | 31                             | 96    |
|                 | 1520-3          | ○               | ○                       | 52                                    | 25.5  | 31                             | 96    |
|                 | 1530-1          | ×               | ○                       | —                                     | 25.5  | 31                             | (84)  |
|                 | 1530-3          | ×               | ○                       | —                                     | 25.5  | 31                             | (114) |
|                 | 1540-1.5        | ×               | ○                       | —                                     | 25.5  | 31                             | (93)  |
|                 | 2040-1          | ×               | △                       | —                                     | —   | —                              | —     |
|                 | 2040-3          | ×               | △                       | —                                     | —   | —                              | —     |
|                 | 2060-1.5        | ×               | △                       | —                                     | —   | —                              | —     |
|                 | 2550-1          | ×               | △                       | —                                     | —   | —                              | —     |
|                 | 2550-3          | ×               | △                       | —                                     | —   | —                              | —     |
|                 | 3060-1          | ×               | ○                       | —                                     | 37.5  | 53                             | (137) |
|                 | 3060-3          | ×               | ○                       | —                                     | 37.5  | 53                             | (197) |
| 3090-1.5        | ×               | ○               | —                       | 37.5                                  | 53  | (167)                          |       |
| 4080-1          | ×               | △               | —                       | —                                     | —   | —                              |       |
| 4080-3          | ×               | △               | —                       | —                                     | —   | —                              |       |
| 50100-1         | ×               | △               | —                       | —                                     | —   | —                              |       |
| 50100-3         | ×               | △               | —                       | —                                     | —   | —                              |       |
| BNK             | 0401-3          | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 0501-3          | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 0601-3          | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 0801-3          | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 0802-3          | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 0810-3          | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 1002-3          | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 1004-2.5        | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 1010-1.5        | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 1205-2.5        | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 1402-3          | ×               | ×                       | —                                     | —   | —                              | —     |
|                 | 1404-3          | △               | ×                       | —                                     | —   | —                              | —     |
|                 | 1408-2.5        | △               | △                       | —                                     | —   | —                              | —     |

Unit: mm

| Model No.    | WW availability | QZ availability | Dimensions including WW | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |      |
|--------------|-----------------|-----------------|-------------------------|---------------------------------------|---|--------------------------------|------|
|              |                 |                 |                         |                                       |   | L                              | AL   |
| BNK          | 1510-5.6        | ○               | ○                       | 51                                    | 25.5  | 31                             | 95   |
|              | 1520-3          | △               | ○                       | —                                     | 25.5  | 31                             | (96) |
|              | 1616-3.6        | △               | ○                       | —                                     | 25.5  | 31                             | (93) |
|              | 2010-2.5        | ○               | △                       | 54                                    | —   | —                              | —    |
|              | 2020-3.6        | ○               | △                       | 59                                    | —   | —                              | —    |
|              | 2520-3.6        | △               | △                       | —                                     | —   | —                              | —    |
| JPF          | 1404-4          | △               | ×                       | —                                     | —   | —                              | —    |
|              | 1405-4          | △               | ×                       | —                                     | —   | —                              | —    |
|              | 1605-4          | ○               | ×                       | 60                                    | —   | —                              | —    |
|              | 2005-6          | ○               | ×                       | 80                                    | —   | —                              | —    |
|              | 2505-6          | ○               | ×                       | 80                                    | —   | —                              | —    |
|              | 2510-4          | ○               | ×                       | 112                                   | —   | —                              | —    |
|              | 2805-6          | ○               | ×                       | 80                                    | —   | —                              | —    |
|              | 2806-6          | ○               | ×                       | 90                                    | —   | —                              | —    |
|              | 3210-6          | ○               | ×                       | 135                                   | —   | —                              | —    |
|              | 3610-6          | ○               | ×                       | 138                                   | —   | —                              | —    |
| BTK-V        | 4010-6          | ○               | ×                       | 138                                   | —   | —                              | —    |
|              | 1006-2.6        | ×               | △                       | —                                     | —   | —                              | —    |
|              | 1208-2.6        | ×               | △                       | —                                     | —   | —                              | —    |
|              | 1404-3.6        | △               | △                       | —                                     | —   | —                              | —    |
|              | 1405-2.6        | ○               | △                       | 40                                    | —   | —                              | —    |
|              | 1605-2.6        | ○               | △                       | 40                                    | —   | —                              | —    |
|              | 1808-3.6        | △               | △                       | —                                     | —   | —                              | —    |
|              | 2005-2.6        | ○               | △                       | 40                                    | —   | —                              | —    |
|              | 2010-2.6        | ○               | △                       | 61                                    | —   | —                              | —    |
|              | 2505-2.6        | ○               | △                       | 40                                    | —   | —                              | —    |
|              | 2510-5.3        | ○               | ○                       | 98                                    | 32.5  | 45                             | 163  |
|              | 2806-2.6        | ○               | △                       | 47                                    | —   | —                              | —    |
|              | 2806-5.3        | ○               | △                       | 65                                    | —   | —                              | —    |
|              | 3210-2.6        | ○               | ○                       | 68                                    | 32  | 57                             | 132  |
|              | 3210-5.3        | ○               | ○                       | 98                                    | 32  | 57                             | 162  |
| 3610-2.6     | ○               | ○               | 70                      | 31                                    | 64  | 132                            |      |
| 3610-5.3     | ○               | ○               | 100                     | 31                                    | 64  | 162                            |      |
| 4010-5.3     | ○               | ○               | 100                     | 34                                    | 66  | 168                            |      |
| 4512-5.3     | △               | △               | —                       | —                                     | —   | —                              |      |
| 5016-5.3     | ○               | ○               | 145                     | 35                                    | 79  | 215                            |      |
| MTF          | 0601-3.7        | ×               | ×                       | —                                     | —   | —                              | —    |
|              | 0801-3.7        | ×               | ×                       | —                                     | —   | —                              | —    |
|              | 0802-3.7        | ×               | ×                       | —                                     | —   | —                              | —    |
|              | 0805-2.7        | ×               | ×                       | —                                     | —   | —                              | —    |
|              | 1002-3.7        | ×               | ×                       | —                                     | —   | —                              | —    |
|              | 1004-2.7        | ×               | ×                       | —                                     | —   | —                              | —    |
|              | 1202-3.7        | ×               | ×                       | —                                     | —   | —                              | —    |
|              | 1402-3.7        | ×               | ×                       | —                                     | —   | —                              | —    |
| BLK (Rolled) | 0808-3.2        | ×               | ×                       | —                                     | —   | —                              | —    |
|              | 1010-3.2        | ×               | ×                       | —                                     | —   | —                              | —    |
|              | 1510-5.6        | ○               | ○                       | 51                                    | 25.5  | 31                             | 95   |
|              | 1616-3.6        | △               | ○                       | —                                     | 25.5  | 31                             | (89) |
|              | 1616-7.2        | △               | ○                       | —                                     | 25.5  | 31                             | (89) |
|              | 2020-3.6        | ○               | △                       | 52                                    | —   | —                              | —    |
|              | 2020-7.2        | ○               | △                       | 52                                    | —   | —                              | —    |
|              | 2525-3.6        | ○               | △                       | 62                                    | —   | —                              | —    |
|              | 2525-7.2        | ○               | △                       | 62                                    | —   | —                              | —    |

○ : Available △ : Available per request × : Not available  
 \*Please contact THK for more information regarding the model numbers that do not support WW and QZ.  
 Parentheses indicate the dimensions with QZ but without WW.

Unit: mm

| Model No.       | WW availability | QZ availability | Dimensions including WW | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |         |
|-----------------|-----------------|-----------------|-------------------------|---------------------------------------|---|--------------------------------|---------|
|                 |                 |                 | L                       | QWL                                   | QWD   | AL                             |         |
| BLK<br>(Rolled) | 3232-3.6        | ○               | ○                       | 77.6                                  | 37.5  | 53                             | 145     |
|                 | 3232-7.2        | ○               | ○                       | 77.6                                  | 37.5  | 53                             | 145     |
|                 | 3620-5.6        | ○               | △                       | 88                                    | —   | —                              | —       |
|                 | 3624-5.6        | ○               | △                       | 104                                   | —   | —                              | —       |
|                 | 3636-3.6        | △               | △                       | —                                     | —   | —                              | —       |
|                 | 3636-7.2        | △               | △                       | —                                     | —   | —                              | —       |
|                 | 4040-3.6        | △               | △                       | —                                     | —   | —                              | —       |
|                 | 4040-7.2        | △               | △                       | —                                     | —   | —                              | —       |
|                 | 5050-3.6        | △               | △                       | —                                     | —   | —                              | —       |
|                 | 5050-7.2        | △               | △                       | —                                     | —   | —                              | —       |
| WTF             | 1520-3          | ○               | ○                       | 52                                    | 25.5  | 31                             | 96      |
|                 | 1520-6          | ○               | ○                       | 52                                    | 25.5  | 31                             | 96      |
|                 | 1530-2          | ×               | ○                       | —                                     | 25.5  | 31                             | (84)    |
|                 | 1530-3          | ×               | ○                       | —                                     | 25.5  | 31                             | (114)   |
|                 | 2040-2          | ×               | △                       | —                                     | —   | —                              | —       |
|                 | 2040-3          | ×               | △                       | —                                     | —   | —                              | —       |
|                 | 2550-2          | ×               | △                       | —                                     | —   | —                              | —       |
|                 | 2550-3          | ×               | △                       | —                                     | —   | —                              | —       |
|                 | 3060-2          | ×               | ○                       | —                                     | 37.5  | 53                             | (137.5) |
|                 | 3060-3          | ×               | ○                       | —                                     | 37.5  | 53                             | (197.5) |
|                 | 4080-2          | ×               | △                       | —                                     | —   | —                              | —       |
|                 | 4080-3          | ×               | △                       | —                                     | —   | —                              | —       |
|                 | 50100-2         | ×               | △                       | —                                     | —   | —                              | —       |
| 50100-3         | ×               | △               | —                       | —                                     | —   | —                              |         |

Unit: mm

| Model No.                          | WW availability | QZ availability | Dimensions including WW | Length of protrusion with QZ attached | Outer diameter of protrusion with QZ attached | Dimensions including QZ and WW |       |
|------------------------------------|-----------------|-----------------|-------------------------|---------------------------------------|---|--------------------------------|-------|
|                                    |                 |                 | L                       | QWL                                   | QWD   | AL                             |       |
| CNF                                | 1530-6          | ×               | ○                       | —                                     | 25.5  | 31                             | (114) |
|                                    | 2040-6          | ×               | △                       | —                                     | —   | —                              | —     |
|                                    | 2550-6          | ×               | △                       | —                                     | —   | —                              | —     |
|                                    | 3060-6          | ×               | ○                       | —                                     | 37.5  | 53                             | (197) |
|                                    | 1404-3.6        | △               | ×                       | —                                     | —   | —                              | —     |
| BNT<br>(Both precision and rolled) | 1405-2.6        | △               | ×                       | 35                                    | —   | —                              | —     |
|                                    | 1605-2.6        | △               | △                       | 36                                    | 29  | 31                             | 94    |
|                                    | 1808-3.6        | △               | △                       | —                                     | —   | —                              | —     |
|                                    | 2005-2.6        | △               | △                       | 35                                    | —   | —                              | —     |
|                                    | 2010-2.6        | △               | △                       | 58                                    | —   | —                              | —     |
|                                    | 2505-2.6        | △               | △                       | 35                                    | —   | —                              | —     |
|                                    | 2510-5.3        | △               | △                       | 94                                    | —   | —                              | —     |
|                                    | 2806-2.6        | △               | △                       | 42                                    | —   | —                              | —     |
|                                    | 2806-5.3        | △               | △                       | 67                                    | —   | —                              | —     |
|                                    | 3210-2.6        | △               | △                       | 64                                    | —   | —                              | —     |
|                                    | 3210-5.3        | △               | △                       | 94                                    | —   | —                              | —     |
|                                    | 3610-2.6        | △               | △                       | 64                                    | —   | —                              | —     |
|                                    | 3610-5.3        | △               | △                       | 96                                    | —   | —                              | —     |
| 4512-5.3                           | △               | △               | 115                     | —                                     | —   | —                              |       |

○ : Available △ : Available per request × : Not available  
 \*Please contact THK for more information regarding the model numbers that do not support WW and QZ.  
 Parentheses indicate the dimensions with QZ but without WW.

## Model number coding

**BIF2505V-5 QZ WW G0 +1000L C5**


With QZ Lubricator

With wiper ring W

Note) QZ Lubricator and wiper ring W are not sold alone.



## Ball Screw Nut Dimensions with Canvas Seal




Unit: mm

| Model No.     | SDA-V TT<br>(with thin film seal) |                | SDA-V CC<br>(with canvas seal) |                |
|---------------|-----------------------------------|----------------|--------------------------------|----------------|
|               | L <sub>1</sub>                    | B <sub>4</sub> | L <sub>1</sub>                 | B <sub>4</sub> |
| SDAN 3110V-5  | 135                               | 62             | 136                            | 63             |
| SDAN 3112V-5  | 158                               | 72             | 159                            | 72             |
| SDAN 3116V-5  | 189                               | 90             | 190                            | 91             |
| SDAN 3120V-5  | 232                               | 109            | 233                            | 110            |
| SDAN 3205V-4  | 62                                | 29             | 62                             | 29             |
| SDAN 3206V-5  | 84                                | 39             | 85                             | 40             |
| SDAN 3208V-5  | 108                               | 49             | 108                            | 49             |
| SDAN 3210V-5  | 121                               | 58             | 122                            | 59             |
| SDAN 3210VA-5 | 135                               | 62             | 136                            | 63             |
| SDAN 3212VA-5 | 158                               | 72             | 160                            | 72             |
| SDAN 3216VA-5 | 189                               | 90             | 190                            | 91             |
| SDAN 3220VA-5 | 232                               | 109            | 233                            | 110            |
| SDAN 3606V-4  | 72                                | 33             | 73                             | 34             |
| SDAN 3610V-5  | 135                               | 62             | 136                            | 63             |
| SDAN 3612V-5  | 158                               | 72             | 159                            | 72             |
| SDAN 3616V-5  | 189                               | 90             | 190                            | 91             |
| SDAN 3620V-5  | 232                               | 109            | 233                            | 110            |
| SDAN 3810V-5  | 135                               | 62             | 136                            | 63             |
| SDAN 3812V-5  | 158                               | 71             | 159                            | 72             |
| SDAN 3816V-5  | 189                               | 90             | 190                            | 91             |
| SDAN 3820V-5  | 232                               | 109            | 233                            | 110            |
| SDAN 4008VX-5 | 111                               | 52             | 111                            | 52             |
| SDAN 4010VA-5 | 135                               | 62             | 136                            | 63             |
| SDAN 4012VA-5 | 158                               | 72             | 160                            | 72             |
| SDAN 4016VA-5 | 189                               | 90             | 190                            | 91             |
| SDAN 4020VA-5 | 232                               | 109            | 233                            | 110            |
| SDAN 4510V-5  | 135                               | 62             | 136                            | 63             |
| SDAN 4510VA-5 | 135                               | 62             | 136                            | 63             |
| SDAN 4512V-5  | 158                               | 72             | 159                            | 72             |
| SDAN 4512VA-5 | 158                               | 72             | 160                            | 72             |
| SDAN 4516V-5  | 189                               | 90             | 190                            | 91             |
| SDAN 4516VA-5 | 189                               | 90             | 190                            | 91             |

Unit: mm

| Model No.      | SDA-V TT<br>(with thin film seal) |                | SDA-V CC<br>(with canvas seal) |                |
|----------------|-----------------------------------|----------------|--------------------------------|----------------|
|                | L <sub>1</sub>                    | B <sub>4</sub> | L <sub>1</sub>                 | B <sub>4</sub> |
| SDAN 4520V-5   | 232                               | 109            | 233                            | 110            |
| SDAN 4520VA-5  | 232                               | 109            | 233                            | 110            |
| SDAN 5010V-5   | 135                               | 62             | 136                            | 63             |
| SDAN 5010VA-5  | 135                               | 62             | 136                            | 63             |
| SDAN 5012V-5   | 158                               | 72             | 159                            | 72             |
| SDAN 5012VA-5  | 158                               | 72             | 160                            | 72             |
| SDAN 5016V-5   | 189                               | 90             | 190                            | 91             |
| SDAN 5016VA-5  | 189                               | 90             | 190                            | 91             |
| SDAN 5020V-5   | 232                               | 109            | 233                            | 110            |
| SDAN 5020VA-5  | 232                               | 109            | 233                            | 110            |
| SDAN 5025V-4   | 235                               | 108            | 237                            | 108            |
| SDAN 5025VA-4  | 235                               | 108            | 237                            | 108            |
| SDAN 5030V-4   | 265                               | 128            | 266                            | 128            |
| SDAN 5030VA-4  | 265                               | 128            | 267                            | 128            |
| SDAN 5040V-3   | 268                               | 126            | 270                            | 126            |
| SDAN 5040VA-3  | 269                               | 126            | 270                            | 126            |
| SDAN 5510VX-4  | 115                               | 52             | 116                            | 53             |
| SDAN 5510VAX-4 | 115                               | 52             | 116                            | 53             |
| SDAN 5512VX-4  | 134                               | 60             | 135                            | 60             |
| SDAN 5512VAX-4 | 134                               | 60             | 135                            | 60             |
| SDAN 5516VX-4  | 157                               | 74             | 158                            | 75             |
| SDAN 5516VAX-4 | 157                               | 74             | 158                            | 75             |
| SDAN 5520VX-4  | 192                               | 89             | 193                            | 90             |
| SDAN 5520VAX-4 | 192                               | 89             | 193                            | 90             |
| SDAN 6310VX-4  | 115                               | 52             | 116                            | 53             |
| SDAN 6312VX-4  | 135                               | 61             | 143                            | 64             |
| SDAN 6316VX-4  | 158                               | 75             | 165                            | 79             |
| SDAN 6320VX-4  | 193                               | 90             | 200                            | 94             |
| SDAN 6325VX-4  | 237                               | 109            | 244                            | 113            |
| SDAN 6330VX-4  | 266                               | 128            | 273                            | 132            |
| SDAN 6340VX-3  | 269                               | 126            | 276                            | 130            |



Unit: mm

| Model No.   | SDA-V_TT<br>(with thin film seal) |                | SDA-V_CC<br>(with canvas seal) |                |
|-------------|-----------------------------------|----------------|--------------------------------|----------------|
|             | L <sub>1</sub>                    | B <sub>1</sub> | L <sub>1</sub>                 | B <sub>1</sub> |
| SDA1004VZ-4 | 24                                | 16             | —                              | —              |
| SDA1005VZ-4 | 28                                | 20             | —                              | —              |
| SDA1010VZ-3 | 37                                | 29             | —                              | —              |
| SDA1205VZ-3 | 25                                | 17             | —                              | —              |
| SDA1210VZ-2 | 29                                | 21             | —                              | —              |
| SDA1220VZ-2 | 47                                | 39             | —                              | —              |
| SDA1230VZ-2 | 65                                | 57             | —                              | —              |
| SDA1405V-4  | 30                                | 20             | 31                             | 21             |
| SDA1505V-3  | 25                                | 15             | 26                             | 16             |
| SDA1510V-3  | 38                                | 28             | 39                             | 29             |
| SDA1520V-4  | 46                                | 36             | 47                             | 37             |
| SDA1530V-4  | 65                                | 55             | 65                             | 55             |
| SDA1605V-3  | 25                                | 15             | 26                             | 16             |
| SDA1610V-3  | 39                                | 29             | 40                             | 30             |
| SDA1616V-3  | 56                                | 46             | 56                             | 46             |
| SDA2004V-4  | 27                                | 17             | 27                             | 17             |
| SDA2005V-3  | 27                                | 17             | 27                             | 17             |
| SDA2006V-4  | 35                                | 25             | 36                             | 26             |
| SDA2010V-3  | 40                                | 30             | 41                             | 31             |
| SDA2010V-6  | 40                                | 30             | 41                             | 31             |
| SDA2020V-3  | 67                                | 57             | 68                             | 58             |
| SDA2020V-6  | 67                                | 57             | 68                             | 58             |
| SDA2030V-2  | 66                                | 56             | 67                             | 57             |
| SDA2040V-2  | 84                                | 74             | 85                             | 75             |
| SDA2505V-3  | 27                                | 17             | 27                             | 17             |
| SDA2510V-3  | 40                                | 30             | 41                             | 31             |
| SDA2520V-3  | 67                                | 57             | 68                             | 58             |
| SDA2525V-3  | 82                                | 72             | 82                             | 72             |
| SDA2530V-2  | 66                                | 56             | 66                             | 56             |
| SDA2530V-4  | 66                                | 56             | 66                             | 56             |
| SDA2550V-2  | 102                               | 92             | 103                            | 93             |
| SDA2806V-5  | 42                                | 30             | 43                             | 31             |
| SDA3110V-5  | 65                                | 50             | 66                             | 51             |
| SDA3112V-5  | 74                                | 59             | 75                             | 60             |
| SDA3116V-5  | 93                                | 78             | 94                             | 79             |

Unit: mm

| Model No.    | SDA-V_TT<br>(with thin film seal) |                | SDA-V_CC<br>(with canvas seal) |                |
|--------------|-----------------------------------|----------------|--------------------------------|----------------|
|              | L <sub>1</sub>                    | B <sub>1</sub> | L <sub>1</sub>                 | B <sub>1</sub> |
| SDA3120V-5   | 112                               | 97             | 113                            | 98             |
| SDA3132V-2   | 73                                | 58             | 74                             | 59             |
| SDA3205V-4   | 32                                | 20             | 32                             | 20             |
| SDA3206V-5   | 42                                | 30             | 43                             | 31             |
| SDA3208V-5   | 52                                | 40             | 52                             | 40             |
| SDA3210V-5   | 61                                | 49             | 62                             | 50             |
| SDA3210VA-5  | 65                                | 50             | 66                             | 51             |
| SDA3212VA-5  | 74                                | 59             | 76                             | 61             |
| SDA3216VA-5  | 93                                | 78             | 94                             | 79             |
| SDA3220VA-5  | 112                               | 97             | 113                            | 98             |
| SDA3232VA-2  | 73                                | 58             | 75                             | 60             |
| SDA3610V-5   | 65                                | 50             | 66                             | 51             |
| SDA3612V-5   | 74                                | 59             | 75                             | 60             |
| SDA3616V-5   | 93                                | 78             | 94                             | 79             |
| SDA3620V-5   | 112                               | 97             | 113                            | 98             |
| SDA3636V-2   | 81                                | 66             | 83                             | 68             |
| SDA3810V-5   | 65                                | 50             | 66                             | 51             |
| SDA3812V-5   | 74                                | 59             | 75                             | 60             |
| SDA3815V-5   | 88                                | 73             | 89                             | 74             |
| SDA3816V-5   | 93                                | 78             | 94                             | 79             |
| SDA3820V-5   | 112                               | 97             | 113                            | 98             |
| SDA3825V-4   | 111                               | 96             | 112                            | 97             |
| SDA3830V-3   | 100                               | 85             | 101                            | 86             |
| SDA3840V-2   | 87                                | 72             | 89                             | 74             |
| SDA4008VZ-5  | 55                                | 41             | 55                             | 41             |
| SDA4010VA-5  | 65                                | 50             | 66                             | 51             |
| SDA4012VA-5  | 74                                | 59             | 76                             | 61             |
| SDA4015VA-5  | 88                                | 74             | 90                             | 74             |
| SDA4016VA-5  | 93                                | 78             | 94                             | 79             |
| SDA4020VA-5  | 112                               | 97             | 113                            | 98             |
| SDA4020VA-10 | 112                               | 97             | 113                            | 98             |
| SDA4025VA-4  | 112                               | 97             | 113                            | 98             |
| SDA4030VA-3  | 101                               | 86             | 102                            | 87             |
| SDA4030VA-6  | 101                               | 86             | 102                            | 87             |
| SDA4040VA-2  | 88                                | 73             | 89                             | 74             |

## Options

## Dimensions of Each Model with an Option Attached

Unit: mm

Unit: mm

| Model No.    | SDA-V_TT<br>(with thin film seal) |                | SDA-V_CC<br>(with canvas seal) |                |
|--------------|-----------------------------------|----------------|--------------------------------|----------------|
|              | L <sub>1</sub>                    | B <sub>1</sub> | L <sub>1</sub>                 | B <sub>1</sub> |
| SDA4040VA-4  | 88                                | 73             | 89                             | 74             |
| SDA4510V-5   | 65                                | 48             | 66                             | 49             |
| SDA4510VA-5  | 65                                | 48             | 66                             | 49             |
| SDA4512V-5   | 74                                | 57             | 75                             | 58             |
| SDA4512VA-5  | 74                                | 57             | 76                             | 59             |
| SDA4516V-5   | 93                                | 76             | 94                             | 77             |
| SDA4516VA-5  | 93                                | 76             | 94                             | 77             |
| SDA4520V-5   | 112                               | 95             | 113                            | 96             |
| SDA4520VA-5  | 112                               | 95             | 113                            | 96             |
| SDA4520VA-10 | 112                               | 95             | 113                            | 96             |
| SDA4525V-4   | 110                               | 93             | 112                            | 95             |
| SDA4525VA-4  | 110                               | 93             | 112                            | 95             |
| SDA4530V-4   | 130                               | 113            | 132                            | 115            |
| SDA4530VA-4  | 131                               | 114            | 132                            | 115            |
| SDA4540V-3   | 129                               | 112            | 130                            | 113            |
| SDA4540VA-3  | 129                               | 112            | 130                            | 113            |
| SDA5010V-5   | 65                                | 48             | 66                             | 49             |
| SDA5010VA-5  | 65                                | 48             | 66                             | 49             |
| SDA5012V-5   | 74                                | 57             | 75                             | 58             |

| Model No.    | SDA-V_TT<br>(with thin film seal) |                | SDA-V_CC<br>(with canvas seal) |                |
|--------------|-----------------------------------|----------------|--------------------------------|----------------|
|              | L <sub>1</sub>                    | B <sub>1</sub> | L <sub>1</sub>                 | B <sub>1</sub> |
| SDA5012VA-5  | 74                                | 57             | 76                             | 59             |
| SDA5016V-5   | 93                                | 76             | 94                             | 77             |
| SDA5016VA-5  | 93                                | 76             | 94                             | 77             |
| SDA5020V-5   | 112                               | 95             | 113                            | 96             |
| SDA5020V-10  | 112                               | 95             | 113                            | 96             |
| SDA5020VA-5  | 112                               | 95             | 113                            | 96             |
| SDA5020VA-10 | 112                               | 95             | 113                            | 96             |
| SDA5025V-4   | 110                               | 93             | 112                            | 95             |
| SDA5025VA-4  | 110                               | 93             | 112                            | 95             |
| SDA5025VA-8  | 110                               | 93             | 112                            | 95             |
| SDA5030V-4   | 130                               | 113            | 131                            | 114            |
| SDA5030VA-4  | 130                               | 113            | 132                            | 115            |
| SDA5030VA-8  | 130                               | 113            | 132                            | 115            |
| SDA5040V-3   | 128                               | 111            | 130                            | 113            |
| SDA5040VA-3  | 129                               | 112            | 130                            | 113            |
| SDA5040VA-6  | 129                               | 112            | 130                            | 113            |
| SDA5050V-2   | 107                               | 90             | 108                            | 91             |
| SDA5050VA-2  | 107                               | 90             | 108                            | 91             |


Model number coding

SDA2505V-3 CC G0 +1000L C5

With canvas seal

## Specifications of the Bellows

Bellows are available as a contamination protection accessory. Use this specification sheet.



### Specifications of the Bellows

#### Supported Ball Screw models:

#### Dimensions of the Bellows

Stroke: ( ) mm MAX: ( ) mm MIN: ( ) mm

Permissible outer diameter: (φ OD ) Desired inner diameter: (φ ID )

#### How It Is Used

Installation direction: (horizontal, vertical, slant) Speed: ( ) mm/sec. mm/min.

Motion: (reciprocation, vibration)

#### Conditions

Resistance to oil and water: (necessary, unnecessary) Oil name ( )

Chemical resistance: Name ( ) × ( ) %

Location: (indoor, outdoor)

#### Remarks:

Number of Units To Be Manufactured:

## Model Number Coding

The model number configuration for ball screws differs depending on the type. Table 1 Refer to the corresponding configuration example shown in Table 3.

THK can also provide shaft end shapes matched to support units. These can also be denoted in the symbols, which should be used for this purpose.

### [Precision ball screw types and sample model number configurations]

Table 1

|                   | Model No.   |                    | Shaft end shape                         | Model number coding |
|-------------------|---|--------------------|---|---------------------|
| Precision         | SBN-V, SBK, SDAN-V, SDA-V, HBN-V/HBN-K/HBN-KA/HBN, SBKH, BIF-V, BNFN-V/BNFN, MDK, MBF, BNF-V/BNF, DIK, DKN, BLW, DK, WHF, BLK, WGF, BNT |                    | Fixed Side : H, J<br>Supported Side : K | [1]                 |
|                   | Unfinished Shaft Ends A   | MBF, MDK, BNF, BIF |   | [2]                 |
|                   | Unfinished Shaft Ends B   | BNF, BIF           |   |                     |
|                   | Finished Shaft Ends   | BNK                | Y                                       | [3]                 |
|                   | Rotary Ball Screw   | BLR, DIR           | Fixed Side : H, J<br>Supported Side : K | [4]                 |
| Ball Screw/Spline | BNS-V, BNS-A, BNS, NS-V, NS-A, NS   | —                  | [5]                                     |                     |

### [Rolled ball screw types and sample model number configurations]

Table 2

|        | Model No.   |                                     | Shaft end shape                         | Model number coding |
|--------|---|-------------------------------------|---|---------------------|
| Rolled | Ball screw nut and screw shaft combination products | JPF, BTK-V, MTF, BLK, WTF, CNF, BNT | Fixed Side : H, J<br>Supported Side : K | [6]                 |
|        | Rotary Ball Screw                                   | BLR                                 |   | [7]                 |
|        | Standalone screw shafts                             | TS                                  |   |                     |
|        | Standalone ball screw nuts                          | BTK-V, BLK, WTF, CNF, BNT, BLR      | —                                       | [8]                 |


### [Support unit, nut bracket and lock nut types and sample model number configurations]

Table 3

|                      | Model No.              |  | Shaft end shape | Model number coding |
|----------------------|------------------------|--|-----------------|---------------------|
| Support Unit         | EK, BK, FK, EF, BF, FF |  | —               | [9]                 |
| Nut brackets for BNK | MC                     |  | —               |                     |
| Lock Nut             | RN                     |  | —               |                     |

### [1 Precision Ball Screw]

- Models SBN-V, SBK, SDAN-V, SDA-V, HBN-V/HBN-K/HBN-KA/HBN, SBKH, BIF-V, BNFN-V/BNFN, MDK, MBF, BNF-V/BNF, DIK, DKN, BLW, DK, WHF, BLK, WGF and BNT



(\*1) See **A15-322** to **A15-327**.  
(\*2) (\*3) (\*4) See **A15-334**, **A15-335**.

Note) The ball nut flange faces the fixed side unless otherwise specified.  
If desiring the flange to face the supported side, add symbol G in the end of the Ball Screw model number when placing an order.

### [2 Precision Ball Screw Unfinished Shaft Ends]

- Models BIF, MDK, MBF and BNF

**BIF2505-5RRG0+720LC5A**

Unfinished shaft ends code (A or B)

**[3 Precision Ball Screw Finished Shaft Ends]**

- Model BNK

**BNK2010-2.5RRG2+699LC7Y**

Finished shaft ends code

Refer to **A15-140** for the corresponding model number.

**[4 Rotary Ball Screw]**

- Models BLR and DIR

**BLR2020-3.6 K UU G1 +1000L C5**

Model No.

Flange orientation  
symbol

Symbol for clearance  
in the axial direction

Symbol for  
support bearing seal

Overall screw shaft  
length (in mm)

Accuracy symbol

**[5 Ball Screw/Spline]**

- Models BNS-V, BNS-A, BNS, NS-V, NS-A, and NS

**BNS2525 +600L C5**

Model No.


Overall shaft length  
(in mm)

Accuracy symbol

### [6 Rolled Ball Screw]

#### ● Models BTK-V, MTF, BLK, WTF, CNF and BNT (Rolled)

- Combination of the Ball Screw Nut and the Screw Shaft




Note) The ball nut flange faces the fixed side unless otherwise specified.  
If desiring the flange to face the supported side, add symbol G at the end of the ball screw model number when placing an order.

### [6 Rolled Ball Screw]


#### ● Model JPF

- Rolled Ball Screw model JPF



### [7 Rolled Rotary Ball Screw]

#### ● Model BLR (Rolled)



Note) For clearance in the axial direction, see [A15-19](#).



**[8 Standalone rolled shafts/nuts]**

- Models BTK-V, BLK/WTF, CNF, BNT(Rolled), BLR(Rolled) and TS

Rolled shaft only

**TS 14 05 +500L C7**

Lead (in mm)

Screw shaft outer diameter (in mm)

Accuracy symbol (see page **A15-12**) (no symbol for class C10)

Overall screw shaft length (in mm)

Nut only

**BTK1405V-2.6 ZZ**

Model No.

Seal symbol  
no symbol: without seal  
ZZ: brush seal attached to both ends of the ball screw nut (see **A15-334**)

Symbol for rolled ball screw shaft

**[9 Support units, nut brackets and lock nuts]**

- Models EK, BK, FK, EF, BF, FF, MC and RN

**EK12**

Model No.

**[10 Ball screw options, W wiper rings and QZ lubricators]**

**BIF2505V-5 QZ WW G0 +1000L C5**

With QZ Lubricator

With wiper ring W

(\*) See **A15-344**.**Notes on Ordering****[Options]**

The details of the product options differ according to the model number. Check before ordering. See **A15-333**.

**[Other notes on specifications]**

Contact THK separately for information on the specifications below.

- Shaft end shape (for recommended shaft end shapes, indicate the symbol).
- Surface Treatment (see **B0-20**)
- Grease used
- Nipple mounting

## Precautions on Use

## Ball Screw

### [Handling]

- (1) Please use at least two people to move any product weighing 20 kg or more, or use a dolly or another conveyance. Doing so may cause injury or damage.
- (2) Do not disassemble the parts. This will result in loss of functionality.
- (3) Tilting the Ball Screw shaft and the Ball Screw nut may cause them to fall by their own weight.
- (4) Take care not to drop or strike the Ball Screw. Failure to do so could cause injury or product damage. Giving an impact to it could also cause damage to its function even if the product looks intact.
- (5) When assembling, do not remove the Ball Screw nut from the Ball Screw shaft.
- (6) When handling the product, wear protective gloves, safety shoes, etc., as necessary to ensure safety.

### [Precautions on Use]

- (1) Prevent foreign material, such as cutting chips or coolant, from entering the product. Failure to do so may cause damage.
- (2) If the product is used in an environment where cutting chips, coolant, corrosive solvents, water, etc., may enter the product, use bellows, covers, etc., to prevent them from entering the product.
- (3) Do not use the product at temperature of 80°C or higher. Except for the heat-resistant models, exposure to higher temperatures may cause the resin/rubber parts to deform/be damaged.
- (4) If foreign material such as cutting chips adheres to the product, replenish the lubricant after cleaning the product.
- (5) Micro-oscillation makes it difficult for oil film to form on the raceway in contact with the rolling element, and may lead to fretting. Accordingly, use grease offering excellent fretting toughness. It is also recommended that the Ball Screw nut be turned once or so on a regular basis to make sure oil film is formed between the raceway and rolling element.
- (6) When using the return-pipe or return-piece type ball screw in a horizontal orientation, there is a difference in torque on the outbound and inbound cycle depending on the mounting orientation of the circulation part (return pipe or return piece). To use the product with a consistent torque, we recommend designing the product with the mounting orientation of the circulation part facing downwards.
- (7) Do not use undue force when fitting parts (pin, key, etc.) to the product. This may generate pressure marks on the raceway, leading to loss of functionality.
- (8) If an offset or skewing occurs with the Ball Screw shaft support and the Ball Screw nut, it may substantially shorten the service life. Pay much attention to components to be mounted and to the mounting accuracy.
- (9) If any of the rolling elements falls from the Ball Screw nut, contact THK instead of using the product.
- (10) When using this product with a vertical orientation, take preventive measures such as adding a safety mechanism to prevent falls. The own weight of the Ball Screw nut may cause it to fall.
- (11) Do not use this product beyond its permissible rotational speed. Doing so may cause accidents or component damage. Be sure to use the product within the specification range designated by THK.
- (12) Do not cause the Ball Screw nut to overshoot. The ball may drop, circulating parts may be damaged, raceway in contact with the ball may develop pressure marks, etc., resulting in malfunction. Continuing to use the product in this condition may lead to premature wear or damage to circulating parts.

## Precautions on Use

- (13) Use the Ball Screw by providing a LM Guide, Ball Spline or other guide element. Otherwise, the Ball Screw may be damaged.
- (14) Insufficient rigidity or accuracy of mounting members causes the bearing load to concentrate on one point and the bearing performance will drop significantly. Accordingly, give sufficient consideration to the rigidity/accuracy of the housing and base and strength of the fixing bolts.

### [Lubrication]

- (1) Thoroughly wipe off anti-rust oil and feed lubricant before using the product.
- (2) Do not mix different lubricants. Mixing greases using the same type of thickening agent may still cause adverse interaction between the two greases if they use different additives, etc.
- (3) When using the product in locations exposed to constant vibrations or in special environments such as clean rooms, vacuum and low/high temperature, use the grease appropriate for the specification/environment.
- (4) When lubricating a product having no grease nipple or lubrication hole, apply grease directly on the raceway and stroke the product several times to let the grease spread inside.
- (5) The consistency of grease changes according to the temperature. Take note that the torque of the Ball Screw also changes as the consistency of grease changes.
- (6) After lubrication, the rotational torque of the Ball Screw may increase due to the agitation resistance of grease. Be sure to perform a break-in to let the grease spread fully, before operating the machine.
- (7) Excess grease may scatter immediately after lubrication, so wipe off scattered grease as necessary.
- (8) The properties of grease deteriorate and its lubrication performance drops over time, so grease must be checked and added properly according to the use frequency of the machine.
- (9) Although the lubrication interval may vary according to operating conditions and the service environment, lubrication should be performed approximately every 100 km in travel distance (three to six months). Set the final lubrication interval/amount based on the actual machine.
- (10) Depending on the mounting orientation and access position, lubricant may not spread fully and poor lubrication may occur. Give full consideration to these factors in the design stage.
- (11) When using a Ball Screw, it is necessary to provide effective lubrication. Using the product without lubrication may increase wear of the rolling elements or shorten the service life. Table1 (B15-108) shows a guideline for the feed amount of oil.

### [Storage]

When storing the Ball Screw, enclose it in a package designated by THK and store it in a room in a horizontal orientation while avoiding high temperature, low temperature and high humidity. After the product has been in storage for an extended period of time, lubricant inside may have deteriorated, so add new lubricant before use.

### [Disposal]

Dispose of the product properly as industrial waste.

# Precautions on Using Options for the Ball Screw

## QZ Lubricator for the Ball Screw

---

For details regarding the QZ Lubricator, see **A15-342**.

### [Precaution on Selection]

Make sure the stroke length exceeds the total length of the screw shaft with the QZ Lubricator attached.

### [Handling]

Take care not to drop or strike the product, which could result in injury or damage.


Keep air holes clear of grease or other obstructions.

The QZ Lubricator lubricates the raceway only, so it must be used in combination with regular greasing or oil lubrication.

In models equipped with the QZ Lubricator, raceways are provided with the minimum required level of lubrication. Please note: Use of the product in a vertical position, or other usage conditions, may cause lubricant to drip from the ball screw shaft.

### [Service environment]

Be sure the service temperature of this product is between  $-10$  to  $50^{\circ}\text{C}$ , and do not clean the product by immersing it in an organic solvent or white kerosene, or leave it unpacked.



# Ball Screw

THK General Catalog

# Ball Screw

THK General Catalog

## B Support Book

|   |         |   |          |
|---|---------|---|----------|
| <b>Features and Types</b> .....   | B 15-6  | <b>Examples of Selecting a Ball Screw</b> .....                 | B 15-69  |
| Features of the Ball Screw .....  | B 15-6  | • High-speed Transfer Equipment (Horizontal Use) ..             | B 15-69  |
| • Driving Torque One Third of the Sliding Screw ..                        | B 15-6  | • Vertical Conveyance System .....                              | B 15-83  |
| • Examples of Calculating Driving Torque .....                            | B 15-8  | <b>Options</b> .....  | B 15-95  |
| • Ensuring High Accuracy .....  | B 15-9  | Contaminator Protection .....                                   | B 15-96  |
| • Capable of Micro Feeding .....  | B 15-10 | Lubrication .....   | B 15-97  |
| • High Rigidity without Backlash .....                                    | B 15-11 | Corrosion Resistance (Surface Treatment, etc.) ..               | B 15-97  |
| • Capable of Fast Feed .....  | B 15-12 | Contamination Protection Seal for Ball Screws ..                | B 15-98  |
| Overview of THK Ball Screws .....   | B 15-14 | Wiper Ring W .....  | B 15-99  |
| <b>Point of Selection</b> .....   | B 15-16 | Canvas seal CC .....  | B 15-101 |
| Flowchart for Selecting a Ball Screw .....                                | B 15-16 | Dust Cover for Ball Screws .....                                | B 15-103 |
| Accuracy of the Ball Screw .....  | B 15-19 | QZ Lubricator .....   | B 15-104 |
| • Lead Angle Accuracy .....   | B 15-19 | <b>Mounting Procedure and Maintenance</b> ..                    | B 15-106 |
| • Accuracy of the Mounting Surface .....                                  | B 15-22 | Mounting Procedure .....  | B 15-106 |
| • Axial Clearance .....   | B 15-27 | • Installing the Support Unit .....                             | B 15-106 |
| • Preload .....   | B 15-28 | • Installation onto the Table and the Base ..                   | B 15-106 |
| • Example of calculating the preload torque .....                         | B 15-31 | • Checking the Accuracy and Fully Fastening the Support Unit .. | B 15-107 |
| Selecting a Screw Shaft .....   | B 15-32 | • Connection with the Motor .....                               | B 15-107 |
| • Maximum Manufacturing Length of the Screw Shaft ..                      | B 15-32 | Maintenance Method .....  | B 15-108 |
| • Combinations of Shaft Diameter and Lead for the Precision Ball Screw .. | B 15-34 | • Amount of Lubricant .....                                     | B 15-108 |
| • Combinations of Shaft Diameter and Lead for the Rolled Ball Screw ..    | B 15-35 | <b>Model No.</b> .....  | B 15-109 |
| Method for Mounting the Ball Screw Shaft ..                               | B 15-36 | • Model Number Coding .....                                     | B 15-109 |
| Permissible Axial Load .....  | B 15-38 | • Notes on Ordering .....                                       | B 15-113 |
| Permissible Rotational Speed .....  | B 15-40 | <b>Precautions on Use</b> .....                                 | B 15-114 |
| Selecting a Nut .....   | B 15-43 | Precautions on Using Options for the Ball Screw ..              | B 15-116 |
| • Types of Nuts .....   | B 15-43 | • QZ Lubricator for the Ball Screw .....                        | B 15-116 |
| Selecting a Model Number .....  | B 15-46 |   |          |
| • Calculating the Axial Load .....  | B 15-46 |   |          |
| • Static Safety Factor .....  | B 15-47 |   |          |
| • Studying the Service Life .....   | B 15-48 |   |          |
| Studying the Rigidity .....   | B 15-51 |   |          |
| • Axial Rigidity of the Feed Screw System ..                              | B 15-51 |   |          |
| Studying the Positioning Accuracy .....                                   | B 15-55 |   |          |
| • Causes of Error in the Positioning Accuracy ..                          | B 15-55 |   |          |
| • Studying the Lead Angle Accuracy .....                                  | B 15-55 |   |          |
| • Studying the Axial Clearance .....                                      | B 15-55 |   |          |
| • Studying the Axial Clearance of the Feed Screw System ..                | B 15-57 |   |          |
| • Example of considering the rigidity of a feed screw system ..           | B 15-57 |   |          |
| • Studying the Thermal Displacement through Heat Generation ..            | B 15-59 |   |          |
| • Studying the Orientation Change during Traveling ..                     | B 15-60 |   |          |
| Studying the Rotational Torque .....                                      | B 15-61 |   |          |
| • Frictional Torque Due to an External Load ..                            | B 15-61 |   |          |
| • Torque Due to a Preload on the Ball Screw ..                            | B 15-62 |   |          |
| • Torque Required for Acceleration .....                                  | B 15-63 |   |          |
| • Investigating the Terminal Strength of Ball Screw Shafts ..             | B 15-64 |   |          |
| Studying the Driving Motor .....  | B 15-66 |   |          |
| • When Using a Servomotor .....   | B 15-66 |   |          |
| • When Using a Stepping Motor (Pulse Motor) ..                            | B 15-68 |   |          |

## **A** Product Descriptions (Separate)

|   |        |
|---|--------|
| Overview of THK Ball Screws.....  | A15-6  |
| <b>Point of Selection</b> .....   | A15-8  |
| Flowchart for Selecting a Ball Screw .....                                  | A15-8  |
| Accuracy of the Ball Screw .....  | A15-11 |
| • Lead Angle Accuracy .....   | A15-11 |
| • Accuracy of the Mounting Surface .....                                    | A15-14 |
| • Axial Clearance .....   | A15-19 |
| • Preload .....   | A15-20 |
| Selecting a Screw Shaft .....   | A15-24 |
| • Maximum Manufacturing Length of the Screw Shaft ..                        | A15-24 |
| • Combinations of Shaft Diameter and Lead for the Precision Ball Screw ..   | A15-26 |
| • Combinations of Shaft Diameter and Lead for the Rolled Ball Screw ..      | A15-27 |
| Method for Mounting the Ball Screw Shaft ..                                 | A15-28 |
| Permissible Axial Load .....  | A15-30 |
| Permissible Rotational Speed .....  | A15-32 |
| Studying the Caged Technology .....   | A15-35 |
| • Types and Features .....  | A15-38 |
| Selecting a Nut .....   | A15-41 |
| • Types of Nuts .....   | A15-41 |
| Selecting a Model Number .....  | A15-46 |
| • Calculating the Axial Load .....  | A15-46 |
| • Static Safety Factor .....  | A15-47 |
| • Studying the Service Life .....   | A15-48 |
| Studying the Rigidity .....   | A15-51 |
| • Axial Rigidity of the Feed Screw System ..                                | A15-51 |
| Studying the Positioning Accuracy .....                                     | A15-55 |
| • Causes of Error in the Positioning Accuracy ..                            | A15-55 |
| • Studying the Lead Angle Accuracy .....                                    | A15-55 |
| • Studying the Axial Clearance .....  | A15-55 |
| • Studying the Axial Clearance of the Feed Screw System ..                  | A15-57 |
| • Studying the Thermal Displacement through Heat Generation ..              | A15-59 |
| • Studying the Orientation Change during Traveling ..                       | A15-60 |
| Studying the Rotational Torque .....  | A15-61 |
| • Frictional Torque Due to an External Load ..                              | A15-61 |
| • Torque Due to a Preload on the Ball Screw ..                              | A15-62 |
| • Torque Required for Acceleration .....                                    | A15-63 |
| • Investigating the Terminal Strength of Ball Screw Shafts ..               | A15-64 |
| Studying the Driving Motor .....  | A15-66 |
| • When Using a Servomotor .....   | A15-66 |
| • When Using a Stepping Motor (Pulse Motor) ..                              | A15-68 |
| <b>Features of Each Model</b> .....   | A15-69 |
| <b>Overview of THK Ball Screws</b> .....                                    | A15-70 |
| <b>Positioning, ISO 3408 compliant</b> .....                                | A15-72 |
| • Standard combinations of outer diameters and leads of the screw shafts .. | A15-74 |

## **Dimensional Drawing, Dimensional Table**

|                          |        |
|--------------------------|--------|
| Models SDAN-V .....      | A15-76 |
| Models SDA-V/SDA-VZ..... | A15-82 |
| Model EPB-V.....         | A15-94 |
| Model EBB-V .....        | A15-96 |

## **Positioning Ball Screw**.....

- Standard combinations of outer diameters and leads of the screw shafts ..

## **Dimensional Drawing, Dimensional Table**

|   |         |
|---|---------|
| Model SBN-V.....                            | A15-110 |
| Model SBK.....                              | A15-114 |
| Model BIF-V.....                            | A15-118 |
| Model BNFN-V .....                          | A15-124 |
| Model BNFN .....                            | A15-126 |
| Model DIK.....                              | A15-130 |
| Model DKN .....                             | A15-136 |
| Model BLW .....                             | A15-138 |
| BNK0401-3 Shaft diameter: 4; lead: 1...     | A15-140 |
| BNK0501-3 Shaft diameter: 5; lead: 1...     | A15-142 |
| BNK0601-3 Shaft diameter: 6; lead: 1...     | A15-144 |
| BNK0801-3 Shaft diameter: 8; lead: 1...     | A15-146 |
| BNK0802-3 Shaft diameter: 8; lead: 2...     | A15-148 |
| BNK0810-3 Shaft diameter: 8; lead: 10..     | A15-150 |
| BNK1002-3 Shaft diameter: 10; lead: 2...    | A15-152 |
| BNK1004-2.5 Shaft diameter: 10; lead: 4...  | A15-154 |
| BNK1010-1.5 Shaft diameter: 10; lead: 10..  | A15-156 |
| BNK1202-3 Shaft diameter: 12; lead: 2...    | A15-158 |
| BNK1205-2.5 Shaft diameter: 12; lead: 5...  | A15-160 |
| BNK1208-2.6 Shaft diameter: 12; lead: 8...  | A15-162 |
| BNK1402-3 Shaft diameter: 14; lead: 2...    | A15-164 |
| BNK1404-3 Shaft diameter: 14; lead: 4...    | A15-166 |
| BNK1408-2.5 Shaft diameter: 14; lead: 8...  | A15-168 |
| BNK1510-5.6 Shaft diameter: 15; lead: 10... | A15-170 |
| BNK1520-3 Shaft diameter: 15; lead: 20...   | A15-172 |
| BNK1616-3.6 Shaft diameter: 16; lead: 16... | A15-174 |
| BNK2010-2.5 Shaft diameter: 20; lead: 10... | A15-176 |
| BNK2020-3.6 Shaft diameter: 20; lead: 20... | A15-178 |
| BNK2520-3.6 Shaft diameter: 25; lead: 20... | A15-180 |
| Model MDK.....                              | A15-182 |
| Model MBF .....                             | A15-188 |
| Model BNF-V.....                            | A15-192 |
| Model BNF.....                              | A15-198 |
| Model DK .....                              | A15-202 |
| Model WHF.....                              | A15-210 |
| Model BLK .....                             | A15-212 |
| Model WGF .....                             | A15-214 |
| Model BNT.....                              | A15-216 |

|   |                 |
|---|-----------------|
| <b>High-Thrust Ball Screw</b> .....   | <b>A</b> 15-218 |
| • Standard combinations of outer diameters and leads of the screw shafts .. | <b>A</b> 15-220 |
| • Examples of Assembling Models HBN-V, HBN-K, HBN-KA, HBN, and SBKH .....   | <b>A</b> 15-222 |

### Dimensional Drawing, Dimensional Table

|                               |                 |
|-------------------------------|-----------------|
| Model HBN-V .....             | <b>A</b> 15-224 |
| Models HBN-K and HBN-KA ..... | <b>A</b> 15-226 |
| Model HBN .....               | <b>A</b> 15-232 |
| Model SBKH .....              | <b>A</b> 15-234 |

|                                   |                 |
|-----------------------------------|-----------------|
| <b>Transport Ball Screw</b> ..... | <b>A</b> 15-236 |
|-----------------------------------|-----------------|

- Standard combinations of outer diameters and leads of the screw shafts .. **A** 15-238

### Dimensional Drawing, Dimensional Table

|                   |                 |
|-------------------|-----------------|
| Model JPF .....   | <b>A</b> 15-240 |
| Model BTK-V ..... | <b>A</b> 15-242 |
| Model BNT .....   | <b>A</b> 15-244 |
| Model BLK .....   | <b>A</b> 15-246 |
| Model WTF .....   | <b>A</b> 15-248 |
| Model CNF .....   | <b>A</b> 15-250 |
| Model MTF .....   | <b>A</b> 15-252 |

|                                    |                 |
|------------------------------------|-----------------|
| <b>Rotary Nut Ball Screw</b> ..... | <b>A</b> 15-256 |
|------------------------------------|-----------------|

- Standard combinations of outer diameters and leads of the screw shafts .. **A** 15-258
  - Accuracy Standards .....
- |       |                 |
|-------|-----------------|
| ..... | <b>A</b> 15-260 |
|-------|-----------------|
- Example of Assembly .....
- |       |                 |
|-------|-----------------|
| ..... | <b>A</b> 15-265 |
|-------|-----------------|
- Action Patterns .....
- |       |                 |
|-------|-----------------|
| ..... | <b>A</b> 15-267 |
|-------|-----------------|
- Example of Assembly .....
- |       |                 |
|-------|-----------------|
| ..... | <b>A</b> 15-270 |
|-------|-----------------|
- Example of Use .....
- |       |                 |
|-------|-----------------|
| ..... | <b>A</b> 15-271 |
|-------|-----------------|
- Precautions on Use .....
- |       |                 |
|-------|-----------------|
| ..... | <b>A</b> 15-272 |
|-------|-----------------|
- Permissible Rotational Speeds for Rotary Ball Screws .. **A** 15-273

### Dimensional Drawing, Dimensional Table

|  |                 |
|--|-----------------|
| Model DIR .....                                      | <b>A</b> 15-274 |
| Model BLR .....                                      | <b>A</b> 15-276 |
| Model BNS-V .....                                    | <b>A</b> 15-280 |
| Model BNS-A .....                                    | <b>A</b> 15-282 |
| Model BNS .....                                      | <b>A</b> 15-284 |
| Model NS-V .....                                     | <b>A</b> 15-286 |
| Model NS-A .....                                     | <b>A</b> 15-288 |
| Model NS .....                                       | <b>A</b> 15-290 |
| • Ball Screw/Spine Permissible Rotational Speeds ..  | <b>A</b> 15-292 |
| • Maximum Manufacturing Length of the Screw Shaft .. | <b>A</b> 15-294 |

|                                     |                 |
|-------------------------------------|-----------------|
| <b>Ball Screw Peripherals</b> ..... | <b>A</b> 15-297 |
|-------------------------------------|-----------------|

### Support Unit

|  |                 |
|--|-----------------|
| <b>Models EK, BK, FK, EF, BF and FF</b> ....                           | <b>A</b> 15-298 |
| • Structure and Features .....   | <b>A</b> 15-298 |
| • Type .....   | <b>A</b> 15-300 |
| • Types of Support Units and Applicable Screw Shaft Outer Diameters .. | <b>A</b> 15-301 |
| • Model Numbers of Bearings and Characteristic Values ..               | <b>A</b> 15-302 |
| • Example of Installation .....  | <b>A</b> 15-303 |
| • Mounting Procedure .....   | <b>A</b> 15-304 |
| • Types of Recommended Shapes of the Shaft Ends ..                     | <b>A</b> 15-306 |

### Dimensional Drawing, Dimensional Table

|   |                 |
|---|-----------------|
| Model EK Square Type Support Unit on the Fixed Side ..  | <b>A</b> 15-308 |
| Model BK Square Type Support Unit on the Fixed Side ..  | <b>A</b> 15-310 |
| Model FK Round Type Support Unit on the Fixed Side ..   | <b>A</b> 15-312 |
| Model EF Square Type Support Unit on the Supported Side ..  | <b>A</b> 15-316 |
| Model BF Square Type Support Unit on the Supported Side ..  | <b>A</b> 15-318 |
| Model FF Round Type Support Unit on the Supported Side ..   | <b>A</b> 15-320 |
| Recommended Shapes of Shaft Ends - Shape H (H1, H2 and H3) (For Support Unit Models FK and EK) .. | <b>A</b> 15-322 |
| Recommended Shapes of Shaft Ends - Shape J (J1, J2 and J3) (For Support Unit Model BK) ..         | <b>A</b> 15-324 |
| Recommended Shapes of Shaft Ends - Shape K (For Support Unit Models FF, EF and BF) ....           | <b>A</b> 15-326 |

|                                     |                 |
|-------------------------------------|-----------------|
| <b>Nut Bracket (Model MC)</b> ..... | <b>A</b> 15-328 |
| • Structure and Features .....      | <b>A</b> 15-328 |
| • Type .....                        | <b>A</b> 15-328 |

### Dimensional Drawing, Dimensional Table

|                   |                 |
|-------------------|-----------------|
| Nut Bracket ..... | <b>A</b> 15-329 |
|-------------------|-----------------|

|                                  |                 |
|----------------------------------|-----------------|
| <b>Lock Nut (Model RN)</b> ..... | <b>A</b> 15-330 |
| • Structure and Features .....   | <b>A</b> 15-330 |
| • Type .....                     | <b>A</b> 15-330 |

### Dimensional Drawing, Dimensional Table

|                |                 |
|----------------|-----------------|
| Lock Nut ..... | <b>A</b> 15-331 |
|----------------|-----------------|

|  |                 |
|--|-----------------|
| <b>Options</b> .....   | <b>A</b> 15-333 |
| Contaminant Protection .....   | <b>A</b> 15-334 |
| Lubrication .....  | <b>A</b> 15-335 |
| Corrosion Resistance (Surface Treatment, etc.) ..                                  | <b>A</b> 15-335 |
| Contamination Protection Seal for Ball Screws ..                                   | <b>A</b> 15-336 |
| Wiper Ring W .....   | <b>A</b> 15-337 |
| Canvas seal CC .....   | <b>A</b> 15-339 |
| Dust Cover for Ball Screws .....   | <b>A</b> 15-341 |
| QZ Lubricator .....  | <b>A</b> 15-342 |
| Dimensions of Each Model with an Option Attached ..                                | <b>A</b> 15-344 |
| • Dimensions of the Ball Screw Nut Attached with Wiper Ring W and QZ Lubricator .. | <b>A</b> 15-344 |



- Ball Screw Nut Dimensions with Canvas Seal.... **A**15-353
- Specifications of the Bellows ..... **A**15-356

**Model No.** ..... **A**15-357

- Model Number Coding ..... **A**15-357
- Notes on Ordering..... **A**15-361

**Precautions on Use** ..... **A**15-362

Precautions on Using Options for the Ball Screw . **A**15-364

- QZ Lubricator for the Ball Screw ..... **A**15-364

## Features of the Ball Screw

### Driving Torque One Third of the Sliding Screw

With the Ball Screw, balls roll between the screw shaft and the nut to achieve high efficiency. Its required driving torque is only one third of the conventional sliding screw. (See Fig.1 and Fig.2.) As a result, it is capable of not only converting rotational motion to straight motion, but also converting straight motion to rotational motion.




Fig.1 Positive Efficiency (Rotational to Linear)




Fig.2 Reverse Efficiency (Linear to Rotational)

### [Calculating the Lead Angle]

$$\tan\beta = \frac{Ph}{\pi \cdot d_p}$$

- $\beta$  : Lead angle (°)  
 $d_p$  : Ball center-to-center diameter (mm)  
 $Ph$  : Feed screw lead (mm)

**[Relationship between Thrust and Torque]**

The torque or thrust generated when thrust or torque is applied is obtained from equations (1) to (3).

● **Driving Torque Required to Gain Thrust**

$$T = \frac{F_a \cdot Ph}{2\pi \cdot \eta_1} \dots\dots(1)$$

T : Driving torque (N·mm)

F<sub>a</sub> : Frictional resistance on the guide surface (N)

F<sub>a</sub> = μ × mg


μ : Frictional coefficient of the guide surface

g : Gravitational acceleration (9.8 m/s<sup>2</sup>)

m : Mass of the transferred object (kg)

Ph : Feed screw lead (mm)

η<sub>1</sub> : Positive efficiency of feed screw  
(see Fig.1 on **B15-6**)



● **Thrust Generated When Torque is Applied**

$$F_a = \frac{2\pi \cdot \eta_1 \cdot T}{Ph} \dots\dots(2)$$

F<sub>a</sub> : Thrust generated (N)

T : Driving torque (N·mm)

Ph : Feed screw lead (mm)

η<sub>1</sub> : Positive efficiency of feed screw  
(see Fig.1 on **B15-6**)

● **Torque Generated When Thrust is Applied**

$$T = \frac{Ph \cdot \eta_2 \cdot F_a}{2\pi} \dots\dots(3)$$

T : Torque generated (N·m)

F<sub>a</sub> : Thrust generated (N)

Ph : Feed screw lead (mm)


η<sub>2</sub> : Reverse efficiency of feed screw  
(see Fig.2 on **B15-6**)

## Examples of Calculating Driving Torque

When moving an object with a mass of 500 kg using a screw with an effective diameter of 33 mm and a lead length of 10 mm (lead angle:  $5^{\circ}30'$ ), the required torque is obtained as follows.

**Rolling guide ( $\mu=0.003$ )**

**Ball Screw (from  $\mu=0.003$ ,  $\eta=0.96$ )**



Frictional resistance on the guide surface


$$F_a = 0.003 \times 500 \times 9.8 = 14.7 \text{ N}$$

Driving torque

$$T = \frac{14.7 \times 10}{2\pi \times 0.96} = 24 \text{ N}\cdot\text{mm}$$

**Rolling guide ( $\mu=0.003$ )**

**Ball Screw (from  $\mu=0.2$ ,  $\eta=0.32$ )**



Frictional resistance on the guide surface

$$F_a = 0.003 \times 500 \times 9.8 = 14.7 \text{ N}$$

Driving torque

$$T = \frac{14.7 \times 10}{2\pi \times 0.32} = 73 \text{ N}\cdot\text{mm}$$

## Ensuring High Accuracy

The Ball Screw is ground with the highest-level facilities and equipment at a strictly temperature-controlled factory. Its accuracy is assured under a thorough quality control system that covers assembly to inspection.



Automatic lead-measuring machine using laser




Fig.3 Lead Accuracy Measurement

[Conditions]

Model No.: BIF3205-10RRG0+903LC2

Table1 Lead Accuracy Measurement Unit: mm

| Item                                 | Standard value | Actual measurement |
|--------------------------------------|----------------|--------------------|
| Directional target point             | 0              | —                  |
| Representative travel distance error | $\pm 0.011$    | -0.0012            |
| Fluctuation                          | 0.008          | 0.0017             |

## Capable of Micro Feeding

The Ball Screw requires a minimal starting torque due to its rolling motion, and does not cause a slip, which is inevitable with a sliding motion. Therefore, it is capable of an accurate micro feeding. Fig.4 shows a travel distance of the Ball Screw in one-pulse, 0.1- $\mu\text{m}$  feeding. (LM Guide is used for the guide surface.)




Fig.4 Data on Travel in 0.1- $\mu\text{m}$  Feeding

## High Rigidity without Backlash

Since the Ball Screw is capable of receiving a preload, the axial clearance can be reduced to below zero and the high rigidity is achieved because of the preload. In Fig.5, when an axial load is applied in the positive (+) direction, the table is displaced in the same (+) direction. When an axial load is provided in the reverse (-) direction, the table is displaced in the same (-) direction. Fig.6 shows the relationship between the axial load and the axial displacement. As indicated in Fig.6, as the direction of the axial load changes, the axial clearance occurs as a displacement. Additionally, when the Ball Screw is provided with a preload, it gains a higher rigidity and a smaller axial displacement than a zero clearance in the axial direction.




Fig.5




Fig.6 Axial Displacement in Relation to Axial Load

## Capable of Fast Feed

Since the Ball Screw is highly efficient and generates little heat, it is capable of a fast feed.

### [Example of High Speed]

Fig.7 shows a speed diagram for a large lead rolled Ball Screw operating at 2 m/s.

[Conditions]

| Item          | Description   |
|---------------|---|
| Sample        | Large Lead Rolled Ball Screw<br>WTF3060<br>(Shaft diameter: 30 mm; lead: 60 mm) |
| Maximum speed | 2 m/s<br>(Ball Screw rotational speed: 2,000 min <sup>-1</sup> )                |
| Guide surface | LM Guide model SR25W  |




Fig.7 Velocity diagram



## Features and Types

### Features of the Ball Screw

# Overview of THK Ball Screws

## Positioning Ball Screw

▲15-72

ISO 3408 compliant

## Positioning Ball Screw

▲15-102

Preload

Preload/  
No preload

Preload

Preload/  
No preload

No preload

### SDAN-V

Caged Ball

Double nut

High speed

Compact

### SDAN-VX

Double nut

High speed

Compact

### EPB-V

High speed

Compact

### SDA-V

Caged Ball

High speed

Various leads

Compact

### SDA-VZ

High speed

Various leads

Compact

### EBB-V

High speed

Compact

### SBN-V

Caged Ball

High speed

### SBK

Caged Ball

High speed

Large lead

### BIF-V

High speed

### BNFN-V

Double nut

High speed

### DIK

Compact

### DKN

Compact

Double nut

### BLW

Double nut

Large lead

### BNK

Standard to large lead

### MDK

### MBF

Miniature

### BNF-V

High speed

### DK

Compact

### WHF

High speed

Large lead

### BLK

### WGF


Large lead

### BNT

Flat nut

## Features and Types


### Overview of THK Ball Screws



## Flowchart for Selecting a Ball Screw


### [Ball Screw Selection Procedure]

When selecting a Ball Screw, it is necessary to make a selection while considering various parameters. The following is a flowchart for selecting a Ball Screw.



## Point of Selection

Flowchart for Selecting a Ball Screw



## [Conditions of the Ball Screw]

The following conditions are required when selecting a Ball Screw.

Transfer orientation (horizontal, vertical, etc.)  
 Transferred mass  $m$  (kg)  
 Table guide method (sliding, rolling)  
 Frictional coefficient of the guide surface  $\mu$  (—)  
 Guide surface resistance  $f$  (N)  
 External load in the axial direction  $F$  (N)  
 Desired service life time  $L_h$  (h)

Stroke length  $l_s$  (mm)  
 Operating speed  $V_{max}$  (m/s)  
 Acceleration time  $t_1$  (s)  
 Even speed time  $t_2$  (s)  
 Deceleration time  $t_3$  (s)

Acceleration  $\alpha = \frac{V_{max}}{t_1}$  (m/s<sup>2</sup>)

Acceleration distance  $l_1 = V_{max} \times t_1 \times 1000/2$  (mm)

Even speed distance  $l_2 = V_{max} \times t_2 \times 1000$  (mm)

Deceleration distance  $l_3 = V_{max} \times t_3 \times 1000/2$  (mm)

Number of reciprocations per minute  $n$  (min<sup>-1</sup>)

Positioning accuracy (mm)  
 Positioning accuracy repeatability (mm)  
 Backlash (mm)  
 Minimum feed amount  $s$  (mm/pulse)


Driving motor (AC servomotor, stepping motor, etc.)

The rated rotation speed of the motor  $N_{MO}$  (min<sup>-1</sup>)

Inertial moment of the motor  $J_M$  (kg·m<sup>2</sup>)

Motor resolution (pulse/rev)

Reduction ratio  $A$  (—)



Velocity diagram

# Accuracy of the Ball Screw

## Lead Angle Accuracy

The lead angle accuracy of the ball screw is controlled in accordance with the JIS standard JIS B 1192 (ISO 3408).

Accuracy grades C0 to C5 are defined in the linearity and the directional property, and C7 to C10 in the travel distance error in relation to 300 mm.




Fig.1 Terms on Lead Angle Accuracy

### [Actual Travel Distance]

An error in the travel distance measured with an actual Ball Screw.

### [Reference Travel Distance]

Generally, it is the same as nominal travel distance, but can be an intentionally corrected value of the nominal travel distance according to the intended use.

### [Target Value for Reference Travel Distance]

You may provide some tension in order to prevent the screw shaft from runout, or set the reference travel distance in “negative” or “positive” value in advance given the possible expansion/contraction from external load or temperature. In such cases, indicate a target value for the reference travel distance.

### [Representative Travel Distance]

It is a straight line representing the tendency in the actual travel distance, and obtained with the least squares method from the curve that indicates the actual travel distance.

### [Representative Travel Distance Error (in $\pm$ )]

Difference between the representative travel distance and the reference travel distance.

### [Fluctuation]

The maximum width of the actual travel distance between two straight lines drawn in parallel with the representative travel distance.

### [Fluctuation/300]

Indicates a fluctuation against a given thread length of 300 mm.

### [Fluctuation/2 $\pi$ ]

A fluctuation in one revolution of the screw shaft.

Table1 Lead Angle Accuracy (Permissible Value)

Unit:  $\mu\text{m}$ 

| Accuracy grades         |         | Precision Ball Screw                 |             |                                      |             |                                      |             |                                      |             |                                      |             | Rolled Ball Screw     |                       |                       |
|-------------------------|---------|--------------------------------------|-------------|--------------------------------------|-------------|--------------------------------------|-------------|--------------------------------------|-------------|--------------------------------------|-------------|-----------------------|-----------------------|-----------------------|
|                         |         | C0                                   |             | C1                                   |             | C2                                   |             | C3                                   |             | C5                                   |             | C7                    | C8                    | C10                   |
| Effective thread length |         | Representative travel distance error | Fluctuation | Representative travel distance error | Fluctuation | Representative travel distance error | Fluctuation | Representative travel distance error | Fluctuation | Representative travel distance error | Fluctuation | Travel distance error | Travel distance error | Travel distance error |
| Above                   | Or less |                                      |             |                                      |             |                                      |             |                                      |             |                                      |             |                       |                       |                       |
| —                       | 100     | 3                                    | 3           | 3.5                                  | 5           | 5                                    | 7           | 8                                    | 8           | 18                                   | 18          | ±50/<br>300 mm        | ±100/<br>300 mm       | ±210/<br>300 mm       |
| 100                     | 200     | 3.5                                  | 3           | 4.5                                  | 5           | 7                                    | 7           | 10                                   | 8           | 20                                   | 18          |                       |                       |                       |
| 200                     | 315     | 4                                    | 3.5         | 6                                    | 5           | 8                                    | 7           | 12                                   | 8           | 23                                   | 18          |                       |                       |                       |
| 315                     | 400     | 5                                    | 3.5         | 7                                    | 5           | 9                                    | 7           | 13                                   | 10          | 25                                   | 20          |                       |                       |                       |
| 400                     | 500     | 6                                    | 4           | 8                                    | 5           | 10                                   | 7           | 15                                   | 10          | 27                                   | 20          |                       |                       |                       |
| 500                     | 630     | 6                                    | 4           | 9                                    | 6           | 11                                   | 8           | 16                                   | 12          | 30                                   | 23          |                       |                       |                       |
| 630                     | 800     | 7                                    | 5           | 10                                   | 7           | 13                                   | 9           | 18                                   | 13          | 35                                   | 25          |                       |                       |                       |
| 800                     | 1000    | 8                                    | 6           | 11                                   | 8           | 15                                   | 10          | 21                                   | 15          | 40                                   | 27          |                       |                       |                       |
| 1000                    | 1250    | 9                                    | 6           | 13                                   | 9           | 18                                   | 11          | 24                                   | 16          | 46                                   | 30          |                       |                       |                       |
| 1250                    | 1600    | 11                                   | 7           | 15                                   | 10          | 21                                   | 13          | 29                                   | 18          | 54                                   | 35          |                       |                       |                       |
| 1600                    | 2000    | —                                    | —           | 18                                   | 11          | 25                                   | 15          | 35                                   | 21          | 65                                   | 40          |                       |                       |                       |
| 2000                    | 2500    | —                                    | —           | 22                                   | 13          | 30                                   | 18          | 41                                   | 24          | 77                                   | 46          |                       |                       |                       |
| 2500                    | 3150    | —                                    | —           | 26                                   | 15          | 36                                   | 21          | 50                                   | 29          | 93                                   | 54          |                       |                       |                       |
| 3150                    | 4000    | —                                    | —           | 30                                   | 18          | 44                                   | 25          | 60                                   | 35          | 115                                  | 65          |                       |                       |                       |
| 4000                    | 5000    | —                                    | —           | —                                    | —           | 52                                   | 30          | 72                                   | 41          | 140                                  | 77          |                       |                       |                       |
| 5000                    | 6300    | —                                    | —           | —                                    | —           | 65                                   | 36          | 90                                   | 50          | 170                                  | 93          |                       |                       |                       |
| 6300                    | 8000    | —                                    | —           | —                                    | —           | —                                    | —           | 110                                  | 60          | 210                                  | 115         |                       |                       |                       |
| 8000                    | 10000   | —                                    | —           | —                                    | —           | —                                    | —           | —                                    | —           | 260                                  | 140         |                       |                       |                       |

Note) Unit of effective thread length: mm

Table2 Fluctuation in Thread Length of 300 mm and in One Revolution (permissible value)

Unit:  $\mu\text{m}$ 

| Accuracy grades     | C0  | C1 | C2 | C3 | C5 | C7 | C8 | C10 |
|---------------------|-----|----|----|----|----|----|----|-----|
| Fluctuation/300     | 3.5 | 5  | 7  | 8  | 18 | —  | —  | —   |
| Fluctuation/ $2\pi$ | 3   | 4  | 5  | 6  | 8  | —  | —  | —   |

Table3 Types and Grades

| Type            | Grade             | Remarks       |
|-----------------|-------------------|---------------|
| For positioning | 0, 1, 3, 5        | ISO compliant |
| For transport   | 0, 1, 3, 5, 7, 10 |               |



## Point of Selection

## Accuracy of the Ball Screw

Example: When the lead of a Ball Screw manufactured is measured with a target value for the reference travel distance of  $-9 \mu\text{m}/500 \text{ mm}$ , the following data are obtained.

Table4 Measurement Data on Travel Distance Error

Unit: mm

|                             |         |         |         |         |
|-----------------------------|---------|---------|---------|---------|
| Command position (A)        | 0       | 50      | 100     | 150     |
| Travel distance (B)         | 0       | 49.998  | 100.001 | 149.996 |
| Travel distance error (A-B) | 0       | -0.002  | +0.001  | -0.004  |
| Command position (A)        | 200     | 250     | 300     | 350     |
| Travel distance (B)         | 199.995 | 249.993 | 299.989 | 349.985 |
| Travel distance error (A-B) | -0.005  | -0.007  | -0.011  | -0.015  |
| Command position (A)        | 400     | 450     | 500     |         |
| Travel distance (B)         | 399.983 | 449.981 | 499.984 |         |
| Travel distance error (A-B) | -0.017  | -0.019  | -0.016  |         |

The measurement data are expressed in a graph as shown in Fig.2.

The positioning error (A-B) is indicated as the actual travel distance while the straight line representing the tendency of the (A-B) graph refers to the representative travel distance.

The difference between the reference travel distance and the representative travel distance appears as the representative travel distance error.




Fig.2 Measurement Data on Travel Distance Error


[Measurements]

Representative travel distance error:  $-7 \mu\text{m}$

Fluctuation:  $8.8 \mu\text{m}$

## Accuracy of the Mounting Surface

The accuracy of the Ball Screw mounting surface complies with the JIS standard JIS B 1192 (ISO 3408).



Note) For the permissible overall radial runout of the outer diameter of the screw in relation to the screw shaft support axis, refer to JIS B 1192 (ISO 3408).

Fig.3 Accuracy of the Mounting Surface of the Ball Screw

### [Accuracy Standards for the Mounting Surface]


Table5 to Table9 show accuracy standards for the mounting surfaces of the precision Ball Screw.

Table5 Permissible Radial Runout of the Grooved Surface of the Screw in Relation to the Screw Shaft Support Axis and the Permissible Radial Runout of the Part-Mounting Surface  
Unit:  $\mu\text{m}$

| Screw shaft outer diameter (mm) |         | Runout (maximum) |    |    |    |    |    |
|---------------------------------|---------|------------------|----|----|----|----|----|
| Above                           | Or less | C0               | C1 | C2 | C3 | C5 | C7 |
| —                               | 8       | 3                | 5  | 7  | 8  | 10 | 14 |
| 8                               | 12      | 4                | 5  | 7  | 8  | 11 | 14 |
| 12                              | 20      | 4                | 6  | 8  | 9  | 12 | 14 |
| 20                              | 32      | 5                | 7  | 9  | 10 | 13 | 20 |
| 32                              | 50      | 6                | 8  | 10 | 12 | 15 | 20 |
| 50                              | 80      | 7                | 9  | 11 | 13 | 17 | 20 |
| 80                              | 100     | —                | 10 | 12 | 15 | 20 | 30 |

Note) The measurements on these items include the effect of the runout of the screw shaft diameter. Therefore, it is necessary to obtain the correction value from the overall runout of the screw shaft axis, using the ratio of the distance between the fulcrum and measurement point to the overall screw shaft length, and add the obtained value to the table above.

Example: model No. DIK2005-6RRGO+500LC5



$$E_1 = e + \Delta e$$

$e$  : Standard value in Table5(0.012)

$\Delta e$  : Correction value

$$\Delta e = \frac{L_1}{L} \times E_2$$

$$= \frac{80}{500} \times 0.06$$

$$= 0.01$$

$L$  : Overall screw shaft length

$L_1$  : Distance between the fulcrum and the measurement point

$E_2$  : Overall radial runout of the screw shaft axis (0.06)

$$E_1 = 0.012 + 0.01$$

$$= 0.022$$

Note) For the permissible overall radial runout of the outer diameter of the screw in relation to the screw shaft support axis, refer to JIS B 1192 (ISO 3408).

Table6 Permissible Radial Runout of the Support End Face in Relation to the Screw Shaft Support Axis

Unit:  $\mu\text{m}$ 

| Screw shaft outer diameter (mm) |         | Permissible radial runout (maximum) |    |    |    |    |    |
|---------------------------------|---------|-------------------------------------|----|----|----|----|----|
| Above                           | Or less | C0                                  | C1 | C2 | C3 | C5 | C7 |
| —                               | 8       | 2                                   | 3  | 3  | 4  | 5  | 7  |
| 8                               | 12      | 2                                   | 3  | 3  | 4  | 5  | 7  |
| 12                              | 20      | 2                                   | 3  | 3  | 4  | 5  | 7  |
| 20                              | 32      | 2                                   | 3  | 3  | 4  | 5  | 7  |
| 32                              | 50      | 2                                   | 3  | 3  | 4  | 5  | 8  |
| 50                              | 80      | 3                                   | 4  | 4  | 5  | 7  | 10 |
| 80                              | 100     | —                                   | 4  | 5  | 6  | 8  | 11 |

Table7 Permissible Radial Runout of the Flange Mounting Surface in Relation to the Screw Shaft Axis

Unit:  $\mu\text{m}$ 

| Nut diameter (mm) |         | Permissible radial runout (maximum) |    |    |    |    |    |
|-------------------|---------|-------------------------------------|----|----|----|----|----|
| Above             | Or less | C0                                  | C1 | C2 | C3 | C5 | C7 |
| —                 | 20      | 5                                   | 6  | 7  | 8  | 10 | 14 |
| 20                | 32      | 5                                   | 6  | 7  | 8  | 10 | 14 |
| 32                | 50      | 6                                   | 7  | 8  | 8  | 11 | 18 |
| 50                | 80      | 7                                   | 8  | 9  | 10 | 13 | 18 |
| 80                | 125     | 7                                   | 9  | 10 | 12 | 15 | 20 |
| 125               | 160     | 8                                   | 10 | 11 | 13 | 17 | 20 |
| 160               | 200     | —                                   | 11 | 12 | 14 | 18 | 25 |

Table8 Permissible Radial Runout of the Nut Circumference in Relation to the Screw Shaft Axis

Unit:  $\mu\text{m}$ 

| Nut diameter (mm) |         | Permissible radial runout |    |    |    |    |    |
|-------------------|---------|---------------------------|----|----|----|----|----|
| Above             | Or less | C0                        | C1 | C2 | C3 | C5 | C7 |
| —                 | 20      | 5                         | 6  | 7  | 9  | 12 | 20 |
| 20                | 32      | 6                         | 7  | 8  | 10 | 12 | 20 |
| 32                | 50      | 7                         | 8  | 10 | 12 | 15 | 30 |
| 50                | 80      | 8                         | 10 | 12 | 15 | 19 | 30 |
| 80                | 125     | 9                         | 12 | 16 | 20 | 27 | 40 |
| 125               | 160     | 10                        | 13 | 17 | 22 | 30 | 40 |
| 160               | 200     | —                         | 16 | 20 | 25 | 34 | 50 |

Table9 Permissible Parallelism of the Nut Circumference (Flat Mounting Surface) to the Screw Shaft Axis


Unit:  $\mu\text{m}$ 

| Mounting reference length (mm) |         | Permissible parallelism |    |    |    |    |    |
|--------------------------------|---------|-------------------------|----|----|----|----|----|
| Above                          | Or less | C0                      | C1 | C2 | C3 | C5 | C7 |
| —                              | 50      | 5                       | 6  | 7  | 8  | 10 | 17 |
| 50                             | 100     | 7                       | 8  | 9  | 10 | 13 | 17 |
| 100                            | 200     | —                       | 10 | 11 | 13 | 17 | 30 |

### [Method for Measuring Accuracy of the Mounting Surface]

#### ● Radial Runout of the Circumference of the Motor-mounting Shaft-end in Relation to the Bearing Journals of the Screw Shaft (see Table5 on [E15-23](#))


Support the end journal of the screw shaft on V blocks. Place a probe on the circumference of the motor-mounting shaft-end, and record the largest difference on the dial gauge as a measurement while rotating the screw shaft through one revolution.



Surface table


● **Radial Runout of the Circumference of the Raceway Threads in Relation to the Bearing Journals of the Screw Shaft (see Table5 on B15-23)**

Support the end journal of the screw shaft on V blocks. Place a probe on the circumference of the nut, and record the largest difference on the dial gauge as a measurement while rotating the screw shaft by one revolution without rotating the nut.




● **Radial Runout of the Support End Face in Relation to the Screw Shaft Axis Support (see Table6 on B15-24)**

Support the bearing journal portions of the screw shaft on V blocks. Place a probe on the screw shaft's supporting portion end, and record the largest difference on the dial gauge as a measurement while rotating the screw shaft through one revolution.




● **Radial Runout of the Flange Mounting Surface in Relation to the Screw Shaft Axis (see Table7 on B15-24)**

Support the thread of the screw shaft on V blocks near the nut. Place a probe on the flange end, and record the largest difference on the dial gauge as a measurement while simultaneously rotating the screw shaft and the nut through one revolution.




● **Radial Runout of the Nut Circumference in Relation to the Screw Shaft Axis (see Table 8 on B15-24)**

Support the thread of the screw shaft on V blocks near the nut. Place a probe on the circumference of the nut, and record the largest difference on the dial gauge as a measurement while rotating the nut through one revolution without rotating the screw shaft.




● **Parallelism of the Nut Circumference (Flat Mounting Surface) to the Screw Shaft Axis (see Table 9 on B15-24)**

Support the thread of the screw shaft on V blocks near the nut. Place a probe on the circumference of the nut (flat mounting surface), and record the largest difference on the dial gauge as a measurement while moving the dial gauge in parallel with the screw shaft.



● **Overall Radial Runout of the Screw Diameter Relative to the Shaft Support Axis**

Support the supporting portion of the screw shaft on V blocks. Place a probe on the circumference of the screw shaft, and record the largest difference on the dial gauge at several points in the axial directions as a measurement while rotating the screw shaft through one revolution.



Note) For the permissible overall radial runout of the outer diameter of the screw in relation to the screw shaft support axis, refer to JIS B 1192 (ISO 3408).

## Axial Clearance

### [Axial Clearance of the Precision Ball Screw]

Table10 shows the axial clearance of the precision Ball Screw. If the manufacturing length exceeds the value in Table11, the resultant clearance may partially be negative (preload applied).

The manufacturing limit lengths of the Ball Screws compliant with the DIN standard are provided in Table12. For the axial clearance of the Precision Caged Ball Screw, see **A15-76** to **A15-93**, **A15-110** to **A15-117**, **A15-224** to **A15-235**.

Table10 Axial Clearance of the Precision Ball Screw

Unit: mm

| Clearance symbol | G0        | GT         | G1        | G2        | G3        |
|------------------|-----------|------------|-----------|-----------|-----------|
| Axial Clearance  | 0 or less | 0 to 0.005 | 0 to 0.01 | 0 to 0.02 | 0 to 0.05 |

Table11 Maximum Manufacturing Length of Precision Ball Screws by Accuracy Grade

Unit: mm

| Screw shaft outer diameter | Clearance GT |      |       |      | Clearance G1 |      |       |      | Clearance G2 |      |      |      |      |      |  |
|----------------------------|--------------|------|-------|------|--------------|------|-------|------|--------------|------|------|------|------|------|--|
|                            | C0           | C1   | C2·C3 | C5   | C0           | C1   | C2·C3 | C5   | C0           | C1   | C2   | C3   | C5   | C7   |  |
| 4·6                        | 80           | 80   | 80    | 100  | 80           | 80   | 80    | 100  | 80           | 80   | 80   | 80   | 100  | 120  |  |
| 8                          | 230          | 250  | 250   | 200  | 230          | 250  | 250   | 250  | 230          | 250  | 250  | 250  | 300  | 300  |  |
| 10                         | 250          | 250  | 250   | 200  | 250          | 250  | 250   | 250  | 250          | 250  | 250  | 250  | 300  | 300  |  |
| 12·13                      | 440          | 500  | 500   | 400  | 440          | 500  | 500   | 500  | 440          | 500  | 630  | 680  | 600  | 500  |  |
| 14                         | 500          | 500  | 500   | 400  | 500          | 500  | 500   | 500  | 530          | 620  | 700  | 700  | 600  | 500  |  |
| 15                         | 500          | 500  | 500   | 400  | 500          | 500  | 500   | 500  | 570          | 670  | 700  | 700  | 600  | 500  |  |
| 16                         | 500          | 500  | 500   | 400  | 500          | 500  | 500   | 500  | 620          | 700  | 700  | 700  | 600  | 500  |  |
| 18                         | 720          | 800  | 800   | 700  | 720          | 800  | 800   | 700  | 720          | 840  | 1000 | 1000 | 1000 | 1000 |  |
| 20                         | 800          | 800  | 800   | 700  | 800          | 800  | 800   | 700  | 820          | 950  | 1000 | 1000 | 1000 | 1000 |  |
| 25                         | 800          | 800  | 800   | 700  | 800          | 800  | 800   | 700  | 1000         | 1000 | 1000 | 1000 | 1000 | 1000 |  |
| 28                         | 900          | 900  | 900   | 800  | 1100         | 1100 | 1100  | 900  | 1300         | 1400 | 1400 | 1400 | 1200 | 1200 |  |
| 30·32                      | 900          | 900  | 900   | 800  | 1100         | 1100 | 1100  | 900  | 1400         | 1400 | 1400 | 1400 | 1200 | 1200 |  |
| 36·40·45                   | 1000         | 1000 | 1000  | 800  | 1300         | 1300 | 1300  | 1000 | 2000         | 2000 | 2000 | 2000 | 1500 | 1500 |  |
| 50·55·63·70                | 1200         | 1200 | 1200  | 1000 | 1600         | 1600 | 1600  | 1300 | 2000         | 2500 | 2500 | 2500 | 2000 | 2000 |  |
| 80·100                     | —            | —    | —     | —    | 1800         | 1800 | 1800  | 1500 | 2000         | 4000 | 4000 | 4000 | 3000 | 3000 |  |

\* When manufacturing the Ball Screw of precision-grade accuracy C7 with clearance GT or G1, the resultant clearance is partially negative.

G0 clearance is not available for models HBN-V, HBN-K (KA), HBN, and SBKH.

Accuracy grade C7 is not available when manufacturing a miniature ball screw (screw shaft outer diameter  $\phi$ 14 mm or less) with a G0 clearance.

Table12 Manufacturing limit lengths of precision Ball Screws with axial clearances (DIN standard compliant Ball Screws)

Unit: mm

| Shaft diameter | Clearance GT |              | Clearance G1 |              | Clearance G2 |              |         |
|----------------|--------------|--------------|--------------|--------------|--------------|--------------|---------|
|                | C3, Cp3      | C5, Cp5, Ct5 | C3, Cp3      | C5, Cp5, Ct5 | C3, Cp3      | C5, Cp5, Ct5 | C7, Cp7 |
| 16             | 500          | 400          | 500          | 500          | 700          | 600          | 500     |
| 20, 25         | 800          | 700          | 800          | 700          | 1000         | 1000         | 1000    |
| 32             | 900          | 800          | 1100         | 900          | 1400         | 1200         | 1200    |
| 40             | 1000         | 800          | 1300         | 1000         | 2000         | 1500         | 1500    |
| 50, 63         | 1200         | 1000         | 1600         | 1300         | 2500         | 2000         | 2000    |

\* When manufacturing the Ball Screw of precision-grade accuracy C7 (Ct7) with clearance GT or G1, the resultant clearance is partially negative.

### [Axial Clearance of the Rolled Ball Screw]

Table13 shows axial clearance of the rolled Ball Screw.

Table13 Axial Clearance of the Rolled Ball Screw

Unit: mm

| Screw shaft outer diameter | Axial clearance (maximum) |
|----------------------------|---------------------------|
| 6 to 12                    | 0.05                      |
| 14 to 28                   | 0.1                       |
| 30 to 32                   | 0.14                      |
| 36 to 45                   | 0.17                      |
| 50                         | 0.2                       |

## Preload

A preload is provided in order to eliminate the axial clearance and minimize the displacement under an axial load.

When performing a highly accurate positioning, a preload is generally provided.

### [Rigidity of the Ball Screw under a Preload]

When a preload is provided to the Ball Screw, the rigidity of the nut is increased.

Fig.4 shows elastic displacement curves of the Ball Screw under a preload and without a preload.




Fig.4 Elastic Displacement Curve of the Ball Screw



Fig.5 shows a single-nut type of the Ball Screw.




Fig.5




Fig.6

The A and B sides are provided with preload  $F_{a0}$  by changing the groove pitch in the center of the nut to create a phase. Because of the preload, the A and B sides are elastically displaced by  $\delta_{a0}$  each. If an axial load ( $F_a$ ) is applied from outside in this state, the displacement of the A and B sides is calculated as follows.

$$\delta_A = \delta_{a0} + \delta a \quad \delta_B = \delta_{a0} - \delta a$$

In other words, the loads on the A and B sides are expressed as follows:

$$F_A = F_{a0} + (F_a - F_{a'}) \quad F_B = F_{a0} - F_{a'}$$

Therefore, under a preload, the load that the A side receives equals to  $F_a - F_{a'}$ . This means that since load  $F_{a'}$ , which is applied when the A side receives no preload, is deducted from  $F_a$ , the displacement of the A side is smaller.

This effect extends to the point where the displacement ( $\delta_{a0}$ ) caused by the preload applied on the B side reaches zero.

To what extent is the elastic displacement reduced? The relationship between the axial load on the Ball Screw under no preload and the elastic displacement can be expressed by  $\delta_a \propto F_a^{2/3}$ . From Fig.6, the following equations are established.

$$\delta_{a0} = K F_{a0}^{2/3} \quad (K : \text{constant})$$

$$2\delta_{a0} = K F_t^{2/3}$$

$$\left(\frac{F_t}{F_{a0}}\right)^{2/3} = 2 \quad F_t = 2^{3/2} \times F_{a0} = 2.8F_{a0} \doteq 3F_{a0}$$

Thus, the Ball Screw under a preload is displaced by  $\delta_{a0}$  when an axial load ( $F_t$ ) approximately three times greater than the preload is provided from outside. As a result, the displacement of the Ball Screw under a preload is half the displacement ( $2\delta_{a0}$ ) of the Ball Screw without a preload.

As stated above, since the preloading is effective up to approximately three times the applied preload, the optimum preload is one third of the maximum axial load.

Note that an excessive preload adversely affects the service life and heat generation. The maximum pre-load should be set at 10% of the basic dynamic load rating ( $C_a$ ) in the axial direction.

## [Preload Torque]

The preload torque of the Ball Screw is controlled in accordance with the JIS standard JIS B 1192 (ISO 3408).




Fig.7 Terms on Preload Torque

### ● Dynamic Preload Torque

A torque required to continuously rotate the screw shaft of a Ball Screw under a given preload without an external load applied.

### ● Actual Torque

A dynamic preload torque measured with an actual Ball Screw.

### ● Torque Fluctuation

Variation in a dynamic preload torque set at a target value. It can be positive or negative in relation to the reference torque.

### ● Coefficient of Torque Fluctuation

Ratio of torque fluctuation to the reference torque.

### ● Reference Torque

A dynamic preload torque set as a target.

### ● Calculating the Reference Torque

The reference torque of a Ball Screw provided with a preload is obtained in the following equation (4).

$$T_p = 0.05 (\tan\beta)^{-0.5} \frac{F_{a0} \cdot Ph}{2\pi} \dots\dots(4)$$

$T_p$  : Reference torque (N·mm)

$\beta$  : Lead angle

$F_{a0}$  : Applied preload (N)

$Ph$  : Lead (mm)

## Example of calculating the preload torque

When a preload of 3,000 N is provided to the Ball Screw model BIF4010-10G0 + 1500LC3 with a thread length of 1,300 mm (shaft diameter: 40 mm; ball center-to-center diameter: 41.75 mm; lead: 10 mm), the preload torque of the Ball Screw is calculated in the steps below.

### ■ Calculating the Reference Torque

$\beta$  : Lead angle

$$\tan\beta = \frac{\text{lead}}{\pi \times \text{ball center-to-center diameter}} = \frac{10}{\pi \times 41.75} = 0.0762$$

$F_{a0}$  : Applied preload=3000 N

$Ph$  : Lead = 10 mm

$$T_p = 0.05 (\tan\beta)^{-0.5} \frac{F_{a0} \cdot Ph}{2\pi} = 0.05 (0.0762)^{-0.5} \frac{3000 \times 10}{2\pi} = 865 \text{ N}\cdot\text{mm}$$

### ■ Calculating the Torque Fluctuation

$$\frac{\text{thread length}}{\text{screw shaft outer diameter}} = \frac{1300}{40} = 32.5 \leq 40$$

Thus, with the reference torque in Table14 being between 600 and 1,000 N·mm, effective thread length 4,000 mm or less and accuracy grade C3, the coefficient of torque fluctuation is obtained as  $\pm 30\%$ .

As a result, the torque fluctuation is calculated as follows.

$$865 \times (1 \pm 0.3) = 606 \text{ N}\cdot\text{mm} \text{ to } 1125 \text{ N}\cdot\text{mm}$$

### ■ Result

Reference torque : 865 N·mm

Torque fluctuation : 606 N·mm to 1125 N·mm

Table14 Tolerance Range in Torque Fluctuation

| Reference torque<br>N·mm |         | Effective thread length  |      |      |      |      |      |  |      |      |      |      |   |      |  |
|--------------------------|---------|--|------|------|------|------|------|--|------|------|------|------|---|------|--|
|                          |         | 4000mm or less   |      |      |      |      |      |  |      |      |      |      | Above 4,000 mm and<br>10,000 mm or less |      |  |
|                          |         | $\frac{\text{thread length}}{\text{screw shaft outer diameter}} \leq 40$ |      |      |      |      |      | $40 < \frac{\text{thread length}}{\text{screw shaft outer diameter}} < 60$ |      |      |      |      | —                                       |      |  |
|                          |         | Accuracy grades  |      |      |      |      |      | Accuracy grades  |      |      |      |      | Accuracy grades                         |      |  |
| Above                    | Or less | C0   | C1   | C3   | C5   | C7   | C0   | C1   | C3   | C5   | C7   | C3   | C5                                      | C7   |  |
| 200                      | 400     | ±30%   | ±35% | ±40% | ±50% | —    | ±40% | ±40%   | ±50% | ±60% | —    | —    | —                                       | —    |  |
| 400                      | 600     | ±25%   | ±30% | ±35% | ±40% | —    | ±35% | ±35%   | ±40% | ±45% | —    | —    | —                                       | —    |  |
| 600                      | 1000    | ±20%   | ±25% | ±30% | ±35% | ±40% | ±30% | ±30%   | ±35% | ±40% | ±45% | ±40% | ±45%                                    | ±50% |  |
| 1000                     | 2500    | ±15%   | ±20% | ±25% | ±30% | ±35% | ±25% | ±25%   | ±30% | ±35% | ±40% | ±35% | ±40%                                    | ±45% |  |
| 2500                     | 6300    | ±10%   | ±15% | ±20% | ±25% | ±30% | ±20% | ±20%   | ±25% | ±30% | ±35% | ±30% | ±35%                                    | ±40% |  |
| 6300                     | 10000   | —  | —    | ±15% | ±20% | ±30% | —    | —  | ±20% | ±25% | ±35% | ±25% | ±30%                                    | ±35% |  |

# Selecting a Screw Shaft

## Maximum Manufacturing Length of the Screw Shaft

Table15 shows the maximum manufacturing lengths of precision ball screws by accuracy grade, Table16 shows the maximum manufacturing lengths of precision ball screws compliant with DIN standards by accuracy grade, and Table17 shows the maximum manufacturing lengths of rolled ball screws by accuracy grade.

If the shaft dimensions exceed the maximum manufacturing lengths in Table15, Table16, or Table17, contact THK.

Table15 Maximum Manufacturing Length of Precision Ball Screws by Accuracy Grade

Unit: mm

| Screw shaft<br>outer diameter | Overall screw shaft length |      |      |       |       |       |
|-------------------------------|----------------------------|------|------|-------|-------|-------|
|                               | C0                         | C1   | C2   | C3    | C5    | C7    |
| 4                             | 90                         | 110  | 120  | 120   | 120   | 120   |
| 6                             | 150                        | 170  | 210  | 210   | 210   | 210   |
| 8                             | 230                        | 270  | 340  | 340   | 340   | 340   |
| 10                            | 350                        | 400  | 500  | 500   | 500   | 500   |
| 12                            | 440                        | 500  | 630  | 680   | 680   | 680   |
| 13                            | 440                        | 500  | 630  | 680   | 680   | 680   |
| 14                            | 530                        | 620  | 770  | 870   | 890   | 890   |
| 15                            | 570                        | 670  | 830  | 950   | 980   | 1100  |
| 16                            | 620                        | 730  | 900  | 1050  | 1100  | 1400  |
| 18                            | 720                        | 840  | 1050 | 1220  | 1350  | 1600  |
| 20                            | 820                        | 950  | 1200 | 1400  | 1600  | 1800  |
| 25                            | 1100                       | 1400 | 1600 | 1800  | 2000  | 2400  |
| 28                            | 1300                       | 1600 | 1900 | 2100  | 2350  | 2700  |
| 30                            | 1450                       | 1700 | 2050 | 2300  | 2570  | 2950  |
| 32                            | 1600                       | 1800 | 2200 | 2500  | 2800  | 3200  |
| 36                            | 2000                       | 2100 | 2550 | 2950  | 3250  | 3650  |
| 40                            | 2000                       | 2400 | 2900 | 3400  | 3700  | 4300  |
| 45                            | 2000                       | 2750 | 3350 | 3950  | 4350  | 5050  |
| 50                            | 2000                       | 3100 | 3800 | 4500  | 5000  | 5800  |
| 55                            | 2000                       | 3450 | 4150 | 5300  | 6050  | 6500  |
| 63                            | 2000                       | 4000 | 5200 | 5800  | 6700  | 7700  |
| 70                            | 2000                       | 4000 | 6300 | 6450  | 7650  | 9000  |
| 80                            | 2000                       | 4000 | 6300 | 7900  | 9000  | 11000 |
| 100                           | 2000                       | 4000 | 6300 | 11000 | 11000 | 11000 |

\*For ball screw models HBN-V, HBN-K, HBN-KA, HBN, and SBKH, the standard maximum length of the screw shaft is 3000 mm. For lengths greater than this, please contact THK. For details, refer to **B15-294**.

## Point of Selection

## Selecting a Screw Shaft

Table16 Maximum Manufacturing Length of Precision Ball Screws (DIN Standard-Compliant Ball Screws)

Unit: mm

| Shaft diameter | Ground shaft |      |      | CES shaft |      |      |      |
|----------------|--------------|------|------|-----------|------|------|------|
|                | C3           | C5   | C7   | Cp3       | Cp5  | Ct5  | Ct7  |
| 16             | 1050         | 1100 | 1400 | 1050      | 1100 | 1100 | 1400 |
| 20             | 1400         | 1600 | 1800 | 1400      | 1600 | 1600 | 1800 |
| 25             | 1800         | 2000 | 2400 | 1800      | 2000 | 2000 | 2400 |
| 32             | 2500         | 2800 | 3200 | 2500      | 2800 | 2800 | 3200 |
| 40             | 3400         | 3700 | 4300 | 3400      | 3700 | 3700 | 4300 |
| 50             | 4500         | 5000 | 5800 | —         | —    | —    | —    |
| 63             | 5800         | 6700 | 7700 | —         | —    | —    | —    |

Table17 Maximum Manufacturing Length of Rolled Ball Screws  
by Accuracy Grade

Unit: mm

| Screw shaft<br>outer diameter | Overall screw shaft length |      |      |
|-------------------------------|----------------------------|------|------|
|                               | C7                         | C8   | C10  |
| 6 to 8                        | 320                        | 320  | —    |
| 10 to 12                      | 500                        | 1000 | —    |
| 14 to 15                      | 1500                       | 1500 | 1500 |
| 16 to 18                      | 1500                       | 1800 | 1800 |
| 20                            | 2000                       | 2200 | 2200 |
| 25                            | 2000                       | 3000 | 3000 |
| 28                            | 3000                       | 3000 | 3000 |
| 30                            | 3000                       | 3000 | 4000 |
| 32 to 36                      | 3000                       | 4000 | 4000 |
| 40                            | 3000                       | 5000 | 5000 |
| 45                            | 3000                       | 5500 | 5500 |
| 50                            | 3000                       | 6000 | 6000 |

For details, refer to **■15-294**.

## Combinations of Shaft Diameter and Lead for the Precision Ball Screw

Table18 shows combinations of shaft diameters and leads of precision ball screws, and Table19 shows combinations of shaft diameters and leads of precision ball screws compliant with DIN standards.

If a ball screw not covered by the table is required, contact THK.

Table18 Combinations of Screw Shaft Diameter and Lead (Precision Ball Screw)

Unit: mm

| Screw shaft outer diameter | Lead |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |  |
|----------------------------|------|-----|---|-----|---|---|---|---|---|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|-----|---|---|--|
|                            | 1    | 1.5 | 2 | 2.5 | 3 | 4 | 5 | 6 | 8 | 10 | 12 | 15 | 16 | 20 | 24 | 25 | 30 | 32 | 35 | 36 | 40 | 42 | 50 | 60 | 80 | 90 | 100 |   |   |  |
| 4                          | ●    |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |  |
| 5                          | ●    |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |  |
| 6                          | ●    |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |  |
| 8                          | ●    | ●   | ● | ●   | ● | ● |   | ● | ● | ●  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |  |
| 10                         | ●    | ●   | ● | ●   | ● | ● | ● | ● | ● | ●  | ●  | ●  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |  |
| 12                         |      |     | ● | ●   | ● | ● | ● | ● | ● | ●  | ●  | ●  |    | ●  |    |    |    | ●  |    |    |    |    |    |    |    |    |     |   |   |  |
| 13                         |      |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    | ●  |    |    |    |    |    |    |    |    |     |   |   |  |
| 14                         |      |     | ● |     |   | ● | ● | ● | ● |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |  |
| 15                         |      |     |   |     |   | ● | ● | ● | ● | ●  | ●  | ●  |    | ●  |    |    |    | ●  |    |    |    |    | ●  |    |    |    |     |   |   |  |
| 16                         |      |     |   |     |   | ● | ● | ● | ● | ●  | ●  | ●  |    | ●  |    |    |    |    |    |    |    |    | ●  |    |    |    |     |   |   |  |
| 18                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |  |
| 20                         |      |     |   |     |   | ● | ● | ● | ● | ●  | ●  | ●  |    | ●  |    |    | ●  | ●  | ●  |    |    | ●  |    |    | ●  |    |     |   |   |  |
| 25                         |      |     |   |     |   | ● | ● | ● | ● | ●  | ●  | ●  |    | ●  |    |    | ●  | ●  | ●  |    |    |    |    | ●  |    |    |     |   |   |  |
| 28                         |      |     |   |     |   |   |   |   |   |    |    | ●  |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   |   |  |
| 30                         |      |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    | ●  |    |     | ● |   |  |
| 31                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  |    |    |    | ●  |    |    |    |    |    | ●  |    |     | ● |   |  |
| 32                         |      |     |   |     |   | ● | ● | ● | ● | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    | ●  |    |    |    |    |    |    |    |     |   |   |  |
| 36                         |      |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    | ●  |    |    |    |    |     |   |   |  |
| 38                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    | ●  |    |    |    |     |   |   |  |
| 40                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    | ●  |    |    | ●  |     |   |   |  |
| 45                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    |    |     |   |   |  |
| 50                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    |     |   | ● |  |
| 55                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  |    |    |     |   |   |  |
| 63                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |  |
| 70                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |  |
| 80                         |      |     |   |     |   |   |   |   |   | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |  |
| 100                        |      |     |   |     |   |   |   |   |   |    |    |    |    | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●  | ●   | ● | ● |  |
| 120                        |      |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   | ● |  |
| 140                        |      |     |   |     |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |     |   | ● |  |

Table19 Standard Combinations of Outer Diameters and Leads of the Screw Shafts (DIN Standard-Compliant Ball Screws)

Unit: mm

| Shaft diameter | Lead |    |    |
|----------------|------|----|----|
|                | 5    | 10 | 20 |
| 16             | ●    | —  | —  |
| 20             | ●    | —  | —  |
| 25             | ●    | ●  | —  |
| 32             | ●    | ●  | —  |
| 40             | ○    | ●  | ○* |
| 50             | —    | ○  | ○* |
| 63             | —    | ○  | ○* |

●: Ground shaft, CES shaft

○: Ground shaft only

\*: Model EB (no preload) only

## Combinations of Shaft Diameter and Lead for the Rolled Ball Screw

Table20 shows the combinations of shaft diameter and lead for the rolled ball screw.

Table20 Combinations of Screw Shaft Diameter and Lead (Rolled Ball Screw)

Unit: mm

| Screw shaft<br>outer diameter | Lead |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
|-------------------------------|------|---|---|---|---|---|----|----|----|----|----|----|----|----|----|----|----|----|----|-----|
|                               | 1    | 2 | 4 | 5 | 6 | 8 | 10 | 12 | 16 | 20 | 24 | 25 | 30 | 32 | 36 | 40 | 50 | 60 | 80 | 100 |
| 6                             | ●    |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 8                             | ●    | ● |   | ● |   | ● |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 10                            |      | ● | ● |   | ● |   | ●  |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 12                            |      | ● |   |   |   | ● |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 14                            |      | ● | ● | ● |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 15                            |      |   |   |   |   |   | ●  |    | ●  |    |    | ●  |    |    |    |    |    |    |    |     |
| 16                            |      |   |   | ● |   |   |    |    | ●  |    |    |    |    |    |    |    |    |    |    |     |
| 18                            |      |   |   |   |   | ● |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 20                            |      |   |   | ● |   |   | ●  |    | ●  |    |    |    |    |    |    | ●  |    |    |    |     |
| 25                            |      |   |   | ● |   |   | ●  |    |    |    |    | ●  |    |    |    |    | ●  |    |    |     |
| 28                            |      |   |   | ● | ● |   |    |    |    |    |    |    |    |    |    |    |    |    |    |     |
| 30                            |      |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    | ●  |    |     |
| 32                            |      |   |   |   |   |   | ●  |    |    |    |    |    |    | ●  |    |    |    |    |    |     |
| 36                            |      |   |   |   |   |   | ●  |    | ●  | ●  |    |    |    |    | ●  |    |    |    |    |     |
| 40                            |      |   |   |   |   |   | ●  |    |    |    |    |    |    |    |    | ●  |    |    | ●  |     |
| 45                            |      |   |   |   |   |   |    | ●  |    |    |    |    |    |    |    |    |    |    |    |     |
| 50                            |      |   |   |   |   |   |    |    | ●  |    |    |    |    |    |    |    | ●  |    |    | ●   |

## Method for Mounting the Ball Screw Shaft

Fig.1 to Fig.4 show the representative mounting methods for the screw shaft.

The permissible axial load and the permissible rotational speed vary with mounting methods for the screw shaft. Therefore, it is necessary to select an appropriate mounting method according to the conditions.




Fig.1 Screw Shaft Mounting Method: Fixed - Free




Fig.2 Screw Shaft Mounting Method: Fixed - Supported



## Point of Selection

## Method for Mounting the Ball Screw Shaft




Fig.3 Screw Shaft Mounting Method: Fixed - Fixed




Fig.4 Screw Shaft Mounting Method for Rotary Nut Ball Screw: Fixed - Fixed

## Permissible Axial Load

### [Buckling Load on the Screw Shaft]

With the Ball Screw, it is necessary to select a screw shaft so that it will not buckle when the maximum compressive load is applied in the axial direction.

Fig.5 on **B15-39** shows the relationship between the screw shaft diameter and a buckling load. If determining a buckling load by calculation, it can be obtained from the equation (5) below. Note that in this equation, a safety factor of 0.5 is multiplied to the result.

$$P_1 = \frac{\eta_1 \cdot \pi^2 \cdot E \cdot I}{\ell_a^2} \cdot 0.5 = \eta_2 \frac{d_1^4}{\ell_a^2} \cdot 10^4 \quad \dots\dots(5)$$

$P_1$  : Buckling load (N)

$\ell_a$  : Distance between two mounting surfaces (mm)

$E$  : Young's modulus ( $2.06 \times 10^5$  N/mm<sup>2</sup>)

$I$  : Minimum geometrical moment of inertia of the shaft (mm<sup>4</sup>)

$$I = \frac{\pi}{64} d_1^4 \quad d_1: \text{screw-shaft thread minor diameter (mm)}$$

$\eta_1, \eta_2$ : Factor according to the mounting method

Fixed - free             $\eta_1=0.25$      $\eta_2=1.3$

Fixed - supported     $\eta_1=2$          $\eta_2=10$

Fixed - fixed          $\eta_1=4$          $\eta_2=20$

### [Permissible Tensile Compressive Load on the Screw Shaft]

If an axial load is applied to the Ball Screw, it is necessary to take into account not only the buckling load but also the permissible tensile compressive load in relation to the yielding stress on the screw shaft.

The permissible tensile compressive load is obtained from the equation (6).

$$P_2 = \sigma \frac{\pi}{4} d_1^2 = 116d_1^2 \quad \dots\dots(6)$$

$P_2$  : Permissible tensile compressive load (N)

$\sigma$  : Permissible tensile compressive stress (147 MPa)

$d_1$  : Screw-shaft thread minor diameter (mm)




Fig.5 Permissible Tensile Compressive Load Diagram

## Permissible Rotational Speed

### [Critical Speed of the Screw Shaft]

When the rotational speed reaches a high magnitude, the Ball Screw may resonate and eventually become unable to operate due to the screw shaft's natural frequency. Therefore, it is necessary to select a model so that it is used below the resonance point (critical speed).

Fig.6 on **B15-42** shows the relationship between the screw shaft diameter and the critical speed.

If determining the critical speed by calculation, it can be obtained from the equation (7) below. Note that in this equation, a safety factor of 0.8 is multiplied to the result.

$$N_1 = \frac{60 \cdot \lambda_1^2}{2\pi \cdot \ell_b^2} \times \sqrt{\frac{E \times 10^3 \cdot I}{\gamma \cdot A}} \times 0.8 = \lambda_2 \cdot \frac{d_1}{\ell_b^2} \cdot 10^7 \dots\dots(7)$$

$N_1$  : Permissible rotational speed determined  
by the critical speed (min<sup>-1</sup>)

$\ell_b$  : Distance between two mounting surfaces  
(mm)

$E$  : Young's modulus (2.06 × 10<sup>5</sup> N/mm<sup>2</sup>)

$I$  : Minimum geometrical moment of inertia  
of the shaft (mm<sup>4</sup>)

$$I = \frac{\pi}{64} d_1^4 \quad d_1: \text{screw-shaft thread minor diameter (mm)}$$

$\gamma$  : Density (specific gravity)  
(7.85 × 10<sup>-6</sup> kg/mm<sup>3</sup>)

$A$  : Screw shaft cross-sectional area (mm<sup>2</sup>)

$$A = \frac{\pi}{4} d_1^2$$

$\lambda_1, \lambda_2$  : Factor according to the mounting method

Fixed - free  $\lambda_1=1.875$   $\lambda_2=3.4$

Supported - supported  $\lambda_1=3.142$   $\lambda_2=9.7$

Fixed - supported  $\lambda_1=3.927$   $\lambda_2=15.1$

Fixed - fixed  $\lambda_1=4.73$   $\lambda_2=21.9$

## Point of Selection

## Permissible Rotational Speed

## [DN Value]

The permissible rotational speed of the Ball Screw must be obtained from the critical speed of the screw shaft and the DN value. The permissible rotational speed determined by the DN value is obtained using the equations (8) to (17) below.

| Model No.  |                         |   | Permissible rotational speed determined by the DN value<br>$N_2$ : |  |
|--|-------------------------|---|--|--|
| Precision  | Caged Ball              | Models SDAN-V and SDA-V   | Standard lead/ Super lead $N_2 = \frac{160000}{D}$ .....(8)        |  |
|  |                         | Model SBK (Medium)<br>(SBK3636, SBK4040, and SBK5050)                                   | Large lead $N_2 = \frac{210000}{D}$ .....(9-1)                     |  |
|  |                         | Model SBK (Medium)<br>(Other than the above model numbers and the small size model SBK) |  | $N_2 = \frac{160000}{D}$ .....(9-2)                  |
|  |                         | Model SBK (Small)   | $N_2 = \frac{130000}{D}$ .....(9-3)                                |  |
|  |                         | Models SBN-V (Medium), HBN-V  | Standard lead $N_2 = \frac{160000}{D}$ .....(10-1)                 |  |
|  |                         | Models SBN-V (Small), HBN, and SBKH   |  | $N_2 = \frac{130000}{D}$ .....(10-2)                 |
|  | Models HBN-K and HBN-KA | $N_2 = \frac{120000}{D}$ .....(10-3)  |  |  |
|  | Full-Complement Ball    | Models SDAN-VX and SDA-VZ<br>(shaft diameters $\phi 28$ to $63$ )                       | Standard lead/ Super lead $N_2 = \frac{130000}{D}$ .....(11-1)     |  |
|  |                         |   |  | Model SDA-VZ<br>(shaft diameters $\phi 10$ to $25$ ) |
|  |                         | Model WHF   | Super lead $N_2 = \frac{120000}{D}$ .....(12-1)                    |  |
|  |                         | Model WGF   |  | $N_2 = \frac{70000}{D}$ .....(12-2)                  |
|  |                         | Models BNS-V and NS-V   | Large lead $N_2 = \frac{100000}{D}$ .....(13-1)                    |  |
|  |                         | Models BLW, BLK, BLR, BNS-A, BNS, NS-A, and NS  |  | $N_2 = \frac{70000}{D}$ .....(13-2)                  |
|  |                         | Models BIF-V (Medium), BNFN-V (Medium), and BNF-V (Medium)                              | Standard lead $N_2 = \frac{130000}{D}$ .....(14-1)                 |  |
|  |                         | Models BIF-V (Small), BNFN-V (Small), and BNF-V (Small)                                 |  | $N_2 = \frac{100000}{D}$ .....(14-2)                 |
|  |                         | Models BIF, DIK, BNFN, DKN, BNF, BNT, DK, MDK, MBF, BNK, and DIR                        |  | $N_2 = \frac{70000}{D}$ .....(14-3)                  |
|  |                         | Full-Complement Ball (DIN Standard Compliant)   |  | Standard lead $N_2 = \frac{130000}{D}$ .....(14-4)   |
| Models EPB-V, EBB-V (2806 to 8020)<br>Models EPB-V, EBB-V (1605 to 2512) |                         |   |  |  |
| Rolled   | Full-Complement Ball    | Models WTF and CNF  | Super lead $N_2 = \frac{70000}{D}$ .....(15)                       |  |
|  |                         | Models BLK and BLR  | Large lead $N_2 = \frac{70000}{D}$ .....(16)                       |  |
|  |                         | Model BTK-V   | Standard lead $N_2 = \frac{100000}{D}$ .....(17-1)                 |  |
|  |                         | Models JPF, BNT, and MTF  |  | $N_2 = \frac{50000}{D}$ .....(17-2)                  |

$N_2$  : Permissible rotational speed determined by the DN value ( $\text{min}^{-1}$ )

D : Ball center-to-center diameter

(indicated in the dimensional tables of the respective model numbers)

When considering the rotational speed, the permissible rotational speed is regarded as the lower of the following rotational speed guidelines: the critical speed of the screw shaft ( $N_1$ ) or the permissible rotational speed determined by the DN value ( $N_2$ ). Refer to the dimensional tables of the respective model numbers for the permissible rotational speed.

If the service rotational speed exceeds the guidelines for maximum rotational speed, contact THK.




Fig.6 Permissible Rotational Speed Diagram

# Selecting a Nut

## Types of Nuts

The nuts of the Ball Screws are categorized by the ball circulation method into the return-pipe type, the deflector type and end cap type. These three nut types are described as follows.


In addition to the circulation methods, the Ball Screws are categorized also by the preloading method.

### [Types by Ball Circulation Method]

#### ● Return-Pipe Type

(Models SBN-V (Medium), BIF-V (Medium), BIF, BNF-V (Medium), BNF, BNFN-V (Medium), BNFN, BNT, BTK-V),  
Return-Piece Type  
(Models SBN-V (Small), HBN, BIF-V (Small), BNF-V (Small), BNFN-V (Small))

These are the most common types of nuts, which use a return pipe for ball circulation. The return pipe allows balls to be picked up, pass through the pipe and return piece, and return to their original positions to circulate endlessly.




Example of Structure of Return-Pipe Nut

#### ● Deflector Type

(Models EBB-V, EPB-V, DK, DKN, DIK, JPF, DIR and MDK)


These are the most compact type of nut. The balls change their traveling direction with a deflector, pass over the circumference of the screw shaft, and return to their original positions to complete an infinite motion.



Example of Structure of Simple Nut

#### ● End-cap Type: Large lead Nut (Models SBK, SBKH, WHF, BLK, WGF, BLW, WTF, CNF and BLR)

These nuts are most suitable for the fast feed. The balls are picked up with an end cap, pass through the through hole of the nut, and return to their original positions to complete an infinite motion.




Example of Structure of Large lead Nut

### [Types by Preloading Method]

#### ● Fixed-point Preloading

#### ■ Double-nut Preload (Models SDAN-V, BNFN-V, BNFN, DKN and BLW)

A spacer is inserted between two nuts to provide a preload.



Model SDAN-V



Models BNFN-V and BNFN




Model DKN



Model BLW

#### ■ Offset Preload (Models SBK, SBN-V, BIF-V, BIF, EPB-V, DIK and DIR)

More compact than the double-nut method, the offset preloading provides a preload by changing the groove pitch of the nut without using a spacer.



Model SBK



Model SBN-V



Models BIF-V and BIF



Model EPB-V



Model DIK



Model DIR




## Point of Selection

### Selecting a Nut

#### ● Constant Pressure Preloading (Model JPF)

With this method, a spring structure is installed almost in the middle of the nut, and it provides a preload by changing the groove pitch in the middle of the nut.



Model JPF

# Selecting a Model Number

## Calculating the Axial Load

### [In Horizontal Mount]

With ordinary conveyance systems, the axial load ( $F_{a_n}$ ) applied when horizontally reciprocating the work is obtained in the equation below.

$$F_{a_1} = \mu \cdot mg + f + m\alpha \quad \dots\dots\dots (18)$$

$$F_{a_2} = \mu \cdot mg + f \quad \dots\dots\dots (19)$$

$$F_{a_3} = \mu \cdot mg + f - m\alpha \quad \dots\dots\dots (20)$$

$$F_{a_4} = -\mu \cdot mg - f - m\alpha \quad \dots\dots\dots (21)$$

$$F_{a_5} = -\mu \cdot mg - f \quad \dots\dots\dots (22)$$

$$F_{a_6} = -\mu \cdot mg - f + m\alpha \quad \dots\dots\dots (23)$$

$V_{\max}$  : Maximum speed (m/s)

$t_1$  : Acceleration time (s)

$$\alpha = \frac{V_{\max}}{t_1} : \text{Acceleration} \quad (m/s^2)$$


$F_{a_1}$  : Axial load during forward acceleration (N)

$F_{a_2}$  : Axial load during forward uniform motion (N)

$F_{a_3}$  : Axial load during forward deceleration (N)

$F_{a_4}$  : Axial load during backward acceleration (N)

$F_{a_5}$  : Axial load during uniform backward motion (N)



$F_{a_6}$  : Axial load during backward deceleration (N)

$m$  : Transferred mass (kg)

$\mu$  : Frictional coefficient of the guide surface (-)

$f$  : Guide surface resistance (without load) (N)

### [In Vertical Mount]

With ordinary conveyance systems, the axial load ( $F_{a_n}$ ) applied when vertically reciprocating the work is obtained in the equation below.

$$F_{a_1} = mg + f + m\alpha \quad \dots\dots\dots (24)$$

$$F_{a_2} = mg + f \quad \dots\dots\dots (25)$$

$$F_{a_3} = mg + f - m\alpha \quad \dots\dots\dots (26)$$

$$F_{a_4} = mg - f - m\alpha \quad \dots\dots\dots (27)$$

$$F_{a_5} = mg - f \quad \dots\dots\dots (28)$$

$$F_{a_6} = mg - f + m\alpha \quad \dots\dots\dots (29)$$

$V_{\max}$  : Maximum speed (m/s)

$t_1$  : Acceleration time (s)

$$\alpha = \frac{V_{\max}}{t_1} : \text{Acceleration} \quad (m/s^2)$$


$F_{a_1}$  : Axial load during upward acceleration (N)

$F_{a_2}$  : Axial load during uniform upward motion (N)

$F_{a_3}$  : Axial load during upward deceleration (N)

$F_{a_4}$  : Axial load during downward acceleration (N)

$F_{a_5}$  : Axial load during uniform downward motion (N)



$F_{a_6}$  : Axial load during downward deceleration (N)

$m$  : Transferred mass (kg)

$f$  : Guide surface resistance (without load) (N)

## Static Safety Factor

The basic static load rating ( $C_{0a}$ ) generally equals to the permissible axial load of a Ball Screw. Depending on the conditions, it is necessary to take into account the following static safety factor against the calculated load. When the Ball Screw is stationary or in motion, unexpected external force may be applied through an inertia caused by the impact or the start and stop.

$$F_{a_{\max}} = \frac{C_{0a}}{f_s} \dots\dots(30)$$

$F_{a_{\max}}$  : Allowable Axial Load (kN)

$C_{0a}$  : Basic static load rating\* (kN)

$f_s$  : Static safety factor (see Table1)

Table1 Static Safety Factor ( $f_s$ )

| Machine using the LM system  | Load conditions             | Lower limit of $f_s$ |
|------------------------------|-----------------------------|----------------------|
| General industrial machinery | Without vibration or impact | 1.0 to 3.5           |
|                              | With vibration or impact    | 2.0 to 5.0           |
| Machine tool                 | Without vibration or impact | 1.0 to 4.0           |
|                              | With vibration or impact    | 2.5 to 7.0           |

\*The basic static load rating ( $C_{0a}$ ) is a static load with a constant direction and magnitude whereby the sum of the permanent deformation of the rolling element and that of the raceway on the contact area under the maximum stress is 0.0001 times the rolling element diameter. With the Ball Screw, it is defined as the axial load. (Specific values of each Ball Screw model are indicated in the specification tables for the corresponding model number.)

### [Permissible Load Safety Margin (Models HBN-V, HBN-K, HBN-KA, HBN, and SBKH)]

In comparison to previous ball screws, high-load ball screw models HBN-V, HBN-K (KA), HBN, and SBKH are designed to achieve longer service lives under high load conditions, and it is necessary to consider the permissible load  $F_p$  for the axial load. Permissible load  $F_p$  indicates the maximum axial load that the high-load ball screw can support, and this range should not be exceeded.

$$\frac{F_p}{F_a} > 1 \dots\dots(31)$$

$F_p$  : Permissible Axial Load (kN)

$F_a$  : Applied Axial Load (kN)

## Studying the Service Life

### [Service Life of the Ball Screw]

A Ball Screw in motion under an external load receives repeated stress on its raceways and balls. When the stress reaches the limit, the raceways break from fatigue, and their surfaces flake like scales. This phenomenon is called flaking. The service life of the Ball Screw is the total number of revolutions until the first flaking occurs on any of the raceways or the balls as a result of rolling fatigue of the material.

The service life of the Ball Screw varies from unit to unit even if they are manufactured in the same process and used in the same operating conditions. For this reason, when determining the service life of a Ball Screw unit, the nominal life as defined below is used as a guideline.

The nominal life is the total number of revolutions that 90% of identical Ball Screw units in a group achieve without flaking after they independently operate in the same conditions.

### [Calculating the Rated Life]

The service life of the Ball Screw is calculated from the formula (32) below using the basic dynamic load rating (Ca) and the applied axial load.

#### ● Calculating the Nominal Life

The nominal life ( $L_{10}$ ) is obtained from the following formula using the basic dynamic load rating (Ca) and the applied load in the axial direction (Fa).

$$L_{10} = \left( \frac{Ca}{Fa} \right)^3 \times 10^6 \dots\dots\dots(32-1)$$

$L_{10}$  : Nominal life (rev.)  
 $Ca$  : Basic dynamic load rating (N)  
 $Fa$  : Applied axial load (N)

#### ● Calculating the Modified Nominal Life

During use, a ball screw may be subjected to vibrations and shocks as well as fluctuating loads, which are difficult to detect. Taking these factors into account, the modified nominal life ( $L_{10m}$ ) can be calculated according to the following formula (32-2).

•Modified factor  $\alpha$

$$\alpha = \frac{1}{f_w}$$

$\alpha$  : Modified factor  
 $f_w$  : Load factor (see Table2)

•Modified nominal life  $L_{10m}$

$$L_{10m} = \left( \alpha \times \frac{Ca}{Fa} \right)^3 \times 10^6 \dots\dots\dots(32-2)$$

$L_{10m}$  : Modified nominal life (rev.)  
 $Ca$  : Basic dynamic load rating (N)  
 $Fa$  : Applied axial load (N)

Table2 Load Factor ( $f_w$ )

| Vibrations/impact | Speed (V)                     | $f_w$      |
|-------------------|-------------------------------|------------|
| Faint             | Very low<br>$V \leq 0.25$ m/s | 1 to 1.2   |
| Weak              | Slow<br>$0.25 < V \leq 1$ m/s | 1.2 to 1.5 |
| Medium            | Medium<br>$1 < V \leq 2$ m/s  | 1.5 to 2   |
| Strong            | High<br>$V > 2$ m/s           | 2 to 3.5   |

\*The basic dynamic load rating (Ca) is used in calculations of service life when the ball screw is under an axial load. The basic dynamic load rating is defined as a load rating based on the movement of a set of identical ball screws with a rated life (L) of  $10^6$  revolutions, using a load applied in the axial direction that does not vary in either magnitude or direction. (The basic dynamic load ratings (Ca) for each model number are indicated in the specification tables.)

\*The rated service life is estimated by calculating the load on the premise that the product is set up in ideal mounting conditions with the assurance of good lubrication. The service life can be affected by the precision of the mounting materials used and any distortion.

### ● Service Life Time

If the revolutions per minute is determined, the service life time can be calculated from the equation (33) below using the nominal life ( $L_{10}$ ).

$$L_h = \frac{L_{10}}{60 \times N} = \frac{L_{10} \times Ph}{2 \times 60 \times n \times \ell_s} \dots\dots\dots(33)$$

|          |                                       |                       |
|----------|---------------------------------------|-----------------------|
| $L_h$    | : Service life time                   | (h)                   |
| $N$      | : Revolutions per minute              | ( $\text{min}^{-1}$ ) |
| $n$      | : Number of reciprocations per minute | ( $\text{min}^{-1}$ ) |
| $Ph$     | : Ball Screw lead                     | (mm)                  |
| $\ell_s$ | : Stroke length                       | (mm)                  |

### ● Service Life in Travel Distance

The service life in travel distance can be calculated from the equation (34) below using the nominal life ( $L_{10}$ ) and the Ball Screw lead.

$$L_s = \frac{L_{10} \times Ph}{10^5} \dots\dots\dots(34)$$

|       |                                   |      |
|-------|-----------------------------------|------|
| $L_s$ | : Service Life in Travel Distance | (km) |
| $Ph$  | : Ball Screw lead                 | (mm) |

### ● Applied Load and Service Life with a Preload Taken into Account

If the Ball Screw is used under a preload (medium preload), it is necessary to consider the applied preload in calculating the service life since the ball screw nut already receives an internal load. For details on applied preload for a specific model number, contact THK.

### ● Average Axial Load

If an axial load acting on the Ball Screw is present, it is necessary to calculate the service life by determining the average axial load.

The average axial load ( $F_m$ ) is a constant load that equals to the service life in fluctuating the load conditions.

If the load changes in steps, the average axial load can be obtained from the equation below.

$$F_m = \sqrt[3]{\frac{1}{\ell} (Fa_1^3 \ell_1 + Fa_2^3 \ell_2 + \dots + Fa_n^3 \ell_n)} \dots\dots\dots(35)$$

|          |  |     |
|----------|--|-----|
| $F_m$    | : Average Axial Load                     | (N) |
| $Fa_n$   | : Varying load                           | (N) |
| $\ell_n$ | : Distance traveled under load ( $F_n$ ) |     |
| $\ell$   | : Total travel distance                  |     |

To determine the average axial load using a rotational speed and time, instead of a distance, calculate the average axial load by determining the distance in the equation below.

$$l = l_1 + l_2 + \dots + l_n$$

$$l_1 = N_1 \cdot t_1$$

$$l_2 = N_2 \cdot t_2$$

$$l_n = N_n \cdot t_n$$


N: Rotational speed

t: Time

### ■When the Applied Load Sign Changes

If the sign (positive or negative) used for variable load is always the same, there are no problems with formula (35). However, if the variable load sign changes depending on the type of operation, calculate the average axial load for either positive or negative load, allowing for the load direction. (If the average axial load for positive load is calculated, the negative load is taken to be zero.) The larger of the two average axial loads is taken as the average axial load when the service life is calculated.

Example: Calculate the average axial load with the following load conditions.



| Operation No. | Varying load<br>$F_{a_i}$ (N) | Travel distance<br>$l_n$ (mm) |
|---------------|-------------------------------|-------------------------------|
| No.1          | 10                            | 10                            |
| No.2          | 50                            | 50                            |
| No.3          | -40                           | 10                            |
| No.4          | -10                           | 70                            |

\*The subscripts of the fluctuating load symbol and the travel distance symbol indicate operation numbers.

#### ● Average axial load of positive-sign load

\*To calculate the average axial load of the positive-sign load, assume  $F_{a_3}$  and  $F_{a_4}$  to be zero.

$$F_{m1} = \sqrt[3]{\frac{F_{a1}^3 \times l_1 + F_{a2}^3 \times l_2}{l_1 + l_2 + l_3 + l_4}} = 35.5 \text{ N}$$

#### ● Average axial load of negative-sign load

\*To calculate the average axial load of the negative-sign load, assume  $F_{a_1}$  and  $F_{a_2}$  to be zero.

$$F_{m2} = \sqrt[3]{\frac{|F_{a3}|^3 \times l_3 + |F_{a4}|^3 \times l_4}{l_1 + l_2 + l_3 + l_4}} = 17.2 \text{ N}$$

Accordingly, the average axial load of the positive-sign load ( $F_{m1}$ ) is adopted as the average axial load ( $F_m$ ) for calculating the service life.

## Studying the Rigidity

To increase the positioning accuracy of feed screws in NC machine tools or the precision machines, or to reduce the displacement caused by the cutting force, it is necessary to design the rigidity of the components in a well-balanced manner.

### Axial Rigidity of the Feed Screw System

When the axial rigidity of a feed screw system is  $K$ , the elastic displacement in the axial direction can be obtained using the equation (36) below.

$$\delta = \frac{Fa}{K} \quad \dots\dots(36)$$

- $\delta$  : Elastic displacement of a feed screw system in the axial direction ( $\mu\text{m}$ )  
 $Fa$  : Applied axial load (N)

The axial rigidity ( $K$ ) of the feed screw system is obtained using the equation (37) below.

$$\frac{1}{K} = \frac{1}{K_s} + \frac{1}{K_n} + \frac{1}{K_b} + \frac{1}{K_H} \quad \dots\dots(37)$$

- $K$  : Axial Rigidity of the Feed Screw System ( $\text{N}/\mu\text{m}$ )  
 $K_s$  : Axial rigidity of the screw shaft ( $\text{N}/\mu\text{m}$ )  
 $K_n$  : Axial rigidity of the nut ( $\text{N}/\mu\text{m}$ )  
 $K_b$  : Axial rigidity of the support bearing ( $\text{N}/\mu\text{m}$ )  
 $K_H$  : Rigidity of the nut bracket and the support bearing bracket ( $\text{N}/\mu\text{m}$ )

#### [Axial rigidity of the screw shaft]

The axial rigidity of a screw shaft varies depending on the method for mounting the shaft.

#### ● For Fixed-Supported (or -Free) Configuration


$$K_s = \frac{A \cdot E}{1000 \cdot L} \quad \dots\dots(38)$$

$A$  : Screw shaft cross-sectional area ( $\text{mm}^2$ )

$$A = \frac{\pi}{4} d_1^2$$

- $d_1$  : Screw-shaft thread minor diameter (mm)  
 $E$  : Young's modulus ( $2.06 \times 10^5 \text{ N}/\text{mm}^2$ )  
 $L$  : Distance between two mounting surfaces (mm)

Fig.7 on **B15-52** shows an axial rigidity diagram for the screw shaft.



● For Fixed-Fixed Configuration

$$K_s = \frac{A \cdot E \cdot L}{1000 \cdot a \cdot b} \dots\dots (39)$$

$K_s$  becomes the lowest and the elastic displacement in the axial direction is the greatest at the position of  $a = b = \frac{L}{2}$ .

$$K_s = \frac{4A \cdot E}{1000L}$$

Fig.8 on **B15-53** shows an axial rigidity diagram of the screw shaft in this configuration.





Fig.7 Axial Rigidity of the Screw Shaft (Fixed-Free, Fixed-Supported)






Fig.8 Axial Rigidity of the Screw Shaft (Fixed-Fixed)

#### [Axial rigidity of the nut]

The axial rigidity of the nut varies widely with preloads.

#### ● No Preload Type

The logical rigidity in the axial direction when an axial load accounting for 30% of the basic dynamic load rating ( $C_a$ ) is applied is indicated in the specification tables of the corresponding model number. This value does not include the rigidity of the components related to the nut-mounting bracket. In general, set the rigidity at roughly 80% of the value in the table.

The rigidity when the applied axial load is not 30% of the basic dynamic load rating ( $C_a$ ) is calculated using the equation (40) below.

$$K_N = K \left( \frac{F_a}{0.3C_a} \right)^{\frac{1}{3}} \times 0.8 \quad \dots\dots(40)$$

$K_N$  : Axial rigidity of the nut (N/μm)

$K$  : Rigidity value in the specification tables (N/μm)

$F_a$  : Applied axial load (N)

$C_a$  : Basic dynamic load rating (N)

### ● Preload Type

The logical rigidity in the axial direction when an axial load accounting for 10% of the basic dynamic load rating (Ca) is applied is indicated in the dimensional table of the corresponding model number. This value does not include the rigidity of the components related to the nut-mounting bracket. In general, generally set the rigidity at roughly 80% of the value in the table.

The rigidity when the applied preload is not 10% of the basic dynamic load rating (Ca) is calculated using the equation (41) below.

$$K_N = K \left( \frac{Fa_0}{0.1Ca} \right)^{\frac{1}{3}} \times 0.8 \quad \dots\dots(41)$$

$K_N$  : Axial rigidity of the nut (N/ $\mu$ m)

$K$  : Rigidity value in the specification tables (N/ $\mu$ m)

$Fa_0$  : Applied preload (N)

$Ca$  : Basic dynamic load rating (N)

### [Axial rigidity of the support bearing]

The rigidity of the Ball Screw support bearing varies depending on the support bearing used.

The calculation of the rigidity with a representative angular contact ball bearing is shown in the equation (42) below.

$$K_B \doteq \frac{3Fa_0}{\delta a_0} \quad \dots\dots(42)$$

$K_B$  : Axial rigidity of the support bearing (N/ $\mu$ m)

$Fa_0$  : Applied preload of the support bearing (N)

$\delta a_0$  : Axial displacements ( $\mu$ m)

$$\delta a_0 = \frac{0.45}{\sin\alpha} \left( \frac{Q^2}{Da} \right)^{\frac{1}{3}}$$

$$Q = \frac{Fa_0}{Z\sin\alpha}$$

$Q$  : Axial load (N)

$Da$  : Ball diameter of the support bearing (mm)

$\alpha$  : Initial contact angle of the support bearing ( $^\circ$ )

$Z$  : Number of balls

For details of a specific support bearing, contact its manufacturer.

### [Axial Rigidity of the Nut Bracket and the Support Bearing Bracket]

Take this factor into consideration when designing your machine. Set the rigidity as high as possible.

# Studying the Positioning Accuracy

---

## Causes of Error in the Positioning Accuracy

---

The causes of error in the positioning accuracy include the lead angle accuracy, the axial clearance and the axial rigidity of the feed screw system. Other important factors include the thermal displacement from heat and the orientation change of the guide system during traveling.

---

## Studying the Lead Angle Accuracy

---

It is necessary to select the correct accuracy grade of the Ball Screw that satisfies the required positioning accuracy from the Ball Screw accuracies (Table1 on [B15-20](#)). Table3 on [B15-56](#) shows examples of selecting the accuracy grades by the application.

---

## Studying the Axial Clearance

---

The axial clearance is not a factor of positioning accuracy in single-directional feed. However, it will cause a backlash when the feed direction is inversed or the axial load is inversed. Select an axial clearance that meets the required backlash from Table10 and Table13 on [B15-27](#).

Table3 Examples of Selecting Accuracy Grades by Application


| Applications                               |  | Shaft    | Accuracy grades |    |    |    |    |    |    |     |
|--|--|----------|-----------------|----|----|----|----|----|----|-----|
|  |  |          | C0              | C1 | C2 | C3 | C5 | C7 | C8 | C10 |
| NC machine tools                           | Lathe                                  | X        |                 | ●  | ●  | ●  | ●  |    |    |     |
|  |  | Z        |                 |    |    | ●  | ●  |    |    |     |
|  | Machining center                       | XY       |                 |    | ●  | ●  | ●  |    |    |     |
|  |  | Z        |                 |    | ●  | ●  | ●  |    |    |     |
|  | Drilling machine                       | XY       |                 |    |    | ●  | ●  |    |    |     |
|  |  | Z        |                 |    |    |    | ●  | ●  |    |     |
|  | Jig borer                              | XY       | ●               | ●  |    |    |    |    |    |     |
|  |  | Z        | ●               | ●  |    |    |    |    |    |     |
|  | Surface grinder                        | X        |                 |    |    | ●  | ●  |    |    |     |
|  |  | Y        |                 | ●  | ●  | ●  | ●  |    |    |     |
|  |  | Z        |                 | ●  | ●  | ●  | ●  |    |    |     |
|  | Cylindrical grinder                    | X        | ●               | ●  | ●  |    |    |    |    |     |
|  |  | Z        |                 | ●  | ●  | ●  |    |    |    |     |
|  | Electric discharge machine             | XY       | ●               | ●  | ●  |    |    |    |    |     |
|  |  | Z        |                 | ●  | ●  | ●  | ●  |    |    |     |
|  | Electric discharge machine             | XY       | ●               | ●  | ●  |    |    |    |    |     |
|  |  | Z        | ●               | ●  | ●  | ●  |    |    |    |     |
|  | Wire cutting machine                   | UV       |                 | ●  | ●  | ●  |    |    |    |     |
|  |  | XY       |                 |    |    | ●  | ●  | ●  |    |     |
|  | Laser beam machine                     | X        |                 |    |    | ●  | ●  | ●  |    |     |
| Z  |  |          |                 |    | ●  | ●  | ●  |    |    |     |
| Woodworking machine                        |  |          |                 |    |    | ●  | ●  | ●  | ●  |     |
| General-purpose machine; dedicated machine |  |          |                 |    | ●  | ●  | ●  | ●  | ●  |     |
| Industrial robot                           | Cartesian coordinate                   | Assembly |                 |    |    | ●  | ●  | ●  | ●  |     |
|  |  | Other    |                 |    |    |    | ●  | ●  | ●  | ●   |
|  | Vertical articulated type              | Assembly |                 |    |    |    | ●  | ●  | ●  |     |
|  |  | Other    |                 |    |    |    |    | ●  | ●  |     |
| Cylindrical coordinate                     |  |          |                 |    | ●  | ●  | ●  |    |    |     |
| Semiconductor manufacturing machine        | Photolithography machine               |          | ●               | ●  |    |    |    |    |    |     |
|  | Chemical treatment machine             |          |                 |    | ●  | ●  | ●  | ●  | ●  |     |
|  | Wire bonding machine                   |          |                 | ●  | ●  |    |    |    |    |     |
|  | Prober                                 |          | ●               | ●  | ●  | ●  |    |    |    |     |
|  | Printed circuit board drilling machine |          |                 | ●  | ●  | ●  | ●  | ●  |    |     |
|  | Electronic component inserter          |          |                 |    | ●  | ●  | ●  | ●  |    |     |
| 3D measuring instrument                    |  | ●        | ●               | ●  |    |    |    |    |    |     |
| Image processing machine                   |  | ●        | ●               | ●  |    |    |    |    |    |     |
| Injection molding machine                  |  |          |                 |    |    |    | ●  | ●  | ●  |     |
| Office equipment                           |  |          |                 |    |    | ●  | ●  | ●  | ●  |     |

## Studying the Axial Clearance of the Feed Screw System

Of the axial rigidities of the feed screw system, the axial rigidity of the screw shaft fluctuates according to the stroke position. When the axial rigidity is large, such change in the axial rigidity of the screw shaft will affect the positioning accuracy. Therefore, it is necessary to take into account the rigidity of the feed screw system (**B15-51** to **B15-54**).

### Example of considering the rigidity of a feed screw system

Example: Positioning error due to the axial rigidity of the feed screw system during a vertical transfer



[Conditions]

Transferred weight: 1,000 N; table weight: 500 N

Ball Screw used: model BNF2512-2.5 (screw-shaft thread minor diameter  $d_1 = 21.9$  mm)

Stroke length: 600 mm ( $L=100$  mm to 700 mm)

Screw shaft mounting type: fixed-supported

[Consideration]

The difference in axial rigidity between  $L = 100$  mm and  $L = 700$  mm applied only to the axial rigidity of the screw shaft.

Therefore, positioning error due to the axial rigidity of the feed screw system equals to the difference in the axial displacement of the screw shaft between  $L = 100$  mm and  $L = 700$  mm.

**[Axial Rigidity of the Screw Shaft (see B15-51 and B15-52)]**

$$K_s = \frac{A \cdot E}{1000L} = \frac{376.5 \times 2.06 \times 10^5}{1000 \times L} = \frac{77.6 \times 10^3}{L}$$

$$A = \frac{\pi}{4} d_1^2 = \frac{\pi}{4} \times 21.9^2 = 376.5 \text{ mm}^2$$

$$E = 2.06 \times 10^5 \text{ N/mm}^2$$

(1) When L = 100 mm

$$K_{s1} = \frac{77.6 \times 10^3}{100} = 776 \text{ N/}\mu\text{m}$$

(2) When L = 700mm

$$K_{s2} = \frac{77.6 \times 10^3}{700} = 111 \text{ N/}\mu\text{m}$$

**[Axial Displacement due to Axial Rigidity of the Screw Shaft]**

(1) When L = 100 mm

$$\delta_1 = \frac{Fa}{K_{s1}} = \frac{1000+500}{776} = 1.9 \text{ }\mu\text{m}$$

(2) When L = 700mm

$$\delta_2 = \frac{Fa}{K_{s2}} = \frac{1000+500}{111} = 13.5 \text{ }\mu\text{m}$$

**[Positioning Error due to Axial Rigidity of the Feed Screw System]**

$$\begin{aligned} \text{Positioning accuracy} &= \delta_1 - \delta_2 = 1.9 - 13.5 \\ &= -11.6 \text{ }\mu\text{m} \end{aligned}$$

Therefore, the positioning error due to the axial rigidity of the feed screw system is 11.6  $\mu\text{m}$ .

## Studying the Thermal Displacement through Heat Generation

If the temperature of the screw shaft increases during operation, the screw shaft is elongated due to heat thereby to lower the positioning accuracy. The expansion and contraction of the screw shaft is calculated using the equation (43) below.

$$\Delta l = \rho \times \Delta t \times l \quad \dots\dots(43)$$

$\Delta l$  : Axial expansion/contraction of the screw shaft (mm)

$\rho$  : Thermal expansion coefficient ( $12 \times 10^{-6}/^{\circ}\text{C}$ )

$\Delta t$  : Temperature change in the screw shaft ( $^{\circ}\text{C}$ )

$l$  : Effective thread length (mm)

Thus, if the temperature of the screw shaft increases by  $1^{\circ}\text{C}$ , the screw shaft is elongated by  $12 \mu\text{m}$  per meter. Therefore, as the Ball Screw travels faster, the more heat is generated. So, as the temperature increases, the positioning accuracy lowers. Accordingly, if high accuracy is required, it is necessary to take measures to cope with the temperature increase.

### [Measures to Cope with the Temperature Rise]

#### ● Minimize the Heat Generation

- Minimize the preloads on the Ball Screw and the support bearing.
- Increase the Ball Screw lead and reduce the rotational speed.
- Select a correct lubricant. (See Accessories for Lubrication on **A24-2**.)
- Cool the circumference of the screw shaft with a lubricant or air.

#### ● Avoid Effect of Temperature Rise through Heat Generation

- Set a negative target value for the reference travel distance of the Ball Screw.  
Generally, set a negative target value for the reference travel distance assuming a temperature increase of  $2^{\circ}\text{C}$  to  $5^{\circ}\text{C}$  by heat.  
( $-0.02\text{mm}$  to  $-0.06 \text{mm/m}$ )
- Preload the shaft screw with tension. (See Fig.3 of the structure on **B15-37**.)

## Studying the Orientation Change during Traveling

The lead angle accuracy of the Ball Screw equals the positioning accuracy of the shaft center of the Ball Screw. Normally, the point where the highest positioning accuracy is required changes according to the ball screw center and the vertical or horizontal direction. Therefore, the orientation change during traveling affects the positioning accuracy.

The largest factor of orientation change affecting the positioning accuracy is pitching if the change occurs in the ball screw center and the vertical direction, and yawing if the change occurs in the horizontal direction.

Accordingly, it is necessary to study the orientation change (accuracy in pitching, yawing, etc.) during the traveling on the basis of the distance from the ball screw center to the location where positioning accuracy is required.

Positioning error due to pitching and yawing is obtained using the equation (44) below.

$$A = \ell \times \sin\theta \quad \dots\dots(44)$$

A : Positioning accuracy due to pitching (or yawing) (mm)

$\ell$  : Vertical (or horizontal) distance from the ball screw center (mm) (see Fig.9)

$\theta$  : Pitching (or yawing) ( $^{\circ}$ )




Fig.9



## Studying the Rotational Torque

The rotational torque required to convert rotational motion of the Ball Screw into straight motion is obtained using the equation (45) below.

### [During Uniform Motion]

$$\mathbf{T_t = (T_1 + T_2 + T_4) \cdot A} \dots\dots\dots(45)$$

- $T_t$  : Rotation torque required during uniform motion (N·mm)  
 $T_1$  : Friction torque due to an external load (N·mm)  
 $T_2$  : Preload torque of the Ball Screw (N·mm)  
 $T_4$  : Other torque (N·mm)  
 (frictional torque of the support bearing and oil seal)  
 $A$  : Reduction ratio

### [During Acceleration]

$$\mathbf{T_k = T_t + T_3} \dots\dots\dots(46)$$

- $T_k$  : Rotation torque required during acceleration (N·mm)  
 $T_3$  : Torque required for acceleration (N·mm)

### [During Deceleration]

$$\mathbf{T_g = T_t - T_3} \dots\dots\dots(47)$$

- $T_g$  : Rotational torque required for deceleration (N·mm)

---

## Frictional Torque Due to an External Load

---

Of the turning forces required for the Ball Screw, the rotational torque needed for an external load (guide surface resistance or external force) is obtained using the equation (48) below.

$$\mathbf{T_1 = \frac{F_a \cdot Ph}{2\pi \cdot \eta}} \dots\dots\dots(48)$$

- $T_1$  : Friction torque due to an external load (N·mm)  
 $F_a$  : Applied load (N)  
 $Ph$  : Ball Screw lead (mm)  
 $\eta$  : Ball Screw efficiency (0.9 to 0.95)

---

## Torque Due to a Preload on the Ball Screw

---

For a preload on the Ball Screw, see “Preload Torque” on [B15-30](#).

## Torque Required for Acceleration

$$T_3 = J \times \omega' \times 10^3 \dots\dots(49)$$

$T_3$  : Torque required for acceleration (N·mm)

$J$  : Inertial moment (kg·m<sup>2</sup>)

$\omega'$  : Angular acceleration (rad/s<sup>2</sup>)

$$J = m \left( \frac{Ph}{2\pi} \right)^2 \cdot A^2 \cdot 10^{-6} + J_s \cdot A^2 + J_A \cdot A^2 + J_B$$

$m$  : Transferred mass (kg)

$Ph$  : Ball Screw lead (mm)

$J_s$  : Inertial moment of the screw shaft (kg·m<sup>2</sup>)  
(indicated in the specification tables of the respective model number)

$A$  : Reduction ratio

$J_A$  : Inertial moment of gears, etc. attached to the screw shaft side (kg·m<sup>2</sup>)

$J_B$  : Inertial moment of gears, etc. attached to the motor side (kg·m<sup>2</sup>)

$$\omega' = \frac{2\pi \cdot Nm}{60t}$$

$Nm$  : Motor revolutions per minute (min<sup>-1</sup>)

$t$  : Acceleration time (s)

[Ref.] Inertial moment of a round object

$$J = \frac{m \cdot D^2}{8 \cdot 10^6}$$

$J$  : Inertial moment (kg·m<sup>2</sup>)

$m$  : Mass of a round object (kg)

$D$  : Screw shaft outer diameter (mm)

## Investigating the Terminal Strength of Ball Screw Shafts

When torque is conveyed through the screw shaft in a ball screw, the strength of the screw shaft must be taken into consideration since it experiences both torsion load and bending load.

### [Screw shaft under torsion]

When torsion load is applied to the end of a ball screw shaft, use equation (50) to obtain the end diameter of the screw shaft.

$$T = \tau_a \cdot Z_P \quad \text{and} \quad Z_P = \frac{T}{\tau_a} \quad \dots\dots(50)$$


$T$  : Maximum torsion moment (N·mm)

$\tau_a$  : Permissible torsion stress of the screw Shaft (49 N/mm<sup>2</sup>)

$Z_P$  : Section modulus (mm<sup>3</sup>)

$$Z_P = \frac{\pi \cdot d^3}{16}$$

T: Torsion moment



### [Screw shaft under bending]

When bending load is applied to the end of a ball screw shaft, use equation (51) to obtain the end diameter of the screw shaft.

$$M = \sigma \cdot Z \quad \text{and} \quad Z = \frac{M}{\sigma} \quad \dots\dots(51)$$


$M$  : Maximum bending moment (N·mm)

$\sigma$  : Permissible bending stress of the screw shaft (98 N/mm<sup>2</sup>)

$Z$  : Section Modulus (mm<sup>3</sup>)

$$Z = \frac{\pi \cdot d^3}{32}$$

M: Bending moment



## Point of Selection

### Studying the Rotational Torque

#### [If the shaft experiences both torsion and bending]

When torsion load and bending load are both applied simultaneously to the end of a ball screw shaft, calculate the diameter of the screw shaft separately for each, taking into consideration the corresponding bending moment ( $M_e$ ) and the corresponding torsion moment ( $T_e$ ). Then calculate the thickness of the screw shaft and use the largest of the values.

#### Equivalent bending moment

$$M_e = \frac{M + \sqrt{M^2 + T^2}}{2} = \frac{M}{2} \left\{ 1 + \sqrt{1 + \left(\frac{T}{M}\right)^2} \right\}$$

$$M_e = \sigma \cdot Z$$

#### Equivalent torsion moment

$$T_e = \sqrt{M^2 + T^2} = M \cdot \sqrt{1 + \left(\frac{T}{M}\right)^2}$$

$$T_e = \tau_a \cdot Z_P$$

## Studying the Driving Motor

When selecting a driving motor required to rotate the Ball Screw, normally take into account the rotational speed, rotational torque and minimum feed amount.

---

### When Using a Servomotor

---

#### [Rotational Speed]

The rotation speed required for the motor is obtained using the equation (52) based on the feed speed, Ball Screw lead and reduction ratio.

$$N_M = \frac{V \times 1000 \times 60}{Ph} \times \frac{1}{A} \dots\dots(52)$$

- $N_M$  : Required rotation speed of the motor ( $\text{min}^{-1}$ )  
 $V$  : Feeding speed (m/s)  
 $Ph$  : Ball Screw lead (mm)  
 $A$  : Reduction ratio

The rated rotational speed of the motor must be equal to or above the calculated value ( $N_M$ ) above.

$$N_M \leq N_R$$

- $N_R$  : The rated rotation speed of the motor ( $\text{min}^{-1}$ )

#### [Required Resolution]

Resolutions required for the encoder and the driver are obtained using the equation (53) based on the minimum feed amount, Ball Screw lead and reduction ratio.

$$B = \frac{Ph \cdot A}{S} \dots\dots(53)$$

- $B$  : Resolution required for the encoder and the driver (p/rev)  
 $Ph$  : Ball Screw lead (mm)  
 $A$  : Reduction ratio  
 $S$  : Minimum feed amount (mm)

**[Motor Torque]**

The torque required for the motor differs between uniform motion, acceleration and deceleration. To calculate the rotational torque, see “Studying the Rotational Torque” on **B15-61**.

a. Maximum torque

The maximum torque required for the motor must be equal to or below the maximum peak torque of the motor.

$$T_{\max} \leq T_{p\max}$$

$T_{\max}$  : Maximum torque acting on the motor

$T_{p\max}$  : Maximum peak torque of the motor

b. Effective torque value

The effective value of the torque required for the motor must be calculated. The effective value of the torque is obtained using the equation (54).

$$T_{\text{rms}} = \sqrt{\frac{T_1^2 \times t_1 + T_2^2 \times t_2 + T_3^2 \times t_3}{t}} \dots\dots\dots(54)$$

$T_{\text{rms}}$  : Effective torque value (N·mm)

$T_n$  : Fluctuating torque (N·mm)

$t_n$  : Time during which the torque  $T_n$  is applied (s)

$t$  : Cycle time (s)

$$(t=t_1+t_2+t_3)$$

The calculated effective value of the torque must be equal to or below the rated torque of the motor.

$$T_{\text{rms}} \leq T_R$$

$T_R$  : Rated torque of the motor (N·mm)

**[Inertial Moment]**

The inertial moment required for the motor is obtained using the equation (55).

$$J_M = \frac{J}{C} \dots\dots\dots(55)$$

$J_M$  : Inertial moment required for the motor (kg·m<sup>2</sup>)

$C$  : Factor determined by the motor and the driver

(It is normally between 3 to 10. However, it varies depending on the motor and the driver. Check the specific value in the catalog by the motor manufacturer.)

The inertial moment of the motor must be equal to or above the calculated  $J_M$  value.

## When Using a Stepping Motor (Pulse Motor)

### [Minimal Feed Amount(per Step)]

The step angle required for the motor and the driver is obtained using the equation (56) based on the minimum feed amount, Ball Screw lead and reduction ratio.

$$E = \frac{360S}{Ph \cdot A} \dots\dots(56)$$

E : Step angle required for the motor and the driver (°)

S : Minimum feed amount (mm)  
(per step)

Ph : Ball Screw lead (mm)

A : Reduction ratio

### [Pulse Speed and Motor Torque]

#### a. Pulse speed

The pulse speed is obtained using the equation (57) based on the feed speed and the minimum feed amount.

$$f = \frac{V \times 1000}{S} \dots\dots(57)$$

f : Pulse speed (Hz)

V : Feeding speed (m/s)

S : Minimum feed amount (mm)

#### b. Torque required for the motor

The torque required for the motor differs between the uniform motion, the acceleration and the deceleration. To calculate the rotational torque, see “Studying the Rotational Torque” on **B15-61**.

Thus, the pulse speed required for the motor and the required torque can be calculated in the manner described above.

Although the torque varies depending on the motors, normally the calculated torque should be doubled to ensure safety. Check if the torque can be used in the motor’s speed-torque curve.




# Examples of Selecting a Ball Screw

## High-speed Transfer Equipment (Horizontal Use)

### [Selection Conditions]

|                                     |   |   |  |
|-------------------------------------|---|---|--|
| Table Mass                          | $m_1 = 60 \text{ kg}$   | Positioning accuracy repeatability          | $\pm 0.1 \text{ mm}$                               |
| Work Mass                           | $m_2 = 20 \text{ kg}$   | Minimum feed amount                         | $s = 0.02 \text{ mm/pulse}$                        |
| Stroke length                       | $l_s = 1000 \text{ mm}$   | Desired service life time                   | 30000 h  |
| Maximum speed                       | $V_{\max} = 1 \text{ m/s}$  | Driving motor                               | AC servo motor                                     |
| Acceleration time                   | $t_1 = 0.15 \text{ s}$  |   | Rated rotational speed:                            |
| Deceleration time                   | $t_3 = 0.15 \text{ s}$  |   | $3,000 \text{ min}^{-1}$                           |
| Number of reciprocations per minute | $n = 8 \text{ min}^{-1}$  | Inertial moment of the motor                | $J_m = 1 \times 10^{-3} \text{ kg}\cdot\text{m}^2$ |
| Backlash                            | 0.15 mm   | Reduction gear                              | None (direct coupling) $A=1$                       |
| Positioning accuracy                | $\pm 0.3 \text{ mm}/1000 \text{ mm}$<br>(Perform positioning from the negative direction) | Frictional coefficient of the guide surface | $\mu = 0.003$ (rolling)                            |
|                                     |   | Guide surface resistance                    | $f = 15 \text{ N}$ (without load)                  |



### [Selection Items]

- Screw shaft diameter
- Lead
- Nut model No.
- Accuracy
- Axial clearance
- Screw shaft support method
- Driving motor

### [Selecting Lead Angle Accuracy and Axial Clearance]

#### ● Selecting Lead Angle Accuracy

To achieve positioning accuracy of  $\pm 0.3$  mm/1,000 mm:

$$\frac{\pm 0.3}{1000} = \frac{\pm 0.09}{300}$$

The lead angle accuracy must be  $\pm 0.09$  mm/300 mm or higher.

Therefore, select the following as the accuracy grade of the Ball Screw (see Table1 on **B 15-20**).

C7 (travel distance error:  $\pm 0.05$ mm/300mm)

Accuracy grade C7 is available for both the Rolled and the Precision Ball Screws. Assume that a Rolled Ball Screw is selected here because it is less costly.

#### ● Selecting Axial Clearance

To satisfy the backlash of 0.15 mm, it is necessary to select a Ball Screw with an axial clearance of 0.15 mm or less.

Therefore, a Rolled Ball Screw model with a screw shaft diameter of 32 mm or less that meets the axial clearance of 0.15 mm or less (see Table13 on **B 15-27**) meets the requirements.

Thus, a Rolled Ball Screw model with a screw shaft diameter of 32 mm or less and an accuracy grade of C7 is selected.

### [Selecting a Screw Shaft]

#### ● Assuming the Screw Shaft Length

Assume the overall nut length to be 100 mm and the screw shaft end length to be 100 mm.

Therefore, the overall length is determined as follows based on the stroke length of 1,000 mm.

$$1000 + 200 = 1200 \text{ mm}$$

Thus, the screw shaft length is assumed to be 1,200 mm.

#### ● Selecting a Lead

With the driving motor's rated rotational speed being  $3,000 \text{ min}^{-1}$  and the maximum speed 1 m/s, the Ball Screw lead is obtained as follows:

$$\frac{1 \times 1000 \times 60}{3000} = 20 \text{ mm}$$

Therefore, it is necessary to select a type with a lead of 20 mm or longer.

In addition, the Ball Screw and the motor can be mounted in direct coupling without using a reduction gear. The minimum resolution per revolution of an AC servomotor is obtained based on the resolution of the encoder (1,000 p/rev; 1,500 p/rev) provided as a standard accessory for the AC servomotor, as indicated below.

1000 p/rev(without multiplication)

1500 p/rev(without multiplication)

2000 p/rev(doubled)

3000 p/rev(doubled)

4000 p/rev(quadrupled)

6000 p/rev(quadrupled)

To meet the minimum feed amount of 0.02 mm/pulse, which is the selection requirement, the following should apply.

|      |       |   |            |
|------|-------|---|------------|
| Lead | 20 mm | — | 1000 p/rev |
|      | 30 mm | — | 1500 p/rev |
|      | 40 mm | — | 2000 p/rev |
|      | 60 mm | — | 3000 p/rev |
|      | 80 mm | — | 4000 p/rev |

### ● Selecting a Screw Shaft Diameter

Those Ball Screw models that meet the requirements defined in Section [Selecting Lead Angle Accuracy and Axial Clearance] on **B15-70**: a rolled Ball Screw with a screw shaft diameter of 32 mm or less; and the requirement defined in Section [Selecting a Screw Shaft] on **B15-70**: a lead of 20, 30, 40, 60 or 80 mm (see Table20 on **B15-35**) are as follows.

| Shaft diameter | Lead    |
|----------------|---------|
| 15 mm          | — 20 mm |
| 15 mm          | — 30 mm |
| 20 mm          | — 20 mm |
| 20 mm          | — 40 mm |
| 30 mm          | — 60 mm |

Since the screw shaft length has to be 1,200 mm as indicated in Section [Selecting a Screw Shaft] on **B15-70**, the shaft diameter of 15 mm is insufficient. Therefore, the Ball Screw should have a screw shaft diameter of 20 mm or greater.

Accordingly, there are three combinations of screw shaft diameters and leads that meet the requirements: screw shaft diameter of 20 mm/lead of 20 mm; 20 mm/40 mm; and 30 mm/60 mm.

### ● Selecting a Screw Shaft Support Method

Since the assumed type has a long stroke length of 1,000 mm and operates at high speed of 1 m/s, select either the fixed-supported or fixed-fixed configuration for the screw shaft support.

However, the fixed-fixed configuration requires a complicated structure, needs high accuracy in the installation.

Accordingly, the fixed-supported configuration is selected as the screw shaft support method.

## ● Studying the Permissible Axial Load

### ■ Calculating the Maximum Axial Load

|   |                                 |
|---|---------------------------------|
| Guide surface resistance                    | $f=15 \text{ N}$ (without load) |
| Table Mass                                  | $m_1 =60 \text{ kg}$            |
| Work Mass                                   | $m_2 =20 \text{ kg}$            |
| Frictional coefficient of the guide surface | $\mu= 0.003$                    |
| Maximum speed                               | $V_{\max}=1 \text{ m/s}$        |
| Gravitational acceleration                  | $g = 9.807 \text{ m/s}^2$       |
| Acceleration time                           | $t_1 = 0.15 \text{ s}$          |

Accordingly, the required values are obtained as follows.

Acceleration:

$$\alpha = \frac{V_{\max}}{t_1} = 6.67 \text{ m/s}^2$$

During forward acceleration:

$$Fa_1 = \mu \cdot (m_1 + m_2) g + f + (m_1 + m_2) \cdot \alpha = 550 \text{ N}$$

During forward uniform motion:

$$Fa_2 = \mu \cdot (m_1 + m_2) g + f = 17 \text{ N}$$

During forward deceleration:

$$Fa_3 = \mu \cdot (m_1 + m_2) g + f - (m_1 + m_2) \cdot \alpha = -516 \text{ N}$$

During backward acceleration:

$$Fa_4 = -\mu \cdot (m_1 + m_2) g - f - (m_1 + m_2) \cdot \alpha = -550 \text{ N}$$

During uniform backward motion:

$$Fa_5 = -\mu \cdot (m_1 + m_2) g - f = -17 \text{ N}$$

During backward deceleration:

$$Fa_6 = -\mu \cdot (m_1 + m_2) g - f + (m_1 + m_2) \cdot \alpha = 516 \text{ N}$$

Thus, the maximum axial load applied on the Ball Screw is as follows:

$$Fa_{\max} = Fa_1 = 550 \text{ N}$$

Therefore, if there is no problem with a shaft diameter of 20 mm and a lead of 20 mm (smallest thread minor diameter of 17.5 mm), then the screw shaft diameter of 30 mm should meet the requirements. Thus, the following calculations for the buckling load and the permissible compressive and tensile load of the screw shaft are performed while assuming a screw shaft diameter of 20 mm and a lead of 20 mm.

### ■ Buckling Load on the Screw Shaft

Factor according to the mounting method

$\eta_2=20$  (see **B15-38**)

Since the mounting method for the section between the nut and the bearing, where buckling is to be considered, is “fixed-fixed: “

Distance between two mounting surfaces

$\ell_a=1100$  mm (estimate)

Screw-shaft thread minor diameter

$d_1=17.5$  mm

$$P_1 = \eta_2 \cdot \frac{d_1^4}{\ell_a^2} \times 10^4 = 20 \times \frac{17.5^4}{1100^2} \times 10^4 = 15500 \text{ N}$$

### ■ Permissible Compressive and Tensile Load of the Screw Shaft

$$P_2 = 116 \times d_1^2 = 116 \times 17.5^2 = 35500 \text{ N}$$

Thus, the buckling load and the permissible compressive and the tensile load of the screw shaft are at least equal to the maximum axial load. Therefore, a Ball Screw that meets these requirements can be used without a problem.

### ● Studying the Permissible Rotational Speed

#### ■ Maximum Rotational Speed

- Screw shaft diameter: 20 mm; lead: 20 mm

Maximum speed  $V_{\max}=1$  m/s

Lead  $Ph=20$  mm

$$N_{\max} = \frac{V_{\max} \times 60 \times 10^3}{Ph} = 3000 \text{ min}^{-1}$$

- Screw shaft diameter: 20 mm; lead: 40 mm

Maximum speed  $V_{\max}=1$  m/s

Lead  $Ph=40$  mm

$$N_{\max} = \frac{V_{\max} \times 60 \times 10^3}{Ph} = 1500 \text{ min}^{-1}$$

- Screw shaft diameter: 30 mm; lead: 60 mm

Maximum speed  $V_{\max}=1$  m/s

Lead  $Ph=60$  mm

$$N_{\max} = \frac{V_{\max} \times 60 \times 10^3}{Ph} = 1000 \text{ min}^{-1}$$

### ■ Permissible Rotational Speed Determined by the Dangerous Speed of the Screw Shaft

Factor according to the mounting method

$$\lambda_2 = 15.1 \text{ (see B15-40)}$$

Since the mounting method for the section between the nut and the bearing, where dangerous speed is to be considered, is "fixed-supported: "

Distance between two mounting surfaces

$$\ell_b = 1100 \text{ mm (estimate)}$$

- Screw shaft diameter: 20 mm; lead: 20 mm and 40 mm

Screw-shaft thread minor diameter

$$d_i = 17.5 \text{ mm}$$

$$N_1 = \lambda_2 \times \frac{d_1}{\ell_b^2} 10^7 = 15.1 \times \frac{17.5}{1100^2} \times 10^7 = 2180 \text{ min}^{-1}$$

- Screw shaft diameter: 30 mm; lead: 60 mm

Screw-shaft thread minor diameter

$$d_i = 26.4 \text{ mm}$$

$$N_1 = \lambda_2 \times \frac{d_1}{\ell_b^2} 10^7 = 15.1 \times \frac{26.4}{1100^2} \times 10^7 = 3294 \text{ min}^{-1}$$

### ■ Permissible Rotational Speed Determined by the DN Value

- Screw shaft diameter: 20 mm; lead: 20 mm and 40 mm (large lead Ball Screw)

Ball center-to-center diameter

$$D = 20.75 \text{ mm}$$

$$N_2 = \frac{70000}{D} = \frac{70000}{20.75} = 3370 \text{ min}^{-1}$$

- Screw shaft diameter: 30 mm; lead: 60 mm (large lead Ball Screw)

Ball center-to-center diameter

$$D = 31.25 \text{ mm}$$

$$N_2 = \frac{70000}{D} = \frac{70000}{31.25} = 2240 \text{ min}^{-1}$$

Thus, with a Ball Screw having a screw shaft diameter of 20 mm and a lead of 20 mm, the maximum rotational speed exceeds the dangerous speed.

In contrast, a combination of a screw shaft diameter of 20 mm and a lead of 40 mm, and another of a screw shaft diameter of 30 mm and a lead of 60 mm, meet the dangerous speed and the DN value.

Accordingly, a Ball Screw with a screw shaft diameter of 20 mm and a lead of 40 mm, or with a screw shaft diameter of 30 mm and a lead of 60 mm, is selected.

### [Selecting a Nut]

#### ● Selecting a Nut Model Number

Rolled Ball Screw models with a screw shaft diameter of 20 mm and a lead of 40 mm, or with a screw shaft diameter of 30 mm and a lead of 60 mm, are large lead Rolled Ball Screw model WTF variations.

WTF2040-2

(Ca=5.4 kN, C<sub>0a</sub>=13.6 kN)

WTF2040-3

(Ca=6.6 kN, C<sub>0a</sub>=17.2 kN)

WTF3060-2

(Ca=11.8 kN, C<sub>0a</sub>=30.6 kN)

WTF3060-3

(Ca=14.5 kN, C<sub>0a</sub>=38.9 kN)

### ● Studying the Permissible Axial Load

Study the permissible axial load of model WTF2040-2 ( $C_{0a} = 13.6$  kN).

Assuming that this model is used in high-speed transfer equipment and an impact load is applied during deceleration, set the static safety factor ( $f_s$ ) at 2.5 (see Table1 on **B15-47**).

$$\frac{C_{0a}}{f_s} = \frac{13.6}{2.5} = 5.44 \text{ kN} = 5440 \text{ N}$$

The obtained permissible axial load is greater than the maximum axial load of 550 N, and therefore, there will be no problem with this model.

### ■ Calculating the Travel Distance

Maximum speed  $V_{\max} = 1$  m/s

Acceleration time  $t_1 = 0.15$  s

Deceleration time  $t_3 = 0.15$  s

- Travel distance during acceleration

$$l_{1,4} = \frac{V_{\max} \cdot t_1}{2} \times 10^3 = \frac{1 \times 0.15}{2} \times 10^3 = 75 \text{ mm}$$

- Travel distance during uniform motion

$$l_{2,5} = l_s - \frac{V_{\max} \cdot t_1 + V_{\max} \cdot t_3}{2} \times 10^3 = 1000 - \frac{1 \times 0.15 + 1 \times 0.15}{2} \times 10^3 = 850 \text{ mm}$$

- Travel distance during deceleration

$$l_{3,6} = \frac{V_{\max} \cdot t_3}{2} \times 10^3 = \frac{1 \times 0.15}{2} \times 10^3 = 75 \text{ mm}$$

Based on the conditions above, the relationship between the applied axial load and the travel distance is shown in the table below.

| Motion                               | Applied axial load<br>$F_{a_i}$ (N) | Travel distance<br>$l_i$ (mm) |
|--------------------------------------|-------------------------------------|-------------------------------|
| No.1: During forward acceleration    | 550                                 | 75                            |
| No.2: During forward uniform motion  | 17                                  | 850                           |
| No.3: During forward deceleration    | -516                                | 75                            |
| No.4: During backward acceleration   | -550                                | 75                            |
| No.5: During uniform backward motion | -17                                 | 850                           |
| No.6: During backward deceleration   | 516                                 | 75                            |

\* The subscript (N) indicates a motion number.

Since the load direction (as expressed in positive or negative sign) is reversed with  $F_{a_3}$ ,  $F_{a_4}$  and  $F_{a_5}$ , calculate the average axial load in the two directions.

### ■ Average Axial Load

- Average axial load in the positive direction

Since the load direction varies, calculate the average axial load while assuming  $F_{a_{3,4,5}} = 0$  N.

$$F_{am1} = \sqrt[3]{\frac{F_{a1}^3 \times l_1 + F_{a2}^3 \times l_2 + F_{a6}^3 \times l_6}{l_1 + l_2 + l_3 + l_4 + l_5 + l_6}} = 225 \text{ N}$$

- Average axial load in the negative direction

Since the load direction varies, calculate the average axial load while assuming  $F_{a_{1,2,6}} = 0$  N.

$$F_{am2} = \sqrt[3]{\frac{|F_{a3}|^3 \times l_3 + |F_{a4}|^3 \times l_4 + |F_{a5}|^3 \times l_5}{l_1 + l_2 + l_3 + l_4 + l_5 + l_6}} = 225 \text{ N}$$

Since  $F_{am1} = F_{am2}$ , assume the average axial load to be  $F_{am} = F_{am1} = F_{am2} = 225$  N.

### ■ Nominal Life

Load factor  $f_w = 1.5$  (see Table2 on [B15-48](#))

Average load  $F_m = 225$  N

Nominal life  $L_{10m}$  (rev)

$$L_{10m} = \left( \alpha \times \frac{C_a}{F_{am}} \right)^3 \times 10^6$$

$$\alpha = \frac{1}{f_w}$$

| Assumed model number | Dynamic load rating Ca(N) | Nominal life $L_{10m}$ (rev) |
|----------------------|---------------------------|------------------------------|
| WTF 2040-2           | 5400                      | $4.1 \times 10^9$            |
| WTF 2040-3           | 6600                      | $7.47 \times 10^9$           |
| WTF 3060-2           | 11800                     | $4.27 \times 10^{10}$        |
| WTF 3060-3           | 14500                     | $7.93 \times 10^{10}$        |



### ■ Average Revolutions per Minute

Number of reciprocations per minute  $n = 8 \text{ min}^{-1}$   
 Stroke  $l_s = 1000 \text{ mm}$

- Lead:  $Ph = 40 \text{ mm}$

$$N_m = \frac{2 \times n \times l_s}{Ph} = \frac{2 \times 8 \times 1000}{40} = 400 \text{ min}^{-1}$$

- Lead:  $Ph = 60 \text{ mm}$

$$N_m = \frac{2 \times n \times l_s}{Ph} = \frac{2 \times 8 \times 1000}{60} = 267 \text{ min}^{-1}$$

### ■ Calculating the Service Life Time on the Basis of the Nominal Life

- WTF2040-2

Nominal life  $L_{10m} = 4.1 \times 10^9 \text{ rev}$   
 Average revolutions per minute  $N_m = 400 \text{ min}^{-1}$

$$L_h = \frac{L_{10m}}{60 \times N_m} = \frac{4.1 \times 10^9}{60 \times 400} = 171000 \text{ h}$$

- WTF2040-3

Nominal life  $L_{10m} = 7.47 \times 10^9 \text{ rev}$   
 Average revolutions per minute  $N_m = 400 \text{ min}^{-1}$

$$L_h = \frac{L_{10m}}{60 \times N_m} = \frac{7.47 \times 10^9}{60 \times 400} = 311000 \text{ h}$$

- WTF3060-2

Nominal life  $L_{10m} = 4.27 \times 10^{10} \text{ rev}$   
 Average revolutions per minute  $N_m = 267 \text{ min}^{-1}$

$$L_h = \frac{L_{10m}}{60 \times N_m} = \frac{4.27 \times 10^{10}}{60 \times 267} = 2670000 \text{ h}$$

- WTF3060-3

Nominal life  $L_{10m} = 7.93 \times 10^{10} \text{ rev}$   
 Average revolutions per minute  $N_m = 267 \text{ min}^{-1}$

$$L_h = \frac{L_{10m}}{60 \times N_m} = \frac{7.93 \times 10^{10}}{60 \times 267} = 4950000 \text{ h}$$

## ■ Calculating the Service Life in Travel Distance on the Basis of the Nominal Life

- WTF2040-2
 

|  |                               |
|--|-------------------------------|
| Nominal life   | $L_{10m}=4.1 \times 10^9$ rev |
| Lead   | Ph= 40 mm                     |
| $L_s = L_{10m} \times Ph \times 10^{-6} = 164000$ km |                               |
- WTF2040-3
 

|  |                                |
|--|--------------------------------|
| Nominal life   | $L_{10m}=7.47 \times 10^9$ rev |
| Lead   | Ph= 40 mm                      |
| $L_s = L_{10m} \times Ph \times 10^{-6} = 298800$ km |                                |
- WTF3060-2
 

|   |                                   |
|---|-----------------------------------|
| Nominal life  | $L_{10m}=4.27 \times 10^{10}$ rev |
| Lead  | Ph= 60 mm                         |
| $L_s = L_{10m} \times Ph \times 10^{-6} = 2562000$ km |                                   |
- WTF3060-3
 

|   |                                   |
|---|-----------------------------------|
| Nominal life  | $L_{10m}=7.93 \times 10^{10}$ rev |
| Lead  | Ph= 60 mm                         |
| $L_s = L_{10m} \times Ph \times 10^{-6} = 4758000$ km |                                   |

With all the conditions stated above, the following models satisfying the desired service life time of 30,000 hours are selected.

WTF 2040-2

WTF 2040-3

WTF 3060-2

WTF 3060-3

**[Studying the Rigidity]**

Since the conditions for selection do not include rigidity and this element is not particularly necessary, it is not described here.

**[Studying the Positioning Accuracy]****● Studying the Lead Angle Accuracy**

Accuracy grade C7 was selected in Section [Selecting Lead Angle Accuracy and Axial Clearance] on **B15-70**.

C7 (travel distance error:  $\pm 0.05\text{mm}/300\text{mm}$ )

**● Studying the Axial Clearance**

Since positioning is performed in a given direction only, axial clearance is not included in the positioning accuracy. As a result, there is no need to study the axial clearance.

WTF2040: axial clearance: 0.1 mm

WTF3060: axial clearance: 0.14 mm

**● Studying the Axial Rigidity**

Since the load direction does not change, it is unnecessary to study the positioning accuracy on the basis of the axial rigidity.

**● Studying the Thermal Displacement through Heat Generation**

Assume the temperature rise during operation to be  $5^{\circ}\text{C}$ .

The positioning accuracy based on the temperature rise is obtained as follows:

$$\begin{aligned}\Delta\ell &= \rho \times \Delta t \times \ell \\ &= 12 \times 10^{-6} \times 5 \times 1000 \\ &= 0.06 \text{ mm}\end{aligned}$$

**● Studying the Orientation Change during Traveling**

Since the ball screw center is 150 mm away from the point where the highest accuracy is required, it is necessary to study the orientation change during traveling.

Assume that pitching can be done within  $\pm 10$  seconds because of the structure. The positioning error due to the pitching is obtained as follows:

$$\begin{aligned}\Delta a &= \ell \times \sin\theta \\ &= 150 \times \sin(\pm 10'') \\ &= \pm 0.007 \text{ mm}\end{aligned}$$

Thus, the positioning accuracy ( $\Delta p$ ) is obtained as follows:

$$\Delta p = \frac{\pm 0.05 \times 1000}{300} \pm 0.007 + 0.06 = 0.234 \text{ mm}$$

Since models WTF2040-2, WTF2040-3, WTF3060-2 and WTF3060-3 meet the selection requirements throughout the studying process in Section [Selecting Lead Angle Accuracy and Axial Clearance] on **B15-70** to Section [Studying the Positioning Accuracy] on **B15-79**, the most compact model WTF2040-2 is selected.

### [Studying the Rotational Torque]

#### ● Friction Torque Due to an External Load

The friction torque is obtained as follows:

$$T_1 = \frac{F_a \cdot Ph}{2\pi \cdot \eta} \cdot A = \frac{17 \times 40}{2 \times \pi \times 0.9} \times 1 = 120 \text{ N}\cdot\text{mm}$$

#### ● Torque Due to a Preload on the Ball Screw

The Ball Screw is not provided with a preload.

#### ● Torque Required for Acceleration

Inertial Moment

Since the inertial moment per unit length of the screw shaft is  $1.23 \times 10^{-3} \text{ kg}\cdot\text{cm}^2/\text{mm}$  (see the specification table), the inertial moment of the screw shaft with an overall length of 1200 mm is obtained as follows.

$$J_s = 1.23 \times 10^{-3} \times 1200 = 1.48 \text{ kg}\cdot\text{cm}^2 \\ = 1.48 \times 10^{-4} \text{ kg}\cdot\text{m}^2$$

$$J = (m_1 + m_2) \left( \frac{Ph}{2 \times \pi} \right)^2 \cdot A^2 \times 10^{-6} + J_s \cdot A^2 = (60 + 20) \left( \frac{40}{2 \times \pi} \right)^2 \times 1^2 \times 10^{-6} + 1.48 \times 10^{-4} \times 1^2 \\ = 3.39 \times 10^{-3} \text{ kg}\cdot\text{m}^2$$

Angular acceleration:

$$\omega' = \frac{2\pi \cdot Nm}{60 \cdot t_1} = \frac{2\pi \times 1500}{60 \times 0.15} = 1050 \text{ rad/s}^2$$

Based on the above, the torque required for acceleration is obtained as follows.

$$T_2 = (J + J_m) \times \omega' = (3.39 \times 10^{-3} + 1 \times 10^{-3}) \times 1050 = 4.61 \text{ N}\cdot\text{m} \\ = 4.61 \times 10^3 \text{ N}\cdot\text{mm}$$

Therefore, the required torque is specified as follows.

During acceleration

$$T_k = T_1 + T_2 = 120 + 4.61 \times 10^3 = 4730 \text{ N}\cdot\text{mm}$$

During uniform motion

$$T_i = T_1 = 120 \text{ N}\cdot\text{mm}$$

During deceleration

$$T_g = T_i - T_2 = 120 - 4.61 \times 10^3 = -4490 \text{ N}\cdot\text{mm}$$

**[Studying the Driving Motor]****● Rotational Speed**

Since the Ball Screw lead is selected based on the rated rotational speed of the motor, it is unnecessary to study the rotational speed of the motor.

Maximum working rotational speed : 1500 min<sup>-1</sup>

Rated rotational speed of the motor: 3000 min<sup>-1</sup>

**● Minimum Feed Amount**

As with the rotational speed, the Ball Screw lead is selected based on the encoder normally used for an AC servomotor. Therefore, it is unnecessary to study this factor.

Encoder resolution: 1000 p/rev.

Doubled: 2000 p/rev

**● Motor Torque**

The torque during acceleration calculated in Section [Studying the Rotational Torque] on **B15-80** is the required maximum torque.

$$T_{\max} = 4730 \text{ N}\cdot\text{mm}$$

Therefore, the instantaneous maximum torque of the AC servomotor needs to be at least 4,730 N·mm.

**● Effective Torque Value**

The selection requirements and the torque calculated in Section [Studying the Rotational Torque] on **B15-80** can be expressed as follows.

During acceleration:

$$T_k = 4730 \text{ N}\cdot\text{mm}$$

$$t_1 = 0.15 \text{ s}$$

During uniform motion:

$$T_l = 120 \text{ N}\cdot\text{mm}$$

$$t_2 = 0.85 \text{ s}$$

During deceleration:

$$T_g = 4490 \text{ N}\cdot\text{mm}$$

$$t_3 = 0.15 \text{ s}$$

When stationary:

$$T_s = 0$$

$$t_4 = 2.6 \text{ s}$$

The effective torque is obtained as follows, and the rated torque of the motor must be 1305 N·mm or greater.

$$T_{\text{rms}} = \sqrt{\frac{T_k^2 \cdot t_1 + T_l^2 \cdot t_2 + T_g^2 \cdot t_3 + T_s^2 \cdot t_4}{t_1 + t_2 + t_3 + t_4}} = \sqrt{\frac{4730^2 \times 0.15 + 120^2 \times 0.85 + 4490^2 \times 0.15 + 0}{0.15 + 0.85 + 0.15 + 2.6}}$$

$$= 1305 \text{ N}\cdot\text{mm}$$

- **Inertial Moment**

The inertial moment applied to the motor equals to the inertial moment calculated in Section [Studying the Rotational Torque] on **B15-80**.

$$J = 3.39 \times 10^{-3} \text{ kg} \cdot \text{m}^2$$

Normally, the motor needs to have an inertial moment at least one tenth of the inertial moment applied to the motor, although the specific value varies depending on the motor manufacturer.


Therefore, the inertial moment of the AC servomotor must be  $3.39 \times 10^{-4} \text{ kg} \cdot \text{m}^2$  or greater.

The selection has been completed.

## Vertical Conveyance System

### [Selection Conditions]

|   |  |
|---|--|
| Table Mass                                  | $m_1 = 40 \text{ kg}$                                |
| Work Mass                                   | $m_2 = 10 \text{ kg}$                                |
| Stroke length                               | $l_s = 600 \text{ mm}$                               |
| Maximum speed                               | $V_{\max} = 0.3 \text{ m/s}$                         |
| Acceleration time                           | $t_1 = 0.2 \text{ s}$                                |
| Deceleration time                           | $t_3 = 0.2 \text{ s}$                                |
| Number of reciprocations per minute         | $n = 5 \text{ min}^{-1}$                             |
| Backlash                                    | $0.1 \text{ mm}$                                     |
| Positioning accuracy                        | $\pm 0.7 \text{ mm}/600 \text{ mm}$                  |
| Positioning accuracy repeatability          | $\pm 0.05 \text{ mm}$                                |
| Minimum feed amount                         | $s = 0.01 \text{ mm/pulse}$                          |
| Service life time                           | $20000 \text{ h}$                                    |
| Driving motor                               | AC servo motor                                       |
|   | Rated rotational speed: $3,000 \text{ min}^{-1}$     |
| Inertial moment of the motor                | $J_m = 5 \times 10^{-6} \text{ kg} \cdot \text{m}^2$ |
| Reduction gear                              | None (direct coupling)                               |
| Frictional coefficient of the guide surface | $\mu = 0.003$ (rolling)                              |
| Guide surface resistance                    | $f = 20 \text{ N}$ (without load)                    |



### [Selection Items]

Screw shaft diameter  
 Lead  
 Nut model No.  
 Accuracy  
 Axial clearance  
 Screw shaft support method  
 Driving motor

### [Selecting Lead Angle Accuracy and Axial Clearance]

#### ● Selecting the Lead Angle Accuracy

To achieve positioning accuracy of  $\pm 0.7$  mm/600 mm:

$$\frac{\pm 0.7}{600} = \frac{\pm 0.35}{300}$$

The lead angle accuracy must be  $\pm 0.35$ mm/300 mm or higher.

Therefore, the accuracy grade of the Ball Screw (see Table 1 on [B15-20](#)) needs to be C10 (travel distance error:  $\pm 0.21$  mm/300 mm).

Accuracy grade C10 is available for low priced, Rolled Ball Screws. Assume that a Rolled Ball Screw is selected.

#### ● Selecting the Axial Clearance

The required backlashes is 0.1 mm or less. However, since an axial load is constantly applied in a single direction with vertical mount, the axial load does not serve as a backlash no matter how large it is.

Therefore, a low price, rolled Ball Screw is selected since there will not be a problem in axial clearance.

### [Selecting a Screw Shaft]

#### ● Assuming the Screw Shaft Length

Assume the overall nut length to be 100 mm and the screw shaft end length to be 100 mm.

Therefore, the overall length is determined as follows based on the stroke length of 600mm.

$$600 + 200 = 800 \text{ mm}$$

Thus, the screw shaft length is assumed to be 800 mm.

#### ● Selecting the Lead

With the driving motor's rated rotational speed being  $3,000 \text{ min}^{-1}$  and the maximum speed 0.3 m/s, the Ball Screw lead is obtained as follows:

$$\frac{0.3 \times 60 \times 1000}{3000} = 6 \text{ mm}$$

Therefore, it is necessary to select a type with a lead of 6mm or longer.

In addition, the Ball Screw and the motor can be mounted in direct coupling without using a reduction gear. The minimum resolution per revolution of an AC servomotor is obtained based on the resolution of the encoder (1,000 p/rev; 1,500 p/rev) provided as a standard accessory for the AC servomotor, as indicated below.

1000 p/rev(without multiplication)

1500 p/rev(without multiplication)

2000 p/rev(doubled)

3000 p/rev(doubled)

4000 p/rev(quadrupled)

6000 p/rev(quadrupled)



## Point of Selection

### Examples of Selecting a Ball Screw

To meet the minimum feed amount of 0.010 mm/pulse, which is the selection requirement, the following should apply.

|      |       |   |            |
|------|-------|---|------------|
| Lead | 6 mm  | — | 3000 p/rev |
|      | 8 mm  | — | 4000 p/rev |
|      | 10 mm | — | 1000 p/rev |
|      | 20 mm | — | 2000 p/rev |
|      | 40 mm | — | 2000 p/rev |

However, with the lead being 6 mm or 8 mm, the feed distance is 0.002 mm/pulse, and the starting pulse of the controller that issues commands to the motor driver needs to be at least 150 kpps, and the cost of the controller may be higher.

In addition, if the lead of the Ball Screw is greater, the torque required for the motor is also greater, and thus the cost will be higher.

Therefore, select 10 mm for the Ball Screw lead.

#### ● Selecting the Screw Shaft Diameter

Those Ball Screw models that meet the lead being 10 mm as described in Section [Selecting Lead Angle Accuracy and Axial Clearance] on **B15-84** and Section [Selecting a Screw Shaft] on **B15-84** (see Table20 on **B15-35**) are as follows.

| Shaft diameter | Lead    |
|----------------|---------|
| 15 mm          | — 10 mm |
| 20 mm          | — 10 mm |
| 25 mm          | — 10 mm |

Accordingly, the combination of a screw shaft diameter of 15 mm and a lead 10 mm is selected.

#### ● Selecting the Screw Shaft Support Method

Since the assumed Ball Screw has a stroke length of 600 mm and operates at a maximum speed of 0.3 m/s (Ball Screw rotational speed: 1,800 min<sup>-1</sup>), select the fixed-supported configuration for the screw shaft support.

## ● Studying the Permissible Axial Load

### ■ Calculating the Maximum Axial Load

|                          |                         |
|--------------------------|-------------------------|
| Guide surface resistance | $f=20$ N (without load) |
| Table Mass               | $m_1=40$ kg             |
| Work Mass                | $m_2=10$ kg             |
| Maximum speed            | $V_{\max}=0.3$ m/s      |
| Acceleration time        | $t_1=0.2$ s             |

Accordingly, the required values are obtained as follows.

Acceleration

$$\alpha = \frac{V_{\max}}{t_1} = 1.5 \text{ m/s}^2$$

During upward acceleration:

$$Fa_1 = (m_1 + m_2) \cdot g + f + (m_1 + m_2) \cdot \alpha = 585 \text{ N}$$

During upward uniform motion:

$$Fa_2 = (m_1 + m_2) \cdot g + f = 510 \text{ N}$$

During upward deceleration:

$$Fa_3 = (m_1 + m_2) \cdot g + f - (m_1 + m_2) \cdot \alpha = 435 \text{ N}$$

During downward acceleration:

$$Fa_4 = (m_1 + m_2) \cdot g - f - (m_1 + m_2) \cdot \alpha = 395 \text{ N}$$

During downward uniform motion:

$$Fa_5 = (m_1 + m_2) \cdot g - f = 470 \text{ N}$$

During downward deceleration:

$$Fa_6 = (m_1 + m_2) \cdot g - f + (m_1 + m_2) \cdot \alpha = 545 \text{ N}$$

Thus, the maximum axial load applied on the Ball Screw is as follows:

$$Fa_{\max} = Fa_1 = 585 \text{ N}$$

### ■ Buckling Load of the Screw Shaft

Factor according to the mounting method

$\eta_2=20$  (see [B15-38](#))

Since the mounting method for the section between the nut and the bearing, where buckling is to be considered, is "fixed-fixed: "

Distance between two mounting surfaces

$\ell_a=700$  mm (estimate)

Screw-shaft thread minor diameter

$d_1=12.5$  mm

$$P_1 = \eta_2 \cdot \frac{d_1^4}{\ell_a^2} \times 10^4 = 20 \times \frac{12.5^4}{700^2} \times 10^4 = 9960 \text{ N}$$

### ■ Permissible Compressive and Tensile Load of the Screw Shaft

$$P_2 = 116d_1^2 = 116 \times 12.5^2 = 18100 \text{ N}$$

Thus, the buckling load and the permissible compressive and tensile load of the screw shaft are at least equal to the maximum axial load. Therefore, a Ball Screw that meets these requirements can be used without a problem.

- Studying the Permissible Rotational Speed

- Maximum Rotational Speed

- Screw shaft diameter: 15 mm; lead: 10 mm

Maximum speed

$$V_{\max}=0.3 \text{ m/s}$$

Lead

$$Ph=10 \text{ mm}$$

$$N_{\max} = \frac{V_{\max} \times 60 \times 10^3}{Ph} = 1800 \text{ min}^{-1}$$

- Permissible Rotational Speed Determined by the Dangerous Speed of the Screw Shaft

Factor according to the mounting method

$$\lambda_{z2}=15.1 \text{ (see B15-40)}$$

Since the mounting method for the section between the nut and the bearing, where dangerous speed is to be considered, is "fixed-supported: "

Distance between two mounting surfaces

$$\ell_b=700 \text{ mm (estimate)}$$

- Screw shaft diameter: 15 mm; lead: 10 mm

Screw-shaft thread minor diameter

$$d_1=12.5 \text{ mm}$$

$$N_1 = \lambda_{z2} \times \frac{d_1}{\ell_b^2} \times 10^7 = 15.1 \times \frac{12.5}{700^2} \times 10^7 = 3852 \text{ min}^{-1}$$

- Permissible Rotational Speed Determined by the DN Value

- Screw shaft diameter: 15 mm; lead: 10 mm (large lead Ball Screw)

Ball center-to-center diameter

$$D=15.75 \text{ mm}$$

$$N_2 = \frac{70000}{D} = \frac{70000}{15.75} = 4444 \text{ min}^{-1}$$

Thus, the dangerous speed and the DN value of the screw shaft are met.

### [Selecting a Nut]

#### ● Selecting a Nut Model Number

The Rolled Ball Screw with a screw shaft diameter of 15 mm and a lead of 10 mm is the following large-lead Rolled Ball Screw model.

BLK1510-5.6

( $C_a=9.8$  kN,  $C_{0a}=25.2$  kN)

#### ● Studying the Permissible Axial Load

Assuming that an impact load is applied during an acceleration and a deceleration, set the static safety factor ( $f_s$ ) at 2 (see Table 1 on **B15-47**).

$$F_{a_{\max}} = \frac{C_{0a}}{f_s} = \frac{25.2}{2} = 12.6 \text{ kN} = 12600 \text{ N}$$

The obtained permissible axial load is greater than the maximum axial load of 585 N, and therefore, there will be no problem with this model.

#### ● Studying the Service Life

##### ■ Calculating the Travel Distance

Maximum speed  $V_{\max}=0.3$  m/s

Acceleration time  $t_1 = 0.2$  s

Deceleration time  $t_3 = 0.2$  s

- Travel distance during acceleration

$$\ell_{1,4} = \frac{V_{\max} \cdot t_1}{2} \times 10^3 = \frac{0.3 \times 0.2}{2} \times 10^3 = 30 \text{ mm}$$

- Travel distance during uniform motion

$$\ell_{2,5} = \ell_s - \frac{V_{\max} \cdot t_1 + V_{\max} \cdot t_3}{2} \times 10^3 = 600 - \frac{0.3 \times 0.2 + 0.3 \times 0.2}{2} \times 10^3 = 540 \text{ mm}$$

- Travel distance during deceleration

$$\ell_{3,6} = \frac{V_{\max} \cdot t_3}{2} \times 10^3 = \frac{0.3 \times 0.2}{2} \times 10^3 = 30 \text{ mm}$$

Based on the conditions above, the relationship between the applied axial load and the travel distance is shown in the table below.

| Motion                              | Applied axial load<br>$F_{a(N)}$ | Travel distance<br>$\ell_N(\text{mm})$ |
|-------------------------------------|----------------------------------|--|
| No1: During upward acceleration     | 585                              | 30                                     |
| No2: During upward uniform motion   | 510                              | 540                                    |
| No3: During upward deceleration     | 435                              | 30                                     |
| No4: During downward acceleration   | 395                              | 30                                     |
| No5: During downward uniform motion | 470                              | 540                                    |
| No6: During downward deceleration   | 545                              | 30                                     |

\* The subscript (N) indicates a motion number.

### ■Average Axial Load

$$F_{am} = \sqrt[3]{\frac{1}{2 \times l_s} (F_{a1}^3 \cdot l_1 + F_{a2}^3 \cdot l_2 + F_{a3}^3 \cdot l_3 + F_{a4}^3 \cdot l_4 + F_{a5}^3 \cdot l_5 + F_{a6}^3 \cdot l_6)} = 492 \text{ N}$$

### ■Nominal Life

Dynamic load rating  
Load factor  
Average load  
Nominal life

$C_a = 9800 \text{ N}$   
 $f_w = 1.5$  (see Table 2 on **B15-48**)  
 $F_{am} = 492 \text{ N}$   
 $L_{10}$  (rev)

$$L_{10m} = \left( \alpha \times \frac{C_a}{F_{am}} \right)^3 \times 10^6 = \left( \frac{9800}{1.5 \times 492} \right)^3 \times 10^6 = 2.34 \times 10^9 \text{ rev}$$

$$\alpha = \frac{1}{f_w}$$

### ■Average Revolutions per Minute

Number of reciprocations per minute  
Stroke  
Lead

$n = 5 \text{ min}^{-1}$   
 $l_s = 600 \text{ mm}$   
 $Ph = 10 \text{ mm}$

$$N_m = \frac{2 \times n \times l_s}{Ph} = \frac{2 \times 5 \times 600}{10} = 600 \text{ min}^{-1}$$

### ■Calculating the Service Life Time on the Basis of the Nominal Life

Nominal life  
Average revolutions per minute

$L_{10m} = 2.34 \times 10^9 \text{ rev}$   
 $N_m = 600 \text{ min}^{-1}$

$$L_h = \frac{L_{10m}}{60 \cdot N_m} = \frac{2.34 \times 10^9}{60 \times 600} = 65000 \text{ h}$$

### ■Calculating the Service Life in Travel Distance on the Basis of the Nominal Life

Nominal life  
Lead

$L_{10m} = 2.34 \times 10^9 \text{ rev}$   
 $Ph = 10 \text{ mm}$

$$L_s = L_{10m} \times Ph \times 10^{-6} = 23400 \text{ km}$$

With all the conditions stated above, model BLK1510-5.6 satisfies the desired service life time of 20,000 hours.

### [Studying the Rigidity]

Since the conditions for selection do not include rigidity and this element is not particularly necessary, it is not described here.

### [Studying the Positioning Accuracy]

#### ● Studying the Lead Angle Accuracy

Accuracy grade C10 was selected in Section [Selecting Lead Angle Accuracy and Axial Clearance] on **B15-84**.

C10 (travel distance error:  $\pm 0.21$  mm/300 mm)

#### ● Studying the Axial Clearance

Since the axial load is constantly present in a given direction only because of vertical mount, there is no need to study the axial clearance.

#### ● Studying the Axial Rigidity

Since the lead angle accuracy is achieved beyond the required positioning accuracy, there is no need to study the positioning accuracy determined by axial rigidity.

#### ● Studying the Thermal Displacement through Heat Generation

Since the lead angle accuracy is achieved beyond the required positioning accuracy, there is no need to study the positioning accuracy determined by the heat generation.

#### ● Studying the Orientation Change during Traveling

Since the lead angle accuracy is achieved at a much higher degree than the required positioning accuracy, there is no need to study the positioning accuracy.

### [Studying the Rotational Torque]

#### ● Frictional Torque Due to an External Load

During upward uniform motion:

$$T_1 = \frac{F_{a2} \cdot Ph}{2 \times \pi \times \eta} = \frac{510 \times 10}{2 \times \pi \times 0.9} = 900 \text{ N}\cdot\text{mm}$$

During downward uniform motion:

$$T_2 = \frac{F_{a5} \cdot Ph}{2 \times \pi \times \eta} = \frac{470 \times 10}{2 \times \pi \times 0.9} = 830 \text{ N}\cdot\text{mm}$$

#### ● Torque Due to a Preload on the Ball Screw

The Ball Screw is not provided with a preload.

### ● Torque Required for Acceleration

Inertial Moment:

Since the inertial moment per unit length of the screw shaft is  $3.9 \times 10^{-4} \text{ kg}\cdot\text{cm}^2/\text{mm}$  (see the specification table), the inertial moment of the screw shaft with an overall length of 800mm is obtained as follows.

$$J_s = 3.9 \times 10^{-4} \times 800 = 0.31 \text{ kg}\cdot\text{cm}^2 \\ = 0.31 \times 10^{-4} \text{ kg}\cdot\text{m}^2$$

$$J = (m_1 + m_2) \left( \frac{Ph}{2 \times \pi} \right)^2 \cdot A^2 \times 10^{-6} + J_s \cdot A^2 = (40 + 10) \left( \frac{10}{2 \times \pi} \right)^2 \times 1^2 \times 10^{-6} + 0.31 \times 10^{-4} \times 1^2 \\ = 1.58 \times 10^{-4} \text{ kg}\cdot\text{m}^2$$

Angular acceleration:

$$\omega' = \frac{2\pi \cdot N_{\text{max}}}{60 \cdot t} = \frac{2\pi \times 1800}{60 \times 0.2} = 942 \text{ rad/s}^2$$

Based on the above, the torque required for acceleration is obtained as follows.

$$T_3 = (J + J_m) \cdot \omega' = (1.58 \times 10^{-4} + 5 \times 10^{-5}) \times 942 = 0.2 \text{ N}\cdot\text{m} = 200 \text{ N}\cdot\text{mm}$$

Therefore, the required torque is specified as follows.

During upward acceleration:

$$T_{k1} = T_1 + T_3 = 900 + 200 = 1100 \text{ N}\cdot\text{mm}$$

During upward uniform motion:

$$T_{t1} = T_1 = 900 \text{ N}\cdot\text{mm}$$

During upward deceleration:

$$T_{g1} = T_1 - T_3 = 900 - 200 = 700 \text{ N}\cdot\text{mm}$$

During downward acceleration:

$$T_{k2} = 630 \text{ N}\cdot\text{mm}$$

During downward uniform motion:

$$T_{t2} = 830 \text{ N}\cdot\text{mm}$$

During downward deceleration:

$$T_{g2} = 1030 \text{ N}\cdot\text{mm}$$

### [Studying the Driving Motor]

#### ● Rotational Speed

Since the Ball Screw lead is selected based on the rated rotational speed of the motor, it is unnecessary to study the rotational speed of the motor.

Maximum working rotational speed :  $1800 \text{ min}^{-1}$

Rated rotational speed of the motor:  $3000 \text{ min}^{-1}$

#### ● Minimum Feed Amount

As with the rotational speed, the Ball Screw lead is selected based on the encoder normally used for an AC servomotor. Therefore, it is unnecessary to study this factor.

Encoder resolution:  $1000 \text{ p/rev}$ .

#### ● Motor Torque

The torque during acceleration calculated in Section [Studying the Rotational Torque] on **B15-90** is the required maximum torque.

$$T_{\max} = T_{k1} = 1100 \text{ N}\cdot\text{mm}$$

Therefore, the maximum peak torque of the AC servomotor needs to be at least  $1100 \text{ N}\cdot\text{mm}$ .

#### ● Effective Torque Value

The selection requirements and the torque calculated in Section [Studying the Rotational Torque] on **B15-90** can be expressed as follows.

During upward acceleration:

$$T_{k1} = 1100 \text{ N}\cdot\text{mm}$$

$$t_1 = 0.2 \text{ s}$$

During upward uniform motion:

$$T_{t1} = 900 \text{ N}\cdot\text{mm}$$

$$t_2 = 1.8 \text{ s}$$

During upward deceleration:

$$T_{g1} = 700 \text{ N}\cdot\text{mm}$$

$$t_3 = 0.2 \text{ s}$$

During downward acceleration:

$$T_{k2} = 630 \text{ N}\cdot\text{mm}$$

$$t_1 = 0.2 \text{ s}$$

During downward uniform motion:

$$T_{t2} = 830 \text{ N}\cdot\text{mm}$$

$$t_2 = 1.8 \text{ s}$$

During downward deceleration:

$$T_{g2} = 1030 \text{ N}\cdot\text{mm}$$

$$t_3 = 0.2 \text{ s}$$

When stationary( $m_2=0$ ):

$$T_s = 658 \text{ N}\cdot\text{mm}$$

$$t_4 = 7.6 \text{ s}$$



## Point of Selection

### Examples of Selecting a Ball Screw

The effective torque is obtained as follows, and the rated torque of the motor must be 743 N·mm or greater.

$$\begin{aligned}
 T_{\text{rms}} &= \sqrt{\frac{T_{k1}^2 \cdot t_1 + T_{t1}^2 \cdot t_2 + T_{g1}^2 \cdot t_3 + T_{k2}^2 \cdot t_1 + T_{t2}^2 \cdot t_2 + T_{g2}^2 \cdot t_3 + T_s^2 \cdot t_4}{t_1 + t_2 + t_3 + t_1 + t_2 + t_3 + t_4}} \\
 &= \sqrt{\frac{1100^2 \times 0.2 + 900^2 \times 1.8 + 700^2 \times 0.2 + 630^2 \times 0.2 + 830^2 \times 1.8 + 1030^2 \times 0.2 + 658^2 \times 7.6}{0.2 + 1.8 + 0.2 + 0.2 + 1.8 + 0.2 + 7.6}} \\
 &= 743 \text{ N}\cdot\text{mm}
 \end{aligned}$$

#### ● Inertial Moment

The inertial moment applied to the motor equals to the inertial moment calculated in Section [Studying the Rotational Torque] on **B15-90**.

$$J = 1.58 \times 10^{-4} \text{ kg}\cdot\text{m}^2$$

Normally, the motor needs to have an inertial moment at least one tenth of the inertial moment applied to the motor, although the specific value varies depending on the motor manufacturer.

Therefore, the inertial moment of the AC servomotor must be  $1.58 \times 10^{-5} \text{ kg}\cdot\text{m}^2$  or greater.

The selection has been completed.







# Ball Screw Options

## Contaminaton Protection



If foreign material enters the interior of the ball screw, abnormal levels of abrasion and ball clogging are more likely to occur. This can also shorten the overall lifespan of the product.

As such, foreign material needs to be prevented from entering. If there is a chance that foreign material may get in, it is important to choose an effective contamination protection product that suits the usage conditions.

|   |  |
|---|--|
| <p>Labyrinth seal<br/>(Precision Ball Screw)<br/>(Rolled Ball Screw Model JPF)<br/>Symbol: RR</p> |  <p style="text-align: right;"><b>▲15-336</b></p>   |
| <p>Brush seal<br/>(Rolled Ball Screw)<br/>Symbol: ZZ</p>  |  <p style="text-align: right;"><b>▲15-336</b></p>   |
| <p>Wiper ring<br/>Symbol: WW</p>  |  <p style="text-align: right;"><b>▲15-337~</b></p> |
| <p>Thin film seal<br/>(SDA-V, SDA-VZ, SDAN-V only)<br/>Symbol: TT</p>                             |   |

## Options

## Lubrication

|   |   |
|---|---|
| <p>Canvas seal<br/>(SDA-V, SDAN-V, HBN-V only)<br/>Symbol: CC</p> |  <p style="text-align: right;"><b>A15-339~</b></p> |
| <p>Dust cover<br/>Bellows<br/>Screw cover</p>                     |  <p style="text-align: right;"><b>A15-341</b></p>  |


Ball Screw (Options)

## Lubrication

To maximize the performance of the Ball Screw, it is necessary to select a lubricant and a lubrication method according to the conditions.

For types of lubricants, characteristics of lubricants and lubrication methods, see the section on “Accessories for Lubrication” on **A24-2**.

Also, QZ Lubricator is available as an optional accessory that significantly increases the maintenance interval.



## Corrosion Resistance (Surface Treatment, etc.)

Depending on the service environment, the Ball Screw requires corrosion resistance treatment or a different material. For details of corrosion resistance treatment and material change, contact THK. (see **B0-18**)

## Contamination Protection Seal for Ball Screws


If the Ball Screw is used in an atmosphere free from foreign material but with suspended dust, a labyrinth seal (with symbol RR) and a brush seal (with symbol ZZ) can be used as contamination protection accessories.

The labyrinth seal is designed to maintain a slight clearance between the seal and the screw shaft raceway so that torque does not develop and no heat is generated, though its effect in contamination protection is limited.

With Ball Screws except the large lead and super lead types, there is no difference in nut dimensions between those with and without a seal.

### Labyrinth seal


Symbol: RR (Precision Ball Screw)  
(Rolled Ball Screw Model JPF)



Labyrinth seal

### Brush seal

Symbol: ZZ (Rolled Ball Screw)




Brush seal

# Wiper Ring W

● For the supported models and the ball screw nut dimension with Wiper ring W attached, see [A15-344](#) to [A15-352](#).

With the wiper ring W, special resin with high wear resistance and low dust generation removes foreign material and prevents foreign material from entering the ball screw nut while elastically contacting the circumference of the ball screw shaft and the screw thread.




## [Features]

- A total of eight slits on the circumference remove foreign materials in succession, and prevent entrance of foreign material.
- Contacts the ball screw shaft to reduce the flowing out of grease.
- Contacts the ball screw shaft at a constant pressure level using a spring, thus to minimize the heat generation.
- Since the material is highly resistant to the wear and the chemicals, its performance will not easily be deteriorated even if it is used over a long period.

Can be attached together with QZ Lubricator.

For the applicable models and the ball screw nut dimensions after wiper ring W is attached, see [A15-344](#).



## Model number coding

**BIF2505V-5 QZ WW G0 +1000L C5**

With QZ  
Lubricator

With wiper ring W


(\*) See [A15-344](#).

## ● Test in an environment exposed to contaminated environment

[Test conditions]



| Item                                 | Description   |
|--------------------------------------|---|
| Model No.                            | BIF3210V-5G0+1500LC5  |
| Maximum rotational speed             | 1000 min <sup>-1</sup>  |
| Maximum speed                        | 10 m/min  |
| Maximum circumferential speed        | 1.8 m/s   |
| Time constant                        | 60 ms   |
| Dowel                                | 1 s   |
| Stroke                               | 900 mm  |
| Load (through internal load)         | 1.31 kN   |
| Grease                               | THK AFG Grease 8 cm <sup>3</sup><br>(Initial lubrication to the ball screw nut only.) |
| Foundry dust                         | FCD400 average particle diameter: 250 μm  |
| Volume of foreign material per shaft | 5 g/h   |

[Test result]



- Type with wiper ring  
Slight flaking occurred in the ball screw shaft at travel distant of 1,000 km.
- Type with labyrinth seal  
Flaking occurred throughout the circumference of the screw shaft raceway at travel distance of 200 km.  
Flaking occurred on the balls after traveling 1,500 km.

Change in the ball after traveling 2000 km



- Type with wiper ring  
Wear of balls at a travel distance of 2,000 km: 1.4 μm.
- Type with labyrinth seal  
Starts to be worn rapidly after 500 km, and the ball wear amount at the travel distance of 2,000 km: 11 μm.




### ● Heat Generation Test

[Test conditions]

| Item                          | Description   |
|-------------------------------|---|
| Model No.                     | BLK3232-3.6G0+1426LC5   |
| Maximum rotational speed      | 1000 min <sup>-1</sup>  |
| Maximum speed                 | 32 m/min  |
| Maximum circumferential speed | 1.7 m/s   |
| Time constant                 | 100 ms  |
| Stroke                        | 1000 mm   |
| Load (through internal load)  | 0.98 kN   |
| Grease                        | THK AFG Grease 5 cm <sup>3</sup><br>(contained in the ball screw nut) |

[Test result]





| Item                        | With wiper ring | Without seal |
|-----------------------------|-----------------|--------------|
| Heat generation temperature | 37.1            | 34.5         |
| Temperature rise            | 12.2            | 8.9          |

## Canvas seal CC

● See [A15-353](#) for compatible models and ball screw nut dimensions after canvas seal installation.

Canvas seals are made from resin with high slidability and superior wear resistance. They prevent foreign material from entering the nut through elastic contact with the outer diameter of the ball screw shaft and the groove.



[Features]

- The seal is in contact with the ball screw shaft, so it prevents the intrusion of foreign material and reduces the discharge of grease.
- The rubber base and high slidability resin used on the part that slides along the shaft minimizes heat generation despite the seal coming in contact with the shaft.

Model number coding

SDA2505V-3 CC G0 +1000L C5


With canvas seal

## ● Foreign material test

[Test conditions]

| Item                         | Description   |
|------------------------------|---|
| Test pieces                  | Precision Ball Screw $\phi 40$                                      |
| Maximum rotational speed     | 100 min <sup>-1</sup>   |
| Maximum speed                | 3 m/min   |
| Stroke                       | 800 mm  |
| Load (through internal load) | 2.25 kN   |
| Grease                       | THK AFJ Grease 12 cm <sup>3</sup> (contained in the ball screw nut) |
| Applied test material        | Steel powder and grease mixture<br>Powder-to-grease ratio = 1:2     |
| Test material amount         | 0.1 g   |
| Run time                     | 1 h   |

[Test result]




## ● Heat generation test

[Test conditions]

| Item                         | Description   |
|------------------------------|---|
| Test pieces                  | Precision Ball Screw $\phi 40$                                      |
| Maximum rotational speed     | 2500 min <sup>-1</sup>  |
| Maximum speed                | 75 m/min  |
| Stroke                       | 800 mm  |
| Load (through internal load) | 2.25 kN   |
| Grease                       | THK AFJ Grease 12 cm <sup>3</sup> (contained in the ball screw nut) |

[Test result]




| Item                        | With canvas seal | Without seal |
|-----------------------------|------------------|--------------|
| Heat generation temperature | 45.8             | 43.6         |
| Temperature rise            | 25.7             | 24.1         |

## ● Grease sealing test

[Test conditions]

| Item                         | Description   |
|------------------------------|---|
| Test pieces                  | Precision Ball Screw $\phi 40$                                      |
| Maximum rotational speed     | 100 min <sup>-1</sup>   |
| Maximum speed                | 3 m/min   |
| Stroke                       | 800 mm  |
| Load (through internal load) | 2.25 kN   |
| Grease                       | THK AFJ Grease 12 cm <sup>3</sup> (contained in the ball screw nut) |
| Run time                     | 1 h   |


[Test result]



# Dust Cover for Ball Screws

## Bellows/Screw cover

In the case of an environment with much dust and foreign material, be sure to prevent intrusion of foreign material by using bellows, a screw cover or the like. The contamination protection can be increased by also using a contamination protection seal. For details, contact THK. When conferring with us, please use the bellows specifications (**■15-356**).




# QZ Lubricator


● For the supported models and the ball screw nut dimension with QZ attached, see [A15-344](#) to [A15-352](#).

QZ Lubricator feeds a right amount of lubricant to the raceway of the ball screw shaft. This allows an oil film to be constantly formed between the balls and the raceway, improves lubricity and significantly extends the lubrication maintenance interval.

The structure of QZ Lubricator consists of three major components: (1) a heavily oil-impregnated fiber net (stores the lubricant), (2) a high-density fiber net (applies the lubricant to the raceway) and (3) an oil-control plate (adjusts the oil flow). The lubricant contained in the QZ Lubricator is fed by the capillary phenomenon, which is used also in felt pens and many other products.



Appearance Drawing



Structural Drawing

## [Features]

- Since it supplements an oil loss, the lubrication maintenance interval can be significantly extended.
- Since the right amount of lubricant is applied to the ball raceway, an environmentally friendly lubrication system that does not contaminate the surroundings is achieved.

Note) Some types of QZ have a vent hole. Be careful not to block the hole with grease or other obstructions.

## Model number coding

**BIF2505V-5 QZ WW G0 +1000L C5**


With QZ  
Lubricator

With wiper ring W

(\* See [A15-344](#).)

### ● Significantly extended maintenance interval

Since QZ Lubricator continuously feeds a lubricant over a long period, the maintenance interval can be significantly extended.




[Test conditions]

| Item                     | Description            |
|--------------------------|------------------------|
| Ball Screw               | BIF2510V               |
| Maximum rotational speed | 2500 min <sup>-1</sup> |
| Maximum speed            | 25 m/min               |
| Stroke                   | 500 mm                 |
| Load                     | Internal preload only  |

### ● Environmentally friendly lubrication system

Since QZ Lubricator feeds the right amount of lubricant directly to the raceway, the lubricant can effectively be used without waste.



**QZ Lubricator + THK AFA Grease**

**32 cm<sup>3</sup>**

(QZ Lubricator attached to both ends of the ball screw nut)



**Forced lubrication**

**0.25 cm<sup>3</sup>/3 min × 24 h × 125d**

**=15000 cm<sup>3</sup>**

Reduced to approx.  $\frac{1}{470}$

## Mounting Procedure


### Installing the Support Unit

- (1) Install the fixed side Support Unit with the screw shaft.
- (2) After inserting the fixed side Support Unit, secure the lock nut using the fastening set piece and the hexagonal socket-head setscrews.
- (3) Attach the supported side bearing to the screw shaft and secure the bearing using the snap ring, and then install the assembly to the housing on the supported side.

Note1) Do not disassemble the Support Unit.


Note2) When inserting the screw shaft to the Support Unit, take care not to let the oil seal lip turn outward.

Note3) When securing the set piece with a hexagonal socket-head setscrew, apply an adhesive to the hexagonal socket-head setscrew before tightening it in order to prevent the screw from loosening. If planning to use the product in a harsh environment, it is also necessary to take a measure to prevent other components/parts from loosening. Contact THK for details.




### Installation onto the Table and the Base

- (1) If using a bracket when mounting the ball screw nut to the table, insert the nut into the bracket and temporarily fasten it.
- (2) Temporarily fasten the fixed side Support Unit to the base. In doing so, press the table toward the fixed side Support Unit to align the axial center, and adjust the table so that it can travel freely.
  - If using the fixed side Support Unit as the reference point, secure a clearance between the ball screw nut and the table or inside the bracket when making adjustment.
  - If using the table as the reference point, make the adjustment either by using the shim (for a square type Support Unit), or securing the clearance between the outer surface of the nut and the inner surface of the mounting section (for a round type Support Unit).
- (3) Press the table toward the fixed-side Support Unit to align the axial center. Make the adjustment by reciprocating the table several times so that the nut travels smoothly throughout the whole stroke, and temporarily secure the Support Unit to the base.




## Checking the Accuracy and Fully Fastening the Support Unit

While checking the runout of the ball screw shaft end and the axial clearance using a dial gauge, fully fasten the ball screw nut, the nut bracket, the fixed side Support Unit and the supported-side Support Unit, in this order.



## Connection with the Motor

- (1) Mount the motor bracket to the base.
- (2) Connect the motor and the ball screw using a coupling.  
Note) Make sure the mounting accuracy is maintained.
- (3) Thoroughly perform the break-in for the system.



# Maintenance Method

## Amount of Lubricant

If the amount of the lubricant to the Ball Screw is insufficient, it may cause a lubrication breakdown, and if it is excessive, it may generate heat and increase resistance. It is necessary to select an amount that meets the conditions.

### [Grease]

The feed amount of grease is generally approximately one third of the spatial volume inside the nut. For details on feed amount of grease, contact THK.

### [Oil]

Table 1 shows a guideline for the feed amount of oil.

Note, that the amount varies according to the stroke, the oil type and the conditions (e.g., suppressed heat generation).

Table1 Guideline for the Feed Amount of Oil  
(Interval: 3 minutes)

| Shaft diameter (mm) | Amount of lubricant (cc) |
|---------------------|--------------------------|
| 4 to 8              | 0.03                     |
| 10 to 14            | 0.05                     |
| 15 to 18            | 0.07                     |
| 20 to 25            | 0.1                      |
| 28 to 32            | 0.15                     |
| 36 to 40            | 0.25                     |
| 45 to 50            | 0.3                      |
| 55 to 63            | 0.4                      |
| 70 to 100           | 0.5                      |



## Model Number Coding

The model number configuration for ball screws differs depending on the type. Table 2 Refer to the corresponding configuration example shown in Table 4.

THK can also provide shaft end shapes matched to support units. These can also be denoted in the symbols, which should be used for this purpose.

### [Precision ball screw types and sample model number configurations]

Table 2

|                   | Model No.   |                    | Shaft end shape                         | Model number coding |
|-------------------|---|--------------------|---|---------------------|
| Precision         | SBN-V, SBK, SDAN-V, SDA-V, HBN-V/HBN-K/HBN-KA/HBN, SBKH, BIF-V, BNFN-V/BNFN, MDK, MBF, BNF-V/BNF, DIK, DKN, BLW, DK, WHF, BLK, WGF, BNT |                    | Fixed Side : H, J<br>Supported Side : K | [1]                 |
|                   | Unfinished Shaft Ends A   | MBF, MDK, BNF, BIF |   | [2]                 |
|                   | Unfinished Shaft Ends B   | BNF, BIF           | Y                                       | [3]                 |
|                   | Finished Shaft Ends   | BNK                |   | [4]                 |
|                   | Rotary Ball Screw   | BLR, DIR           | Fixed Side : H, J<br>Supported Side : K | [5]                 |
| Ball Screw/Spline | BNS-V, BNS-A, BNS, NS-V, NS-A, NS   | —                  | [6]                                     |                     |

### [Rolled ball screw types and sample model number configurations]

Table 3

|        | Model No.   |                                     | Shaft end shape                         | Model number coding |
|--------|---|-------------------------------------|---|---------------------|
| Rolled | Ball screw nut and screw shaft combination products | JPF, BTK-V, MTF, BLK, WTF, CNF, BNT | Fixed Side : H, J<br>Supported Side : K | [6]                 |
|        | Rotary Ball Screw                                   | BLR                                 |   | [7]                 |
|        | Standalone screw shafts                             | TS                                  |   | [8]                 |
|        | Standalone ball screw nuts                          | BTK-V, BLK, WTF, CNF, BNT, BLR      | —                                       |                     |


### [Support unit, nut bracket and lock nut types and sample model number configurations]

Table 4

|                      | Model No.              |  | Shaft end shape | Model number coding |
|----------------------|------------------------|--|-----------------|---------------------|
| Support Unit         | EK, BK, FK, EF, BF, FF |  | —               | [9]                 |
| Nut brackets for BNK | MC                     |  | —               |                     |
| Lock Nut             | RN                     |  | —               |                     |

### [1 Precision Ball Screw]

- Models SBN-V, SBK, SDAN-V, SDA-V, HBN-V/HBN-K/HBN-KA/HBN, SBKH, BIF-V, BNFN-V/BNFN, MDK, MBF, BNF-V/BNF, DIK, DKN, BLW, DK, WHF, BLK, WGF and BNT



(\*1) See **A15-322** to **A15-327**.  
(\*2) (\*3) (\*4) See **B15-96**, **B15-97**.

Note) The ball nut flange faces the fixed side unless otherwise specified.  
If desiring the flange to face the supported side, add symbol G in the end of the Ball Screw model number when placing an order.

### [2 Precision Ball Screw Unfinished Shaft Ends]

- Models BIF, MDK, MBF and BNF

**BIF2505-5RRG0+720LC5A**

Unfinished shaft ends code (A or B)

## [3 Precision Ball Screw Finished Shaft Ends]

- Model BNK

**BNK2010-2.5RRG2+699LC7Y**

Finished shaft ends code

Refer to **■15-140** for the corresponding model number.

## [4 Rotary Ball Screw]

- Models BLR and DIR

**BLR2020-3.6 K UU G1 +1000L C5**

Model No.

Flange orientation  
symbol

Symbol for clearance  
in the axial direction

Symbol for  
support bearing seal

Overall screw shaft  
length (in mm)

Accuracy symbol

## [5 Ball Screw/Spline]

- Models BNS-V, BNS-A, BNS, NS-V, NS-A, and NS

**BNS2525 +600L C5**

Model No.


Overall shaft length  
(in mm)

Accuracy symbol

### [6 Rolled Ball Screw]

#### ● Models BTK-V, MTF, BLK, WTF, CNF and BNT (Rolled)

- Combination of the Ball Screw Nut and the Screw Shaft




Note) The ball nut flange faces the fixed side unless otherwise specified.

If desiring the flange to face the supported side, add symbol G at the end of the ball screw model number when placing an order.

### [6 Rolled Ball Screw]


#### ● Model JPF

- Rolled Ball Screw model JPF



### [7 Rolled Rotary Ball Screw]

#### ● Model BLR (Rolled)



Note) For clearance in the axial direction, see [B15-27](#).

### [8 Standalone rolled shafts/nuts]

- Models BTK-V, BLK/WTF, CNF, BNT(Rolled), BLR(Rolled) and TS

Rolled shaft only

Nut only

|           |                                       |                 |                                       |   |                     |  |
|-----------|---------------------------------------|-----------------|---------------------------------------|---|---------------------|--|
| <b>TS</b> | <b>14</b>                             | <b>05</b>       | <b>+500L</b>                          | <b>C7</b>   | <b>BTK1405V-2.6</b> | <b>ZZ</b>  |
|           |                                       | Lead<br>(in mm) |                                       | Accuracy symbol<br>(see page <a href="#">15-12</a> )<br>(no symbol for class C10) | Model No.           | Seal symbol<br>no symbol: without seal<br>ZZ: brush seal attached to<br>both ends of the ball screw nut<br>(see <a href="#">15-334</a> ) |
|           | Screw shaft outer<br>diameter (in mm) |                 | Overall screw shaft length<br>(in mm) |   |                     |  |

Symbol for rolled ball screw shaft

### [9 Support units, nut brackets and lock nuts]

- Models EK, BK, FK, EF, BF, FF, MC and RN

**EK12**

Model No.

### [10 Ball screw options, W wiper rings and QZ lubricators]

**BIF2505V-5 QZ WW G0 +1000L C5**

With QZ  
Lubricator

With wiper ring W

(\*) See [15-344](#).

## Notes on Ordering

### [Options]

The details of the product options differ according to the model number. Check before ordering. See [15-95](#).

### [Other notes on specifications]

Contact THK separately for information on the specifications below.

- Shaft end shape (for recommended shaft end shapes, indicate the symbol).
- Surface Treatment (see [10-20](#))
- Grease used
- Nipple mounting

## Precautions on Use

## Ball Screw

### [Handling]

- (1) Please use at least two people to move any product weighing 20 kg or more, or use a dolly or another conveyance. Doing so may cause injury or damage.
- (2) Do not disassemble the parts. This will result in loss of functionality.
- (3) Tilting the Ball Screw shaft and the Ball Screw nut may cause them to fall by their own weight.
- (4) Take care not to drop or strike the Ball Screw. Failure to do so could cause injury or product damage. Giving an impact to it could also cause damage to its function even if the product looks intact.
- (5) When assembling, do not remove the Ball Screw nut from the Ball Screw shaft.
- (6) When handling the product, wear protective gloves, safety shoes, etc., as necessary to ensure safety.

### [Precautions on Use]

- (1) Prevent foreign material, such as cutting chips or coolant, from entering the product. Failure to do so may cause damage.
- (2) If the product is used in an environment where cutting chips, coolant, corrosive solvents, water, etc., may enter the product, use bellows, covers, etc., to prevent them from entering the product.
- (3) Do not use the product at temperature of 80°C or higher. Except for the heat-resistant models, exposure to higher temperatures may cause the resin/rubber parts to deform/be damaged.
- (4) If foreign material such as cutting chips adheres to the product, replenish the lubricant after cleaning the product.
- (5) Micro-oscillation makes it difficult for oil film to form on the raceway in contact with the rolling element, and may lead to fretting. Accordingly, use grease offering excellent fretting toughness. It is also recommended that the Ball Screw nut be turned once or so on a regular basis to make sure oil film is formed between the raceway and rolling element.
- (6) When using the return-pipe or return-piece type ball screw in a horizontal orientation, there is a difference in torque on the outbound and inbound cycle depending on the mounting orientation of the circulation part (return pipe or return piece). To use the product with a consistent torque, we recommend designing the product with the mounting orientation of the circulation part facing downwards.
- (7) Do not use undue force when fitting parts (pin, key, etc.) to the product. This may generate pressure marks on the raceway, leading to loss of functionality.
- (8) If an offset or skewing occurs with the Ball Screw shaft support and the Ball Screw nut, it may substantially shorten the service life. Pay much attention to components to be mounted and to the mounting accuracy.
- (9) If any of the rolling elements falls from the Ball Screw nut, contact THK instead of using the product.
- (10) When using this product with a vertical orientation, take preventive measures such as adding a safety mechanism to prevent falls. The own weight of the Ball Screw nut may cause it to fall.
- (11) Do not use this product beyond its permissible rotational speed. Doing so may cause accidents or component damage. Be sure to use the product within the specification range designated by THK.
- (12) Do not cause the Ball Screw nut to overshoot. The ball may drop, circulating parts may be damaged, raceway in contact with the ball may develop pressure marks, etc., resulting in malfunction. Continuing to use the product in this condition may lead to premature wear or damage to circulating parts.

## Precautions on Use

- (13) Use the Ball Screw by providing a LM Guide, Ball Spline or other guide element. Otherwise, the Ball Screw may be damaged.
- (14) Insufficient rigidity or accuracy of mounting members causes the bearing load to concentrate on one point and the bearing performance will drop significantly. Accordingly, give sufficient consideration to the rigidity/accuracy of the housing and base and strength of the fixing bolts.

### [Lubrication]

- (1) Thoroughly wipe off anti-rust oil and feed lubricant before using the product.
- (2) Do not mix different lubricants. Mixing greases using the same type of thickening agent may still cause adverse interaction between the two greases if they use different additives, etc.
- (3) When using the product in locations exposed to constant vibrations or in special environments such as clean rooms, vacuum and low/high temperature, use the grease appropriate for the specification/environment.
- (4) When lubricating a product having no grease nipple or lubrication hole, apply grease directly on the raceway and stroke the product several times to let the grease spread inside.
- (5) The consistency of grease changes according to the temperature. Take note that the torque of the Ball Screw also changes as the consistency of grease changes.
- (6) After lubrication, the rotational torque of the Ball Screw may increase due to the agitation resistance of grease. Be sure to perform a break-in to let the grease spread fully, before operating the machine.
- (7) Excess grease may scatter immediately after lubrication, so wipe off scattered grease as necessary.
- (8) The properties of grease deteriorate and its lubrication performance drops over time, so grease must be checked and added properly according to the use frequency of the machine.
- (9) Although the lubrication interval may vary according to operating conditions and the service environment, lubrication should be performed approximately every 100 km in travel distance (three to six months). Set the final lubrication interval/amount based on the actual machine.
- (10) Depending on the mounting orientation and access position, lubricant may not spread fully and poor lubrication may occur. Give full consideration to these factors in the design stage.
- (11) When using a Ball Screw, it is necessary to provide effective lubrication. Using the product without lubrication may increase wear of the rolling elements or shorten the service life. Table1 (B15-108) shows a guideline for the feed amount of oil.

### [Storage]

When storing the Ball Screw, enclose it in a package designated by THK and store it in a room in a horizontal orientation while avoiding high temperature, low temperature and high humidity. After the product has been in storage for an extended period of time, lubricant inside may have deteriorated, so add new lubricant before use.

### [Disposal]

Dispose of the product properly as industrial waste.

# Precautions on Using Options for the Ball Screw

## QZ Lubricator for the Ball Screw

---

For details regarding the QZ Lubricator, see **B15-104**.

### [Precaution on Selection]

Make sure the stroke length exceeds the total length of the screw shaft with the QZ Lubricator attached.

### [Handling]

Take care not to drop or strike the product, which could result in injury or damage.

Keep air holes clear of grease or other obstructions.

The QZ Lubricator supplies oil only to the raceway, so use it in combination with regular greasing/oil lubrication.

In models equipped with the QZ Lubricator, raceways are provided with the minimum required level of lubrication. Please note: Use of the product in a vertical position, or other usage conditions, may cause lubricant to drip from the ball screw shaft.

### [Service environment]

Be sure the service temperature of this product is between  $-10$  to  $50^{\circ}\text{C}$ , and do not clean the product by immersing it in an organic solvent or white kerosene, or leave it unpacked.